

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332083-940

Luminaire Tested: **S123DIP-S1165D1195U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332083-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8220.3 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	95	91	87	91	88	84	82	75	73	71	63	62	60	53	51	50	45				45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38				38
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33				33
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32	28				28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25				25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22				22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19				19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17				17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16				16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15569	15569	15569	15569
5°	18567	15637	13857	15637
10°	23240	15557	12516	15557
15°	28505	15432	11652	15432
20°	33956	15237	11094	15237
25°	36056	14998	10969	14998
30°	30904	14825	11028	14825
35°	21494	14578	11143	14578
40°	16190	14289	11108	14289
45°	13443	13857	10966	13857
50°	12042	12980	10868	12980
55°	11258	12033	10732	12033
60°	10559	11044	10622	11044
65°	9926	10068	10282	10068
70°	9309	8954	9791	8954
75°	8339	7839	8979	7839
80°	7296	6428	7736	6428
85°	5718	4668	5199	4668



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.5	1.7
10°-20°	456.9	5.6
20°-30°	766.8	9.3
30°-40°	868.3	10.6
40°-50°	778.6	9.5
50°-60°	628.3	7.6
60°-70°	437.9	5.3
70°-80°	230.1	2.8
80°-90°	60.3	0.7
90°-100°	284.8	3.5
100°-110°	806.5	9.8
110°-120°	793.4	9.7
120°-130°	632.8	7.7
130°-140°	498.9	6.1
140°-150°	372.4	4.5
150°-160°	259.6	3.2
160°-170°	152.5	1.9
170°-180°	49.6	0.6
0°-30°	1366.2	16.6
0°-40°	2234.5	27.2
0°-60°	3641.5	44.3
0°-90°	4369.7	53.2
90°-120°	1884.7	22.9
90°-150°	3388.9	41.2
90°-180°	3851.0	46.8
0°-180°	8220.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1446	1446	1446	1446	1446	
5°	1718	1447	1282	1447	1718	178
15°	2558	1385	1046	1385	2558	739
25°	3036	1263	924	1263	3036	1331
35°	1636	1109	848	1109	1636	1063
45°	883	910	720	910	883	699
55°	600	641	572	641	600	538
65°	390	395	404	395	390	388
75°	200	188	216	188	200	215
85°	46	38	42	38	46	55
90°	30	2	30	2	30	18
95°	120	35	120	35	120	217
105°	1318	120	1318	120	1318	1300
115°	1603	212	1603	212	1603	1557
125°	1264	295	1264	295	1264	1145
135°	1025	346	1025	346	1025	795
145°	801	395	801	395	801	509
155°	664	449	664	449	664	310
165°	579	490	579	490	579	166
175°	521	511	521	511	521	51
180°	512	512	512	512	512	



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1535.1	1533.9	1531.2	1533.4	1528.9	1522.7	1522.2	1516.5	1500.3	1499.1	1494.7
5°	1718.4	1712.8	1712.1	1711.4	1701.6	1688.3	1663.0	1660.9	1627.3	1610.4	1590.2
7.5°	1955.8	1958.7	1948.6	1939.6	1909.6	1889.8	1862.8	1828.2	1786.8	1744.9	1717.0
10°	2126.3	2149.4	2120.7	2101.0	2082.9	2048.4	2008.6	1958.7	1909.0	1850.8	1806.7
12.5°	2309.1	2320.4	2314.6	2296.2	2267.8	2215.5	2144.7	2090.0	2044.2	1947.3	1908.2
15°	2558.0	2600.8	2573.4	2510.3	2511.7	2461.9	2369.5	2267.8	2213.9	2129.0	2013.5
17.5°	2823.2	2828.5	2816.8	2764.3	2729.3	2660.9	2575.5	2478.1	2368.7	2266.2	2143.5
20°	2964.4	2960.2	2935.7	2908.4	2848.1	2794.9	2701.6	2593.0	2452.8	2352.0	2218.0
22.5°	3043.0	3035.9	3024.3	3001.4	2951.3	2894.0	2810.4	2691.7	2558.2	2419.2	2264.6
25°	3035.9	3045.0	3046.4	3040.1	3022.6	2988.3	2922.4	2827.8	2694.7	2516.0	2354.7
27.5°	2761.2	2774.1	2811.6	2844.7	2881.9	2919.7	2914.6	2867.7	2769.2	2614.9	2417.8
30°	2486.4	2458.4	2527.8	2615.5	2675.0	2780.1	2839.0	2842.5	2787.1	2654.7	2462.6
32.5°	2105.2	2136.1	2166.8	2274.6	2404.8	2522.8	2640.0	2734.3	2745.1	2656.9	2489.0
35°	1635.7	1674.3	1730.3	1786.4	1926.5	2047.1	2253.1	2432.5	2575.5	2594.4	2491.4
37.5°	1318.1	1337.1	1372.6	1428.8	1520.5	1663.5	1822.8	2049.6	2256.7	2410.8	2417.5
40°	1152.2	1157.7	1197.7	1240.5	1314.7	1432.4	1576.1	1776.6	2024.6	2239.8	2329.5
42.5°	1027.7	1040.0	1056.9	1098.1	1157.2	1245.8	1379.4	1545.0	1772.4	2020.0	2195.5
45°	883.1	897.1	907.6	934.9	977.0	1036.5	1129.7	1281.1	1454.2	1709.9	1946.2
47.5°	787.5	788.5	796.4	817.0	845.6	890.3	956.2	1053.5	1212.4	1419.9	1662.3
50°	719.1	730.2	733.1	749.1	771.6	804.5	859.2	941.9	1072.3	1254.5	1477.3
52.5°	670.8	674.2	682.1	693.7	713.3	739.0	786.3	851.0	953.4	1108.7	1313.6
55°	599.9	599.9	607.6	616.7	627.9	651.0	682.6	730.2	808.1	928.5	1098.1
57.5°	534.3	537.8	543.2	546.1	555.6	570.9	597.3	633.4	691.4	784.2	919.1
60°	490.5	496.9	496.1	501.8	510.2	522.1	544.6	574.0	625.8	700.1	813.7
62.5°	452.5	452.0	451.9	458.6	467.0	478.4	492.9	518.4	562.5	628.4	725.1
65°	389.7	388.3	393.2	397.3	400.2	408.6	419.8	442.2	471.6	520.7	595.7
67.5°	333.9	329.8	332.4	333.9	338.7	345.2	355.7	369.6	393.0	432.4	488.9
70°	295.8	292.2	291.5	292.9	297.1	302.0	309.8	323.1	344.8	376.3	417.7
72.5°	256.5	254.1	254.0	257.1	259.0	262.3	267.7	279.9	297.1	320.8	359.4
75°	200.5	200.5	200.5	201.2	203.2	206.1	210.3	216.5	229.9	246.6	272.6
77.5°	150.3	150.1	149.3	149.1	152.2	153.5	154.4	160.3	167.7	179.1	198.0
80°	117.7	114.2	115.7	117.7	119.1	119.8	122.0	123.3	129.7	136.0	149.3
82.5°	87.5	84.5	84.8	88.0	88.3	89.0	91.1	93.1	95.4	101.2	108.3
85°	46.3	46.3	47.0	47.0	47.6	47.0	49.0	49.8	49.8	53.2	57.4
87.5°	22.8	21.9	22.3	22.6	22.3	22.4	22.7	23.1	23.5	24.3	24.2
90°	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9	24.9	25.9	22.8
92.5°	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2	120.2	159.3	175.3
95°	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0	498.3	614.4	547.1
97.5°	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7	1018.6	952.1	697.1
100°	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5	1185.3	981.1	663.1
102.5°	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5	1193.5	927.3	613.3
105°	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8	1130.3	832.9	552.2
107.5°	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2	1019.7	749.7	513.3
110°	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3	950.0	702.4	498.3



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2	889.6	670.9	490.1
115°	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1	816.4	637.1	487.0
117.5°	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1	772.2	617.2	488.8
120°	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1	749.0	608.1	492.1
122.5°	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4	730.0	602.4	497.9
125°	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7	705.5	594.7	506.6
127.5°	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0	684.0	590.9	516.6
130°	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6	672.3	588.4	523.2
132.5°	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9	661.6	587.6	528.2
135°	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9	647.6	586.4	535.7
137.5°	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4	635.3	584.1	540.6
140°	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5	627.9	583.3	543.9
142.5°	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5	621.2	581.7	546.4
145°	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4	612.3	579.2	548.0
147.5°	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6	603.6	575.2	548.0
150°	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6	597.8	571.9	548.0
152.5°	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5	591.2	567.8	545.5
155°	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8	581.2	560.5	542.9
157.5°	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3	570.0	554.1	539.4
160°	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0	562.6	549.1	537.7
162.5°	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1	555.1	544.1	534.4
165°	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2	544.9	536.6	529.4
167.5°	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1	535.2	529.2	524.4
170°	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6	529.4	524.2	521.1
172.5°	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0	523.6	520.0	518.6
175°	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1	517.0	514.9	514.9
177.5°	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4	512.6	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1491.3	1486.8	1482.4	1474.5	1467.8	1458.2	1455.5	1452.1	1442.0	1433.1	1426.3
5°	1582.4	1565.6	1541.1	1518.7	1500.5	1476.0	1461.9	1447.2	1426.1	1407.2	1391.8
7.5°	1677.8	1644.7	1606.5	1565.3	1527.0	1490.0	1460.1	1433.4	1404.0	1376.1	1354.4
10°	1753.5	1705.8	1652.5	1595.1	1546.0	1498.3	1458.4	1423.3	1385.5	1352.5	1325.3
12.5°	1839.8	1769.2	1695.7	1625.9	1567.9	1501.7	1453.3	1408.8	1365.9	1326.2	1295.6
15°	1942.0	1852.3	1765.3	1669.4	1581.0	1498.3	1440.9	1384.8	1335.1	1294.4	1255.2
17.5°	2035.1	1933.4	1818.9	1702.1	1595.6	1497.5	1417.0	1353.7	1291.5	1241.7	1202.6
20°	2087.8	1972.1	1842.5	1721.2	1603.5	1494.2	1405.9	1330.2	1262.8	1210.3	1166.2
22.5°	2133.2	1997.9	1863.8	1734.1	1602.9	1485.1	1385.1	1307.2	1234.3	1182.9	1135.9
25°	2180.2	2018.4	1883.8	1731.7	1585.3	1463.3	1351.2	1262.8	1190.0	1129.7	1081.4
27.5°	2220.6	2017.0	1857.3	1693.7	1557.5	1435.3	1315.5	1220.8	1143.4	1078.0	1028.9
30°	2247.5	2019.7	1829.8	1667.9	1530.6	1404.4	1288.1	1192.8	1111.5	1044.9	998.6
32.5°	2264.3	2018.0	1804.6	1632.1	1488.0	1376.4	1258.4	1159.7	1076.2	1010.8	966.2
35°	2274.1	2005.7	1761.1	1557.9	1419.2	1310.5	1211.7	1109.4	1021.8	960.8	910.3
37.5°	2254.5	1979.8	1710.7	1486.4	1334.5	1227.5	1144.4	1057.2	973.4	906.3	862.8
40°	2223.7	1963.0	1671.4	1436.0	1276.2	1173.1	1102.4	1016.9	934.2	870.4	829.7
42.5°	2164.8	1928.8	1628.3	1379.9	1215.7	1112.6	1047.4	976.0	897.8	837.9	797.3
45°	2021.2	1854.3	1563.5	1295.8	1126.2	1019.7	962.2	910.3	839.5	781.4	746.4
47.5°	1821.9	1742.4	1469.9	1207.1	1032.9	930.4	870.7	828.9	777.2	730.2	696.6
50°	1683.4	1650.4	1406.5	1146.6	970.6	870.4	813.0	775.1	738.0	691.0	660.1
52.5°	1523.6	1543.9	1332.6	1083.7	907.3	808.8	754.7	724.6	690.9	652.3	625.4
55°	1298.6	1372.2	1204.7	978.3	813.0	719.1	667.9	641.2	621.6	592.9	569.8
57.5°	1088.0	1181.6	1066.5	869.7	720.3	639.3	590.2	561.2	548.6	533.6	515.4
60°	963.0	1055.4	967.9	796.8	658.1	580.9	537.5	513.0	500.3	489.9	474.5
62.5°	851.3	944.9	871.4	722.8	596.9	525.5	487.6	463.7	453.9	448.4	435.2
65°	698.0	778.6	729.5	607.6	509.5	446.4	412.1	395.3	386.1	384.1	375.7
67.5°	568.1	629.5	593.7	504.0	426.8	372.3	343.1	328.9	321.8	321.1	314.8
70°	482.9	540.3	513.0	431.7	365.2	322.4	297.1	284.5	280.4	279.6	276.2
72.5°	416.7	456.8	435.1	367.2	315.8	277.0	258.4	245.3	240.5	241.5	239.2
75°	308.4	338.5	325.9	278.9	237.6	212.3	196.9	188.5	184.3	186.5	183.6
77.5°	221.9	240.9	229.6	197.1	171.6	153.4	142.0	136.8	133.0	132.9	131.6
80°	167.5	178.7	172.4	152.8	131.8	116.4	107.2	103.7	101.7	100.9	100.2
82.5°	119.3	128.9	121.4	107.9	93.6	84.4	79.2	74.5	73.0	73.5	72.8
85°	60.3	63.8	61.0	52.5	47.0	42.7	39.9	37.8	36.5	37.2	35.8
87.5°	24.7	24.6	22.3	19.6	18.1	15.8	15.4	13.9	13.2	13.6	13.6
90°	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1	4.1	6.2	9.4
92.5°	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8	19.1	27.7	35.8
95°	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2	38.3	49.8	67.3
97.5°	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1	61.1	70.0	85.3
100°	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7	77.7	85.0	99.4
102.5°	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1	95.9	102.4	116.0
105°	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2	123.3	129.5	142.0
107.5°	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9	151.1	157.0	169.2
110°	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8	170.9	176.1	187.5



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1	189.2	194.4	205.7
115°	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4	216.5	222.7	233.1
117.5°	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7	243.4	248.6	258.2
120°	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9	260.0	265.2	275.6
122.5°	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7	275.8	281.0	292.1
125°	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2	297.4	303.5	315.0
127.5°	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5	315.6	323.2	334.8
130°	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2	326.4	335.6	348.1
132.5°	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5	335.5	345.6	360.5
135°	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1	350.2	361.6	377.1
137.5°	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7	364.1	375.2	391.8
140°	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8	374.0	384.3	400.9
142.5°	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8	383.2	394.3	409.2
145°	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8	397.8	407.2	422.7
147.5°	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9	412.8	421.9	435.3
150°	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7	422.7	431.0	444.4
152.5°	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5	432.7	441.0	452.7
155°	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6	448.6	454.9	465.2
157.5°	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5	462.3	467.3	476.4
160°	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4	471.4	475.5	483.8
162.5°	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8	478.8	482.1	488.8
165°	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1	489.0	491.1	496.2
167.5°	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6	497.3	498.3	502.3
170°	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5	501.4	502.5	505.6
172.5°	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8	505.6	505.8	508.1
175°	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8	509.7	508.7	510.8
177.5°	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6	511.8	511.0	511.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1422.4	1418.4	1412.8	1404.4	1397.7	1387.1	1387.1	1388.8	1388.8	1388.2	1387.1
5°	1379.2	1368.7	1356.1	1341.4	1326.0	1310.5	1307.7	1302.1	1297.9	1295.1	1291.6
7.5°	1333.6	1315.0	1296.6	1276.0	1257.2	1241.7	1230.9	1221.9	1216.2	1210.1	1205.5
10°	1302.8	1279.7	1257.9	1236.3	1212.4	1193.5	1181.6	1173.1	1166.9	1161.3	1158.4
12.5°	1266.4	1239.9	1215.9	1195.3	1169.2	1149.8	1138.4	1134.4	1127.0	1115.3	1109.1
15°	1213.1	1188.6	1159.8	1128.3	1115.7	1091.9	1078.5	1072.3	1068.0	1058.9	1056.1
17.5°	1167.5	1135.4	1103.2	1079.7	1056.2	1036.9	1029.5	1021.6	1016.0	1008.6	1006.4
20°	1131.1	1102.4	1072.9	1047.8	1023.1	1002.2	995.9	990.2	984.6	981.1	978.3
22.5°	1094.1	1065.4	1041.0	1017.4	991.2	977.5	970.6	964.5	960.6	958.1	955.4
25°	1042.1	1016.9	989.5	968.5	947.5	938.3	934.2	930.7	927.9	924.3	923.6
27.5°	995.6	968.1	945.9	926.3	911.2	903.7	899.6	897.9	898.5	899.7	900.5
30°	960.8	935.6	917.4	900.5	886.5	879.5	878.8	878.8	881.6	882.3	883.7
32.5°	928.9	908.1	889.9	873.6	863.0	858.2	860.9	860.9	863.1	865.0	867.5
35°	882.3	864.1	850.1	836.1	827.0	829.0	830.5	831.9	835.4	839.5	842.4
37.5°	837.9	822.1	807.4	796.6	792.4	796.1	799.5	802.5	806.5	809.8	812.5
40°	805.9	794.0	780.0	770.2	771.6	773.7	776.5	780.0	783.5	785.6	788.5
42.5°	776.2	763.8	753.1	744.9	746.9	749.6	751.3	753.1	757.2	761.0	762.6
45°	730.9	721.1	711.3	706.4	707.8	709.3	710.6	712.7	716.2	719.1	719.7
47.5°	680.1	673.2	666.6	661.8	664.1	663.5	665.4	669.9	670.9	672.6	676.5
50°	647.6	641.2	633.6	632.1	632.1	632.1	632.8	638.5	638.5	641.2	644.1
52.5°	611.7	607.6	602.7	600.2	599.1	599.1	602.0	604.8	605.9	609.8	612.7
55°	558.6	554.4	550.1	548.0	546.6	548.0	553.7	555.0	558.6	560.6	562.8
57.5°	503.2	500.0	496.6	495.4	495.2	497.0	500.1	504.3	505.2	511.6	514.8
60°	466.7	461.8	459.1	459.1	457.6	464.0	462.5	469.6	470.9	475.2	480.1
62.5°	429.2	422.6	421.5	421.5	423.5	425.3	427.2	430.3	433.9	439.3	443.1
65°	368.6	365.2	370.1	369.3	367.9	372.1	372.1	375.7	379.9	384.8	392.4
67.5°	311.3	309.5	309.9	309.9	312.0	314.4	316.4	319.4	324.5	329.7	334.7
70°	272.6	274.7	271.3	274.0	276.2	276.8	278.2	282.4	288.0	291.5	297.1
72.5°	235.1	234.9	235.3	236.5	238.5	239.8	241.2	246.0	252.2	255.1	259.6
75°	180.8	180.1	182.2	182.2	185.7	187.1	188.5	190.6	196.3	200.5	203.9
77.5°	132.1	132.9	132.4	134.8	133.8	134.1	138.5	140.6	141.2	149.5	151.2
80°	99.5	100.9	101.7	102.3	103.0	101.7	106.6	108.6	108.6	113.5	117.0
82.5°	71.5	72.3	74.2	74.8	75.0	76.4	76.8	78.4	80.1	82.1	86.8
85°	35.8	37.8	38.5	37.8	38.5	37.2	39.2	39.9	40.7	40.7	40.7
87.5°	13.5	14.4	14.5	15.7	15.8	16.9	16.8	15.9	16.1	17.9	16.1
90°	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9	26.9	28.0	30.1
92.5°	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2	69.2	61.1	55.7
95°	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0	252.8	197.9	160.6
97.5°	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7	744.7	611.1	487.1
100°	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5	1137.6	1016.4	869.2
102.5°	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5	1315.7	1245.1	1151.8
105°	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8	1450.5	1470.2	1443.2
107.5°	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2	1433.4	1524.2	1561.1
110°	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3	1378.0	1508.5	1581.0



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2	1305.0	1451.3	1544.5
115°	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1	1188.3	1340.6	1453.6
117.5°	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1	1089.7	1226.5	1341.0
120°	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1	1035.0	1159.3	1264.0
122.5°	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4	991.0	1106.3	1203.5
125°	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7	936.6	1036.0	1118.9
127.5°	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0	888.7	978.4	1053.8
130°	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6	858.9	942.8	1013.3
132.5°	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9	830.7	908.8	976.0
135°	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9	790.5	857.8	916.9
137.5°	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4	751.7	809.8	860.9
140°	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5	729.3	779.1	823.7
142.5°	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5	707.8	750.9	789.7
145°	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4	679.7	712.8	742.8
147.5°	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6	658.7	685.5	706.8
150°	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6	645.4	667.2	686.9
152.5°	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5	633.0	652.3	668.7
155°	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8	615.4	631.0	643.4
157.5°	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3	598.2	610.2	619.9
160°	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0	587.5	597.8	605.0
162.5°	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1	575.9	585.3	591.7
165°	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2	559.5	566.7	571.9
167.5°	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1	546.8	551.0	554.7
170°	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6	537.7	541.8	543.9
172.5°	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0	530.2	533.6	534.8
175°	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1	520.0	522.2	522.2
177.5°	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4	514.2	515.1	515.1
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1383.1	1382.6	1386.5	1383.7	1386.5	1382.6	1383.1	1387.1	1388.2	1388.8	1388.8
5°	1287.4	1289.5	1282.5	1282.5	1282.5	1289.5	1287.4	1291.6	1295.1	1297.9	1302.1
7.5°	1202.2	1199.1	1199.4	1195.6	1199.4	1199.1	1202.2	1205.5	1210.1	1216.2	1221.9
10°	1150.0	1145.8	1144.4	1145.1	1144.4	1145.8	1150.0	1158.4	1161.3	1166.9	1173.1
12.5°	1106.9	1106.0	1096.8	1096.9	1096.8	1106.0	1106.9	1109.1	1115.3	1127.0	1134.4
15°	1056.1	1042.9	1041.4	1045.6	1041.4	1042.9	1056.1	1056.1	1058.9	1068.0	1072.3
17.5°	1005.2	998.3	998.6	996.6	998.6	998.3	1005.2	1006.4	1008.6	1016.0	1021.6
20°	978.3	974.1	973.4	968.5	973.4	974.1	978.3	978.3	981.1	984.6	990.2
22.5°	953.7	952.3	952.7	947.3	952.7	952.3	953.7	955.4	958.1	960.6	964.5
25°	923.0	926.5	923.6	923.6	923.6	926.5	923.0	923.6	924.3	927.9	930.7
27.5°	902.2	902.1	900.7	900.7	900.7	902.1	902.2	900.5	899.7	898.5	897.9
30°	886.5	885.8	887.3	887.3	887.3	885.8	886.5	883.7	882.3	881.6	878.8
32.5°	870.8	871.8	872.1	872.6	872.1	871.8	870.8	867.5	865.0	863.1	860.9
35°	846.6	847.3	849.4	848.0	849.4	847.3	846.6	842.4	839.5	835.4	831.9
37.5°	813.8	817.0	816.3	817.4	816.3	817.0	813.8	812.5	809.8	806.5	802.5
40°	789.1	791.2	790.5	790.5	790.5	791.2	789.1	788.5	785.6	783.5	780.0
42.5°	763.9	765.4	763.6	762.5	763.6	765.4	763.9	762.6	761.0	757.2	753.1
45°	722.6	721.1	723.3	720.4	723.3	721.1	722.6	719.7	719.1	716.2	712.7
47.5°	676.3	677.7	678.2	680.4	678.2	677.7	676.3	676.5	672.6	670.9	669.9
50°	645.4	649.6	649.6	649.0	649.6	649.6	645.4	644.1	641.2	638.5	638.5
52.5°	615.2	617.2	619.9	619.8	619.9	617.2	615.2	612.7	609.8	605.9	604.8
55°	568.4	569.8	571.1	571.9	571.1	569.8	568.4	562.8	560.6	558.6	555.0
57.5°	519.9	519.3	522.6	523.6	522.6	519.3	519.9	514.8	511.6	505.2	504.3
60°	485.6	485.6	491.2	493.4	491.2	485.6	485.6	480.1	475.2	470.9	469.6
62.5°	449.2	451.5	457.1	454.1	457.1	451.5	449.2	443.1	439.3	433.9	430.3
65°	395.9	401.5	400.8	403.7	400.8	401.5	395.9	392.4	384.8	379.9	375.7
67.5°	340.3	343.8	348.8	349.3	348.8	343.8	340.3	334.7	329.7	324.5	319.4
70°	302.7	306.2	309.1	311.1	309.1	306.2	302.7	297.1	291.5	288.0	282.4
72.5°	266.4	268.1	274.8	271.9	274.8	268.1	266.4	259.6	255.1	252.2	246.0
75°	208.8	213.7	217.9	215.9	217.9	213.7	208.8	203.9	200.5	196.3	190.6
77.5°	154.4	159.3	161.3	159.5	161.3	159.3	154.4	151.2	149.5	141.2	140.6
80°	122.0	121.3	125.5	124.8	125.5	121.3	122.0	117.0	113.5	108.6	108.6
82.5°	89.4	88.7	90.7	91.1	90.7	88.7	89.4	86.8	82.1	80.1	78.4
85°	43.4	45.6	42.7	42.1	42.7	45.6	43.4	40.7	40.7	40.7	39.9
87.5°	15.9	16.1	15.8	15.0	15.8	16.1	15.9	16.1	17.9	16.1	15.9
90°	29.0	30.1	31.1	30.1	31.1	30.1	29.0	30.1	28.0	26.9	25.9
92.5°	53.9	50.7	51.8	49.9	51.8	50.7	53.9	55.7	61.1	69.2	87.2
95°	140.9	131.6	124.3	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0
97.5°	410.7	364.1	336.1	327.2	336.1	364.1	410.7	487.1	611.1	744.7	929.7
100°	764.6	688.9	648.5	649.6	648.5	688.9	764.6	869.2	1016.4	1137.6	1221.5
102.5°	1070.4	1010.6	976.8	953.0	976.8	1010.6	1070.4	1151.8	1245.1	1315.7	1318.5
105°	1395.5	1356.2	1323.0	1317.9	1323.0	1356.2	1395.5	1443.2	1470.2	1450.5	1346.8
107.5°	1561.9	1548.6	1537.5	1527.9	1537.5	1548.6	1561.9	1561.1	1524.2	1433.4	1265.2
110°	1610.0	1618.3	1616.2	1614.2	1616.2	1618.3	1610.0	1581.0	1508.5	1378.0	1187.3



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1597.6	1623.3	1631.1	1631.6	1631.1	1623.3	1597.6	1544.5	1451.3	1305.0	1110.2
115°	1531.2	1576.8	1597.6	1602.8	1597.6	1576.8	1531.2	1453.6	1340.6	1188.3	1008.1
117.5°	1422.1	1474.3	1504.1	1511.2	1504.1	1474.3	1422.1	1341.0	1226.5	1089.7	934.1
120°	1345.8	1403.8	1428.7	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1
122.5°	1276.2	1328.4	1355.8	1363.6	1355.8	1328.4	1276.2	1203.5	1106.3	991.0	864.4
125°	1185.3	1230.8	1256.7	1264.0	1256.7	1230.8	1185.3	1118.9	1036.0	936.6	823.7
127.5°	1112.9	1151.8	1175.3	1181.9	1175.3	1151.8	1112.9	1053.8	978.4	888.7	788.0
130°	1068.2	1105.5	1127.2	1135.5	1127.2	1105.5	1068.2	1013.3	942.8	858.9	765.6
132.5°	1027.5	1064.8	1084.1	1089.9	1084.1	1064.8	1027.5	976.0	908.8	830.7	744.9
135°	967.7	998.7	1017.4	1024.7	1017.4	998.7	967.7	916.9	857.8	790.5	716.9
137.5°	903.7	935.1	950.8	955.6	950.8	935.1	903.7	860.9	809.8	751.7	691.4
140°	863.0	892.1	908.6	907.6	908.6	892.1	863.0	823.7	779.1	729.3	676.5
142.5°	823.2	848.9	863.8	862.8	863.8	848.9	823.2	789.7	750.9	707.8	662.5
145°	768.7	790.5	798.8	800.8	798.8	790.5	768.7	742.8	712.8	679.7	645.4
147.5°	726.5	741.2	749.0	749.8	749.0	741.2	726.5	706.8	685.5	658.7	631.6
150°	702.4	713.8	720.1	720.1	720.1	713.8	702.4	686.9	667.2	645.4	621.6
152.5°	680.9	691.4	695.2	695.2	695.2	691.4	680.9	668.7	652.3	633.0	612.5
155°	652.7	661.0	663.1	664.1	663.1	661.0	652.7	643.4	631.0	615.4	598.8
157.5°	628.0	634.3	635.9	635.7	635.9	634.3	628.0	619.9	610.2	598.2	584.3
160°	612.3	618.5	618.5	617.5	618.5	618.5	612.3	605.0	597.8	587.5	576.0
162.5°	596.6	601.9	601.9	600.9	601.9	601.9	596.6	591.7	585.3	575.9	566.1
165°	576.0	580.1	579.2	579.2	579.2	580.1	576.0	571.9	566.7	559.5	553.2
167.5°	556.5	559.5	558.4	558.4	558.4	559.5	556.5	554.7	551.0	546.8	542.1
170°	544.9	547.1	546.0	546.0	546.0	547.1	544.9	543.9	541.8	537.7	534.6
172.5°	535.0	537.1	535.2	534.4	535.2	537.1	535.0	534.8	533.6	530.2	528.0
175°	522.2	523.2	522.2	521.1	522.2	523.2	522.2	522.2	522.2	520.0	519.1
177.5°	514.2	515.1	513.4	513.4	513.4	515.1	514.2	515.1	515.1	514.2	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1387.1	1387.1	1397.7	1404.4	1412.8	1418.4	1422.4	1426.3	1433.1	1442.0	1452.1
5°	1307.7	1310.5	1326.0	1341.4	1356.1	1368.7	1379.2	1391.8	1407.2	1426.1	1447.2
7.5°	1230.9	1241.7	1257.2	1276.0	1296.6	1315.0	1333.6	1354.4	1376.1	1404.0	1433.4
10°	1181.6	1193.5	1212.4	1236.3	1257.9	1279.7	1302.8	1325.3	1352.5	1385.5	1423.3
12.5°	1138.4	1149.8	1169.2	1195.3	1215.9	1239.9	1266.4	1295.6	1326.2	1365.9	1408.8
15°	1078.5	1091.9	1115.7	1128.3	1159.8	1188.6	1213.1	1255.2	1294.4	1335.1	1384.8
17.5°	1029.5	1036.9	1056.2	1079.7	1103.2	1135.4	1167.5	1202.6	1241.7	1291.5	1353.7
20°	995.9	1002.2	1023.1	1047.8	1072.9	1102.4	1131.1	1166.2	1210.3	1262.8	1330.2
22.5°	970.6	977.5	991.2	1017.4	1041.0	1065.4	1094.1	1135.9	1182.9	1234.3	1307.2
25°	934.2	938.3	947.5	968.5	989.5	1016.9	1042.1	1081.4	1129.7	1190.0	1262.8
27.5°	899.6	903.7	911.2	926.3	945.9	968.1	995.6	1028.9	1078.0	1143.4	1220.8
30°	878.8	879.5	886.5	900.5	917.4	935.6	960.8	998.6	1044.9	1111.5	1192.8
32.5°	860.9	858.2	863.0	873.6	889.9	908.1	928.9	966.2	1010.8	1076.2	1159.7
35°	830.5	829.0	827.0	836.1	850.1	864.1	882.3	910.3	960.8	1021.8	1109.4
37.5°	799.5	796.1	792.4	796.6	807.4	822.1	837.9	862.8	906.3	973.4	1057.2
40°	776.5	773.7	771.6	770.2	780.0	794.0	805.9	829.7	870.4	934.2	1016.9
42.5°	751.3	749.6	746.9	744.9	753.1	763.8	776.2	797.3	837.9	897.8	976.0
45°	710.6	709.3	707.8	706.4	711.3	721.1	730.9	746.4	781.4	839.5	910.3
47.5°	665.4	663.5	664.1	661.8	666.6	673.2	680.1	696.6	730.2	777.2	828.9
50°	632.8	632.1	632.1	632.1	633.6	641.2	647.6	660.1	691.0	738.0	775.1
52.5°	602.0	599.1	599.1	600.2	602.7	607.6	611.7	625.4	652.3	690.9	724.6
55°	553.7	548.0	546.6	548.0	550.1	554.4	558.6	569.8	592.9	621.6	641.2
57.5°	500.1	497.0	495.2	495.4	496.6	500.0	503.2	515.4	533.6	548.6	561.2
60°	462.5	464.0	457.6	459.1	459.1	461.8	466.7	474.5	489.9	500.3	513.0
62.5°	427.2	425.3	423.5	421.5	421.5	422.6	429.2	435.2	448.4	453.9	463.7
65°	372.1	372.1	367.9	369.3	370.1	365.2	368.6	375.7	384.1	386.1	395.3
67.5°	316.4	314.4	312.0	309.9	309.9	309.5	311.3	314.8	321.1	321.8	328.9
70°	278.2	276.8	276.2	274.0	271.3	274.7	272.6	276.2	279.6	280.4	284.5
72.5°	241.2	239.8	238.5	236.5	235.3	234.9	235.1	239.2	241.5	240.5	245.3
75°	188.5	187.1	185.7	182.2	182.2	180.1	180.8	183.6	186.5	184.3	188.5
77.5°	138.5	134.1	133.8	134.8	132.4	132.9	132.1	131.6	132.9	133.0	136.8
80°	106.6	101.7	103.0	102.3	101.7	100.9	99.5	100.2	100.9	101.7	103.7
82.5°	76.8	76.4	75.0	74.8	74.2	72.3	71.5	72.8	73.5	73.0	74.5
85°	39.2	37.2	38.5	37.8	38.5	37.8	35.8	35.8	37.2	36.5	37.8
87.5°	16.8	16.9	15.8	15.7	14.5	14.4	13.5	13.6	13.6	13.2	13.9
90°	24.9	25.9	22.8	19.7	16.6	13.5	11.4	9.4	6.2	4.1	2.1
92.5°	120.2	159.3	175.3	131.6	87.0	59.9	44.6	35.8	27.7	19.1	12.8
95°	498.3	614.4	547.1	377.1	222.7	134.6	94.3	67.3	49.8	38.3	35.2
97.5°	1018.6	952.1	697.1	413.8	239.8	155.6	111.9	85.3	70.0	61.1	60.1
100°	1185.3	981.1	663.1	390.6	237.3	164.7	124.3	99.4	85.0	77.7	76.7
102.5°	1193.5	927.3	613.3	370.7	240.6	175.5	138.4	116.0	102.4	95.9	94.1
105°	1130.3	832.9	552.2	356.4	249.7	193.8	161.6	142.0	129.5	123.3	120.2
107.5°	1019.7	749.7	513.3	355.3	266.7	217.6	187.7	169.2	157.0	151.1	147.9
110°	950.0	702.4	498.3	359.5	280.8	234.2	205.1	187.5	176.1	170.9	167.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	889.6	670.9	490.1	367.8	294.9	251.6	223.4	205.7	194.4	189.2	186.1
115°	816.4	637.1	487.0	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4
117.5°	772.2	617.2	488.8	399.0	342.7	303.8	277.9	258.2	248.6	243.4	238.7
120°	749.0	608.1	492.1	412.3	358.5	321.2	295.2	275.6	265.2	260.0	256.9
122.5°	730.0	602.4	497.9	424.8	375.1	338.6	311.0	292.1	281.0	275.8	272.7
125°	705.5	594.7	506.6	444.4	398.9	362.6	334.7	315.0	303.5	297.4	295.2
127.5°	684.0	590.9	516.6	460.7	419.5	384.6	356.6	334.8	323.2	315.6	312.5
130°	672.3	588.4	523.2	471.4	432.0	397.8	369.9	348.1	335.6	326.4	323.2
132.5°	661.6	587.6	528.2	481.3	442.8	409.5	382.3	360.5	345.6	335.5	331.5
135°	647.6	586.4	535.7	494.2	459.0	426.9	398.9	377.1	361.6	350.2	346.1
137.5°	635.3	584.1	540.6	503.7	470.1	439.3	413.4	391.8	375.2	364.1	359.7
140°	627.9	583.3	543.9	508.7	477.6	447.5	421.7	400.9	384.3	374.0	368.8
142.5°	621.2	581.7	546.4	513.6	483.4	454.2	430.0	409.2	394.3	383.2	378.8
145°	612.3	579.2	548.0	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.8
147.5°	603.6	575.2	548.0	522.4	497.3	472.6	452.4	435.3	421.9	412.8	410.9
150°	597.8	571.9	548.0	523.2	501.4	477.6	459.0	444.4	431.0	422.7	421.7
152.5°	591.2	567.8	545.5	524.9	503.9	483.4	465.6	452.7	441.0	432.7	432.5
155°	581.2	560.5	542.9	525.3	508.7	491.1	476.5	465.2	454.9	448.6	448.6
157.5°	570.0	554.1	539.4	526.3	511.4	497.3	486.1	476.4	467.3	462.3	461.5
160°	562.6	549.1	537.7	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4
162.5°	555.1	544.1	534.4	525.5	514.7	503.9	495.3	488.8	482.1	478.8	478.8
165°	544.9	536.6	529.4	523.2	515.9	507.7	500.4	496.2	491.1	489.0	490.1
167.5°	535.2	529.2	524.4	521.6	515.8	509.7	505.2	502.3	498.3	497.3	498.6
170°	529.4	524.2	521.1	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5
172.5°	523.6	520.0	518.6	518.3	514.9	510.6	509.3	508.1	505.8	505.6	506.8
175°	517.0	514.9	514.9	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8
177.5°	512.6	511.8	512.6	514.2	512.6	511.8	511.8	511.8	511.0	511.8	512.6
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1455.5	1458.2	1467.8	1474.5	1482.4	1486.8	1491.3	1494.7	1499.1	1500.3	1516.5
5°	1461.9	1476.0	1500.5	1518.7	1541.1	1565.6	1582.4	1590.2	1610.4	1627.3	1660.9
7.5°	1460.1	1490.0	1527.0	1565.3	1606.5	1644.7	1677.8	1717.0	1744.9	1786.8	1828.2
10°	1458.4	1498.3	1546.0	1595.1	1652.5	1705.8	1753.5	1806.7	1850.8	1909.0	1958.7
12.5°	1453.3	1501.7	1567.9	1625.9	1695.7	1769.2	1839.8	1908.2	1947.3	2044.2	2090.0
15°	1440.9	1498.3	1581.0	1669.4	1765.3	1852.3	1942.0	2013.5	2129.0	2213.9	2267.8
17.5°	1417.0	1497.5	1595.6	1702.1	1818.9	1933.4	2035.1	2143.5	2266.2	2368.7	2478.1
20°	1405.9	1494.2	1603.5	1721.2	1842.5	1972.1	2087.8	2218.0	2352.0	2452.8	2593.0
22.5°	1385.1	1485.1	1602.9	1734.1	1863.8	1997.9	2133.2	2264.6	2419.2	2558.2	2691.7
25°	1351.2	1463.3	1585.3	1731.7	1883.8	2018.4	2180.2	2354.7	2516.0	2694.7	2827.8
27.5°	1315.5	1435.3	1557.5	1693.7	1857.3	2017.0	2220.6	2417.8	2614.9	2769.2	2867.7
30°	1288.1	1404.4	1530.6	1667.9	1829.8	2019.7	2247.5	2462.6	2654.7	2787.1	2842.5
32.5°	1258.4	1376.4	1488.0	1632.1	1804.6	2018.0	2264.3	2489.0	2656.9	2745.1	2734.3
35°	1211.7	1310.5	1419.2	1557.9	1761.1	2005.7	2274.1	2491.4	2594.4	2575.5	2432.5
37.5°	1144.4	1227.5	1334.5	1486.4	1710.7	1979.8	2254.5	2417.5	2410.8	2256.7	2049.6
40°	1102.4	1173.1	1276.2	1436.0	1671.4	1963.0	2223.7	2329.5	2239.8	2024.6	1776.6
42.5°	1047.4	1112.6	1215.7	1379.9	1628.3	1928.8	2164.8	2195.5	2020.0	1772.4	1545.0
45°	962.2	1019.7	1126.2	1295.8	1563.5	1854.3	2021.2	1946.2	1709.9	1454.2	1281.1
47.5°	870.7	930.4	1032.9	1207.1	1469.9	1742.4	1821.9	1662.3	1419.9	1212.4	1053.5
50°	813.0	870.4	970.6	1146.6	1406.5	1650.4	1683.4	1477.3	1254.5	1072.3	941.9
52.5°	754.7	808.8	907.3	1083.7	1332.6	1543.9	1523.6	1313.6	1108.7	953.4	851.0
55°	667.9	719.1	813.0	978.3	1204.7	1372.2	1298.6	1098.1	928.5	808.1	730.2
57.5°	590.2	639.3	720.3	869.7	1066.5	1181.6	1088.0	919.1	784.2	691.4	633.4
60°	537.5	580.9	658.1	796.8	967.9	1055.4	963.0	813.7	700.1	625.8	574.0
62.5°	487.6	525.5	596.9	722.8	871.4	944.9	851.3	725.1	628.4	562.5	518.4
65°	412.1	446.4	509.5	607.6	729.5	778.6	698.0	595.7	520.7	471.6	442.2
67.5°	343.1	372.3	426.8	504.0	593.7	629.5	568.1	488.9	432.4	393.0	369.6
70°	297.1	322.4	365.2	431.7	513.0	540.3	482.9	417.7	376.3	344.8	323.1
72.5°	258.4	277.0	315.8	367.2	435.1	456.8	416.7	359.4	320.8	297.1	279.9
75°	196.9	212.3	237.6	278.9	325.9	338.5	308.4	272.6	246.6	229.9	216.5
77.5°	142.0	153.4	171.6	197.1	229.6	240.9	221.9	198.0	179.1	167.7	160.3
80°	107.2	116.4	131.8	152.8	172.4	178.7	167.5	149.3	136.0	129.7	123.3
82.5°	79.2	84.4	93.6	107.9	121.4	128.9	119.3	108.3	101.2	95.4	93.1
85°	39.9	42.7	47.0	52.5	61.0	63.8	60.3	57.4	53.2	49.8	49.8
87.5°	15.4	15.8	18.1	19.6	22.3	24.6	24.7	24.2	24.3	23.5	23.1
90°	4.1	6.2	9.4	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9
92.5°	19.1	27.7	35.8	44.6	59.9	87.0	131.6	175.3	159.3	120.2	87.2
95°	38.3	49.8	67.3	94.3	134.6	222.7	377.1	547.1	614.4	498.3	373.0
97.5°	61.1	70.0	85.3	111.9	155.6	239.8	413.8	697.1	952.1	1018.6	929.7
100°	77.7	85.0	99.4	124.3	164.7	237.3	390.6	663.1	981.1	1185.3	1221.5
102.5°	95.9	102.4	116.0	138.4	175.5	240.6	370.7	613.3	927.3	1193.5	1318.5
105°	123.3	129.5	142.0	161.6	193.8	249.7	356.4	552.2	832.9	1130.3	1346.8
107.5°	151.1	157.0	169.2	187.7	217.6	266.7	355.3	513.3	749.7	1019.7	1265.2
110°	170.9	176.1	187.5	205.1	234.2	280.8	359.5	498.3	702.4	950.0	1187.3



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	189.2	194.4	205.7	223.4	251.6	294.9	367.8	490.1	670.9	889.6	1110.2
115°	216.5	222.7	233.1	250.7	278.7	318.1	381.3	487.0	637.1	816.4	1008.1
117.5°	243.4	248.6	258.2	277.9	303.8	342.7	399.0	488.8	617.2	772.2	934.1
120°	260.0	265.2	275.6	295.2	321.2	358.5	412.3	492.1	608.1	749.0	895.1
122.5°	275.8	281.0	292.1	311.0	338.6	375.1	424.8	497.9	602.4	730.0	864.4
125°	297.4	303.5	315.0	334.7	362.6	398.9	444.4	506.6	594.7	705.5	823.7
127.5°	315.6	323.2	334.8	356.6	384.6	419.5	460.7	516.6	590.9	684.0	788.0
130°	326.4	335.6	348.1	369.9	397.8	432.0	471.4	523.2	588.4	672.3	765.6
132.5°	335.5	345.6	360.5	382.3	409.5	442.8	481.3	528.2	587.6	661.6	744.9
135°	350.2	361.6	377.1	398.9	426.9	459.0	494.2	535.7	586.4	647.6	716.9
137.5°	364.1	375.2	391.8	413.4	439.3	470.1	503.7	540.6	584.1	635.3	691.4
140°	374.0	384.3	400.9	421.7	447.5	477.6	508.7	543.9	583.3	627.9	676.5
142.5°	383.2	394.3	409.2	430.0	454.2	483.4	513.6	546.4	581.7	621.2	662.5
145°	397.8	407.2	422.7	440.3	464.1	491.1	519.1	548.0	579.2	612.3	645.4
147.5°	412.8	421.9	435.3	452.4	472.6	497.3	522.4	548.0	575.2	603.6	631.6
150°	422.7	431.0	444.4	459.0	477.6	501.4	523.2	548.0	571.9	597.8	621.6
152.5°	432.7	441.0	452.7	465.6	483.4	503.9	524.9	545.5	567.8	591.2	612.5
155°	448.6	454.9	465.2	476.5	491.1	508.7	525.3	542.9	560.5	581.2	598.8
157.5°	462.3	467.3	476.4	486.1	497.3	511.4	526.3	539.4	554.1	570.0	584.3
160°	471.4	475.5	483.8	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0
162.5°	478.8	482.1	488.8	495.3	503.9	514.7	525.5	534.4	544.1	555.1	566.1
165°	489.0	491.1	496.2	500.4	507.7	515.9	523.2	529.4	536.6	544.9	553.2
167.5°	497.3	498.3	502.3	505.2	509.7	515.8	521.6	524.4	529.2	535.2	542.1
170°	501.4	502.5	505.6	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6
172.5°	505.6	505.8	508.1	509.3	510.6	514.9	518.3	518.6	520.0	523.6	528.0
175°	509.7	508.7	510.8	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1
177.5°	511.8	511.0	511.8	511.8	511.8	512.6	514.2	512.6	511.8	512.6	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1522.2	1522.7	1528.9	1533.4	1531.2	1533.9	1535.1
5°	1663.0	1688.3	1701.6	1711.4	1712.1	1712.8	1718.4
7.5°	1862.8	1889.8	1909.6	1939.6	1948.6	1958.7	1955.8
10°	2008.6	2048.4	2082.9	2101.0	2120.7	2149.4	2126.3
12.5°	2144.7	2215.5	2267.8	2296.2	2314.6	2320.4	2309.1
15°	2369.5	2461.9	2511.7	2510.3	2573.4	2600.8	2558.0
17.5°	2575.5	2660.9	2729.3	2764.3	2816.8	2828.5	2823.2
20°	2701.6	2794.9	2848.1	2908.4	2935.7	2960.2	2964.4
22.5°	2810.4	2894.0	2951.3	3001.4	3024.3	3035.9	3043.0
25°	2922.4	2988.3	3022.6	3040.1	3046.4	3045.0	3035.9
27.5°	2914.6	2919.7	2881.9	2844.7	2811.6	2774.1	2761.2
30°	2839.0	2780.1	2675.0	2615.5	2527.8	2458.4	2486.4
32.5°	2640.0	2522.8	2404.8	2274.6	2166.8	2136.1	2105.2
35°	2253.1	2047.1	1926.5	1786.4	1730.3	1674.3	1635.7
37.5°	1822.8	1663.5	1520.5	1428.8	1372.6	1337.1	1318.1
40°	1576.1	1432.4	1314.7	1240.5	1197.7	1157.7	1152.2
42.5°	1379.4	1245.8	1157.2	1098.1	1056.9	1040.0	1027.7
45°	1129.7	1036.5	977.0	934.9	907.6	897.1	883.1
47.5°	956.2	890.3	845.6	817.0	796.4	788.5	787.5
50°	859.2	804.5	771.6	749.1	733.1	730.2	719.1
52.5°	786.3	739.0	713.3	693.7	682.1	674.2	670.8
55°	682.6	651.0	627.9	616.7	607.6	599.9	599.9
57.5°	597.3	570.9	555.6	546.1	543.2	537.8	534.3
60°	544.6	522.1	510.2	501.8	496.1	496.9	490.5
62.5°	492.9	478.4	467.0	458.6	451.9	452.0	452.5
65°	419.8	408.6	400.2	397.3	393.2	388.3	389.7
67.5°	355.7	345.2	338.7	333.9	332.4	329.8	333.9
70°	309.8	302.0	297.1	292.9	291.5	292.2	295.8
72.5°	267.7	262.3	259.0	257.1	254.0	254.1	256.5
75°	210.3	206.1	203.2	201.2	200.5	200.5	200.5
77.5°	154.4	153.5	152.2	149.1	149.3	150.1	150.3
80°	122.0	119.8	119.1	117.7	115.7	114.2	117.7
82.5°	91.1	89.0	88.3	88.0	84.8	84.5	87.5
85°	49.0	47.0	47.6	47.0	47.0	46.3	46.3
87.5°	22.7	22.4	22.3	22.6	22.3	21.9	22.8
90°	26.9	28.0	30.1	29.0	30.1	31.1	30.1
92.5°	69.2	61.1	55.7	53.9	50.7	51.8	49.9
95°	252.8	197.9	160.6	140.9	131.6	124.3	120.2
97.5°	744.7	611.1	487.1	410.7	364.1	336.1	327.2
100°	1137.6	1016.4	869.2	764.6	688.9	648.5	649.6
102.5°	1315.7	1245.1	1151.8	1070.4	1010.6	976.8	953.0
105°	1450.5	1470.2	1443.2	1395.5	1356.2	1323.0	1317.9
107.5°	1433.4	1524.2	1561.1	1561.9	1548.6	1537.5	1527.9
110°	1378.0	1508.5	1581.0	1610.0	1618.3	1616.2	1614.2



TEST NUMBER: P332083-940

CATALOG NUMBER: S123DIP-S1165D1195U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1305.0	1451.3	1544.5	1597.6	1623.3	1631.1	1631.6
115°	1188.3	1340.6	1453.6	1531.2	1576.8	1597.6	1602.8
117.5°	1089.7	1226.5	1341.0	1422.1	1474.3	1504.1	1511.2
120°	1035.0	1159.3	1264.0	1345.8	1403.8	1428.7	1434.9
122.5°	991.0	1106.3	1203.5	1276.2	1328.4	1355.8	1363.6
125°	936.6	1036.0	1118.9	1185.3	1230.8	1256.7	1264.0
127.5°	888.7	978.4	1053.8	1112.9	1151.8	1175.3	1181.9
130°	858.9	942.8	1013.3	1068.2	1105.5	1127.2	1135.5
132.5°	830.7	908.8	976.0	1027.5	1064.8	1084.1	1089.9
135°	790.5	857.8	916.9	967.7	998.7	1017.4	1024.7
137.5°	751.7	809.8	860.9	903.7	935.1	950.8	955.6
140°	729.3	779.1	823.7	863.0	892.1	908.6	907.6
142.5°	707.8	750.9	789.7	823.2	848.9	863.8	862.8
145°	679.7	712.8	742.8	768.7	790.5	798.8	800.8
147.5°	658.7	685.5	706.8	726.5	741.2	749.0	749.8
150°	645.4	667.2	686.9	702.4	713.8	720.1	720.1
152.5°	633.0	652.3	668.7	680.9	691.4	695.2	695.2
155°	615.4	631.0	643.4	652.7	661.0	663.1	664.1
157.5°	598.2	610.2	619.9	628.0	634.3	635.9	635.7
160°	587.5	597.8	605.0	612.3	618.5	618.5	617.5
162.5°	575.9	585.3	591.7	596.6	601.9	601.9	600.9
165°	559.5	566.7	571.9	576.0	580.1	579.2	579.2
167.5°	546.8	551.0	554.7	556.5	559.5	558.4	558.4
170°	537.7	541.8	543.9	544.9	547.1	546.0	546.0
172.5°	530.2	533.6	534.8	535.0	537.1	535.2	534.4
175°	520.0	522.2	522.2	522.2	523.2	522.2	521.1
177.5°	514.2	515.1	515.1	514.2	515.1	513.4	513.4
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8

(END OF REPORT)