

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332070-935

Luminaire Tested: **S123DIP-S1165D805U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332070-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D805U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6472.6 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	80	77	74	70	68	66	60	59	58	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	47	39	33	56	45	37	32	40	34	29	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.3	2.3
10°-20°	418.7	6.5
20°-30°	618.4	9.6
30°-40°	722.4	11.2
40°-50°	726.3	11.2
50°-60°	638.0	9.9
60°-70°	475.3	7.3
70°-80°	270.8	4.2
80°-90°	80.3	1.2
90°-100°	55.8	0.9
100°-110°	167.1	2.6
110°-120°	284.2	4.4
120°-130°	373.8	5.8
130°-140°	420.2	6.5
140°-150°	413.0	6.4
150°-160°	347.7	5.4
160°-170°	231.4	3.6
170°-180°	81.0	1.3
0°-30°	1185.3	18.3
0°-40°	1907.7	29.5
0°-60°	3272.0	50.6
0°-90°	4098.3	63.3
90°-120°	507.1	7.8
90°-150°	1714.1	26.5
90°-180°	2374.0	36.7
0°-180°	6472.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	8	16	19	20	6
95°	40	44	50	52	52	45
105°	151	153	159	159	160	162
115°	286	288	287	287	287	283
125°	419	421	419	417	414	373
135°	543	547	547	544	543	418
145°	659	660	662	662	659	411
155°	755	755	755	758	753	347
165°	822	820	820	824	819	232
175°	855	852	852	856	852	81
180°	857	857	857	857	857	



TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.3	27.9	27.5	27.0	26.6	26.4	26.6	26.8	26.9	27.0	26.9
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	16.3	17.3	18.3	19.4	20.3	21.4	22.6	23.7	24.7	25.8	26.3
95°	39.7	40.7	41.8	42.9	43.9	45.0	46.2	47.4	48.6	49.9	50.5
97.5°	70.5	71.3	72.1	72.8	73.7	74.5	75.3	76.2	77.1	77.9	78.6
100°	91.5	92.5	93.3	94.3	95.1	96.0	96.7	97.5	98.2	98.9	99.4
102.5°	115.8	116.3	116.8	117.4	118.0	118.7	119.7	120.7	121.7	122.7	123.1
105°	151.4	151.8	152.1	152.4	152.7	153.5	154.8	156.2	157.6	158.9	158.9
107.5°	193.0	193.1	193.3	193.5	193.6	194.0	194.6	195.1	195.6	196.1	196.7
110°	218.8	219.0	219.4	219.6	220.0	220.2	220.6	220.8	221.2	221.4	222.1



TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.7	245.9	246.1	246.2	246.4	246.5	246.6	246.7	246.8	246.8	247.5
115°	286.1	286.5	287.0	287.4	287.9	288.0	287.7	287.4	287.1	286.8	286.9
117.5°	326.7	327.1	327.4	327.6	328.0	327.9	327.5	327.1	326.7	326.3	326.3
120°	352.1	352.9	353.9	354.7	355.7	355.8	355.0	354.2	353.5	352.8	352.6
122.5°	378.5	379.1	379.8	380.4	381.1	381.3	380.8	380.5	380.0	379.7	379.3
125°	418.7	419.1	419.6	420.1	420.5	420.6	420.3	420.0	419.7	419.4	418.8
127.5°	455.9	456.8	457.8	458.7	459.7	460.0	459.7	459.3	459.0	458.7	457.9
130°	480.6	481.8	483.0	484.2	485.4	485.8	485.3	484.9	484.5	484.0	483.4
132.5°	505.4	506.6	507.8	509.0	510.2	510.7	510.3	510.0	509.6	509.3	508.6
135°	543.2	544.2	545.0	546.0	546.8	547.3	547.1	546.9	546.7	546.6	546.0
137.5°	578.2	579.0	579.7	580.5	581.3	581.8	582.2	582.6	583.0	583.3	582.7
140°	602.4	603.2	604.0	604.8	605.5	605.9	606.1	606.2	606.4	606.5	606.4
142.5°	624.6	625.3	626.0	626.8	627.6	628.1	628.4	628.6	628.9	629.1	629.0
145°	659.0	659.4	659.6	660.0	660.2	660.6	661.1	661.5	661.9	662.4	662.3
147.5°	689.2	689.7	690.3	690.8	691.4	691.8	692.2	692.7	693.1	693.5	693.5
150°	710.2	710.5	710.8	711.1	711.4	711.7	712.0	712.3	712.6	712.9	712.9
152.5°	727.5	727.8	728.2	728.7	729.1	729.4	729.6	729.8	730.0	730.1	730.4
155°	754.6	754.6	754.6	754.6	754.6	754.7	754.8	755.0	755.2	755.3	755.9
157.5°	777.7	777.6	777.4	777.2	777.1	777.1	777.1	777.3	777.4	777.5	778.2
160°	792.3	792.0	791.7	791.4	791.1	791.0	791.0	791.0	791.0	791.0	791.7
162.5°	805.2	804.9	804.4	804.0	803.6	803.4	803.6	803.7	803.7	803.9	804.6
165°	821.9	821.5	821.0	820.6	820.1	819.9	819.9	819.9	819.9	819.9	820.8
167.5°	835.3	834.7	834.1	833.4	832.8	832.7	832.8	832.8	833.0	833.1	834.1
170°	842.8	842.2	841.6	841.0	840.4	840.1	840.1	840.1	840.1	840.1	841.2
172.5°	848.7	848.2	847.6	847.0	846.4	846.0	846.0	846.0	846.0	846.0	847.0
175°	854.9	854.3	853.8	853.2	852.6	852.2	852.2	852.2	852.2	852.2	853.2
177.5°	857.5	857.0	856.5	856.0	855.6	855.3	855.3	855.3	855.3	855.3	856.0
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0



TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	26.8	26.7	26.6	26.5	26.6	26.7	26.7	26.8
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	26.8	27.3	27.7	27.9	27.7	27.6	27.4	27.2
95°	51.0	51.6	52.2	52.5	52.5	52.5	52.5	52.5
97.5°	79.3	80.0	80.7	81.0	80.9	80.9	80.8	80.8
100°	99.9	100.3	100.7	101.2	101.4	101.7	102.0	102.3
102.5°	123.6	124.0	124.4	124.7	124.6	124.5	124.5	124.4
105°	158.9	158.9	158.9	159.0	159.3	159.6	159.9	160.2
107.5°	197.1	197.6	198.1	198.2	198.0	197.9	197.7	197.5
110°	222.7	223.3	223.9	224.0	223.7	223.4	223.1	222.8





TEST NUMBER: P332070-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	248.2	248.9	249.7	249.9	249.9	249.9	249.8	249.8
115°	287.1	287.2	287.4	287.4	287.2	287.1	286.9	286.8
117.5°	326.3	326.2	326.2	326.0	325.6	325.2	324.8	324.3
120°	352.4	352.3	352.1	351.9	351.6	351.3	351.0	350.7
122.5°	378.9	378.5	378.2	377.7	377.3	376.9	376.4	376.0
125°	418.2	417.6	417.0	416.4	415.8	415.2	414.6	414.0
127.5°	457.0	456.2	455.4	454.6	453.9	453.2	452.5	451.9
130°	482.8	482.2	481.6	480.8	479.7	478.7	477.7	476.6
132.5°	507.9	507.1	506.4	505.7	504.9	504.0	503.3	502.5
135°	545.4	544.8	544.2	543.8	543.5	543.2	542.9	542.6
137.5°	582.1	581.5	580.8	580.2	579.7	579.1	578.6	578.0
140°	606.2	606.1	605.9	605.4	604.2	603.2	602.2	601.2
142.5°	628.9	628.7	628.5	628.1	627.2	626.5	625.6	624.8
145°	662.1	661.9	661.8	661.4	660.8	660.2	659.6	659.0
147.5°	693.5	693.5	693.5	693.0	692.2	691.2	690.3	689.5
150°	712.9	712.9	712.9	712.5	711.5	710.7	709.7	708.9
152.5°	730.6	730.8	731.1	730.8	730.0	729.3	728.5	727.7
155°	756.5	757.1	757.7	757.4	756.4	755.4	754.3	753.3
157.5°	778.8	779.4	780.0	779.9	779.1	778.3	777.4	776.5
160°	792.5	793.2	793.9	794.0	793.4	792.8	792.2	791.6
162.5°	805.4	806.2	806.9	806.8	805.8	804.9	803.9	803.0
165°	821.7	822.6	823.5	823.5	822.4	821.3	820.3	819.2
167.5°	835.0	835.9	836.8	836.8	835.9	835.0	834.1	833.1
170°	842.2	843.3	844.3	844.3	843.3	842.2	841.2	840.1
172.5°	847.9	848.9	849.7	849.7	848.6	847.6	846.5	845.5
175°	854.0	854.9	855.8	855.7	854.7	853.7	852.6	851.5
177.5°	856.8	857.5	858.2	858.2	857.3	856.4	855.7	854.8
180°	857.0	857.0	857.0	857.0	857.0	857.0	857.0	857.0

(END OF REPORT)