

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332071-935

Luminaire Tested: **S123DIP-S1165D805U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332071-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6600.2 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	51	71	61	54	49	54	48	44	48	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.2
10°-20°	418.7	6.3
20°-30°	618.4	9.4
30°-40°	722.4	10.9
40°-50°	726.3	11.0
50°-60°	638.0	9.7
60°-70°	475.3	7.2
70°-80°	270.8	4.1
80°-90°	80.3	1.2
90°-100°	185.1	2.8
100°-110°	524.0	7.9
110°-120°	515.5	7.8
120°-130°	411.2	6.2
130°-140°	324.2	4.9
140°-150°	242.0	3.7
150°-160°	168.6	2.6
160°-170°	99.1	1.5
170°-180°	32.2	0.5
0°-30°	1185.3	18.0
0°-40°	1907.7	28.9
0°-60°	3272.0	49.6
0°-90°	4098.3	62.1
90°-120°	1224.6	18.6
90°-150°	2201.9	33.4
90°-180°	2502.0	37.9
0°-180°	6600.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	8	17	19	20	5
95°	23	74	399	116	78	25
105°	78	115	541	946	856	83
115°	138	172	414	908	1041	137
125°	192	226	386	700	821	170
135°	225	268	381	576	666	174
145°	256	294	376	473	520	161
155°	291	314	364	414	431	134
165°	318	327	349	370	376	90
175°	332	332	335	339	339	32
180°	332	332	332	332	332	



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.4	28.0	27.6	27.2	26.8	26.5	26.7	26.9	27.0	27.2	26.8
90°	1.4	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2
92.5°	8.4	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1
95°	22.9	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8
97.5°	39.0	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9
100°	49.9	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1
102.5°	61.1	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5
105°	78.1	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4
107.5°	96.1	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5
110°	109.1	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	120.9	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0
115°	138.0	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5
117.5°	155.1	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8
120°	166.9	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7
122.5°	177.2	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3
125°	191.8	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4
127.5°	203.0	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4
130°	210.0	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9
132.5°	215.4	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9
135°	224.8	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7
137.5°	233.7	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8
140°	239.6	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9
142.5°	246.1	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6
145°	256.5	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9
147.5°	267.0	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2
150°	274.0	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4
152.5°	280.9	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1
155°	291.4	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6
157.5°	299.8	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4
160°	306.3	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5
162.5°	311.2	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7
165°	318.4	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0
167.5°	323.9	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8
170°	327.2	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0
172.5°	329.3	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2
175°	331.8	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9
177.5°	333.0	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	26.7	26.6	26.5	26.6	26.5	26.6	26.8	26.6
90°	16.8	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	56.7	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	242.4	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	604.1	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	793.7	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	856.6	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	875.1	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	822.1	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	771.5	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P332071-935

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.3	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	655.0	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	606.9	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	581.6	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	561.7	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	535.1	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	512.0	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	497.5	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	484.0	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	465.8	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	449.3	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	439.5	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	430.4	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	419.4	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	410.4	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	403.9	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	398.0	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	389.1	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	379.6	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	374.3	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	367.8	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	359.5	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	352.1	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	347.3	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	343.0	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.3	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	333.6	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)