

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831308

Luminaire Tested: S123DIP-S1165D805U935-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831308
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U935-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7087.6 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60	56		
2	93	86	80	75	87	81	76	72	72	68	65	64	61	58	56	54	52	48		
3	86	76	69	64	80	72	66	61	64	59	55	57	53	50	50	47	45	42		
4	79	68	61	55	74	65	58	52	58	52	48	52	47	44	46	42	40	36		
5	73	61	54	48	68	58	51	46	52	47	42	47	42	39	42	38	35	32		
6	67	56	48	42	63	53	46	41	48	42	37	43	38	34	38	34	32	29		
7	63	51	43	37	59	48	41	36	44	38	34	39	35	31	35	31	28	26		
8	59	46	39	34	55	44	37	33	40	34	30	36	32	28	33	29	26	24		
9	55	43	35	30	52	41	34	30	37	32	28	34	29	26	30	27	24	22		
10	52	40	33	28	49	38	31	27	35	29	25	31	27	24	28	25	22	20		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	30697	30697	30697	30697	30697
5°	38821	36641	30972	24959	22936
10°	39198	40384	30766	19896	17386
15°	29524	37494	30556	16848	14703
20°	20570	30340	30166	14734	13355
25°	15686	23332	29500	13556	12526
30°	13570	18537	28439	12722	11859
35°	12590	15650	27215	12121	11390
40°	11920	14039	25493	11547	11231
45°	11523	12994	23307	11100	11160
50°	11323	12166	20719	10692	11102
55°	10903	11560	18179	10306	11151
60°	10512	10910	15668	9944	10968
65°	9875	10297	13517	9556	10753
70°	9120	9517	11493	8913	10121
75°	8255	8530	9852	8284	9245
80°	6806	7463	7792	7221	7792
85°	5397	6052	5718	6126	6212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 26612 cd/sqm



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.6	3.8
10°-20°	670.7	9.5
20°-30°	794.2	11.2
30°-40°	798.5	11.3
40°-50°	732.6	10.3
50°-60°	604.7	8.5
60°-70°	427.7	6.0
70°-80°	228.3	3.2
80°-90°	59.8	0.8
90°-100°	180.4	2.5
100°-110°	528.3	7.5
110°-120°	515.9	7.3
120°-130°	410.9	5.8
130°-140°	324.2	4.6
140°-150°	241.8	3.4
150°-160°	168.6	2.4
160°-170°	99.0	1.4
170°-180°	32.2	0.5
0°-30°	1734.5	24.5
0°-40°	2533.1	35.7
0°-60°	3870.4	54.6
0°-90°	4586.2	64.7
90°-120°	1224.6	17.3
90°-150°	2201.5	31.1
90°-180°	2501.0	35.3
0°-180°	7087.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2852	2852	2852	2852	2852	
5°	3593	3391	2866	2310	2123	342
15°	2649	3365	2742	1512	1319	732
25°	1321	1964	2484	1141	1055	623
35°	958	1191	2071	922	867	602
45°	757	854	1531	729	733	586
55°	581	616	969	549	594	520
65°	388	404	531	375	422	385
75°	198	205	237	199	222	209
85°	44	49	46	50	50	49
90°	20	17	1	17	20	13
95°	78	399	23	399	78	127
105°	856	541	78	541	856	854
115°	1041	414	138	414	1041	1016
125°	821	386	192	386	821	743
135°	666	381	225	381	666	516
145°	520	376	256	376	520	330
155°	432	364	292	364	432	201
165°	376	349	318	349	376	107
175°	339	335	332	335	339	33
180°	332	332	332	332	332	



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8
2.5°	3214.4	3211.1	3207.8	3191.3	3174.7	3166.8	3158.9	3135.0	3111.2	3084.7	3058.3
5°	3592.9	3602.2	3611.4	3600.9	3590.3	3557.8	3525.4	3482.4	3439.4	3391.1	3342.8
7.5°	3767.6	3772.9	3778.2	3771.6	3764.9	3756.3	3747.7	3709.4	3671.0	3621.4	3571.7
10°	3586.3	3598.2	3610.1	3635.9	3661.7	3690.8	3720.0	3714.7	3709.4	3694.8	3680.3
12.5°	3188.0	3202.5	3217.1	3268.7	3320.3	3386.5	3452.6	3509.5	3566.4	3606.1	3645.8
15°	2649.4	2689.7	2730.1	2777.1	2824.0	2921.3	3018.6	3138.3	3258.1	3364.6	3471.2
17.5°	2182.2	2197.4	2212.7	2262.9	2313.2	2435.6	2558.0	2696.3	2834.6	3011.3	3188.0
20°	1795.8	1809.7	1823.6	1889.8	1955.9	2051.9	2147.8	2303.3	2458.8	2648.7	2838.6
22.5°	1508.6	1530.5	1552.3	1589.4	1626.4	1718.4	1810.4	1948.6	2086.9	2296.7	2506.4
25°	1320.7	1336.6	1352.5	1375.0	1397.5	1470.9	1544.4	1658.2	1772.0	1964.5	2157.1
27.5°	1192.3	1199.0	1205.6	1228.1	1250.6	1298.2	1345.9	1443.8	1541.7	1705.1	1868.6
30°	1091.8	1096.4	1101.0	1120.9	1140.7	1173.2	1205.6	1276.4	1347.2	1491.4	1635.7
32.5°	1021.6	1024.9	1028.2	1043.5	1058.7	1081.8	1105.0	1156.6	1208.2	1327.3	1446.4
35°	958.1	960.1	962.1	973.3	984.6	1001.8	1019.0	1058.0	1097.1	1191.0	1285.0
37.5°	902.5	905.2	907.8	914.4	921.1	936.3	951.5	982.6	1013.7	1085.8	1157.9
40°	848.3	852.9	857.5	862.2	866.8	879.4	891.9	915.8	939.6	999.1	1058.7
42.5°	802.0	806.6	811.2	813.2	815.2	822.5	829.7	851.6	873.4	917.7	962.1
45°	757.0	758.9	760.9	762.9	764.9	770.9	776.8	796.0	815.2	853.6	891.9
47.5°	715.9	715.9	715.9	717.3	718.6	723.9	729.2	743.1	757.0	786.7	816.5
50°	676.2	676.2	676.2	674.3	672.3	675.6	678.9	689.5	700.1	726.5	753.0
52.5°	628.6	628.6	628.6	629.3	629.9	629.9	629.9	639.2	648.4	672.3	696.1
55°	581.0	583.6	586.2	584.3	582.3	583.6	584.9	590.9	596.8	616.0	635.2
57.5°	533.3	534.6	536.0	535.3	534.6	535.3	536.0	541.3	546.5	561.1	575.7
60°	488.3	488.3	488.3	487.0	485.7	487.0	488.3	491.0	493.6	506.8	520.1
62.5°	438.0	438.7	439.4	440.0	440.7	439.4	438.0	441.3	444.6	454.6	464.5
65°	387.7	388.4	389.1	391.1	393.0	391.7	390.4	393.7	397.0	404.3	411.6
67.5°	342.7	341.4	340.1	340.8	341.4	343.4	345.4	346.1	346.7	354.7	362.6
70°	289.8	291.1	292.5	291.8	291.1	291.8	292.5	294.4	296.4	302.4	308.3
72.5°	242.2	242.8	243.5	243.5	243.5	244.8	246.1	248.1	250.1	253.4	256.7
75°	198.5	198.5	198.5	199.8	201.2	201.8	202.5	202.5	202.5	205.1	207.8
77.5°	150.9	154.2	157.5	156.8	156.2	157.5	158.8	160.8	162.8	164.1	165.4
80°	109.8	109.8	109.8	110.5	111.2	113.1	115.1	116.5	117.8	120.4	123.1
82.5°	70.1	70.8	71.5	73.4	75.4	76.8	78.1	80.1	82.0	82.0	82.0
85°	43.7	42.3	41.0	42.3	43.7	45.0	46.3	47.0	47.6	49.0	50.3
87.5°	21.2	21.2	21.2	21.2	21.2	21.8	22.5	22.5	22.5	22.5	22.5
90°	19.5	20.2	19.5	18.8	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	35.7	37.0	36.3	39.0	40.4	45.1	51.8	66.6	93.6	125.2	138.7
95°	78.1	80.8	85.5	91.5	104.3	128.6	164.2	242.3	323.8	399.2	355.4
97.5°	160.2	167.6	183.8	209.3	254.4	331.2	420.0	556.7	634.8	613.9	458.4
100°	422.1	421.4	447.6	496.8	564.8	660.4	739.1	793.6	770.1	637.5	430.8
102.5°	668.4	688.0	708.8	745.2	794.3	846.1	883.8	872.4	776.8	593.7	390.4
105°	856.2	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	978.8	986.2	994.9	1007.0	1011.1	992.9	940.4	834.7	673.8	494.8	335.9
110°	1048.8	1050.1	1051.5	1046.1	1027.2	980.1	895.3	771.4	617.3	456.4	323.8



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1062.9	1062.2	1055.5	1036.0	997.6	933.7	836.0	708.8	568.1	430.8	317.1
115°	1041.4	1038.0	1024.5	994.9	944.4	871.0	772.1	655.0	530.4	414.0	316.4
117.5°	994.2	989.5	969.3	936.3	883.8	807.8	716.9	613.2	505.5	402.5	317.1
120°	932.3	928.3	912.1	874.4	821.2	753.2	672.5	581.6	486.7	395.1	319.7
122.5°	874.4	869.0	850.9	817.9	772.1	710.2	636.8	556.7	471.2	390.4	324.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.5	535.2	458.4	386.4	329.2
127.5°	775.5	771.4	755.9	730.4	691.3	641.5	582.3	515.6	446.3	384.4	334.6
130°	737.8	732.4	718.2	694.0	658.3	612.6	558.0	497.5	436.9	382.3	339.9
132.5°	700.7	697.4	685.3	661.0	628.0	585.0	535.2	480.6	428.1	381.7	344.0
135°	665.7	661.0	648.9	628.7	595.7	557.4	513.6	465.8	420.7	381.0	348.0
137.5°	628.7	624.7	614.6	593.7	565.4	531.1	492.1	451.7	414.0	379.7	350.7
140°	589.7	590.3	579.6	560.7	535.2	506.2	473.9	439.6	407.9	379.0	353.4
142.5°	553.3	554.0	544.6	528.4	507.6	483.3	456.4	428.1	402.5	377.6	355.4
145°	520.3	519.0	513.6	499.5	482.6	463.1	441.6	419.4	397.8	376.3	356.1
147.5°	492.1	491.4	486.0	475.9	462.5	448.3	430.1	412.0	393.1	374.3	356.1
150°	467.8	467.8	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	447.6	447.6	445.6	438.9	431.5	421.4	409.3	396.5	383.0	368.2	354.1
155°	431.5	430.8	429.5	424.1	418.0	409.9	399.8	389.1	377.6	364.2	352.7
157.5°	416.0	416.0	414.7	410.6	405.2	398.5	390.4	381.0	371.6	360.8	350.7
160°	401.2	401.9	401.9	397.8	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	387.7	388.4	388.4	385.0	382.3	378.3	372.2	366.2	359.5	352.7	346.7
165°	376.3	376.3	377.0	374.3	371.6	368.2	363.5	359.5	354.1	348.7	344.0
167.5°	364.8	364.8	365.5	363.5	362.2	359.5	356.8	353.4	348.7	344.7	341.3
170°	354.7	354.7	355.4	354.1	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	345.3	346.0	347.3	346.0	346.0	345.3	343.3	342.0	339.3	337.2	336.6
175°	338.6	339.3	339.9	339.3	339.3	339.3	337.9	337.2	335.9	334.6	334.6
177.5°	333.9	333.9	335.2	334.6	335.2	335.2	334.6	333.9	333.2	332.5	333.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8
2.5°	3050.3	3042.4	3013.3	2984.2	2951.1	2918.0	2893.5	2869.0	2832.6	2796.3	2766.5
5°	3305.7	3268.7	3207.2	3145.6	3062.2	2978.9	2922.6	2866.4	2791.0	2715.5	2655.3
7.5°	3508.2	3444.7	3358.7	3272.7	3163.5	3054.3	2951.1	2847.9	2732.7	2617.6	2523.6
10°	3637.2	3594.2	3495.0	3395.7	3249.5	3103.3	2959.0	2814.8	2666.6	2518.3	2394.0
12.5°	3649.8	3653.8	3562.5	3471.2	3305.7	3140.3	2965.0	2789.6	2603.0	2416.4	2271.5
15°	3539.3	3607.5	3557.2	3506.9	3340.2	3173.4	2957.7	2742.0	2526.9	2311.9	2144.5
17.5°	3334.2	3480.4	3487.7	3495.0	3328.2	3161.5	2922.6	2683.8	2440.3	2196.8	2020.8
20°	3054.3	3270.0	3344.1	3418.2	3282.6	3146.9	2890.2	2633.5	2360.9	2088.3	1903.6
22.5°	2768.5	3030.5	3166.1	3301.8	3201.2	3100.6	2827.4	2554.1	2266.2	1978.4	1791.2
25°	2442.9	2728.8	2937.2	3145.6	3084.1	3022.5	2753.2	2483.9	2177.6	1871.2	1680.0
27.5°	2159.1	2449.5	2701.0	2952.4	2939.2	2925.9	2658.6	2391.3	2077.7	1764.0	1579.4
30°	1906.3	2176.9	2458.1	2739.3	2771.8	2804.2	2546.1	2288.1	1973.8	1659.5	1481.5
32.5°	1682.6	1918.9	2220.6	2522.3	2585.8	2649.4	2416.4	2183.5	1872.5	1561.6	1390.2
35°	1499.4	1713.7	2015.5	2317.2	2396.6	2476.0	2273.5	2071.1	1768.0	1465.0	1301.5
37.5°	1337.3	1516.6	1811.0	2105.5	2202.7	2300.0	2118.7	1937.4	1653.5	1369.7	1219.5
40°	1202.9	1347.2	1617.8	1888.4	2000.9	2113.4	1963.9	1814.3	1545.0	1275.7	1137.4
42.5°	1090.4	1218.8	1464.3	1709.8	1817.6	1925.5	1799.1	1672.7	1433.2	1193.7	1067.3
45°	994.5	1097.1	1320.0	1543.0	1645.6	1748.2	1639.6	1531.1	1320.0	1109.0	991.2
47.5°	904.5	992.5	1183.1	1373.6	1465.0	1556.3	1471.6	1386.9	1208.2	1029.6	923.0
50°	823.8	894.6	1061.3	1228.1	1307.5	1386.9	1312.1	1237.3	1090.4	943.6	850.9
52.5°	753.7	811.2	950.8	1090.4	1158.6	1226.8	1162.6	1098.4	981.9	865.5	784.8
55°	684.2	733.1	854.2	975.3	1021.6	1067.9	1018.3	968.7	874.7	780.8	712.6
57.5°	619.3	663.0	762.3	861.5	897.2	933.0	888.0	843.0	772.2	701.4	644.5
60°	555.8	591.5	674.3	757.0	778.8	800.6	764.2	727.8	678.2	628.6	577.6
62.5°	496.9	529.3	590.9	652.4	667.0	681.5	653.7	625.9	588.2	550.5	510.8
65°	436.0	460.5	510.8	561.1	570.4	579.6	555.1	530.7	502.2	473.8	444.6
67.5°	379.8	397.0	438.0	479.1	479.7	480.4	460.5	440.7	424.8	408.9	385.8
70°	324.9	341.4	368.6	395.7	396.3	397.0	381.1	365.2	353.3	341.4	324.2
72.5°	268.6	280.6	301.1	321.6	320.3	318.9	309.0	299.1	289.8	280.6	268.0
75°	217.7	227.6	241.5	255.4	251.4	247.5	242.2	236.9	228.9	221.0	213.1
77.5°	171.4	177.3	185.3	193.2	190.6	187.9	183.3	178.7	172.7	166.7	163.4
80°	125.7	128.4	133.7	139.0	137.6	136.3	131.0	125.7	124.4	123.1	118.4
82.5°	85.4	88.7	90.0	91.3	90.6	90.0	86.0	82.0	80.7	79.4	78.7
85°	50.9	51.6	52.3	52.9	50.9	49.0	47.6	46.3	46.3	46.3	45.7
87.5°	23.2	23.8	23.8	23.8	23.2	22.5	21.2	19.9	20.5	21.2	21.2
90°	12.8	10.8	8.8	7.4	6.1	4.0	2.7	1.3	2.7	4.0	6.1
92.5°	103.7	68.0	46.4	34.3	27.6	21.5	14.8	10.1	14.8	21.5	27.6
95°	245.0	144.7	87.5	61.3	43.8	32.3	24.9	22.9	24.9	32.3	43.8
97.5°	272.6	156.2	99.6	70.7	53.2	43.1	37.0	36.3	37.0	43.1	53.2
100°	253.8	154.2	107.0	80.8	64.6	55.2	50.5	49.8	50.5	55.2	64.6
102.5°	237.6	156.8	115.8	92.2	78.1	69.3	65.3	63.9	65.3	69.3	78.1
105°	231.6	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.2	171.0	138.7	119.1	107.0	99.0	94.9	92.9	94.9	99.0	107.0
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.0	111.1	114.4	121.8



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	240.3	193.9	166.3	148.1	136.6	129.2	125.9	123.9	125.9	129.2	136.6
115°	247.7	206.7	181.1	162.9	151.5	144.7	140.7	138.0	140.7	144.7	151.5
117.5°	257.1	220.1	194.5	177.7	164.9	158.9	155.5	152.1	155.5	158.9	164.9
120°	267.9	232.9	208.7	191.8	179.1	172.3	169.0	166.9	169.0	172.3	179.1
122.5°	278.0	246.4	222.8	204.6	192.5	185.1	181.7	179.7	181.7	185.1	192.5
125°	288.8	259.2	235.6	217.4	204.6	197.2	193.2	191.8	193.2	197.2	204.6
127.5°	297.5	270.6	247.7	229.5	215.4	208.0	203.3	201.3	203.3	208.0	215.4
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.0	210.0	212.0	218.1	226.2
132.5°	314.4	289.5	267.9	250.4	236.3	226.2	219.4	216.8	219.4	226.2	236.3
135°	321.1	298.2	277.3	259.2	245.0	234.9	227.5	224.8	227.5	234.9	245.0
137.5°	326.5	304.3	284.1	267.2	253.1	242.3	234.9	232.2	234.9	242.3	253.1
140°	330.5	310.3	290.8	274.0	260.5	249.7	243.0	239.6	243.0	249.7	260.5
142.5°	334.6	315.0	296.2	280.7	267.2	257.8	250.4	247.7	250.4	257.8	267.2
145°	337.2	319.1	301.6	286.1	274.6	264.5	258.5	256.5	258.5	264.5	274.6
147.5°	339.3	322.4	306.3	292.8	281.4	272.6	266.6	265.2	266.6	272.6	281.4
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.6	274.0	274.6	280.0	288.8
152.5°	341.3	327.8	315.0	303.6	295.5	288.1	282.7	282.7	282.7	288.1	295.5
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.5	291.5	291.5	295.5	302.2
157.5°	342.0	331.9	322.4	315.0	308.3	302.2	298.9	298.2	298.9	302.2	308.3
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.3	334.6	327.8	322.4	318.4	314.4	312.3	312.3	312.3	314.4	318.4
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	339.3	335.2	331.2	327.8	325.8	323.1	322.4	323.1	322.4	323.1	325.8
170°	337.2	334.6	331.2	329.8	328.5	326.5	325.8	327.1	325.8	326.5	328.5
172.5°	336.6	334.6	331.9	331.2	330.5	329.2	329.2	329.8	329.2	329.2	330.5
175°	335.2	333.9	332.5	331.9	331.9	330.5	331.2	331.9	331.2	330.5	331.9
177.5°	334.6	333.2	332.5	332.5	332.5	331.9	332.5	333.2	332.5	331.9	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8	2851.8
2.5°	2736.7	2710.9	2685.1	2665.2	2645.4	2611.6	2577.9	2570.0	2562.0	2550.8	2539.5
5°	2595.1	2531.6	2468.1	2411.2	2354.3	2309.9	2265.6	2236.5	2207.4	2186.2	2165.0
7.5°	2429.7	2334.4	2239.1	2171.6	2104.1	2040.0	1975.8	1955.3	1934.7	1907.0	1879.2
10°	2269.6	2164.3	2059.1	1971.1	1883.1	1820.3	1757.4	1732.3	1707.1	1672.1	1637.0
12.5°	2126.6	2011.5	1896.4	1807.7	1719.0	1658.2	1597.3	1560.9	1524.5	1504.7	1484.8
15°	1977.1	1854.0	1731.0	1648.9	1566.9	1511.9	1457.0	1425.3	1393.5	1374.3	1355.1
17.5°	1844.8	1723.0	1601.3	1522.5	1443.8	1393.5	1343.2	1315.4	1287.6	1273.1	1258.5
20°	1719.0	1599.9	1480.8	1404.1	1327.3	1286.3	1245.3	1227.4	1209.5	1197.6	1185.7
22.5°	1603.9	1486.8	1369.7	1304.2	1238.7	1205.6	1172.5	1159.9	1147.4	1137.4	1127.5
25°	1488.8	1384.2	1279.7	1224.1	1168.5	1141.4	1114.3	1101.7	1089.1	1079.2	1069.3
27.5°	1394.8	1294.9	1195.0	1147.4	1099.7	1078.5	1057.4	1047.4	1037.5	1028.2	1019.0
30°	1303.5	1214.2	1124.9	1083.8	1042.8	1023.6	1004.4	994.5	984.6	976.0	967.4
32.5°	1218.8	1142.1	1065.3	1027.6	989.9	974.0	958.1	946.2	934.3	927.7	921.1
35°	1138.1	1069.3	1000.5	969.4	938.3	922.4	906.5	896.6	886.6	881.4	876.1
37.5°	1069.3	1007.7	946.2	916.4	886.6	871.4	856.2	847.6	839.0	837.0	835.0
40°	999.1	946.2	893.3	864.2	835.0	821.8	808.6	803.3	798.0	796.7	795.3
42.5°	940.9	889.3	837.7	811.2	784.8	773.5	762.3	759.6	757.0	758.9	760.9
45°	873.4	830.4	787.4	762.9	738.4	729.2	719.9	717.9	715.9	719.9	723.9
47.5°	816.5	776.8	737.1	714.0	690.8	684.2	677.6	676.9	676.2	681.5	686.8
50°	758.3	719.9	681.5	663.0	644.5	638.5	632.6	634.5	636.5	645.1	653.7
52.5°	704.0	668.3	632.6	615.4	598.2	594.2	590.2	594.8	599.5	608.7	618.0
55°	644.5	612.1	579.6	566.4	553.2	549.2	545.2	554.5	563.7	572.4	581.0
57.5°	587.6	559.1	530.7	518.8	506.8	506.2	505.5	514.1	522.7	532.0	541.3
60°	526.7	502.9	479.1	469.8	460.5	461.9	463.2	473.1	483.0	490.3	497.6
62.5°	471.1	451.3	431.4	422.8	414.2	417.5	420.8	430.8	440.7	449.3	457.9
65°	415.5	399.0	382.5	376.5	370.5	375.2	379.8	388.4	397.0	403.0	408.9
67.5°	362.6	348.7	334.8	330.2	325.5	330.2	334.8	343.4	352.0	358.0	363.9
70°	307.0	295.8	284.5	281.2	277.9	283.2	288.5	295.8	303.0	309.0	315.0
72.5°	255.4	246.8	238.2	237.5	236.9	241.5	246.1	253.4	260.7	264.7	268.6
75°	205.1	200.5	195.9	195.2	194.5	199.2	203.8	207.8	211.7	215.0	218.4
77.5°	160.1	156.2	152.2	152.8	153.5	156.8	160.1	164.1	168.1	170.1	172.0
80°	113.8	112.5	111.2	112.5	113.8	116.5	119.1	121.7	124.4	125.7	127.0
82.5°	78.1	76.8	75.4	77.4	79.4	81.4	83.4	85.4	87.3	88.0	88.7
85°	45.0	47.0	49.0	49.0	49.0	49.6	50.3	50.9	51.6	50.9	50.3
87.5°	21.2	21.8	22.5	22.5	22.5	23.2	23.8	23.8	23.8	23.2	22.5
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	34.3	46.4	68.0	103.7	138.7	125.2	93.6	66.6	51.8	45.1	40.4
95°	61.3	87.5	144.7	245.0	355.4	399.2	323.8	242.3	164.2	128.6	104.3
97.5°	70.7	99.6	156.2	272.6	458.4	613.9	634.8	556.7	420.0	331.2	254.4
100°	80.8	107.0	154.2	253.8	430.8	637.5	770.1	793.6	739.1	660.4	564.8
102.5°	92.2	115.8	156.8	237.6	390.4	593.7	776.8	872.4	883.8	846.1	794.3
105°	105.0	125.9	162.2	231.6	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	119.1	138.7	171.0	230.2	335.9	494.8	673.8	834.7	940.4	992.9	1011.1
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.4	895.3	980.1	1027.2



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	148.1	166.3	193.9	240.3	317.1	430.8	568.1	708.8	836.0	933.7	997.6
115°	162.9	181.1	206.7	247.7	316.4	414.0	530.4	655.0	772.1	871.0	944.4
117.5°	177.7	194.5	220.1	257.1	317.1	402.5	505.5	613.2	716.9	807.8	883.8
120°	191.8	208.7	232.9	267.9	319.7	395.1	486.7	581.6	672.5	753.2	821.2
122.5°	204.6	222.8	246.4	278.0	324.5	390.4	471.2	556.7	636.8	710.2	772.1
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.2	608.5	673.1	727.0
127.5°	229.5	247.7	270.6	297.5	334.6	384.4	446.3	515.6	582.3	641.5	691.3
130°	240.3	258.5	280.7	306.3	339.9	382.3	436.9	497.5	558.0	612.6	658.3
132.5°	250.4	267.9	289.5	314.4	344.0	381.7	428.1	480.6	535.2	585.0	628.0
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.4	595.7
137.5°	267.2	284.1	304.3	326.5	350.7	379.7	414.0	451.7	492.1	531.1	565.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.6	473.9	506.2	535.2
142.5°	280.7	296.2	315.0	334.6	355.4	377.6	402.5	428.1	456.4	483.3	507.6
145°	286.1	301.6	319.1	337.2	356.1	376.3	397.8	419.4	441.6	463.1	482.6
147.5°	292.8	306.3	322.4	339.3	356.1	374.3	393.1	412.0	430.1	448.3	462.5
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	303.6	315.0	327.8	341.3	354.1	368.2	383.0	396.5	409.3	421.4	431.5
155°	309.6	319.1	330.5	341.3	352.7	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.0	322.4	331.9	342.0	350.7	360.8	371.6	381.0	390.4	398.5	405.2
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	322.4	327.8	334.6	341.3	346.7	352.7	359.5	366.2	372.2	378.3	382.3
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.1	359.5	363.5	368.2	371.6
167.5°	327.8	331.2	335.2	339.3	341.3	344.7	348.7	353.4	356.8	359.5	362.2
170°	329.8	331.2	334.6	337.2	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	331.2	331.9	334.6	336.6	336.6	337.2	339.3	342.0	343.3	345.3	346.0
175°	331.9	332.5	333.9	335.2	334.6	334.6	335.9	337.2	337.9	339.3	339.3
177.5°	332.5	332.5	333.2	334.6	333.2	332.5	333.2	333.9	334.6	335.2	335.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2851.8	2851.8	2851.8	2851.8
2.5°	2534.9	2530.3	2511.7	2493.2
5°	2149.1	2133.3	2128.0	2122.7
7.5°	1877.8	1876.5	1848.7	1820.9
10°	1639.0	1641.0	1615.8	1590.7
12.5°	1468.3	1451.7	1449.7	1447.8
15°	1339.9	1324.7	1322.0	1319.4
17.5°	1249.2	1240.0	1237.3	1234.7
20°	1180.4	1175.1	1170.5	1165.9
22.5°	1120.9	1114.3	1110.3	1106.3
25°	1063.3	1057.4	1056.0	1054.7
27.5°	1011.7	1004.4	1004.4	1004.4
30°	962.7	958.1	956.1	954.1
32.5°	917.1	913.1	913.1	913.1
35°	874.1	872.1	869.4	866.8
37.5°	835.0	835.0	833.7	832.4
40°	797.3	799.3	799.3	799.3
42.5°	762.9	764.9	764.9	764.9
45°	727.2	730.5	731.8	733.1
47.5°	692.1	697.4	698.7	700.1
50°	657.7	661.7	662.3	663.0
52.5°	622.6	627.3	630.6	633.9
55°	585.6	590.2	592.2	594.2
57.5°	545.9	550.5	551.2	551.8
60°	502.2	506.8	508.2	509.5
62.5°	460.5	463.2	464.5	465.8
65°	412.9	416.9	419.5	422.2
67.5°	367.2	370.5	370.5	370.5
70°	316.3	317.6	319.6	321.6
72.5°	269.3	270.0	270.0	270.0
75°	219.7	221.0	221.7	222.3
77.5°	172.7	173.4	173.4	173.4
80°	126.4	125.7	125.7	125.7
82.5°	86.7	84.7	84.7	84.7
85°	49.6	49.0	49.6	50.3
87.5°	22.5	22.5	22.5	22.5
90°	18.8	19.5	20.2	19.5
92.5°	39.0	36.3	37.0	35.7
95°	91.5	85.5	80.8	78.1
97.5°	209.3	183.8	167.6	160.2
100°	496.8	447.6	421.4	422.1
102.5°	745.2	708.8	688.0	668.4
105°	906.7	881.1	859.6	856.2
107.5°	1007.0	994.9	986.2	978.8
110°	1046.1	1051.5	1050.1	1048.8



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1036.0	1055.5	1062.2	1062.9
115°	994.9	1024.5	1038.0	1041.4
117.5°	936.3	969.3	989.5	994.2
120°	874.4	912.1	928.3	932.3
122.5°	817.9	850.9	869.0	874.4
125°	770.1	799.7	816.5	821.2
127.5°	730.4	755.9	771.4	775.5
130°	694.0	718.2	732.4	737.8
132.5°	661.0	685.3	697.4	700.7
135°	628.7	648.9	661.0	665.7
137.5°	593.7	614.6	624.7	628.7
140°	560.7	579.6	590.3	589.7
142.5°	528.4	544.6	554.0	553.3
145°	499.5	513.6	519.0	520.3
147.5°	475.9	486.0	491.4	492.1
150°	456.4	463.8	467.8	467.8
152.5°	438.9	445.6	447.6	447.6
155°	424.1	429.5	430.8	431.5
157.5°	410.6	414.7	416.0	416.0
160°	397.8	401.9	401.9	401.2
162.5°	385.0	388.4	388.4	387.7
165°	374.3	377.0	376.3	376.3
167.5°	363.5	365.5	364.8	364.8
170°	354.1	355.4	354.7	354.7
172.5°	346.0	347.3	346.0	345.3
175°	339.3	339.9	339.3	338.6
177.5°	334.6	335.2	333.9	333.9
180°	332.5	332.5	332.5	332.5



TEST NUMBER: P831308

CATALOG NUMBER: S123DIP-S1165D805U935-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.74	17.70	17.57	18.54	19.59	18.98	19.94	19.80	20.78	21.83
	3H	18.39	19.25	19.24	20.11	21.18	20.41	21.27	21.25	22.12	23.20
	4H	18.98	19.79	19.83	20.65	21.74	20.86	21.67	21.72	22.54	23.62
	6H	19.35	20.10	20.22	20.97	22.07	21.14	21.89	22.01	22.76	23.86
	8H	19.45	20.16	20.33	21.05	22.15	21.21	21.92	22.09	22.81	23.91
	12H	19.50	20.18	20.38	21.06	22.18	21.23	21.91	22.11	22.79	23.91
4H	2H	17.33	18.14	18.19	19.00	20.09	19.15	19.96	20.01	20.82	21.91
	3H	19.16	19.84	20.04	20.73	21.83	20.78	21.45	21.65	22.35	23.45
	4H	19.87	20.48	20.75	21.37	22.50	21.37	21.98	22.25	22.87	24.00
	6H	20.35	20.88	21.25	21.79	22.92	21.78	22.31	22.68	23.22	24.35
	8H	20.48	20.98	21.39	21.89	23.03	21.89	22.38	22.79	23.29	24.44
	12H	20.56	21.00	21.48	21.93	23.08	21.94	22.38	22.86	23.31	24.46
8H	4H	20.14	20.63	21.04	21.54	22.69	21.48	21.97	22.38	22.88	24.03
	6H	20.73	21.14	21.66	22.09	23.23	21.99	22.39	22.91	23.34	24.49
	8H	20.94	21.30	21.88	22.24	23.40	22.17	22.53	23.10	23.47	24.63
	12H	21.07	21.38	22.01	22.32	23.53	22.27	22.59	23.21	23.52	24.74
12H	4H	20.14	20.59	21.07	21.52	22.67	21.46	21.90	22.38	22.83	23.98
	6H	20.78	21.14	21.72	22.09	23.25	22.00	22.36	22.94	23.30	24.46
	8H	21.02	21.34	21.96	22.27	23.49	22.20	22.52	23.15	23.46	24.67