

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332054-940

Luminaire Tested: **S123DIP-S1165D585U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332054-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D585U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6455.3 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	68	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	67	59	53	74	64	57	51	57	52	47	51	47	43	46	42	39	36
5	72	60	52	46	68	57	50	44	52	45	41	46	41	38	41	37	34	32
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15569	15569	15569	15569
5°	18567	15637	13857	15637
10°	23240	15557	12516	15557
15°	28505	15432	11652	15432
20°	33956	15237	11094	15237
25°	36056	14998	10969	14998
30°	30904	14825	11028	14825
35°	21494	14578	11143	14578
40°	16190	14289	11108	14289
45°	13443	13857	10966	13857
50°	12042	12980	10868	12980
55°	11258	12033	10732	12033
60°	10559	11044	10622	11044
65°	9926	10068	10282	10068
70°	9309	8954	9791	8954
75°	8339	7839	8979	7839
80°	7296	6428	7736	6428
85°	5718	4668	5199	4668



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.5	2.2
10°-20°	456.9	7.1
20°-30°	766.8	11.9
30°-40°	868.3	13.5
40°-50°	778.6	12.1
50°-60°	628.3	9.7
60°-70°	437.9	6.8
70°-80°	230.1	3.6
80°-90°	58.2	0.9
90°-100°	24.9	0.4
100°-110°	118.6	1.8
110°-120°	284.9	4.4
120°-130°	362.8	5.6
130°-140°	387.7	6.0
140°-150°	362.5	5.6
150°-160°	292.4	4.5
160°-170°	188.7	2.9
170°-180°	65.0	1.0
0°-30°	1366.2	21.2
0°-40°	2234.5	34.6
0°-60°	3641.5	56.4
0°-90°	4367.7	67.7
90°-120°	428.4	6.6
90°-150°	1541.4	23.9
90°-180°	2088.0	32.3
0°-180°	6455.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1446	1446	1446	1446	1446	
5°	1718	1447	1282	1447	1718	178
15°	2558	1385	1046	1385	2558	739
25°	3036	1263	924	1263	3036	1331
35°	1636	1109	848	1109	1636	1063
45°	883	910	720	910	883	699
55°	600	641	572	641	600	538
65°	390	395	404	395	390	388
75°	200	188	216	188	200	215
85°	46	38	42	38	46	55
90°	15	0	15	0	15	9
95°	19	31	19	31	19	16
105°	22	152	22	152	22	51
115°	299	284	299	284	299	276
125°	409	401	409	401	409	365
135°	504	499	504	499	504	389
145°	581	576	581	576	581	363
155°	633	634	633	634	633	292
165°	667	669	667	669	667	188
175°	682	685	682	685	682	65
180°	685	685	685	685	685	



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1535.1	1533.9	1531.2	1533.4	1528.9	1522.7	1522.2	1516.5	1500.3	1499.1	1494.7
5°	1718.4	1712.8	1712.1	1711.4	1701.6	1688.3	1663.0	1660.9	1627.3	1610.4	1590.2
7.5°	1955.8	1958.7	1948.6	1939.6	1909.6	1889.8	1862.8	1828.2	1786.8	1744.9	1717.0
10°	2126.3	2149.4	2120.7	2101.0	2082.9	2048.4	2008.6	1958.7	1909.0	1850.8	1806.7
12.5°	2309.1	2320.4	2314.6	2296.2	2267.8	2215.5	2144.7	2090.0	2044.2	1947.3	1908.2
15°	2558.0	2600.8	2573.4	2510.3	2511.7	2461.9	2369.5	2267.8	2213.9	2129.0	2013.5
17.5°	2823.2	2828.5	2816.8	2764.3	2729.3	2660.9	2575.5	2478.1	2368.7	2266.2	2143.5
20°	2964.4	2960.2	2935.7	2908.4	2848.1	2794.9	2701.6	2593.0	2452.8	2352.0	2218.0
22.5°	3043.0	3035.9	3024.3	3001.4	2951.3	2894.0	2810.4	2691.7	2558.2	2419.2	2264.6
25°	3035.9	3045.0	3046.4	3040.1	3022.6	2988.3	2922.4	2827.8	2694.7	2516.0	2354.7
27.5°	2761.2	2774.1	2811.6	2844.7	2881.9	2919.7	2914.6	2867.7	2769.2	2614.9	2417.8
30°	2486.4	2458.4	2527.8	2615.5	2675.0	2780.1	2839.0	2842.5	2787.1	2654.7	2462.6
32.5°	2105.2	2136.1	2166.8	2274.6	2404.8	2522.8	2640.0	2734.3	2745.1	2656.9	2489.0
35°	1635.7	1674.3	1730.3	1786.4	1926.5	2047.1	2253.1	2432.5	2575.5	2594.4	2491.4
37.5°	1318.1	1337.1	1372.6	1428.8	1520.5	1663.5	1822.8	2049.6	2256.7	2410.8	2417.5
40°	1152.2	1157.7	1197.7	1240.5	1314.7	1432.4	1576.1	1776.6	2024.6	2239.8	2329.5
42.5°	1027.7	1040.0	1056.9	1098.1	1157.2	1245.8	1379.4	1545.0	1772.4	2020.0	2195.5
45°	883.1	897.1	907.6	934.9	977.0	1036.5	1129.7	1281.1	1454.2	1709.9	1946.2
47.5°	787.5	788.5	796.4	817.0	845.6	890.3	956.2	1053.5	1212.4	1419.9	1662.3
50°	719.1	730.2	733.1	749.1	771.6	804.5	859.2	941.9	1072.3	1254.5	1477.3
52.5°	670.8	674.2	682.1	693.7	713.3	739.0	786.3	851.0	953.4	1108.7	1313.6
55°	599.9	599.9	607.6	616.7	627.9	651.0	682.6	730.2	808.1	928.5	1098.1
57.5°	534.3	537.8	543.2	546.1	555.6	570.9	597.3	633.4	691.4	784.2	919.1
60°	490.5	496.9	496.1	501.8	510.2	522.1	544.6	574.0	625.8	700.1	813.7
62.5°	452.5	452.0	451.9	458.6	467.0	478.4	492.9	518.4	562.5	628.4	725.1
65°	389.7	388.3	393.2	397.3	400.2	408.6	419.8	442.2	471.6	520.7	595.7
67.5°	333.9	329.8	332.4	333.9	338.7	345.2	355.7	369.6	393.0	432.4	488.9
70°	295.8	292.2	291.5	292.9	297.1	302.0	309.8	323.1	344.8	376.3	417.7
72.5°	256.5	254.1	254.0	257.1	259.0	262.3	267.7	279.9	297.1	320.8	359.4
75°	200.5	200.5	200.5	201.2	203.2	206.1	210.3	216.5	229.9	246.6	272.6
77.5°	150.3	150.1	149.3	149.1	152.2	153.5	154.4	160.3	167.7	179.1	198.0
80°	117.7	114.2	115.7	117.7	119.1	119.8	122.0	123.3	129.7	136.0	149.3
82.5°	87.5	84.5	84.8	88.0	88.3	89.0	91.1	93.1	95.4	101.2	108.3
85°	46.3	46.3	47.0	47.0	47.6	47.0	49.0	49.8	49.8	53.2	57.4
87.5°	19.9	18.7	19.3	19.7	19.2	19.6	20.1	20.6	21.0	21.5	21.8
90°	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4	13.7	13.0	11.9
95°	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4	16.6	15.8	14.5
97.5°	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2	17.3	16.4	24.5
100°	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5	17.7	16.8	34.4
102.5°	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8	30.7	33.4	52.7
105°	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3	91.4	111.4	121.5
107.5°	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8	189.5	204.1	202.5
110°	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9	225.6	229.3	228.1



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1	255.1	255.0	253.8
115°	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2	293.1	291.9	290.9
117.5°	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6	328.7	327.7	327.3
120°	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8	351.9	350.9	350.6
122.5°	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4	374.8	374.2	373.7
125°	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3	407.1	406.9	406.4
127.5°	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3	439.0	438.6	438.1
130°	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6	458.2	457.7	457.3
132.5°	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0	476.5	476.1	475.6
135°	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0	503.5
137.5°	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4	528.9	528.3	528.1
140°	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1	544.7	544.2	543.9
142.5°	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0	559.6	559.3	558.9
145°	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8	580.5	580.3	580.1
147.5°	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4	599.1	599.0	598.7
150°	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7	610.6	610.3	610.1
152.5°	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9	620.5	620.1	619.9
155°	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8	634.3	633.7	633.6
157.5°	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9	646.3	645.6	645.7
160°	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9	653.2	652.6	652.6
162.5°	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1	659.4	658.6	658.7
165°	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6	667.7	666.7	666.9
167.5°	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2	673.2
170°	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9	676.9
172.5°	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2	680.3	679.4	679.3
175°	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1	683.3	682.5	682.4
177.5°	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2	684.5	683.8	683.7
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1491.3	1486.8	1482.4	1474.5	1467.8	1458.2	1455.5	1452.1	1442.0	1433.1	1426.3
5°	1582.4	1565.6	1541.1	1518.7	1500.5	1476.0	1461.9	1447.2	1426.1	1407.2	1391.8
7.5°	1677.8	1644.7	1606.5	1565.3	1527.0	1490.0	1460.1	1433.4	1404.0	1376.1	1354.4
10°	1753.5	1705.8	1652.5	1595.1	1546.0	1498.3	1458.4	1423.3	1385.5	1352.5	1325.3
12.5°	1839.8	1769.2	1695.7	1625.9	1567.9	1501.7	1453.3	1408.8	1365.9	1326.2	1295.6
15°	1942.0	1852.3	1765.3	1669.4	1581.0	1498.3	1440.9	1384.8	1335.1	1294.4	1255.2
17.5°	2035.1	1933.4	1818.9	1702.1	1595.6	1497.5	1417.0	1353.7	1291.5	1241.7	1202.6
20°	2087.8	1972.1	1842.5	1721.2	1603.5	1494.2	1405.9	1330.2	1262.8	1210.3	1166.2
22.5°	2133.2	1997.9	1863.8	1734.1	1602.9	1485.1	1385.1	1307.2	1234.3	1182.9	1135.9
25°	2180.2	2018.4	1883.8	1731.7	1585.3	1463.3	1351.2	1262.8	1190.0	1129.7	1081.4
27.5°	2220.6	2017.0	1857.3	1693.7	1557.5	1435.3	1315.5	1220.8	1143.4	1078.0	1028.9
30°	2247.5	2019.7	1829.8	1667.9	1530.6	1404.4	1288.1	1192.8	1111.5	1044.9	998.6
32.5°	2264.3	2018.0	1804.6	1632.1	1488.0	1376.4	1258.4	1159.7	1076.2	1010.8	966.2
35°	2274.1	2005.7	1761.1	1557.9	1419.2	1310.5	1211.7	1109.4	1021.8	960.8	910.3
37.5°	2254.5	1979.8	1710.7	1486.4	1334.5	1227.5	1144.4	1057.2	973.4	906.3	862.8
40°	2223.7	1963.0	1671.4	1436.0	1276.2	1173.1	1102.4	1016.9	934.2	870.4	829.7
42.5°	2164.8	1928.8	1628.3	1379.9	1215.7	1112.6	1047.4	976.0	897.8	837.9	797.3
45°	2021.2	1854.3	1563.5	1295.8	1126.2	1019.7	962.2	910.3	839.5	781.4	746.4
47.5°	1821.9	1742.4	1469.9	1207.1	1032.9	930.4	870.7	828.9	777.2	730.2	696.6
50°	1683.4	1650.4	1406.5	1146.6	970.6	870.4	813.0	775.1	738.0	691.0	660.1
52.5°	1523.6	1543.9	1332.6	1083.7	907.3	808.8	754.7	724.6	690.9	652.3	625.4
55°	1298.6	1372.2	1204.7	978.3	813.0	719.1	667.9	641.2	621.6	592.9	569.8
57.5°	1088.0	1181.6	1066.5	869.7	720.3	639.3	590.2	561.2	548.6	533.6	515.4
60°	963.0	1055.4	967.9	796.8	658.1	580.9	537.5	513.0	500.3	489.9	474.5
62.5°	851.3	944.9	871.4	722.8	596.9	525.5	487.6	463.7	453.9	448.4	435.2
65°	698.0	778.6	729.5	607.6	509.5	446.4	412.1	395.3	386.1	384.1	375.7
67.5°	568.1	629.5	593.7	504.0	426.8	372.3	343.1	328.9	321.8	321.1	314.8
70°	482.9	540.3	513.0	431.7	365.2	322.4	297.1	284.5	280.4	279.6	276.2
72.5°	416.7	456.8	435.1	367.2	315.8	277.0	258.4	245.3	240.5	241.5	239.2
75°	308.4	338.5	325.9	278.9	237.6	212.3	196.9	188.5	184.3	186.5	183.6
77.5°	221.9	240.9	229.6	197.1	171.6	153.4	142.0	136.8	133.0	132.9	131.6
80°	167.5	178.7	172.4	152.8	131.8	116.4	107.2	103.7	101.7	100.9	100.2
82.5°	119.3	128.9	121.4	107.9	93.6	84.4	79.2	74.5	73.0	73.5	72.8
85°	60.3	63.8	61.0	52.5	47.0	42.7	39.9	37.8	36.5	37.2	35.8
87.5°	22.6	22.8	20.9	18.4	17.0	15.2	14.9	13.6	12.7	12.9	12.6
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5	9.2	8.8	8.5
95°	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0	26.4	21.8	17.1
97.5°	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3	60.3	58.2	56.1
100°	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0	88.2	90.5	92.7
102.5°	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8	114.4	116.1	117.7
105°	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6	152.8	154.1	155.2
107.5°	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4	193.4	194.5	195.5
110°	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7	220.6	221.5	222.4





TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8	246.6	247.4	248.2
115°	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3	285.0	285.6	286.3
117.5°	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6	322.4	323.3	324.1
120°	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8	345.8	346.9	347.9
122.5°	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5	369.3	370.1	371.0
125°	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7	401.7	402.6	403.5
127.5°	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1	433.0	433.9	434.8
130°	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7	452.5	453.4	454.3
132.5°	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4	471.3	472.2	473.1
135°	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9	499.6	500.2	501.0
137.5°	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3	524.2	525.0	525.9
140°	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6	540.3	541.0	541.6
142.5°	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6	555.4	556.1	556.7
145°	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7	576.5	577.3	578.1
147.5°	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6	596.1	596.6	597.1
150°	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8	608.1	608.4	608.8
152.5°	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8	618.9	619.0	619.2
155°	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2	634.0	633.7	633.6
157.5°	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2	646.2	646.1	646.1
160°	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5	653.4	653.4	653.2
162.5°	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5	660.1	659.9	659.6
165°	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8	668.4	668.2	667.8
167.5°	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3	674.8	674.4	674.0
170°	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9	678.5	678.1	677.6
172.5°	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4	680.9	680.3	679.8
175°	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6	684.0	683.4	682.9
177.5°	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4	684.9	684.5	684.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1422.4	1418.4	1412.8	1404.4	1397.7	1387.1	1387.1	1388.8	1388.8	1388.2	1387.1
5°	1379.2	1368.7	1356.1	1341.4	1326.0	1310.5	1307.7	1302.1	1297.9	1295.1	1291.6
7.5°	1333.6	1315.0	1296.6	1276.0	1257.2	1241.7	1230.9	1221.9	1216.2	1210.1	1205.5
10°	1302.8	1279.7	1257.9	1236.3	1212.4	1193.5	1181.6	1173.1	1166.9	1161.3	1158.4
12.5°	1266.4	1239.9	1215.9	1195.3	1169.2	1149.8	1138.4	1134.4	1127.0	1115.3	1109.1
15°	1213.1	1188.6	1159.8	1128.3	1115.7	1091.9	1078.5	1072.3	1068.0	1058.9	1056.1
17.5°	1167.5	1135.4	1103.2	1079.7	1056.2	1036.9	1029.5	1021.6	1016.0	1008.6	1006.4
20°	1131.1	1102.4	1072.9	1047.8	1023.1	1002.2	995.9	990.2	984.6	981.1	978.3
22.5°	1094.1	1065.4	1041.0	1017.4	991.2	977.5	970.6	964.5	960.6	958.1	955.4
25°	1042.1	1016.9	989.5	968.5	947.5	938.3	934.2	930.7	927.9	924.3	923.6
27.5°	995.6	968.1	945.9	926.3	911.2	903.7	899.6	897.9	898.5	899.7	900.5
30°	960.8	935.6	917.4	900.5	886.5	879.5	878.8	878.8	881.6	882.3	883.7
32.5°	928.9	908.1	889.9	873.6	863.0	858.2	860.9	860.9	863.1	865.0	867.5
35°	882.3	864.1	850.1	836.1	827.0	829.0	830.5	831.9	835.4	839.5	842.4
37.5°	837.9	822.1	807.4	796.6	792.4	796.1	799.5	802.5	806.5	809.8	812.5
40°	805.9	794.0	780.0	770.2	771.6	773.7	776.5	780.0	783.5	785.6	788.5
42.5°	776.2	763.8	753.1	744.9	746.9	749.6	751.3	753.1	757.2	761.0	762.6
45°	730.9	721.1	711.3	706.4	707.8	709.3	710.6	712.7	716.2	719.1	719.7
47.5°	680.1	673.2	666.6	661.8	664.1	663.5	665.4	669.9	670.9	672.6	676.5
50°	647.6	641.2	633.6	632.1	632.1	632.1	632.8	638.5	638.5	641.2	644.1
52.5°	611.7	607.6	602.7	600.2	599.1	599.1	602.0	604.8	605.9	609.8	612.7
55°	558.6	554.4	550.1	548.0	546.6	548.0	553.7	555.0	558.6	560.6	562.8
57.5°	503.2	500.0	496.6	495.4	495.2	497.0	500.1	504.3	505.2	511.6	514.8
60°	466.7	461.8	459.1	459.1	457.6	464.0	462.5	469.6	470.9	475.2	480.1
62.5°	429.2	422.6	421.5	421.5	423.5	425.3	427.2	430.3	433.9	439.3	443.1
65°	368.6	365.2	370.1	369.3	367.9	372.1	372.1	375.7	379.9	384.8	392.4
67.5°	311.3	309.5	309.9	309.9	312.0	314.4	316.4	319.4	324.5	329.7	334.7
70°	272.6	274.7	271.3	274.0	276.2	276.8	278.2	282.4	288.0	291.5	297.1
72.5°	235.1	234.9	235.3	236.5	238.5	239.8	241.2	246.0	252.2	255.1	259.6
75°	180.8	180.1	182.2	182.2	185.7	187.1	188.5	190.6	196.3	200.5	203.9
77.5°	132.1	132.9	132.4	134.8	133.8	134.1	138.5	140.6	141.2	149.5	151.2
80°	99.5	100.9	101.7	102.3	103.0	101.7	106.6	108.6	108.6	113.5	117.0
82.5°	71.5	72.3	74.2	74.8	75.0	76.4	76.8	78.4	80.1	82.1	86.8
85°	35.8	37.8	38.5	37.8	38.5	37.2	39.2	39.9	40.7	40.7	40.7
87.5°	12.2	13.0	12.8	13.6	13.4	14.2	14.3	13.3	13.4	15.2	12.9
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4	15.2	15.9	16.3
95°	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4	18.1	18.9	19.4
97.5°	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2	19.1	20.0	20.5
100°	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5	19.5	20.4	20.9
102.5°	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8	25.1	22.3	21.0
105°	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3	51.4	31.4	21.5
107.5°	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8	160.2	145.4	130.6
110°	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9	218.2	214.5	204.5



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1	255.2	255.3	253.6
115°	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2	295.3	296.5	297.2
117.5°	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6	330.5	331.4	331.9
120°	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8	353.7	354.5	355.0
122.5°	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4	376.0	376.7	377.0
125°	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3	407.5	407.8	408.0
127.5°	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3	439.7	440.1	440.1
130°	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6	459.1	459.5	459.7
132.5°	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0	477.4	477.9	478.0
135°	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7	505.1	505.3	505.3
137.5°	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4	529.9	530.5	530.7
140°	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1	545.5	546.0	546.1
142.5°	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0	560.4	560.7	560.7
145°	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8	580.9	581.2	581.3
147.5°	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4	599.6	599.9	599.7
150°	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7	611.0	611.2	611.2
152.5°	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9	621.3	621.7	621.6
155°	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8	635.4	636.0	635.9
157.5°	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9	647.6	648.4	648.2
160°	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9	654.5	655.2	655.1
162.5°	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1	660.9	661.7	661.7
165°	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6	669.5	670.4	670.5
167.5°	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1	676.0	676.9	676.9
170°	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8	679.7	680.6	680.6
172.5°	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2	682.1	683.0	683.0
175°	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1	684.9	685.7	685.6
177.5°	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2	685.9	686.6	686.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1383.1	1382.6	1386.5	1383.7	1386.5	1382.6	1383.1	1387.1	1388.2	1388.8	1388.8
5°	1287.4	1289.5	1282.5	1282.5	1282.5	1289.5	1287.4	1291.6	1295.1	1297.9	1302.1
7.5°	1202.2	1199.1	1199.4	1195.6	1199.4	1199.1	1202.2	1205.5	1210.1	1216.2	1221.9
10°	1150.0	1145.8	1144.4	1145.1	1144.4	1145.8	1150.0	1158.4	1161.3	1166.9	1173.1
12.5°	1106.9	1106.0	1096.8	1096.9	1096.8	1106.0	1106.9	1109.1	1115.3	1127.0	1134.4
15°	1056.1	1042.9	1041.4	1045.6	1041.4	1042.9	1056.1	1056.1	1058.9	1068.0	1072.3
17.5°	1005.2	998.3	998.6	996.6	998.6	998.3	1005.2	1006.4	1008.6	1016.0	1021.6
20°	978.3	974.1	973.4	968.5	973.4	974.1	978.3	978.3	981.1	984.6	990.2
22.5°	953.7	952.3	952.7	947.3	952.7	952.3	953.7	955.4	958.1	960.6	964.5
25°	923.0	926.5	923.6	923.6	923.6	926.5	923.0	923.6	924.3	927.9	930.7
27.5°	902.2	902.1	900.7	900.7	900.7	902.1	902.2	900.5	899.7	898.5	897.9
30°	886.5	885.8	887.3	887.3	887.3	885.8	886.5	883.7	882.3	881.6	878.8
32.5°	870.8	871.8	872.1	872.6	872.1	871.8	870.8	867.5	865.0	863.1	860.9
35°	846.6	847.3	849.4	848.0	849.4	847.3	846.6	842.4	839.5	835.4	831.9
37.5°	813.8	817.0	816.3	817.4	816.3	817.0	813.8	812.5	809.8	806.5	802.5
40°	789.1	791.2	790.5	790.5	790.5	791.2	789.1	788.5	785.6	783.5	780.0
42.5°	763.9	765.4	763.6	762.5	763.6	765.4	763.9	762.6	761.0	757.2	753.1
45°	722.6	721.1	723.3	720.4	723.3	721.1	722.6	719.7	719.1	716.2	712.7
47.5°	676.3	677.7	678.2	680.4	678.2	677.7	676.3	676.5	672.6	670.9	669.9
50°	645.4	649.6	649.6	649.0	649.6	649.6	645.4	644.1	641.2	638.5	638.5
52.5°	615.2	617.2	619.9	619.8	619.9	617.2	615.2	612.7	609.8	605.9	604.8
55°	568.4	569.8	571.1	571.9	571.1	569.8	568.4	562.8	560.6	558.6	555.0
57.5°	519.9	519.3	522.6	523.6	522.6	519.3	519.9	514.8	511.6	505.2	504.3
60°	485.6	485.6	491.2	493.4	491.2	485.6	485.6	480.1	475.2	470.9	469.6
62.5°	449.2	451.5	457.1	454.1	457.1	451.5	449.2	443.1	439.3	433.9	430.3
65°	395.9	401.5	400.8	403.7	400.8	401.5	395.9	392.4	384.8	379.9	375.7
67.5°	340.3	343.8	348.8	349.3	348.8	343.8	340.3	334.7	329.7	324.5	319.4
70°	302.7	306.2	309.1	311.1	309.1	306.2	302.7	297.1	291.5	288.0	282.4
72.5°	266.4	268.1	274.8	271.9	274.8	268.1	266.4	259.6	255.1	252.2	246.0
75°	208.8	213.7	217.9	215.9	217.9	213.7	208.8	203.9	200.5	196.3	190.6
77.5°	154.4	159.3	161.3	159.5	161.3	159.3	154.4	151.2	149.5	141.2	140.6
80°	122.0	121.3	125.5	124.8	125.5	121.3	122.0	117.0	113.5	108.6	108.6
82.5°	89.4	88.7	90.7	91.1	90.7	88.7	89.4	86.8	82.1	80.1	78.4
85°	43.4	45.6	42.7	42.1	42.7	45.6	43.4	40.7	40.7	40.7	39.9
87.5°	13.0	13.0	12.6	12.0	12.6	13.0	13.0	12.9	15.2	13.4	13.3
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1
92.5°	16.5	16.6	16.8	16.9	16.8	16.6	16.5	16.3	15.9	15.2	14.4
95°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.9	18.1	17.4
97.5°	20.6	20.7	20.9	21.0	20.9	20.7	20.6	20.5	20.0	19.1	18.2
100°	21.0	21.1	21.2	21.4	21.2	21.1	21.0	20.9	20.4	19.5	18.5
102.5°	21.1	21.4	21.6	21.8	21.6	21.4	21.1	21.0	22.3	25.1	27.8
105°	21.7	21.9	22.1	22.4	22.1	21.9	21.7	21.5	31.4	51.4	71.3
107.5°	115.5	100.4	85.3	70.3	85.3	100.4	115.5	130.6	145.4	160.2	174.8
110°	188.3	172.2	156.0	139.8	156.0	172.2	188.3	204.5	214.5	218.2	221.9



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	250.2	246.7	243.3	240.0	243.3	246.7	250.2	253.6	255.3	255.2	255.1
115°	297.7	298.2	298.6	299.1	298.6	298.2	297.7	297.2	296.5	295.3	294.2
117.5°	332.0	332.1	332.2	332.3	332.2	332.1	332.0	331.9	331.4	330.5	329.6
120°	355.0	355.0	355.0	355.0	355.0	355.0	355.0	355.0	354.5	353.7	352.8
122.5°	377.1	377.2	377.3	377.4	377.3	377.2	377.1	377.0	376.7	376.0	375.4
125°	408.2	408.5	408.7	408.9	408.7	408.5	408.2	408.0	407.8	407.5	407.3
127.5°	439.9	439.7	439.4	439.3	439.4	439.7	439.9	440.1	440.1	439.7	439.3
130°	459.4	459.2	459.0	458.8	459.0	459.2	459.4	459.7	459.5	459.1	458.6
132.5°	477.6	477.2	477.0	476.6	477.0	477.2	477.6	478.0	477.9	477.4	477.0
135°	505.1	504.7	504.4	504.0	504.4	504.7	505.1	505.3	505.3	505.1	504.7
137.5°	530.4	530.2	529.9	529.8	529.9	530.2	530.4	530.7	530.5	529.9	529.4
140°	545.9	545.6	545.5	545.2	545.5	545.6	545.9	546.1	546.0	545.5	545.1
142.5°	560.4	560.1	559.7	559.5	559.7	560.1	560.4	560.7	560.7	560.4	560.0
145°	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.3	581.2	580.9	580.8
147.5°	599.1	598.6	598.2	597.6	598.2	598.6	599.1	599.7	599.9	599.6	599.4
150°	610.8	610.5	610.1	609.8	610.1	610.5	610.8	611.2	611.2	611.0	610.7
152.5°	621.2	620.6	620.1	619.6	620.1	620.6	621.2	621.6	621.7	621.3	620.9
155°	635.3	634.5	633.9	633.2	633.9	634.5	635.3	635.9	636.0	635.4	634.8
157.5°	647.3	646.5	645.6	644.7	645.6	646.5	647.3	648.2	648.4	647.6	646.9
160°	654.4	653.6	652.8	652.0	652.8	653.6	654.4	655.1	655.2	654.5	653.9
162.5°	661.0	660.3	659.6	659.0	659.6	660.3	661.0	661.7	661.7	660.9	660.1
165°	669.7	668.9	668.1	667.3	668.1	668.9	669.7	670.5	670.4	669.5	668.6
167.5°	676.0	675.1	674.2	673.2	674.2	675.1	676.0	676.9	676.9	676.0	675.1
170°	679.7	678.8	677.9	676.9	677.9	678.8	679.7	680.6	680.6	679.7	678.8
172.5°	682.0	681.0	679.9	678.9	679.9	681.0	682.0	683.0	683.0	682.1	681.2
175°	684.7	683.9	683.0	682.0	683.0	683.9	684.7	685.6	685.7	684.9	684.1
177.5°	685.6	684.7	683.9	683.0	683.9	684.7	685.6	686.5	686.6	685.9	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1387.1	1387.1	1397.7	1404.4	1412.8	1418.4	1422.4	1426.3	1433.1	1442.0	1452.1
5°	1307.7	1310.5	1326.0	1341.4	1356.1	1368.7	1379.2	1391.8	1407.2	1426.1	1447.2
7.5°	1230.9	1241.7	1257.2	1276.0	1296.6	1315.0	1333.6	1354.4	1376.1	1404.0	1433.4
10°	1181.6	1193.5	1212.4	1236.3	1257.9	1279.7	1302.8	1325.3	1352.5	1385.5	1423.3
12.5°	1138.4	1149.8	1169.2	1195.3	1215.9	1239.9	1266.4	1295.6	1326.2	1365.9	1408.8
15°	1078.5	1091.9	1115.7	1128.3	1159.8	1188.6	1213.1	1255.2	1294.4	1335.1	1384.8
17.5°	1029.5	1036.9	1056.2	1079.7	1103.2	1135.4	1167.5	1202.6	1241.7	1291.5	1353.7
20°	995.9	1002.2	1023.1	1047.8	1072.9	1102.4	1131.1	1166.2	1210.3	1262.8	1330.2
22.5°	970.6	977.5	991.2	1017.4	1041.0	1065.4	1094.1	1135.9	1182.9	1234.3	1307.2
25°	934.2	938.3	947.5	968.5	989.5	1016.9	1042.1	1081.4	1129.7	1190.0	1262.8
27.5°	899.6	903.7	911.2	926.3	945.9	968.1	995.6	1028.9	1078.0	1143.4	1220.8
30°	878.8	879.5	886.5	900.5	917.4	935.6	960.8	998.6	1044.9	1111.5	1192.8
32.5°	860.9	858.2	863.0	873.6	889.9	908.1	928.9	966.2	1010.8	1076.2	1159.7
35°	830.5	829.0	827.0	836.1	850.1	864.1	882.3	910.3	960.8	1021.8	1109.4
37.5°	799.5	796.1	792.4	796.6	807.4	822.1	837.9	862.8	906.3	973.4	1057.2
40°	776.5	773.7	771.6	770.2	780.0	794.0	805.9	829.7	870.4	934.2	1016.9
42.5°	751.3	749.6	746.9	744.9	753.1	763.8	776.2	797.3	837.9	897.8	976.0
45°	710.6	709.3	707.8	706.4	711.3	721.1	730.9	746.4	781.4	839.5	910.3
47.5°	665.4	663.5	664.1	661.8	666.6	673.2	680.1	696.6	730.2	777.2	828.9
50°	632.8	632.1	632.1	632.1	633.6	641.2	647.6	660.1	691.0	738.0	775.1
52.5°	602.0	599.1	599.1	600.2	602.7	607.6	611.7	625.4	652.3	690.9	724.6
55°	553.7	548.0	546.6	548.0	550.1	554.4	558.6	569.8	592.9	621.6	641.2
57.5°	500.1	497.0	495.2	495.4	496.6	500.0	503.2	515.4	533.6	548.6	561.2
60°	462.5	464.0	457.6	459.1	459.1	461.8	466.7	474.5	489.9	500.3	513.0
62.5°	427.2	425.3	423.5	421.5	421.5	422.6	429.2	435.2	448.4	453.9	463.7
65°	372.1	372.1	367.9	369.3	370.1	365.2	368.6	375.7	384.1	386.1	395.3
67.5°	316.4	314.4	312.0	309.9	309.9	309.5	311.3	314.8	321.1	321.8	328.9
70°	278.2	276.8	276.2	274.0	271.3	274.7	272.6	276.2	279.6	280.4	284.5
72.5°	241.2	239.8	238.5	236.5	235.3	234.9	235.1	239.2	241.5	240.5	245.3
75°	188.5	187.1	185.7	182.2	182.2	180.1	180.8	183.6	186.5	184.3	188.5
77.5°	138.5	134.1	133.8	134.8	132.4	132.9	132.1	131.6	132.9	133.0	136.8
80°	106.6	101.7	103.0	102.3	101.7	100.9	99.5	100.2	100.9	101.7	103.7
82.5°	76.8	76.4	75.0	74.8	74.2	72.3	71.5	72.8	73.5	73.0	74.5
85°	39.2	37.2	38.5	37.8	38.5	37.8	35.8	35.8	37.2	36.5	37.8
87.5°	14.3	14.2	13.4	13.6	12.8	13.0	12.2	12.6	12.9	12.7	13.6
90°	12.7	12.2	10.7	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5
92.5°	13.7	13.0	11.9	10.8	9.7	8.6	8.2	8.5	8.8	9.2	9.5
95°	16.6	15.8	14.5	13.3	12.0	10.8	12.5	17.1	21.8	26.4	31.0
97.5°	17.3	16.4	24.5	32.6	40.8	49.0	54.0	56.1	58.2	60.3	62.3
100°	17.7	16.8	34.4	52.1	69.6	87.3	95.0	92.7	90.5	88.2	86.0
102.5°	30.7	33.4	52.7	72.0	91.2	110.5	119.3	117.7	116.1	114.4	112.8
105°	91.4	111.4	121.5	131.7	141.9	152.0	156.5	155.2	154.1	152.8	151.6
107.5°	189.5	204.1	202.5	200.9	199.3	197.7	196.4	195.5	194.5	193.4	192.4
110°	225.6	229.3	228.1	226.9	225.6	224.4	223.3	222.4	221.5	220.6	219.7



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	255.1	255.0	253.8	252.5	251.3	250.0	249.0	248.2	247.4	246.6	245.8
115°	293.1	291.9	290.9	289.9	288.9	287.8	287.0	286.3	285.6	285.0	284.3
117.5°	328.7	327.7	327.3	326.7	326.2	325.7	324.9	324.1	323.3	322.4	321.6
120°	351.9	350.9	350.6	350.3	349.9	349.6	348.9	347.9	346.9	345.8	344.8
122.5°	374.8	374.2	373.7	373.3	372.8	372.4	371.8	371.0	370.1	369.3	368.5
125°	407.1	406.9	406.4	406.0	405.6	405.1	404.4	403.5	402.6	401.7	400.7
127.5°	439.0	438.6	438.1	437.6	436.9	436.4	435.7	434.8	433.9	433.0	432.1
130°	458.2	457.7	457.3	456.8	456.4	455.9	455.2	454.3	453.4	452.5	451.7
132.5°	476.5	476.1	475.6	475.3	474.9	474.6	473.9	473.1	472.2	471.3	470.4
135°	504.4	504.0	503.5	503.1	502.7	502.2	501.7	501.0	500.2	499.6	498.9
137.5°	528.9	528.3	528.1	527.8	527.5	527.4	526.7	525.9	525.0	524.2	523.3
140°	544.7	544.2	543.9	543.5	543.1	542.9	542.3	541.6	541.0	540.3	539.6
142.5°	559.6	559.3	558.9	558.6	558.2	557.9	557.4	556.7	556.1	555.4	554.6
145°	580.5	580.3	580.1	579.9	579.6	579.4	578.9	578.1	577.3	576.5	575.7
147.5°	599.1	599.0	598.7	598.4	598.2	598.0	597.6	597.1	596.6	596.1	595.6
150°	610.6	610.3	610.1	609.8	609.7	609.4	609.1	608.8	608.4	608.1	607.8
152.5°	620.5	620.1	619.9	619.8	619.6	619.6	619.4	619.2	619.0	618.9	618.8
155°	634.3	633.7	633.6	633.5	633.4	633.3	633.3	633.6	633.7	634.0	634.2
157.5°	646.3	645.6	645.7	645.9	646.0	646.0	646.1	646.1	646.1	646.2	646.2
160°	653.2	652.6	652.6	652.7	652.8	653.0	653.1	653.2	653.4	653.4	653.5
162.5°	659.4	658.6	658.7	658.9	659.0	659.1	659.2	659.6	659.9	660.1	660.5
165°	667.7	666.7	666.9	667.0	667.1	667.2	667.4	667.8	668.2	668.4	668.8
167.5°	674.2	673.2	673.2	673.2	673.2	673.2	673.5	674.0	674.4	674.8	675.3
170°	677.9	676.9	676.9	676.9	676.9	676.9	677.2	677.6	678.1	678.5	678.9
172.5°	680.3	679.4	679.3	679.2	679.1	679.0	679.2	679.8	680.3	680.9	681.4
175°	683.3	682.5	682.4	682.3	682.2	682.1	682.3	682.9	683.4	684.0	684.6
177.5°	684.5	683.8	683.7	683.6	683.5	683.4	683.6	684.0	684.5	684.9	685.4
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1455.5	1458.2	1467.8	1474.5	1482.4	1486.8	1491.3	1494.7	1499.1	1500.3	1516.5
5°	1461.9	1476.0	1500.5	1518.7	1541.1	1565.6	1582.4	1590.2	1610.4	1627.3	1660.9
7.5°	1460.1	1490.0	1527.0	1565.3	1606.5	1644.7	1677.8	1717.0	1744.9	1786.8	1828.2
10°	1458.4	1498.3	1546.0	1595.1	1652.5	1705.8	1753.5	1806.7	1850.8	1909.0	1958.7
12.5°	1453.3	1501.7	1567.9	1625.9	1695.7	1769.2	1839.8	1908.2	1947.3	2044.2	2090.0
15°	1440.9	1498.3	1581.0	1669.4	1765.3	1852.3	1942.0	2013.5	2129.0	2213.9	2267.8
17.5°	1417.0	1497.5	1595.6	1702.1	1818.9	1933.4	2035.1	2143.5	2266.2	2368.7	2478.1
20°	1405.9	1494.2	1603.5	1721.2	1842.5	1972.1	2087.8	2218.0	2352.0	2452.8	2593.0
22.5°	1385.1	1485.1	1602.9	1734.1	1863.8	1997.9	2133.2	2264.6	2419.2	2558.2	2691.7
25°	1351.2	1463.3	1585.3	1731.7	1883.8	2018.4	2180.2	2354.7	2516.0	2694.7	2827.8
27.5°	1315.5	1435.3	1557.5	1693.7	1857.3	2017.0	2220.6	2417.8	2614.9	2769.2	2867.7
30°	1288.1	1404.4	1530.6	1667.9	1829.8	2019.7	2247.5	2462.6	2654.7	2787.1	2842.5
32.5°	1258.4	1376.4	1488.0	1632.1	1804.6	2018.0	2264.3	2489.0	2656.9	2745.1	2734.3
35°	1211.7	1310.5	1419.2	1557.9	1761.1	2005.7	2274.1	2491.4	2594.4	2575.5	2432.5
37.5°	1144.4	1227.5	1334.5	1486.4	1710.7	1979.8	2254.5	2417.5	2410.8	2256.7	2049.6
40°	1102.4	1173.1	1276.2	1436.0	1671.4	1963.0	2223.7	2329.5	2239.8	2024.6	1776.6
42.5°	1047.4	1112.6	1215.7	1379.9	1628.3	1928.8	2164.8	2195.5	2020.0	1772.4	1545.0
45°	962.2	1019.7	1126.2	1295.8	1563.5	1854.3	2021.2	1946.2	1709.9	1454.2	1281.1
47.5°	870.7	930.4	1032.9	1207.1	1469.9	1742.4	1821.9	1662.3	1419.9	1212.4	1053.5
50°	813.0	870.4	970.6	1146.6	1406.5	1650.4	1683.4	1477.3	1254.5	1072.3	941.9
52.5°	754.7	808.8	907.3	1083.7	1332.6	1543.9	1523.6	1313.6	1108.7	953.4	851.0
55°	667.9	719.1	813.0	978.3	1204.7	1372.2	1298.6	1098.1	928.5	808.1	730.2
57.5°	590.2	639.3	720.3	869.7	1066.5	1181.6	1088.0	919.1	784.2	691.4	633.4
60°	537.5	580.9	658.1	796.8	967.9	1055.4	963.0	813.7	700.1	625.8	574.0
62.5°	487.6	525.5	596.9	722.8	871.4	944.9	851.3	725.1	628.4	562.5	518.4
65°	412.1	446.4	509.5	607.6	729.5	778.6	698.0	595.7	520.7	471.6	442.2
67.5°	343.1	372.3	426.8	504.0	593.7	629.5	568.1	488.9	432.4	393.0	369.6
70°	297.1	322.4	365.2	431.7	513.0	540.3	482.9	417.7	376.3	344.8	323.1
72.5°	258.4	277.0	315.8	367.2	435.1	456.8	416.7	359.4	320.8	297.1	279.9
75°	196.9	212.3	237.6	278.9	325.9	338.5	308.4	272.6	246.6	229.9	216.5
77.5°	142.0	153.4	171.6	197.1	229.6	240.9	221.9	198.0	179.1	167.7	160.3
80°	107.2	116.4	131.8	152.8	172.4	178.7	167.5	149.3	136.0	129.7	123.3
82.5°	79.2	84.4	93.6	107.9	121.4	128.9	119.3	108.3	101.2	95.4	93.1
85°	39.9	42.7	47.0	52.5	61.0	63.8	60.3	57.4	53.2	49.8	49.8
87.5°	14.9	15.2	17.0	18.4	20.9	22.8	22.6	21.8	21.5	21.0	20.6
90°	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1
92.5°	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7	14.4
95°	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6	17.4
97.5°	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3	18.2
100°	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7	18.5
102.5°	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7	27.8
105°	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4	71.3
107.5°	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5	174.8
110°	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6	221.9





TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1	255.1
115°	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1	294.2
117.5°	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7	329.6
120°	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9	352.8
122.5°	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8	375.4
125°	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1	407.3
127.5°	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0	439.3
130°	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2	458.6
132.5°	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5	477.0
135°	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4	504.7
137.5°	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9	529.4
140°	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7	545.1
142.5°	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6	560.0
145°	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5	580.8
147.5°	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1	599.4
150°	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6	610.7
152.5°	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5	620.9
155°	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3	634.8
157.5°	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3	646.9
160°	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2	653.9
162.5°	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4	660.1
165°	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7	668.6
167.5°	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2	675.1
170°	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9	678.8
172.5°	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3	681.2
175°	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3	684.1
177.5°	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5	685.2
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1522.2	1522.7	1528.9	1533.4	1531.2	1533.9	1535.1
5°	1663.0	1688.3	1701.6	1711.4	1712.1	1712.8	1718.4
7.5°	1862.8	1889.8	1909.6	1939.6	1948.6	1958.7	1955.8
10°	2008.6	2048.4	2082.9	2101.0	2120.7	2149.4	2126.3
12.5°	2144.7	2215.5	2267.8	2296.2	2314.6	2320.4	2309.1
15°	2369.5	2461.9	2511.7	2510.3	2573.4	2600.8	2558.0
17.5°	2575.5	2660.9	2729.3	2764.3	2816.8	2828.5	2823.2
20°	2701.6	2794.9	2848.1	2908.4	2935.7	2960.2	2964.4
22.5°	2810.4	2894.0	2951.3	3001.4	3024.3	3035.9	3043.0
25°	2922.4	2988.3	3022.6	3040.1	3046.4	3045.0	3035.9
27.5°	2914.6	2919.7	2881.9	2844.7	2811.6	2774.1	2761.2
30°	2839.0	2780.1	2675.0	2615.5	2527.8	2458.4	2486.4
32.5°	2640.0	2522.8	2404.8	2274.6	2166.8	2136.1	2105.2
35°	2253.1	2047.1	1926.5	1786.4	1730.3	1674.3	1635.7
37.5°	1822.8	1663.5	1520.5	1428.8	1372.6	1337.1	1318.1
40°	1576.1	1432.4	1314.7	1240.5	1197.7	1157.7	1152.2
42.5°	1379.4	1245.8	1157.2	1098.1	1056.9	1040.0	1027.7
45°	1129.7	1036.5	977.0	934.9	907.6	897.1	883.1
47.5°	956.2	890.3	845.6	817.0	796.4	788.5	787.5
50°	859.2	804.5	771.6	749.1	733.1	730.2	719.1
52.5°	786.3	739.0	713.3	693.7	682.1	674.2	670.8
55°	682.6	651.0	627.9	616.7	607.6	599.9	599.9
57.5°	597.3	570.9	555.6	546.1	543.2	537.8	534.3
60°	544.6	522.1	510.2	501.8	496.1	496.9	490.5
62.5°	492.9	478.4	467.0	458.6	451.9	452.0	452.5
65°	419.8	408.6	400.2	397.3	393.2	388.3	389.7
67.5°	355.7	345.2	338.7	333.9	332.4	329.8	333.9
70°	309.8	302.0	297.1	292.9	291.5	292.2	295.8
72.5°	267.7	262.3	259.0	257.1	254.0	254.1	256.5
75°	210.3	206.1	203.2	201.2	200.5	200.5	200.5
77.5°	154.4	153.5	152.2	149.1	149.3	150.1	150.3
80°	122.0	119.8	119.1	117.7	115.7	114.2	117.7
82.5°	91.1	89.0	88.3	88.0	84.8	84.5	87.5
85°	49.0	47.0	47.6	47.0	47.0	46.3	46.3
87.5°	20.1	19.6	19.2	19.7	19.3	18.7	19.9
90°	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	218.2	214.5	204.5	188.3	172.2	156.0	139.8



TEST NUMBER: P332054-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)