

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332056-940

Luminaire Tested: **S123DIP-S1165D585U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332056-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6258.0 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	70		
1	103	98	94	91	97	93	90	87	83	81	78	75	73	71	66	65	64	64	64	64	64	64	64	60		
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	56	54	54	54	54	54	54	54	50		
3	86	76	69	63	81	72	66	60	65	60	56	59	54	51	52	49	46	46	46	46	46	46	46	43		
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	40	40	40	40	40	40	37		
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35	35	35	35	35	35	35	32		
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	31	31	31	31	31	31	29		
7	62	49	41	36	58	47	40	34	43	37	32	39	34	30	35	31	28	28	28	28	28	28	28	25		
8	58	45	37	32	54	43	36	31	39	33	29	36	31	27	32	28	25	25	25	25	25	25	25	23		
9	54	41	34	28	51	39	32	27	36	30	26	33	28	24	30	26	23	23	23	23	23	23	23	21		
10	50	38	30	26	48	36	29	25	33	27	23	30	25	22	28	24	20	20	20	20	20	20	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15569	15569	15569	15569
5°	18567	15637	13857	15637
10°	23240	15557	12516	15557
15°	28505	15432	11652	15432
20°	33956	15237	11094	15237
25°	36056	14998	10969	14998
30°	30904	14825	11028	14825
35°	21494	14578	11143	14578
40°	16190	14289	11108	14289
45°	13443	13857	10966	13857
50°	12042	12980	10868	12980
55°	11258	12033	10732	12033
60°	10559	11044	10622	11044
65°	9926	10068	10282	10068
70°	9309	8954	9791	8954
75°	8339	7839	8979	7839
80°	7296	6428	7736	6428
85°	5718	4668	5199	4668



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.5	2.3
10°-20°	456.9	7.3
20°-30°	766.8	12.3
30°-40°	868.3	13.9
40°-50°	778.6	12.4
50°-60°	628.3	10.0
60°-70°	437.9	7.0
70°-80°	230.1	3.7
80°-90°	58.2	0.9
90°-100°	139.8	2.2
100°-110°	395.9	6.3
110°-120°	389.5	6.2
120°-130°	310.7	5.0
130°-140°	244.9	3.9
140°-150°	182.8	2.9
150°-160°	127.4	2.0
160°-170°	74.9	1.2
170°-180°	24.4	0.4
0°-30°	1366.2	21.8
0°-40°	2234.5	35.7
0°-60°	3641.5	58.2
0°-90°	4367.7	69.8
90°-120°	925.2	14.8
90°-150°	1663.7	26.6
90°-180°	1890.0	30.2
0°-180°	6258.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1446	1446	1446	1446	1446	
5°	1718	1447	1282	1447	1718	178
15°	2558	1385	1046	1385	2558	739
25°	3036	1263	924	1263	3036	1331
35°	1636	1109	848	1109	1636	1063
45°	883	910	720	910	883	699
55°	600	641	572	641	600	538
65°	390	395	404	395	390	388
75°	200	188	216	188	200	215
85°	46	38	42	38	46	55
90°	15	1	15	1	15	10
95°	59	17	59	17	59	106
105°	647	59	647	59	647	638
115°	787	104	787	104	787	764
125°	620	145	620	145	620	562
135°	503	170	503	170	503	390
145°	393	194	393	194	393	250
155°	326	220	326	220	326	152
165°	284	241	284	241	284	81
175°	256	251	256	251	256	25
180°	251	251	251	251	251	



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1535.1	1533.9	1531.2	1533.4	1528.9	1522.7	1522.2	1516.5	1500.3	1499.1	1494.7
5°	1718.4	1712.8	1712.1	1711.4	1701.6	1688.3	1663.0	1660.9	1627.3	1610.4	1590.2
7.5°	1955.8	1958.7	1948.6	1939.6	1909.6	1889.8	1862.8	1828.2	1786.8	1744.9	1717.0
10°	2126.3	2149.4	2120.7	2101.0	2082.9	2048.4	2008.6	1958.7	1909.0	1850.8	1806.7
12.5°	2309.1	2320.4	2314.6	2296.2	2267.8	2215.5	2144.7	2090.0	2044.2	1947.3	1908.2
15°	2558.0	2600.8	2573.4	2510.3	2511.7	2461.9	2369.5	2267.8	2213.9	2129.0	2013.5
17.5°	2823.2	2828.5	2816.8	2764.3	2729.3	2660.9	2575.5	2478.1	2368.7	2266.2	2143.5
20°	2964.4	2960.2	2935.7	2908.4	2848.1	2794.9	2701.6	2593.0	2452.8	2352.0	2218.0
22.5°	3043.0	3035.9	3024.3	3001.4	2951.3	2894.0	2810.4	2691.7	2558.2	2419.2	2264.6
25°	3035.9	3045.0	3046.4	3040.1	3022.6	2988.3	2922.4	2827.8	2694.7	2516.0	2354.7
27.5°	2761.2	2774.1	2811.6	2844.7	2881.9	2919.7	2914.6	2867.7	2769.2	2614.9	2417.8
30°	2486.4	2458.4	2527.8	2615.5	2675.0	2780.1	2839.0	2842.5	2787.1	2654.7	2462.6
32.5°	2105.2	2136.1	2166.8	2274.6	2404.8	2522.8	2640.0	2734.3	2745.1	2656.9	2489.0
35°	1635.7	1674.3	1730.3	1786.4	1926.5	2047.1	2253.1	2432.5	2575.5	2594.4	2491.4
37.5°	1318.1	1337.1	1372.6	1428.8	1520.5	1663.5	1822.8	2049.6	2256.7	2410.8	2417.5
40°	1152.2	1157.7	1197.7	1240.5	1314.7	1432.4	1576.1	1776.6	2024.6	2239.8	2329.5
42.5°	1027.7	1040.0	1056.9	1098.1	1157.2	1245.8	1379.4	1545.0	1772.4	2020.0	2195.5
45°	883.1	897.1	907.6	934.9	977.0	1036.5	1129.7	1281.1	1454.2	1709.9	1946.2
47.5°	787.5	788.5	796.4	817.0	845.6	890.3	956.2	1053.5	1212.4	1419.9	1662.3
50°	719.1	730.2	733.1	749.1	771.6	804.5	859.2	941.9	1072.3	1254.5	1477.3
52.5°	670.8	674.2	682.1	693.7	713.3	739.0	786.3	851.0	953.4	1108.7	1313.6
55°	599.9	599.9	607.6	616.7	627.9	651.0	682.6	730.2	808.1	928.5	1098.1
57.5°	534.3	537.8	543.2	546.1	555.6	570.9	597.3	633.4	691.4	784.2	919.1
60°	490.5	496.9	496.1	501.8	510.2	522.1	544.6	574.0	625.8	700.1	813.7
62.5°	452.5	452.0	451.9	458.6	467.0	478.4	492.9	518.4	562.5	628.4	725.1
65°	389.7	388.3	393.2	397.3	400.2	408.6	419.8	442.2	471.6	520.7	595.7
67.5°	333.9	329.8	332.4	333.9	338.7	345.2	355.7	369.6	393.0	432.4	488.9
70°	295.8	292.2	291.5	292.9	297.1	302.0	309.8	323.1	344.8	376.3	417.7
72.5°	256.5	254.1	254.0	257.1	259.0	262.3	267.7	279.9	297.1	320.8	359.4
75°	200.5	200.5	200.5	201.2	203.2	206.1	210.3	216.5	229.9	246.6	272.6
77.5°	150.3	150.1	149.3	149.1	152.2	153.5	154.4	160.3	167.7	179.1	198.0
80°	117.7	114.2	115.7	117.7	119.1	119.8	122.0	123.3	129.7	136.0	149.3
82.5°	87.5	84.5	84.8	88.0	88.3	89.0	91.1	93.1	95.4	101.2	108.3
85°	46.3	46.3	47.0	47.0	47.6	47.0	49.0	49.8	49.8	53.2	57.4
87.5°	19.8	18.7	19.2	19.7	19.2	19.5	20.1	20.5	21.0	21.6	21.8
90°	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8	12.2	12.8	11.1
92.5°	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8	59.0	78.2	86.1
95°	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1	244.6	301.6	268.6
97.5°	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5	500.1	467.4	342.1
100°	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7	581.8	481.6	325.5
102.5°	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3	585.9	455.2	301.1
105°	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2	554.9	408.9	271.1
107.5°	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1	500.6	368.0	252.0
110°	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8	466.4	344.8	244.6



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0	436.7	329.4	240.6
115°	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9	400.8	312.8	239.1
117.5°	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5	379.2	303.0	240.0
120°	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4	367.7	298.5	241.6
122.5°	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4	358.4	295.7	244.4
125°	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3	346.3	291.9	248.7
127.5°	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8	335.8	290.1	253.6
130°	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9	330.1	288.9	256.8
132.5°	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7	324.8	288.5	259.3
135°	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0	317.9	287.8	263.0
137.5°	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5	311.9	286.8	265.4
140°	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2	308.2	286.3	267.0
142.5°	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2	305.0	285.5	268.2
145°	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8	300.6	284.3	269.0
147.5°	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0	296.3	282.4	269.0
150°	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1	293.5	280.7	269.0
152.5°	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7	290.3	278.7	267.9
155°	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0	285.3	275.2	266.5
157.5°	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9	279.8	272.0	264.7
160°	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8	276.2	269.6	263.9
162.5°	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9	272.5	267.2	262.3
165°	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6	267.5	263.5	259.9
167.5°	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1	262.8	259.8	257.4
170°	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4	259.9	257.3	255.8
172.5°	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2	257.1	255.3	254.6
175°	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9	253.8	252.8	252.8
177.5°	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1	251.6	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1491.3	1486.8	1482.4	1474.5	1467.8	1458.2	1455.5	1452.1	1442.0	1433.1	1426.3
5°	1582.4	1565.6	1541.1	1518.7	1500.5	1476.0	1461.9	1447.2	1426.1	1407.2	1391.8
7.5°	1677.8	1644.7	1606.5	1565.3	1527.0	1490.0	1460.1	1433.4	1404.0	1376.1	1354.4
10°	1753.5	1705.8	1652.5	1595.1	1546.0	1498.3	1458.4	1423.3	1385.5	1352.5	1325.3
12.5°	1839.8	1769.2	1695.7	1625.9	1567.9	1501.7	1453.3	1408.8	1365.9	1326.2	1295.6
15°	1942.0	1852.3	1765.3	1669.4	1581.0	1498.3	1440.9	1384.8	1335.1	1294.4	1255.2
17.5°	2035.1	1933.4	1818.9	1702.1	1595.6	1497.5	1417.0	1353.7	1291.5	1241.7	1202.6
20°	2087.8	1972.1	1842.5	1721.2	1603.5	1494.2	1405.9	1330.2	1262.8	1210.3	1166.2
22.5°	2133.2	1997.9	1863.8	1734.1	1602.9	1485.1	1385.1	1307.2	1234.3	1182.9	1135.9
25°	2180.2	2018.4	1883.8	1731.7	1585.3	1463.3	1351.2	1262.8	1190.0	1129.7	1081.4
27.5°	2220.6	2017.0	1857.3	1693.7	1557.5	1435.3	1315.5	1220.8	1143.4	1078.0	1028.9
30°	2247.5	2019.7	1829.8	1667.9	1530.6	1404.4	1288.1	1192.8	1111.5	1044.9	998.6
32.5°	2264.3	2018.0	1804.6	1632.1	1488.0	1376.4	1258.4	1159.7	1076.2	1010.8	966.2
35°	2274.1	2005.7	1761.1	1557.9	1419.2	1310.5	1211.7	1109.4	1021.8	960.8	910.3
37.5°	2254.5	1979.8	1710.7	1486.4	1334.5	1227.5	1144.4	1057.2	973.4	906.3	862.8
40°	2223.7	1963.0	1671.4	1436.0	1276.2	1173.1	1102.4	1016.9	934.2	870.4	829.7
42.5°	2164.8	1928.8	1628.3	1379.9	1215.7	1112.6	1047.4	976.0	897.8	837.9	797.3
45°	2021.2	1854.3	1563.5	1295.8	1126.2	1019.7	962.2	910.3	839.5	781.4	746.4
47.5°	1821.9	1742.4	1469.9	1207.1	1032.9	930.4	870.7	828.9	777.2	730.2	696.6
50°	1683.4	1650.4	1406.5	1146.6	970.6	870.4	813.0	775.1	738.0	691.0	660.1
52.5°	1523.6	1543.9	1332.6	1083.7	907.3	808.8	754.7	724.6	690.9	652.3	625.4
55°	1298.6	1372.2	1204.7	978.3	813.0	719.1	667.9	641.2	621.6	592.9	569.8
57.5°	1088.0	1181.6	1066.5	869.7	720.3	639.3	590.2	561.2	548.6	533.6	515.4
60°	963.0	1055.4	967.9	796.8	658.1	580.9	537.5	513.0	500.3	489.9	474.5
62.5°	851.3	944.9	871.4	722.8	596.9	525.5	487.6	463.7	453.9	448.4	435.2
65°	698.0	778.6	729.5	607.6	509.5	446.4	412.1	395.3	386.1	384.1	375.7
67.5°	568.1	629.5	593.7	504.0	426.8	372.3	343.1	328.9	321.8	321.1	314.8
70°	482.9	540.3	513.0	431.7	365.2	322.4	297.1	284.5	280.4	279.6	276.2
72.5°	416.7	456.8	435.1	367.2	315.8	277.0	258.4	245.3	240.5	241.5	239.2
75°	308.4	338.5	325.9	278.9	237.6	212.3	196.9	188.5	184.3	186.5	183.6
77.5°	221.9	240.9	229.6	197.1	171.6	153.4	142.0	136.8	133.0	132.9	131.6
80°	167.5	178.7	172.4	152.8	131.8	116.4	107.2	103.7	101.7	100.9	100.2
82.5°	119.3	128.9	121.4	107.9	93.6	84.4	79.2	74.5	73.0	73.5	72.8
85°	60.3	63.8	61.0	52.5	47.0	42.7	39.9	37.8	36.5	37.2	35.8
87.5°	22.6	22.9	21.0	18.5	17.2	15.2	15.0	13.6	12.8	12.9	12.7
90°	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0	2.1	3.0	4.5
92.5°	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3	9.4	13.6	17.6
95°	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3	18.8	24.4	33.1
97.5°	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5	30.1	34.4	41.9
100°	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6	38.2	41.7	48.9
102.5°	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2	47.1	50.3	57.0
105°	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0	60.5	63.6	69.6
107.5°	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6	74.2	77.1	83.1
110°	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4	83.9	86.5	92.0



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3	92.9	95.4	101.0
115°	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2	106.3	109.3	114.4
117.5°	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2	119.5	122.1	126.7
120°	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2	127.7	130.2	135.3
122.5°	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8	135.4	137.9	143.4
125°	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0	146.0	149.0	154.6
127.5°	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4	154.9	158.7	164.3
130°	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7	160.2	164.8	170.9
132.5°	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7	164.7	169.7	177.0
135°	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9	171.9	177.5	185.1
137.5°	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6	178.7	184.2	192.3
140°	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1	183.6	188.7	196.8
142.5°	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9	188.1	193.6	200.9
145°	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8	195.3	199.9	207.5
147.5°	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7	202.6	207.1	213.7
150°	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0	207.5	211.6	218.2
152.5°	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3	212.4	216.5	222.3
155°	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3	220.3	223.3	228.4
157.5°	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5	226.9	229.3	233.9
160°	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4	231.4	233.4	237.6
162.5°	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1	235.1	236.7	240.0
165°	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6	240.0	241.1	243.6
167.5°	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8	244.2	244.6	246.6
170°	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2	246.2	246.6	248.2
172.5°	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8	248.2	248.3	249.4
175°	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7	250.2	249.8	250.7
177.5°	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6	251.3	250.8	251.3
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1422.4	1418.4	1412.8	1404.4	1397.7	1387.1	1387.1	1388.8	1388.8	1388.2	1387.1
5°	1379.2	1368.7	1356.1	1341.4	1326.0	1310.5	1307.7	1302.1	1297.9	1295.1	1291.6
7.5°	1333.6	1315.0	1296.6	1276.0	1257.2	1241.7	1230.9	1221.9	1216.2	1210.1	1205.5
10°	1302.8	1279.7	1257.9	1236.3	1212.4	1193.5	1181.6	1173.1	1166.9	1161.3	1158.4
12.5°	1266.4	1239.9	1215.9	1195.3	1169.2	1149.8	1138.4	1134.4	1127.0	1115.3	1109.1
15°	1213.1	1188.6	1159.8	1128.3	1115.7	1091.9	1078.5	1072.3	1068.0	1058.9	1056.1
17.5°	1167.5	1135.4	1103.2	1079.7	1056.2	1036.9	1029.5	1021.6	1016.0	1008.6	1006.4
20°	1131.1	1102.4	1072.9	1047.8	1023.1	1002.2	995.9	990.2	984.6	981.1	978.3
22.5°	1094.1	1065.4	1041.0	1017.4	991.2	977.5	970.6	964.5	960.6	958.1	955.4
25°	1042.1	1016.9	989.5	968.5	947.5	938.3	934.2	930.7	927.9	924.3	923.6
27.5°	995.6	968.1	945.9	926.3	911.2	903.7	899.6	897.9	898.5	899.7	900.5
30°	960.8	935.6	917.4	900.5	886.5	879.5	878.8	878.8	881.6	882.3	883.7
32.5°	928.9	908.1	889.9	873.6	863.0	858.2	860.9	860.9	863.1	865.0	867.5
35°	882.3	864.1	850.1	836.1	827.0	829.0	830.5	831.9	835.4	839.5	842.4
37.5°	837.9	822.1	807.4	796.6	792.4	796.1	799.5	802.5	806.5	809.8	812.5
40°	805.9	794.0	780.0	770.2	771.6	773.7	776.5	780.0	783.5	785.6	788.5
42.5°	776.2	763.8	753.1	744.9	746.9	749.6	751.3	753.1	757.2	761.0	762.6
45°	730.9	721.1	711.3	706.4	707.8	709.3	710.6	712.7	716.2	719.1	719.7
47.5°	680.1	673.2	666.6	661.8	664.1	663.5	665.4	669.9	670.9	672.6	676.5
50°	647.6	641.2	633.6	632.1	632.1	632.1	632.8	638.5	638.5	641.2	644.1
52.5°	611.7	607.6	602.7	600.2	599.1	599.1	602.0	604.8	605.9	609.8	612.7
55°	558.6	554.4	550.1	548.0	546.6	548.0	553.7	555.0	558.6	560.6	562.8
57.5°	503.2	500.0	496.6	495.4	495.2	497.0	500.1	504.3	505.2	511.6	514.8
60°	466.7	461.8	459.1	459.1	457.6	464.0	462.5	469.6	470.9	475.2	480.1
62.5°	429.2	422.6	421.5	421.5	423.5	425.3	427.2	430.3	433.9	439.3	443.1
65°	368.6	365.2	370.1	369.3	367.9	372.1	372.1	375.7	379.9	384.8	392.4
67.5°	311.3	309.5	309.9	309.9	312.0	314.4	316.4	319.4	324.5	329.7	334.7
70°	272.6	274.7	271.3	274.0	276.2	276.8	278.2	282.4	288.0	291.5	297.1
72.5°	235.1	234.9	235.3	236.5	238.5	239.8	241.2	246.0	252.2	255.1	259.6
75°	180.8	180.1	182.2	182.2	185.7	187.1	188.5	190.6	196.3	200.5	203.9
77.5°	132.1	132.9	132.4	134.8	133.8	134.1	138.5	140.6	141.2	149.5	151.2
80°	99.5	100.9	101.7	102.3	103.0	101.7	106.6	108.6	108.6	113.5	117.0
82.5°	71.5	72.3	74.2	74.8	75.0	76.4	76.8	78.4	80.1	82.1	86.8
85°	35.8	37.8	38.5	37.8	38.5	37.2	39.2	39.9	40.7	40.7	40.7
87.5°	12.3	13.1	12.8	13.7	13.5	14.4	14.2	13.2	13.3	15.1	13.0
90°	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8	13.2	13.7	14.7
92.5°	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8	34.0	30.1	27.4
95°	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1	124.1	97.1	78.8
97.5°	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5	365.6	300.0	239.2
100°	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7	558.5	498.9	426.7
102.5°	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3	646.0	611.3	565.4
105°	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2	712.0	721.8	708.5
107.5°	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1	703.7	748.2	766.3
110°	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8	676.5	740.6	776.1



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0	640.6	712.5	758.2
115°	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9	583.4	658.2	713.5
117.5°	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5	534.9	602.1	658.4
120°	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4	508.1	569.1	620.5
122.5°	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4	486.5	543.1	590.8
125°	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3	459.8	508.6	549.3
127.5°	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8	436.3	480.4	517.4
130°	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9	421.6	462.8	497.4
132.5°	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7	407.8	446.1	479.1
135°	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0	388.1	421.2	450.1
137.5°	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5	369.1	397.5	422.7
140°	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2	358.0	382.5	404.3
142.5°	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2	347.5	368.6	387.6
145°	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8	333.7	349.9	364.7
147.5°	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0	323.3	336.5	347.0
150°	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1	316.8	327.5	337.2
152.5°	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7	310.8	320.2	328.2
155°	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0	302.1	309.8	315.8
157.5°	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9	293.6	299.6	304.3
160°	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8	288.4	293.5	297.0
162.5°	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9	282.7	287.4	290.5
165°	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6	274.6	278.2	280.7
167.5°	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1	268.4	270.5	272.3
170°	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4	263.9	266.0	267.0
172.5°	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2	260.3	261.9	262.5
175°	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9	255.3	256.4	256.4
177.5°	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1	252.4	252.9	252.9
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1383.1	1382.6	1386.5	1383.7	1386.5	1382.6	1383.1	1387.1	1388.2	1388.8	1388.8
5°	1287.4	1289.5	1282.5	1282.5	1282.5	1289.5	1287.4	1291.6	1295.1	1297.9	1302.1
7.5°	1202.2	1199.1	1199.4	1195.6	1199.4	1199.1	1202.2	1205.5	1210.1	1216.2	1221.9
10°	1150.0	1145.8	1144.4	1145.1	1144.4	1145.8	1150.0	1158.4	1161.3	1166.9	1173.1
12.5°	1106.9	1106.0	1096.8	1096.9	1096.8	1106.0	1106.9	1109.1	1115.3	1127.0	1134.4
15°	1056.1	1042.9	1041.4	1045.6	1041.4	1042.9	1056.1	1056.1	1058.9	1068.0	1072.3
17.5°	1005.2	998.3	998.6	996.6	998.6	998.3	1005.2	1006.4	1008.6	1016.0	1021.6
20°	978.3	974.1	973.4	968.5	973.4	974.1	978.3	978.3	981.1	984.6	990.2
22.5°	953.7	952.3	952.7	947.3	952.7	952.3	953.7	955.4	958.1	960.6	964.5
25°	923.0	926.5	923.6	923.6	923.6	926.5	923.0	923.6	924.3	927.9	930.7
27.5°	902.2	902.1	900.7	900.7	900.7	902.1	902.2	900.5	899.7	898.5	897.9
30°	886.5	885.8	887.3	887.3	887.3	885.8	886.5	883.7	882.3	881.6	878.8
32.5°	870.8	871.8	872.1	872.6	872.1	871.8	870.8	867.5	865.0	863.1	860.9
35°	846.6	847.3	849.4	848.0	849.4	847.3	846.6	842.4	839.5	835.4	831.9
37.5°	813.8	817.0	816.3	817.4	816.3	817.0	813.8	812.5	809.8	806.5	802.5
40°	789.1	791.2	790.5	790.5	790.5	791.2	789.1	788.5	785.6	783.5	780.0
42.5°	763.9	765.4	763.6	762.5	763.6	765.4	763.9	762.6	761.0	757.2	753.1
45°	722.6	721.1	723.3	720.4	723.3	721.1	722.6	719.7	719.1	716.2	712.7
47.5°	676.3	677.7	678.2	680.4	678.2	677.7	676.3	676.5	672.6	670.9	669.9
50°	645.4	649.6	649.6	649.0	649.6	649.6	645.4	644.1	641.2	638.5	638.5
52.5°	615.2	617.2	619.9	619.8	619.9	617.2	615.2	612.7	609.8	605.9	604.8
55°	568.4	569.8	571.1	571.9	571.1	569.8	568.4	562.8	560.6	558.6	555.0
57.5°	519.9	519.3	522.6	523.6	522.6	519.3	519.9	514.8	511.6	505.2	504.3
60°	485.6	485.6	491.2	493.4	491.2	485.6	485.6	480.1	475.2	470.9	469.6
62.5°	449.2	451.5	457.1	454.1	457.1	451.5	449.2	443.1	439.3	433.9	430.3
65°	395.9	401.5	400.8	403.7	400.8	401.5	395.9	392.4	384.8	379.9	375.7
67.5°	340.3	343.8	348.8	349.3	348.8	343.8	340.3	334.7	329.7	324.5	319.4
70°	302.7	306.2	309.1	311.1	309.1	306.2	302.7	297.1	291.5	288.0	282.4
72.5°	266.4	268.1	274.8	271.9	274.8	268.1	266.4	259.6	255.1	252.2	246.0
75°	208.8	213.7	217.9	215.9	217.9	213.7	208.8	203.9	200.5	196.3	190.6
77.5°	154.4	159.3	161.3	159.5	161.3	159.3	154.4	151.2	149.5	141.2	140.6
80°	122.0	121.3	125.5	124.8	125.5	121.3	122.0	117.0	113.5	108.6	108.6
82.5°	89.4	88.7	90.7	91.1	90.7	88.7	89.4	86.8	82.1	80.1	78.4
85°	43.4	45.6	42.7	42.1	42.7	45.6	43.4	40.7	40.7	40.7	39.9
87.5°	12.9	13.0	12.6	11.9	12.6	13.0	12.9	13.0	15.1	13.3	13.2
90°	14.3	14.7	15.2	14.7	15.2	14.7	14.3	14.7	13.7	13.2	12.8
92.5°	26.5	24.9	25.4	24.5	25.4	24.9	26.5	27.4	30.1	34.0	42.8
95°	69.2	64.6	61.0	59.0	61.0	64.6	69.2	78.8	97.1	124.1	183.1
97.5°	201.6	178.7	165.0	160.6	165.0	178.7	201.6	239.2	300.0	365.6	456.5
100°	375.3	338.2	318.4	318.9	318.4	338.2	375.3	426.7	498.9	558.5	599.7
102.5°	525.5	496.1	479.5	467.8	479.5	496.1	525.5	565.4	611.3	646.0	647.3
105°	685.1	665.8	649.5	646.9	649.5	665.8	685.1	708.5	721.8	712.0	661.2
107.5°	766.8	760.3	754.7	750.1	754.7	760.3	766.8	766.3	748.2	703.7	621.1
110°	790.4	794.4	793.4	792.4	793.4	794.4	790.4	776.1	740.6	676.5	582.8



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	784.3	796.9	800.8	800.9	800.8	796.9	784.3	758.2	712.5	640.6	545.0
115°	751.7	774.1	784.3	786.8	784.3	774.1	751.7	713.5	658.2	583.4	494.9
117.5°	698.1	723.7	738.4	741.8	738.4	723.7	698.1	658.4	602.1	534.9	458.5
120°	660.7	689.2	701.3	704.5	701.3	689.2	660.7	620.5	569.1	508.1	439.4
122.5°	626.5	652.1	665.6	669.4	665.6	652.1	626.5	590.8	543.1	486.5	424.4
125°	581.8	604.2	617.0	620.5	617.0	604.2	581.8	549.3	508.6	459.8	404.3
127.5°	546.4	565.4	576.9	580.2	576.9	565.4	546.4	517.4	480.4	436.3	386.8
130°	524.4	542.7	553.4	557.4	553.4	542.7	524.4	497.4	462.8	421.6	375.9
132.5°	504.4	522.7	532.2	535.0	532.2	522.7	504.4	479.1	446.1	407.8	365.7
135°	475.0	490.3	499.4	503.0	499.4	490.3	475.0	450.1	421.2	388.1	352.0
137.5°	443.6	459.1	466.8	469.1	466.8	459.1	443.6	422.7	397.5	369.1	339.5
140°	423.7	437.9	446.0	445.5	446.0	437.9	423.7	404.3	382.5	358.0	332.2
142.5°	404.1	416.8	424.1	423.6	424.1	416.8	404.1	387.6	368.6	347.5	325.2
145°	377.4	388.1	392.2	393.2	392.2	388.1	377.4	364.7	349.9	333.7	316.8
147.5°	356.6	363.8	367.7	368.1	367.7	363.8	356.6	347.0	336.5	323.3	310.0
150°	344.8	350.4	353.5	353.5	353.5	350.4	344.8	337.2	327.5	316.8	305.1
152.5°	334.2	339.5	341.3	341.3	341.3	339.5	334.2	328.2	320.2	310.8	300.7
155°	320.4	324.5	325.5	326.0	325.5	324.5	320.4	315.8	309.8	302.1	294.0
157.5°	308.4	311.4	312.2	312.1	312.2	311.4	308.4	304.3	299.6	293.6	286.9
160°	300.6	303.6	303.6	303.1	303.6	303.6	300.6	297.0	293.5	288.4	282.8
162.5°	292.8	295.5	295.5	295.0	295.5	295.5	292.8	290.5	287.4	282.7	277.9
165°	282.8	284.8	284.3	284.3	284.3	284.8	282.8	280.7	278.2	274.6	271.6
167.5°	273.2	274.6	274.1	274.1	274.1	274.6	273.2	272.3	270.5	268.4	266.1
170°	267.5	268.6	268.0	268.0	268.0	268.6	267.5	267.0	266.0	263.9	262.4
172.5°	262.6	263.7	262.8	262.3	262.8	263.7	262.6	262.5	261.9	260.3	259.2
175°	256.4	256.8	256.4	255.8	256.4	256.8	256.4	256.4	256.4	255.3	254.9
177.5°	252.4	252.9	252.1	252.1	252.1	252.9	252.4	252.9	252.9	252.4	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1387.1	1387.1	1397.7	1404.4	1412.8	1418.4	1422.4	1426.3	1433.1	1442.0	1452.1
5°	1307.7	1310.5	1326.0	1341.4	1356.1	1368.7	1379.2	1391.8	1407.2	1426.1	1447.2
7.5°	1230.9	1241.7	1257.2	1276.0	1296.6	1315.0	1333.6	1354.4	1376.1	1404.0	1433.4
10°	1181.6	1193.5	1212.4	1236.3	1257.9	1279.7	1302.8	1325.3	1352.5	1385.5	1423.3
12.5°	1138.4	1149.8	1169.2	1195.3	1215.9	1239.9	1266.4	1295.6	1326.2	1365.9	1408.8
15°	1078.5	1091.9	1115.7	1128.3	1159.8	1188.6	1213.1	1255.2	1294.4	1335.1	1384.8
17.5°	1029.5	1036.9	1056.2	1079.7	1103.2	1135.4	1167.5	1202.6	1241.7	1291.5	1353.7
20°	995.9	1002.2	1023.1	1047.8	1072.9	1102.4	1131.1	1166.2	1210.3	1262.8	1330.2
22.5°	970.6	977.5	991.2	1017.4	1041.0	1065.4	1094.1	1135.9	1182.9	1234.3	1307.2
25°	934.2	938.3	947.5	968.5	989.5	1016.9	1042.1	1081.4	1129.7	1190.0	1262.8
27.5°	899.6	903.7	911.2	926.3	945.9	968.1	995.6	1028.9	1078.0	1143.4	1220.8
30°	878.8	879.5	886.5	900.5	917.4	935.6	960.8	998.6	1044.9	1111.5	1192.8
32.5°	860.9	858.2	863.0	873.6	889.9	908.1	928.9	966.2	1010.8	1076.2	1159.7
35°	830.5	829.0	827.0	836.1	850.1	864.1	882.3	910.3	960.8	1021.8	1109.4
37.5°	799.5	796.1	792.4	796.6	807.4	822.1	837.9	862.8	906.3	973.4	1057.2
40°	776.5	773.7	771.6	770.2	780.0	794.0	805.9	829.7	870.4	934.2	1016.9
42.5°	751.3	749.6	746.9	744.9	753.1	763.8	776.2	797.3	837.9	897.8	976.0
45°	710.6	709.3	707.8	706.4	711.3	721.1	730.9	746.4	781.4	839.5	910.3
47.5°	665.4	663.5	664.1	661.8	666.6	673.2	680.1	696.6	730.2	777.2	828.9
50°	632.8	632.1	632.1	632.1	633.6	641.2	647.6	660.1	691.0	738.0	775.1
52.5°	602.0	599.1	599.1	600.2	602.7	607.6	611.7	625.4	652.3	690.9	724.6
55°	553.7	548.0	546.6	548.0	550.1	554.4	558.6	569.8	592.9	621.6	641.2
57.5°	500.1	497.0	495.2	495.4	496.6	500.0	503.2	515.4	533.6	548.6	561.2
60°	462.5	464.0	457.6	459.1	459.1	461.8	466.7	474.5	489.9	500.3	513.0
62.5°	427.2	425.3	423.5	421.5	421.5	422.6	429.2	435.2	448.4	453.9	463.7
65°	372.1	372.1	367.9	369.3	370.1	365.2	368.6	375.7	384.1	386.1	395.3
67.5°	316.4	314.4	312.0	309.9	309.9	309.5	311.3	314.8	321.1	321.8	328.9
70°	278.2	276.8	276.2	274.0	271.3	274.7	272.6	276.2	279.6	280.4	284.5
72.5°	241.2	239.8	238.5	236.5	235.3	234.9	235.1	239.2	241.5	240.5	245.3
75°	188.5	187.1	185.7	182.2	182.2	180.1	180.8	183.6	186.5	184.3	188.5
77.5°	138.5	134.1	133.8	134.8	132.4	132.9	132.1	131.6	132.9	133.0	136.8
80°	106.6	101.7	103.0	102.3	101.7	100.9	99.5	100.2	100.9	101.7	103.7
82.5°	76.8	76.4	75.0	74.8	74.2	72.3	71.5	72.8	73.5	73.0	74.5
85°	39.2	37.2	38.5	37.8	38.5	37.8	35.8	35.8	37.2	36.5	37.8
87.5°	14.2	14.4	13.5	13.7	12.8	13.1	12.3	12.7	12.9	12.8	13.6
90°	12.2	12.8	11.1	9.6	8.1	6.6	5.6	4.5	3.0	2.1	1.0
92.5°	59.0	78.2	86.1	64.6	42.7	29.4	21.8	17.6	13.6	9.4	6.3
95°	244.6	301.6	268.6	185.1	109.3	66.1	46.3	33.1	24.4	18.8	17.3
97.5°	500.1	467.4	342.1	203.1	117.7	76.4	54.9	41.9	34.4	30.1	29.5
100°	581.8	481.6	325.5	191.7	116.5	80.9	61.0	48.9	41.7	38.2	37.6
102.5°	585.9	455.2	301.1	182.0	118.1	86.1	67.9	57.0	50.3	47.1	46.2
105°	554.9	408.9	271.1	175.0	122.6	95.1	79.4	69.6	63.6	60.5	59.0
107.5°	500.6	368.0	252.0	174.4	130.9	106.8	92.2	83.1	77.1	74.2	72.6
110°	466.4	344.8	244.6	176.5	137.9	114.9	100.7	92.0	86.5	83.9	82.4



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	436.7	329.4	240.6	180.6	144.7	123.5	109.7	101.0	95.4	92.9	91.3
115°	400.8	312.8	239.1	187.2	156.1	136.8	123.1	114.4	109.3	106.3	104.2
117.5°	379.2	303.0	240.0	195.9	168.3	149.1	136.4	126.7	122.1	119.5	117.2
120°	367.7	298.5	241.6	202.4	175.9	157.7	145.0	135.3	130.2	127.7	126.2
122.5°	358.4	295.7	244.4	208.6	184.1	166.2	152.7	143.4	137.9	135.4	133.8
125°	346.3	291.9	248.7	218.2	195.8	178.0	164.3	154.6	149.0	146.0	145.0
127.5°	335.8	290.1	253.6	226.1	206.0	188.8	175.0	164.3	158.7	154.9	153.4
130°	330.1	288.9	256.8	231.4	212.0	195.3	181.6	170.9	164.8	160.2	158.7
132.5°	324.8	288.5	259.3	236.3	217.4	201.0	187.7	177.0	169.7	164.7	162.7
135°	317.9	287.8	263.0	242.6	225.3	209.6	195.8	185.1	177.5	171.9	169.9
137.5°	311.9	286.8	265.4	247.3	230.8	215.6	203.0	192.3	184.2	178.7	176.6
140°	308.2	286.3	267.0	249.8	234.4	219.7	207.0	196.8	188.7	183.6	181.1
142.5°	305.0	285.5	268.2	252.2	237.3	223.0	211.1	200.9	193.6	188.1	185.9
145°	300.6	284.3	269.0	254.9	241.1	227.8	216.2	207.5	199.9	195.3	193.8
147.5°	296.3	282.4	269.0	256.5	244.2	232.0	222.0	213.7	207.1	202.6	201.7
150°	293.5	280.7	269.0	256.8	246.2	234.4	225.3	218.2	211.6	207.5	207.0
152.5°	290.3	278.7	267.9	257.7	247.4	237.3	228.5	222.3	216.5	212.4	212.3
155°	285.3	275.2	266.5	257.9	249.8	241.1	234.0	228.4	223.3	220.3	220.3
157.5°	279.8	272.0	264.7	258.4	251.0	244.2	238.6	233.9	229.3	226.9	226.5
160°	276.2	269.6	263.9	258.4	252.3	246.2	241.1	237.6	233.4	231.4	231.4
162.5°	272.5	267.2	262.3	258.0	252.7	247.4	243.1	240.0	236.7	235.1	235.1
165°	267.5	263.5	259.9	256.8	253.2	249.2	245.7	243.6	241.1	240.0	240.6
167.5°	262.8	259.8	257.4	256.0	253.2	250.2	248.0	246.6	244.6	244.2	244.8
170°	259.9	257.3	255.8	254.9	252.8	250.2	249.2	248.2	246.6	246.2	247.2
172.5°	257.1	255.3	254.6	254.4	252.8	250.7	250.0	249.4	248.3	248.2	248.8
175°	253.8	252.8	252.8	253.2	252.3	251.3	250.7	250.7	249.8	250.2	250.7
177.5°	251.6	251.3	251.6	252.4	251.6	251.3	251.3	251.3	250.8	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1455.5	1458.2	1467.8	1474.5	1482.4	1486.8	1491.3	1494.7	1499.1	1500.3	1516.5
5°	1461.9	1476.0	1500.5	1518.7	1541.1	1565.6	1582.4	1590.2	1610.4	1627.3	1660.9
7.5°	1460.1	1490.0	1527.0	1565.3	1606.5	1644.7	1677.8	1717.0	1744.9	1786.8	1828.2
10°	1458.4	1498.3	1546.0	1595.1	1652.5	1705.8	1753.5	1806.7	1850.8	1909.0	1958.7
12.5°	1453.3	1501.7	1567.9	1625.9	1695.7	1769.2	1839.8	1908.2	1947.3	2044.2	2090.0
15°	1440.9	1498.3	1581.0	1669.4	1765.3	1852.3	1942.0	2013.5	2129.0	2213.9	2267.8
17.5°	1417.0	1497.5	1595.6	1702.1	1818.9	1933.4	2035.1	2143.5	2266.2	2368.7	2478.1
20°	1405.9	1494.2	1603.5	1721.2	1842.5	1972.1	2087.8	2218.0	2352.0	2452.8	2593.0
22.5°	1385.1	1485.1	1602.9	1734.1	1863.8	1997.9	2133.2	2264.6	2419.2	2558.2	2691.7
25°	1351.2	1463.3	1585.3	1731.7	1883.8	2018.4	2180.2	2354.7	2516.0	2694.7	2827.8
27.5°	1315.5	1435.3	1557.5	1693.7	1857.3	2017.0	2220.6	2417.8	2614.9	2769.2	2867.7
30°	1288.1	1404.4	1530.6	1667.9	1829.8	2019.7	2247.5	2462.6	2654.7	2787.1	2842.5
32.5°	1258.4	1376.4	1488.0	1632.1	1804.6	2018.0	2264.3	2489.0	2656.9	2745.1	2734.3
35°	1211.7	1310.5	1419.2	1557.9	1761.1	2005.7	2274.1	2491.4	2594.4	2575.5	2432.5
37.5°	1144.4	1227.5	1334.5	1486.4	1710.7	1979.8	2254.5	2417.5	2410.8	2256.7	2049.6
40°	1102.4	1173.1	1276.2	1436.0	1671.4	1963.0	2223.7	2329.5	2239.8	2024.6	1776.6
42.5°	1047.4	1112.6	1215.7	1379.9	1628.3	1928.8	2164.8	2195.5	2020.0	1772.4	1545.0
45°	962.2	1019.7	1126.2	1295.8	1563.5	1854.3	2021.2	1946.2	1709.9	1454.2	1281.1
47.5°	870.7	930.4	1032.9	1207.1	1469.9	1742.4	1821.9	1662.3	1419.9	1212.4	1053.5
50°	813.0	870.4	970.6	1146.6	1406.5	1650.4	1683.4	1477.3	1254.5	1072.3	941.9
52.5°	754.7	808.8	907.3	1083.7	1332.6	1543.9	1523.6	1313.6	1108.7	953.4	851.0
55°	667.9	719.1	813.0	978.3	1204.7	1372.2	1298.6	1098.1	928.5	808.1	730.2
57.5°	590.2	639.3	720.3	869.7	1066.5	1181.6	1088.0	919.1	784.2	691.4	633.4
60°	537.5	580.9	658.1	796.8	967.9	1055.4	963.0	813.7	700.1	625.8	574.0
62.5°	487.6	525.5	596.9	722.8	871.4	944.9	851.3	725.1	628.4	562.5	518.4
65°	412.1	446.4	509.5	607.6	729.5	778.6	698.0	595.7	520.7	471.6	442.2
67.5°	343.1	372.3	426.8	504.0	593.7	629.5	568.1	488.9	432.4	393.0	369.6
70°	297.1	322.4	365.2	431.7	513.0	540.3	482.9	417.7	376.3	344.8	323.1
72.5°	258.4	277.0	315.8	367.2	435.1	456.8	416.7	359.4	320.8	297.1	279.9
75°	196.9	212.3	237.6	278.9	325.9	338.5	308.4	272.6	246.6	229.9	216.5
77.5°	142.0	153.4	171.6	197.1	229.6	240.9	221.9	198.0	179.1	167.7	160.3
80°	107.2	116.4	131.8	152.8	172.4	178.7	167.5	149.3	136.0	129.7	123.3
82.5°	79.2	84.4	93.6	107.9	121.4	128.9	119.3	108.3	101.2	95.4	93.1
85°	39.9	42.7	47.0	52.5	61.0	63.8	60.3	57.4	53.2	49.8	49.8
87.5°	15.0	15.2	17.2	18.5	21.0	22.9	22.6	21.8	21.6	21.0	20.5
90°	2.1	3.0	4.5	5.6	6.6	8.1	9.6	11.1	12.8	12.2	12.8
92.5°	9.4	13.6	17.6	21.8	29.4	42.7	64.6	86.1	78.2	59.0	42.8
95°	18.8	24.4	33.1	46.3	66.1	109.3	185.1	268.6	301.6	244.6	183.1
97.5°	30.1	34.4	41.9	54.9	76.4	117.7	203.1	342.1	467.4	500.1	456.5
100°	38.2	41.7	48.9	61.0	80.9	116.5	191.7	325.5	481.6	581.8	599.7
102.5°	47.1	50.3	57.0	67.9	86.1	118.1	182.0	301.1	455.2	585.9	647.3
105°	60.5	63.6	69.6	79.4	95.1	122.6	175.0	271.1	408.9	554.9	661.2
107.5°	74.2	77.1	83.1	92.2	106.8	130.9	174.4	252.0	368.0	500.6	621.1
110°	83.9	86.5	92.0	100.7	114.9	137.9	176.5	244.6	344.8	466.4	582.8



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	92.9	95.4	101.0	109.7	123.5	144.7	180.6	240.6	329.4	436.7	545.0
115°	106.3	109.3	114.4	123.1	136.8	156.1	187.2	239.1	312.8	400.8	494.9
117.5°	119.5	122.1	126.7	136.4	149.1	168.3	195.9	240.0	303.0	379.2	458.5
120°	127.7	130.2	135.3	145.0	157.7	175.9	202.4	241.6	298.5	367.7	439.4
122.5°	135.4	137.9	143.4	152.7	166.2	184.1	208.6	244.4	295.7	358.4	424.4
125°	146.0	149.0	154.6	164.3	178.0	195.8	218.2	248.7	291.9	346.3	404.3
127.5°	154.9	158.7	164.3	175.0	188.8	206.0	226.1	253.6	290.1	335.8	386.8
130°	160.2	164.8	170.9	181.6	195.3	212.0	231.4	256.8	288.9	330.1	375.9
132.5°	164.7	169.7	177.0	187.7	201.0	217.4	236.3	259.3	288.5	324.8	365.7
135°	171.9	177.5	185.1	195.8	209.6	225.3	242.6	263.0	287.8	317.9	352.0
137.5°	178.7	184.2	192.3	203.0	215.6	230.8	247.3	265.4	286.8	311.9	339.5
140°	183.6	188.7	196.8	207.0	219.7	234.4	249.8	267.0	286.3	308.2	332.2
142.5°	188.1	193.6	200.9	211.1	223.0	237.3	252.2	268.2	285.5	305.0	325.2
145°	195.3	199.9	207.5	216.2	227.8	241.1	254.9	269.0	284.3	300.6	316.8
147.5°	202.6	207.1	213.7	222.0	232.0	244.2	256.5	269.0	282.4	296.3	310.0
150°	207.5	211.6	218.2	225.3	234.4	246.2	256.8	269.0	280.7	293.5	305.1
152.5°	212.4	216.5	222.3	228.5	237.3	247.4	257.7	267.9	278.7	290.3	300.7
155°	220.3	223.3	228.4	234.0	241.1	249.8	257.9	266.5	275.2	285.3	294.0
157.5°	226.9	229.3	233.9	238.6	244.2	251.0	258.4	264.7	272.0	279.8	286.9
160°	231.4	233.4	237.6	241.1	246.2	252.3	258.4	263.9	269.6	276.2	282.8
162.5°	235.1	236.7	240.0	243.1	247.4	252.7	258.0	262.3	267.2	272.5	277.9
165°	240.0	241.1	243.6	245.7	249.2	253.2	256.8	259.9	263.5	267.5	271.6
167.5°	244.2	244.6	246.6	248.0	250.2	253.2	256.0	257.4	259.8	262.8	266.1
170°	246.2	246.6	248.2	249.2	250.2	252.8	254.9	255.8	257.3	259.9	262.4
172.5°	248.2	248.3	249.4	250.0	250.7	252.8	254.4	254.6	255.3	257.1	259.2
175°	250.2	249.8	250.7	250.7	251.3	252.3	253.2	252.8	252.8	253.8	254.9
177.5°	251.3	250.8	251.3	251.3	251.3	251.6	252.4	251.6	251.3	251.6	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4	1446.4
2.5°	1522.2	1522.7	1528.9	1533.4	1531.2	1533.9	1535.1
5°	1663.0	1688.3	1701.6	1711.4	1712.1	1712.8	1718.4
7.5°	1862.8	1889.8	1909.6	1939.6	1948.6	1958.7	1955.8
10°	2008.6	2048.4	2082.9	2101.0	2120.7	2149.4	2126.3
12.5°	2144.7	2215.5	2267.8	2296.2	2314.6	2320.4	2309.1
15°	2369.5	2461.9	2511.7	2510.3	2573.4	2600.8	2558.0
17.5°	2575.5	2660.9	2729.3	2764.3	2816.8	2828.5	2823.2
20°	2701.6	2794.9	2848.1	2908.4	2935.7	2960.2	2964.4
22.5°	2810.4	2894.0	2951.3	3001.4	3024.3	3035.9	3043.0
25°	2922.4	2988.3	3022.6	3040.1	3046.4	3045.0	3035.9
27.5°	2914.6	2919.7	2881.9	2844.7	2811.6	2774.1	2761.2
30°	2839.0	2780.1	2675.0	2615.5	2527.8	2458.4	2486.4
32.5°	2640.0	2522.8	2404.8	2274.6	2166.8	2136.1	2105.2
35°	2253.1	2047.1	1926.5	1786.4	1730.3	1674.3	1635.7
37.5°	1822.8	1663.5	1520.5	1428.8	1372.6	1337.1	1318.1
40°	1576.1	1432.4	1314.7	1240.5	1197.7	1157.7	1152.2
42.5°	1379.4	1245.8	1157.2	1098.1	1056.9	1040.0	1027.7
45°	1129.7	1036.5	977.0	934.9	907.6	897.1	883.1
47.5°	956.2	890.3	845.6	817.0	796.4	788.5	787.5
50°	859.2	804.5	771.6	749.1	733.1	730.2	719.1
52.5°	786.3	739.0	713.3	693.7	682.1	674.2	670.8
55°	682.6	651.0	627.9	616.7	607.6	599.9	599.9
57.5°	597.3	570.9	555.6	546.1	543.2	537.8	534.3
60°	544.6	522.1	510.2	501.8	496.1	496.9	490.5
62.5°	492.9	478.4	467.0	458.6	451.9	452.0	452.5
65°	419.8	408.6	400.2	397.3	393.2	388.3	389.7
67.5°	355.7	345.2	338.7	333.9	332.4	329.8	333.9
70°	309.8	302.0	297.1	292.9	291.5	292.2	295.8
72.5°	267.7	262.3	259.0	257.1	254.0	254.1	256.5
75°	210.3	206.1	203.2	201.2	200.5	200.5	200.5
77.5°	154.4	153.5	152.2	149.1	149.3	150.1	150.3
80°	122.0	119.8	119.1	117.7	115.7	114.2	117.7
82.5°	91.1	89.0	88.3	88.0	84.8	84.5	87.5
85°	49.0	47.0	47.6	47.0	47.0	46.3	46.3
87.5°	20.1	19.5	19.2	19.7	19.2	18.7	19.8
90°	13.2	13.7	14.7	14.3	14.7	15.2	14.7
92.5°	34.0	30.1	27.4	26.5	24.9	25.4	24.5
95°	124.1	97.1	78.8	69.2	64.6	61.0	59.0
97.5°	365.6	300.0	239.2	201.6	178.7	165.0	160.6
100°	558.5	498.9	426.7	375.3	338.2	318.4	318.9
102.5°	646.0	611.3	565.4	525.5	496.1	479.5	467.8
105°	712.0	721.8	708.5	685.1	665.8	649.5	646.9
107.5°	703.7	748.2	766.3	766.8	760.3	754.7	750.1
110°	676.5	740.6	776.1	790.4	794.4	793.4	792.4



TEST NUMBER: P332056-940

CATALOG NUMBER: S123DIP-S1165D585U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	640.6	712.5	758.2	784.3	796.9	800.8	800.9
115°	583.4	658.2	713.5	751.7	774.1	784.3	786.8
117.5°	534.9	602.1	658.4	698.1	723.7	738.4	741.8
120°	508.1	569.1	620.5	660.7	689.2	701.3	704.5
122.5°	486.5	543.1	590.8	626.5	652.1	665.6	669.4
125°	459.8	508.6	549.3	581.8	604.2	617.0	620.5
127.5°	436.3	480.4	517.4	546.4	565.4	576.9	580.2
130°	421.6	462.8	497.4	524.4	542.7	553.4	557.4
132.5°	407.8	446.1	479.1	504.4	522.7	532.2	535.0
135°	388.1	421.2	450.1	475.0	490.3	499.4	503.0
137.5°	369.1	397.5	422.7	443.6	459.1	466.8	469.1
140°	358.0	382.5	404.3	423.7	437.9	446.0	445.5
142.5°	347.5	368.6	387.6	404.1	416.8	424.1	423.6
145°	333.7	349.9	364.7	377.4	388.1	392.2	393.2
147.5°	323.3	336.5	347.0	356.6	363.8	367.7	368.1
150°	316.8	327.5	337.2	344.8	350.4	353.5	353.5
152.5°	310.8	320.2	328.2	334.2	339.5	341.3	341.3
155°	302.1	309.8	315.8	320.4	324.5	325.5	326.0
157.5°	293.6	299.6	304.3	308.4	311.4	312.2	312.1
160°	288.4	293.5	297.0	300.6	303.6	303.6	303.1
162.5°	282.7	287.4	290.5	292.8	295.5	295.5	295.0
165°	274.6	278.2	280.7	282.8	284.8	284.3	284.3
167.5°	268.4	270.5	272.3	273.2	274.6	274.1	274.1
170°	263.9	266.0	267.0	267.5	268.6	268.0	268.0
172.5°	260.3	261.9	262.5	262.6	263.7	262.8	262.3
175°	255.3	256.4	256.4	256.4	256.8	256.4	255.8
177.5°	252.4	252.9	252.9	252.4	252.9	252.1	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3

(END OF REPORT)