

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331901-935

Luminaire Tested: **S123DIP-S340D1195U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331901-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5359.3 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	59	53	49	47	38	36	34	25	24	23	17
3	76	67	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	8
8	50	39	31	26	45	35	28	24	27	22	19	20	17	15	13	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	0.8
10°-20°	130.8	2.4
20°-30°	219.5	4.1
30°-40°	248.5	4.6
40°-50°	222.9	4.2
50°-60°	179.8	3.4
60°-70°	125.3	2.3
70°-80°	65.9	1.2
80°-90°	19.9	0.4
90°-100°	48.9	0.9
100°-110°	233.3	4.4
110°-120°	560.4	10.5
120°-130°	713.6	13.3
130°-140°	762.5	14.2
140°-150°	713.0	13.3
150°-160°	575.1	10.7
160°-170°	371.2	6.9
170°-180°	127.9	2.4
0°-30°	391.0	7.3
0°-40°	639.5	11.9
0°-60°	1042.2	19.4
0°-90°	1253.3	23.4
90°-120°	842.6	15.7
90°-150°	3031.7	56.6
90°-180°	4106.0	76.6
0°-180°	5359.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	16
90°	30	1	30	1	30	14
95°	38	61	38	61	38	32
105°	44	298	44	298	44	101
115°	588	559	588	559	588	543
125°	804	788	804	788	804	718
135°	991	981	991	981	991	764
145°	1143	1132	1143	1132	1143	714
155°	1245	1247	1245	1247	1245	574
165°	1312	1315	1312	1315	1312	371
175°	1341	1346	1341	1346	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	10.8	10.4	10.5	10.6	10.3	10.3	10.3	10.3	10.2	10.2	9.8
90°	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7	24.9	24.0	21.1
92.5°	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4	27.0	25.6	23.4
95°	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1	32.5	31.0	28.6
97.5°	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7	34.0	32.2	48.2
100°	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6	34.8	33.0	67.7
102.5°	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8	60.3	65.8	103.7
105°	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3	179.7	219.0	239.1
107.5°	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8	372.6	401.6	398.4
110°	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4	443.8	451.2	448.7



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8	501.7	501.5	499.1
115°	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6	576.4	574.2	572.2
117.5°	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2	646.4	644.6	643.6
120°	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8	692.0	690.2	689.6
122.5°	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3	737.1	735.8	734.9
125°	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2	800.7	800.2	799.4
127.5°	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1	863.4	862.6	861.6
130°	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1	901.2	900.3	899.4
132.5°	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1	937.2	936.3	935.6
135°	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4	990.4
137.5°	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3	1040.2	1039.1	1038.6
140°	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1	1071.3	1070.3	1069.7
142.5°	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4	1100.7	1099.9	1099.3
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3	1141.8	1141.3	1140.9
147.5°	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9	1178.5	1177.9	1177.5
150°	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3	1200.8	1200.4	1200.0
152.5°	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2	1220.4	1219.6	1219.3
155°	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6	1247.5	1246.4	1246.2
157.5°	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5	1271.2	1269.8	1270.1
160°	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1	1284.8	1283.4	1283.7
162.5°	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5	1296.9	1295.4	1295.6
165°	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0	1313.2	1311.4	1311.6
167.5°	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2	1324.2
170°	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5	1331.5
172.5°	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8	1338.0	1336.2	1336.0
175°	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6	1344.0	1342.4	1342.2
177.5°	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6	1346.3	1344.8	1344.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	9.6	9.1	8.1	7.0	6.2	5.3	4.8	4.0	4.1	4.6	4.9
90°	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6	18.0	17.4	16.7
95°	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0	51.9	42.8	33.7
97.5°	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6	118.6	114.4	110.4
100°	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0	173.5	178.0	182.4
102.5°	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9	225.1	228.3	231.4
105°	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1	300.6	303.0	305.4
107.5°	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5	380.5	382.5	384.4
110°	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1	433.9	435.7	437.5



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4	484.9	486.6	488.2
115°	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2	560.5	561.8	563.2
117.5°	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6	634.2	635.8	637.6
120°	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2	680.2	682.3	684.2
122.5°	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6	726.3	727.9	729.5
125°	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2	790.1	791.8	793.6
127.5°	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9	851.6	853.4	855.2
130°	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3	890.1	891.8	893.6
132.5°	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1	926.9	928.7	930.4
135°	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3	982.7	984.0	985.3
137.5°	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3	1031.0	1032.7	1034.4
140°	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4	1062.6	1064.0	1065.3
142.5°	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0	1092.3	1093.6	1094.9
145°	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4	1133.9	1135.5	1137.0
147.5°	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4	1172.4	1173.5	1174.4
150°	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4	1196.0	1196.7	1197.4
152.5°	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0	1217.3	1217.6	1217.9
155°	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4	1247.0	1246.5	1246.0
157.5°	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0	1270.9	1270.9	1270.8
160°	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4	1285.2	1285.0	1284.8
162.5°	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0	1298.5	1297.9	1297.3
165°	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4	1314.7	1314.1	1313.5
167.5°	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3	1327.3	1326.5	1325.6
170°	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4	1334.6	1333.7	1332.7
172.5°	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2	1339.2	1338.1	1337.0
175°	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4	1345.3	1344.2	1343.1
177.5°	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1	1347.1	1346.3	1345.4
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	5.2	5.9	6.3	7.0	7.4	8.2	8.4	8.2	8.4	9.0	8.5
90°	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7	26.7	27.6	28.2
92.5°	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4	29.9	31.3	32.1
95°	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1	35.6	37.2	38.0
97.5°	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7	37.5	39.3	40.3
100°	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6	38.3	40.1	41.2
102.5°	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8	49.2	43.7	41.2
105°	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3	101.0	61.6	42.3
107.5°	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8	315.0	286.1	256.8
110°	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4	429.1	421.8	402.3



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8	502.0	502.1	498.8
115°	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6	580.8	583.1	584.6
117.5°	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2	650.0	651.7	652.7
120°	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8	695.5	697.3	698.2
122.5°	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3	739.6	740.8	741.5
125°	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2	801.6	802.0	802.5
127.5°	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1	864.8	865.5	865.6
130°	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1	902.9	903.9	904.0
132.5°	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1	939.0	939.9	940.0
135°	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6	993.3	994.0	994.0
137.5°	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3	1042.3	1043.4	1043.7
140°	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1	1073.0	1073.9	1074.1
142.5°	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4	1102.1	1102.8	1102.9
145°	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3	1142.7	1143.1	1143.3
147.5°	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9	1179.3	1179.7	1179.5
150°	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3	1201.7	1202.1	1202.0
152.5°	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2	1222.0	1222.8	1222.7
155°	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6	1249.7	1250.9	1250.7
157.5°	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5	1273.8	1275.1	1275.0
160°	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1	1287.4	1288.7	1288.7
162.5°	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5	1299.9	1301.5	1301.5
165°	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0	1316.7	1318.5	1318.6
167.5°	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4
170°	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5
172.5°	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8	1341.5	1343.3	1343.2
175°	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6	1347.1	1348.7	1348.5
177.5°	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6	1349.1	1350.5	1350.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	8.6	8.7	8.6	8.6	8.6	8.7	8.6	8.5	9.0	8.4	8.2
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7
92.5°	32.4	32.7	33.0	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4
95°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1
97.5°	40.6	40.8	41.0	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7
100°	41.3	41.6	41.8	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6
102.5°	41.6	42.0	42.4	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8
105°	42.7	43.1	43.6	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3
107.5°	227.2	197.5	167.9	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8
110°	370.5	338.6	306.9	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.1	485.3	478.6	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8
115°	585.5	586.4	587.3	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6
117.5°	652.9	653.1	653.2	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2
120°	698.2	698.2	698.2	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8
122.5°	741.7	741.8	742.1	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3
125°	802.9	803.4	803.8	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2
127.5°	865.2	864.8	864.4	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1
130°	903.6	903.2	902.8	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1
132.5°	939.4	938.7	938.1	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1
135°	993.3	992.6	992.0	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6
137.5°	1043.3	1042.8	1042.4	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3
140°	1073.7	1073.2	1072.8	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1
142.5°	1102.3	1101.6	1101.0	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3
147.5°	1178.5	1177.4	1176.4	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9
150°	1201.4	1200.8	1200.1	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3
152.5°	1221.7	1220.6	1219.6	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2
155°	1249.4	1248.1	1246.7	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6
157.5°	1273.2	1271.4	1269.7	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5
160°	1287.1	1285.6	1283.9	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1
162.5°	1300.1	1298.7	1297.4	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5
165°	1317.1	1315.5	1314.0	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0
167.5°	1329.6	1327.7	1326.0	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7
170°	1336.8	1335.0	1333.2	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0
172.5°	1341.3	1339.4	1337.4	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8
175°	1346.8	1345.0	1343.2	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6
177.5°	1348.6	1346.8	1345.0	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	8.4	8.2	7.4	7.0	6.3	5.9	5.2	4.9	4.6	4.1	4.0
90°	24.9	24.0	21.1	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6
95°	32.5	31.0	28.6	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0
97.5°	34.0	32.2	48.2	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6
100°	34.8	33.0	67.7	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0
102.5°	60.3	65.8	103.7	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9
105°	179.7	219.0	239.1	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1
107.5°	372.6	401.6	398.4	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5
110°	443.8	451.2	448.7	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	501.7	501.5	499.1	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4
115°	576.4	574.2	572.2	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2
117.5°	646.4	644.6	643.6	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6
120°	692.0	690.2	689.6	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2
122.5°	737.1	735.8	734.9	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6
125°	800.7	800.2	799.4	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2
127.5°	863.4	862.6	861.6	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9
130°	901.2	900.3	899.4	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3
132.5°	937.2	936.3	935.6	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1
135°	992.0	991.4	990.4	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3
137.5°	1040.2	1039.1	1038.6	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3
140°	1071.3	1070.3	1069.7	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4
142.5°	1100.7	1099.9	1099.3	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0
145°	1141.8	1141.3	1140.9	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4
147.5°	1178.5	1177.9	1177.5	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4
150°	1200.8	1200.4	1200.0	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4
152.5°	1220.4	1219.6	1219.3	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0
155°	1247.5	1246.4	1246.2	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4
157.5°	1271.2	1269.8	1270.1	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0
160°	1284.8	1283.4	1283.7	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4
162.5°	1296.9	1295.4	1295.6	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0
165°	1313.2	1311.4	1311.6	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4
167.5°	1326.0	1324.2	1324.2	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3
170°	1333.2	1331.5	1331.5	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4
172.5°	1338.0	1336.2	1336.0	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2
175°	1344.0	1342.4	1342.2	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4
177.5°	1346.3	1344.8	1344.6	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	4.8	5.3	6.2	7.0	8.1	9.1	9.6	9.8	10.2	10.2	10.3
90°	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7
92.5°	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4
95°	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1
97.5°	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7
100°	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6
102.5°	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8
105°	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3
107.5°	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8
110°	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8
115°	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6
117.5°	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2
120°	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8
122.5°	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3
125°	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2
127.5°	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1
130°	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1
132.5°	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1
135°	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6
137.5°	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3
140°	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1
142.5°	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4
145°	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3
147.5°	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9
150°	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3
152.5°	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2
155°	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6
157.5°	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5
160°	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1
162.5°	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5
165°	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0
167.5°	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7
170°	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0
172.5°	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8
175°	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6
177.5°	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	10.3	10.3	10.3	10.6	10.5	10.4	10.8
90°	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P331901-935

CATALOG NUMBER: S123DIP-S340D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)