

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331889-935

Luminaire Tested: **S123DIP-S340D805U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331889-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D805U935-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3979.6 lumens  
Efficiency: N/A  
Efficacy: 127.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31				
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21				
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17	13				
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12				
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10				
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12	9				
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8				
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5022	5022	5022
5°	5046	4976	5010
10°	5012	4933	4964
15°	4953	4878	4886
20°	4885	4798	4802
25°	4793	4703	4694
30°	4692	4598	4561
35°	4586	4486	4428
40°	4477	4363	4295
45°	4354	4250	4147
50°	4232	4113	3997
55°	4074	3969	3847
60°	3914	3800	3679
65°	3769	3617	3505
70°	3559	3408	3257
75°	3256	3136	3003
80°	2938	2814	2783
85°	2569	2482	2384



TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	124.1	3.1
20°-30°	183.3	4.6
30°-40°	214.1	5.4
40°-50°	215.3	5.4
50°-60°	189.1	4.8
60°-70°	140.9	3.5
70°-80°	80.3	2.0
80°-90°	25.6	0.6
90°-100°	32.9	0.8
100°-110°	157.0	3.9
110°-120°	377.1	9.5
120°-130°	480.2	12.1
130°-140°	513.1	12.9
140°-150°	479.8	12.1
150°-160°	387.0	9.7
160°-170°	249.8	6.3
170°-180°	86.1	2.2
0°-30°	351.4	8.8
0°-40°	565.5	14.2
0°-60°	969.9	24.4
0°-90°	1216.6	30.6
90°-120°	567.0	14.2
90°-150°	2040.1	51.3
90°-180°	2763.0	69.4
0°-180°	3979.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	467	467	467	467	467	
5°	467	465	460	464	464	44
15°	444	443	438	441	438	125
25°	404	401	396	396	395	186
35°	349	346	341	339	337	218
45°	286	284	279	275	272	221
55°	217	216	212	207	205	194
65°	148	146	142	139	138	146
75°	78	77	75	73	72	84
85°	21	20	20	19	19	23
90°	1	8	16	19	20	3
95°	41	15	21	25	26	51
105°	201	204	147	35	30	213
115°	376	380	386	393	396	371
125°	530	536	538	540	541	474
135°	660	664	667	669	667	508
145°	762	766	768	769	769	477
155°	839	838	839	842	838	387
165°	885	883	882	887	883	250
175°	906	903	903	907	903	86
180°	906	906	906	906	906	



TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	468.2	467.9	467.6	467.4	467.0	466.5	465.7	464.9	464.2	463.4	464.1
5°	467.0	466.5	466.1	465.6	465.2	464.5	463.5	462.5	461.5	460.5	461.4
7.5°	462.4	461.9	461.5	461.1	460.6	459.9	458.9	457.9	456.8	455.8	456.6
10°	458.6	458.1	457.6	457.2	456.8	456.0	454.8	453.7	452.5	451.3	452.1
12.5°	453.4	453.1	452.6	452.3	451.9	451.2	450.1	449.0	447.9	446.9	447.5
15°	444.5	444.2	443.8	443.4	443.1	442.3	441.2	440.0	438.9	437.7	438.4
17.5°	434.1	433.7	433.3	432.7	432.3	431.5	430.3	429.2	428.0	426.9	427.3
20°	426.5	425.9	425.4	424.8	424.3	423.4	422.3	421.1	420.0	418.9	419.2
22.5°	417.8	417.2	416.7	416.2	415.7	414.8	413.6	412.5	411.3	410.2	410.4
25°	403.6	403.0	402.5	402.0	401.5	400.6	399.4	398.3	397.1	396.0	396.1
27.5°	388.4	387.9	387.4	386.8	386.3	385.5	384.3	383.0	381.8	380.5	380.6
30°	377.5	377.0	376.6	376.2	375.7	374.9	373.7	372.4	371.2	369.9	369.9
32.5°	366.6	366.0	365.4	364.8	364.3	363.4	362.5	361.5	360.6	359.6	359.1
35°	349.0	348.5	347.9	347.4	346.9	346.0	344.9	343.7	342.6	341.4	340.9
37.5°	331.1	330.4	329.7	329.0	328.4	327.4	326.2	325.0	323.9	322.7	322.1
40°	318.6	318.0	317.5	316.9	316.4	315.5	314.3	313.0	311.8	310.5	309.8
42.5°	306.0	305.4	304.8	304.2	303.6	302.6	301.4	300.1	298.9	297.6	297.0
45°	286.0	285.7	285.3	285.0	284.6	283.9	282.7	281.5	280.3	279.2	278.2
47.5°	266.2	265.7	265.2	264.7	264.2	263.4	262.3	261.1	260.1	259.0	258.0
50°	252.7	252.3	251.8	251.4	251.0	250.1	249.0	247.9	246.7	245.6	244.5
52.5°	238.6	238.3	238.0	237.7	237.4	236.6	235.4	234.2	233.0	231.7	230.9
55°	217.1	217.0	216.9	216.8	216.7	216.0	214.9	213.7	212.6	211.5	210.4
57.5°	196.5	196.2	195.9	195.6	195.3	194.7	193.7	192.8	191.9	191.0	190.1
60°	181.8	181.7	181.6	181.5	181.4	180.8	179.7	178.7	177.6	176.5	175.7
62.5°	168.6	168.3	168.2	167.9	167.6	167.0	165.9	164.9	163.8	162.7	162.0
65°	148.0	147.6	147.1	146.7	146.3	145.6	144.7	143.8	142.9	142.0	141.3
67.5°	126.3	125.9	125.5	125.1	124.8	124.2	123.6	122.9	122.2	121.5	120.9
70°	113.1	112.6	112.1	111.5	111.0	110.5	109.9	109.3	108.8	108.3	107.7
72.5°	99.4	98.9	98.6	98.2	97.7	97.3	96.7	96.1	95.5	94.9	94.3
75°	78.3	77.8	77.5	77.1	76.8	76.5	76.2	75.9	75.7	75.4	75.0
77.5°	59.5	59.3	59.2	59.0	58.7	58.5	58.2	57.9	57.5	57.2	56.9
80°	47.4	47.1	46.8	46.6	46.2	46.1	45.9	45.7	45.5	45.4	45.2
82.5°	35.5	35.4	35.4	35.3	35.2	35.2	35.1	35.1	35.1	35.0	34.9
85°	20.8	20.7	20.5	20.3	20.1	20.1	20.1	20.1	20.1	20.1	19.9
87.5°	8.4	8.5	8.6	8.7	8.8	9.0	9.3	9.6	10.0	10.3	10.3
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	12.5	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2
95°	41.1	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0
97.5°	82.5	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9
100°	113.7	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4
102.5°	149.3	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6
105°	200.6	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0
107.5°	254.7	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8
110°	290.8	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7



TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6
115°	376.3	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9
117.5°	425.7	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0
120°	456.4	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6
122.5°	487.6	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0
125°	530.5	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8
127.5°	571.9	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0
130°	597.7	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4
132.5°	622.5	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7
135°	660.3	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5
137.5°	692.7	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0
140°	714.2	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8
142.5°	734.1	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6
145°	762.0	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4
147.5°	788.2	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0
150°	804.3	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0
152.5°	818.9	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2
155°	839.4	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5
157.5°	855.2	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4
160°	865.0	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5
162.5°	874.1	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7
165°	885.2	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6
167.5°	893.8	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3
170°	898.6	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2
172.5°	901.8	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3
175°	906.0	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4
177.5°	907.1	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	466.6	466.6	466.6	466.6	466.6	466.6	466.6	466.6
2.5°	464.8	465.5	466.2	466.6	466.5	466.4	466.3	466.2
5°	462.4	463.2	464.2	464.5	464.3	464.2	463.9	463.7
7.5°	457.4	458.2	459.0	459.3	459.3	459.2	459.1	458.9
10°	453.0	453.7	454.5	454.9	454.7	454.5	454.3	454.2
12.5°	448.0	448.6	449.2	449.4	449.4	449.2	449.1	449.0
15°	439.1	439.8	440.6	440.7	440.1	439.5	439.0	438.5
17.5°	427.8	428.3	428.9	429.0	428.8	428.6	428.4	428.3
20°	419.6	419.9	420.3	420.3	420.0	419.7	419.5	419.2
22.5°	410.7	411.0	411.3	411.3	411.0	410.6	410.3	409.9
25°	396.1	396.2	396.3	396.2	396.0	395.7	395.5	395.2
27.5°	380.6	380.7	380.7	380.6	380.3	380.0	379.6	379.3
30°	369.9	369.9	369.9	369.5	368.9	368.3	367.7	367.0
32.5°	358.6	358.1	357.7	357.2	356.9	356.5	356.2	355.9
35°	340.4	339.8	339.2	338.8	338.4	337.9	337.4	337.0
37.5°	321.4	320.8	320.1	319.7	319.4	319.1	318.8	318.6
40°	309.1	308.4	307.6	307.1	306.8	306.4	306.1	305.7
42.5°	296.3	295.5	294.8	294.3	293.9	293.6	293.3	292.8
45°	277.1	276.0	274.9	274.2	273.7	273.3	272.9	272.4
47.5°	256.9	255.9	254.8	254.1	253.7	253.3	252.9	252.5
50°	243.6	242.5	241.6	240.8	240.3	239.8	239.3	238.7
52.5°	230.1	229.2	228.3	227.6	227.1	226.6	226.1	225.6
55°	209.5	208.4	207.5	206.8	206.4	205.9	205.4	205.0
57.5°	189.2	188.3	187.4	186.8	186.2	185.7	185.2	184.7
60°	175.0	174.1	173.3	172.7	172.2	171.8	171.3	170.9
62.5°	161.1	160.3	159.5	158.9	158.7	158.3	158.1	157.7
65°	140.6	139.9	139.1	138.7	138.4	138.1	137.8	137.6
67.5°	120.2	119.6	119.0	118.5	118.1	117.7	117.4	117.0
70°	107.1	106.4	105.8	105.3	104.9	104.4	103.9	103.5
72.5°	93.8	93.2	92.6	92.2	92.0	91.8	91.5	91.3
75°	74.6	74.0	73.6	73.3	73.0	72.8	72.5	72.2
77.5°	56.6	56.3	56.0	55.9	55.9	55.9	55.9	55.9
80°	45.1	45.0	44.9	44.9	44.9	44.9	44.9	44.9
82.5°	34.8	34.6	34.4	34.3	34.3	34.2	34.1	34.0
85°	19.7	19.5	19.4	19.3	19.3	19.3	19.3	19.3
87.5°	10.4	10.4	10.5	10.5	10.6	10.7	10.7	10.8
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	19.1	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	23.0	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	24.1	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	24.6	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	36.9	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	94.5	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	231.4	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	293.7	288.8	283.9	270.7	249.3	227.9	206.5	185.1





TEST NUMBER: P331889-935

CATALOG NUMBER: S123DIP-S340D805U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	389.3	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	436.2	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	466.8	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	496.8	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.1	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.4	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.0	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.2	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	700.7	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	721.4	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.1	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	768.6	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.2	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.3	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	821.7	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.2	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	856.3	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	865.4	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	873.7	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	884.8	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	901.6	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	905.4	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	906.9	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)