

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331900-940

Luminaire Tested: **S123DIP-S340D1025U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331900-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4568.9 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	36	36	36	28
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	31	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21	16
4	70	60	52	46	63	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	20	18	16	12
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	1.0
10°-20°	128.5	2.8
20°-30°	189.9	4.2
30°-40°	221.8	4.9
40°-50°	223.0	4.9
50°-60°	195.8	4.3
60°-70°	145.9	3.2
70°-80°	83.1	1.8
80°-90°	27.3	0.6
90°-100°	244.7	5.4
100°-110°	692.9	15.2
110°-120°	681.6	14.9
120°-130°	543.7	11.9
130°-140°	428.7	9.4
140°-150°	319.9	7.0
150°-160°	223.0	4.9
160°-170°	131.0	2.9
170°-180°	42.6	0.9
0°-30°	363.9	8.0
0°-40°	585.7	12.8
0°-60°	1004.5	22.0
0°-90°	1260.8	27.6
90°-120°	1619.2	35.4
90°-150°	2911.5	63.7
90°-180°	3308.0	72.4
0°-180°	4568.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	2	11	22	25	26	3
95°	30	98	528	154	103	33
105°	103	153	716	1251	1132	110
115°	182	227	547	1200	1377	181
125°	254	300	511	926	1086	225
135°	297	355	504	762	880	230
145°	339	389	498	625	688	213
155°	385	416	482	547	570	177
165°	421	433	461	489	498	119
175°	439	439	442	449	448	42
180°	440	440	440	440	440	



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	9.0	9.1	9.3	9.5	9.7	9.9	10.3	10.9	11.3	11.8	11.5
90°	1.8	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4
92.5°	11.1	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3
95°	30.2	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1
97.5°	51.6	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1
100°	65.9	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2
102.5°	80.8	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4
105°	103.3	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1
107.5°	127.1	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0
110°	144.2	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.9	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2
115°	182.4	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4
117.5°	205.1	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4
120°	220.7	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5
122.5°	234.3	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1
125°	253.7	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2
127.5°	268.5	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6
130°	277.7	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7
132.5°	284.8	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4
135°	297.3	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3
137.5°	309.1	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8
140°	316.9	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4
142.5°	325.4	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7
145°	339.1	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0
147.5°	353.0	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5
150°	362.3	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5
152.5°	371.5	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9
155°	385.4	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4
157.5°	396.5	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7
160°	405.0	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3
162.5°	411.4	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9
165°	421.0	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1
167.5°	428.3	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9
170°	432.6	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9
172.5°	435.4	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9
175°	438.8	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2
177.5°	440.4	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	11.6	11.7	11.9	12.1	11.9	12.1	12.3	12.1
90°	22.3	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	74.9	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	320.4	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	798.8	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	1049.5	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1132.7	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1157.1	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1087.0	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1020.0	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P331900-940

CATALOG NUMBER: S123DIP-S340D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	953.8	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	866.0	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	802.5	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	769.0	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	742.7	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	707.7	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	677.0	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	657.8	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	640.0	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	615.9	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	594.1	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	581.2	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	569.1	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	554.6	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	542.6	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	534.0	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	526.2	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	514.4	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	502.0	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	494.9	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	486.3	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	475.3	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	465.7	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	459.3	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	453.6	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	445.9	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.1	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)