

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331880-940

Luminaire Tested: **S123DIP-S340D585U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331880-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D585U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3346.9 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32
2	86	79	73	68	78	72	67	62	59	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	1.4
10°-20°	128.5	3.8
20°-30°	189.9	5.7
30°-40°	221.8	6.6
40°-50°	223.0	6.7
50°-60°	195.8	5.9
60°-70°	145.9	4.4
70°-80°	83.1	2.5
80°-90°	25.8	0.8
90°-100°	24.9	0.7
100°-110°	118.6	3.5
110°-120°	284.9	8.5
120°-130°	362.8	10.8
130°-140°	387.7	11.6
140°-150°	362.5	10.8
150°-160°	292.4	8.7
160°-170°	188.7	5.6
170°-180°	65.0	1.9
0°-30°	363.9	10.9
0°-40°	585.7	17.5
0°-60°	1004.5	30.0
0°-90°	1259.3	37.6
90°-120°	428.4	12.8
90°-150°	1541.4	46.1
90°-180°	2088.0	62.4
0°-180°	3346.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	0	6	12	14	15	3
95°	31	12	16	19	19	38
105°	152	154	111	26	22	161
115°	284	287	292	297	299	281
125°	401	405	407	408	409	358
135°	499	502	504	505	504	384
145°	576	579	580	581	581	360
155°	634	633	634	636	633	292
165°	669	667	667	670	667	189
175°	685	682	682	686	682	65
180°	685	685	685	685	685	



TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.7	8.7	8.7	8.7	8.7	8.9	9.1	9.3	9.5	9.7	9.8
90°	0.5	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7
92.5°	9.5	9.2	8.8	8.5	8.2	8.6	9.7	10.8	11.9	13.0	13.7
95°	31.0	26.4	21.8	17.1	12.5	10.8	12.0	13.3	14.5	15.8	16.6
97.5°	62.3	60.3	58.2	56.1	54.0	49.0	40.8	32.6	24.5	16.4	17.3
100°	86.0	88.2	90.5	92.7	95.0	87.3	69.6	52.1	34.4	16.8	17.7
102.5°	112.8	114.4	116.1	117.7	119.3	110.5	91.2	72.0	52.7	33.4	30.7
105°	151.6	152.8	154.1	155.2	156.5	152.0	141.9	131.7	121.5	111.4	91.4
107.5°	192.4	193.4	194.5	195.5	196.4	197.7	199.3	200.9	202.5	204.1	189.5
110°	219.7	220.6	221.5	222.4	223.3	224.4	225.6	226.9	228.1	229.3	225.6



TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.6	247.4	248.2	249.0	250.0	251.3	252.5	253.8	255.0	255.1
115°	284.3	285.0	285.6	286.3	287.0	287.8	288.9	289.9	290.9	291.9	293.1
117.5°	321.6	322.4	323.3	324.1	324.9	325.7	326.2	326.7	327.3	327.7	328.7
120°	344.8	345.8	346.9	347.9	348.9	349.6	349.9	350.3	350.6	350.9	351.9
122.5°	368.5	369.3	370.1	371.0	371.8	372.4	372.8	373.3	373.7	374.2	374.8
125°	400.7	401.7	402.6	403.5	404.4	405.1	405.6	406.0	406.4	406.9	407.1
127.5°	432.1	433.0	433.9	434.8	435.7	436.4	436.9	437.6	438.1	438.6	439.0
130°	451.7	452.5	453.4	454.3	455.2	455.9	456.4	456.8	457.3	457.7	458.2
132.5°	470.4	471.3	472.2	473.1	473.9	474.6	474.9	475.3	475.6	476.1	476.5
135°	498.9	499.6	500.2	501.0	501.7	502.2	502.7	503.1	503.5	504.0	504.4
137.5°	523.3	524.2	525.0	525.9	526.7	527.4	527.5	527.8	528.1	528.3	528.9
140°	539.6	540.3	541.0	541.6	542.3	542.9	543.1	543.5	543.9	544.2	544.7
142.5°	554.6	555.4	556.1	556.7	557.4	557.9	558.2	558.6	558.9	559.3	559.6
145°	575.7	576.5	577.3	578.1	578.9	579.4	579.6	579.9	580.1	580.3	580.5
147.5°	595.6	596.1	596.6	597.1	597.6	598.0	598.2	598.4	598.7	599.0	599.1
150°	607.8	608.1	608.4	608.8	609.1	609.4	609.7	609.8	610.1	610.3	610.6
152.5°	618.8	618.9	619.0	619.2	619.4	619.6	619.6	619.8	619.9	620.1	620.5
155°	634.2	634.0	633.7	633.6	633.3	633.3	633.4	633.5	633.6	633.7	634.3
157.5°	646.2	646.2	646.1	646.1	646.1	646.0	646.0	645.9	645.7	645.6	646.3
160°	653.5	653.4	653.4	653.2	653.1	653.0	652.8	652.7	652.6	652.6	653.2
162.5°	660.5	660.1	659.9	659.6	659.2	659.1	659.0	658.9	658.7	658.6	659.4
165°	668.8	668.4	668.2	667.8	667.4	667.2	667.1	667.0	666.9	666.7	667.7
167.5°	675.3	674.8	674.4	674.0	673.5	673.2	673.2	673.2	673.2	673.2	674.2
170°	678.9	678.5	678.1	677.6	677.2	676.9	676.9	676.9	676.9	676.9	677.9
172.5°	681.4	680.9	680.3	679.8	679.2	679.0	679.1	679.2	679.3	679.4	680.3
175°	684.6	684.0	683.4	682.9	682.3	682.1	682.2	682.3	682.4	682.5	683.3
177.5°	685.4	684.9	684.5	684.0	683.6	683.4	683.5	683.6	683.7	683.8	684.5
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6



TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	9.8	9.8	9.8	9.8	9.9	9.9	10.0	10.1
90°	13.1	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	14.4	15.2	15.9	16.3	16.5	16.6	16.8	16.9
95°	17.4	18.1	18.9	19.4	19.4	19.4	19.4	19.4
97.5°	18.2	19.1	20.0	20.5	20.6	20.7	20.9	21.0
100°	18.5	19.5	20.4	20.9	21.0	21.1	21.2	21.4
102.5°	27.8	25.1	22.3	21.0	21.1	21.4	21.6	21.8
105°	71.3	51.4	31.4	21.5	21.7	21.9	22.1	22.4
107.5°	174.8	160.2	145.4	130.6	115.5	100.4	85.3	70.3
110°	221.9	218.2	214.5	204.5	188.3	172.2	156.0	139.8





TEST NUMBER: P331880-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	255.2	255.3	253.6	250.2	246.7	243.3	240.0
115°	294.2	295.3	296.5	297.2	297.7	298.2	298.6	299.1
117.5°	329.6	330.5	331.4	331.9	332.0	332.1	332.2	332.3
120°	352.8	353.7	354.5	355.0	355.0	355.0	355.0	355.0
122.5°	375.4	376.0	376.7	377.0	377.1	377.2	377.3	377.4
125°	407.3	407.5	407.8	408.0	408.2	408.5	408.7	408.9
127.5°	439.3	439.7	440.1	440.1	439.9	439.7	439.4	439.3
130°	458.6	459.1	459.5	459.7	459.4	459.2	459.0	458.8
132.5°	477.0	477.4	477.9	478.0	477.6	477.2	477.0	476.6
135°	504.7	505.1	505.3	505.3	505.1	504.7	504.4	504.0
137.5°	529.4	529.9	530.5	530.7	530.4	530.2	529.9	529.8
140°	545.1	545.5	546.0	546.1	545.9	545.6	545.5	545.2
142.5°	560.0	560.4	560.7	560.7	560.4	560.1	559.7	559.5
145°	580.8	580.9	581.2	581.3	581.3	581.3	581.3	581.3
147.5°	599.4	599.6	599.9	599.7	599.1	598.6	598.2	597.6
150°	610.7	611.0	611.2	611.2	610.8	610.5	610.1	609.8
152.5°	620.9	621.3	621.7	621.6	621.2	620.6	620.1	619.6
155°	634.8	635.4	636.0	635.9	635.3	634.5	633.9	633.2
157.5°	646.9	647.6	648.4	648.2	647.3	646.5	645.6	644.7
160°	653.9	654.5	655.2	655.1	654.4	653.6	652.8	652.0
162.5°	660.1	660.9	661.7	661.7	661.0	660.3	659.6	659.0
165°	668.6	669.5	670.4	670.5	669.7	668.9	668.1	667.3
167.5°	675.1	676.0	676.9	676.9	676.0	675.1	674.2	673.2
170°	678.8	679.7	680.6	680.6	679.7	678.8	677.9	676.9
172.5°	681.2	682.1	683.0	683.0	682.0	681.0	679.9	678.9
175°	684.1	684.9	685.7	685.6	684.7	683.9	683.0	682.0
177.5°	685.2	685.9	686.6	686.5	685.6	684.7	683.9	683.0
180°	684.6	684.6	684.6	684.6	684.6	684.6	684.6	684.6

(END OF REPORT)