

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331882-940

Luminaire Tested: **S123DIP-S340D585U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331882-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D585U940-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3149.6 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	68	79	73	67	63	60	56	53	47	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	24	21	21	19	16	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5201	5201	5201
5°	5226	5154	5190
10°	5191	5109	5141
15°	5131	5051	5060
20°	5060	4969	4974
25°	4963	4871	4861
30°	4860	4762	4724
35°	4750	4646	4586
40°	4636	4519	4449
45°	4509	4402	4294
50°	4382	4258	4140
55°	4219	4110	3984
60°	4052	3935	3810
65°	3904	3744	3629
70°	3688	3531	3374
75°	3373	3248	3111
80°	3037	2913	2882
85°	2668	2569	2470



TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.5	1.4
10°-20°	128.5	4.1
20°-30°	189.9	6.0
30°-40°	221.8	7.0
40°-50°	223.0	7.1
50°-60°	195.8	6.2
60°-70°	145.9	4.6
70°-80°	83.1	2.6
80°-90°	25.8	0.8
90°-100°	139.8	4.4
100°-110°	395.9	12.6
110°-120°	389.5	12.4
120°-130°	310.7	9.9
130°-140°	244.9	7.8
140°-150°	182.8	5.8
150°-160°	127.4	4.0
160°-170°	74.9	2.4
170°-180°	24.4	0.8
0°-30°	363.9	11.6
0°-40°	585.7	18.6
0°-60°	1004.5	31.9
0°-90°	1259.3	40.0
90°-120°	925.2	29.4
90°-150°	1663.7	52.8
90°-180°	1890.0	60.0
0°-180°	3149.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	483	483	483	483	483	
5°	484	481	477	481	480	46
15°	460	458	453	456	454	130
25°	418	415	410	410	409	192
35°	362	359	354	351	349	226
45°	296	294	289	284	282	229
55°	225	224	219	215	212	201
65°	153	151	147	144	142	151
75°	81	79	78	76	75	87
85°	22	21	21	20	20	24
90°	1	6	13	14	15	2
95°	17	56	302	88	59	19
105°	59	87	409	715	647	63
115°	104	130	313	686	787	103
125°	145	171	292	529	620	129
135°	170	203	288	436	503	131
145°	194	222	284	357	393	121
155°	220	238	275	313	326	101
165°	241	247	264	279	284	68
175°	251	251	253	256	256	24
180°	251	251	251	251	251	



TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	484.9	484.6	484.3	484.0	483.7	483.1	482.3	481.5	480.7	479.9	480.6
5°	483.7	483.1	482.7	482.2	481.8	481.1	480.0	479.0	478.0	477.0	477.9
7.5°	478.9	478.4	478.0	477.5	477.1	476.3	475.3	474.2	473.1	472.1	472.9
10°	474.9	474.5	473.9	473.5	473.1	472.3	471.0	469.8	468.6	467.4	468.2
12.5°	469.6	469.2	468.8	468.4	468.1	467.3	466.2	465.0	463.9	462.8	463.4
15°	460.4	460.0	459.6	459.2	458.9	458.1	456.9	455.7	454.5	453.3	454.1
17.5°	449.6	449.2	448.7	448.2	447.7	446.9	445.7	444.5	443.3	442.1	442.6
20°	441.7	441.1	440.6	440.0	439.4	438.5	437.4	436.1	435.0	433.8	434.2
22.5°	432.7	432.1	431.6	431.1	430.5	429.6	428.4	427.2	426.0	424.8	425.1
25°	417.9	417.4	416.9	416.3	415.8	414.9	413.7	412.5	411.3	410.1	410.2
27.5°	402.3	401.7	401.2	400.6	400.1	399.2	398.0	396.6	395.4	394.0	394.1
30°	391.0	390.5	390.0	389.6	389.1	388.3	387.0	385.7	384.4	383.1	383.1
32.5°	379.7	379.1	378.4	377.8	377.3	376.4	375.4	374.4	373.4	372.5	371.9
35°	361.5	361.0	360.3	359.8	359.3	358.4	357.2	356.0	354.8	353.6	353.0
37.5°	342.9	342.1	341.4	340.7	340.1	339.1	337.9	336.6	335.5	334.2	333.6
40°	329.9	329.3	328.8	328.2	327.7	326.7	325.5	324.1	322.9	321.6	320.8
42.5°	316.9	316.3	315.7	315.0	314.4	313.4	312.2	310.9	309.6	308.3	307.6
45°	296.2	295.9	295.5	295.2	294.8	294.0	292.7	291.6	290.3	289.2	288.1
47.5°	275.7	275.2	274.6	274.1	273.6	272.8	271.6	270.5	269.4	268.2	267.2
50°	261.7	261.3	260.8	260.4	259.9	259.0	257.9	256.7	255.5	254.3	253.2
52.5°	247.1	246.8	246.5	246.2	245.8	245.0	243.8	242.5	241.3	240.0	239.2
55°	224.8	224.7	224.6	224.5	224.4	223.7	222.6	221.3	220.2	219.0	217.9
57.5°	203.5	203.2	202.9	202.6	202.2	201.6	200.6	199.7	198.8	197.8	196.9
60°	188.2	188.2	188.1	188.0	187.9	187.3	186.1	185.0	184.0	182.8	182.0
62.5°	174.6	174.3	174.2	173.9	173.6	173.0	171.8	170.8	169.6	168.5	167.7
65°	153.3	152.8	152.4	151.9	151.5	150.8	149.9	148.9	148.0	147.0	146.3
67.5°	130.8	130.4	130.0	129.6	129.2	128.6	128.0	127.2	126.5	125.8	125.2
70°	117.2	116.6	116.1	115.5	114.9	114.4	113.9	113.2	112.7	112.2	111.6
72.5°	102.9	102.5	102.1	101.7	101.2	100.8	100.1	99.5	98.9	98.3	97.6
75°	81.1	80.6	80.3	79.9	79.5	79.2	78.9	78.6	78.4	78.1	77.7
77.5°	61.6	61.4	61.3	61.1	60.8	60.5	60.3	59.9	59.6	59.2	58.9
80°	49.0	48.8	48.5	48.2	47.9	47.7	47.5	47.3	47.2	47.0	46.8
82.5°	36.7	36.6	36.6	36.6	36.5	36.5	36.4	36.4	36.4	36.3	36.1
85°	21.6	21.4	21.2	21.0	20.9	20.8	20.8	20.8	20.8	20.8	20.6
87.5°	8.8	8.8	8.8	8.9	8.9	8.9	9.2	9.4	9.6	9.9	9.7
90°	1.0	2.1	3.0	4.5	5.6	6.6	8.1	9.6	11.1	12.8	12.2
92.5°	6.3	9.4	13.6	17.6	21.8	29.4	42.7	64.6	86.1	78.2	59.0
95°	17.3	18.8	24.4	33.1	46.3	66.1	109.3	185.1	268.6	301.6	244.6
97.5°	29.5	30.1	34.4	41.9	54.9	76.4	117.7	203.1	342.1	467.4	500.1
100°	37.6	38.2	41.7	48.9	61.0	80.9	116.5	191.7	325.5	481.6	581.8
102.5°	46.2	47.1	50.3	57.0	67.9	86.1	118.1	182.0	301.1	455.2	585.9
105°	59.0	60.5	63.6	69.6	79.4	95.1	122.6	175.0	271.1	408.9	554.9
107.5°	72.6	74.2	77.1	83.1	92.2	106.8	130.9	174.4	252.0	368.0	500.6
110°	82.4	83.9	86.5	92.0	100.7	114.9	137.9	176.5	244.6	344.8	466.4



TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	91.3	92.9	95.4	101.0	109.7	123.5	144.7	180.6	240.6	329.4	436.7
115°	104.2	106.3	109.3	114.4	123.1	136.8	156.1	187.2	239.1	312.8	400.8
117.5°	117.2	119.5	122.1	126.7	136.4	149.1	168.3	195.9	240.0	303.0	379.2
120°	126.2	127.7	130.2	135.3	145.0	157.7	175.9	202.4	241.6	298.5	367.7
122.5°	133.8	135.4	137.9	143.4	152.7	166.2	184.1	208.6	244.4	295.7	358.4
125°	145.0	146.0	149.0	154.6	164.3	178.0	195.8	218.2	248.7	291.9	346.3
127.5°	153.4	154.9	158.7	164.3	175.0	188.8	206.0	226.1	253.6	290.1	335.8
130°	158.7	160.2	164.8	170.9	181.6	195.3	212.0	231.4	256.8	288.9	330.1
132.5°	162.7	164.7	169.7	177.0	187.7	201.0	217.4	236.3	259.3	288.5	324.8
135°	169.9	171.9	177.5	185.1	195.8	209.6	225.3	242.6	263.0	287.8	317.9
137.5°	176.6	178.7	184.2	192.3	203.0	215.6	230.8	247.3	265.4	286.8	311.9
140°	181.1	183.6	188.7	196.8	207.0	219.7	234.4	249.8	267.0	286.3	308.2
142.5°	185.9	188.1	193.6	200.9	211.1	223.0	237.3	252.2	268.2	285.5	305.0
145°	193.8	195.3	199.9	207.5	216.2	227.8	241.1	254.9	269.0	284.3	300.6
147.5°	201.7	202.6	207.1	213.7	222.0	232.0	244.2	256.5	269.0	282.4	296.3
150°	207.0	207.5	211.6	218.2	225.3	234.4	246.2	256.8	269.0	280.7	293.5
152.5°	212.3	212.4	216.5	222.3	228.5	237.3	247.4	257.7	267.9	278.7	290.3
155°	220.3	220.3	223.3	228.4	234.0	241.1	249.8	257.9	266.5	275.2	285.3
157.5°	226.5	226.9	229.3	233.9	238.6	244.2	251.0	258.4	264.7	272.0	279.8
160°	231.4	231.4	233.4	237.6	241.1	246.2	252.3	258.4	263.9	269.6	276.2
162.5°	235.1	235.1	236.7	240.0	243.1	247.4	252.7	258.0	262.3	267.2	272.5
165°	240.6	240.0	241.1	243.6	245.7	249.2	253.2	256.8	259.9	263.5	267.5
167.5°	244.8	244.2	244.6	246.6	248.0	250.2	253.2	256.0	257.4	259.8	262.8
170°	247.2	246.2	246.6	248.2	249.2	250.2	252.8	254.9	255.8	257.3	259.9
172.5°	248.8	248.2	248.3	249.4	250.0	250.7	252.8	254.4	254.6	255.3	257.1
175°	250.7	250.2	249.8	250.7	250.7	251.3	252.3	253.2	252.8	252.8	253.8
177.5°	251.6	251.3	250.8	251.3	251.3	251.3	251.6	252.4	251.6	251.3	251.6
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3



TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	483.2	483.2	483.2	483.2	483.2	483.2	483.2	483.2
2.5°	481.3	482.1	482.9	483.2	483.1	483.0	483.0	482.9
5°	478.8	479.7	480.7	481.1	480.9	480.7	480.5	480.3
7.5°	473.8	474.6	475.4	475.7	475.6	475.5	475.5	475.3
10°	469.1	469.9	470.7	471.1	470.9	470.7	470.6	470.4
12.5°	464.0	464.6	465.2	465.5	465.4	465.2	465.1	465.0
15°	454.8	455.5	456.3	456.4	455.8	455.2	454.7	454.1
17.5°	443.1	443.6	444.2	444.3	444.1	443.9	443.7	443.5
20°	434.5	434.9	435.2	435.3	435.0	434.7	434.4	434.2
22.5°	425.3	425.7	426.0	426.0	425.6	425.3	424.9	424.5
25°	410.3	410.4	410.5	410.4	410.1	409.8	409.6	409.3
27.5°	394.2	394.3	394.3	394.2	393.9	393.5	393.2	392.8
30°	383.1	383.1	383.1	382.7	382.1	381.5	380.8	380.1
32.5°	371.4	370.9	370.4	370.0	369.6	369.3	368.9	368.5
35°	352.5	352.0	351.3	350.9	350.4	349.9	349.5	349.0
37.5°	332.9	332.3	331.5	331.1	330.8	330.5	330.2	329.9
40°	320.1	319.4	318.6	318.1	317.7	317.4	317.0	316.6
42.5°	306.8	306.0	305.3	304.8	304.4	304.1	303.7	303.3
45°	287.0	285.9	284.7	284.0	283.5	283.0	282.6	282.1
47.5°	266.1	265.0	263.9	263.1	262.7	262.3	261.9	261.5
50°	252.3	251.2	250.2	249.4	248.9	248.3	247.8	247.2
52.5°	238.3	237.4	236.5	235.8	235.2	234.7	234.2	233.6
55°	217.0	215.9	214.9	214.2	213.7	213.2	212.8	212.3
57.5°	196.0	195.0	194.1	193.4	192.9	192.3	191.8	191.3
60°	181.2	180.3	179.5	178.9	178.3	177.9	177.5	177.0
62.5°	166.8	166.0	165.2	164.6	164.3	164.0	163.7	163.4
65°	145.6	144.9	144.1	143.7	143.4	143.0	142.8	142.5
67.5°	124.5	123.9	123.2	122.7	122.3	121.9	121.5	121.2
70°	110.9	110.2	109.6	109.1	108.6	108.2	107.6	107.2
72.5°	97.1	96.5	95.9	95.5	95.3	95.1	94.8	94.5
75°	77.2	76.7	76.2	75.9	75.6	75.3	75.1	74.8
77.5°	58.6	58.3	58.0	57.9	57.9	57.9	57.9	57.9
80°	46.7	46.6	46.5	46.5	46.5	46.5	46.5	46.5
82.5°	36.0	35.8	35.7	35.5	35.5	35.4	35.3	35.2
85°	20.4	20.2	20.1	20.0	20.0	20.0	20.0	20.0
87.5°	9.7	9.7	9.7	9.9	9.8	9.9	10.1	9.9
90°	12.8	13.2	13.7	14.7	14.3	14.7	15.2	14.7
92.5°	42.8	34.0	30.1	27.4	26.5	24.9	25.4	24.5
95°	183.1	124.1	97.1	78.8	69.2	64.6	61.0	59.0
97.5°	456.5	365.6	300.0	239.2	201.6	178.7	165.0	160.6
100°	599.7	558.5	498.9	426.7	375.3	338.2	318.4	318.9
102.5°	647.3	646.0	611.3	565.4	525.5	496.1	479.5	467.8
105°	661.2	712.0	721.8	708.5	685.1	665.8	649.5	646.9
107.5°	621.1	703.7	748.2	766.3	766.8	760.3	754.7	750.1
110°	582.8	676.5	740.6	776.1	790.4	794.4	793.4	792.4





TEST NUMBER: P331882-940

CATALOG NUMBER: S123DIP-S340D585U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	545.0	640.6	712.5	758.2	784.3	796.9	800.8	800.9
115°	494.9	583.4	658.2	713.5	751.7	774.1	784.3	786.8
117.5°	458.5	534.9	602.1	658.4	698.1	723.7	738.4	741.8
120°	439.4	508.1	569.1	620.5	660.7	689.2	701.3	704.5
122.5°	424.4	486.5	543.1	590.8	626.5	652.1	665.6	669.4
125°	404.3	459.8	508.6	549.3	581.8	604.2	617.0	620.5
127.5°	386.8	436.3	480.4	517.4	546.4	565.4	576.9	580.2
130°	375.9	421.6	462.8	497.4	524.4	542.7	553.4	557.4
132.5°	365.7	407.8	446.1	479.1	504.4	522.7	532.2	535.0
135°	352.0	388.1	421.2	450.1	475.0	490.3	499.4	503.0
137.5°	339.5	369.1	397.5	422.7	443.6	459.1	466.8	469.1
140°	332.2	358.0	382.5	404.3	423.7	437.9	446.0	445.5
142.5°	325.2	347.5	368.6	387.6	404.1	416.8	424.1	423.6
145°	316.8	333.7	349.9	364.7	377.4	388.1	392.2	393.2
147.5°	310.0	323.3	336.5	347.0	356.6	363.8	367.7	368.1
150°	305.1	316.8	327.5	337.2	344.8	350.4	353.5	353.5
152.5°	300.7	310.8	320.2	328.2	334.2	339.5	341.3	341.3
155°	294.0	302.1	309.8	315.8	320.4	324.5	325.5	326.0
157.5°	286.9	293.6	299.6	304.3	308.4	311.4	312.2	312.1
160°	282.8	288.4	293.5	297.0	300.6	303.6	303.6	303.1
162.5°	277.9	282.7	287.4	290.5	292.8	295.5	295.5	295.0
165°	271.6	274.6	278.2	280.7	282.8	284.8	284.3	284.3
167.5°	266.1	268.4	270.5	272.3	273.2	274.6	274.1	274.1
170°	262.4	263.9	266.0	267.0	267.5	268.6	268.0	268.0
172.5°	259.2	260.3	261.9	262.5	262.6	263.7	262.8	262.3
175°	254.9	255.3	256.4	256.4	256.4	256.8	256.4	255.8
177.5°	252.1	252.4	252.9	252.9	252.4	252.9	252.1	252.1
180°	251.3	251.3	251.3	251.3	251.3	251.3	251.3	251.3

(END OF REPORT)