

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331948-935

Luminaire Tested: **S123DIP-S560D1195U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331948-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5776.0 lumens  
Efficiency: N/A  
Efficacy: 116.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36				
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30				
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27	22				
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19				
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17				
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15				
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16	13				
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	18	16	14	12				
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10				
10	45	33	26	22	41	31	25	20	25	21	17	20	17	14	16	13	12	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7326	7326	7326	7326
5°	8737	7358	6521	7358
10°	10935	7321	5889	7321
15°	13412	7261	5483	7261
20°	15978	7170	5220	7170
25°	16966	7058	5162	7058
30°	14542	6976	5189	6976
35°	10113	6859	5243	6859
40°	7617	6724	5227	6724
45°	6325	6520	5160	6520
50°	5667	6107	5114	6107
55°	5296	5662	5050	5662
60°	4969	5197	4997	5197
65°	4669	4737	4837	4737
70°	4378	4214	4607	4214
75°	3922	3689	4225	3689
80°	3434	3025	3639	3025
85°	2692	2198	2445	2198



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.0	1.2
10°-20°	215.0	3.7
20°-30°	360.8	6.2
30°-40°	408.6	7.1
40°-50°	366.4	6.3
50°-60°	295.7	5.1
60°-70°	206.0	3.6
70°-80°	108.3	1.9
80°-90°	30.3	0.5
90°-100°	275.0	4.8
100°-110°	778.7	13.5
110°-120°	766.1	13.3
120°-130°	611.0	10.6
130°-140°	481.8	8.3
140°-150°	359.6	6.2
150°-160°	250.6	4.3
160°-170°	147.2	2.5
170°-180°	47.9	0.8
0°-30°	642.9	11.1
0°-40°	1051.4	18.2
0°-60°	1713.5	29.7
0°-90°	2058.1	35.6
90°-120°	1819.8	31.5
90°-150°	3272.2	56.7
90°-180°	3718.0	64.4
0°-180°	5776.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	681	681	681	681	681	
5°	809	681	604	681	809	84
15°	1204	652	492	652	1204	348
25°	1428	594	435	594	1428	626
35°	770	522	399	522	770	500
45°	416	428	339	428	416	329
55°	282	302	269	302	282	253
65°	183	186	190	186	183	183
75°	94	89	102	89	94	101
85°	22	18	20	18	22	27
90°	29	2	29	2	29	16
95°	116	34	116	34	116	209
105°	1272	116	1272	116	1272	1255
115°	1548	205	1548	205	1548	1504
125°	1220	285	1220	285	1220	1106
135°	989	334	989	334	989	767
145°	773	381	773	381	773	492
155°	641	433	641	433	641	299
165°	559	473	559	473	559	160
175°	503	493	503	493	503	49
180°	494	494	494	494	494	



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	722.3	721.8	720.5	721.5	719.4	716.5	716.3	713.6	705.9	705.4	703.4
5°	808.6	805.9	805.6	805.3	800.6	794.4	782.5	781.5	765.7	757.8	748.2
7.5°	920.3	921.7	916.9	912.7	898.5	889.2	876.5	860.2	840.8	821.0	807.9
10°	1000.5	1011.3	997.8	988.6	980.1	963.9	945.1	921.7	898.3	870.9	850.2
12.5°	1086.5	1091.8	1089.2	1080.4	1067.1	1042.5	1009.2	983.4	961.8	916.3	897.9
15°	1203.6	1223.7	1210.9	1181.2	1181.9	1158.5	1114.9	1067.1	1041.7	1001.8	947.4
17.5°	1328.4	1330.9	1325.4	1300.7	1284.2	1252.1	1211.9	1166.1	1114.6	1066.3	1008.6
20°	1394.9	1392.9	1381.4	1368.5	1340.1	1315.1	1271.2	1220.1	1154.2	1106.6	1043.7
22.5°	1431.8	1428.5	1423.1	1412.3	1388.7	1361.8	1322.4	1266.5	1203.8	1138.3	1065.6
25°	1428.5	1432.8	1433.5	1430.5	1422.3	1406.1	1375.1	1330.6	1267.9	1183.9	1108.0
27.5°	1299.2	1305.3	1322.9	1338.6	1356.1	1373.8	1371.5	1349.4	1303.0	1230.4	1137.6
30°	1170.0	1156.8	1189.5	1230.6	1258.7	1308.1	1335.8	1337.5	1311.5	1249.1	1158.7
32.5°	990.6	1005.1	1019.5	1070.2	1131.5	1187.1	1242.2	1286.6	1291.7	1250.2	1171.1
35°	769.6	787.8	814.2	840.6	906.5	963.2	1060.1	1144.6	1211.9	1220.7	1172.3
37.5°	620.2	629.2	645.8	672.3	715.4	782.7	857.7	964.4	1061.9	1134.4	1137.6
40°	542.1	544.8	563.5	583.7	618.6	674.0	741.7	835.9	952.7	1054.0	1096.1
42.5°	483.5	489.4	497.3	516.7	544.5	586.2	649.0	727.0	834.0	950.5	1033.0
45°	415.5	422.1	427.1	439.9	459.7	487.7	531.6	602.8	684.2	804.6	915.8
47.5°	370.5	371.0	374.7	384.4	397.9	419.0	450.0	495.7	570.5	668.0	782.2
50°	338.4	343.6	344.9	352.5	363.1	378.6	404.3	443.2	504.5	590.3	695.2
52.5°	315.6	317.2	320.9	326.4	335.6	347.7	370.0	400.5	448.6	521.7	618.1
55°	282.2	282.2	285.9	290.2	295.5	306.3	321.2	343.6	380.2	437.0	516.8
57.5°	251.4	253.0	255.6	256.9	261.4	268.6	281.0	298.1	325.4	369.0	432.5
60°	230.8	233.8	233.5	236.1	240.0	245.6	256.2	270.1	294.5	329.4	382.9
62.5°	212.9	212.7	212.7	215.8	219.7	225.1	232.0	243.9	264.7	295.7	341.1
65°	183.3	182.7	185.0	187.0	188.3	192.3	197.5	208.1	222.0	245.0	280.3
67.5°	157.1	155.2	156.4	157.1	159.4	162.5	167.4	173.9	184.9	203.5	230.1
70°	139.1	137.5	137.2	137.8	139.8	142.2	145.8	152.1	162.2	177.1	196.6
72.5°	120.7	119.6	119.5	121.0	121.9	123.4	126.0	131.7	139.8	150.9	169.1
75°	94.3	94.3	94.3	94.6	95.7	96.9	98.9	101.9	108.1	116.1	128.3
77.5°	70.7	70.6	70.3	70.2	71.6	72.2	72.7	75.4	79.0	84.3	93.2
80°	55.4	53.7	54.4	55.4	56.1	56.4	57.3	58.0	61.0	64.0	70.3
82.5°	41.2	39.8	39.9	41.4	41.6	41.8	42.9	43.8	44.9	47.6	51.0
85°	21.8	21.8	22.1	22.1	22.4	22.1	23.1	23.4	23.4	25.1	27.0
87.5°	13.7	13.4	13.4	13.5	13.4	13.3	13.3	13.4	13.5	13.9	13.6
90°	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2	116.1	153.9	169.3
95°	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2	481.1	593.2	528.2
97.5°	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7	983.5	919.3	673.0
100°	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4	1144.4	947.4	640.2
102.5°	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1	1152.4	895.4	592.2
105°	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5	1091.4	804.3	533.2
107.5°	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6	984.6	723.8	495.6
110°	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4	917.3	678.2	481.1



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9	858.9	647.8	473.2
115°	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4	788.2	615.2	470.2
117.5°	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9	745.6	596.0	472.0
120°	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3	723.2	587.2	475.2
122.5°	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7	704.8	581.6	480.8
125°	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3	681.2	574.2	489.1
127.5°	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9	660.5	570.6	498.8
130°	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3	649.2	568.2	505.1
132.5°	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3	638.9	567.4	510.0
135°	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2	625.3	566.2	517.2
137.5°	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6	613.4	564.0	522.0
140°	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2	606.2	563.2	525.2
142.5°	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6	599.8	561.6	527.6
145°	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2	591.2	559.2	529.2
147.5°	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8	582.8	555.4	529.2
150°	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2	577.2	552.2	529.2
152.5°	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4	570.8	548.2	526.8
155°	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2	561.2	541.2	524.2
157.5°	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2	550.4	535.0	520.8
160°	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2	543.2	530.2	519.2
162.5°	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6	536.0	525.4	516.0
165°	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2	526.2	518.1	511.2
167.5°	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4	516.8	511.0	506.4
170°	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2	511.2	506.2	503.2
172.5°	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8	505.6	502.1	500.8
175°	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2	499.2	497.1	497.1
177.5°	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	701.7	699.6	697.5	693.8	690.6	686.1	684.8	683.3	678.6	674.2	671.1
5°	744.6	736.7	725.1	714.5	706.0	694.5	687.9	681.0	671.1	662.2	654.9
7.5°	789.5	773.9	756.0	736.6	718.5	701.0	687.0	674.5	660.6	647.5	637.3
10°	825.1	802.6	777.6	750.5	727.5	705.0	686.2	669.8	651.9	636.5	623.5
12.5°	865.6	832.4	797.9	765.0	737.7	706.6	683.9	662.9	642.7	624.1	609.6
15°	913.8	871.6	830.7	785.5	743.9	705.0	678.0	651.6	628.2	609.1	590.6
17.5°	957.5	909.7	855.8	800.9	750.8	704.6	666.8	637.0	607.7	584.3	565.8
20°	982.3	927.9	866.9	809.9	754.5	703.0	661.5	625.9	594.3	569.5	548.7
22.5°	1003.8	940.0	876.9	816.0	754.2	698.8	651.8	615.1	580.7	556.6	534.5
25°	1025.9	949.7	886.4	814.9	745.9	688.5	635.8	594.3	559.9	531.6	508.9
27.5°	1044.9	949.1	873.9	796.9	732.9	675.4	619.1	574.5	538.0	507.2	484.1
30°	1057.6	950.4	861.0	784.8	720.2	660.8	606.1	561.3	523.0	491.6	469.9
32.5°	1065.5	949.6	849.1	767.9	700.2	647.6	592.1	545.7	506.4	475.6	454.6
35°	1070.1	943.7	828.7	733.1	667.8	616.6	570.2	522.0	480.8	452.1	428.3
37.5°	1060.8	931.6	804.9	699.4	627.9	577.6	538.5	497.5	458.1	426.5	406.0
40°	1046.3	923.7	786.4	675.7	600.5	552.0	518.8	478.5	439.5	409.6	390.5
42.5°	1018.6	907.6	766.2	649.3	572.0	523.5	492.8	459.3	422.4	394.3	375.1
45°	951.1	872.5	735.7	609.8	529.9	479.8	452.8	428.3	395.0	367.6	351.2
47.5°	857.2	819.8	691.6	568.0	486.0	437.8	409.7	390.0	365.7	343.6	327.8
50°	792.1	776.6	661.9	539.5	456.7	409.6	382.5	364.7	347.2	325.1	310.6
52.5°	716.9	726.4	627.0	510.0	426.9	380.6	355.1	341.0	325.1	306.9	294.3
55°	611.1	645.7	566.9	460.4	382.5	338.4	314.3	301.7	292.5	279.0	268.1
57.5°	512.0	555.9	501.8	409.2	338.9	300.8	277.8	264.1	258.1	251.1	242.5
60°	453.1	496.6	455.4	375.0	309.6	273.4	253.0	241.4	235.5	230.5	223.3
62.5°	400.6	444.6	410.0	340.1	280.9	247.3	229.5	218.2	213.5	210.9	204.7
65°	328.5	366.4	343.3	285.9	239.7	210.1	193.9	186.0	181.7	180.7	176.8
67.5°	267.3	296.2	279.4	237.1	200.8	175.1	161.4	154.7	151.4	151.1	148.1
70°	227.2	254.3	241.4	203.1	171.8	151.7	139.8	133.9	131.9	131.6	129.9
72.5°	196.0	214.9	204.7	172.8	148.6	130.4	121.6	115.4	113.1	113.7	112.5
75°	145.1	159.3	153.3	131.2	111.8	99.9	92.6	88.7	86.7	87.7	86.4
77.5°	104.4	113.4	108.1	92.7	80.8	72.2	66.8	64.4	62.6	62.5	61.9
80°	78.8	84.1	81.1	71.9	62.0	54.8	50.5	48.8	47.8	47.5	47.2
82.5°	56.1	60.6	57.1	50.8	44.1	39.7	37.3	35.1	34.4	34.5	34.3
85°	28.3	30.0	28.7	24.7	22.1	20.1	18.8	17.8	17.1	17.5	16.8
87.5°	13.6	13.3	11.8	10.4	9.5	8.1	7.7	6.7	6.6	7.0	7.3
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4	18.4	26.8	34.6
95°	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0	37.0	48.0	65.0
97.5°	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0	59.0	67.6	82.4
100°	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0	75.0	82.1	96.0
102.5°	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8	92.6	98.8	112.0
105°	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1	119.1	125.0	137.1
107.5°	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8	145.9	151.6	163.4
110°	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0	165.1	170.0	181.1





TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7	182.7	187.7	198.6
115°	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1	209.1	215.1	225.1
117.5°	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5	235.1	240.0	249.3
120°	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1	251.1	256.1	266.1
122.5°	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3	266.3	271.3	282.1
125°	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1	287.1	293.1	304.1
127.5°	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7	304.7	312.1	323.3
130°	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1	315.1	324.1	336.1
132.5°	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1	323.9	333.7	348.1
135°	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2	338.1	349.1	364.1
137.5°	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3	351.5	362.3	378.3
140°	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1	361.1	371.1	387.1
142.5°	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8	370.0	380.7	395.1
145°	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2	384.1	393.1	408.1
147.5°	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7	398.6	407.3	420.3
150°	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2	408.1	416.1	429.1
152.5°	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6	417.8	425.8	437.1
155°	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2	433.2	439.2	449.2
157.5°	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6	446.3	451.2	459.9
160°	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1	455.1	459.2	467.2
162.5°	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4	462.4	465.5	472.0
165°	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2	472.2	474.2	479.1
167.5°	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4	480.2	481.1	485.0
170°	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2	484.1	485.2	488.2
172.5°	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4	488.2	488.4	490.6
175°	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2	492.1	491.2	493.2
177.5°	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0	494.2	493.4	494.2
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	669.3	667.4	664.8	660.8	657.6	652.6	652.6	653.4	653.4	653.2	652.6
5°	648.9	644.0	638.1	631.2	623.9	616.6	615.4	612.7	610.7	609.4	607.8
7.5°	627.5	618.8	610.1	600.5	591.6	584.3	579.2	575.0	572.2	569.4	567.2
10°	613.0	602.1	591.9	581.7	570.5	561.5	555.9	552.0	549.1	546.4	545.1
12.5°	595.9	583.4	572.1	562.4	550.2	541.0	535.6	533.8	530.3	524.8	521.9
15°	570.8	559.3	545.8	530.9	525.0	513.8	507.5	504.5	502.6	498.3	497.0
17.5°	549.4	534.3	519.1	508.0	497.0	487.9	484.4	480.7	478.1	474.6	473.6
20°	532.3	518.8	504.9	493.0	481.5	471.6	468.6	466.0	463.3	461.7	460.4
22.5°	514.8	501.3	489.8	478.7	466.4	459.9	456.7	453.8	451.9	450.8	449.5
25°	490.3	478.5	465.6	455.7	445.8	441.5	439.5	437.9	436.6	435.0	434.6
27.5°	468.5	455.6	445.1	435.8	428.8	425.2	423.3	422.5	422.8	423.4	423.7
30°	452.1	440.2	431.6	423.7	417.2	413.9	413.5	413.5	414.8	415.2	415.9
32.5°	437.0	427.3	418.7	411.0	406.0	403.8	405.1	405.1	406.1	407.0	408.2
35°	415.2	406.6	400.0	393.4	389.1	390.1	390.7	391.4	393.0	395.0	396.4
37.5°	394.3	386.8	380.0	374.8	372.8	374.6	376.2	377.5	379.5	381.0	382.3
40°	379.2	373.6	367.0	362.4	363.1	364.0	365.4	367.0	368.7	369.6	371.0
42.5°	365.2	359.4	354.4	350.5	351.5	352.8	353.5	354.4	356.3	358.1	358.9
45°	344.0	339.3	334.7	332.4	333.0	333.7	334.4	335.4	337.0	338.4	338.6
47.5°	320.0	316.8	313.7	311.4	312.5	312.2	313.1	315.2	315.7	316.5	318.3
50°	304.7	301.7	298.1	297.5	297.5	297.5	297.7	300.4	300.4	301.7	303.1
52.5°	287.8	285.9	283.6	282.4	281.9	281.9	283.3	284.6	285.1	287.0	288.3
55°	262.8	260.8	258.9	257.9	257.2	257.9	260.5	261.1	262.8	263.8	264.8
57.5°	236.8	235.2	233.7	233.2	233.0	233.8	235.3	237.3	237.7	240.7	242.2
60°	219.6	217.3	216.0	216.0	215.3	218.3	217.7	220.9	221.6	223.6	225.9
62.5°	201.9	198.8	198.3	198.3	199.2	200.1	201.0	202.5	204.2	206.7	208.4
65°	173.5	171.8	174.1	173.7	173.1	175.1	175.1	176.8	178.7	181.1	184.7
67.5°	146.5	145.6	145.9	145.9	146.8	147.9	148.9	150.3	152.7	155.2	157.5
70°	128.3	129.2	127.6	129.0	129.9	130.3	130.9	132.9	135.5	137.2	139.8
72.5°	110.6	110.6	110.7	111.2	112.3	112.9	113.5	115.7	118.6	120.0	122.2
75°	85.1	84.7	85.8	85.8	87.4	88.1	88.7	89.7	92.3	94.3	96.0
77.5°	62.2	62.5	62.3	63.5	63.0	63.1	65.2	66.1	66.4	70.3	71.2
80°	46.8	47.5	47.8	48.1	48.5	47.8	50.1	51.1	51.1	53.4	55.1
82.5°	33.7	34.0	34.9	35.2	35.3	35.9	36.2	36.9	37.6	38.7	40.8
85°	16.8	17.8	18.2	17.8	18.2	17.5	18.4	18.8	19.1	19.1	19.1
87.5°	7.5	8.2	8.4	9.3	9.6	10.5	10.3	10.0	10.2	11.2	10.6
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	29.0
92.5°	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2	66.8	59.0	53.8
95°	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2	244.1	191.1	155.1
97.5°	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7	719.0	590.0	470.4
100°	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4	1098.4	981.4	839.3
102.5°	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1	1270.4	1202.2	1112.2
105°	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5	1400.5	1419.5	1393.5
107.5°	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6	1384.1	1471.7	1507.4
110°	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4	1330.5	1456.6	1526.6



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9	1260.1	1401.3	1491.3
115°	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4	1147.4	1294.4	1403.5
117.5°	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9	1052.1	1184.2	1294.9
120°	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3	999.4	1119.4	1220.5
122.5°	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7	956.9	1068.2	1162.0
125°	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3	904.3	1000.3	1080.4
127.5°	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9	858.1	944.7	1017.5
130°	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3	829.3	910.3	978.4
132.5°	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3	802.1	877.5	942.4
135°	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2	763.3	828.3	885.3
137.5°	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6	725.8	781.9	831.3
140°	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2	704.2	752.3	795.3
142.5°	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6	683.5	725.0	762.5
145°	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2	656.3	688.3	717.2
147.5°	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8	636.0	661.9	682.4
150°	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2	623.2	644.2	663.2
152.5°	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4	611.2	629.8	645.7
155°	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2	594.2	609.2	621.2
157.5°	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2	577.6	589.2	598.6
160°	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2	567.2	577.2	584.2
162.5°	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6	556.0	565.2	571.4
165°	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2	540.2	547.2	552.2
167.5°	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4	528.0	532.0	535.6
170°	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2	519.2	523.1	525.2
172.5°	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8	512.0	515.2	516.3
175°	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2	502.1	504.2	504.2
177.5°	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8	496.5	497.4	497.4
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	650.8	650.6	652.4	651.1	652.4	650.6	650.8	652.6	653.2	653.4	653.4
5°	605.8	606.7	603.5	603.5	603.5	606.7	605.8	607.8	609.4	610.7	612.7
7.5°	565.7	564.2	564.4	562.6	564.4	564.2	565.7	567.2	569.4	572.2	575.0
10°	541.1	539.2	538.5	538.8	538.5	539.2	541.1	545.1	546.4	549.1	552.0
12.5°	520.8	520.4	516.1	516.2	516.1	520.4	520.8	521.9	524.8	530.3	533.8
15°	497.0	490.7	490.0	492.0	490.0	490.7	497.0	497.0	498.3	502.6	504.5
17.5°	473.0	469.7	469.9	468.9	469.9	469.7	473.0	473.6	474.6	478.1	480.7
20°	460.4	458.4	458.1	455.7	458.1	458.4	460.4	460.4	461.7	463.3	466.0
22.5°	448.8	448.1	448.2	445.7	448.2	448.1	448.8	449.5	450.8	451.9	453.8
25°	434.3	435.9	434.6	434.6	434.6	435.9	434.3	434.6	435.0	436.6	437.9
27.5°	424.6	424.5	423.8	423.8	423.8	424.5	424.6	423.7	423.4	422.8	422.5
30°	417.2	416.8	417.5	417.5	417.5	416.8	417.2	415.9	415.2	414.8	413.5
32.5°	409.7	410.2	410.4	410.6	410.4	410.2	409.7	408.2	407.0	406.1	405.1
35°	398.4	398.6	399.7	399.0	399.7	398.6	398.4	396.4	395.0	393.0	391.4
37.5°	382.9	384.4	384.1	384.6	384.1	384.4	382.9	382.3	381.0	379.5	377.5
40°	371.3	372.3	372.0	372.0	372.0	372.3	371.3	371.0	369.6	368.7	367.0
42.5°	359.5	360.2	359.3	358.8	359.3	360.2	359.5	358.9	358.1	356.3	354.4
45°	340.0	339.3	340.4	339.0	340.4	339.3	340.0	338.6	338.4	337.0	335.4
47.5°	318.2	318.9	319.2	320.1	319.2	318.9	318.2	318.3	316.5	315.7	315.2
50°	303.7	305.7	305.7	305.4	305.7	305.7	303.7	303.1	301.7	300.4	300.4
52.5°	289.5	290.4	291.7	291.6	291.7	290.4	289.5	288.3	287.0	285.1	284.6
55°	267.4	268.1	268.7	269.1	268.7	268.1	267.4	264.8	263.8	262.8	261.1
57.5°	244.6	244.4	245.9	246.4	245.9	244.4	244.6	242.2	240.7	237.7	237.3
60°	228.5	228.5	231.2	232.1	231.2	228.5	228.5	225.9	223.6	221.6	220.9
62.5°	211.4	212.4	215.1	213.7	215.1	212.4	211.4	208.4	206.7	204.2	202.5
65°	186.3	189.0	188.6	189.9	188.6	189.0	186.3	184.7	181.1	178.7	176.8
67.5°	160.1	161.8	164.2	164.4	164.2	161.8	160.1	157.5	155.2	152.7	150.3
70°	142.5	144.1	145.4	146.4	145.4	144.1	142.5	139.8	137.2	135.5	132.9
72.5°	125.3	126.1	129.3	127.9	129.3	126.1	125.3	122.2	120.0	118.6	115.7
75°	98.2	100.6	102.5	101.6	102.5	100.6	98.2	96.0	94.3	92.3	89.7
77.5°	72.7	75.0	75.9	75.1	75.9	75.0	72.7	71.2	70.3	66.4	66.1
80°	57.3	57.1	59.1	58.7	59.1	57.1	57.3	55.1	53.4	51.1	51.1
82.5°	42.1	41.8	42.7	42.9	42.7	41.8	42.1	40.8	38.7	37.6	36.9
85°	20.4	21.4	20.1	19.8	20.1	21.4	20.4	19.1	19.1	19.1	18.8
87.5°	10.3	10.6	10.5	10.0	10.5	10.6	10.3	10.6	11.2	10.2	10.0
90°	28.0	29.0	30.0	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0
92.5°	52.0	49.0	50.0	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2
95°	136.0	127.1	120.0	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2
97.5°	396.6	351.5	324.5	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7
100°	738.2	665.2	626.2	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4
102.5°	1033.5	975.8	943.1	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1
105°	1347.5	1309.5	1277.5	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5
107.5°	1508.1	1495.3	1484.5	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6
110°	1554.5	1562.5	1560.6	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1542.6	1567.4	1574.9	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9
115°	1478.5	1522.5	1542.6	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4
117.5°	1373.1	1423.5	1452.3	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9
120°	1299.4	1355.5	1379.5	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3
122.5°	1232.3	1282.6	1309.1	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7
125°	1144.4	1188.4	1213.4	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3
127.5°	1074.6	1112.2	1134.8	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9
130°	1031.4	1067.4	1088.4	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3
132.5°	992.1	1028.1	1046.8	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3
135°	934.4	964.3	982.3	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2
137.5°	872.5	902.9	918.1	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6
140°	833.3	861.3	877.3	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2
142.5°	794.9	819.7	834.1	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6
145°	742.3	763.3	771.3	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2
147.5°	701.5	715.7	723.2	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8
150°	678.2	689.2	695.3	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2
152.5°	657.5	667.6	671.2	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4
155°	630.3	638.3	640.2	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2
157.5°	606.4	612.4	614.0	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2
160°	591.2	597.2	597.2	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2
162.5°	576.0	581.2	581.2	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6
165°	556.2	560.2	559.2	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2
167.5°	537.4	540.2	539.2	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4
170°	526.2	528.2	527.2	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2
172.5°	516.6	518.6	516.8	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8
175°	504.2	505.1	504.2	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2
177.5°	496.5	497.4	495.8	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	652.6	652.6	657.6	660.8	664.8	667.4	669.3	671.1	674.2	678.6	683.3
5°	615.4	616.6	623.9	631.2	638.1	644.0	648.9	654.9	662.2	671.1	681.0
7.5°	579.2	584.3	591.6	600.5	610.1	618.8	627.5	637.3	647.5	660.6	674.5
10°	555.9	561.5	570.5	581.7	591.9	602.1	613.0	623.5	636.5	651.9	669.8
12.5°	535.6	541.0	550.2	562.4	572.1	583.4	595.9	609.6	624.1	642.7	662.9
15°	507.5	513.8	525.0	530.9	545.8	559.3	570.8	590.6	609.1	628.2	651.6
17.5°	484.4	487.9	497.0	508.0	519.1	534.3	549.4	565.8	584.3	607.7	637.0
20°	468.6	471.6	481.5	493.0	504.9	518.8	532.3	548.7	569.5	594.3	625.9
22.5°	456.7	459.9	466.4	478.7	489.8	501.3	514.8	534.5	556.6	580.7	615.1
25°	439.5	441.5	445.8	455.7	465.6	478.5	490.3	508.9	531.6	559.9	594.3
27.5°	423.3	425.2	428.8	435.8	445.1	455.6	468.5	484.1	507.2	538.0	574.5
30°	413.5	413.9	417.2	423.7	431.6	440.2	452.1	469.9	491.6	523.0	561.3
32.5°	405.1	403.8	406.0	411.0	418.7	427.3	437.0	454.6	475.6	506.4	545.7
35°	390.7	390.1	389.1	393.4	400.0	406.6	415.2	428.3	452.1	480.8	522.0
37.5°	376.2	374.6	372.8	374.8	380.0	386.8	394.3	406.0	426.5	458.1	497.5
40°	365.4	364.0	363.1	362.4	367.0	373.6	379.2	390.5	409.6	439.5	478.5
42.5°	353.5	352.8	351.5	350.5	354.4	359.4	365.2	375.1	394.3	422.4	459.3
45°	334.4	333.7	333.0	332.4	334.7	339.3	344.0	351.2	367.6	395.0	428.3
47.5°	313.1	312.2	312.5	311.4	313.7	316.8	320.0	327.8	343.6	365.7	390.0
50°	297.7	297.5	297.5	297.5	298.1	301.7	304.7	310.6	325.1	347.2	364.7
52.5°	283.3	281.9	281.9	282.4	283.6	285.9	287.8	294.3	306.9	325.1	341.0
55°	260.5	257.9	257.2	257.9	258.9	260.8	262.8	268.1	279.0	292.5	301.7
57.5°	235.3	233.8	233.0	233.2	233.7	235.2	236.8	242.5	251.1	258.1	264.1
60°	217.7	218.3	215.3	216.0	216.0	217.3	219.6	223.3	230.5	235.5	241.4
62.5°	201.0	200.1	199.2	198.3	198.3	198.8	201.9	204.7	210.9	213.5	218.2
65°	175.1	175.1	173.1	173.7	174.1	171.8	173.5	176.8	180.7	181.7	186.0
67.5°	148.9	147.9	146.8	145.9	145.9	145.6	146.5	148.1	151.1	151.4	154.7
70°	130.9	130.3	129.9	129.0	127.6	129.2	128.3	129.9	131.6	131.9	133.9
72.5°	113.5	112.9	112.3	111.2	110.7	110.6	110.6	112.5	113.7	113.1	115.4
75°	88.7	88.1	87.4	85.8	85.8	84.7	85.1	86.4	87.7	86.7	88.7
77.5°	65.2	63.1	63.0	63.5	62.3	62.5	62.2	61.9	62.5	62.6	64.4
80°	50.1	47.8	48.5	48.1	47.8	47.5	46.8	47.2	47.5	47.8	48.8
82.5°	36.2	35.9	35.3	35.2	34.9	34.0	33.7	34.3	34.5	34.4	35.1
85°	18.4	17.5	18.2	17.8	18.2	17.8	16.8	16.8	17.5	17.1	17.8
87.5°	10.3	10.5	9.6	9.3	8.4	8.2	7.5	7.3	7.0	6.6	6.7
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	116.1	153.9	169.3	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4
95°	481.1	593.2	528.2	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0
97.5°	983.5	919.3	673.0	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0
100°	1144.4	947.4	640.2	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0
102.5°	1152.4	895.4	592.2	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8
105°	1091.4	804.3	533.2	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1
107.5°	984.6	723.8	495.6	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8
110°	917.3	678.2	481.1	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	858.9	647.8	473.2	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7
115°	788.2	615.2	470.2	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1
117.5°	745.6	596.0	472.0	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5
120°	723.2	587.2	475.2	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1
122.5°	704.8	581.6	480.8	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3
125°	681.2	574.2	489.1	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1
127.5°	660.5	570.6	498.8	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7
130°	649.2	568.2	505.1	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1
132.5°	638.9	567.4	510.0	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1
135°	625.3	566.2	517.2	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2
137.5°	613.4	564.0	522.0	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3
140°	606.2	563.2	525.2	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1
142.5°	599.8	561.6	527.6	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8
145°	591.2	559.2	529.2	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2
147.5°	582.8	555.4	529.2	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7
150°	577.2	552.2	529.2	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2
152.5°	570.8	548.2	526.8	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6
155°	561.2	541.2	524.2	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2
157.5°	550.4	535.0	520.8	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6
160°	543.2	530.2	519.2	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1
162.5°	536.0	525.4	516.0	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4
165°	526.2	518.1	511.2	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2
167.5°	516.8	511.0	506.4	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4
170°	511.2	506.2	503.2	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2
172.5°	505.6	502.1	500.8	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4
175°	499.2	497.1	497.1	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2
177.5°	495.0	494.2	495.0	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	684.8	686.1	690.6	693.8	697.5	699.6	701.7	703.4	705.4	705.9	713.6
5°	687.9	694.5	706.0	714.5	725.1	736.7	744.6	748.2	757.8	765.7	781.5
7.5°	687.0	701.0	718.5	736.6	756.0	773.9	789.5	807.9	821.0	840.8	860.2
10°	686.2	705.0	727.5	750.5	777.6	802.6	825.1	850.2	870.9	898.3	921.7
12.5°	683.9	706.6	737.7	765.0	797.9	832.4	865.6	897.9	916.3	961.8	983.4
15°	678.0	705.0	743.9	785.5	830.7	871.6	913.8	947.4	1001.8	1041.7	1067.1
17.5°	666.8	704.6	750.8	800.9	855.8	909.7	957.5	1008.6	1066.3	1114.6	1166.1
20°	661.5	703.0	754.5	809.9	866.9	927.9	982.3	1043.7	1106.6	1154.2	1220.1
22.5°	651.8	698.8	754.2	816.0	876.9	940.0	1003.8	1065.6	1138.3	1203.8	1266.5
25°	635.8	688.5	745.9	814.9	886.4	949.7	1025.9	1108.0	1183.9	1267.9	1330.6
27.5°	619.1	675.4	732.9	796.9	873.9	949.1	1044.9	1137.6	1230.4	1303.0	1349.4
30°	606.1	660.8	720.2	784.8	861.0	950.4	1057.6	1158.7	1249.1	1311.5	1337.5
32.5°	592.1	647.6	700.2	767.9	849.1	949.6	1065.5	1171.1	1250.2	1291.7	1286.6
35°	570.2	616.6	667.8	733.1	828.7	943.7	1070.1	1172.3	1220.7	1211.9	1144.6
37.5°	538.5	577.6	627.9	699.4	804.9	931.6	1060.8	1137.6	1134.4	1061.9	964.4
40°	518.8	552.0	600.5	675.7	786.4	923.7	1046.3	1096.1	1054.0	952.7	835.9
42.5°	492.8	523.5	572.0	649.3	766.2	907.6	1018.6	1033.0	950.5	834.0	727.0
45°	452.8	479.8	529.9	609.8	735.7	872.5	951.1	915.8	804.6	684.2	602.8
47.5°	409.7	437.8	486.0	568.0	691.6	819.8	857.2	782.2	668.0	570.5	495.7
50°	382.5	409.6	456.7	539.5	661.9	776.6	792.1	695.2	590.3	504.5	443.2
52.5°	355.1	380.6	426.9	510.0	627.0	726.4	716.9	618.1	521.7	448.6	400.5
55°	314.3	338.4	382.5	460.4	566.9	645.7	611.1	516.8	437.0	380.2	343.6
57.5°	277.8	300.8	338.9	409.2	501.8	555.9	512.0	432.5	369.0	325.4	298.1
60°	253.0	273.4	309.6	375.0	455.4	496.6	453.1	382.9	329.4	294.5	270.1
62.5°	229.5	247.3	280.9	340.1	410.0	444.6	400.6	341.1	295.7	264.7	243.9
65°	193.9	210.1	239.7	285.9	343.3	366.4	328.5	280.3	245.0	222.0	208.1
67.5°	161.4	175.1	200.8	237.1	279.4	296.2	267.3	230.1	203.5	184.9	173.9
70°	139.8	151.7	171.8	203.1	241.4	254.3	227.2	196.6	177.1	162.2	152.1
72.5°	121.6	130.4	148.6	172.8	204.7	214.9	196.0	169.1	150.9	139.8	131.7
75°	92.6	99.9	111.8	131.2	153.3	159.3	145.1	128.3	116.1	108.1	101.9
77.5°	66.8	72.2	80.8	92.7	108.1	113.4	104.4	93.2	84.3	79.0	75.4
80°	50.5	54.8	62.0	71.9	81.1	84.1	78.8	70.3	64.0	61.0	58.0
82.5°	37.3	39.7	44.1	50.8	57.1	60.6	56.1	51.0	47.6	44.9	43.8
85°	18.8	20.1	22.1	24.7	28.7	30.0	28.3	27.0	25.1	23.4	23.4
87.5°	7.7	8.1	9.5	10.4	11.8	13.3	13.6	13.6	13.9	13.5	13.4
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2
95°	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2
97.5°	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7
100°	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4
102.5°	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1
105°	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5
107.5°	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6
110°	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4





TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9
115°	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4
117.5°	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9
120°	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3
122.5°	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7
125°	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3
127.5°	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9
130°	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3
132.5°	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3
135°	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2
137.5°	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6
140°	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2
142.5°	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6
145°	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2
147.5°	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8
150°	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2
152.5°	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4
155°	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2
157.5°	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2
160°	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2
162.5°	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6
165°	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2
167.5°	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4
170°	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2
172.5°	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8
175°	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2
177.5°	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	680.6	680.6	680.6	680.6	680.6	680.6	680.6
2.5°	716.3	716.5	719.4	721.5	720.5	721.8	722.3
5°	782.5	794.4	800.6	805.3	805.6	805.9	808.6
7.5°	876.5	889.2	898.5	912.7	916.9	921.7	920.3
10°	945.1	963.9	980.1	988.6	997.8	1011.3	1000.5
12.5°	1009.2	1042.5	1067.1	1080.4	1089.2	1091.8	1086.5
15°	1114.9	1158.5	1181.9	1181.2	1210.9	1223.7	1203.6
17.5°	1211.9	1252.1	1284.2	1300.7	1325.4	1330.9	1328.4
20°	1271.2	1315.1	1340.1	1368.5	1381.4	1392.9	1394.9
22.5°	1322.4	1361.8	1388.7	1412.3	1423.1	1428.5	1431.8
25°	1375.1	1406.1	1422.3	1430.5	1433.5	1432.8	1428.5
27.5°	1371.5	1373.8	1356.1	1338.6	1322.9	1305.3	1299.2
30°	1335.8	1308.1	1258.7	1230.6	1189.5	1156.8	1170.0
32.5°	1242.2	1187.1	1131.5	1070.2	1019.5	1005.1	990.6
35°	1060.1	963.2	906.5	840.6	814.2	787.8	769.6
37.5°	857.7	782.7	715.4	672.3	645.8	629.2	620.2
40°	741.7	674.0	618.6	583.7	563.5	544.8	542.1
42.5°	649.0	586.2	544.5	516.7	497.3	489.4	483.5
45°	531.6	487.7	459.7	439.9	427.1	422.1	415.5
47.5°	450.0	419.0	397.9	384.4	374.7	371.0	370.5
50°	404.3	378.6	363.1	352.5	344.9	343.6	338.4
52.5°	370.0	347.7	335.6	326.4	320.9	317.2	315.6
55°	321.2	306.3	295.5	290.2	285.9	282.2	282.2
57.5°	281.0	268.6	261.4	256.9	255.6	253.0	251.4
60°	256.2	245.6	240.0	236.1	233.5	233.8	230.8
62.5°	232.0	225.1	219.7	215.8	212.7	212.7	212.9
65°	197.5	192.3	188.3	187.0	185.0	182.7	183.3
67.5°	167.4	162.5	159.4	157.1	156.4	155.2	157.1
70°	145.8	142.2	139.8	137.8	137.2	137.5	139.1
72.5°	126.0	123.4	121.9	121.0	119.5	119.6	120.7
75°	98.9	96.9	95.7	94.6	94.3	94.3	94.3
77.5°	72.7	72.2	71.6	70.2	70.3	70.6	70.7
80°	57.3	56.4	56.1	55.4	54.4	53.7	55.4
82.5°	42.9	41.8	41.6	41.4	39.9	39.8	41.2
85°	23.1	22.1	22.4	22.1	22.1	21.8	21.8
87.5°	13.3	13.3	13.4	13.5	13.4	13.4	13.7
90°	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6



TEST NUMBER: P331948-935

CATALOG NUMBER: S123DIP-S560D1195U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)