

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331916-935

Luminaire Tested: **S123DIP-S560D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331916-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3245.9 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.2
10°-20°	204.0	6.3
20°-30°	301.4	9.3
30°-40°	352.0	10.8
40°-50°	353.9	10.9
50°-60°	310.9	9.6
60°-70°	231.6	7.1
70°-80°	132.0	4.1
80°-90°	39.0	1.2
90°-100°	14.9	0.5
100°-110°	71.0	2.2
110°-120°	170.4	5.3
120°-130°	217.0	6.7
130°-140°	231.9	7.1
140°-150°	216.9	6.7
150°-160°	174.9	5.4
160°-170°	112.9	3.5
170°-180°	38.9	1.2
0°-30°	577.6	17.8
0°-40°	929.7	28.6
0°-60°	1594.5	49.1
0°-90°	1997.1	61.5
90°-120°	256.3	7.9
90°-150°	922.1	28.4
90°-180°	1249.0	38.5
0°-180°	3245.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	0	3	7	8	9	3
95°	19	7	10	11	12	23
105°	91	92	67	16	13	96
115°	170	172	175	178	179	168
125°	240	242	243	244	245	214
135°	298	300	302	302	302	230
145°	344	346	347	348	348	216
155°	379	379	379	380	379	175
165°	400	399	399	401	399	113
175°	410	408	408	410	408	39
180°	410	410	410	410	410	



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.8	13.6	13.3	13.1	12.9	12.8	12.9	12.9	13.0	13.1	13.0
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	5.7	5.5	5.3	5.1	4.9	5.2	5.8	6.5	7.1	7.7	8.2
95°	18.6	15.8	13.0	10.2	7.5	6.5	7.2	7.9	8.7	9.5	9.9
97.5°	37.3	36.1	34.8	33.6	32.3	29.3	24.4	19.5	14.6	9.8	10.3
100°	51.4	52.8	54.2	55.4	56.8	52.3	41.7	31.2	20.6	10.1	10.6
102.5°	67.5	68.4	69.4	70.4	71.4	66.1	54.6	43.0	31.5	20.1	18.3
105°	90.7	91.4	92.1	92.9	93.7	91.0	84.9	78.8	72.8	66.6	54.7
107.5°	115.1	115.7	116.3	116.9	117.5	118.3	119.2	120.2	121.1	122.1	113.3
110°	131.5	132.0	132.5	133.0	133.6	134.2	135.0	135.7	136.5	137.2	135.0



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	147.5	148.0	148.4	149.0	149.6	150.3	151.1	151.8	152.6	152.6
115°	170.0	170.5	170.9	171.3	171.7	172.2	172.8	173.4	174.0	174.6	175.3
117.5°	192.4	193.0	193.4	193.9	194.4	194.8	195.1	195.4	195.8	196.0	196.6
120°	206.3	206.9	207.5	208.1	208.7	209.1	209.3	209.6	209.7	209.9	210.5
122.5°	220.4	220.9	221.4	221.9	222.4	222.7	223.0	223.3	223.5	223.8	224.2
125°	239.8	240.3	240.8	241.3	241.9	242.3	242.6	242.9	243.1	243.4	243.6
127.5°	258.5	259.1	259.6	260.1	260.6	261.1	261.4	261.7	262.1	262.3	262.6
130°	270.2	270.7	271.2	271.8	272.3	272.8	273.0	273.3	273.5	273.8	274.1
132.5°	281.4	281.9	282.5	283.0	283.5	283.9	284.1	284.4	284.6	284.8	285.1
135°	298.5	298.9	299.3	299.7	300.1	300.4	300.7	301.0	301.3	301.5	301.7
137.5°	313.1	313.6	314.1	314.6	315.1	315.5	315.6	315.7	315.9	316.1	316.4
140°	322.8	323.2	323.6	324.0	324.4	324.8	324.9	325.1	325.4	325.5	325.8
142.5°	331.8	332.3	332.6	333.0	333.5	333.7	334.0	334.2	334.3	334.6	334.8
145°	344.4	344.9	345.3	345.9	346.3	346.6	346.7	346.9	347.0	347.2	347.3
147.5°	356.3	356.6	356.9	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
150°	363.6	363.8	363.9	364.2	364.4	364.5	364.7	364.8	365.0	365.1	365.2
152.5°	370.1	370.2	370.3	370.4	370.5	370.7	370.7	370.7	370.8	370.9	371.2
155°	379.4	379.3	379.1	379.0	378.8	378.8	378.9	378.9	379.0	379.1	379.4
157.5°	386.6	386.6	386.6	386.5	386.5	386.5	386.4	386.3	386.2	386.2	386.6
160°	391.0	390.9	390.8	390.7	390.7	390.6	390.5	390.5	390.5	390.4	390.7
162.5°	395.1	394.9	394.8	394.6	394.4	394.3	394.2	394.2	394.1	394.0	394.4
165°	400.1	399.8	399.7	399.5	399.2	399.2	399.1	399.0	398.9	398.9	399.4
167.5°	404.0	403.7	403.5	403.2	402.9	402.8	402.8	402.8	402.8	402.8	403.3
170°	406.1	405.9	405.6	405.4	405.1	404.9	404.9	404.9	404.9	404.9	405.5
172.5°	407.6	407.3	407.0	406.7	406.3	406.2	406.2	406.3	406.4	406.4	407.0
175°	409.5	409.1	408.8	408.5	408.2	408.0	408.1	408.2	408.2	408.3	408.8
177.5°	410.0	409.7	409.5	409.2	408.9	408.8	408.9	408.9	409.0	409.1	409.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	12.9	12.9	12.8	12.8	12.8	12.8	12.9	12.9
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	8.7	9.1	9.6	9.8	9.8	9.9	10.0	10.1
95°	10.4	10.8	11.4	11.5	11.5	11.5	11.5	11.5
97.5°	10.8	11.5	12.0	12.2	12.3	12.4	12.5	12.6
100°	11.1	11.6	12.2	12.5	12.6	12.7	12.7	12.7
102.5°	16.7	15.0	13.3	12.6	12.7	12.7	12.9	13.0
105°	42.7	30.7	18.8	12.8	13.0	13.1	13.3	13.3
107.5°	104.6	95.8	87.0	78.1	69.1	60.1	51.1	42.0
110°	132.8	130.5	128.3	122.3	112.7	103.0	93.3	83.7



TEST NUMBER: P331916-935

CATALOG NUMBER: S123DIP-S560D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.7	152.7	152.7	151.7	149.6	147.7	145.6	143.5
115°	176.0	176.7	177.4	177.8	178.1	178.4	178.7	178.9
117.5°	197.2	197.7	198.2	198.5	198.5	198.6	198.7	198.7
120°	211.0	211.5	212.1	212.4	212.4	212.4	212.4	212.4
122.5°	224.5	225.0	225.3	225.5	225.6	225.7	225.7	225.8
125°	243.7	243.8	243.9	244.1	244.2	244.4	244.5	244.6
127.5°	262.8	263.0	263.3	263.3	263.1	263.0	262.9	262.8
130°	274.4	274.7	274.9	275.0	274.8	274.7	274.6	274.4
132.5°	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.2
135°	302.0	302.1	302.3	302.3	302.1	302.0	301.7	301.5
137.5°	316.7	317.0	317.4	317.5	317.3	317.2	317.0	316.9
140°	326.1	326.3	326.7	326.7	326.6	326.4	326.3	326.1
142.5°	335.0	335.2	335.4	335.4	335.3	335.0	334.8	334.7
145°	347.4	347.6	347.7	347.8	347.8	347.8	347.8	347.8
147.5°	358.5	358.7	358.9	358.8	358.4	358.1	357.8	357.5
150°	365.4	365.5	365.7	365.6	365.4	365.2	365.0	364.8
152.5°	371.4	371.7	372.0	371.9	371.6	371.3	370.9	370.7
155°	379.8	380.1	380.5	380.4	380.0	379.6	379.2	378.8
157.5°	387.0	387.4	387.9	387.8	387.3	386.8	386.2	385.6
160°	391.2	391.6	392.0	391.9	391.5	391.0	390.5	390.0
162.5°	394.9	395.4	395.8	395.9	395.5	395.0	394.6	394.2
165°	399.9	400.5	401.1	401.1	400.6	400.1	399.7	399.2
167.5°	403.8	404.4	404.9	404.9	404.4	403.8	403.3	402.8
170°	406.0	406.6	407.1	407.1	406.6	406.0	405.5	404.9
172.5°	407.5	408.0	408.5	408.5	407.9	407.3	406.7	406.1
175°	409.2	409.7	410.2	410.2	409.7	409.1	408.5	408.0
177.5°	409.9	410.4	410.8	410.7	410.2	409.7	409.1	408.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5

(END OF REPORT)