

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331885-940

Luminaire Tested: **S123DIP-S340D805U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331885-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U940-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3887.8 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4614	4614	4614	4614
5°	5503	4635	4107	4635
10°	6889	4612	3711	4612
15°	8449	4574	3455	4574
20°	10065	4517	3289	4517
25°	10688	4445	3252	4445
30°	9161	4395	3269	4395
35°	6370	4322	3303	4322
40°	4799	4235	3292	4235
45°	3984	4107	3252	4107
50°	3569	3848	3220	3848
55°	3337	3567	3181	3567
60°	3130	3272	3147	3272
65°	2942	2985	3049	2985
70°	2760	2656	2902	2656
75°	2470	2325	2662	2325
80°	2163	1909	2294	1909
85°	1692	1383	1544	1383



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.2	1.1
10°-20°	135.4	3.5
20°-30°	227.3	5.8
30°-40°	257.4	6.6
40°-50°	230.8	5.9
50°-60°	186.3	4.8
60°-70°	129.8	3.3
70°-80°	68.2	1.8
80°-90°	19.3	0.5
90°-100°	191.7	4.9
100°-110°	542.7	14.0
110°-120°	533.9	13.7
120°-130°	425.8	11.0
130°-140°	335.7	8.6
140°-150°	250.6	6.4
150°-160°	174.7	4.5
160°-170°	102.6	2.6
170°-180°	33.4	0.9
0°-30°	405.0	10.4
0°-40°	662.4	17.0
0°-60°	1079.4	27.8
0°-90°	1296.8	33.4
90°-120°	1268.2	32.6
90°-150°	2280.4	58.7
90°-180°	2591.0	66.6
0°-180°	3887.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	429	429	429	429	429	
5°	509	429	380	429	509	53
15°	758	410	310	410	758	219
25°	900	374	274	374	900	395
35°	485	329	251	329	485	315
45°	262	270	214	270	262	207
55°	178	190	170	190	178	160
65°	116	117	120	117	116	115
75°	59	56	64	56	59	64
85°	14	11	12	11	14	17
90°	20	1	20	1	20	11
95°	81	24	81	24	81	146
105°	887	81	887	81	887	875
115°	1078	143	1078	143	1078	1048
125°	850	199	850	199	850	771
135°	690	233	690	233	690	535
145°	539	266	539	266	539	343
155°	447	302	447	302	447	208
165°	390	330	390	330	390	111
175°	351	344	351	344	351	34
180°	344	344	344	344	344	



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	455.0	454.7	453.9	454.5	453.2	451.4	451.2	449.5	444.7	444.4	443.1
5°	509.3	507.7	507.5	507.3	504.4	500.4	492.9	492.3	482.3	477.4	471.4
7.5°	579.8	580.6	577.6	575.0	566.1	560.2	552.1	541.9	529.7	517.2	509.0
10°	630.3	637.1	628.7	622.8	617.4	607.3	595.4	580.6	565.9	548.7	535.6
12.5°	684.5	687.8	686.1	680.6	672.3	656.7	635.8	619.5	605.9	577.2	565.6
15°	758.2	770.9	762.8	744.1	744.5	729.8	702.4	672.3	656.2	631.1	596.8
17.5°	836.9	838.4	835.0	819.4	809.0	788.7	763.4	734.6	702.1	671.7	635.3
20°	878.7	877.4	870.2	862.1	844.3	828.5	800.8	768.7	727.1	697.1	657.5
22.5°	902.0	899.9	896.4	889.7	874.9	857.9	833.0	797.9	758.3	717.1	671.3
25°	899.9	902.6	903.0	901.2	896.0	885.8	866.3	838.2	798.8	745.7	698.0
27.5°	818.5	822.3	833.4	843.3	854.3	865.5	864.0	850.1	820.8	775.1	716.7
30°	737.1	728.7	749.3	775.3	792.9	824.1	841.5	842.6	826.2	786.9	730.0
32.5°	624.0	633.2	642.3	674.2	712.8	747.8	782.6	810.5	813.7	787.6	737.8
35°	484.8	496.3	512.9	529.5	571.1	606.8	667.9	721.0	763.4	769.0	738.5
37.5°	390.7	396.4	406.9	423.6	450.7	493.1	540.3	607.5	669.0	714.6	716.6
40°	341.5	343.2	355.0	367.7	389.7	424.6	467.2	526.6	600.1	664.0	690.5
42.5°	304.6	308.3	313.3	325.5	343.0	369.3	408.8	458.0	525.4	598.8	650.8
45°	261.7	265.9	269.0	277.1	289.6	307.3	334.8	379.8	431.1	506.8	576.8
47.5°	233.4	233.7	236.0	242.2	250.7	263.9	283.5	312.3	359.4	420.9	492.8
50°	213.1	216.4	217.3	222.0	228.7	238.4	254.7	279.2	317.8	371.8	437.9
52.5°	198.9	199.8	202.2	205.6	211.4	219.0	233.1	252.3	282.6	328.7	389.4
55°	177.8	177.8	180.1	182.8	186.1	193.0	202.3	216.4	239.5	275.3	325.6
57.5°	158.4	159.4	161.0	161.8	164.7	169.2	177.0	187.8	204.9	232.5	272.4
60°	145.4	147.3	147.0	148.7	151.2	154.8	161.4	170.1	185.5	207.5	241.2
62.5°	134.1	134.0	133.9	136.0	138.4	141.8	146.2	153.6	166.7	186.3	214.9
65°	115.5	115.1	116.5	117.8	118.6	121.1	124.4	131.1	139.8	154.4	176.6
67.5°	99.0	97.7	98.5	99.0	100.4	102.4	105.5	109.6	116.5	128.1	144.9
70°	87.7	86.6	86.4	86.9	88.1	89.5	91.8	95.8	102.2	111.6	123.8
72.5°	76.1	75.3	75.3	76.2	76.8	77.8	79.4	82.9	88.1	95.1	106.6
75°	59.4	59.4	59.4	59.7	60.3	61.1	62.3	64.2	68.1	73.1	80.8
77.5°	44.5	44.5	44.2	44.2	45.1	45.5	45.7	47.5	49.8	53.1	58.7
80°	34.9	33.9	34.2	34.9	35.3	35.5	36.1	36.6	38.4	40.3	44.2
82.5°	25.9	25.1	25.1	26.1	26.2	26.4	27.0	27.6	28.3	30.0	32.1
85°	13.7	13.7	13.9	13.9	14.1	13.9	14.5	14.7	14.7	15.8	17.0
87.5°	9.0	8.8	8.8	8.9	8.8	8.7	8.7	8.8	8.8	9.1	8.9
90°	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4	16.8	17.4	15.3
92.5°	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7	80.9	107.2	118.0
95°	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0	335.4	413.4	368.1
97.5°	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6	685.5	640.7	469.0
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0	797.5	660.2	446.2
102.5°	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2	803.2	623.9	412.7
105°	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4	686.2	504.4	345.4
110°	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0	639.3	472.7	335.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1	598.6	451.5	329.8
115°	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3	549.4	428.7	327.7
117.5°	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6	519.7	415.4	329.0
120°	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4	504.1	409.2	331.2
122.5°	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8	491.2	405.4	335.0
125°	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2	474.7	400.2	340.9
127.5°	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3	460.3	397.7	347.6
130°	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2	452.5	396.0	352.0
132.5°	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2	445.2	395.4	355.4
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3	427.5	393.1	363.8
140°	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2	422.5	392.5	366.0
142.5°	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8	418.0	391.4	367.7
145°	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4	412.1	389.7	368.8
147.5°	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0	406.2	387.1	368.8
150°	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3	402.3	384.9	368.8
152.5°	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1	397.8	382.0	367.1
155°	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0	391.1	377.2	365.3
157.5°	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2	383.6	372.8	362.9
160°	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6	378.5	369.5	361.9
162.5°	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9	373.5	366.1	359.6
165°	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3	366.7	361.1	356.2
167.5°	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7	360.2	356.1	352.9
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7	356.2	352.8	350.7
172.5°	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3	352.3	350.0	349.0
175°	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3	347.9	346.5	346.5
177.5°	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	442.0	440.8	439.4	437.1	435.1	432.3	431.4	430.4	427.4	424.8	422.8
5°	469.0	464.0	456.8	450.1	444.8	437.5	433.4	429.0	422.8	417.1	412.6
7.5°	497.3	487.5	476.2	464.0	452.6	441.7	432.8	424.9	416.2	408.0	401.4
10°	519.8	505.6	489.8	472.8	458.3	444.2	432.3	422.0	410.7	400.9	392.8
12.5°	545.4	524.4	502.7	482.0	464.8	445.1	430.8	417.6	404.8	393.2	384.1
15°	575.6	549.0	523.3	494.8	468.7	444.2	427.1	410.5	395.7	383.7	372.0
17.5°	603.2	573.1	539.1	504.5	473.0	443.9	420.1	401.3	382.8	368.1	356.5
20°	618.8	584.6	546.2	510.2	475.3	442.9	416.7	394.3	374.3	358.7	345.7
22.5°	632.3	592.2	552.4	514.0	475.1	440.2	410.5	387.4	365.9	350.6	336.7
25°	646.3	598.2	558.4	513.4	469.9	433.7	400.6	374.3	352.8	334.8	320.6
27.5°	658.3	597.9	550.5	502.0	461.6	425.4	389.9	361.9	338.9	319.5	305.0
30°	666.2	598.7	542.4	494.5	453.7	416.3	381.8	353.6	329.5	309.8	296.0
32.5°	671.2	598.2	534.9	483.8	441.0	408.0	373.0	343.8	319.0	299.6	286.4
35°	674.1	594.5	522.0	461.8	420.7	388.4	359.2	328.9	302.9	284.8	269.8
37.5°	668.2	586.8	507.1	440.6	395.6	363.9	339.2	313.4	288.6	268.7	255.7
40°	659.2	581.8	495.4	425.6	378.3	347.8	326.8	301.4	276.9	258.0	245.9
42.5°	641.7	571.8	482.7	409.0	360.3	329.8	310.5	289.3	266.1	248.3	236.3
45°	599.1	549.7	463.4	384.1	333.9	302.3	285.3	269.8	248.9	231.7	221.2
47.5°	540.0	516.5	435.7	357.8	306.1	275.8	258.1	245.8	230.4	216.4	206.5
50°	499.0	489.2	417.0	339.8	287.8	258.0	240.9	229.8	218.7	204.8	195.7
52.5°	451.7	457.6	395.0	321.3	268.9	239.7	223.7	214.8	204.8	193.3	185.4
55°	385.0	406.7	357.1	290.0	240.9	213.1	198.0	190.1	184.2	175.8	168.9
57.5°	322.5	350.3	316.1	257.8	213.5	189.5	175.0	166.4	162.6	158.2	152.8
60°	285.4	312.8	286.9	236.2	195.1	172.2	159.3	152.0	148.3	145.2	140.6
62.5°	252.4	280.1	258.3	214.3	176.9	155.8	144.5	137.4	134.6	133.0	129.0
65°	206.9	230.8	216.2	180.1	151.1	132.3	122.2	117.2	114.5	113.9	111.4
67.5°	168.4	186.5	176.0	149.4	126.5	110.4	101.7	97.5	95.4	95.1	93.3
70°	143.1	160.2	152.0	128.0	108.3	95.6	88.1	84.4	83.1	82.9	81.9
72.5°	123.5	135.4	128.9	108.9	93.6	82.1	76.6	72.7	71.3	71.6	70.9
75°	91.4	100.3	96.6	82.7	70.4	63.0	58.4	55.9	54.7	55.3	54.4
77.5°	65.8	71.4	68.0	58.4	50.8	45.5	42.1	40.6	39.4	39.4	39.1
80°	49.7	53.0	51.1	45.3	39.1	34.5	31.7	30.8	30.1	29.9	29.7
82.5°	35.4	38.2	35.9	32.0	27.7	25.0	23.5	22.1	21.7	21.8	21.6
85°	17.8	18.9	18.1	15.6	13.9	12.7	11.9	11.2	10.8	11.0	10.6
87.5°	8.8	8.6	7.7	6.7	6.1	5.2	4.9	4.3	4.2	4.5	4.7
90°	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4	2.8	4.2	6.2
92.5°	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6	12.8	18.7	24.2
95°	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7	25.8	33.4	45.3
97.5°	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4	41.1	47.2	57.4
100°	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6	52.3	57.2	67.0
102.5°	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3	64.6	68.8	78.1
105°	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9	82.9	87.1	95.5
107.5°	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5	101.7	105.7	113.9
110°	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0	115.0	118.5	126.2



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2	127.3	130.8	138.5
115°	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6	163.8	167.3	173.7
120°	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9	175.0	178.4	185.5
122.5°	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5	185.6	189.0	196.6
125°	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7	200.1	204.3	212.0
127.5°	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3	212.3	217.5	225.3
130°	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5	219.6	225.9	234.3
132.5°	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1	225.8	232.6	242.6
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8	235.7	243.3	253.8
137.5°	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0	245.0	252.5	263.7
140°	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2	251.6	258.7	269.8
142.5°	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9	257.8	265.4	275.4
145°	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6	267.7	274.0	284.5
147.5°	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5	277.8	283.9	292.9
150°	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7	284.5	290.0	299.1
152.5°	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0	291.1	296.7	304.7
155°	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8	301.8	306.0	313.0
157.5°	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5	311.0	314.4	320.6
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3	322.3	324.5	329.0
165°	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8	329.0	330.5	333.9
167.5°	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5	334.7	335.4	338.0
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9	337.4	338.1	340.2
172.5°	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1	340.2	340.4	341.9
175°	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9	344.4	343.8	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	421.6	420.4	418.8	416.3	414.3	411.2	411.2	411.6	411.6	411.5	411.2
5°	408.8	405.7	402.0	397.6	393.1	388.4	387.6	385.9	384.8	383.9	382.9
7.5°	395.3	389.8	384.3	378.3	372.6	368.1	364.9	362.2	360.5	358.6	357.3
10°	386.2	379.3	372.9	366.5	359.4	353.7	350.3	347.8	345.9	344.2	343.4
12.5°	375.4	367.6	360.4	354.3	346.6	340.8	337.4	336.3	334.1	330.6	328.8
15°	359.6	352.3	343.8	334.5	330.7	323.7	319.7	317.8	316.6	313.9	313.1
17.5°	346.1	336.6	327.0	320.0	313.1	307.4	305.1	302.8	301.2	299.0	298.3
20°	335.3	326.8	318.1	310.6	303.3	297.0	295.2	293.6	291.9	290.9	290.0
22.5°	324.3	315.8	308.5	301.6	293.8	289.7	287.8	285.9	284.7	284.0	283.2
25°	308.9	301.4	293.3	287.1	280.9	278.1	276.9	275.9	275.0	274.0	273.8
27.5°	295.2	287.0	280.4	274.6	270.1	267.9	266.6	266.2	266.4	266.7	267.0
30°	284.8	277.3	272.0	267.0	262.8	260.7	260.5	260.5	261.4	261.5	262.0
32.5°	275.4	269.2	263.8	259.0	255.8	254.4	255.2	255.2	255.8	256.4	257.2
35°	261.5	256.1	252.0	247.8	245.1	245.8	246.2	246.6	247.6	248.9	249.7
37.5°	248.3	243.7	239.3	236.1	234.9	235.9	237.0	237.8	239.1	240.0	240.9
40°	238.9	235.3	231.2	228.3	228.7	229.3	230.2	231.2	232.3	232.9	233.7
42.5°	230.1	226.4	223.2	220.8	221.4	222.2	222.7	223.2	224.4	225.6	226.0
45°	216.7	213.7	210.9	209.4	209.8	210.3	210.6	211.2	212.3	213.1	213.4
47.5°	201.6	199.6	197.6	196.2	196.9	196.7	197.2	198.6	198.9	199.4	200.5
50°	192.0	190.1	187.8	187.3	187.3	187.3	187.6	189.2	189.2	190.1	190.9
52.5°	181.3	180.1	178.7	177.9	177.5	177.5	178.4	179.2	179.6	180.7	181.6
55°	165.6	164.3	163.1	162.5	162.0	162.5	164.1	164.5	165.6	166.2	166.8
57.5°	149.2	148.2	147.2	146.9	146.8	147.3	148.2	149.5	149.7	151.7	152.6
60°	138.4	136.9	136.1	136.1	135.6	137.5	137.1	139.2	139.6	140.9	142.3
62.5°	127.2	125.3	124.9	124.9	125.6	126.1	126.6	127.5	128.7	130.2	131.3
65°	109.2	108.3	109.7	109.5	109.1	110.3	110.3	111.4	112.6	114.0	116.4
67.5°	92.3	91.8	91.8	91.8	92.5	93.2	93.8	94.7	96.2	97.7	99.2
70°	80.8	81.4	80.4	81.2	81.9	82.0	82.5	83.7	85.3	86.4	88.1
72.5°	69.6	69.6	69.7	70.1	70.7	71.1	71.5	72.9	74.7	75.6	77.0
75°	53.6	53.4	54.0	54.0	55.0	55.5	55.9	56.5	58.1	59.4	60.5
77.5°	39.1	39.4	39.2	39.9	39.7	39.8	41.0	41.6	41.8	44.3	44.9
80°	29.5	29.9	30.1	30.3	30.5	30.1	31.6	32.2	32.2	33.6	34.7
82.5°	21.2	21.4	21.9	22.2	22.2	22.6	22.7	23.2	23.7	24.3	25.7
85°	10.6	11.2	11.4	11.2	11.4	11.0	11.6	11.9	12.0	12.0	12.0
87.5°	4.8	5.3	5.5	6.2	6.4	7.0	6.9	6.7	6.8	7.4	7.0
90°	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4	18.1	18.8	20.2
92.5°	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7	46.5	41.1	37.5
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0	170.1	133.1	108.1
97.5°	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6	501.1	411.2	327.8
100°	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0	765.4	683.9	584.9
102.5°	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2	885.4	837.9	775.1
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.2
107.5°	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4	964.6	1025.6	1050.4
110°	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0	927.2	1015.0	1063.9



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1	878.2	976.6	1039.3
115°	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3	799.6	902.1	978.1
117.5°	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6	733.3	825.3	902.4
120°	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4	696.4	780.2	850.5
122.5°	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8	666.9	744.4	809.9
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2	630.3	697.1	753.0
127.5°	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3	598.0	658.4	709.2
130°	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2	577.9	634.5	681.8
132.5°	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2	559.0	611.5	656.7
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3	505.9	544.9	579.3
140°	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.2	554.2
142.5°	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8	476.3	505.3	531.4
145°	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4	457.4	479.7	499.9
147.5°	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0	443.3	461.3	475.6
150°	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3	434.4	449.0	462.2
152.5°	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1	426.0	438.9	450.0
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.5	432.9
157.5°	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2	402.5	410.6	417.1
160°	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6	395.3	402.3	407.2
162.5°	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9	387.4	393.9	398.2
165°	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3	376.5	381.4	384.9
167.5°	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7	367.9	370.8	373.3
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.9	364.6	366.0
172.5°	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3	356.8	359.0	359.9
175°	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3	350.0	351.3	351.3
177.5°	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5	346.1	346.6	346.6
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	410.0	409.8	411.0	410.2	411.0	409.8	410.0	411.2	411.5	411.6	411.6
5°	381.7	382.3	380.1	380.1	380.1	382.3	381.7	382.9	383.9	384.8	385.9
7.5°	356.3	355.4	355.5	354.4	355.5	355.4	356.3	357.3	358.6	360.5	362.2
10°	340.9	339.7	339.2	339.5	339.2	339.7	340.9	343.4	344.2	345.9	347.8
12.5°	328.1	327.9	325.1	325.1	325.1	327.9	328.1	328.8	330.6	334.1	336.3
15°	313.1	309.2	308.7	310.0	308.7	309.2	313.1	313.1	313.9	316.6	317.8
17.5°	298.0	295.9	296.0	295.4	296.0	295.9	298.0	298.3	299.0	301.2	302.8
20°	290.0	288.7	288.6	287.1	288.6	288.7	290.0	290.0	290.9	291.9	293.6
22.5°	282.7	282.3	282.4	280.8	282.4	282.3	282.7	283.2	284.0	284.7	285.9
25°	273.6	274.6	273.8	273.8	273.8	274.6	273.6	273.8	274.0	275.0	275.9
27.5°	267.4	267.4	267.0	267.0	267.0	267.4	267.4	267.0	266.7	266.4	266.2
30°	262.8	262.6	263.0	263.0	263.0	262.6	262.8	262.0	261.5	261.4	260.5
32.5°	258.2	258.4	258.5	258.7	258.5	258.4	258.2	257.2	256.4	255.8	255.2
35°	250.9	251.2	251.8	251.4	251.8	251.2	250.9	249.7	248.9	247.6	246.6
37.5°	241.2	242.2	242.0	242.3	242.0	242.2	241.2	240.9	240.0	239.1	237.8
40°	233.9	234.5	234.3	234.3	234.3	234.5	233.9	233.7	232.9	232.3	231.2
42.5°	226.4	226.9	226.3	226.0	226.3	226.9	226.4	226.0	225.6	224.4	223.2
45°	214.2	213.7	214.4	213.6	214.4	213.7	214.2	213.4	213.1	212.3	211.2
47.5°	200.5	200.9	201.1	201.7	201.1	200.9	200.5	200.5	199.4	198.9	198.6
50°	191.4	192.6	192.6	192.3	192.6	192.6	191.4	190.9	190.1	189.2	189.2
52.5°	182.4	182.9	183.8	183.7	183.8	182.9	182.4	181.6	180.7	179.6	179.2
55°	168.4	168.9	169.3	169.5	169.3	168.9	168.4	166.8	166.2	165.6	164.5
57.5°	154.1	153.9	154.9	155.2	154.9	153.9	154.1	152.6	151.7	149.7	149.5
60°	143.9	143.9	145.6	146.2	145.6	143.9	143.9	142.3	140.9	139.6	139.2
62.5°	133.1	133.8	135.5	134.6	135.5	133.8	133.1	131.3	130.2	128.7	127.5
65°	117.3	119.0	118.9	119.7	118.9	119.0	117.3	116.4	114.0	112.6	111.4
67.5°	100.9	101.9	103.4	103.5	103.4	101.9	100.9	99.2	97.7	96.2	94.7
70°	89.7	90.8	91.6	92.2	91.6	90.8	89.7	88.1	86.4	85.3	83.7
72.5°	78.9	79.5	81.5	80.6	81.5	79.5	78.9	77.0	75.6	74.7	72.9
75°	61.9	63.4	64.6	64.0	64.6	63.4	61.9	60.5	59.4	58.1	56.5
77.5°	45.7	47.3	47.8	47.3	47.8	47.3	45.7	44.9	44.3	41.8	41.6
80°	36.1	35.9	37.2	37.0	37.2	35.9	36.1	34.7	33.6	32.2	32.2
82.5°	26.5	26.3	26.8	27.0	26.8	26.3	26.5	25.7	24.3	23.7	23.2
85°	12.8	13.5	12.7	12.5	12.7	13.5	12.8	12.0	12.0	12.0	11.9
87.5°	6.9	7.0	7.0	6.7	7.0	7.0	6.9	7.0	7.4	6.8	6.7
90°	19.5	20.2	21.0	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4
92.5°	36.3	34.2	34.9	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7
95°	94.8	88.5	83.6	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0
97.5°	276.3	245.0	226.1	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6
100°	514.5	463.6	436.4	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0
102.5°	720.3	680.0	657.3	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2
105°	939.1	912.6	890.3	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3
107.5°	1051.1	1042.1	1034.6	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4
110°	1083.3	1089.0	1087.5	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1075.0	1092.3	1097.6	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1
115°	1030.4	1061.0	1075.0	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3
117.5°	956.9	992.0	1012.1	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6
120°	905.6	944.7	961.4	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4
122.5°	858.7	893.9	912.3	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8
125°	797.5	828.2	845.6	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2
127.5°	748.9	775.1	790.9	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3
130°	718.8	743.9	758.5	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2
132.5°	691.4	716.6	729.5	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2
135°	651.1	672.1	684.6	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4
137.5°	608.1	629.3	639.9	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3
140°	580.8	600.2	611.4	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2
142.5°	553.9	571.2	581.3	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8
145°	517.3	531.9	537.5	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4
147.5°	488.8	498.7	504.1	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0
150°	472.7	480.4	484.6	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3
152.5°	458.2	465.3	467.8	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1
155°	439.2	444.8	446.2	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0
157.5°	422.6	426.8	427.9	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2
160°	412.1	416.2	416.2	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6
162.5°	401.4	405.0	405.0	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9
165°	387.6	390.4	389.7	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3
167.5°	374.5	376.5	375.8	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7
170°	366.7	368.1	367.4	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7
172.5°	360.0	361.4	360.2	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3
175°	351.3	352.0	351.3	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3
177.5°	346.1	346.6	345.5	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	411.2	411.2	414.3	416.3	418.8	420.4	421.6	422.8	424.8	427.4	430.4
5°	387.6	388.4	393.1	397.6	402.0	405.7	408.8	412.6	417.1	422.8	429.0
7.5°	364.9	368.1	372.6	378.3	384.3	389.8	395.3	401.4	408.0	416.2	424.9
10°	350.3	353.7	359.4	366.5	372.9	379.3	386.2	392.8	400.9	410.7	422.0
12.5°	337.4	340.8	346.6	354.3	360.4	367.6	375.4	384.1	393.2	404.8	417.6
15°	319.7	323.7	330.7	334.5	343.8	352.3	359.6	372.0	383.7	395.7	410.5
17.5°	305.1	307.4	313.1	320.0	327.0	336.6	346.1	356.5	368.1	382.8	401.3
20°	295.2	297.0	303.3	310.6	318.1	326.8	335.3	345.7	358.7	374.3	394.3
22.5°	287.8	289.7	293.8	301.6	308.5	315.8	324.3	336.7	350.6	365.9	387.4
25°	276.9	278.1	280.9	287.1	293.3	301.4	308.9	320.6	334.8	352.8	374.3
27.5°	266.6	267.9	270.1	274.6	280.4	287.0	295.2	305.0	319.5	338.9	361.9
30°	260.5	260.7	262.8	267.0	272.0	277.3	284.8	296.0	309.8	329.5	353.6
32.5°	255.2	254.4	255.8	259.0	263.8	269.2	275.4	286.4	299.6	319.0	343.8
35°	246.2	245.8	245.1	247.8	252.0	256.1	261.5	269.8	284.8	302.9	328.9
37.5°	237.0	235.9	234.9	236.1	239.3	243.7	248.3	255.7	268.7	288.6	313.4
40°	230.2	229.3	228.7	228.3	231.2	235.3	238.9	245.9	258.0	276.9	301.4
42.5°	222.7	222.2	221.4	220.8	223.2	226.4	230.1	236.3	248.3	266.1	289.3
45°	210.6	210.3	209.8	209.4	210.9	213.7	216.7	221.2	231.7	248.9	269.8
47.5°	197.2	196.7	196.9	196.2	197.6	199.6	201.6	206.5	216.4	230.4	245.8
50°	187.6	187.3	187.3	187.3	187.8	190.1	192.0	195.7	204.8	218.7	229.8
52.5°	178.4	177.5	177.5	177.9	178.7	180.1	181.3	185.4	193.3	204.8	214.8
55°	164.1	162.5	162.0	162.5	163.1	164.3	165.6	168.9	175.8	184.2	190.1
57.5°	148.2	147.3	146.8	146.9	147.2	148.2	149.2	152.8	158.2	162.6	166.4
60°	137.1	137.5	135.6	136.1	136.1	136.9	138.4	140.6	145.2	148.3	152.0
62.5°	126.6	126.1	125.6	124.9	124.9	125.3	127.2	129.0	133.0	134.6	137.4
65°	110.3	110.3	109.1	109.5	109.7	108.3	109.2	111.4	113.9	114.5	117.2
67.5°	93.8	93.2	92.5	91.8	91.8	91.8	92.3	93.3	95.1	95.4	97.5
70°	82.5	82.0	81.9	81.2	80.4	81.4	80.8	81.9	82.9	83.1	84.4
72.5°	71.5	71.1	70.7	70.1	69.7	69.6	69.6	70.9	71.6	71.3	72.7
75°	55.9	55.5	55.0	54.0	54.0	53.4	53.6	54.4	55.3	54.7	55.9
77.5°	41.0	39.8	39.7	39.9	39.2	39.4	39.1	39.1	39.4	39.4	40.6
80°	31.6	30.1	30.5	30.3	30.1	29.9	29.5	29.7	29.9	30.1	30.8
82.5°	22.7	22.6	22.2	22.2	21.9	21.4	21.2	21.6	21.8	21.7	22.1
85°	11.6	11.0	11.4	11.2	11.4	11.2	10.6	10.6	11.0	10.8	11.2
87.5°	6.9	7.0	6.4	6.2	5.5	5.3	4.8	4.7	4.5	4.2	4.3
90°	16.8	17.4	15.3	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4
92.5°	80.9	107.2	118.0	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6
95°	335.4	413.4	368.1	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7
97.5°	685.5	640.7	469.0	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4
100°	797.5	660.2	446.2	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6
102.5°	803.2	623.9	412.7	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3
105°	760.6	560.5	371.6	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9
107.5°	686.2	504.4	345.4	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5
110°	639.3	472.7	335.4	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	598.6	451.5	329.8	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2
115°	549.4	428.7	327.7	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9
117.5°	519.7	415.4	329.0	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6
120°	504.1	409.2	331.2	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9
122.5°	491.2	405.4	335.0	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5
125°	474.7	400.2	340.9	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7
127.5°	460.3	397.7	347.6	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3
130°	452.5	396.0	352.0	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5
132.5°	445.2	395.4	355.4	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1
135°	435.7	394.6	360.4	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8
137.5°	427.5	393.1	363.8	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0
140°	422.5	392.5	366.0	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2
142.5°	418.0	391.4	367.7	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9
145°	412.1	389.7	368.8	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6
147.5°	406.2	387.1	368.8	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5
150°	402.3	384.9	368.8	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7
152.5°	397.8	382.0	367.1	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0
155°	391.1	377.2	365.3	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8
157.5°	383.6	372.8	362.9	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5
160°	378.5	369.5	361.9	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2
162.5°	373.5	366.1	359.6	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3
165°	366.7	361.1	356.2	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8
167.5°	360.2	356.1	352.9	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5
170°	356.2	352.8	350.7	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9
172.5°	352.3	350.0	349.0	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1
175°	347.9	346.5	346.5	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7
177.5°	344.9	344.4	344.9	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	431.4	432.3	435.1	437.1	439.4	440.8	442.0	443.1	444.4	444.7	449.5
5°	433.4	437.5	444.8	450.1	456.8	464.0	469.0	471.4	477.4	482.3	492.3
7.5°	432.8	441.7	452.6	464.0	476.2	487.5	497.3	509.0	517.2	529.7	541.9
10°	432.3	444.2	458.3	472.8	489.8	505.6	519.8	535.6	548.7	565.9	580.6
12.5°	430.8	445.1	464.8	482.0	502.7	524.4	545.4	565.6	577.2	605.9	619.5
15°	427.1	444.2	468.7	494.8	523.3	549.0	575.6	596.8	631.1	656.2	672.3
17.5°	420.1	443.9	473.0	504.5	539.1	573.1	603.2	635.3	671.7	702.1	734.6
20°	416.7	442.9	475.3	510.2	546.2	584.6	618.8	657.5	697.1	727.1	768.7
22.5°	410.5	440.2	475.1	514.0	552.4	592.2	632.3	671.3	717.1	758.3	797.9
25°	400.6	433.7	469.9	513.4	558.4	598.2	646.3	698.0	745.7	798.8	838.2
27.5°	389.9	425.4	461.6	502.0	550.5	597.9	658.3	716.7	775.1	820.8	850.1
30°	381.8	416.3	453.7	494.5	542.4	598.7	666.2	730.0	786.9	826.2	842.6
32.5°	373.0	408.0	441.0	483.8	534.9	598.2	671.2	737.8	787.6	813.7	810.5
35°	359.2	388.4	420.7	461.8	522.0	594.5	674.1	738.5	769.0	763.4	721.0
37.5°	339.2	363.9	395.6	440.6	507.1	586.8	668.2	716.6	714.6	669.0	607.5
40°	326.8	347.8	378.3	425.6	495.4	581.8	659.2	690.5	664.0	600.1	526.6
42.5°	310.5	329.8	360.3	409.0	482.7	571.8	641.7	650.8	598.8	525.4	458.0
45°	285.3	302.3	333.9	384.1	463.4	549.7	599.1	576.8	506.8	431.1	379.8
47.5°	258.1	275.8	306.1	357.8	435.7	516.5	540.0	492.8	420.9	359.4	312.3
50°	240.9	258.0	287.8	339.8	417.0	489.2	499.0	437.9	371.8	317.8	279.2
52.5°	223.7	239.7	268.9	321.3	395.0	457.6	451.7	389.4	328.7	282.6	252.3
55°	198.0	213.1	240.9	290.0	357.1	406.7	385.0	325.6	275.3	239.5	216.4
57.5°	175.0	189.5	213.5	257.8	316.1	350.3	322.5	272.4	232.5	204.9	187.8
60°	159.3	172.2	195.1	236.2	286.9	312.8	285.4	241.2	207.5	185.5	170.1
62.5°	144.5	155.8	176.9	214.3	258.3	280.1	252.4	214.9	186.3	166.7	153.6
65°	122.2	132.3	151.1	180.1	216.2	230.8	206.9	176.6	154.4	139.8	131.1
67.5°	101.7	110.4	126.5	149.4	176.0	186.5	168.4	144.9	128.1	116.5	109.6
70°	88.1	95.6	108.3	128.0	152.0	160.2	143.1	123.8	111.6	102.2	95.8
72.5°	76.6	82.1	93.6	108.9	128.9	135.4	123.5	106.6	95.1	88.1	82.9
75°	58.4	63.0	70.4	82.7	96.6	100.3	91.4	80.8	73.1	68.1	64.2
77.5°	42.1	45.5	50.8	58.4	68.0	71.4	65.8	58.7	53.1	49.8	47.5
80°	31.7	34.5	39.1	45.3	51.1	53.0	49.7	44.2	40.3	38.4	36.6
82.5°	23.5	25.0	27.7	32.0	35.9	38.2	35.4	32.1	30.0	28.3	27.6
85°	11.9	12.7	13.9	15.6	18.1	18.9	17.8	17.0	15.8	14.7	14.7
87.5°	4.9	5.2	6.1	6.7	7.7	8.6	8.8	8.9	9.1	8.8	8.8
90°	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4
92.5°	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7
95°	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0
97.5°	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6
100°	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0
102.5°	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2
105°	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3
107.5°	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4
110°	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1
115°	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3
117.5°	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6
120°	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4
122.5°	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8
125°	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2
127.5°	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3
130°	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2
132.5°	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2
135°	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4
137.5°	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3
140°	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2
142.5°	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8
145°	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4
147.5°	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0
150°	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3
152.5°	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1
155°	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0
157.5°	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2
160°	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6
162.5°	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9
165°	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3
167.5°	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7
170°	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7
172.5°	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3
175°	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3
177.5°	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	428.7	428.7	428.7	428.7	428.7	428.7	428.7
2.5°	451.2	451.4	453.2	454.5	453.9	454.7	455.0
5°	492.9	500.4	504.4	507.3	507.5	507.7	509.3
7.5°	552.1	560.2	566.1	575.0	577.6	580.6	579.8
10°	595.4	607.3	617.4	622.8	628.7	637.1	630.3
12.5°	635.8	656.7	672.3	680.6	686.1	687.8	684.5
15°	702.4	729.8	744.5	744.1	762.8	770.9	758.2
17.5°	763.4	788.7	809.0	819.4	835.0	838.4	836.9
20°	800.8	828.5	844.3	862.1	870.2	877.4	878.7
22.5°	833.0	857.9	874.9	889.7	896.4	899.9	902.0
25°	866.3	885.8	896.0	901.2	903.0	902.6	899.9
27.5°	864.0	865.5	854.3	843.3	833.4	822.3	818.5
30°	841.5	824.1	792.9	775.3	749.3	728.7	737.1
32.5°	782.6	747.8	712.8	674.2	642.3	633.2	624.0
35°	667.9	606.8	571.1	529.5	512.9	496.3	484.8
37.5°	540.3	493.1	450.7	423.6	406.9	396.4	390.7
40°	467.2	424.6	389.7	367.7	355.0	343.2	341.5
42.5°	408.8	369.3	343.0	325.5	313.3	308.3	304.6
45°	334.8	307.3	289.6	277.1	269.0	265.9	261.7
47.5°	283.5	263.9	250.7	242.2	236.0	233.7	233.4
50°	254.7	238.4	228.7	222.0	217.3	216.4	213.1
52.5°	233.1	219.0	211.4	205.6	202.2	199.8	198.9
55°	202.3	193.0	186.1	182.8	180.1	177.8	177.8
57.5°	177.0	169.2	164.7	161.8	161.0	159.4	158.4
60°	161.4	154.8	151.2	148.7	147.0	147.3	145.4
62.5°	146.2	141.8	138.4	136.0	133.9	134.0	134.1
65°	124.4	121.1	118.6	117.8	116.5	115.1	115.5
67.5°	105.5	102.4	100.4	99.0	98.5	97.7	99.0
70°	91.8	89.5	88.1	86.9	86.4	86.6	87.7
72.5°	79.4	77.8	76.8	76.2	75.3	75.3	76.1
75°	62.3	61.1	60.3	59.7	59.4	59.4	59.4
77.5°	45.7	45.5	45.1	44.2	44.2	44.5	44.5
80°	36.1	35.5	35.3	34.9	34.2	33.9	34.9
82.5°	27.0	26.4	26.2	26.1	25.1	25.1	25.9
85°	14.5	13.9	14.1	13.9	13.9	13.7	13.7
87.5°	8.7	8.7	8.8	8.9	8.8	8.8	9.0
90°	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P331885-940

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)