

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831578

Luminaire Tested: S123DIP-S560D805U935-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831578
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U935-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4737.3 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831578
CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	43	41	40				35	
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	39	36	34				30	
4	75	65	57	52	69	60	53	48	51	46	42	43	39	36	35	32	30				27	
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27				24	
6	64	52	45	39	59	49	42	37	42	36	32	35	31	28	29	26	24				21	
7	59	48	40	35	55	44	38	33	38	33	29	32	28	25	27	24	22				19	
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	25	22	20				17	
9	52	40	33	28	48	37	31	26	32	27	24	28	24	21	23	20	18				16	
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17				15	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	14960	14960	14960	14960	14960
5°	18919	17856	15092	12163	11177
10°	19102	19680	14993	9696	8473
15°	14388	18272	14890	8211	7165
20°	10024	14786	14700	7180	6509
25°	7644	11371	14377	6606	6105
30°	6612	9033	13858	6200	5780
35°	6135	7627	13263	5907	5550
40°	5809	6842	12424	5628	5473
45°	5616	6333	11357	5409	5439
50°	5518	5928	10098	5211	5411
55°	5313	5634	8860	5022	5435
60°	5124	5317	7636	4846	5345
65°	4814	5018	6586	4656	5239
70°	4444	4639	5602	4343	4932
75°	4022	4159	4799	4038	4504
80°	3316	3639	3800	3521	3800
85°	2631	2952	2791	2989	3026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 12968 cd/sqm



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.4	2.8
10°-20°	326.9	6.9
20°-30°	387.0	8.2
30°-40°	389.1	8.2
40°-50°	357.0	7.5
50°-60°	294.7	6.2
60°-70°	208.5	4.4
70°-80°	111.3	2.3
80°-90°	30.1	0.6
90°-100°	180.4	3.8
100°-110°	528.3	11.2
110°-120°	515.9	10.9
120°-130°	410.9	8.7
130°-140°	324.2	6.8
140°-150°	241.8	5.1
150°-160°	168.6	3.6
160°-170°	99.0	2.1
170°-180°	32.2	0.7
0°-30°	845.3	17.8
0°-40°	1234.4	26.1
0°-60°	1886.1	39.8
0°-90°	2235.9	47.2
90°-120°	1224.6	25.9
90°-150°	2201.5	46.5
90°-180°	2501.0	52.8
0°-180°	4737.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1390	1390	1390	1390	1390	
5°	1751	1653	1397	1126	1034	167
15°	1291	1640	1336	737	643	357
25°	644	957	1210	556	514	304
35°	467	580	1009	450	422	293
45°	369	416	746	355	357	286
55°	283	300	472	268	290	253
65°	189	197	259	183	206	188
75°	97	100	115	97	108	102
85°	21	24	23	24	24	24
90°	20	17	1	17	20	12
95°	78	399	23	399	78	127
105°	856	541	78	541	856	854
115°	1041	414	138	414	1041	1016
125°	821	386	192	386	821	743
135°	666	381	225	381	666	516
145°	520	376	256	376	520	330
155°	432	364	292	364	432	201
165°	376	349	318	349	376	107
175°	339	335	332	335	339	33
180°	332	332	332	332	332	



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1566.5	1564.8	1563.2	1555.2	1547.1	1543.2	1539.4	1527.8	1516.2	1503.3	1490.4
5°	1750.9	1755.4	1759.9	1754.8	1749.6	1733.8	1718.0	1697.0	1676.1	1652.6	1629.0
7.5°	1836.0	1838.6	1841.2	1838.0	1834.7	1830.5	1826.3	1807.6	1788.9	1764.8	1740.6
10°	1747.7	1753.5	1759.3	1771.9	1784.4	1798.6	1812.8	1810.2	1807.6	1800.6	1793.5
12.5°	1553.6	1560.7	1567.7	1592.9	1618.0	1650.3	1682.5	1710.3	1738.0	1757.3	1776.7
15°	1291.1	1310.8	1330.4	1353.3	1376.2	1423.6	1471.0	1529.4	1587.7	1639.7	1691.6
17.5°	1063.4	1070.9	1078.3	1102.8	1127.3	1186.9	1246.6	1314.0	1381.4	1467.5	1553.6
20°	875.1	881.9	888.7	920.9	953.2	999.9	1046.7	1122.4	1198.2	1290.8	1383.3
22.5°	735.2	745.8	756.5	774.5	792.6	837.4	882.2	949.6	1017.0	1119.2	1221.4
25°	643.6	651.3	659.1	670.0	681.0	716.8	752.6	808.1	863.5	957.4	1051.2
27.5°	581.1	584.3	587.5	598.5	609.4	632.6	655.9	703.6	751.3	831.0	910.6
30°	532.0	534.3	536.6	546.2	555.9	571.7	587.5	622.0	656.5	726.8	797.1
32.5°	497.9	499.5	501.1	508.5	515.9	527.2	538.5	563.6	588.8	646.8	704.9
35°	466.9	467.9	468.8	474.3	479.8	488.2	496.6	515.6	534.6	580.4	626.2
37.5°	439.8	441.1	442.4	445.6	448.8	456.3	463.7	478.8	494.0	529.1	564.3
40°	413.4	415.6	417.9	420.2	422.4	428.5	434.7	446.3	457.9	486.9	515.9
42.5°	390.8	393.1	395.3	396.3	397.3	400.8	404.4	415.0	425.6	447.2	468.8
45°	368.9	369.8	370.8	371.8	372.8	375.7	378.6	387.9	397.3	416.0	434.7
47.5°	348.9	348.9	348.9	349.5	350.2	352.8	355.3	362.1	368.9	383.4	397.9
50°	329.5	329.5	329.5	328.6	327.6	329.2	330.8	336.0	341.2	354.0	366.9
52.5°	306.3	306.3	306.3	306.6	307.0	307.0	307.0	311.5	316.0	327.6	339.2
55°	283.1	284.4	285.7	284.7	283.8	284.4	285.0	287.9	290.8	300.2	309.6
57.5°	259.9	260.5	261.2	260.9	260.5	260.9	261.2	263.8	266.3	273.4	280.5
60°	238.0	238.0	238.0	237.3	236.7	237.3	238.0	239.3	240.5	247.0	253.4
62.5°	213.5	213.8	214.1	214.4	214.8	214.1	213.5	215.1	216.7	221.5	226.4
65°	189.0	189.3	189.6	190.6	191.5	190.9	190.2	191.9	193.5	197.0	200.6
67.5°	167.0	166.4	165.7	166.1	166.4	167.4	168.3	168.6	169.0	172.8	176.7
70°	141.2	141.9	142.5	142.2	141.9	142.2	142.5	143.5	144.5	147.4	150.3
72.5°	118.0	118.3	118.7	118.7	118.7	119.3	120.0	120.9	121.9	123.5	125.1
75°	96.7	96.7	96.7	97.4	98.0	98.3	98.7	98.7	98.7	100.0	101.2
77.5°	73.5	75.1	76.7	76.4	76.1	76.7	77.4	78.4	79.3	80.0	80.6
80°	53.5	53.5	53.5	53.8	54.2	55.1	56.1	56.8	57.4	58.7	60.0
82.5°	34.2	34.5	34.8	35.8	36.8	37.4	38.0	39.0	40.0	40.0	40.0
85°	21.3	20.6	20.0	20.6	21.3	21.9	22.6	22.9	23.2	23.9	24.5
87.5°	10.3	10.3	10.3	10.3	10.3	10.6	11.0	11.0	11.0	11.0	11.0
90°	19.5	20.2	19.5	18.8	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	35.7	37.0	36.3	39.0	40.4	45.1	51.8	66.6	93.6	125.2	138.7
95°	78.1	80.8	85.5	91.5	104.3	128.6	164.2	242.3	323.8	399.2	355.4
97.5°	160.2	167.6	183.8	209.3	254.4	331.2	420.0	556.7	634.8	613.9	458.4
100°	422.1	421.4	447.6	496.8	564.8	660.4	739.1	793.6	770.1	637.5	430.8
102.5°	668.4	688.0	708.8	745.2	794.3	846.1	883.8	872.4	776.8	593.7	390.4
105°	856.2	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	978.8	986.2	994.9	1007.0	1011.1	992.9	940.4	834.7	673.8	494.8	335.9
110°	1048.8	1050.1	1051.5	1046.1	1027.2	980.1	895.3	771.4	617.3	456.4	323.8



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1062.9	1062.2	1055.5	1036.0	997.6	933.7	836.0	708.8	568.1	430.8	317.1
115°	1041.4	1038.0	1024.5	994.9	944.4	871.0	772.1	655.0	530.4	414.0	316.4
117.5°	994.2	989.5	969.3	936.3	883.8	807.8	716.9	613.2	505.5	402.5	317.1
120°	932.3	928.3	912.1	874.4	821.2	753.2	672.5	581.6	486.7	395.1	319.7
122.5°	874.4	869.0	850.9	817.9	772.1	710.2	636.8	556.7	471.2	390.4	324.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.5	535.2	458.4	386.4	329.2
127.5°	775.5	771.4	755.9	730.4	691.3	641.5	582.3	515.6	446.3	384.4	334.6
130°	737.8	732.4	718.2	694.0	658.3	612.6	558.0	497.5	436.9	382.3	339.9
132.5°	700.7	697.4	685.3	661.0	628.0	585.0	535.2	480.6	428.1	381.7	344.0
135°	665.7	661.0	648.9	628.7	595.7	557.4	513.6	465.8	420.7	381.0	348.0
137.5°	628.7	624.7	614.6	593.7	565.4	531.1	492.1	451.7	414.0	379.7	350.7
140°	589.7	590.3	579.6	560.7	535.2	506.2	473.9	439.6	407.9	379.0	353.4
142.5°	553.3	554.0	544.6	528.4	507.6	483.3	456.4	428.1	402.5	377.6	355.4
145°	520.3	519.0	513.6	499.5	482.6	463.1	441.6	419.4	397.8	376.3	356.1
147.5°	492.1	491.4	486.0	475.9	462.5	448.3	430.1	412.0	393.1	374.3	356.1
150°	467.8	467.8	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	447.6	447.6	445.6	438.9	431.5	421.4	409.3	396.5	383.0	368.2	354.1
155°	431.5	430.8	429.5	424.1	418.0	409.9	399.8	389.1	377.6	364.2	352.7
157.5°	416.0	416.0	414.7	410.6	405.2	398.5	390.4	381.0	371.6	360.8	350.7
160°	401.2	401.9	401.9	397.8	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	387.7	388.4	388.4	385.0	382.3	378.3	372.2	366.2	359.5	352.7	346.7
165°	376.3	376.3	377.0	374.3	371.6	368.2	363.5	359.5	354.1	348.7	344.0
167.5°	364.8	364.8	365.5	363.5	362.2	359.5	356.8	353.4	348.7	344.7	341.3
170°	354.7	354.7	355.4	354.1	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	345.3	346.0	347.3	346.0	346.0	345.3	343.3	342.0	339.3	337.2	336.6
175°	338.6	339.3	339.9	339.3	339.3	339.3	337.9	337.2	335.9	334.6	334.6
177.5°	333.9	333.9	335.2	334.6	335.2	335.2	334.6	333.9	333.2	332.5	333.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1486.5	1482.6	1468.4	1454.2	1438.1	1422.0	1410.1	1398.1	1380.4	1362.7	1348.2
5°	1611.0	1592.9	1562.9	1532.9	1492.3	1451.7	1424.3	1396.8	1360.1	1323.3	1294.0
7.5°	1709.6	1678.7	1636.8	1594.8	1541.6	1488.4	1438.1	1387.8	1331.7	1275.6	1229.8
10°	1772.5	1751.5	1703.2	1654.8	1583.5	1512.3	1442.0	1371.7	1299.5	1227.2	1166.6
12.5°	1778.6	1780.6	1736.1	1691.6	1611.0	1530.3	1444.9	1359.4	1268.5	1177.6	1107.0
15°	1724.8	1758.0	1733.5	1709.0	1627.7	1546.5	1441.3	1336.2	1231.4	1126.6	1045.1
17.5°	1624.8	1696.1	1699.6	1703.2	1621.9	1540.7	1424.3	1307.9	1189.2	1070.5	984.8
20°	1488.4	1593.5	1629.7	1665.8	1599.7	1533.6	1408.5	1283.3	1150.5	1017.6	927.7
22.5°	1349.1	1476.8	1542.9	1609.0	1560.0	1511.0	1377.8	1244.7	1104.4	964.1	872.9
25°	1190.5	1329.8	1431.4	1532.9	1502.9	1472.9	1341.7	1210.5	1061.2	911.9	818.7
27.5°	1052.2	1193.7	1316.2	1438.8	1432.3	1425.9	1295.6	1165.3	1012.5	859.6	769.7
30°	929.0	1060.9	1197.9	1334.9	1350.7	1366.5	1240.8	1115.0	961.9	808.7	722.0
32.5°	820.0	935.1	1082.1	1229.2	1260.1	1291.1	1177.6	1064.1	912.5	761.0	677.5
35°	730.7	835.1	982.2	1129.2	1167.9	1206.6	1107.9	1009.3	861.6	713.9	634.3
37.5°	651.7	739.1	882.5	1026.0	1073.4	1120.8	1032.5	944.1	805.8	667.5	594.3
40°	586.2	656.5	788.4	920.3	975.1	1029.9	957.0	884.2	752.9	621.7	554.3
42.5°	531.4	594.0	713.6	833.2	885.8	938.3	876.7	815.2	698.4	581.7	520.1
45°	484.6	534.6	643.3	752.0	801.9	851.9	799.0	746.1	643.3	540.4	483.0
47.5°	440.8	483.7	576.5	669.4	713.9	758.4	717.1	675.9	588.8	501.7	449.8
50°	401.4	436.0	517.2	598.5	637.2	675.9	639.4	603.0	531.4	459.8	414.7
52.5°	367.3	395.3	463.4	531.4	564.6	597.8	566.5	535.3	478.5	421.8	382.4
55°	333.4	357.3	416.3	475.3	497.9	520.4	496.2	472.1	426.3	380.5	347.3
57.5°	301.8	323.1	371.5	419.8	437.2	454.7	432.7	410.8	376.3	341.8	314.1
60°	270.9	288.3	328.6	368.9	379.5	390.2	372.4	354.7	330.5	306.3	281.5
62.5°	242.2	258.0	287.9	317.9	325.0	332.1	318.6	305.0	286.7	268.3	248.9
65°	212.5	224.4	248.9	273.4	278.0	282.5	270.5	258.6	244.7	230.9	216.7
67.5°	185.1	193.5	213.5	233.5	233.8	234.1	224.4	214.8	207.0	199.3	188.0
70°	158.3	166.4	179.6	192.8	193.1	193.5	185.7	178.0	172.2	166.4	158.0
72.5°	130.9	136.7	146.7	156.7	156.1	155.4	150.6	145.7	141.2	136.7	130.6
75°	106.1	110.9	117.7	124.5	122.5	120.6	118.0	115.4	111.6	107.7	103.8
77.5°	83.5	86.4	90.3	94.2	92.9	91.6	89.3	87.1	84.2	81.3	79.6
80°	61.3	62.6	65.1	67.7	67.1	66.4	63.8	61.3	60.6	60.0	57.7
82.5°	41.6	43.2	43.9	44.5	44.2	43.9	41.9	40.0	39.3	38.7	38.4
85°	24.8	25.2	25.5	25.8	24.8	23.9	23.2	22.6	22.6	22.6	22.2
87.5°	11.3	11.6	11.6	11.6	11.3	11.0	10.3	9.7	10.0	10.3	10.3
90°	12.8	10.8	8.8	7.4	6.1	4.0	2.7	1.3	2.7	4.0	6.1
92.5°	103.7	68.0	46.4	34.3	27.6	21.5	14.8	10.1	14.8	21.5	27.6
95°	245.0	144.7	87.5	61.3	43.8	32.3	24.9	22.9	24.9	32.3	43.8
97.5°	272.6	156.2	99.6	70.7	53.2	43.1	37.0	36.3	37.0	43.1	53.2
100°	253.8	154.2	107.0	80.8	64.6	55.2	50.5	49.8	50.5	55.2	64.6
102.5°	237.6	156.8	115.8	92.2	78.1	69.3	65.3	63.9	65.3	69.3	78.1
105°	231.6	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.2	171.0	138.7	119.1	107.0	99.0	94.9	92.9	94.9	99.0	107.0
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.0	111.1	114.4	121.8



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	240.3	193.9	166.3	148.1	136.6	129.2	125.9	123.9	125.9	129.2	136.6
115°	247.7	206.7	181.1	162.9	151.5	144.7	140.7	138.0	140.7	144.7	151.5
117.5°	257.1	220.1	194.5	177.7	164.9	158.9	155.5	152.1	155.5	158.9	164.9
120°	267.9	232.9	208.7	191.8	179.1	172.3	169.0	166.9	169.0	172.3	179.1
122.5°	278.0	246.4	222.8	204.6	192.5	185.1	181.7	179.7	181.7	185.1	192.5
125°	288.8	259.2	235.6	217.4	204.6	197.2	193.2	191.8	193.2	197.2	204.6
127.5°	297.5	270.6	247.7	229.5	215.4	208.0	203.3	201.3	203.3	208.0	215.4
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.0	210.0	212.0	218.1	226.2
132.5°	314.4	289.5	267.9	250.4	236.3	226.2	219.4	216.8	219.4	226.2	236.3
135°	321.1	298.2	277.3	259.2	245.0	234.9	227.5	224.8	227.5	234.9	245.0
137.5°	326.5	304.3	284.1	267.2	253.1	242.3	234.9	232.2	234.9	242.3	253.1
140°	330.5	310.3	290.8	274.0	260.5	249.7	243.0	239.6	243.0	249.7	260.5
142.5°	334.6	315.0	296.2	280.7	267.2	257.8	250.4	247.7	250.4	257.8	267.2
145°	337.2	319.1	301.6	286.1	274.6	264.5	258.5	256.5	258.5	264.5	274.6
147.5°	339.3	322.4	306.3	292.8	281.4	272.6	266.6	265.2	266.6	272.6	281.4
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.6	274.0	274.6	280.0	288.8
152.5°	341.3	327.8	315.0	303.6	295.5	288.1	282.7	282.7	282.7	288.1	295.5
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.5	291.5	291.5	295.5	302.2
157.5°	342.0	331.9	322.4	315.0	308.3	302.2	298.9	298.2	298.9	302.2	308.3
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.3	334.6	327.8	322.4	318.4	314.4	312.3	312.3	312.3	314.4	318.4
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	339.3	335.2	331.2	327.8	325.8	323.1	322.4	323.1	322.4	323.1	325.8
170°	337.2	334.6	331.2	329.8	328.5	326.5	325.8	327.1	325.8	326.5	328.5
172.5°	336.6	334.6	331.9	331.2	330.5	329.2	329.2	329.8	329.2	329.2	330.5
175°	335.2	333.9	332.5	331.9	331.9	330.5	331.2	331.9	331.2	330.5	331.9
177.5°	334.6	333.2	332.5	332.5	332.5	331.9	332.5	333.2	332.5	331.9	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8	1389.8
2.5°	1333.6	1321.1	1308.5	1298.8	1289.2	1272.7	1256.3	1252.4	1248.5	1243.0	1237.6
5°	1264.6	1233.7	1202.7	1175.0	1147.3	1125.7	1104.1	1089.9	1075.7	1065.4	1055.1
7.5°	1184.0	1137.6	1091.2	1058.3	1025.4	994.1	962.8	952.8	942.8	929.3	915.8
10°	1106.0	1054.7	1003.5	960.6	917.7	887.1	856.4	844.2	831.9	814.8	797.7
12.5°	1036.4	980.2	924.1	880.9	837.7	808.1	778.4	760.7	742.9	733.2	723.6
15°	963.5	903.5	843.5	803.5	763.6	736.8	710.0	694.6	679.1	669.7	660.4
17.5°	899.0	839.7	780.3	742.0	703.6	679.1	654.6	641.0	627.5	620.4	613.3
20°	837.7	779.7	721.6	684.2	646.8	626.8	606.8	598.1	589.4	583.6	577.8
22.5°	781.6	724.5	667.5	635.5	603.6	587.5	571.4	565.3	559.1	554.3	549.5
25°	725.5	674.6	623.6	596.5	569.4	556.2	543.0	536.9	530.8	525.9	521.1
27.5°	679.7	631.0	582.3	559.1	535.9	525.6	515.3	510.4	505.6	501.1	496.6
30°	635.2	591.7	548.2	528.2	508.2	498.8	489.5	484.6	479.8	475.6	471.4
32.5°	594.0	556.5	519.1	500.8	482.4	474.6	466.9	461.1	455.3	452.1	448.8
35°	554.6	521.1	487.5	472.4	457.2	449.5	441.8	436.9	432.1	429.5	426.9
37.5°	521.1	491.1	461.1	446.6	432.1	424.7	417.2	413.1	408.9	407.9	406.9
40°	486.9	461.1	435.3	421.1	406.9	400.5	394.0	391.5	388.9	388.2	387.6
42.5°	458.5	433.4	408.2	395.3	382.4	376.9	371.5	370.2	368.9	369.8	370.8
45°	425.6	404.7	383.7	371.8	359.9	355.3	350.8	349.9	348.9	350.8	352.8
47.5°	397.9	378.6	359.2	347.9	336.6	333.4	330.2	329.9	329.5	332.1	334.7
50°	369.5	350.8	332.1	323.1	314.1	311.2	308.3	309.2	310.2	314.4	318.6
52.5°	343.1	325.7	308.3	299.9	291.5	289.6	287.6	289.9	292.1	296.7	301.2
55°	314.1	298.3	282.5	276.0	269.6	267.6	265.7	270.2	274.7	278.9	283.1
57.5°	286.3	272.5	258.6	252.8	247.0	246.7	246.4	250.5	254.7	259.2	263.8
60°	256.7	245.1	233.5	228.9	224.4	225.1	225.7	230.6	235.4	238.9	242.5
62.5°	229.6	219.9	210.2	206.0	201.9	203.5	205.1	209.9	214.8	218.9	223.1
65°	202.5	194.4	186.4	183.5	180.6	182.8	185.1	189.3	193.5	196.4	199.3
67.5°	176.7	169.9	163.2	160.9	158.6	160.9	163.2	167.4	171.5	174.4	177.3
70°	149.6	144.1	138.7	137.0	135.4	138.0	140.6	144.1	147.7	150.6	153.5
72.5°	124.5	120.3	116.1	115.8	115.4	117.7	120.0	123.5	127.0	129.0	130.9
75°	100.0	97.7	95.4	95.1	94.8	97.1	99.3	101.2	103.2	104.8	106.4
77.5°	78.0	76.1	74.2	74.5	74.8	76.4	78.0	80.0	81.9	82.9	83.8
80°	55.5	54.8	54.2	54.8	55.5	56.8	58.0	59.3	60.6	61.3	61.9
82.5°	38.0	37.4	36.8	37.7	38.7	39.7	40.6	41.6	42.6	42.9	43.2
85°	21.9	22.9	23.9	23.9	23.9	24.2	24.5	24.8	25.2	24.8	24.5
87.5°	10.3	10.6	11.0	11.0	11.0	11.3	11.6	11.6	11.6	11.3	11.0
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	34.3	46.4	68.0	103.7	138.7	125.2	93.6	66.6	51.8	45.1	40.4
95°	61.3	87.5	144.7	245.0	355.4	399.2	323.8	242.3	164.2	128.6	104.3
97.5°	70.7	99.6	156.2	272.6	458.4	613.9	634.8	556.7	420.0	331.2	254.4
100°	80.8	107.0	154.2	253.8	430.8	637.5	770.1	793.6	739.1	660.4	564.8
102.5°	92.2	115.8	156.8	237.6	390.4	593.7	776.8	872.4	883.8	846.1	794.3
105°	105.0	125.9	162.2	231.6	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	119.1	138.7	171.0	230.2	335.9	494.8	673.8	834.7	940.4	992.9	1011.1
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.4	895.3	980.1	1027.2



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	148.1	166.3	193.9	240.3	317.1	430.8	568.1	708.8	836.0	933.7	997.6
115°	162.9	181.1	206.7	247.7	316.4	414.0	530.4	655.0	772.1	871.0	944.4
117.5°	177.7	194.5	220.1	257.1	317.1	402.5	505.5	613.2	716.9	807.8	883.8
120°	191.8	208.7	232.9	267.9	319.7	395.1	486.7	581.6	672.5	753.2	821.2
122.5°	204.6	222.8	246.4	278.0	324.5	390.4	471.2	556.7	636.8	710.2	772.1
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.2	608.5	673.1	727.0
127.5°	229.5	247.7	270.6	297.5	334.6	384.4	446.3	515.6	582.3	641.5	691.3
130°	240.3	258.5	280.7	306.3	339.9	382.3	436.9	497.5	558.0	612.6	658.3
132.5°	250.4	267.9	289.5	314.4	344.0	381.7	428.1	480.6	535.2	585.0	628.0
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.4	595.7
137.5°	267.2	284.1	304.3	326.5	350.7	379.7	414.0	451.7	492.1	531.1	565.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.6	473.9	506.2	535.2
142.5°	280.7	296.2	315.0	334.6	355.4	377.6	402.5	428.1	456.4	483.3	507.6
145°	286.1	301.6	319.1	337.2	356.1	376.3	397.8	419.4	441.6	463.1	482.6
147.5°	292.8	306.3	322.4	339.3	356.1	374.3	393.1	412.0	430.1	448.3	462.5
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	303.6	315.0	327.8	341.3	354.1	368.2	383.0	396.5	409.3	421.4	431.5
155°	309.6	319.1	330.5	341.3	352.7	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.0	322.4	331.9	342.0	350.7	360.8	371.6	381.0	390.4	398.5	405.2
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	322.4	327.8	334.6	341.3	346.7	352.7	359.5	366.2	372.2	378.3	382.3
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.1	359.5	363.5	368.2	371.6
167.5°	327.8	331.2	335.2	339.3	341.3	344.7	348.7	353.4	356.8	359.5	362.2
170°	329.8	331.2	334.6	337.2	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	331.2	331.9	334.6	336.6	336.6	337.2	339.3	342.0	343.3	345.3	346.0
175°	331.9	332.5	333.9	335.2	334.6	334.6	335.9	337.2	337.9	339.3	339.3
177.5°	332.5	332.5	333.2	334.6	333.2	332.5	333.2	333.9	334.6	335.2	335.2
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1389.8	1389.8	1389.8	1389.8
2.5°	1235.3	1233.0	1224.0	1215.0
5°	1047.3	1039.6	1037.0	1034.4
7.5°	915.1	914.5	900.9	887.4
10°	798.7	799.7	787.4	775.2
12.5°	715.5	707.5	706.5	705.5
15°	653.0	645.5	644.3	643.0
17.5°	608.8	604.3	603.0	601.7
20°	575.2	572.7	570.4	568.2
22.5°	546.2	543.0	541.1	539.1
25°	518.2	515.3	514.6	514.0
27.5°	493.0	489.5	489.5	489.5
30°	469.2	466.9	465.9	465.0
32.5°	446.9	445.0	445.0	445.0
35°	426.0	425.0	423.7	422.4
37.5°	406.9	406.9	406.3	405.6
40°	388.6	389.5	389.5	389.5
42.5°	371.8	372.8	372.8	372.8
45°	354.4	356.0	356.6	357.3
47.5°	337.3	339.9	340.5	341.2
50°	320.5	322.4	322.8	323.1
52.5°	303.4	305.7	307.3	308.9
55°	285.4	287.6	288.6	289.6
57.5°	266.0	268.3	268.6	268.9
60°	244.7	247.0	247.6	248.3
62.5°	224.4	225.7	226.4	227.0
65°	201.2	203.1	204.4	205.7
67.5°	179.0	180.6	180.6	180.6
70°	154.1	154.8	155.7	156.7
72.5°	131.2	131.6	131.6	131.6
75°	107.1	107.7	108.0	108.3
77.5°	84.2	84.5	84.5	84.5
80°	61.6	61.3	61.3	61.3
82.5°	42.2	41.3	41.3	41.3
85°	24.2	23.9	24.2	24.5
87.5°	11.0	11.0	11.0	11.0
90°	18.8	19.5	20.2	19.5
92.5°	39.0	36.3	37.0	35.7
95°	91.5	85.5	80.8	78.1
97.5°	209.3	183.8	167.6	160.2
100°	496.8	447.6	421.4	422.1
102.5°	745.2	708.8	688.0	668.4
105°	906.7	881.1	859.6	856.2
107.5°	1007.0	994.9	986.2	978.8
110°	1046.1	1051.5	1050.1	1048.8



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1036.0	1055.5	1062.2	1062.9
115°	994.9	1024.5	1038.0	1041.4
117.5°	936.3	969.3	989.5	994.2
120°	874.4	912.1	928.3	932.3
122.5°	817.9	850.9	869.0	874.4
125°	770.1	799.7	816.5	821.2
127.5°	730.4	755.9	771.4	775.5
130°	694.0	718.2	732.4	737.8
132.5°	661.0	685.3	697.4	700.7
135°	628.7	648.9	661.0	665.7
137.5°	593.7	614.6	624.7	628.7
140°	560.7	579.6	590.3	589.7
142.5°	528.4	544.6	554.0	553.3
145°	499.5	513.6	519.0	520.3
147.5°	475.9	486.0	491.4	492.1
150°	456.4	463.8	467.8	467.8
152.5°	438.9	445.6	447.6	447.6
155°	424.1	429.5	430.8	431.5
157.5°	410.6	414.7	416.0	416.0
160°	397.8	401.9	401.9	401.2
162.5°	385.0	388.4	388.4	387.7
165°	374.3	377.0	376.3	376.3
167.5°	363.5	365.5	364.8	364.8
170°	354.1	355.4	354.7	354.7
172.5°	346.0	347.3	346.0	345.3
175°	339.3	339.9	339.3	338.6
177.5°	334.6	335.2	333.9	333.9
180°	332.5	332.5	332.5	332.5



TEST NUMBER: P831578

CATALOG NUMBER: S123DIP-S560D805U935-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.70	13.50	13.69	14.50	15.81	14.93	15.74	15.92	16.73	18.05
	3H	14.34	15.06	15.34	16.06	17.40	16.36	17.07	17.35	18.08	19.41
	4H	14.92	15.60	15.93	16.60	17.95	16.80	17.48	17.81	18.49	19.83
	6H	15.28	15.91	16.31	16.92	18.28	17.08	17.70	18.10	18.71	20.07
	8H	15.38	15.97	16.41	17.00	18.35	17.14	17.73	18.16	18.76	20.11
	12H	15.42	15.99	16.45	17.01	18.38	17.15	17.72	18.19	18.74	20.12
4H	2H	13.27	13.95	14.28	14.95	16.30	15.09	15.77	16.11	16.78	18.12
	3H	15.09	15.66	16.12	16.69	18.05	16.71	17.27	17.73	18.31	19.66
	4H	15.79	16.30	16.82	17.33	18.71	17.29	17.81	18.32	18.83	20.21
	6H	16.26	16.70	17.30	17.75	19.13	17.69	18.13	18.73	19.19	20.56
	8H	16.39	16.81	17.44	17.85	19.24	17.80	18.21	18.84	19.26	20.65
	12H	16.46	16.83	17.52	17.89	19.29	17.84	18.22	18.90	19.28	20.67
8H	4H	16.05	16.46	17.09	17.51	18.90	17.39	17.80	18.43	18.85	20.24
	6H	16.63	16.98	17.70	18.06	19.45	17.89	18.23	18.96	19.32	20.71
	8H	16.84	17.14	17.92	18.21	19.62	18.07	18.37	19.14	19.44	20.85
	12H	16.96	17.23	18.04	18.29	19.74	18.17	18.43	19.25	19.50	20.95
12H	4H	16.05	16.42	17.11	17.48	18.88	17.36	17.74	18.42	18.80	20.19
	6H	16.68	16.99	17.76	18.06	19.46	17.90	18.20	18.98	19.27	20.68
	8H	16.92	17.18	17.99	18.25	19.70	18.10	18.36	19.18	19.43	20.88