

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831444

Luminaire Tested: S123DIP-S340D805U940-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831444  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D805U940-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4269.8 lumens  
Efficiency: N/A  
Efficacy: 129.4 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 33  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

### Luminous Intensity Polar Plot



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33				
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	36	35	28				
2	86	79	73	69	77	72	67	63	57	54	51	44	42	40	32	31	30	24				
3	79	70	63	58	71	63	57	53	51	47	43	40	37	35	29	27	26	21				
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	37	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	38	32	51	41	35	30	34	29	25	27	23	21	20	18	16	13				
8	53	41	34	29	48	37	31	27	31	26	23	25	21	19	19	16	15	12				
9	49	37	30	26	44	34	28	24	28	24	20	23	19	17	17	15	13	11				
10	46	34	28	23	41	32	25	21	26	22	18	21	18	15	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	9424	9424	9424	9424	9424
5°	11918	11249	9508	7662	7042
10°	12034	12398	9445	6108	5337
15°	9063	11510	9381	5173	4513
20°	6315	9314	9261	4523	4100
25°	4816	7163	9057	4162	3846
30°	4166	5691	8730	3905	3640
35°	3865	4804	8355	3721	3497
40°	3659	4310	7827	3545	3448
45°	3538	3988	7155	3408	3427
50°	3476	3734	6362	3282	3408
55°	3348	3549	5581	3164	3423
60°	3227	3350	4809	3053	3367
65°	3031	3161	4149	2934	3301
70°	2801	2921	3528	2735	3106
75°	2533	2620	3023	2541	2840
80°	2089	2294	2393	2219	2393
85°	1655	1853	1754	1877	1902

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 8170 cd/sqm



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.8	1.9
10°-20°	205.9	4.8
20°-30°	243.8	5.7
30°-40°	245.1	5.7
40°-50°	224.9	5.3
50°-60°	185.6	4.3
60°-70°	131.3	3.1
70°-80°	70.1	1.6
80°-90°	19.7	0.5
90°-100°	33.1	0.8
100°-110°	159.9	3.7
110°-120°	392.0	9.2
120°-130°	497.7	11.7
130°-140°	531.7	12.5
140°-150°	497.2	11.6
150°-160°	401.0	9.4
160°-170°	258.8	6.1
170°-180°	89.2	2.1
0°-30°	532.5	12.5
0°-40°	777.6	18.2
0°-60°	1188.2	27.8
0°-90°	1409.3	33.0
90°-120°	585.0	13.7
90°-150°	2111.5	49.5
90°-180°	2860.0	67.0
0°-180°	4269.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	876	876	876	876	876	
5°	1103	1041	880	709	652	105
15°	813	1033	842	464	405	225
25°	406	603	763	350	324	191
35°	294	366	636	283	266	185
45°	232	262	470	224	225	180
55°	178	189	297	169	182	160
65°	119	124	163	115	130	118
75°	61	63	73	61	68	64
85°	13	15	14	15	15	15
90°	21	17	1	17	21	10
95°	26	22	42	22	26	22
105°	31	153	208	153	31	64
115°	410	400	390	400	410	386
125°	560	558	549	558	560	501
135°	691	691	684	691	691	533
145°	797	795	789	795	797	498
155°	868	869	869	869	868	400
165°	915	914	917	914	915	258
175°	935	936	938	936	935	89
180°	938	938	938	938	938	



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5
2.5°	986.8	985.8	984.8	979.7	974.6	972.2	969.8	962.4	955.1	947.0	938.9
5°	1103.0	1105.9	1108.7	1105.5	1102.2	1092.2	1082.3	1069.1	1055.9	1041.1	1026.2
7.5°	1156.6	1158.3	1159.9	1157.9	1155.8	1153.2	1150.5	1138.8	1127.0	1111.7	1096.5
10°	1101.0	1104.6	1108.3	1116.2	1124.1	1133.1	1142.0	1140.4	1138.8	1134.3	1129.8
12.5°	978.7	983.2	987.6	1003.5	1019.3	1039.6	1059.9	1077.4	1094.9	1107.1	1119.3
15°	813.3	825.7	838.1	852.5	867.0	896.8	926.7	963.5	1000.2	1032.9	1065.6
17.5°	669.9	674.6	679.3	694.7	710.2	747.7	785.3	827.8	870.2	924.5	978.7
20°	551.3	555.6	559.8	580.1	600.5	629.9	659.4	707.1	754.8	813.1	871.4
22.5°	463.1	469.8	476.6	487.9	499.3	527.5	555.8	598.2	640.7	705.1	769.5
25°	405.5	410.3	415.2	422.1	429.0	451.6	474.1	509.1	544.0	603.1	662.2
27.5°	366.0	368.1	370.1	377.0	383.9	398.5	413.2	443.2	473.3	523.5	573.6
30°	335.2	336.6	338.0	344.1	350.2	360.2	370.1	391.8	413.6	457.9	502.1
32.5°	313.6	314.7	315.7	320.3	325.0	332.1	339.2	355.1	370.9	407.5	444.0
35°	294.1	294.7	295.4	298.8	302.3	307.5	312.8	324.8	336.8	365.6	394.5
37.5°	277.1	277.9	278.7	280.7	282.8	287.4	292.1	301.7	311.2	333.3	355.5
40°	260.4	261.8	263.3	264.7	266.1	270.0	273.8	281.1	288.4	306.7	325.0
42.5°	246.2	247.6	249.0	249.7	250.3	252.5	254.7	261.4	268.1	281.7	295.4
45°	232.4	233.0	233.6	234.2	234.8	236.7	238.5	244.4	250.3	262.0	273.8
47.5°	219.8	219.8	219.8	220.2	220.6	222.2	223.9	228.1	232.4	241.5	250.7
50°	207.6	207.6	207.6	207.0	206.4	207.4	208.4	211.7	214.9	223.0	231.2
52.5°	193.0	193.0	193.0	193.2	193.4	193.4	193.4	196.2	199.1	206.4	213.7
55°	178.4	179.2	180.0	179.4	178.8	179.2	179.6	181.4	183.2	189.1	195.0
57.5°	163.7	164.1	164.5	164.3	164.1	164.3	164.5	166.2	167.8	172.3	176.7
60°	149.9	149.9	149.9	149.5	149.1	149.5	149.9	150.7	151.5	155.6	159.7
62.5°	134.5	134.7	134.9	135.1	135.3	134.9	134.5	135.5	136.5	139.6	142.6
65°	119.0	119.2	119.4	120.1	120.7	120.3	119.8	120.9	121.9	124.1	126.3
67.5°	105.2	104.8	104.4	104.6	104.8	105.4	106.0	106.2	106.4	108.9	111.3
70°	89.0	89.4	89.8	89.6	89.4	89.6	89.8	90.4	91.0	92.8	94.7
72.5°	74.3	74.5	74.8	74.8	74.8	75.2	75.6	76.2	76.8	77.8	78.8
75°	60.9	60.9	60.9	61.3	61.8	62.0	62.2	62.2	62.2	63.0	63.8
77.5°	46.3	47.3	48.3	48.1	47.9	48.3	48.8	49.4	50.0	50.4	50.8
80°	33.7	33.7	33.7	33.9	34.1	34.7	35.3	35.8	36.2	37.0	37.8
82.5°	21.5	21.7	21.9	22.5	23.2	23.6	24.0	24.6	25.2	25.2	25.2
85°	13.4	13.0	12.6	13.0	13.4	13.8	14.2	14.4	14.6	15.0	15.4
87.5°	6.5	6.5	6.5	6.5	6.5	6.7	6.9	6.9	6.9	6.9	6.9
90°	20.9	20.6	20.3	20.0	19.7	19.2	18.6	18.0	17.4	16.7	14.7
92.5°	23.7	23.5	23.4	23.2	23.1	22.5	21.4	20.3	19.2	18.1	16.7
95°	26.5	26.5	26.5	26.5	26.5	25.9	24.9	23.8	22.7	21.6	19.9
97.5°	28.6	28.4	28.3	28.1	28.0	27.3	26.0	24.8	23.5	22.3	30.2
100°	29.3	29.1	29.0	28.8	28.7	28.0	26.7	25.5	24.2	23.0	47.2
102.5°	30.0	29.7	29.4	29.0	28.7	31.1	36.3	41.4	46.5	51.6	78.5
105°	30.7	30.4	30.1	29.7	29.4	43.0	70.4	97.8	125.3	152.7	166.6
107.5°	72.5	92.8	113.1	133.4	153.7	175.8	199.6	223.5	247.3	271.2	268.9
110°	191.7	213.9	236.0	258.2	280.3	294.0	299.1	304.2	309.3	314.4	312.7



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.2	363.5	363.8	364.1	364.4	363.9	362.5	361.1	359.7	358.3	356.6
115°	409.9	409.3	408.7	408.1	407.4	406.4	404.8	403.3	401.7	400.2	398.8
117.5°	447.6	447.4	447.3	447.1	446.9	446.2	445.0	443.8	442.5	441.3	440.5
120°	486.6	486.6	486.6	486.6	486.6	486.0	484.7	483.5	482.3	481.0	480.6
122.5°	524.9	524.8	524.6	524.5	524.3	523.9	523.1	522.3	521.5	520.8	520.1
125°	560.5	560.2	559.9	559.6	559.3	558.9	558.6	558.3	558.0	557.7	557.1
127.5°	595.4	595.7	596.0	596.3	596.6	596.5	596.0	595.6	595.1	594.7	593.9
130°	628.8	629.1	629.4	629.7	630.1	629.9	629.3	628.7	628.0	627.4	626.8
132.5°	659.5	660.0	660.4	660.9	661.3	661.3	660.7	660.0	659.4	658.8	658.3
135°	690.9	691.3	691.8	692.3	692.7	692.7	692.3	691.8	691.3	690.9	690.2
137.5°	720.8	721.1	721.5	721.8	722.1	721.8	721.1	720.3	719.5	718.7	718.4
140°	747.3	747.6	747.9	748.3	748.6	748.4	747.8	747.2	746.6	745.9	745.5
142.5°	771.7	772.2	772.7	773.1	773.6	773.6	773.1	772.7	772.2	771.7	771.3
145°	796.8	796.8	796.8	796.8	796.8	796.7	796.4	796.0	795.7	795.4	795.1
147.5°	814.9	815.7	816.5	817.3	818.0	818.3	818.0	817.7	817.4	817.0	816.7
150°	835.9	836.3	836.8	837.3	837.7	837.8	837.5	837.2	836.9	836.6	836.3
152.5°	852.6	853.4	854.1	854.9	855.7	855.8	855.2	854.5	853.9	853.3	853.1
155°	867.9	868.9	869.8	870.7	871.7	871.7	871.0	870.2	869.4	868.6	868.5
157.5°	881.2	882.4	883.7	884.9	886.1	886.3	885.4	884.4	883.5	882.6	882.7
160°	893.7	894.8	895.9	897.0	898.1	898.1	897.2	896.3	895.4	894.4	894.6
162.5°	905.6	906.5	907.4	908.4	909.3	909.2	908.1	907.0	906.0	904.9	905.0
165°	914.6	915.7	916.8	917.9	919.0	918.9	917.7	916.4	915.2	913.9	914.1
167.5°	921.6	922.9	924.1	925.3	926.6	926.6	925.3	924.1	922.9	921.6	921.6
170°	927.9	929.1	930.4	931.6	932.8	932.8	931.6	930.4	929.1	927.9	927.9
172.5°	931.4	932.8	934.2	935.6	936.9	937.0	935.8	934.5	933.3	932.1	931.9
175°	934.9	936.1	937.3	938.6	939.8	939.9	938.8	937.7	936.6	935.6	935.4
177.5°	935.6	937.1	938.7	940.2	941.8	941.9	940.7	939.4	938.2	936.9	936.8
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5
2.5°	936.4	934.0	925.1	916.1	906.0	895.8	888.3	880.8	869.6	858.4	849.3
5°	1014.9	1003.5	984.6	965.7	940.1	914.5	897.2	880.0	856.8	833.7	815.2
7.5°	1077.0	1057.5	1031.1	1004.7	971.2	937.7	906.0	874.3	838.9	803.6	774.7
10°	1116.6	1103.4	1072.9	1042.5	997.6	952.7	908.4	864.1	818.6	773.1	734.9
12.5°	1120.5	1121.7	1093.7	1065.6	1014.9	964.1	910.2	856.4	799.1	741.8	697.4
15°	1086.6	1107.5	1092.0	1076.6	1025.4	974.2	908.0	841.8	775.8	709.7	658.4
17.5°	1023.6	1068.5	1070.7	1072.9	1021.8	970.6	897.2	823.9	749.2	674.4	620.4
20°	937.7	1003.9	1026.6	1049.4	1007.7	966.1	887.3	808.5	724.8	641.1	584.4
22.5°	849.9	930.3	972.0	1013.6	982.8	951.9	868.0	784.1	695.7	607.4	549.9
25°	750.0	837.7	901.7	965.7	946.8	927.9	845.2	762.6	668.5	574.5	515.8
27.5°	662.8	752.0	829.2	906.4	902.3	898.3	816.2	734.1	637.8	541.6	484.9
30°	585.2	668.3	754.6	841.0	850.9	860.9	781.7	702.4	605.9	509.5	454.8
32.5°	516.6	589.1	681.7	774.3	793.8	813.3	741.8	670.3	574.9	479.4	426.8
35°	460.3	526.1	618.7	711.4	735.7	760.1	698.0	635.8	542.8	449.7	399.6
37.5°	410.5	465.6	556.0	646.4	676.2	706.1	650.4	594.8	507.6	420.5	374.4
40°	369.3	413.6	496.7	579.7	614.3	648.8	602.9	557.0	474.3	391.6	349.2
42.5°	334.8	374.2	449.5	524.9	558.0	591.1	552.3	513.5	440.0	366.5	327.7
45°	305.3	336.8	405.3	473.7	505.2	536.7	503.4	470.0	405.3	340.5	304.3
47.5°	277.7	304.7	363.2	421.7	449.7	477.8	451.8	425.8	370.9	316.1	283.4
50°	252.9	274.6	325.8	377.0	401.4	425.8	402.8	379.9	334.8	289.7	261.2
52.5°	231.4	249.0	291.9	334.8	355.7	376.6	356.9	337.2	301.4	265.7	240.9
55°	210.0	225.1	262.2	299.4	313.6	327.9	312.6	297.4	268.5	239.7	218.8
57.5°	190.1	203.5	234.0	264.5	275.4	286.4	272.6	258.8	237.1	215.3	197.9
60°	170.6	181.6	207.0	232.4	239.1	245.8	234.6	223.4	208.2	193.0	177.3
62.5°	152.6	162.5	181.4	200.3	204.8	209.2	200.7	192.2	180.6	169.0	156.8
65°	133.9	141.4	156.8	172.3	175.1	177.9	170.4	162.9	154.2	145.4	136.5
67.5°	116.6	121.9	134.5	147.1	147.3	147.5	141.4	135.3	130.4	125.5	118.4
70°	99.7	104.8	113.1	121.5	121.7	121.9	117.0	112.1	108.5	104.8	99.5
72.5°	82.5	86.1	92.4	98.7	98.3	97.9	94.9	91.8	89.0	86.1	82.3
75°	66.8	69.9	74.1	78.4	77.2	76.0	74.3	72.7	70.3	67.8	65.4
77.5°	52.6	54.4	56.9	59.3	58.5	57.7	56.3	54.8	53.0	51.2	50.2
80°	38.6	39.4	41.0	42.7	42.3	41.8	40.2	38.6	38.2	37.8	36.4
82.5°	26.2	27.2	27.6	28.0	27.8	27.6	26.4	25.2	24.8	24.4	24.2
85°	15.6	15.8	16.0	16.3	15.6	15.0	14.6	14.2	14.2	14.2	14.0
87.5°	7.1	7.3	7.3	7.3	7.1	6.9	6.5	6.1	6.3	6.5	6.5
90°	12.7	10.7	8.7	6.9	5.3	3.8	2.2	0.7	2.2	3.8	5.3
92.5°	15.3	13.9	12.5	12.3	13.2	14.2	15.1	16.0	15.1	14.2	13.2
95°	18.2	16.5	14.8	17.1	23.5	29.8	36.2	42.5	36.2	29.8	23.5
97.5°	38.1	46.0	53.9	60.0	64.4	68.7	73.0	77.4	73.0	68.7	64.4
100°	71.3	95.5	119.7	130.2	127.1	124.0	120.9	117.8	120.9	124.0	127.1
102.5°	105.5	132.5	159.4	171.9	169.9	167.9	165.8	163.8	165.8	167.9	169.9
105°	180.6	194.5	208.4	214.6	212.9	211.2	209.5	207.7	209.5	211.2	212.9
107.5°	266.5	264.2	261.9	260.0	258.6	257.2	255.8	254.5	255.8	257.2	258.6
110°	311.0	309.3	307.6	306.1	304.9	303.6	302.4	301.2	302.4	303.6	304.9





TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.9	353.2	351.5	350.1	349.0	347.9	346.9	345.8	346.9	347.9	349.0
115°	397.4	396.0	394.6	393.4	392.5	391.6	390.6	389.7	390.6	391.6	392.5
117.5°	439.7	439.0	438.2	437.3	436.2	435.1	434.0	432.9	434.0	435.1	436.2
120°	480.1	479.6	479.2	478.2	476.8	475.4	474.1	472.7	474.1	475.4	476.8
122.5°	519.5	518.9	518.3	517.4	516.3	515.3	514.2	513.1	514.2	515.3	516.3
125°	556.5	555.8	555.2	554.3	553.1	551.8	550.6	549.3	550.6	551.8	553.1
127.5°	593.1	592.3	591.6	590.6	589.3	588.1	586.8	585.6	586.8	588.1	589.3
130°	626.2	625.6	624.9	624.0	622.8	621.5	620.3	619.1	620.3	621.5	622.8
132.5°	657.9	657.4	656.9	656.1	654.8	653.6	652.4	651.1	652.4	653.6	654.8
135°	689.6	689.0	688.4	687.6	686.7	685.7	684.8	683.9	684.8	685.7	686.7
137.5°	718.1	717.8	717.5	716.7	715.5	714.3	713.0	711.8	713.0	714.3	715.5
140°	745.0	744.5	744.1	743.4	742.4	741.5	740.6	739.7	740.6	741.5	742.4
142.5°	770.8	770.3	769.9	769.2	768.2	767.3	766.4	765.5	766.4	767.3	768.2
145°	794.8	794.5	794.2	793.5	792.4	791.3	790.2	789.2	790.2	791.3	792.4
147.5°	816.4	816.1	815.8	815.3	814.5	813.7	812.9	812.2	812.9	813.7	814.5
150°	835.9	835.6	835.3	834.9	834.5	834.0	833.5	833.1	833.5	834.0	834.5
152.5°	853.0	852.8	852.7	852.5	852.4	852.2	852.1	851.9	852.1	852.2	852.4
155°	868.3	868.2	868.0	868.1	868.4	868.7	869.0	869.3	869.0	868.7	868.4
157.5°	882.9	883.0	883.2	883.3	883.3	883.3	883.3	883.3	883.3	883.3	883.3
160°	894.7	894.9	895.0	895.2	895.4	895.5	895.7	895.8	895.7	895.5	895.4
162.5°	905.2	905.3	905.5	905.8	906.3	906.7	907.2	907.7	907.2	906.7	906.3
165°	914.3	914.4	914.6	914.9	915.3	915.8	916.3	916.7	916.3	915.8	915.3
167.5°	921.6	921.6	921.6	921.9	922.5	923.2	923.8	924.4	923.8	923.2	922.5
170°	927.9	927.9	927.9	928.2	928.8	929.4	930.1	930.7	930.1	929.4	928.8
172.5°	931.8	931.6	931.4	931.8	932.5	933.3	934.1	934.9	934.1	933.3	932.5
175°	935.2	935.1	934.9	935.2	936.0	936.8	937.6	938.3	937.6	936.8	936.0
177.5°	936.6	936.5	936.3	936.6	937.4	938.2	939.0	939.7	939.0	938.2	937.4
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5	875.5
2.5°	840.2	832.2	824.3	818.2	812.1	801.8	791.4	789.0	786.5	783.1	779.6
5°	796.7	777.2	757.7	740.2	722.7	709.1	695.5	686.6	677.7	671.2	664.7
7.5°	745.9	716.7	687.4	666.7	646.0	626.3	606.6	600.3	594.0	585.4	576.9
10°	696.7	664.4	632.2	605.1	578.1	558.8	539.5	531.8	524.1	513.3	502.6
12.5°	652.9	617.5	582.2	555.0	527.7	509.1	490.4	479.2	468.0	461.9	455.8
15°	607.0	569.2	531.4	506.2	481.0	464.2	447.3	437.5	427.8	421.9	416.0
17.5°	566.3	529.0	491.6	467.4	443.2	427.8	412.4	403.8	395.3	390.8	386.4
20°	527.7	491.2	454.6	431.0	407.5	394.9	382.3	376.8	371.3	367.7	364.0
22.5°	492.4	456.4	420.5	400.4	380.3	370.1	360.0	356.1	352.2	349.2	346.1
25°	457.0	425.0	392.9	375.8	358.7	350.4	342.1	338.2	334.4	331.3	328.3
27.5°	428.2	397.5	366.9	352.2	337.6	331.1	324.6	321.6	318.5	315.7	312.8
30°	400.2	372.7	345.3	332.7	320.1	314.2	308.4	305.3	302.3	299.6	297.0
32.5°	374.2	350.6	327.0	315.5	303.9	299.0	294.1	290.5	286.8	284.8	282.8
35°	349.4	328.3	307.1	297.6	288.0	283.2	278.3	275.2	272.2	270.6	268.9
37.5°	328.3	309.4	290.5	281.3	272.2	267.5	262.9	260.2	257.6	257.0	256.4
40°	306.7	290.5	274.2	265.3	256.4	252.3	248.2	246.6	245.0	244.6	244.2
42.5°	288.9	273.0	257.2	249.0	240.9	237.5	234.0	233.2	232.4	233.0	233.6
45°	268.1	254.9	241.7	234.2	226.7	223.9	221.0	220.4	219.8	221.0	222.2
47.5°	250.7	238.5	226.3	219.2	212.1	210.0	208.0	207.8	207.6	209.2	210.9
50°	232.8	221.0	209.2	203.5	197.9	196.0	194.2	194.8	195.4	198.1	200.7
52.5°	216.1	205.2	194.2	188.9	183.6	182.4	181.2	182.6	184.0	186.9	189.7
55°	197.9	187.9	177.9	173.9	169.8	168.6	167.4	170.2	173.1	175.7	178.4
57.5°	180.4	171.6	162.9	159.3	155.6	155.4	155.2	157.8	160.5	163.3	166.2
60°	161.7	154.4	147.1	144.2	141.4	141.8	142.2	145.2	148.3	150.5	152.8
62.5°	144.6	138.5	132.4	129.8	127.2	128.2	129.2	132.2	135.3	137.9	140.6
65°	127.6	122.5	117.4	115.6	113.8	115.2	116.6	119.2	121.9	123.7	125.5
67.5°	111.3	107.1	102.8	101.4	99.9	101.4	102.8	105.4	108.1	109.9	111.7
70°	94.3	90.8	87.3	86.3	85.3	86.9	88.6	90.8	93.0	94.9	96.7
72.5°	78.4	75.8	73.1	72.9	72.7	74.1	75.6	77.8	80.0	81.3	82.5
75°	63.0	61.5	60.1	59.9	59.7	61.1	62.6	63.8	65.0	66.0	67.0
77.5°	49.2	47.9	46.7	46.9	47.1	48.1	49.2	50.4	51.6	52.2	52.8
80°	34.9	34.5	34.1	34.5	34.9	35.8	36.6	37.4	38.2	38.6	39.0
82.5°	24.0	23.6	23.2	23.8	24.4	25.0	25.6	26.2	26.8	27.0	27.2
85°	13.8	14.4	15.0	15.0	15.0	15.2	15.4	15.6	15.8	15.6	15.4
87.5°	6.5	6.7	6.9	6.9	6.9	7.1	7.3	7.3	7.3	7.1	6.9
90°	6.9	8.7	10.7	12.7	14.7	16.7	17.4	18.0	18.6	19.2	19.7
92.5°	12.3	12.5	13.9	15.3	16.7	18.1	19.2	20.3	21.4	22.5	23.1
95°	17.1	14.8	16.5	18.2	19.9	21.6	22.7	23.8	24.9	25.9	26.5
97.5°	60.0	53.9	46.0	38.1	30.2	22.3	23.5	24.8	26.0	27.3	28.0
100°	130.2	119.7	95.5	71.3	47.2	23.0	24.2	25.5	26.7	28.0	28.7
102.5°	171.9	159.4	132.5	105.5	78.5	51.6	46.5	41.4	36.3	31.1	28.7
105°	214.6	208.4	194.5	180.6	166.6	152.7	125.3	97.8	70.4	43.0	29.4
107.5°	260.0	261.9	264.2	266.5	268.9	271.2	247.3	223.5	199.6	175.8	153.7
110°	306.1	307.6	309.3	311.0	312.7	314.4	309.3	304.2	299.1	294.0	280.3



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.1	351.5	353.2	354.9	356.6	358.3	359.7	361.1	362.5	363.9	364.4
115°	393.4	394.6	396.0	397.4	398.8	400.2	401.7	403.3	404.8	406.4	407.4
117.5°	437.3	438.2	439.0	439.7	440.5	441.3	442.5	443.8	445.0	446.2	446.9
120°	478.2	479.2	479.6	480.1	480.6	481.0	482.3	483.5	484.7	486.0	486.6
122.5°	517.4	518.3	518.9	519.5	520.1	520.8	521.5	522.3	523.1	523.9	524.3
125°	554.3	555.2	555.8	556.5	557.1	557.7	558.0	558.3	558.6	558.9	559.3
127.5°	590.6	591.6	592.3	593.1	593.9	594.7	595.1	595.6	596.0	596.5	596.6
130°	624.0	624.9	625.6	626.2	626.8	627.4	628.0	628.7	629.3	629.9	630.1
132.5°	656.1	656.9	657.4	657.9	658.3	658.8	659.4	660.0	660.7	661.3	661.3
135°	687.6	688.4	689.0	689.6	690.2	690.9	691.3	691.8	692.3	692.7	692.7
137.5°	716.7	717.5	717.8	718.1	718.4	718.7	719.5	720.3	721.1	721.8	722.1
140°	743.4	744.1	744.5	745.0	745.5	745.9	746.6	747.2	747.8	748.4	748.6
142.5°	769.2	769.9	770.3	770.8	771.3	771.7	772.2	772.7	773.1	773.6	773.6
145°	793.5	794.2	794.5	794.8	795.1	795.4	795.7	796.0	796.4	796.7	796.8
147.5°	815.3	815.8	816.1	816.4	816.7	817.0	817.4	817.7	818.0	818.3	818.0
150°	834.9	835.3	835.6	835.9	836.3	836.6	836.9	837.2	837.5	837.8	837.7
152.5°	852.5	852.7	852.8	853.0	853.1	853.3	853.9	854.5	855.2	855.8	855.7
155°	868.1	868.0	868.2	868.3	868.5	868.6	869.4	870.2	871.0	871.7	871.7
157.5°	883.3	883.2	883.0	882.9	882.7	882.6	883.5	884.4	885.4	886.3	886.1
160°	895.2	895.0	894.9	894.7	894.6	894.4	895.4	896.3	897.2	898.1	898.1
162.5°	905.8	905.5	905.3	905.2	905.0	904.9	906.0	907.0	908.1	909.2	909.3
165°	914.9	914.6	914.4	914.3	914.1	913.9	915.2	916.4	917.7	918.9	919.0
167.5°	921.9	921.6	921.6	921.6	921.6	921.6	922.9	924.1	925.3	926.6	926.6
170°	928.2	927.9	927.9	927.9	927.9	927.9	929.1	930.4	931.6	932.8	932.8
172.5°	931.8	931.4	931.6	931.8	931.9	932.1	933.3	934.5	935.8	937.0	936.9
175°	935.2	934.9	935.1	935.2	935.4	935.6	936.6	937.7	938.8	939.9	939.8
177.5°	936.6	936.3	936.5	936.6	936.8	936.9	938.2	939.4	940.7	941.9	941.8
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	875.5	875.5	875.5	875.5
2.5°	778.2	776.8	771.1	765.4
5°	659.8	654.9	653.3	651.7
7.5°	576.5	576.1	567.6	559.0
10°	503.2	503.8	496.1	488.3
12.5°	450.8	445.7	445.1	444.5
15°	411.3	406.7	405.9	405.0
17.5°	383.5	380.7	379.9	379.0
20°	362.4	360.8	359.3	357.9
22.5°	344.1	342.1	340.9	339.6
25°	326.4	324.6	324.2	323.8
27.5°	310.6	308.4	308.4	308.4
30°	295.6	294.1	293.5	292.9
32.5°	281.5	280.3	280.3	280.3
35°	268.3	267.7	266.9	266.1
37.5°	256.4	256.4	255.9	255.5
40°	244.8	245.4	245.4	245.4
42.5°	234.2	234.8	234.8	234.8
45°	223.2	224.3	224.7	225.1
47.5°	212.5	214.1	214.5	214.9
50°	201.9	203.1	203.3	203.5
52.5°	191.1	192.6	193.6	194.6
55°	179.8	181.2	181.8	182.4
57.5°	167.6	169.0	169.2	169.4
60°	154.2	155.6	156.0	156.4
62.5°	141.4	142.2	142.6	143.0
65°	126.8	128.0	128.8	129.6
67.5°	112.7	113.8	113.8	113.8
70°	97.1	97.5	98.1	98.7
72.5°	82.7	82.9	82.9	82.9
75°	67.4	67.8	68.0	68.3
77.5°	53.0	53.2	53.2	53.2
80°	38.8	38.6	38.6	38.6
82.5°	26.6	26.0	26.0	26.0
85°	15.2	15.0	15.2	15.4
87.5°	6.9	6.9	6.9	6.9
90°	20.0	20.3	20.6	20.9
92.5°	23.2	23.4	23.5	23.7
95°	26.5	26.5	26.5	26.5
97.5°	28.1	28.3	28.4	28.6
100°	28.8	29.0	29.1	29.3
102.5°	29.0	29.4	29.7	30.0
105°	29.7	30.1	30.4	30.7
107.5°	133.4	113.1	92.8	72.5
110°	258.2	236.0	213.9	191.7



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	364.1	363.8	363.5	363.2
115°	408.1	408.7	409.3	409.9
117.5°	447.1	447.3	447.4	447.6
120°	486.6	486.6	486.6	486.6
122.5°	524.5	524.6	524.8	524.9
125°	559.6	559.9	560.2	560.5
127.5°	596.3	596.0	595.7	595.4
130°	629.7	629.4	629.1	628.8
132.5°	660.9	660.4	660.0	659.5
135°	692.3	691.8	691.3	690.9
137.5°	721.8	721.5	721.1	720.8
140°	748.3	747.9	747.6	747.3
142.5°	773.1	772.7	772.2	771.7
145°	796.8	796.8	796.8	796.8
147.5°	817.3	816.5	815.7	814.9
150°	837.3	836.8	836.3	835.9
152.5°	854.9	854.1	853.4	852.6
155°	870.7	869.8	868.9	867.9
157.5°	884.9	883.7	882.4	881.2
160°	897.0	895.9	894.8	893.7
162.5°	908.4	907.4	906.5	905.6
165°	917.9	916.8	915.7	914.6
167.5°	925.3	924.1	922.9	921.6
170°	931.6	930.4	929.1	927.9
172.5°	935.6	934.2	932.8	931.4
175°	938.6	937.3	936.1	934.9
177.5°	940.2	938.7	937.1	935.6
180°	938.3	938.3	938.3	938.3



TEST NUMBER: P831444

CATALOG NUMBER: S123DIP-S340D805U940-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.52	10.23	10.62	11.32	12.82	11.76	12.47	12.86	13.56	15.05
	3H	11.16	11.79	12.27	12.89	14.41	13.17	13.80	14.28	14.90	16.42
	4H	11.73	12.33	12.85	13.43	14.95	13.62	14.22	14.73	15.32	16.84
	6H	12.09	12.64	13.22	13.75	15.28	13.88	14.44	15.01	15.54	17.07
	8H	12.18	12.71	13.31	13.83	15.35	13.94	14.47	15.07	15.58	17.11
	12H	12.22	12.72	13.36	13.83	15.38	13.96	14.45	15.09	15.57	17.11
4H	2H	10.08	10.68	11.20	11.78	13.30	11.91	12.50	13.03	13.60	15.12
	3H	11.90	12.40	13.02	13.52	15.05	13.51	14.01	14.64	15.14	16.67
	4H	12.59	13.05	13.72	14.16	15.71	14.09	14.55	15.22	15.66	17.22
	6H	13.05	13.45	14.19	14.59	16.13	14.49	14.88	15.62	16.02	17.56
	8H	13.19	13.55	14.33	14.68	16.24	14.59	14.96	15.73	16.09	17.65
	12H	13.25	13.58	14.40	14.72	16.29	14.63	14.96	15.79	16.11	17.67
8H	4H	12.84	13.21	13.98	14.34	15.90	14.18	14.55	15.32	15.68	17.24
	6H	13.43	13.73	14.58	14.90	16.46	14.68	14.98	15.84	16.15	17.71
	8H	13.63	13.90	14.80	15.05	16.62	14.86	15.12	16.02	16.27	17.85
	12H	13.75	13.98	14.92	15.13	16.74	14.95	15.18	16.12	16.33	17.95
12H	4H	12.84	13.17	13.99	14.31	15.88	14.15	14.48	15.30	15.62	17.19
	6H	13.48	13.74	14.64	14.89	16.47	14.69	14.96	15.86	16.11	17.69
	8H	13.70	13.93	14.87	15.08	16.69	14.89	15.12	16.05	16.27	17.88