

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331943-940

Luminaire Tested: **S123DIP-S560D1025U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331943-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5723.9 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76		59	59	59		43	43	43	36
1	95	90	87	83	86	82	79	76	66	64	62		52	50	49		38	37	37	30
2	86	79	73	68	78	72	66	62	58	54	51		45	43	41		34	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43		40	37	34		30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36		36	32	29		27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31		32	28	25		24	21	20	16
6	61	49	41	35	55	44	37	32	36	31	27		29	25	22		22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24		26	22	20		20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21		24	20	17		18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19		22	18	16		17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17		20	17	14		16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8551	8551	8551
5°	8590	8473	8532
10°	8534	8400	8451
15°	8433	8304	8320
20°	8317	8168	8176
25°	8162	8007	7991
30°	7988	7828	7768
35°	7808	7638	7540
40°	7620	7429	7314
45°	7415	7237	7060
50°	7206	7000	6805
55°	6934	6756	6549
60°	6661	6469	6265
65°	6421	6159	5968
70°	6061	5803	5545
75°	5540	5340	5115
80°	4996	4785	4742
85°	4384	4224	4051



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	1.3
10°-20°	211.3	3.7
20°-30°	312.1	5.5
30°-40°	364.6	6.4
40°-50°	366.5	6.4
50°-60°	322.0	5.6
60°-70°	239.9	4.2
70°-80°	136.7	2.4
80°-90°	42.6	0.7
90°-100°	43.6	0.8
100°-110°	207.6	3.6
110°-120°	498.6	8.7
120°-130°	634.9	11.1
130°-140°	678.4	11.9
140°-150°	634.4	11.1
150°-160°	511.7	8.9
160°-170°	330.3	5.8
170°-180°	113.8	2.0
0°-30°	598.2	10.5
0°-40°	962.8	16.8
0°-60°	1651.3	28.9
0°-90°	2070.5	36.2
90°-120°	749.8	13.1
90°-150°	2697.6	47.1
90°-180°	3653.0	63.8
0°-180°	5723.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	794	794	794	794	794	
5°	795	791	784	791	790	75
15°	757	754	745	750	747	213
25°	687	683	674	675	673	316
35°	594	590	581	577	574	372
45°	487	484	475	467	464	376
55°	370	368	360	353	349	331
65°	252	248	242	236	234	249
75°	133	131	128	125	123	142
85°	36	34	34	33	33	39
90°	1	10	21	25	27	4
95°	54	20	28	34	34	67
105°	265	270	195	46	39	281
115°	498	503	511	520	523	491
125°	701	708	712	714	716	626
135°	873	878	882	884	882	672
145°	1008	1014	1016	1017	1017	630
155°	1110	1108	1109	1113	1108	511
165°	1170	1168	1167	1173	1168	331
175°	1198	1194	1194	1200	1194	114
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	797.1	796.7	796.2	795.7	795.2	794.2	792.9	791.6	790.3	789.0	790.1
5°	795.0	794.3	793.5	792.8	792.0	790.9	789.2	787.5	785.9	784.2	785.7
7.5°	787.3	786.6	785.8	785.1	784.3	783.0	781.3	779.5	777.8	776.1	777.5
10°	780.8	780.0	779.3	778.5	777.8	776.3	774.4	772.4	770.4	768.5	769.8
12.5°	772.0	771.3	770.7	770.1	769.5	768.2	766.3	764.5	762.7	760.8	761.8
15°	756.8	756.3	755.6	755.0	754.4	753.1	751.2	749.2	747.2	745.2	746.5
17.5°	739.2	738.4	737.6	736.8	736.0	734.7	732.7	730.8	728.8	726.7	727.6
20°	726.1	725.2	724.2	723.4	722.5	721.0	719.1	717.1	715.1	713.1	713.7
22.5°	711.3	710.4	709.5	708.6	707.7	706.2	704.3	702.3	700.3	698.4	698.8
25°	687.2	686.3	685.4	684.5	683.5	682.1	680.1	678.1	676.2	674.2	674.3
27.5°	661.4	660.5	659.6	658.7	657.8	656.3	654.2	652.1	650.0	647.8	647.9
30°	642.7	642.0	641.2	640.5	639.7	638.3	636.1	634.0	632.0	629.8	629.8
32.5°	624.2	623.2	622.1	621.2	620.2	618.8	617.2	615.5	613.9	612.3	611.4
35°	594.2	593.3	592.5	591.6	590.7	589.2	587.2	585.2	583.3	581.3	580.4
37.5°	563.7	562.5	561.3	560.2	559.0	557.5	555.4	553.5	551.4	549.5	548.4
40°	542.3	541.4	540.6	539.7	538.7	537.2	535.0	533.0	530.8	528.7	527.4
42.5°	521.0	520.0	519.0	517.9	516.9	515.3	513.2	511.1	509.0	506.8	505.6
45°	487.1	486.4	485.8	485.2	484.6	483.3	481.3	479.4	477.4	475.4	473.6
47.5°	453.3	452.4	451.6	450.7	449.8	448.4	446.6	444.7	442.8	441.0	439.2
50°	430.3	429.5	428.8	428.0	427.3	426.0	423.9	422.0	420.0	418.0	416.3
52.5°	406.3	405.7	405.3	404.7	404.2	402.9	400.8	398.8	396.6	394.6	393.2
55°	369.5	369.3	369.3	369.1	368.9	367.8	365.9	363.9	361.9	360.0	358.3
57.5°	334.6	334.0	333.5	333.1	332.5	331.4	329.8	328.3	326.7	325.1	323.7
60°	309.4	309.2	309.2	309.0	308.8	307.8	306.0	304.2	302.4	300.5	299.2
62.5°	287.0	286.6	286.2	285.9	285.4	284.4	282.5	280.7	278.8	277.1	275.7
65°	252.1	251.3	250.6	249.8	249.1	247.9	246.4	244.9	243.3	241.8	240.6
67.5°	215.0	214.4	213.7	213.0	212.3	211.4	210.3	209.1	207.9	206.9	205.8
70°	192.6	191.7	190.8	189.9	189.0	188.1	187.2	186.3	185.3	184.4	183.3
72.5°	169.2	168.4	167.8	167.1	166.5	165.6	164.6	163.5	162.5	161.5	160.5
75°	133.2	132.6	132.0	131.3	130.8	130.3	129.7	129.3	128.9	128.4	127.7
77.5°	101.4	101.0	100.7	100.4	100.0	99.6	99.1	98.5	97.9	97.4	96.9
80°	80.6	80.2	79.7	79.3	78.7	78.4	78.1	77.8	77.5	77.2	77.0
82.5°	60.4	60.3	60.2	60.1	60.0	59.9	59.9	59.8	59.7	59.7	59.4
85°	35.5	35.2	35.0	34.6	34.3	34.2	34.2	34.2	34.2	34.2	33.9
87.5°	14.4	14.4	14.4	14.4	14.5	14.7	15.2	15.5	15.9	16.3	16.3
90°	0.9	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1
92.5°	16.6	16.0	15.4	14.9	14.4	15.1	16.9	18.9	20.9	22.8	24.1
95°	54.3	46.2	38.1	30.0	21.8	18.9	21.0	23.3	25.4	27.6	29.0
97.5°	109.1	105.5	101.8	98.2	94.5	85.6	71.4	57.2	42.9	28.6	30.2
100°	150.4	154.4	158.4	162.3	166.2	152.8	121.9	91.0	60.2	29.3	30.9
102.5°	197.4	200.3	203.1	206.0	208.8	193.4	159.7	126.0	92.3	58.6	53.7
105°	265.2	267.4	269.6	271.8	273.9	266.1	248.3	230.5	212.8	194.9	159.9
107.5°	336.8	338.6	340.3	342.1	343.8	346.1	348.8	351.7	354.5	357.3	331.6
110°	384.5	386.1	387.6	389.2	390.8	392.7	394.8	397.1	399.2	401.4	394.8



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	430.1	431.5	432.9	434.4	435.8	437.6	439.8	441.9	444.1	446.3	446.4
115°	497.6	498.7	499.9	501.1	502.3	503.8	505.5	507.3	509.1	510.9	512.9
117.5°	562.8	564.4	565.8	567.3	568.7	569.9	570.8	571.8	572.7	573.5	575.2
120°	603.4	605.2	607.0	608.8	610.6	611.8	612.3	613.0	613.6	614.1	615.7
122.5°	644.8	646.2	647.6	649.2	650.6	651.8	652.5	653.3	654.0	654.7	655.9
125°	701.3	702.9	704.5	706.1	707.7	708.9	709.7	710.4	711.2	712.0	712.5
127.5°	756.2	757.8	759.4	760.9	762.5	763.8	764.7	765.7	766.6	767.6	768.2
130°	790.4	791.9	793.5	795.1	796.7	797.9	798.7	799.5	800.2	801.0	801.8
132.5°	823.1	824.7	826.3	827.9	829.5	830.5	831.2	831.8	832.5	833.1	833.9
135°	873.2	874.3	875.5	876.7	877.9	878.9	879.7	880.5	881.3	882.1	882.6
137.5°	915.9	917.4	918.9	920.4	921.9	922.8	923.3	923.7	924.2	924.6	925.5
140°	944.3	945.6	946.7	947.9	949.1	950.0	950.6	951.2	951.8	952.3	953.1
142.5°	970.7	971.9	973.0	974.3	975.4	976.3	977.0	977.5	978.1	978.7	979.4
145°	1007.5	1009.0	1010.3	1011.7	1013.1	1014.0	1014.4	1014.8	1015.1	1015.6	1015.9
147.5°	1042.2	1043.2	1044.1	1045.0	1045.9	1046.5	1047.0	1047.3	1047.8	1048.1	1048.6
150°	1063.6	1064.3	1064.8	1065.4	1066.0	1066.5	1066.8	1067.3	1067.6	1068.1	1068.4
152.5°	1082.8	1083.2	1083.4	1083.7	1084.0	1084.2	1084.4	1084.7	1084.9	1085.1	1085.8
155°	1109.9	1109.5	1109.1	1108.8	1108.3	1108.2	1108.4	1108.6	1108.8	1109.0	1110.0
157.5°	1130.9	1130.9	1130.9	1130.8	1130.8	1130.6	1130.4	1130.2	1130.1	1129.8	1131.0
160°	1143.7	1143.5	1143.4	1143.2	1142.9	1142.7	1142.5	1142.4	1142.1	1141.9	1143.2
162.5°	1155.8	1155.3	1154.8	1154.3	1153.8	1153.4	1153.2	1153.0	1152.8	1152.6	1154.0
165°	1170.5	1169.8	1169.2	1168.7	1168.1	1167.7	1167.4	1167.2	1167.1	1166.9	1168.4
167.5°	1181.8	1181.1	1180.3	1179.5	1178.7	1178.2	1178.2	1178.2	1178.2	1178.2	1179.8
170°	1188.2	1187.4	1186.7	1185.9	1185.1	1184.6	1184.6	1184.6	1184.6	1184.6	1186.2
172.5°	1192.5	1191.6	1190.6	1189.6	1188.7	1188.3	1188.5	1188.7	1188.7	1188.9	1190.5
175°	1198.0	1197.0	1196.1	1195.1	1194.1	1193.6	1193.8	1194.1	1194.3	1194.4	1195.9
177.5°	1199.4	1198.6	1197.8	1197.0	1196.3	1196.0	1196.1	1196.3	1196.4	1196.6	1197.8
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	794.4	794.4	794.4	794.4	794.4	794.4	794.4	794.4
2.5°	791.4	792.6	793.8	794.3	794.2	794.1	794.0	793.9
5°	787.2	788.7	790.2	790.9	790.5	790.2	790.0	789.6
7.5°	778.8	780.2	781.6	782.1	781.9	781.8	781.6	781.4
10°	771.2	772.6	773.9	774.5	774.2	773.8	773.6	773.2
12.5°	762.8	763.8	764.8	765.2	765.0	764.8	764.6	764.5
15°	747.7	748.9	750.1	750.2	749.3	748.4	747.5	746.6
17.5°	728.5	729.3	730.2	730.4	730.1	729.8	729.4	729.1
20°	714.3	715.0	715.5	715.6	715.2	714.7	714.3	713.8
22.5°	699.4	699.8	700.3	700.3	699.7	699.1	698.6	697.9
25°	674.5	674.7	674.8	674.7	674.2	673.8	673.2	672.8
27.5°	648.1	648.2	648.3	648.1	647.5	646.9	646.3	645.8
30°	629.8	629.8	629.8	629.3	628.2	627.1	626.1	625.0
32.5°	610.6	609.8	608.9	608.1	607.6	607.1	606.5	605.9
35°	579.4	578.5	577.7	576.8	576.0	575.3	574.5	573.8
37.5°	547.2	546.2	545.1	544.3	543.9	543.3	542.9	542.3
40°	526.3	525.0	523.9	522.9	522.3	521.7	521.1	520.5
42.5°	504.4	503.2	501.9	501.1	500.4	499.9	499.3	498.6
45°	471.8	469.9	468.1	466.8	466.1	465.3	464.6	463.8
47.5°	437.4	435.6	433.8	432.6	431.9	431.2	430.6	429.9
50°	414.7	413.0	411.3	410.1	409.1	408.2	407.3	406.4
52.5°	391.7	390.3	388.9	387.6	386.7	385.8	385.0	384.1
55°	356.6	355.0	353.3	352.0	351.3	350.5	349.8	349.0
57.5°	322.2	320.7	319.2	318.0	317.1	316.3	315.4	314.5
60°	297.8	296.5	295.1	294.0	293.3	292.5	291.8	291.0
62.5°	274.3	273.0	271.6	270.6	270.1	269.7	269.1	268.6
65°	239.3	238.2	236.9	236.1	235.7	235.2	234.8	234.3
67.5°	204.7	203.7	202.6	201.7	201.1	200.5	199.8	199.2
70°	182.3	181.3	180.2	179.2	178.5	177.7	177.0	176.2
72.5°	159.6	158.6	157.7	157.0	156.7	156.2	155.9	155.4
75°	126.9	126.2	125.4	124.8	124.3	123.9	123.4	123.0
77.5°	96.4	95.9	95.3	95.1	95.1	95.1	95.1	95.1
80°	76.9	76.7	76.6	76.5	76.5	76.5	76.5	76.5
82.5°	59.1	58.9	58.6	58.4	58.3	58.1	58.1	58.0
85°	33.5	33.3	32.9	32.8	32.8	32.8	32.8	32.8
87.5°	16.4	16.4	16.4	16.5	16.6	16.7	16.8	16.9
90°	22.9	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	25.3	26.6	27.8	28.6	28.8	29.1	29.3	29.5
95°	30.3	31.7	33.2	33.8	33.8	33.8	33.8	33.8
97.5°	31.8	33.4	35.0	35.8	36.1	36.3	36.5	36.6
100°	32.5	34.2	35.7	36.6	36.8	37.0	37.2	37.4
102.5°	48.8	43.9	39.0	36.6	37.0	37.4	37.7	38.1
105°	124.9	89.9	54.9	37.5	38.0	38.3	38.8	39.1
107.5°	305.9	280.3	254.6	228.5	202.2	175.8	149.4	123.0
110°	388.3	381.8	375.3	357.9	329.6	301.3	273.0	244.8



TEST NUMBER: P331943-940

CATALOG NUMBER: S123DIP-S560D1025U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	446.5	446.7	446.7	443.8	437.8	431.9	425.9	419.9
115°	514.9	516.8	518.8	520.2	520.9	521.7	522.5	523.3
117.5°	576.8	578.3	579.9	580.8	580.9	581.0	581.2	581.4
120°	617.3	618.8	620.5	621.3	621.3	621.3	621.3	621.3
122.5°	656.9	658.1	659.2	659.8	660.0	660.1	660.2	660.4
125°	712.8	713.2	713.6	714.0	714.4	714.8	715.2	715.6
127.5°	768.8	769.5	770.1	770.3	769.8	769.5	769.0	768.7
130°	802.6	803.4	804.2	804.4	804.1	803.6	803.3	802.8
132.5°	834.6	835.4	836.2	836.3	835.8	835.3	834.7	834.2
135°	883.2	883.9	884.4	884.4	883.9	883.2	882.6	882.1
137.5°	926.5	927.5	928.4	928.6	928.3	927.9	927.5	927.1
140°	954.0	954.8	955.6	955.7	955.3	954.9	954.6	954.1
142.5°	980.0	980.6	981.2	981.2	980.7	980.2	979.6	979.1
145°	1016.4	1016.7	1017.2	1017.4	1017.4	1017.4	1017.4	1017.4
147.5°	1048.9	1049.3	1049.7	1049.5	1048.6	1047.7	1046.7	1045.8
150°	1068.9	1069.3	1069.7	1069.5	1069.0	1068.4	1067.7	1067.2
152.5°	1086.5	1087.3	1088.0	1087.9	1087.0	1086.1	1085.2	1084.2
155°	1111.0	1112.0	1112.9	1112.9	1111.7	1110.5	1109.3	1108.1
157.5°	1132.2	1133.4	1134.6	1134.4	1132.8	1131.3	1129.8	1128.3
160°	1144.3	1145.5	1146.7	1146.6	1145.2	1143.8	1142.5	1141.0
162.5°	1155.3	1156.6	1158.0	1158.1	1156.8	1155.6	1154.4	1153.2
165°	1170.0	1171.6	1173.2	1173.3	1171.9	1170.5	1169.1	1167.8
167.5°	1181.4	1183.0	1184.5	1184.5	1183.0	1181.4	1179.8	1178.2
170°	1187.8	1189.5	1191.0	1191.0	1189.5	1187.8	1186.2	1184.6
172.5°	1192.1	1193.6	1195.2	1195.2	1193.5	1191.7	1190.0	1188.2
175°	1197.2	1198.6	1200.0	1199.9	1198.3	1196.8	1195.2	1193.6
177.5°	1199.1	1200.4	1201.7	1201.5	1199.9	1198.4	1196.8	1195.2
180°	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0	1198.0

(END OF REPORT)