

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331984-935

Luminaire Tested: **S123DIP-S775D1025U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331984-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6005.4 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	47	46	45				40	
2	89	82	76	71	81	75	70	66	63	59	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29				25	
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	24	22				19	
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.5
10°-20°	293.9	4.9
20°-30°	493.2	8.2
30°-40°	558.5	9.3
40°-50°	500.8	8.3
50°-60°	404.1	6.7
60°-70°	281.6	4.7
70°-80°	148.0	2.5
80°-90°	39.5	0.7
90°-100°	236.3	3.9
100°-110°	669.0	11.1
110°-120°	658.1	11.0
120°-130°	525.0	8.7
130°-140°	413.9	6.9
140°-150°	308.9	5.1
150°-160°	215.3	3.6
160°-170°	126.5	2.1
170°-180°	41.2	0.7
0°-30°	878.7	14.6
0°-40°	1437.2	23.9
0°-60°	2342.1	39.0
0°-90°	2811.3	46.8
90°-120°	1563.5	26.0
90°-150°	2811.2	46.8
90°-180°	3194.0	53.2
0°-180°	6005.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	25	2	25	2	25	15
95°	100	29	100	29	100	180
105°	1093	100	1093	100	1093	1078
115°	1330	176	1330	176	1330	1292
125°	1048	245	1048	245	1048	950
135°	850	287	850	287	850	659
145°	664	327	664	327	664	423
155°	551	372	551	372	551	257
165°	480	406	480	406	480	137
175°	432	424	432	424	432	42
180°	425	425	425	425	425	



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	15.8	15.2	15.4	15.7	15.4	15.5	15.7	15.8	16.0	16.5	16.4
90°	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5	20.7	21.5	18.9
92.5°	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3	99.7	132.2	145.4
95°	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4	413.4	509.6	453.7
97.5°	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3	845.0	789.8	578.2
100°	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3	983.2	813.9	550.0
102.5°	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7	990.1	769.2	508.8
105°	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2	937.6	691.0	458.1
107.5°	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6	845.8	621.9	425.8
110°	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9	788.1	582.7	413.4



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9	737.9	556.6	406.5
115°	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2	677.3	528.6	403.9
117.5°	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9	640.6	512.0	405.4
120°	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5	621.4	504.5	408.2
122.5°	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1	605.5	499.6	413.0
125°	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3	585.3	493.4	420.3
127.5°	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7	567.4	490.3	428.5
130°	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2	557.8	488.2	434.0
132.5°	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9	548.8	487.5	438.2
135°	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7	537.2	486.5	444.4
137.5°	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6	527.0	484.6	448.4
140°	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2	520.8	483.9	451.2
142.5°	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5	515.3	482.5	453.2
145°	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5	507.9	480.4	454.6
147.5°	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9	500.7	477.2	454.6
150°	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7	495.8	474.4	454.6
152.5°	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1	490.4	471.0	452.5
155°	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7	482.2	464.9	450.3
157.5°	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7	472.9	459.6	447.5
160°	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9	466.7	455.5	446.1
162.5°	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6	460.5	451.3	443.3
165°	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9	452.0	445.2	439.2
167.5°	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6	444.0	439.0	435.1
170°	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5	439.2	434.9	432.3
172.5°	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0	434.4	431.4	430.2
175°	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6	428.9	427.1	427.1
177.5°	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	16.6	16.4	14.9	13.1	12.0	10.4	10.1	9.0	8.6	9.0	9.1
90°	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7	3.4	5.2	7.7
92.5°	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7	15.8	23.1	29.7
95°	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2	31.8	41.2	55.9
97.5°	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9	50.7	58.1	70.8
100°	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6	64.5	70.5	82.5
102.5°	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0	79.6	84.9	96.3
105°	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7	102.3	107.5	117.8
107.5°	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7	125.3	130.3	140.4
110°	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2	141.8	146.1	155.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4	157.0	161.3	170.7
115°	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2	179.6	184.8	193.4
117.5°	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0	202.0	206.3	214.1
120°	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1	215.7	220.0	228.6
122.5°	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2	228.8	233.1	242.4
125°	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0	246.7	251.8	261.2
127.5°	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2	261.7	268.1	277.8
130°	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1	270.7	278.4	288.8
132.5°	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0	278.3	286.7	299.1
135°	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1	290.5	300.0	312.8
137.5°	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4	302.0	311.3	325.0
140°	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0	310.2	318.8	332.6
142.5°	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2	317.8	327.1	339.5
145°	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4	330.0	337.8	350.7
147.5°	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9	342.4	350.0	361.1
150°	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8	350.7	357.5	368.7
152.5°	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7	358.9	365.8	375.6
155°	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1	372.1	377.3	385.9
157.5°	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8	383.5	387.6	395.2
160°	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1	391.1	394.5	401.3
162.5°	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3	397.3	400.0	405.4
165°	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5	405.6	407.3	411.6
167.5°	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5	412.5	413.4	416.6
170°	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7	415.9	416.8	419.4
172.5°	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4	419.4	419.6	421.5
175°	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7	422.8	422.0	423.7
177.5°	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2	424.6	423.9	424.6
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	9.1	9.8	10.0	10.8	11.0	11.9	11.7	11.1	11.3	12.6	11.5
90°	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5	22.4	23.2	24.9
92.5°	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3	57.4	50.7	46.2
95°	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4	209.7	164.2	133.2
97.5°	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3	617.8	506.9	404.1
100°	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3	943.7	843.1	721.1
102.5°	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7	1091.5	1032.9	955.5
105°	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2	1203.2	1219.5	1197.2
107.5°	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6	1189.1	1264.4	1295.0
110°	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9	1143.1	1251.3	1311.5



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9	1082.5	1203.9	1281.3
115°	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2	985.8	1112.1	1205.7
117.5°	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9	904.0	1017.4	1112.4
120°	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5	858.6	961.7	1048.5
122.5°	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1	822.2	917.7	998.3
125°	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3	777.0	859.5	928.2
127.5°	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7	737.2	811.7	874.2
130°	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2	712.5	782.0	840.5
132.5°	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9	689.1	753.9	809.6
135°	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7	655.7	711.6	760.6
137.5°	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6	623.6	671.8	714.2
140°	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2	605.0	646.3	683.3
142.5°	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5	587.2	622.9	655.0
145°	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5	563.8	591.2	616.2
147.5°	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9	546.4	568.6	586.3
150°	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7	535.5	553.5	569.8
152.5°	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1	525.1	541.1	554.7
155°	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7	510.5	523.4	533.7
157.5°	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7	496.2	506.2	514.3
160°	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9	487.3	495.8	501.9
162.5°	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6	477.7	485.6	490.9
165°	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9	464.1	470.1	474.4
167.5°	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6	453.6	457.0	460.1
170°	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5	446.1	449.4	451.2
172.5°	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0	439.9	442.6	443.7
175°	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6	431.4	433.2	433.2
177.5°	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9	426.6	427.3	427.3
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	11.3	11.5	11.3	10.8	11.3	11.5	11.3	11.5	12.6	11.3	11.1
90°	24.0	24.9	25.7	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5
92.5°	44.7	42.1	43.0	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3
95°	116.9	109.2	103.1	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4
97.5°	340.7	302.0	278.8	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3
100°	634.3	571.5	538.0	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3
102.5°	887.9	838.3	810.3	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7
105°	1157.6	1125.0	1097.5	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2
107.5°	1295.7	1284.7	1275.4	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6
110°	1335.6	1342.5	1340.7	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1325.3	1346.5	1353.1	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9
115°	1270.2	1308.0	1325.3	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2
117.5°	1179.7	1223.0	1247.8	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9
120°	1116.4	1164.5	1185.2	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5
122.5°	1058.7	1102.0	1124.6	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1
125°	983.2	1021.0	1042.5	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3
127.5°	923.2	955.5	974.9	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7
130°	886.1	917.1	935.0	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2
132.5°	852.4	883.3	899.3	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9
135°	802.7	828.5	844.0	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7
137.5°	749.6	775.8	788.8	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6
140°	715.9	739.9	753.7	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2
142.5°	682.9	704.2	716.6	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5
145°	637.7	655.7	662.6	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5
147.5°	602.6	614.8	621.4	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9
150°	582.7	592.1	597.3	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7
152.5°	564.8	573.6	576.7	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1
155°	541.5	548.3	550.0	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7
157.5°	521.0	526.2	527.5	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7
160°	507.9	513.1	513.1	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9
162.5°	494.9	499.3	499.3	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6
165°	477.9	481.3	480.4	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9
167.5°	461.7	464.1	463.2	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6
170°	452.0	453.7	452.9	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5
172.5°	443.8	445.6	444.0	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0
175°	433.2	434.0	433.2	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6
177.5°	426.6	427.3	425.9	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	11.7	11.9	11.0	10.8	10.0	9.8	9.1	9.1	9.0	8.6	9.0
90°	20.7	21.5	18.9	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7
92.5°	99.7	132.2	145.4	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7
95°	413.4	509.6	453.7	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2
97.5°	845.0	789.8	578.2	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9
100°	983.2	813.9	550.0	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6
102.5°	990.1	769.2	508.8	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0
105°	937.6	691.0	458.1	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7
107.5°	845.8	621.9	425.8	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7
110°	788.1	582.7	413.4	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	737.9	556.6	406.5	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4
115°	677.3	528.6	403.9	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2
117.5°	640.6	512.0	405.4	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0
120°	621.4	504.5	408.2	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1
122.5°	605.5	499.6	413.0	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2
125°	585.3	493.4	420.3	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0
127.5°	567.4	490.3	428.5	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2
130°	557.8	488.2	434.0	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1
132.5°	548.8	487.5	438.2	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0
135°	537.2	486.5	444.4	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1
137.5°	527.0	484.6	448.4	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4
140°	520.8	483.9	451.2	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0
142.5°	515.3	482.5	453.2	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2
145°	507.9	480.4	454.6	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4
147.5°	500.7	477.2	454.6	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9
150°	495.8	474.4	454.6	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8
152.5°	490.4	471.0	452.5	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7
155°	482.2	464.9	450.3	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1
157.5°	472.9	459.6	447.5	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8
160°	466.7	455.5	446.1	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1
162.5°	460.5	451.3	443.3	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3
165°	452.0	445.2	439.2	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5
167.5°	444.0	439.0	435.1	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5
170°	439.2	434.9	432.3	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7
172.5°	434.4	431.4	430.2	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4
175°	428.9	427.1	427.1	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7
177.5°	425.2	424.6	425.2	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	10.1	10.4	12.0	13.1	14.9	16.4	16.6	16.4	16.5	16.0	15.8
90°	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5
92.5°	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3
95°	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4
97.5°	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3
100°	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3
102.5°	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7
105°	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2
107.5°	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6
110°	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9
115°	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2
117.5°	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9
120°	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5
122.5°	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1
125°	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3
127.5°	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7
130°	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2
132.5°	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9
135°	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7
137.5°	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6
140°	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2
142.5°	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5
145°	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5
147.5°	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9
150°	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7
152.5°	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1
155°	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7
157.5°	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7
160°	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9
162.5°	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6
165°	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9
167.5°	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6
170°	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5
172.5°	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0
175°	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6
177.5°	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	15.7	15.5	15.4	15.7	15.4	15.2	15.8
90°	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P331984-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)