

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331946-940

Luminaire Tested: **S123DIP-S560D1195U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331946-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1195U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6383.8 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	64	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7587	7587	7587	7587
5°	9048	7621	6753	7621
10°	11326	7582	6099	7582
15°	13891	7520	5678	7520
20°	16549	7425	5407	7425
25°	17570	7310	5346	7310
30°	15060	7225	5374	7225
35°	10474	7104	5430	7104
40°	7888	6962	5413	6962
45°	6550	6753	5345	6753
50°	5868	6325	5297	6325
55°	5485	5864	5230	5864
60°	5147	5382	5175	5382
65°	4834	4905	5010	4905
70°	4535	4365	4771	4365
75°	4059	3818	4375	3818
80°	3552	3137	3769	3137
85°	2791	2285	2532	2285



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	1.1
10°-20°	222.7	3.5
20°-30°	373.7	5.9
30°-40°	423.1	6.6
40°-50°	379.5	5.9
50°-60°	306.2	4.8
60°-70°	213.4	3.3
70°-80°	112.2	1.8
80°-90°	31.3	0.5
90°-100°	50.7	0.8
100°-110°	241.6	3.8
110°-120°	580.4	9.1
120°-130°	739.1	11.6
130°-140°	789.7	12.4
140°-150°	738.4	11.6
150°-160°	595.6	9.3
160°-170°	384.4	6.0
170°-180°	132.5	2.1
0°-30°	665.8	10.4
0°-40°	1088.9	17.1
0°-60°	1774.6	27.8
0°-90°	2131.4	33.4
90°-120°	872.7	13.7
90°-150°	3139.9	49.2
90°-180°	4252.0	66.6
0°-180°	6383.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	705	705	705	705	705	
5°	837	705	625	705	837	87
15°	1246	675	510	675	1246	360
25°	1479	616	450	616	1479	649
35°	797	541	413	541	797	518
45°	430	444	351	444	430	340
55°	292	312	279	312	292	262
65°	190	193	197	193	190	189
75°	98	92	105	92	98	105
85°	23	18	20	18	23	27
90°	31	1	31	1	31	15
95°	39	63	39	63	39	33
105°	46	309	46	309	46	104
115°	609	579	609	579	609	563
125°	833	816	833	816	833	744
135°	1027	1016	1027	1016	1027	792
145°	1184	1173	1184	1173	1184	739
155°	1290	1292	1290	1292	1290	595
165°	1359	1362	1359	1362	1359	384
175°	1389	1394	1389	1394	1389	132
180°	1394	1394	1394	1394	1394	



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	748.1	747.5	746.2	747.3	745.0	742.1	741.8	739.0	731.1	730.6	728.4
5°	837.4	834.6	834.4	834.0	829.2	822.7	810.4	809.4	793.0	784.8	774.9
7.5°	953.1	954.6	949.6	945.2	930.6	921.0	907.8	890.9	870.8	850.3	836.7
10°	1036.2	1047.4	1033.4	1023.9	1015.0	998.3	978.8	954.6	930.3	902.0	880.5
12.5°	1125.2	1130.8	1128.0	1118.9	1105.2	1079.7	1045.2	1018.5	996.1	949.0	929.9
15°	1246.5	1267.4	1254.1	1223.3	1224.1	1199.8	1154.7	1105.2	1078.9	1037.5	981.1
17.5°	1375.8	1378.4	1372.7	1347.1	1330.0	1296.7	1255.1	1207.6	1154.3	1104.4	1044.6
20°	1444.7	1442.6	1430.7	1417.3	1387.9	1362.0	1316.5	1263.6	1195.3	1146.1	1080.9
22.5°	1482.9	1479.4	1473.8	1462.7	1438.2	1410.3	1369.6	1311.7	1246.7	1178.9	1103.6
25°	1479.4	1483.9	1484.6	1481.5	1473.0	1456.3	1424.2	1378.0	1313.1	1226.1	1147.5
27.5°	1345.6	1351.8	1370.1	1386.3	1404.4	1422.8	1420.4	1397.5	1349.5	1274.3	1178.2
30°	1211.7	1198.0	1231.9	1274.5	1303.6	1354.8	1383.5	1385.2	1358.3	1293.7	1200.1
32.5°	1025.9	1041.0	1055.9	1108.4	1171.9	1229.4	1286.5	1332.5	1337.7	1294.8	1212.9
35°	797.1	815.9	843.2	870.6	938.9	997.6	1098.0	1185.4	1255.1	1264.3	1214.1
37.5°	642.3	651.7	668.9	696.2	740.9	810.7	888.3	998.8	1099.7	1174.8	1178.1
40°	561.4	564.2	583.6	604.5	640.7	698.0	768.1	865.8	986.7	1091.5	1135.2
42.5°	500.8	506.8	515.1	535.1	563.9	607.1	672.2	753.0	863.7	984.4	1069.9
45°	430.3	437.1	442.3	455.6	476.1	505.1	550.5	624.3	708.6	833.3	948.4
47.5°	383.7	384.2	388.1	398.1	412.1	433.9	466.0	513.4	590.8	691.9	810.1
50°	350.4	355.9	357.2	365.1	376.0	392.1	418.7	459.0	522.5	611.4	720.0
52.5°	326.9	328.5	332.3	338.0	347.6	360.1	383.2	414.7	464.6	540.3	640.2
55°	292.3	292.3	296.1	300.5	306.0	317.3	332.6	355.9	393.8	452.5	535.2
57.5°	260.4	262.1	264.7	266.1	270.7	278.2	291.1	308.7	337.0	382.2	447.9
60°	239.1	242.1	241.8	244.5	248.6	254.4	265.4	279.7	305.0	341.2	396.5
62.5°	220.5	220.3	220.3	223.5	227.6	233.1	240.2	252.6	274.1	306.2	353.3
65°	189.8	189.2	191.6	193.7	195.0	199.1	204.6	215.5	229.9	253.8	290.3
67.5°	162.7	160.7	162.0	162.7	165.1	168.3	173.3	180.1	191.5	210.7	238.3
70°	144.1	142.4	142.0	142.8	144.8	147.2	151.0	157.5	168.0	183.4	203.6
72.5°	125.0	123.9	123.8	125.3	126.3	127.8	130.5	136.4	144.8	156.3	175.1
75°	97.6	97.6	97.6	98.0	99.1	100.4	102.5	105.5	112.0	120.2	132.9
77.5°	73.2	73.1	72.8	72.7	74.2	74.8	75.3	78.1	81.8	87.3	96.5
80°	57.3	55.6	56.4	57.3	58.1	58.4	59.4	60.1	63.2	66.3	72.8
82.5°	42.6	41.2	41.3	42.9	43.1	43.3	44.4	45.4	46.5	49.3	52.8
85°	22.6	22.6	22.9	22.9	23.2	22.9	23.9	24.3	24.3	25.9	28.0
87.5°	14.4	13.7	13.9	14.2	13.7	13.9	14.0	14.1	14.2	14.3	13.9
90°	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7	25.8	24.9	21.8
92.5°	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4	28.0	26.5	24.3
95°	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3	33.7	32.1	29.6
97.5°	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0	35.2	33.3	49.9
100°	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9	36.0	34.2	70.1
102.5°	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7	62.4	68.1	107.4
105°	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3	186.1	226.9	247.6
107.5°	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1	385.9	415.9	412.6
110°	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0	459.7	467.3	464.7



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7	519.6	519.4	516.9
115°	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2	597.0	594.7	592.6
117.5°	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3	669.4	667.6	666.6
120°	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5	716.7	714.8	714.2
122.5°	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6	763.4	762.1	761.2
125°	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7	829.3	828.8	827.9
127.5°	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9	894.2	893.4	892.3
130°	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2	933.4	932.4	931.5
132.5°	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5	970.6	969.7	968.9
135°	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7	1025.7
137.5°	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4	1077.3	1076.2	1075.7
140°	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4	1109.5	1108.5	1107.9
142.5°	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7	1140.0	1139.2	1138.5
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0	1182.5	1182.1	1181.6
147.5°	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9	1220.5	1219.9	1219.5
150°	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1	1243.7	1243.2	1242.8
152.5°	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7	1263.9	1263.1	1262.8
155°	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2	1292.0	1290.8	1290.7
157.5°	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9	1316.5	1315.1	1315.4
160°	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9	1330.6	1329.2	1329.5
162.5°	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8	1343.2	1341.6	1341.8
165°	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9	1360.0	1358.2	1358.4
167.5°	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5	1371.5
170°	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9	1378.9
172.5°	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6	1385.7	1383.8	1383.7
175°	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6	1392.0	1390.3	1390.1
177.5°	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7	1394.3	1392.8	1392.6
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	726.7	724.6	722.4	718.5	715.2	710.6	709.3	707.7	702.8	698.3	695.1
5°	771.2	762.9	751.0	740.0	731.2	719.3	712.4	705.3	695.0	685.8	678.2
7.5°	817.6	801.5	782.9	762.9	744.1	726.0	711.5	698.6	684.2	670.6	660.0
10°	854.5	831.3	805.3	777.3	753.4	730.1	710.7	693.7	675.2	659.2	645.8
12.5°	896.5	862.1	826.3	792.3	764.0	731.8	708.3	686.5	665.7	646.3	631.3
15°	946.4	902.7	860.3	813.5	770.4	730.1	702.1	674.8	650.6	630.8	611.6
17.5°	991.7	942.2	886.4	829.5	777.6	729.8	690.5	659.7	629.4	605.1	586.0
20°	1017.4	961.0	897.9	838.7	781.4	728.1	685.1	648.2	615.5	589.8	568.3
22.5°	1039.6	973.6	908.2	845.1	781.1	723.7	675.0	637.0	601.5	576.4	553.6
25°	1062.5	983.6	918.0	843.9	772.5	713.1	658.4	615.5	579.9	550.5	527.0
27.5°	1082.2	982.9	905.1	825.4	759.0	699.5	641.1	594.9	557.2	525.3	501.4
30°	1095.3	984.3	891.7	812.8	745.9	684.4	627.7	581.3	541.6	509.2	486.7
32.5°	1103.5	983.5	879.4	795.3	725.1	670.7	613.2	565.2	524.4	492.6	470.8
35°	1108.2	977.4	858.3	759.2	691.6	638.6	590.5	540.6	497.9	468.2	443.6
37.5°	1098.7	964.8	833.7	724.3	650.3	598.2	557.7	515.2	474.4	441.7	420.4
40°	1083.6	956.6	814.5	699.8	621.9	571.7	537.3	495.5	455.2	424.2	404.4
42.5°	1055.0	940.0	793.5	672.4	592.4	542.2	510.4	475.6	437.5	408.3	388.5
45°	985.0	903.7	762.0	631.5	548.8	497.0	469.0	443.6	409.1	380.8	363.7
47.5°	887.8	849.1	716.3	588.3	503.4	453.4	424.3	403.9	378.7	355.9	339.5
50°	820.4	804.3	685.5	558.7	473.0	424.2	396.2	377.7	359.6	336.7	321.7
52.5°	742.4	752.3	649.3	528.2	442.1	394.1	367.7	353.1	336.7	317.9	304.8
55°	632.8	668.7	587.1	476.8	396.2	350.4	325.5	312.5	302.9	288.9	277.7
57.5°	530.2	575.8	519.7	423.8	351.0	311.6	287.7	273.5	267.3	260.0	251.2
60°	469.2	514.3	471.6	388.3	320.7	283.1	262.0	250.0	243.9	238.7	231.2
62.5°	414.9	460.5	424.6	352.2	290.9	256.1	237.6	226.0	221.1	218.5	212.0
65°	340.2	379.4	355.5	296.1	248.3	217.6	200.8	192.6	188.2	187.2	183.1
67.5°	276.9	306.7	289.4	245.6	207.9	181.4	167.2	160.2	156.9	156.5	153.4
70°	235.3	263.3	250.0	210.4	177.9	157.1	144.8	138.7	136.6	136.3	134.6
72.5°	203.0	222.6	212.0	179.0	153.9	135.0	125.9	119.5	117.2	117.7	116.5
75°	150.3	165.0	158.8	135.9	115.7	103.4	95.9	91.8	89.8	90.9	89.4
77.5°	108.2	117.4	111.9	96.0	83.6	74.7	69.2	66.7	64.8	64.7	64.1
80°	81.6	87.1	84.0	74.5	64.2	56.7	52.3	50.6	49.5	49.2	48.9
82.5°	58.1	62.8	59.1	52.6	45.7	41.1	38.6	36.4	35.6	35.8	35.5
85°	29.3	31.1	29.7	25.6	22.9	20.9	19.4	18.5	17.7	18.1	17.4
87.5°	13.9	13.6	12.1	10.5	9.5	8.2	7.8	6.8	6.7	7.1	7.3
90°	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1	3.3	5.6	7.9
92.5°	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3	18.6	18.0	17.3
95°	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2	53.8	44.3	34.9
97.5°	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0	122.8	118.5	114.3
100°	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0	179.7	184.3	188.9
102.5°	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8	233.1	236.4	239.7
105°	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7	311.3	313.8	316.3
107.5°	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0	394.0	396.1	398.1
110°	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5	449.4	451.2	453.1



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6	502.2	503.9	505.6
115°	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2	580.5	581.8	583.3
117.5°	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1	656.8	658.5	660.3
120°	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4	704.5	706.6	708.6
122.5°	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5	752.2	753.9	755.5
125°	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4	818.2	820.0	821.9
127.5°	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2	882.0	883.9	885.7
130°	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0	921.9	923.6	925.5
132.5°	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1	959.9	961.8	963.6
135°	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3	1017.7	1019.0	1020.5
137.5°	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0	1067.8	1069.5	1071.3
140°	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2	1100.5	1102.0	1103.3
142.5°	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9	1131.2	1132.7	1134.0
145°	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8	1174.4	1176.0	1177.6
147.5°	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2	1214.2	1215.3	1216.3
150°	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1	1238.7	1239.4	1240.1
152.5°	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4	1260.7	1261.1	1261.3
155°	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9	1291.5	1290.9	1290.5
157.5°	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3	1316.3	1316.3	1316.2
160°	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2	1331.1	1330.8	1330.6
162.5°	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3	1344.8	1344.2	1343.5
165°	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4	1361.6	1360.9	1360.3
167.5°	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6	1374.7	1373.8	1372.9
170°	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0	1382.2	1381.3	1380.3
172.5°	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0	1387.0	1385.8	1384.7
175°	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5	1393.3	1392.1	1391.0
177.5°	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2	1395.2	1394.3	1393.4
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	693.1	691.3	688.5	684.4	681.1	675.9	675.9	676.7	676.7	676.5	675.9
5°	672.1	667.0	660.8	653.7	646.1	638.6	637.3	634.5	632.5	631.2	629.5
7.5°	649.9	640.9	631.9	621.9	612.7	605.1	599.9	595.5	592.6	589.7	587.5
10°	634.9	623.6	613.1	602.4	590.8	581.6	575.8	571.7	568.6	565.9	564.5
12.5°	617.2	604.2	592.5	582.5	569.8	560.3	554.7	552.9	549.2	543.5	540.5
15°	591.2	579.3	565.3	549.8	543.7	532.1	525.6	522.5	520.5	516.0	514.7
17.5°	569.0	553.3	537.6	526.1	514.7	505.3	501.7	497.8	495.2	491.5	490.4
20°	551.3	537.3	522.9	510.6	498.6	488.4	485.3	482.6	479.8	478.1	476.8
22.5°	533.2	519.2	507.3	495.8	483.0	476.4	473.0	470.0	468.1	466.9	465.6
25°	507.8	495.5	482.2	472.0	461.7	457.3	455.2	453.5	452.2	450.5	450.1
27.5°	485.2	471.8	461.0	451.4	444.1	440.3	438.4	437.6	437.8	438.5	438.8
30°	468.2	455.9	447.0	438.8	432.0	428.6	428.3	428.3	429.6	430.0	430.7
32.5°	452.6	442.6	433.6	425.7	420.5	418.2	419.5	419.5	420.6	421.5	422.8
35°	430.0	421.1	414.3	407.4	403.0	404.0	404.7	405.4	407.1	409.1	410.5
37.5°	408.3	400.6	393.5	388.2	386.1	388.0	389.6	391.0	393.1	394.6	395.9
40°	392.7	386.9	380.1	375.3	376.0	377.0	378.4	380.1	381.8	382.8	384.2
42.5°	378.3	372.2	367.0	363.0	364.0	365.3	366.1	367.0	369.0	370.9	371.7
45°	356.2	351.4	346.6	344.3	344.9	345.6	346.3	347.3	349.0	350.4	350.7
47.5°	331.4	328.1	324.9	322.5	323.6	323.3	324.2	326.5	327.0	327.8	329.7
50°	315.6	312.5	308.7	308.1	308.1	308.1	308.4	311.1	311.1	312.5	313.9
52.5°	298.1	296.1	293.7	292.5	291.9	291.9	293.4	294.7	295.2	297.2	298.5
55°	272.2	270.1	268.1	267.1	266.4	267.1	269.8	270.5	272.2	273.2	274.2
57.5°	245.2	243.6	242.0	241.5	241.3	242.2	243.7	245.8	246.2	249.3	250.8
60°	227.5	225.1	223.7	223.7	223.0	226.0	225.4	228.8	229.5	231.6	234.0
62.5°	209.1	205.9	205.4	205.4	206.3	207.2	208.2	209.7	211.5	214.1	215.9
65°	179.7	177.9	180.3	179.9	179.3	181.4	181.4	183.1	185.1	187.5	191.3
67.5°	151.7	150.8	151.1	151.1	152.0	153.2	154.2	155.7	158.1	160.7	163.1
70°	132.9	133.8	132.2	133.6	134.6	134.9	135.5	137.6	140.4	142.0	144.8
72.5°	114.6	114.5	114.7	115.2	116.3	116.9	117.5	119.8	122.9	124.3	126.5
75°	88.1	87.7	88.8	88.8	90.5	91.2	91.8	92.9	95.6	97.6	99.4
77.5°	64.4	64.7	64.6	65.7	65.3	65.4	67.5	68.5	68.8	72.9	73.7
80°	48.5	49.2	49.5	49.8	50.2	49.5	51.9	53.0	53.0	55.3	57.1
82.5°	34.9	35.2	36.1	36.5	36.6	37.2	37.5	38.2	39.0	40.0	42.3
85°	17.4	18.5	18.8	18.5	18.8	18.1	19.1	19.4	19.8	19.8	19.8
87.5°	7.5	8.3	8.6	9.5	9.8	10.7	10.9	10.5	10.7	11.7	10.8
90°	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7	27.6	28.5	29.2
92.5°	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4	30.9	32.5	33.3
95°	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3	36.9	38.5	39.3
97.5°	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0	38.9	40.8	41.7
100°	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9	39.7	41.6	42.6
102.5°	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7	51.0	45.3	42.7
105°	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3	104.6	63.8	43.8
107.5°	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1	326.2	296.3	266.0
110°	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0	444.4	436.8	416.6



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7	519.9	520.0	516.6
115°	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2	601.5	603.9	605.5
117.5°	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3	673.2	674.9	676.0
120°	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5	720.3	722.2	723.1
122.5°	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6	766.0	767.2	767.9
125°	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7	830.2	830.6	831.1
127.5°	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9	895.6	896.3	896.5
130°	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2	935.1	936.1	936.3
132.5°	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5	972.5	973.4	973.5
135°	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5
137.5°	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4	1079.5	1080.6	1080.9
140°	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4	1111.3	1112.2	1112.4
142.5°	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7	1141.4	1142.1	1142.2
145°	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0	1183.5	1183.9	1184.1
147.5°	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9	1221.4	1221.8	1221.6
150°	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1	1244.6	1245.0	1244.9
152.5°	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7	1265.6	1266.4	1266.3
155°	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2	1294.3	1295.5	1295.3
157.5°	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9	1319.2	1320.6	1320.4
160°	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9	1333.3	1334.7	1334.6
162.5°	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8	1346.3	1347.9	1347.9
165°	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9	1363.7	1365.6	1365.7
167.5°	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9
170°	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3
172.5°	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6	1389.4	1391.2	1391.2
175°	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6	1395.2	1396.8	1396.6
177.5°	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7	1397.2	1398.6	1398.5
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	674.0	673.8	675.6	674.3	675.6	673.8	674.0	675.9	676.5	676.7	676.7
5°	627.4	628.4	625.0	625.0	625.0	628.4	627.4	629.5	631.2	632.5	634.5
7.5°	585.9	584.3	584.5	582.6	584.5	584.3	585.9	587.5	589.7	592.6	595.5
10°	560.4	558.4	557.7	558.0	557.7	558.4	560.4	564.5	565.9	568.6	571.7
12.5°	539.4	539.0	534.5	534.6	534.5	539.0	539.4	540.5	543.5	549.2	552.9
15°	514.7	508.2	507.5	509.5	507.5	508.2	514.7	514.7	516.0	520.5	522.5
17.5°	489.9	486.4	486.7	485.6	486.7	486.4	489.9	490.4	491.5	495.2	497.8
20°	476.8	474.7	474.4	472.0	474.4	474.7	476.8	476.8	478.1	479.8	482.6
22.5°	464.8	464.0	464.2	461.6	464.2	464.0	464.8	465.6	466.9	468.1	470.0
25°	449.8	451.5	450.1	450.1	450.1	451.5	449.8	450.1	450.5	452.2	453.5
27.5°	439.7	439.6	438.9	438.9	438.9	439.6	439.7	438.8	438.5	437.8	437.6
30°	432.0	431.7	432.4	432.4	432.4	431.7	432.0	430.7	430.0	429.6	428.3
32.5°	424.4	424.8	425.0	425.3	425.0	424.8	424.4	422.8	421.5	420.6	419.5
35°	412.6	412.9	413.9	413.2	413.9	412.9	412.6	410.5	409.1	407.1	405.4
37.5°	396.5	398.1	397.8	398.3	397.8	398.1	396.5	395.9	394.6	393.1	391.0
40°	384.6	385.6	385.2	385.2	385.2	385.6	384.6	384.2	382.8	381.8	380.1
42.5°	372.3	373.0	372.1	371.6	372.1	373.0	372.3	371.7	370.9	369.0	367.0
45°	352.1	351.4	352.5	351.1	352.5	351.4	352.1	350.7	350.4	349.0	347.3
47.5°	329.6	330.3	330.6	331.5	330.6	330.3	329.6	329.7	327.8	327.0	326.5
50°	314.5	316.6	316.6	316.3	316.6	316.6	314.5	313.9	312.5	311.1	311.1
52.5°	299.8	300.8	302.1	302.0	302.1	300.8	299.8	298.5	297.2	295.2	294.7
55°	277.0	277.7	278.3	278.7	278.3	277.7	277.0	274.2	273.2	272.2	270.5
57.5°	253.3	253.1	254.7	255.2	254.7	253.1	253.3	250.8	249.3	246.2	245.8
60°	236.7	236.7	239.4	240.4	239.4	236.7	236.7	234.0	231.6	229.5	228.8
62.5°	218.9	220.0	222.7	221.3	222.7	220.0	218.9	215.9	214.1	211.5	209.7
65°	193.0	195.7	195.4	196.7	195.4	195.7	193.0	191.3	187.5	185.1	183.1
67.5°	165.9	167.6	170.0	170.2	170.0	167.6	165.9	163.1	160.7	158.1	155.7
70°	147.6	149.3	150.6	151.6	150.6	149.3	147.6	144.8	142.0	140.4	137.6
72.5°	129.7	130.6	133.9	132.5	133.9	130.6	129.7	126.5	124.3	122.9	119.8
75°	101.7	104.2	106.2	105.2	106.2	104.2	101.7	99.4	97.6	95.6	92.9
77.5°	75.3	77.7	78.6	77.8	78.6	77.7	75.3	73.7	72.9	68.8	68.5
80°	59.4	59.1	61.2	60.8	61.2	59.1	59.4	57.1	55.3	53.0	53.0
82.5°	43.6	43.2	44.2	44.4	44.2	43.2	43.6	42.3	40.0	39.0	38.2
85°	21.1	22.2	20.9	20.5	20.9	22.2	21.1	19.8	19.8	19.8	19.4
87.5°	10.9	11.0	10.8	10.6	10.8	11.0	10.9	10.8	11.7	10.7	10.5
90°	29.7	30.1	30.6	31.1	30.6	30.1	29.7	29.2	28.5	27.6	26.7
92.5°	33.5	33.9	34.2	34.4	34.2	33.9	33.5	33.3	32.5	30.9	29.4
95°	39.3	39.3	39.3	39.3	39.3	39.3	39.3	39.3	38.5	36.9	35.3
97.5°	42.0	42.3	42.4	42.7	42.4	42.3	42.0	41.7	40.8	38.9	37.0
100°	42.8	43.1	43.2	43.5	43.2	43.1	42.8	42.6	41.6	39.7	37.9
102.5°	43.1	43.5	44.0	44.3	44.0	43.5	43.1	42.7	45.3	51.0	56.7
105°	44.2	44.7	45.1	45.6	45.1	44.7	44.2	43.8	63.8	104.6	145.3
107.5°	235.3	204.6	173.9	143.2	173.9	204.6	235.3	266.0	296.3	326.2	356.1
110°	383.7	350.7	317.8	284.9	317.8	350.7	383.7	416.6	436.8	444.4	452.0



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	509.6	502.7	495.7	488.7	495.7	502.7	509.6	516.6	520.0	519.9	519.7
115°	606.4	607.3	608.2	609.1	608.2	607.3	606.4	605.5	603.9	601.5	599.2
117.5°	676.2	676.4	676.5	676.7	676.5	676.4	676.2	676.0	674.9	673.2	671.3
120°	723.1	723.1	723.1	723.1	723.1	723.1	723.1	723.1	722.2	720.3	718.5
122.5°	768.1	768.3	768.6	768.7	768.6	768.3	768.1	767.9	767.2	766.0	764.6
125°	831.5	832.1	832.5	832.9	832.5	832.1	831.5	831.1	830.6	830.2	829.7
127.5°	896.1	895.6	895.2	894.7	895.2	895.6	896.1	896.5	896.3	895.6	894.9
130°	935.9	935.4	935.0	934.5	935.0	935.4	935.9	936.3	936.1	935.1	934.2
132.5°	972.9	972.2	971.6	970.9	971.6	972.2	972.9	973.5	973.4	972.5	971.5
135°	1028.8	1028.1	1027.3	1026.7	1027.3	1028.1	1028.8	1029.5	1029.5	1028.8	1028.1
137.5°	1080.5	1080.0	1079.6	1079.1	1079.6	1080.0	1080.5	1080.9	1080.6	1079.5	1078.4
140°	1112.0	1111.5	1111.1	1110.6	1111.1	1111.5	1112.0	1112.4	1112.2	1111.3	1110.4
142.5°	1141.6	1140.9	1140.2	1139.6	1140.2	1140.9	1141.6	1142.2	1142.1	1141.4	1140.7
145°	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1184.1	1183.9	1183.5	1183.0
147.5°	1220.5	1219.4	1218.3	1217.3	1218.3	1219.4	1220.5	1221.6	1221.8	1221.4	1220.9
150°	1244.2	1243.6	1242.9	1242.2	1242.9	1243.6	1244.2	1244.9	1245.0	1244.6	1244.1
152.5°	1265.2	1264.2	1263.1	1262.0	1263.1	1264.2	1265.2	1266.3	1266.4	1265.6	1264.7
155°	1294.0	1292.6	1291.2	1289.9	1291.2	1292.6	1294.0	1295.3	1295.5	1294.3	1293.2
157.5°	1318.7	1316.8	1315.0	1313.2	1315.0	1316.8	1318.7	1320.4	1320.6	1319.2	1317.9
160°	1333.0	1331.4	1329.7	1328.1	1329.7	1331.4	1333.0	1334.6	1334.7	1333.3	1331.9
162.5°	1346.5	1345.1	1343.6	1342.2	1343.6	1345.1	1346.5	1347.9	1347.9	1346.3	1344.8
165°	1364.1	1362.4	1360.8	1359.2	1360.8	1362.4	1364.1	1365.7	1365.6	1363.7	1361.9
167.5°	1377.0	1375.1	1373.3	1371.5	1373.3	1375.1	1377.0	1378.9	1378.9	1377.0	1375.1
170°	1384.5	1382.6	1380.7	1378.9	1380.7	1382.6	1384.5	1386.3	1386.3	1384.5	1382.6
172.5°	1389.1	1387.1	1385.1	1383.0	1385.1	1387.1	1389.1	1391.2	1391.2	1389.4	1387.6
175°	1394.8	1392.9	1391.2	1389.3	1391.2	1392.9	1394.8	1396.6	1396.8	1395.2	1393.6
177.5°	1396.7	1394.8	1392.9	1391.2	1392.9	1394.8	1396.7	1398.5	1398.6	1397.2	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	675.9	675.9	681.1	684.4	688.5	691.3	693.1	695.1	698.3	702.8	707.7
5°	637.3	638.6	646.1	653.7	660.8	667.0	672.1	678.2	685.8	695.0	705.3
7.5°	599.9	605.1	612.7	621.9	631.9	640.9	649.9	660.0	670.6	684.2	698.6
10°	575.8	581.6	590.8	602.4	613.1	623.6	634.9	645.8	659.2	675.2	693.7
12.5°	554.7	560.3	569.8	582.5	592.5	604.2	617.2	631.3	646.3	665.7	686.5
15°	525.6	532.1	543.7	549.8	565.3	579.3	591.2	611.6	630.8	650.6	674.8
17.5°	501.7	505.3	514.7	526.1	537.6	553.3	569.0	586.0	605.1	629.4	659.7
20°	485.3	488.4	498.6	510.6	522.9	537.3	551.3	568.3	589.8	615.5	648.2
22.5°	473.0	476.4	483.0	495.8	507.3	519.2	533.2	553.6	576.4	601.5	637.0
25°	455.2	457.3	461.7	472.0	482.2	495.5	507.8	527.0	550.5	579.9	615.5
27.5°	438.4	440.3	444.1	451.4	461.0	471.8	485.2	501.4	525.3	557.2	594.9
30°	428.3	428.6	432.0	438.8	447.0	455.9	468.2	486.7	509.2	541.6	581.3
32.5°	419.5	418.2	420.5	425.7	433.6	442.6	452.6	470.8	492.6	524.4	565.2
35°	404.7	404.0	403.0	407.4	414.3	421.1	430.0	443.6	468.2	497.9	540.6
37.5°	389.6	388.0	386.1	388.2	393.5	400.6	408.3	420.4	441.7	474.4	515.2
40°	378.4	377.0	376.0	375.3	380.1	386.9	392.7	404.4	424.2	455.2	495.5
42.5°	366.1	365.3	364.0	363.0	367.0	372.2	378.3	388.5	408.3	437.5	475.6
45°	346.3	345.6	344.9	344.3	346.6	351.4	356.2	363.7	380.8	409.1	443.6
47.5°	324.2	323.3	323.6	322.5	324.9	328.1	331.4	339.5	355.9	378.7	403.9
50°	308.4	308.1	308.1	308.1	308.7	312.5	315.6	321.7	336.7	359.6	377.7
52.5°	293.4	291.9	291.9	292.5	293.7	296.1	298.1	304.8	317.9	336.7	353.1
55°	269.8	267.1	266.4	267.1	268.1	270.1	272.2	277.7	288.9	302.9	312.5
57.5°	243.7	242.2	241.3	241.5	242.0	243.6	245.2	251.2	260.0	267.3	273.5
60°	225.4	226.0	223.0	223.7	223.7	225.1	227.5	231.2	238.7	243.9	250.0
62.5°	208.2	207.2	206.3	205.4	205.4	205.9	209.1	212.0	218.5	221.1	226.0
65°	181.4	181.4	179.3	179.9	180.3	177.9	179.7	183.1	187.2	188.2	192.6
67.5°	154.2	153.2	152.0	151.1	151.1	150.8	151.7	153.4	156.5	156.9	160.2
70°	135.5	134.9	134.6	133.6	132.2	133.8	132.9	134.6	136.3	136.6	138.7
72.5°	117.5	116.9	116.3	115.2	114.7	114.5	114.6	116.5	117.7	117.2	119.5
75°	91.8	91.2	90.5	88.8	88.8	87.7	88.1	89.4	90.9	89.8	91.8
77.5°	67.5	65.4	65.3	65.7	64.6	64.7	64.4	64.1	64.7	64.8	66.7
80°	51.9	49.5	50.2	49.8	49.5	49.2	48.5	48.9	49.2	49.5	50.6
82.5°	37.5	37.2	36.6	36.5	36.1	35.2	34.9	35.5	35.8	35.6	36.4
85°	19.1	18.1	18.8	18.5	18.8	18.5	17.4	17.4	18.1	17.7	18.5
87.5°	10.9	10.7	9.8	9.5	8.6	8.3	7.5	7.3	7.1	6.7	6.8
90°	25.8	24.9	21.8	18.9	15.9	12.9	10.3	7.9	5.6	3.3	1.1
92.5°	28.0	26.5	24.3	22.0	19.8	17.5	16.7	17.3	18.0	18.6	19.3
95°	33.7	32.1	29.6	27.0	24.5	22.0	25.4	34.9	44.3	53.8	63.2
97.5°	35.2	33.3	49.9	66.5	83.1	99.7	110.0	114.3	118.5	122.8	127.0
100°	36.0	34.2	70.1	106.0	142.0	177.8	193.5	188.9	184.3	179.7	175.0
102.5°	62.4	68.1	107.4	146.6	185.8	225.1	243.1	239.7	236.4	233.1	229.8
105°	186.1	226.9	247.6	268.3	289.0	309.8	318.9	316.3	313.8	311.3	308.7
107.5°	385.9	415.9	412.6	409.3	406.1	402.8	400.1	398.1	396.1	394.0	392.0
110°	459.7	467.3	464.7	462.2	459.7	457.1	455.0	453.1	451.2	449.4	447.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	519.6	519.4	516.9	514.4	511.8	509.3	507.2	505.6	503.9	502.2	500.6
115°	597.0	594.7	592.6	590.5	588.4	586.4	584.6	583.3	581.8	580.5	579.2
117.5°	669.4	667.6	666.6	665.5	664.4	663.3	662.0	660.3	658.5	656.8	655.1
120°	716.7	714.8	714.2	713.5	712.7	712.1	710.7	708.6	706.6	704.5	702.4
122.5°	763.4	762.1	761.2	760.4	759.5	758.6	757.3	755.5	753.9	752.2	750.5
125°	829.3	828.8	827.9	827.0	826.0	825.1	823.8	821.9	820.0	818.2	816.4
127.5°	894.2	893.4	892.3	891.3	890.1	889.0	887.5	885.7	883.9	882.0	880.2
130°	933.4	932.4	931.5	930.6	929.6	928.7	927.3	925.5	923.6	921.9	920.0
132.5°	970.6	969.7	968.9	968.2	967.5	966.7	965.5	963.6	961.8	959.9	958.1
135°	1027.3	1026.7	1025.7	1024.8	1024.0	1023.0	1021.8	1020.5	1019.0	1017.7	1016.3
137.5°	1077.3	1076.2	1075.7	1075.2	1074.7	1074.2	1073.1	1071.3	1069.5	1067.8	1066.0
140°	1109.5	1108.5	1107.9	1107.1	1106.4	1105.7	1104.7	1103.3	1102.0	1100.5	1099.2
142.5°	1140.0	1139.2	1138.5	1137.8	1137.1	1136.4	1135.4	1134.0	1132.7	1131.2	1129.9
145°	1182.5	1182.1	1181.6	1181.2	1180.7	1180.3	1179.2	1177.6	1176.0	1174.4	1172.8
147.5°	1220.5	1219.9	1219.5	1219.1	1218.6	1218.2	1217.4	1216.3	1215.3	1214.2	1213.2
150°	1243.7	1243.2	1242.8	1242.2	1241.8	1241.4	1240.8	1240.1	1239.4	1238.7	1238.1
152.5°	1263.9	1263.1	1262.8	1262.6	1262.2	1261.9	1261.7	1261.3	1261.1	1260.7	1260.4
155°	1292.0	1290.8	1290.7	1290.4	1290.1	1289.9	1290.0	1290.5	1290.9	1291.5	1291.9
157.5°	1316.5	1315.1	1315.4	1315.5	1315.8	1316.0	1316.2	1316.2	1316.3	1316.3	1316.3
160°	1330.6	1329.2	1329.5	1329.6	1329.9	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2
162.5°	1343.2	1341.6	1341.8	1342.1	1342.3	1342.6	1342.9	1343.5	1344.2	1344.8	1345.3
165°	1360.0	1358.2	1358.4	1358.6	1358.9	1359.1	1359.6	1360.3	1360.9	1361.6	1362.4
167.5°	1373.3	1371.5	1371.5	1371.5	1371.5	1371.5	1371.9	1372.9	1373.8	1374.7	1375.6
170°	1380.7	1378.9	1378.9	1378.9	1378.9	1378.9	1379.4	1380.3	1381.3	1382.2	1383.0
172.5°	1385.7	1383.8	1383.7	1383.5	1383.3	1383.1	1383.6	1384.7	1385.8	1387.0	1388.0
175°	1392.0	1390.3	1390.1	1389.8	1389.6	1389.4	1389.8	1391.0	1392.1	1393.3	1394.5
177.5°	1394.3	1392.8	1392.6	1392.4	1392.2	1392.0	1392.4	1393.4	1394.3	1395.2	1396.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	709.3	710.6	715.2	718.5	722.4	724.6	726.7	728.4	730.6	731.1	739.0
5°	712.4	719.3	731.2	740.0	751.0	762.9	771.2	774.9	784.8	793.0	809.4
7.5°	711.5	726.0	744.1	762.9	782.9	801.5	817.6	836.7	850.3	870.8	890.9
10°	710.7	730.1	753.4	777.3	805.3	831.3	854.5	880.5	902.0	930.3	954.6
12.5°	708.3	731.8	764.0	792.3	826.3	862.1	896.5	929.9	949.0	996.1	1018.5
15°	702.1	730.1	770.4	813.5	860.3	902.7	946.4	981.1	1037.5	1078.9	1105.2
17.5°	690.5	729.8	777.6	829.5	886.4	942.2	991.7	1044.6	1104.4	1154.3	1207.6
20°	685.1	728.1	781.4	838.7	897.9	961.0	1017.4	1080.9	1146.1	1195.3	1263.6
22.5°	675.0	723.7	781.1	845.1	908.2	973.6	1039.6	1103.6	1178.9	1246.7	1311.7
25°	658.4	713.1	772.5	843.9	918.0	983.6	1062.5	1147.5	1226.1	1313.1	1378.0
27.5°	641.1	699.5	759.0	825.4	905.1	982.9	1082.2	1178.2	1274.3	1349.5	1397.5
30°	627.7	684.4	745.9	812.8	891.7	984.3	1095.3	1200.1	1293.7	1358.3	1385.2
32.5°	613.2	670.7	725.1	795.3	879.4	983.5	1103.5	1212.9	1294.8	1337.7	1332.5
35°	590.5	638.6	691.6	759.2	858.3	977.4	1108.2	1214.1	1264.3	1255.1	1185.4
37.5°	557.7	598.2	650.3	724.3	833.7	964.8	1098.7	1178.1	1174.8	1099.7	998.8
40°	537.3	571.7	621.9	699.8	814.5	956.6	1083.6	1135.2	1091.5	986.7	865.8
42.5°	510.4	542.2	592.4	672.4	793.5	940.0	1055.0	1069.9	984.4	863.7	753.0
45°	469.0	497.0	548.8	631.5	762.0	903.7	985.0	948.4	833.3	708.6	624.3
47.5°	424.3	453.4	503.4	588.3	716.3	849.1	887.8	810.1	691.9	590.8	513.4
50°	396.2	424.2	473.0	558.7	685.5	804.3	820.4	720.0	611.4	522.5	459.0
52.5°	367.7	394.1	442.1	528.2	649.3	752.3	742.4	640.2	540.3	464.6	414.7
55°	325.5	350.4	396.2	476.8	587.1	668.7	632.8	535.2	452.5	393.8	355.9
57.5°	287.7	311.6	351.0	423.8	519.7	575.8	530.2	447.9	382.2	337.0	308.7
60°	262.0	283.1	320.7	388.3	471.6	514.3	469.2	396.5	341.2	305.0	279.7
62.5°	237.6	256.1	290.9	352.2	424.6	460.5	414.9	353.3	306.2	274.1	252.6
65°	200.8	217.6	248.3	296.1	355.5	379.4	340.2	290.3	253.8	229.9	215.5
67.5°	167.2	181.4	207.9	245.6	289.4	306.7	276.9	238.3	210.7	191.5	180.1
70°	144.8	157.1	177.9	210.4	250.0	263.3	235.3	203.6	183.4	168.0	157.5
72.5°	125.9	135.0	153.9	179.0	212.0	222.6	203.0	175.1	156.3	144.8	136.4
75°	95.9	103.4	115.7	135.9	158.8	165.0	150.3	132.9	120.2	112.0	105.5
77.5°	69.2	74.7	83.6	96.0	111.9	117.4	108.2	96.5	87.3	81.8	78.1
80°	52.3	56.7	64.2	74.5	84.0	87.1	81.6	72.8	66.3	63.2	60.1
82.5°	38.6	41.1	45.7	52.6	59.1	62.8	58.1	52.8	49.3	46.5	45.4
85°	19.4	20.9	22.9	25.6	29.7	31.1	29.3	28.0	25.9	24.3	24.3
87.5°	7.8	8.2	9.5	10.5	12.1	13.6	13.9	13.9	14.3	14.2	14.1
90°	3.3	5.6	7.9	10.3	12.9	15.9	18.9	21.8	24.9	25.8	26.7
92.5°	18.6	18.0	17.3	16.7	17.5	19.8	22.0	24.3	26.5	28.0	29.4
95°	53.8	44.3	34.9	25.4	22.0	24.5	27.0	29.6	32.1	33.7	35.3
97.5°	122.8	118.5	114.3	110.0	99.7	83.1	66.5	49.9	33.3	35.2	37.0
100°	179.7	184.3	188.9	193.5	177.8	142.0	106.0	70.1	34.2	36.0	37.9
102.5°	233.1	236.4	239.7	243.1	225.1	185.8	146.6	107.4	68.1	62.4	56.7
105°	311.3	313.8	316.3	318.9	309.8	289.0	268.3	247.6	226.9	186.1	145.3
107.5°	394.0	396.1	398.1	400.1	402.8	406.1	409.3	412.6	415.9	385.9	356.1
110°	449.4	451.2	453.1	455.0	457.1	459.7	462.2	464.7	467.3	459.7	452.0



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	502.2	503.9	505.6	507.2	509.3	511.8	514.4	516.9	519.4	519.6	519.7
115°	580.5	581.8	583.3	584.6	586.4	588.4	590.5	592.6	594.7	597.0	599.2
117.5°	656.8	658.5	660.3	662.0	663.3	664.4	665.5	666.6	667.6	669.4	671.3
120°	704.5	706.6	708.6	710.7	712.1	712.7	713.5	714.2	714.8	716.7	718.5
122.5°	752.2	753.9	755.5	757.3	758.6	759.5	760.4	761.2	762.1	763.4	764.6
125°	818.2	820.0	821.9	823.8	825.1	826.0	827.0	827.9	828.8	829.3	829.7
127.5°	882.0	883.9	885.7	887.5	889.0	890.1	891.3	892.3	893.4	894.2	894.9
130°	921.9	923.6	925.5	927.3	928.7	929.6	930.6	931.5	932.4	933.4	934.2
132.5°	959.9	961.8	963.6	965.5	966.7	967.5	968.2	968.9	969.7	970.6	971.5
135°	1017.7	1019.0	1020.5	1021.8	1023.0	1024.0	1024.8	1025.7	1026.7	1027.3	1028.1
137.5°	1067.8	1069.5	1071.3	1073.1	1074.2	1074.7	1075.2	1075.7	1076.2	1077.3	1078.4
140°	1100.5	1102.0	1103.3	1104.7	1105.7	1106.4	1107.1	1107.9	1108.5	1109.5	1110.4
142.5°	1131.2	1132.7	1134.0	1135.4	1136.4	1137.1	1137.8	1138.5	1139.2	1140.0	1140.7
145°	1174.4	1176.0	1177.6	1179.2	1180.3	1180.7	1181.2	1181.6	1182.1	1182.5	1183.0
147.5°	1214.2	1215.3	1216.3	1217.4	1218.2	1218.6	1219.1	1219.5	1219.9	1220.5	1220.9
150°	1238.7	1239.4	1240.1	1240.8	1241.4	1241.8	1242.2	1242.8	1243.2	1243.7	1244.1
152.5°	1260.7	1261.1	1261.3	1261.7	1261.9	1262.2	1262.6	1262.8	1263.1	1263.9	1264.7
155°	1291.5	1290.9	1290.5	1290.0	1289.9	1290.1	1290.4	1290.7	1290.8	1292.0	1293.2
157.5°	1316.3	1316.3	1316.2	1316.2	1316.0	1315.8	1315.5	1315.4	1315.1	1316.5	1317.9
160°	1331.1	1330.8	1330.6	1330.3	1330.1	1329.9	1329.6	1329.5	1329.2	1330.6	1331.9
162.5°	1344.8	1344.2	1343.5	1342.9	1342.6	1342.3	1342.1	1341.8	1341.6	1343.2	1344.8
165°	1361.6	1360.9	1360.3	1359.6	1359.1	1358.9	1358.6	1358.4	1358.2	1360.0	1361.9
167.5°	1374.7	1373.8	1372.9	1371.9	1371.5	1371.5	1371.5	1371.5	1371.5	1373.3	1375.1
170°	1382.2	1381.3	1380.3	1379.4	1378.9	1378.9	1378.9	1378.9	1378.9	1380.7	1382.6
172.5°	1387.0	1385.8	1384.7	1383.6	1383.1	1383.3	1383.5	1383.7	1383.8	1385.7	1387.6
175°	1393.3	1392.1	1391.0	1389.8	1389.4	1389.6	1389.8	1390.1	1390.3	1392.0	1393.6
177.5°	1395.2	1394.3	1393.4	1392.4	1392.0	1392.2	1392.4	1392.6	1392.8	1394.3	1395.7
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	741.8	742.1	745.0	747.3	746.2	747.5	748.1
5°	810.4	822.7	829.2	834.0	834.4	834.6	837.4
7.5°	907.8	921.0	930.6	945.2	949.6	954.6	953.1
10°	978.8	998.3	1015.0	1023.9	1033.4	1047.4	1036.2
12.5°	1045.2	1079.7	1105.2	1118.9	1128.0	1130.8	1125.2
15°	1154.7	1199.8	1224.1	1223.3	1254.1	1267.4	1246.5
17.5°	1255.1	1296.7	1330.0	1347.1	1372.7	1378.4	1375.8
20°	1316.5	1362.0	1387.9	1417.3	1430.7	1442.6	1444.7
22.5°	1369.6	1410.3	1438.2	1462.7	1473.8	1479.4	1482.9
25°	1424.2	1456.3	1473.0	1481.5	1484.6	1483.9	1479.4
27.5°	1420.4	1422.8	1404.4	1386.3	1370.1	1351.8	1345.6
30°	1383.5	1354.8	1303.6	1274.5	1231.9	1198.0	1211.7
32.5°	1286.5	1229.4	1171.9	1108.4	1055.9	1041.0	1025.9
35°	1098.0	997.6	938.9	870.6	843.2	815.9	797.1
37.5°	888.3	810.7	740.9	696.2	668.9	651.7	642.3
40°	768.1	698.0	640.7	604.5	583.6	564.2	561.4
42.5°	672.2	607.1	563.9	535.1	515.1	506.8	500.8
45°	550.5	505.1	476.1	455.6	442.3	437.1	430.3
47.5°	466.0	433.9	412.1	398.1	388.1	384.2	383.7
50°	418.7	392.1	376.0	365.1	357.2	355.9	350.4
52.5°	383.2	360.1	347.6	338.0	332.3	328.5	326.9
55°	332.6	317.3	306.0	300.5	296.1	292.3	292.3
57.5°	291.1	278.2	270.7	266.1	264.7	262.1	260.4
60°	265.4	254.4	248.6	244.5	241.8	242.1	239.1
62.5°	240.2	233.1	227.6	223.5	220.3	220.3	220.5
65°	204.6	199.1	195.0	193.7	191.6	189.2	189.8
67.5°	173.3	168.3	165.1	162.7	162.0	160.7	162.7
70°	151.0	147.2	144.8	142.8	142.0	142.4	144.1
72.5°	130.5	127.8	126.3	125.3	123.8	123.9	125.0
75°	102.5	100.4	99.1	98.0	97.6	97.6	97.6
77.5°	75.3	74.8	74.2	72.7	72.8	73.1	73.2
80°	59.4	58.4	58.1	57.3	56.4	55.6	57.3
82.5°	44.4	43.3	43.1	42.9	41.3	41.2	42.6
85°	23.9	22.9	23.2	22.9	22.9	22.6	22.6
87.5°	14.0	13.9	13.7	14.2	13.9	13.7	14.4
90°	27.6	28.5	29.2	29.7	30.1	30.6	31.1
92.5°	30.9	32.5	33.3	33.5	33.9	34.2	34.4
95°	36.9	38.5	39.3	39.3	39.3	39.3	39.3
97.5°	38.9	40.8	41.7	42.0	42.3	42.4	42.7
100°	39.7	41.6	42.6	42.8	43.1	43.2	43.5
102.5°	51.0	45.3	42.7	43.1	43.5	44.0	44.3
105°	104.6	63.8	43.8	44.2	44.7	45.1	45.6
107.5°	326.2	296.3	266.0	235.3	204.6	173.9	143.2
110°	444.4	436.8	416.6	383.7	350.7	317.8	284.9



TEST NUMBER: P331946-940

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	519.9	520.0	516.6	509.6	502.7	495.7	488.7
115°	601.5	603.9	605.5	606.4	607.3	608.2	609.1
117.5°	673.2	674.9	676.0	676.2	676.4	676.5	676.7
120°	720.3	722.2	723.1	723.1	723.1	723.1	723.1
122.5°	766.0	767.2	767.9	768.1	768.3	768.6	768.7
125°	830.2	830.6	831.1	831.5	832.1	832.5	832.9
127.5°	895.6	896.3	896.5	896.1	895.6	895.2	894.7
130°	935.1	936.1	936.3	935.9	935.4	935.0	934.5
132.5°	972.5	973.4	973.5	972.9	972.2	971.6	970.9
135°	1028.8	1029.5	1029.5	1028.8	1028.1	1027.3	1026.7
137.5°	1079.5	1080.6	1080.9	1080.5	1080.0	1079.6	1079.1
140°	1111.3	1112.2	1112.4	1112.0	1111.5	1111.1	1110.6
142.5°	1141.4	1142.1	1142.2	1141.6	1140.9	1140.2	1139.6
145°	1183.5	1183.9	1184.1	1184.1	1184.1	1184.1	1184.1
147.5°	1221.4	1221.8	1221.6	1220.5	1219.4	1218.3	1217.3
150°	1244.6	1245.0	1244.9	1244.2	1243.6	1242.9	1242.2
152.5°	1265.6	1266.4	1266.3	1265.2	1264.2	1263.1	1262.0
155°	1294.3	1295.5	1295.3	1294.0	1292.6	1291.2	1289.9
157.5°	1319.2	1320.6	1320.4	1318.7	1316.8	1315.0	1313.2
160°	1333.3	1334.7	1334.6	1333.0	1331.4	1329.7	1328.1
162.5°	1346.3	1347.9	1347.9	1346.5	1345.1	1343.6	1342.2
165°	1363.7	1365.6	1365.7	1364.1	1362.4	1360.8	1359.2
167.5°	1377.0	1378.9	1378.9	1377.0	1375.1	1373.3	1371.5
170°	1384.5	1386.3	1386.3	1384.5	1382.6	1380.7	1378.9
172.5°	1389.4	1391.2	1391.2	1389.1	1387.1	1385.1	1383.0
175°	1395.2	1396.8	1396.6	1394.8	1392.9	1391.2	1389.3
177.5°	1397.2	1398.6	1398.5	1396.7	1394.8	1392.9	1391.2
180°	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5	1394.5

(END OF REPORT)