

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331989-935

Luminaire Tested: **S123DIP-S775D1025U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331989-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5762.9 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11286	11286	11286
5°	11339	11182	11261
10°	11262	11086	11154
15°	11131	10961	10981
20°	10977	10781	10791
25°	10772	10568	10546
30°	10544	10331	10253
35°	10307	10081	9950
40°	10058	9805	9653
45°	9785	9552	9319
50°	9512	9239	8982
55°	9154	8916	8646
60°	8792	8540	8269
65°	8474	8130	7875
70°	8003	7660	7320
75°	7311	7049	6750
80°	6595	6316	6261
85°	5780	5570	5348



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	1.7
10°-20°	278.9	4.8
20°-30°	411.9	7.1
30°-40°	481.2	8.3
40°-50°	483.8	8.4
50°-60°	425.0	7.4
60°-70°	316.6	5.5
70°-80°	180.4	3.1
80°-90°	55.0	1.0
90°-100°	71.3	1.2
100°-110°	213.3	3.7
110°-120°	362.8	6.3
120°-130°	477.3	8.3
130°-140°	536.4	9.3
140°-150°	527.3	9.1
150°-160°	443.9	7.7
160°-170°	295.5	5.1
170°-180°	103.5	1.8
0°-30°	789.6	13.7
0°-40°	1270.8	22.1
0°-60°	2179.5	37.8
0°-90°	2731.5	47.4
90°-120°	647.5	11.2
90°-150°	2188.5	38.0
90°-180°	3031.0	52.6
0°-180°	5762.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1049	1045	1035	1043	1042	99
15°	999	995	984	990	985	281
25°	907	901	890	890	888	418
35°	784	779	767	762	757	490
45°	643	639	628	617	612	496
55°	488	486	475	466	461	437
65°	333	328	319	312	309	328
75°	176	172	170	165	162	188
85°	47	45	45	43	43	51
90°	1	10	21	24	26	6
95°	51	57	64	67	67	57
105°	193	195	203	203	205	207
115°	365	368	366	367	366	361
125°	535	537	536	532	529	477
135°	694	698	698	694	693	534
145°	841	843	846	845	841	525
155°	964	964	964	967	962	443
165°	1049	1047	1047	1051	1046	296
175°	1092	1088	1088	1093	1087	104
180°	1094	1094	1094	1094	1094	



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1052.1	1051.5	1050.9	1050.2	1049.6	1048.4	1046.5	1044.8	1043.0	1041.3	1042.8
5°	1049.4	1048.4	1047.4	1046.4	1045.3	1043.8	1041.6	1039.4	1037.2	1034.9	1037.0
7.5°	1039.1	1038.1	1037.1	1036.1	1035.1	1033.5	1031.1	1028.9	1026.6	1024.3	1026.1
10°	1030.4	1029.4	1028.5	1027.4	1026.5	1024.7	1022.0	1019.4	1016.8	1014.3	1016.1
12.5°	1018.9	1018.0	1017.3	1016.4	1015.5	1013.9	1011.5	1009.0	1006.6	1004.1	1005.5
15°	998.9	998.1	997.3	996.5	995.7	994.0	991.4	988.8	986.2	983.6	985.2
17.5°	975.6	974.6	973.5	972.5	971.5	969.7	967.1	964.4	961.8	959.2	960.4
20°	958.3	957.1	956.0	954.8	953.6	951.6	949.0	946.4	943.8	941.2	942.0
22.5°	938.8	937.6	936.4	935.2	934.0	932.1	929.5	927.0	924.4	921.7	922.4
25°	907.0	905.8	904.6	903.4	902.2	900.3	897.6	895.0	892.4	889.8	890.0
27.5°	872.9	871.7	870.6	869.4	868.2	866.3	863.4	860.7	857.8	855.0	855.1
30°	848.3	847.3	846.4	845.3	844.3	842.4	839.6	836.8	834.1	831.2	831.2
32.5°	823.8	822.5	821.1	819.8	818.6	816.8	814.6	812.4	810.3	808.1	807.0
35°	784.4	783.2	782.0	780.8	779.5	777.7	775.0	772.4	769.8	767.2	766.0
37.5°	743.9	742.4	740.9	739.3	737.9	735.8	733.1	730.5	727.8	725.2	723.8
40°	715.8	714.6	713.4	712.2	711.0	709.0	706.2	703.4	700.6	697.8	696.2
42.5°	687.7	686.3	684.9	683.6	682.3	680.2	677.3	674.5	671.8	668.9	667.4
45°	642.8	642.0	641.2	640.4	639.6	637.9	635.2	632.7	630.1	627.5	625.1
47.5°	598.2	597.1	595.9	594.8	593.6	591.8	589.4	586.9	584.4	582.0	579.6
50°	568.0	567.0	565.9	565.0	564.0	562.1	559.6	557.0	554.3	551.7	549.6
52.5°	536.2	535.5	534.9	534.2	533.5	531.8	529.0	526.2	523.5	520.7	518.8
55°	487.8	487.5	487.3	487.2	486.9	485.5	482.9	480.4	477.7	475.1	472.9
57.5°	441.6	440.9	440.2	439.5	438.9	437.5	435.4	433.3	431.2	429.1	427.1
60°	408.4	408.2	408.0	407.8	407.6	406.3	403.9	401.5	399.1	396.7	394.9
62.5°	378.8	378.3	377.8	377.3	376.8	375.3	372.9	370.5	368.1	365.7	363.9
65°	332.7	331.7	330.6	329.7	328.6	327.2	325.1	323.1	321.2	319.2	317.5
67.5°	283.8	282.9	282.1	281.1	280.3	279.1	277.6	276.0	274.5	273.0	271.6
70°	254.3	253.0	251.8	250.6	249.4	248.2	247.0	245.8	244.6	243.4	242.0
72.5°	223.3	222.3	221.4	220.6	219.7	218.6	217.2	215.9	214.5	213.1	211.9
75°	175.8	175.0	174.2	173.4	172.6	171.9	171.3	170.7	170.0	169.5	168.5
77.5°	133.8	133.4	132.9	132.5	132.0	131.5	130.7	130.0	129.3	128.5	127.9
80°	106.4	105.8	105.2	104.6	104.0	103.5	103.1	102.7	102.3	101.9	101.7
82.5°	79.7	79.6	79.5	79.3	79.2	79.1	79.0	79.0	78.9	78.8	78.4
85°	46.8	46.5	46.1	45.7	45.3	45.1	45.1	45.1	45.1	45.1	44.7
87.5°	18.9	18.9	18.7	18.6	18.5	18.7	18.9	19.3	19.6	20.0	20.0
90°	0.9	2.8	4.6	6.6	8.5	10.7	13.2	15.7	18.2	20.7	21.4
92.5°	20.8	22.1	23.4	24.7	26.0	27.4	28.8	30.1	31.6	33.0	33.6
95°	50.7	52.0	53.4	54.8	56.1	57.5	59.0	60.5	62.1	63.6	64.4
97.5°	90.1	91.1	92.0	93.1	94.0	95.1	96.2	97.3	98.4	99.5	100.4
100°	116.9	118.0	119.2	120.3	121.5	122.5	123.5	124.4	125.4	126.3	126.9
102.5°	147.8	148.5	149.2	149.9	150.6	151.5	152.8	154.0	155.3	156.6	157.1
105°	193.4	193.7	194.2	194.5	194.9	196.0	197.7	199.4	201.1	202.9	202.9
107.5°	246.3	246.6	246.8	247.0	247.3	247.7	248.4	249.1	249.8	250.5	251.1
110°	279.3	279.7	280.1	280.4	280.9	281.2	281.6	282.0	282.4	282.8	283.5



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	313.7	313.9	314.2	314.4	314.6	314.8	314.9	315.0	315.0	315.0	316.0
115°	365.2	365.8	366.4	367.0	367.6	367.6	367.3	366.9	366.5	366.1	366.4
117.5°	417.2	417.6	417.9	418.4	418.7	418.6	418.2	417.7	417.2	416.6	416.6
120°	449.5	450.6	451.8	453.0	454.1	454.2	453.2	452.3	451.3	450.4	450.1
122.5°	483.2	484.1	484.8	485.7	486.6	486.7	486.2	485.7	485.3	484.7	484.2
125°	534.6	535.2	535.7	536.3	536.8	537.0	536.6	536.2	535.8	535.5	534.7
127.5°	582.0	583.2	584.4	585.7	586.9	587.3	586.9	586.5	586.1	585.7	584.5
130°	613.6	615.2	616.7	618.2	619.7	620.3	619.7	619.1	618.5	617.9	617.2
132.5°	645.3	646.8	648.3	649.9	651.4	651.9	651.5	651.1	650.7	650.2	649.4
135°	693.6	694.7	695.9	697.0	698.2	698.6	698.4	698.3	698.1	697.8	697.2
137.5°	738.3	739.3	740.2	741.1	742.1	742.8	743.3	743.8	744.3	744.8	744.0
140°	769.2	770.2	771.1	772.1	773.0	773.6	773.8	774.0	774.2	774.4	774.2
142.5°	797.4	798.3	799.4	800.3	801.2	801.8	802.2	802.5	802.9	803.2	803.1
145°	841.4	841.8	842.1	842.6	842.9	843.4	844.0	844.6	845.2	845.7	845.5
147.5°	879.9	880.6	881.3	882.0	882.7	883.3	883.8	884.3	884.8	885.5	885.5
150°	906.7	907.1	907.5	907.8	908.3	908.6	909.0	909.4	909.8	910.2	910.2
152.5°	928.8	929.3	929.8	930.3	930.8	931.3	931.5	931.7	931.9	932.2	932.5
155°	963.5	963.5	963.5	963.5	963.5	963.5	963.7	963.9	964.1	964.3	965.1
157.5°	993.0	992.8	992.6	992.3	992.1	992.0	992.2	992.4	992.6	992.6	993.5
160°	1011.6	1011.2	1010.8	1010.5	1010.0	1009.9	1009.9	1009.9	1009.9	1009.9	1010.8
162.5°	1028.1	1027.5	1027.0	1026.5	1026.0	1025.8	1025.9	1026.1	1026.2	1026.4	1027.3
165°	1049.4	1048.8	1048.3	1047.7	1047.1	1046.8	1046.8	1046.8	1046.8	1046.8	1047.9
167.5°	1066.4	1065.7	1064.9	1064.1	1063.3	1063.1	1063.2	1063.3	1063.5	1063.7	1064.9
170°	1076.1	1075.3	1074.5	1073.8	1073.0	1072.6	1072.6	1072.6	1072.6	1072.6	1073.9
172.5°	1083.6	1082.9	1082.1	1081.3	1080.6	1080.1	1080.1	1080.1	1080.1	1080.1	1081.3
175°	1091.5	1090.7	1089.9	1089.3	1088.5	1088.0	1088.0	1088.0	1088.0	1088.0	1089.3
177.5°	1094.8	1094.2	1093.6	1093.0	1092.4	1092.0	1092.0	1092.0	1092.0	1092.0	1093.0
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1044.5	1046.1	1047.7	1048.4	1048.3	1048.1	1047.9	1047.8
5°	1039.0	1040.9	1043.0	1043.8	1043.4	1043.0	1042.6	1042.2
7.5°	1027.9	1029.8	1031.6	1032.3	1032.1	1031.8	1031.6	1031.4
10°	1017.9	1019.6	1021.4	1022.2	1021.7	1021.3	1021.0	1020.5
12.5°	1006.8	1008.1	1009.4	1010.0	1009.7	1009.4	1009.3	1009.0
15°	986.8	988.3	990.0	990.2	988.9	987.7	986.6	985.4
17.5°	961.5	962.6	963.7	964.1	963.6	963.2	962.8	962.3
20°	942.8	943.6	944.4	944.5	943.9	943.3	942.7	942.1
22.5°	923.0	923.7	924.3	924.2	923.5	922.7	922.0	921.2
25°	890.2	890.4	890.6	890.4	889.8	889.2	888.6	888.0
27.5°	855.3	855.5	855.7	855.3	854.6	853.9	853.1	852.3
30°	831.2	831.2	831.2	830.5	829.1	827.7	826.3	824.9
32.5°	805.9	804.8	803.7	802.7	801.9	801.2	800.4	799.7
35°	764.8	763.6	762.4	761.3	760.3	759.3	758.3	757.2
37.5°	722.3	720.8	719.5	718.4	717.7	717.1	716.4	715.8
40°	694.6	693.0	691.4	690.2	689.4	688.5	687.8	687.0
42.5°	665.7	664.1	662.5	661.3	660.6	659.7	658.9	658.1
45°	622.7	620.3	617.9	616.1	615.2	614.2	613.1	612.2
47.5°	577.3	575.0	572.6	570.9	570.1	569.2	568.3	567.4
50°	547.3	545.1	542.9	541.2	540.0	538.8	537.6	536.4
52.5°	516.9	515.1	513.2	511.7	510.5	509.3	508.1	506.9
55°	470.7	468.5	466.3	464.7	463.6	462.7	461.7	460.7
57.5°	425.2	423.3	421.3	419.7	418.5	417.4	416.2	415.1
60°	393.0	391.2	389.4	388.1	387.0	386.1	385.0	384.1
62.5°	362.1	360.2	358.4	357.2	356.5	355.9	355.2	354.5
65°	315.9	314.4	312.7	311.6	311.0	310.4	309.8	309.2
67.5°	270.2	268.8	267.3	266.2	265.4	264.6	263.7	262.9
70°	240.6	239.2	237.8	236.6	235.6	234.6	233.6	232.6
72.5°	210.6	209.4	208.2	207.2	206.7	206.2	205.7	205.2
75°	167.5	166.5	165.5	164.7	164.1	163.5	162.9	162.3
77.5°	127.2	126.5	125.8	125.5	125.5	125.5	125.5	125.5
80°	101.5	101.3	101.1	101.0	101.0	101.0	101.0	101.0
82.5°	78.1	77.7	77.3	77.1	77.0	76.8	76.6	76.5
85°	44.3	43.9	43.5	43.3	43.3	43.3	43.3	43.3
87.5°	20.0	20.0	20.0	20.0	20.1	20.1	20.2	20.3
90°	22.1	22.9	23.7	24.3	24.6	25.1	25.4	25.7
92.5°	34.3	34.9	35.5	35.6	35.4	35.2	35.0	34.7
95°	65.1	65.9	66.6	67.1	67.1	67.1	67.1	67.1
97.5°	101.3	102.2	103.1	103.4	103.4	103.3	103.2	103.1
100°	127.5	128.0	128.6	129.2	129.5	129.8	130.3	130.6
102.5°	157.7	158.3	158.9	159.1	159.0	158.9	158.9	158.9
105°	202.9	202.9	202.9	203.0	203.4	203.8	204.1	204.6
107.5°	251.7	252.3	252.9	253.0	252.9	252.6	252.4	252.2
110°	284.3	285.1	285.9	286.0	285.6	285.2	284.9	284.5



TEST NUMBER: P331989-935

CATALOG NUMBER: S123DIP-S775D1025U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	316.9	317.8	318.7	319.2	319.1	319.0	318.9	318.8
115°	366.5	366.7	366.9	366.9	366.7	366.5	366.4	366.1
117.5°	416.6	416.6	416.6	416.2	415.7	415.2	414.7	414.1
120°	450.0	449.8	449.6	449.3	448.9	448.6	448.2	447.8
122.5°	483.7	483.3	482.8	482.2	481.7	481.1	480.6	480.1
125°	533.9	533.1	532.4	531.6	530.9	530.1	529.3	528.6
127.5°	583.5	582.5	581.3	580.4	579.5	578.6	577.7	576.9
130°	616.4	615.6	614.9	613.8	612.5	611.1	609.8	608.5
132.5°	648.4	647.6	646.6	645.7	644.6	643.6	642.6	641.5
135°	696.4	695.6	694.8	694.2	693.9	693.4	693.1	692.8
137.5°	743.2	742.4	741.6	740.8	740.1	739.3	738.7	738.0
140°	774.0	773.8	773.6	772.8	771.5	770.2	768.9	767.5
142.5°	802.9	802.7	802.5	801.8	800.8	799.8	798.7	797.7
145°	845.3	845.2	844.9	844.5	843.7	842.9	842.1	841.4
147.5°	885.5	885.5	885.5	884.8	883.7	882.5	881.4	880.3
150°	910.2	910.2	910.2	909.6	908.4	907.3	906.1	905.0
152.5°	932.8	933.1	933.4	933.1	932.0	931.1	930.1	929.1
155°	965.9	966.6	967.3	967.1	965.8	964.4	963.0	961.7
157.5°	994.3	995.1	995.9	995.7	994.7	993.6	992.6	991.4
160°	1011.8	1012.7	1013.7	1013.7	1013.1	1012.3	1011.5	1010.7
162.5°	1028.3	1029.2	1030.2	1030.0	1028.8	1027.6	1026.4	1025.2
165°	1049.1	1050.2	1051.4	1051.3	1050.0	1048.6	1047.3	1045.9
167.5°	1066.0	1067.2	1068.4	1068.4	1067.2	1066.0	1064.9	1063.7
170°	1075.3	1076.6	1078.0	1078.0	1076.6	1075.3	1073.9	1072.6
172.5°	1082.5	1083.7	1084.9	1084.9	1083.5	1082.2	1080.8	1079.4
175°	1090.4	1091.5	1092.7	1092.5	1091.2	1089.9	1088.6	1087.2
177.5°	1093.9	1094.8	1095.7	1095.6	1094.6	1093.5	1092.4	1091.3
180°	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1	1094.1

(END OF REPORT)