

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831500

Luminaire Tested: S123DIP-S560D1195U940-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831500  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U940-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6166.4 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 50.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38				
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28				
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24				
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21				
5	67	56	49	43	61	52	45	40	43	38	34	34	31	28	26	24	22	19				
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	24	22	20	17				
7	58	46	38	33	52	42	36	31	35	30	26	28	25	22	22	20	18	15				
8	54	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14				
9	50	38	31	26	45	35	29	25	30	25	21	24	21	18	19	17	15	13				
10	47	35	28	24	43	32	26	22	27	23	19	22	19	16	18	15	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	15493	15493	15493	15493	15493
5°	19594	18493	15632	12597	11575
10°	19783	20382	15527	10041	8775
15°	14900	18923	15422	8504	7421
20°	10381	15313	15224	7436	6740
25°	7917	11776	14890	6842	6322
30°	6848	9355	14353	6421	5986
35°	6355	7899	13736	6117	5749
40°	6015	7086	12867	5828	5668
45°	5815	6558	11764	5602	5632
50°	5715	6141	10458	5397	5603
55°	5502	5834	9175	5202	5628
60°	5307	5507	7907	5018	5535
65°	4984	5196	6821	4824	5428
70°	4604	4803	5800	4497	5108
75°	4167	4304	4974	4180	4666
80°	3434	3769	3936	3645	3936
85°	2717	3051	2890	3088	3137

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 13431 cd/sqm



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.1	2.2
10°-20°	338.5	5.5
20°-30°	400.8	6.5
30°-40°	403.0	6.5
40°-50°	369.8	6.0
50°-60°	305.2	4.9
60°-70°	215.9	3.5
70°-80°	115.2	1.9
80°-90°	32.1	0.5
90°-100°	277.7	4.5
100°-110°	813.1	13.2
110°-120°	794.0	12.9
120°-130°	632.3	10.3
130°-140°	498.9	8.1
140°-150°	372.2	6.0
150°-160°	259.5	4.2
160°-170°	152.4	2.5
170°-180°	49.6	0.8
0°-30°	875.4	14.2
0°-40°	1278.4	20.7
0°-60°	1953.4	31.7
0°-90°	2316.6	37.6
90°-120°	1884.8	30.6
90°-150°	3388.3	54.9
90°-180°	3850.0	62.4
0°-180°	6166.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1439	1439	1439	1439	1439	
5°	1813	1712	1447	1166	1071	173
15°	1337	1698	1384	763	666	369
25°	667	992	1254	576	532	315
35°	484	601	1045	466	438	304
45°	382	431	773	368	370	296
55°	293	311	489	277	300	262
65°	196	204	268	189	213	194
75°	100	104	120	100	112	105
85°	22	25	23	25	25	25
90°	30	26	2	26	30	17
95°	120	614	35	614	120	195
105°	1318	833	120	833	1318	1315
115°	1603	637	212	637	1603	1563
125°	1264	595	295	595	1264	1144
135°	1025	586	346	586	1025	795
145°	801	579	395	579	801	509
155°	664	560	449	560	664	309
165°	579	537	490	537	579	165
175°	521	515	511	515	521	51
180°	512	512	512	512	512	



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1622.3	1620.7	1619.0	1610.6	1602.3	1598.3	1594.3	1582.3	1570.2	1556.9	1543.5
5°	1813.4	1818.0	1822.7	1817.4	1812.0	1795.7	1779.3	1757.6	1735.9	1711.5	1687.1
7.5°	1901.5	1904.2	1906.9	1903.5	1900.2	1895.8	1891.5	1872.1	1852.8	1827.7	1802.7
10°	1810.0	1816.0	1822.0	1835.1	1848.1	1862.8	1877.5	1874.8	1872.1	1864.8	1857.4
12.5°	1609.0	1616.3	1623.7	1649.7	1675.8	1709.2	1742.6	1771.3	1800.0	1820.0	1840.1
15°	1337.1	1357.5	1377.9	1401.6	1425.3	1474.4	1523.5	1583.9	1644.4	1698.1	1751.9
17.5°	1101.4	1109.1	1116.7	1142.1	1167.5	1229.3	1291.1	1360.8	1430.6	1519.8	1609.0
20°	906.3	913.4	920.4	953.8	987.2	1035.6	1084.0	1162.5	1241.0	1336.8	1432.6
22.5°	761.4	772.4	783.4	802.1	820.9	867.3	913.7	983.5	1053.3	1159.1	1265.0
25°	666.6	674.6	682.6	693.9	705.3	742.4	779.4	836.9	894.3	991.5	1088.7
27.5°	601.8	605.1	608.5	619.8	631.2	655.2	679.3	728.7	778.1	860.6	943.1
30°	551.0	553.4	555.7	565.7	575.7	592.1	608.5	644.2	679.9	752.7	825.5
32.5°	515.6	517.3	519.0	526.6	534.3	546.0	557.7	583.7	609.8	669.9	730.0
35°	483.6	484.6	485.6	491.2	496.9	505.6	514.3	534.0	553.7	601.1	648.5
37.5°	455.5	456.8	458.2	461.5	464.9	472.5	480.2	495.9	511.6	548.0	584.4
40°	428.1	430.5	432.8	435.1	437.5	443.8	450.2	462.2	474.2	504.3	534.3
42.5°	404.7	407.1	409.4	410.4	411.4	415.1	418.8	429.8	440.8	463.2	485.6
45°	382.0	383.0	384.0	385.0	386.0	389.1	392.1	401.7	411.4	430.8	450.2
47.5°	361.3	361.3	361.3	362.0	362.7	365.3	368.0	375.0	382.0	397.1	412.1
50°	341.3	341.3	341.3	340.3	339.3	341.0	342.6	348.0	353.3	366.7	380.0
52.5°	317.3	317.3	317.3	317.6	317.9	317.9	317.9	322.6	327.3	339.3	351.3
55°	293.2	294.5	295.9	294.9	293.9	294.5	295.2	298.2	301.2	310.9	320.6
57.5°	269.2	269.8	270.5	270.2	269.8	270.2	270.5	273.2	275.8	283.2	290.5
60°	246.5	246.5	246.5	245.8	245.1	245.8	246.5	247.8	249.1	255.8	262.5
62.5°	221.1	221.4	221.7	222.1	222.4	221.7	221.1	222.7	224.4	229.4	234.4
65°	195.7	196.0	196.4	197.4	198.4	197.7	197.0	198.7	200.4	204.0	207.7
67.5°	173.0	172.3	171.7	172.0	172.3	173.3	174.3	174.7	175.0	179.0	183.0
70°	146.3	146.9	147.6	147.3	146.9	147.3	147.6	148.6	149.6	152.6	155.6
72.5°	122.2	122.6	122.9	122.9	122.9	123.6	124.2	125.2	126.2	127.9	129.6
75°	100.2	100.2	100.2	100.9	101.5	101.9	102.2	102.2	102.2	103.5	104.9
77.5°	76.1	77.8	79.5	79.1	78.8	79.5	80.1	81.2	82.2	82.8	83.5
80°	55.4	55.4	55.4	55.8	56.1	57.1	58.1	58.8	59.4	60.8	62.1
82.5°	35.4	35.7	36.1	37.1	38.1	38.7	39.4	40.4	41.4	41.4	41.4
85°	22.0	21.4	20.7	21.4	22.0	22.7	23.4	23.7	24.0	24.7	25.4
87.5°	10.7	10.7	10.7	10.7	10.7	11.0	11.4	11.4	11.4	11.4	11.4
90°	30.0	31.1	30.0	29.0	30.0	28.0	26.9	25.9	24.9	25.9	22.8
92.5°	54.9	57.0	55.9	60.1	62.2	69.4	79.8	102.6	144.0	192.7	213.4
95°	120.2	124.3	131.6	140.9	160.6	197.9	252.8	373.0	498.3	614.4	547.0
97.5°	246.6	258.0	282.8	322.2	391.6	509.7	646.5	856.8	977.0	944.9	705.5
100°	649.6	648.6	689.0	764.6	869.2	1016.3	1137.6	1221.5	1185.2	981.1	663.1
102.5°	1028.8	1058.8	1090.9	1146.9	1222.5	1302.3	1360.3	1342.7	1195.6	913.8	600.9
105°	1317.8	1323.0	1356.2	1395.5	1443.2	1470.1	1450.4	1346.8	1130.3	833.0	552.2
107.5°	1506.4	1517.8	1531.3	1549.9	1556.1	1528.1	1447.3	1284.7	1037.1	761.5	517.0
110°	1614.1	1616.2	1618.3	1610.0	1581.0	1508.5	1377.9	1187.3	950.0	702.4	498.3



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1635.9	1634.9	1624.5	1594.5	1535.4	1437.0	1286.8	1090.9	874.4	663.1	488.0
115°	1602.7	1597.6	1576.8	1531.3	1453.6	1340.6	1188.3	1008.1	816.4	637.2	486.9
117.5°	1530.2	1523.0	1491.9	1441.1	1360.3	1243.2	1103.4	943.8	778.1	619.5	488.0
120°	1434.9	1428.7	1403.8	1345.8	1264.0	1159.3	1035.0	895.1	749.1	608.2	492.1
122.5°	1345.8	1337.5	1309.5	1258.8	1188.3	1093.0	980.1	856.8	725.2	600.9	499.4
125°	1264.0	1256.7	1230.8	1185.2	1118.9	1036.0	936.6	823.6	705.5	594.7	506.6
127.5°	1193.5	1187.3	1163.5	1124.1	1064.0	987.3	896.2	793.6	686.9	591.6	514.9
130°	1135.5	1127.2	1105.4	1068.1	1013.2	942.8	858.9	765.6	672.4	588.5	523.2
132.5°	1078.5	1073.3	1054.7	1017.4	966.6	900.3	823.6	739.7	658.9	587.4	529.4
135°	1024.6	1017.4	998.7	967.7	916.9	857.8	790.5	716.9	647.5	586.4	535.6
137.5°	967.7	961.4	945.9	913.8	870.3	817.4	757.3	695.2	637.2	584.3	539.8
140°	907.6	908.6	892.0	863.0	823.6	779.1	729.4	676.5	627.8	583.3	543.9
142.5°	851.6	852.7	838.1	813.3	781.2	743.9	702.4	658.9	619.5	581.2	547.0
145°	800.9	798.8	790.5	768.7	742.8	712.8	679.6	645.4	612.3	579.1	548.1
147.5°	757.3	756.3	748.0	732.5	711.8	690.0	662.0	634.1	605.0	576.0	548.1
150°	720.0	720.0	713.8	702.4	686.9	667.2	645.4	621.6	597.8	571.9	548.1
152.5°	689.0	689.0	685.9	675.5	664.1	648.6	629.9	610.2	589.5	566.7	545.0
155°	664.1	663.1	661.0	652.7	643.4	630.9	615.4	598.8	581.2	560.5	542.9
157.5°	640.3	640.3	638.2	632.0	623.7	613.3	600.9	586.4	571.9	555.3	539.8
160°	617.5	618.5	618.5	612.3	605.0	597.8	587.4	576.0	562.6	549.1	537.7
162.5°	596.8	597.8	597.8	592.6	588.5	582.2	572.9	563.6	553.2	542.9	533.6
165°	579.1	579.1	580.2	576.0	571.9	566.7	559.5	553.2	545.0	536.7	529.4
167.5°	561.5	561.5	562.6	559.5	557.4	553.2	549.1	543.9	536.7	530.4	525.3
170°	546.0	546.0	547.0	545.0	543.9	541.8	537.7	534.6	529.4	524.2	521.1
172.5°	531.5	532.5	534.6	532.5	532.5	531.5	528.4	526.3	522.2	519.1	518.0
175°	521.1	522.2	523.2	522.2	522.2	522.2	520.1	519.1	517.0	514.9	514.9
177.5°	513.9	513.9	515.9	514.9	515.9	515.9	514.9	513.9	512.8	511.8	512.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1539.5	1535.5	1520.8	1506.1	1489.4	1472.7	1460.4	1448.0	1429.6	1411.3	1396.2
5°	1668.4	1649.7	1618.7	1587.6	1545.5	1503.4	1475.1	1446.7	1408.6	1370.5	1340.1
7.5°	1770.6	1738.5	1695.1	1651.7	1596.6	1541.5	1489.4	1437.3	1379.2	1321.1	1273.7
10°	1835.7	1814.0	1763.9	1713.8	1640.0	1566.2	1493.4	1420.6	1345.8	1271.0	1208.2
12.5°	1842.1	1844.1	1798.0	1751.9	1668.4	1584.9	1496.4	1407.9	1313.8	1219.6	1146.5
15°	1786.3	1820.7	1795.3	1769.9	1685.8	1601.6	1492.8	1383.9	1275.4	1166.8	1082.3
17.5°	1682.8	1756.6	1760.3	1763.9	1679.8	1595.6	1475.1	1354.5	1231.6	1108.7	1019.9
20°	1541.5	1650.4	1687.8	1725.2	1656.7	1588.3	1458.7	1329.1	1191.5	1053.9	960.8
22.5°	1397.3	1529.5	1598.0	1666.4	1615.7	1564.9	1427.0	1289.1	1143.8	998.5	904.0
25°	1232.9	1377.2	1482.4	1587.6	1556.5	1525.5	1389.6	1253.7	1099.0	944.4	847.9
27.5°	1089.7	1236.3	1363.2	1490.1	1483.4	1476.7	1341.8	1206.9	1048.6	890.3	797.1
30°	962.1	1098.7	1240.6	1382.6	1398.9	1415.3	1285.0	1154.8	996.2	837.5	747.7
32.5°	849.2	968.5	1120.7	1273.0	1305.1	1337.1	1219.6	1102.0	945.1	788.1	701.6
35°	756.7	864.9	1017.2	1169.5	1209.6	1249.6	1147.5	1045.3	892.3	739.4	656.9
37.5°	674.9	765.4	914.0	1062.6	1111.7	1160.8	1069.3	977.8	834.5	691.3	615.5
40°	607.1	679.9	816.5	953.1	1009.9	1066.6	991.2	915.7	779.8	643.9	574.1
42.5°	550.4	615.1	739.0	862.9	917.4	971.8	908.0	844.2	723.3	602.4	538.7
45°	501.9	553.7	666.2	778.8	830.5	882.3	827.5	772.8	666.2	559.7	500.3
47.5°	456.5	500.9	597.1	693.3	739.4	785.5	742.7	700.0	609.8	519.6	465.9
50°	415.8	451.5	535.7	619.8	659.9	700.0	662.2	624.5	550.4	476.2	429.5
52.5°	380.4	409.4	479.9	550.4	584.7	619.1	586.8	554.4	495.6	436.8	396.1
55°	345.3	370.0	431.1	492.2	515.6	539.0	514.0	488.9	441.5	394.1	359.7
57.5°	312.6	334.6	384.7	434.8	452.8	470.9	448.2	425.5	389.7	354.0	325.3
60°	280.5	298.6	340.3	382.0	393.1	404.1	385.7	367.3	342.3	317.3	291.5
62.5°	250.8	267.2	298.2	329.3	336.6	344.0	329.9	315.9	296.9	277.8	257.8
65°	220.1	232.4	257.8	283.2	287.9	292.5	280.2	267.8	253.5	239.1	224.4
67.5°	191.7	200.4	221.1	241.8	242.1	242.4	232.4	222.4	214.4	206.4	194.7
70°	164.0	172.3	186.0	199.7	200.0	200.4	192.4	184.3	178.3	172.3	163.6
72.5°	135.6	141.6	151.9	162.3	161.6	161.0	156.0	150.9	146.3	141.6	135.3
75°	109.9	114.9	121.9	128.9	126.9	124.9	122.2	119.6	115.5	111.5	107.5
77.5°	86.5	89.5	93.5	97.5	96.2	94.8	92.5	90.2	87.2	84.2	82.5
80°	63.5	64.8	67.5	70.1	69.5	68.8	66.1	63.5	62.8	62.1	59.8
82.5°	43.1	44.7	45.4	46.1	45.8	45.4	43.4	41.4	40.7	40.1	39.7
85°	25.7	26.0	26.4	26.7	25.7	24.7	24.0	23.4	23.4	23.4	23.0
87.5°	11.7	12.0	12.0	12.0	11.7	11.4	10.7	10.0	10.4	10.7	10.7
90°	19.7	16.6	13.5	11.4	9.3	6.2	4.1	2.1	4.1	6.2	9.3
92.5°	159.5	104.6	71.5	52.8	42.5	33.2	22.8	15.5	22.8	33.2	42.5
95°	377.1	222.7	134.7	94.3	67.3	49.7	38.3	35.2	38.3	49.7	67.3
97.5°	419.6	240.4	153.3	108.8	81.8	66.3	57.0	55.9	57.0	66.3	81.8
100°	390.6	237.3	164.7	124.3	99.5	85.0	77.7	76.7	77.7	85.0	99.5
102.5°	365.7	241.4	178.2	141.9	120.2	106.7	100.5	98.4	100.5	106.7	120.2
105°	356.4	249.7	193.7	161.6	141.9	129.5	123.3	120.2	123.3	129.5	141.9
107.5°	354.3	263.2	213.4	183.4	164.7	152.3	146.1	143.0	146.1	152.3	164.7
110°	359.5	280.8	234.1	205.1	187.5	176.1	170.9	167.8	170.9	176.1	187.5





TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.9	298.4	255.9	227.9	210.3	198.9	193.7	190.6	193.7	198.9	210.3
115°	381.3	318.1	278.7	250.7	233.1	222.7	216.5	212.4	216.5	222.7	233.1
117.5°	395.8	338.8	299.4	273.5	253.8	244.5	239.3	234.1	239.3	244.5	253.8
120°	412.3	358.5	321.2	295.3	275.6	265.2	260.0	256.9	260.0	265.2	275.6
122.5°	427.9	379.2	342.9	315.0	296.3	284.9	279.7	276.6	279.7	284.9	296.3
125°	444.5	398.9	362.6	334.6	315.0	303.6	297.3	295.3	297.3	303.6	315.0
127.5°	457.9	416.5	381.3	353.3	331.5	320.1	312.9	309.8	312.9	320.1	331.5
130°	471.4	432.0	397.8	369.9	348.1	335.7	326.3	323.2	326.3	335.7	348.1
132.5°	483.8	445.5	412.3	385.4	363.6	348.1	337.7	333.6	337.7	348.1	363.6
135°	494.2	459.0	426.8	398.9	377.1	361.6	350.2	346.0	350.2	361.6	377.1
137.5°	502.5	468.3	437.2	411.3	389.5	373.0	361.6	357.4	361.6	373.0	389.5
140°	508.7	477.6	447.6	421.7	400.9	384.4	374.0	368.8	374.0	384.4	400.9
142.5°	514.9	484.9	455.9	432.0	411.3	396.8	385.4	381.3	385.4	396.8	411.3
145°	519.1	491.1	464.1	440.3	422.7	407.2	397.8	394.7	397.8	407.2	422.7
147.5°	522.2	496.3	471.4	450.7	433.1	419.6	410.3	408.2	410.3	419.6	433.1
150°	523.2	501.4	477.6	459.0	444.5	431.0	422.7	421.7	422.7	431.0	444.5
152.5°	525.3	504.5	484.9	467.3	454.8	443.4	435.1	435.1	435.1	443.4	454.8
155°	525.3	508.7	491.1	476.6	465.2	454.8	448.6	448.6	448.6	454.8	465.2
157.5°	526.3	510.8	496.3	484.9	474.5	465.2	460.0	459.0	460.0	465.2	474.5
160°	526.3	513.9	501.4	491.1	483.8	475.5	471.4	471.4	471.4	475.5	483.8
162.5°	525.3	514.9	504.5	496.3	490.0	483.8	480.7	480.7	480.7	483.8	490.0
165°	523.2	515.9	507.7	500.4	496.3	491.1	489.0	490.0	489.0	491.1	496.3
167.5°	522.2	515.9	509.7	504.5	501.4	497.3	496.3	497.3	496.3	497.3	501.4
170°	519.1	514.9	509.7	507.7	505.6	502.5	501.4	503.5	501.4	502.5	505.6
172.5°	518.0	514.9	510.8	509.7	508.7	506.6	506.6	507.7	506.6	506.6	508.7
175°	515.9	513.9	511.8	510.8	510.8	508.7	509.7	510.8	509.7	508.7	510.8
177.5°	514.9	512.8	511.8	511.8	511.8	510.8	511.8	512.8	511.8	510.8	511.8
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1381.2	1368.2	1355.2	1345.2	1335.1	1318.1	1301.1	1297.1	1293.1	1287.4	1281.7
5°	1309.8	1277.7	1245.6	1216.9	1188.2	1165.8	1143.4	1128.8	1114.1	1103.4	1092.7
7.5°	1226.3	1178.2	1130.1	1096.0	1062.0	1029.6	997.2	986.8	976.5	962.4	948.4
10°	1145.5	1092.4	1039.3	994.8	950.4	918.7	887.0	874.3	861.6	843.9	826.2
12.5°	1073.3	1015.2	957.1	912.4	867.6	836.9	806.2	787.8	769.4	759.4	749.4
15°	997.8	935.7	873.6	832.2	790.8	763.1	735.4	719.3	703.3	693.6	683.9
17.5°	931.1	869.6	808.2	768.4	728.7	703.3	677.9	663.9	649.9	642.5	635.2
20°	867.6	807.5	747.4	708.6	669.9	649.2	628.5	619.5	610.5	604.5	598.4
22.5°	809.5	750.4	691.3	658.2	625.2	608.5	591.8	585.4	579.1	574.1	569.1
25°	751.4	698.6	645.9	617.8	589.8	576.1	562.4	556.0	549.7	544.7	539.7
27.5°	704.0	653.5	603.1	579.1	555.0	544.3	533.7	528.6	523.6	519.0	514.3
30°	657.9	612.8	567.7	547.0	526.3	516.6	506.9	501.9	496.9	492.6	488.2
32.5°	615.1	576.4	537.7	518.6	499.6	491.6	483.6	477.5	471.5	468.2	464.9
35°	574.4	539.7	504.9	489.2	473.5	465.5	457.5	452.5	447.5	444.8	442.2
37.5°	539.7	508.6	477.5	462.5	447.5	439.8	432.1	427.8	423.4	422.4	421.4
40°	504.3	477.5	450.8	436.1	421.4	414.8	408.1	405.4	402.7	402.1	401.4
42.5°	474.9	448.8	422.8	409.4	396.1	390.4	384.7	383.4	382.0	383.0	384.0
45°	440.8	419.1	397.4	385.0	372.7	368.0	363.3	362.3	361.3	363.3	365.3
47.5°	412.1	392.1	372.0	360.3	348.6	345.3	342.0	341.6	341.3	344.0	346.6
50°	382.7	363.3	344.0	334.6	325.3	322.3	319.3	320.3	321.3	325.6	329.9
52.5°	355.3	337.3	319.3	310.6	301.9	299.9	297.9	300.2	302.6	307.2	311.9
55°	325.3	308.9	292.5	285.9	279.2	277.2	275.2	279.9	284.5	288.9	293.2
57.5°	296.5	282.2	267.8	261.8	255.8	255.5	255.1	259.5	263.8	268.5	273.2
60°	265.8	253.8	241.8	237.1	232.4	233.1	233.8	238.8	243.8	247.5	251.1
62.5°	237.8	227.8	217.7	213.4	209.1	210.7	212.4	217.4	222.4	226.8	231.1
65°	209.7	201.4	193.0	190.0	187.0	189.4	191.7	196.0	200.4	203.4	206.4
67.5°	183.0	176.0	169.0	166.6	164.3	166.6	169.0	173.3	177.7	180.7	183.7
70°	155.0	149.3	143.6	141.9	140.3	142.9	145.6	149.3	152.9	156.0	159.0
72.5°	128.9	124.6	120.2	119.9	119.6	121.9	124.2	127.9	131.6	133.6	135.6
75°	103.5	101.2	98.8	98.5	98.2	100.5	102.9	104.9	106.9	108.5	110.2
77.5°	80.8	78.8	76.8	77.1	77.5	79.1	80.8	82.8	84.8	85.8	86.8
80°	57.4	56.8	56.1	56.8	57.4	58.8	60.1	61.4	62.8	63.5	64.1
82.5°	39.4	38.7	38.1	39.1	40.1	41.1	42.1	43.1	44.1	44.4	44.7
85°	22.7	23.7	24.7	24.7	24.7	25.0	25.4	25.7	26.0	25.7	25.4
87.5°	10.7	11.0	11.4	11.4	11.4	11.7	12.0	12.0	12.0	11.7	11.4
90°	11.4	13.5	16.6	19.7	22.8	25.9	24.9	25.9	26.9	28.0	30.0
92.5°	52.8	71.5	104.6	159.5	213.4	192.7	144.0	102.6	79.8	69.4	62.2
95°	94.3	134.7	222.7	377.1	547.0	614.4	498.3	373.0	252.8	197.9	160.6
97.5°	108.8	153.3	240.4	419.6	705.5	944.9	977.0	856.8	646.5	509.7	391.6
100°	124.3	164.7	237.3	390.6	663.1	981.1	1185.2	1221.5	1137.6	1016.3	869.2
102.5°	141.9	178.2	241.4	365.7	600.9	913.8	1195.6	1342.7	1360.3	1302.3	1222.5
105°	161.6	193.7	249.7	356.4	552.2	833.0	1130.3	1346.8	1450.4	1470.1	1443.2
107.5°	183.4	213.4	263.2	354.3	517.0	761.5	1037.1	1284.7	1447.3	1528.1	1556.1
110°	205.1	234.1	280.8	359.5	498.3	702.4	950.0	1187.3	1377.9	1508.5	1581.0



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	227.9	255.9	298.4	369.9	488.0	663.1	874.4	1090.9	1286.8	1437.0	1535.4
115°	250.7	278.7	318.1	381.3	486.9	637.2	816.4	1008.1	1188.3	1340.6	1453.6
117.5°	273.5	299.4	338.8	395.8	488.0	619.5	778.1	943.8	1103.4	1243.2	1360.3
120°	295.3	321.2	358.5	412.3	492.1	608.2	749.1	895.1	1035.0	1159.3	1264.0
122.5°	315.0	342.9	379.2	427.9	499.4	600.9	725.2	856.8	980.1	1093.0	1188.3
125°	334.6	362.6	398.9	444.5	506.6	594.7	705.5	823.6	936.6	1036.0	1118.9
127.5°	353.3	381.3	416.5	457.9	514.9	591.6	686.9	793.6	896.2	987.3	1064.0
130°	369.9	397.8	432.0	471.4	523.2	588.5	672.4	765.6	858.9	942.8	1013.2
132.5°	385.4	412.3	445.5	483.8	529.4	587.4	658.9	739.7	823.6	900.3	966.6
135°	398.9	426.8	459.0	494.2	535.6	586.4	647.5	716.9	790.5	857.8	916.9
137.5°	411.3	437.2	468.3	502.5	539.8	584.3	637.2	695.2	757.3	817.4	870.3
140°	421.7	447.6	477.6	508.7	543.9	583.3	627.8	676.5	729.4	779.1	823.6
142.5°	432.0	455.9	484.9	514.9	547.0	581.2	619.5	658.9	702.4	743.9	781.2
145°	440.3	464.1	491.1	519.1	548.1	579.1	612.3	645.4	679.6	712.8	742.8
147.5°	450.7	471.4	496.3	522.2	548.1	576.0	605.0	634.1	662.0	690.0	711.8
150°	459.0	477.6	501.4	523.2	548.1	571.9	597.8	621.6	645.4	667.2	686.9
152.5°	467.3	484.9	504.5	525.3	545.0	566.7	589.5	610.2	629.9	648.6	664.1
155°	476.6	491.1	508.7	525.3	542.9	560.5	581.2	598.8	615.4	630.9	643.4
157.5°	484.9	496.3	510.8	526.3	539.8	555.3	571.9	586.4	600.9	613.3	623.7
160°	491.1	501.4	513.9	526.3	537.7	549.1	562.6	576.0	587.4	597.8	605.0
162.5°	496.3	504.5	514.9	525.3	533.6	542.9	553.2	563.6	572.9	582.2	588.5
165°	500.4	507.7	515.9	523.2	529.4	536.7	545.0	553.2	559.5	566.7	571.9
167.5°	504.5	509.7	515.9	522.2	525.3	530.4	536.7	543.9	549.1	553.2	557.4
170°	507.7	509.7	514.9	519.1	521.1	524.2	529.4	534.6	537.7	541.8	543.9
172.5°	509.7	510.8	514.9	518.0	518.0	519.1	522.2	526.3	528.4	531.5	532.5
175°	510.8	511.8	513.9	515.9	514.9	514.9	517.0	519.1	520.1	522.2	522.2
177.5°	511.8	511.8	512.8	514.9	512.8	511.8	512.8	513.9	514.9	515.9	515.9
180°	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8	511.8



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1439.3	1439.3	1439.3	1439.3
2.5°	1279.4	1277.0	1267.7	1258.3
5°	1084.7	1076.7	1074.0	1071.3
7.5°	947.8	947.1	933.1	919.0
10°	827.2	828.2	815.5	802.8
12.5°	741.0	732.7	731.7	730.7
15°	676.3	668.6	667.2	665.9
17.5°	630.5	625.8	624.5	623.2
20°	595.8	593.1	590.8	588.4
22.5°	565.7	562.4	560.4	558.4
25°	536.7	533.7	533.0	532.3
27.5°	510.6	506.9	506.9	506.9
30°	485.9	483.6	482.6	481.6
32.5°	462.9	460.9	460.9	460.9
35°	441.1	440.1	438.8	437.5
37.5°	421.4	421.4	420.8	420.1
40°	402.4	403.4	403.4	403.4
42.5°	385.0	386.0	386.0	386.0
45°	367.0	368.7	369.3	370.0
47.5°	349.3	352.0	352.7	353.3
50°	331.9	334.0	334.3	334.6
52.5°	314.2	316.6	318.3	319.9
55°	295.5	297.9	298.9	299.9
57.5°	275.5	277.8	278.2	278.5
60°	253.5	255.8	256.5	257.1
62.5°	232.4	233.8	234.4	235.1
65°	208.4	210.4	211.7	213.1
67.5°	185.3	187.0	187.0	187.0
70°	159.6	160.3	161.3	162.3
72.5°	135.9	136.3	136.3	136.3
75°	110.9	111.5	111.9	112.2
77.5°	87.2	87.5	87.5	87.5
80°	63.8	63.5	63.5	63.5
82.5°	43.7	42.7	42.7	42.7
85°	25.0	24.7	25.0	25.4
87.5°	11.4	11.4	11.4	11.4
90°	29.0	30.0	31.1	30.0
92.5°	60.1	55.9	57.0	54.9
95°	140.9	131.6	124.3	120.2
97.5°	322.2	282.8	258.0	246.6
100°	764.6	689.0	648.6	649.6
102.5°	1146.9	1090.9	1058.8	1028.8
105°	1395.5	1356.2	1323.0	1317.8
107.5°	1549.9	1531.3	1517.8	1506.4
110°	1610.0	1618.3	1616.2	1614.1



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1594.5	1624.5	1634.9	1635.9
115°	1531.3	1576.8	1597.6	1602.7
117.5°	1441.1	1491.9	1523.0	1530.2
120°	1345.8	1403.8	1428.7	1434.9
122.5°	1258.8	1309.5	1337.5	1345.8
125°	1185.2	1230.8	1256.7	1264.0
127.5°	1124.1	1163.5	1187.3	1193.5
130°	1068.1	1105.4	1127.2	1135.5
132.5°	1017.4	1054.7	1073.3	1078.5
135°	967.7	998.7	1017.4	1024.6
137.5°	913.8	945.9	961.4	967.7
140°	863.0	892.0	908.6	907.6
142.5°	813.3	838.1	852.7	851.6
145°	768.7	790.5	798.8	800.9
147.5°	732.5	748.0	756.3	757.3
150°	702.4	713.8	720.0	720.0
152.5°	675.5	685.9	689.0	689.0
155°	652.7	661.0	663.1	664.1
157.5°	632.0	638.2	640.3	640.3
160°	612.3	618.5	618.5	617.5
162.5°	592.6	597.8	597.8	596.8
165°	576.0	580.2	579.1	579.1
167.5°	559.5	562.6	561.5	561.5
170°	545.0	547.0	546.0	546.0
172.5°	532.5	534.6	532.5	531.5
175°	522.2	523.2	522.2	521.1
177.5°	514.9	515.9	513.9	513.9
180°	511.8	511.8	511.8	511.8



TEST NUMBER: P831500

CATALOG NUMBER: S123DIP-S560D1195U940-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.80	12.54	12.87	13.60	15.04	14.04	14.77	15.10	15.84	17.28
	3H	13.44	14.10	14.51	15.17	16.63	15.45	16.11	16.53	17.18	18.64
	4H	14.01	14.64	15.10	15.71	17.17	15.90	16.52	16.98	17.59	19.06
	6H	14.38	14.95	15.47	16.03	17.50	16.17	16.74	17.26	17.82	19.30
	8H	14.47	15.02	15.57	16.11	17.58	16.23	16.77	17.32	17.86	19.34
	12H	14.51	15.03	15.61	16.11	17.61	16.24	16.76	17.34	17.85	19.34
4H	2H	12.36	12.99	13.45	14.06	15.52	14.19	14.81	15.28	15.88	17.35
	3H	14.18	14.70	15.28	15.80	17.28	15.80	16.31	16.89	17.41	18.89
	4H	14.87	15.35	15.98	16.44	17.94	16.37	16.85	17.48	17.94	19.44
	6H	15.34	15.75	16.45	16.86	18.36	16.77	17.18	17.88	18.29	19.79
	8H	15.48	15.86	16.59	16.96	18.47	16.88	17.26	17.99	18.37	19.88
	12H	15.54	15.88	16.66	17.00	18.51	16.92	17.27	18.05	18.38	19.90
8H	4H	15.13	15.51	16.24	16.62	18.12	16.47	16.85	17.58	17.96	19.46
	6H	15.72	16.03	16.85	17.18	18.68	16.97	17.28	18.10	18.43	19.93
	8H	15.92	16.20	17.06	17.32	18.85	17.15	17.42	18.28	18.55	20.08
	12H	16.04	16.28	17.18	17.41	18.97	17.24	17.49	18.38	18.61	20.17
12H	4H	15.13	15.47	16.25	16.59	18.10	16.44	16.78	17.57	17.90	19.41
	6H	15.77	16.04	16.90	17.17	18.69	16.98	17.26	18.12	18.38	19.91
	8H	15.99	16.24	17.13	17.36	18.92	17.18	17.42	18.32	18.54	20.10