

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331993-935

Luminaire Tested: **S123DIP-S775D1195U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331993-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U935-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6529.7 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79		64	64	64		50	50	50	43
1	96	92	89	85	88	85	81	78	70	68	66		57	55	54		44	43	42	37
2	88	81	75	70	80	74	69	65	62	58	55		50	47	45		39	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46		44	41	38		35	33	31	27
4	74	63	55	49	67	58	51	46	48	43	39		40	36	33		31	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34		36	32	29		28	26	23	20
6	62	50	42	37	57	47	40	34	39	34	30		32	28	25		26	23	21	18
7	58	45	38	32	52	42	35	30	35	30	26		29	25	22		23	21	18	16
8	53	41	34	28	49	38	31	27	32	27	23		27	23	20		22	19	16	14
9	50	38	30	25	45	35	28	24	30	24	21		25	21	18		20	17	15	13
10	46	34	27	23	42	32	26	21	27	22	19		23	19	16		18	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10014	10014	10014	10014
5°	11943	10057	8912	10057
10°	14948	10006	8050	10006
15°	18333	9926	7494	9926
20°	21841	9800	7135	9800
25°	23192	9647	7056	9647
30°	19877	9536	7093	9536
35°	13825	9376	7167	9376
40°	10413	9190	7144	9190
45°	8645	8914	7054	8914
50°	7743	8348	6990	8348
55°	7240	7739	6902	7739
60°	6794	7102	6833	7102
65°	6383	6477	6612	6477
70°	5986	5759	6297	5759
75°	5361	5041	5772	5041
80°	4699	4135	4971	4135
85°	3680	3013	3335	3013



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.6	1.4
10°-20°	293.9	4.5
20°-30°	493.2	7.6
30°-40°	558.5	8.6
40°-50°	500.8	7.7
50°-60°	404.1	6.2
60°-70°	281.6	4.3
70°-80°	148.0	2.3
80°-90°	40.0	0.6
90°-100°	275.0	4.2
100°-110°	778.7	11.9
110°-120°	766.1	11.7
120°-130°	611.0	9.4
130°-140°	481.8	7.4
140°-150°	359.6	5.5
150°-160°	250.6	3.8
160°-170°	147.2	2.3
170°-180°	47.9	0.7
0°-30°	878.7	13.5
0°-40°	1437.2	22.0
0°-60°	2342.1	35.9
0°-90°	2811.8	43.1
90°-120°	1819.8	27.9
90°-150°	3272.2	50.1
90°-180°	3718.0	56.9
0°-180°	6529.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	930	930	930	930	930	
5°	1105	931	825	931	1105	115
15°	1645	891	672	891	1645	475
25°	1953	812	594	812	1953	856
35°	1052	714	545	714	1052	684
45°	568	586	463	586	568	449
55°	386	412	368	412	386	346
65°	251	254	260	254	251	250
75°	129	121	139	121	129	138
85°	30	24	27	24	30	36
90°	29	2	29	2	29	17
95°	116	34	116	34	116	209
105°	1272	116	1272	116	1272	1255
115°	1548	205	1548	205	1548	1504
125°	1220	285	1220	285	1220	1106
135°	989	334	989	334	989	767
145°	773	381	773	381	773	492
155°	641	433	641	433	641	299
165°	559	473	559	473	559	160
175°	503	493	503	493	503	49
180°	494	494	494	494	494	



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	987.3	986.6	984.8	986.3	983.3	979.4	979.0	975.4	964.9	964.2	961.4
5°	1105.3	1101.6	1101.2	1100.7	1094.4	1085.9	1069.6	1068.2	1046.6	1035.8	1022.8
7.5°	1257.9	1259.8	1253.3	1247.5	1228.2	1215.5	1198.1	1175.8	1149.3	1122.3	1104.3
10°	1367.6	1382.4	1364.0	1351.3	1339.6	1317.5	1291.8	1259.8	1227.9	1190.4	1162.0
12.5°	1485.1	1492.5	1488.8	1476.9	1458.6	1425.0	1379.5	1344.2	1314.7	1252.4	1227.3
15°	1645.2	1672.8	1655.2	1614.5	1615.5	1583.5	1524.0	1458.6	1423.9	1369.3	1295.0
17.5°	1815.8	1819.2	1811.7	1778.0	1755.4	1711.4	1656.5	1593.9	1523.5	1457.5	1378.6
20°	1906.7	1903.9	1888.2	1870.6	1831.9	1797.6	1737.7	1667.8	1577.6	1512.7	1426.6
22.5°	1957.1	1952.7	1945.2	1930.4	1898.2	1861.4	1807.6	1731.2	1645.5	1556.0	1456.6
25°	1952.7	1958.5	1959.4	1955.3	1944.1	1922.0	1879.6	1818.8	1733.1	1618.2	1514.5
27.5°	1776.0	1784.3	1808.4	1829.7	1853.6	1877.9	1874.7	1844.4	1781.1	1681.9	1555.1
30°	1599.2	1581.2	1625.8	1682.2	1720.5	1788.1	1826.0	1828.2	1792.6	1707.4	1583.9
32.5°	1354.0	1373.9	1393.6	1462.9	1546.7	1622.6	1698.0	1758.7	1765.6	1708.9	1600.9
35°	1052.1	1076.9	1112.9	1148.9	1239.2	1316.6	1449.1	1564.5	1656.5	1668.7	1602.4
37.5°	847.7	860.1	882.9	918.9	977.9	1069.9	1172.4	1318.3	1451.5	1550.6	1554.9
40°	741.1	744.7	770.3	797.8	845.6	921.4	1013.7	1142.6	1302.2	1440.6	1498.3
42.5°	661.0	668.9	679.8	706.2	744.2	801.2	887.2	993.7	1140.0	1299.2	1412.1
45°	567.9	577.0	583.8	601.3	628.4	666.7	726.6	824.0	935.3	1099.8	1251.7
47.5°	506.4	507.2	512.2	525.5	543.9	572.7	615.0	677.6	779.8	913.2	1069.2
50°	462.4	469.7	471.5	481.8	496.3	517.5	552.6	605.8	689.7	806.8	950.2
52.5°	431.4	433.6	438.7	446.2	458.7	475.3	505.8	547.4	613.2	713.1	844.9
55°	385.8	385.8	390.8	396.7	403.9	418.7	439.0	469.7	519.7	597.3	706.4
57.5°	343.6	345.9	349.4	351.2	357.3	367.2	384.1	407.4	444.7	504.4	591.1
60°	315.6	319.6	319.2	322.7	328.1	335.8	350.3	369.2	402.5	450.3	523.3
62.5°	291.0	290.8	290.7	295.0	300.4	307.7	317.0	333.5	361.8	404.2	466.3
65°	250.6	249.7	252.9	255.5	257.4	262.8	270.0	284.4	303.3	334.9	383.1
67.5°	214.7	212.2	213.9	214.7	217.8	222.1	228.8	237.7	252.8	278.1	314.4
70°	190.2	188.0	187.5	188.4	191.1	194.2	199.2	207.8	221.8	242.0	268.6
72.5°	165.0	163.4	163.3	165.3	166.6	168.7	172.2	180.0	191.1	206.4	231.2
75°	128.9	128.9	128.9	129.3	130.7	132.5	135.3	139.3	147.8	158.7	175.3
77.5°	96.6	96.5	96.0	95.9	97.9	98.8	99.4	103.1	107.9	115.2	127.3
80°	75.8	73.4	74.4	75.8	76.6	77.1	78.4	79.3	83.4	87.5	96.0
82.5°	56.2	54.3	54.5	56.7	56.8	57.3	58.6	59.8	61.4	65.1	69.7
85°	29.8	29.8	30.2	30.2	30.7	30.2	31.5	32.0	32.0	34.3	36.9
87.5°	16.6	16.1	16.3	16.4	16.3	16.2	16.4	16.5	16.7	17.2	17.0
90°	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2	116.1	153.9	169.3
95°	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2	481.1	593.2	528.2
97.5°	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7	983.5	919.3	673.0
100°	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4	1144.4	947.4	640.2
102.5°	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1	1152.4	895.4	592.2
105°	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5	1091.4	804.3	533.2
107.5°	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6	984.6	723.8	495.6
110°	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4	917.3	678.2	481.1



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9	858.9	647.8	473.2
115°	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4	788.2	615.2	470.2
117.5°	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9	745.6	596.0	472.0
120°	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3	723.2	587.2	475.2
122.5°	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7	704.8	581.6	480.8
125°	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3	681.2	574.2	489.1
127.5°	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9	660.5	570.6	498.8
130°	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3	649.2	568.2	505.1
132.5°	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3	638.9	567.4	510.0
135°	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2	625.3	566.2	517.2
137.5°	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6	613.4	564.0	522.0
140°	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2	606.2	563.2	525.2
142.5°	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6	599.8	561.6	527.6
145°	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2	591.2	559.2	529.2
147.5°	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8	582.8	555.4	529.2
150°	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2	577.2	552.2	529.2
152.5°	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4	570.8	548.2	526.8
155°	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2	561.2	541.2	524.2
157.5°	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2	550.4	535.0	520.8
160°	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2	543.2	530.2	519.2
162.5°	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6	536.0	525.4	516.0
165°	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2	526.2	518.1	511.2
167.5°	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4	516.8	511.0	506.4
170°	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2	511.2	506.2	503.2
172.5°	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8	505.6	502.1	500.8
175°	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2	499.2	497.1	497.1
177.5°	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8	495.0	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	959.2	956.3	953.4	948.4	944.1	937.9	936.1	933.9	927.5	921.7	917.4
5°	1017.8	1006.9	991.2	976.8	965.1	949.3	940.3	930.8	917.3	905.1	895.2
7.5°	1079.1	1057.8	1033.3	1006.8	982.1	958.3	939.1	922.0	903.0	885.1	871.2
10°	1127.7	1097.1	1062.9	1025.9	994.4	963.7	938.0	915.5	891.1	870.0	852.4
12.5°	1183.3	1137.9	1090.6	1045.8	1008.4	965.9	934.8	906.1	878.5	853.0	833.3
15°	1249.1	1191.4	1135.4	1073.7	1016.9	963.7	926.8	890.7	858.7	832.5	807.3
17.5°	1308.9	1243.5	1169.8	1094.8	1026.2	963.2	911.5	870.6	830.6	798.7	773.5
20°	1342.8	1268.4	1185.0	1107.1	1031.3	961.0	904.2	855.5	812.3	778.4	750.0
22.5°	1372.0	1285.0	1198.7	1115.3	1031.0	955.2	890.9	840.8	793.8	760.8	730.6
25°	1402.3	1298.1	1211.6	1113.8	1019.6	941.2	869.0	812.3	765.3	726.6	695.5
27.5°	1428.2	1297.3	1194.6	1089.3	1001.8	923.2	846.1	785.2	735.5	693.4	661.8
30°	1445.5	1299.1	1176.9	1072.8	984.5	903.3	828.5	767.2	714.9	672.1	642.3
32.5°	1456.4	1298.0	1160.7	1049.7	957.0	885.3	809.3	745.9	692.2	650.1	621.4
35°	1462.7	1290.0	1132.7	1002.0	912.7	842.9	779.4	713.5	657.2	617.9	585.6
37.5°	1450.1	1273.3	1100.3	956.1	858.3	789.5	736.1	680.0	626.1	582.9	555.0
40°	1430.2	1262.6	1075.0	923.6	820.8	754.6	709.0	654.0	600.8	559.8	533.6
42.5°	1392.3	1240.5	1047.2	887.5	781.9	715.6	673.7	627.8	577.4	538.9	512.8
45°	1299.9	1192.7	1005.6	833.4	724.4	655.8	618.9	585.6	540.0	502.6	480.0
47.5°	1171.7	1120.7	945.4	776.4	664.3	598.4	560.0	533.1	499.9	469.7	448.1
50°	1082.7	1061.5	904.7	737.4	624.3	559.8	522.9	498.5	474.7	444.4	424.6
52.5°	979.9	993.0	857.0	697.1	583.5	520.1	485.3	466.1	444.4	419.6	402.3
55°	835.3	882.5	774.8	629.2	522.9	462.4	429.6	412.4	399.8	381.3	366.4
57.5°	699.7	760.0	686.0	559.4	463.3	411.2	379.6	360.9	352.8	343.2	331.5
60°	619.3	678.8	622.5	512.5	423.3	373.7	345.7	329.9	321.8	315.0	305.1
62.5°	547.6	607.8	560.4	464.9	383.9	337.9	313.7	298.3	291.9	288.3	279.9
65°	448.9	500.8	469.2	390.8	327.7	287.1	265.0	254.3	248.4	247.0	241.6
67.5°	365.4	404.8	381.9	324.2	274.5	239.4	220.7	211.5	207.0	206.6	202.5
70°	310.6	347.5	329.9	277.7	234.9	207.3	191.1	183.0	180.3	179.9	177.6
72.5°	268.0	293.8	279.8	236.2	203.1	178.1	166.3	157.7	154.7	155.3	153.8
75°	198.3	217.7	209.6	179.4	152.8	136.6	126.7	121.2	118.6	119.9	118.1
77.5°	142.7	155.0	147.7	126.7	110.4	98.6	91.4	88.0	85.6	85.5	84.6
80°	107.7	114.9	110.9	98.2	84.7	74.8	69.0	66.7	65.3	64.9	64.5
82.5°	76.7	82.8	78.1	69.4	60.2	54.2	51.0	48.0	47.0	47.3	46.8
85°	38.7	41.0	39.2	33.8	30.2	27.5	25.7	24.4	23.4	23.8	23.0
87.5°	17.1	16.9	15.2	13.3	12.2	10.6	10.2	9.0	8.7	9.1	9.4
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4	18.4	26.8	34.6
95°	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0	37.0	48.0	65.0
97.5°	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0	59.0	67.6	82.4
100°	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0	75.0	82.1	96.0
102.5°	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8	92.6	98.8	112.0
105°	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1	119.1	125.0	137.1
107.5°	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8	145.9	151.6	163.4
110°	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0	165.1	170.0	181.1



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7	182.7	187.7	198.6
115°	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1	209.1	215.1	225.1
117.5°	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5	235.1	240.0	249.3
120°	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1	251.1	256.1	266.1
122.5°	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3	266.3	271.3	282.1
125°	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1	287.1	293.1	304.1
127.5°	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7	304.7	312.1	323.3
130°	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1	315.1	324.1	336.1
132.5°	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1	323.9	333.7	348.1
135°	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2	338.1	349.1	364.1
137.5°	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3	351.5	362.3	378.3
140°	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1	361.1	371.1	387.1
142.5°	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8	370.0	380.7	395.1
145°	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2	384.1	393.1	408.1
147.5°	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7	398.6	407.3	420.3
150°	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2	408.1	416.1	429.1
152.5°	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6	417.8	425.8	437.1
155°	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2	433.2	439.2	449.2
157.5°	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6	446.3	451.2	459.9
160°	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1	455.1	459.2	467.2
162.5°	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4	462.4	465.5	472.0
165°	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2	472.2	474.2	479.1
167.5°	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4	480.2	481.1	485.0
170°	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2	484.1	485.2	488.2
172.5°	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4	488.2	488.4	490.6
175°	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2	492.1	491.2	493.2
177.5°	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0	494.2	493.4	494.2
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	914.8	912.3	908.7	903.3	899.0	892.1	892.1	893.2	893.2	892.9	892.1
5°	887.1	880.3	872.2	862.7	852.8	842.9	841.1	837.5	834.8	833.0	830.7
7.5°	857.8	845.8	834.0	820.7	808.7	798.7	791.7	785.9	782.2	778.3	775.4
10°	837.9	823.0	809.1	795.1	779.8	767.7	760.0	754.6	750.5	746.9	745.1
12.5°	814.5	797.5	782.0	768.8	752.0	739.5	732.2	729.7	724.9	717.3	713.3
15°	780.2	764.5	746.0	725.7	717.6	702.2	693.7	689.7	686.9	681.1	679.2
17.5°	751.0	730.3	709.6	694.4	679.3	666.9	662.1	657.1	653.5	648.7	647.3
20°	727.5	709.0	690.1	673.9	658.1	644.5	640.5	636.9	633.3	631.0	629.2
22.5°	703.7	685.3	669.5	654.4	637.6	628.7	624.3	620.4	617.8	616.3	614.5
25°	670.3	654.0	636.5	622.9	609.4	603.6	600.8	598.6	596.8	594.5	594.1
27.5°	640.3	622.7	608.4	595.8	586.1	581.2	578.6	577.5	577.9	578.7	579.2
30°	617.9	601.8	590.0	579.2	570.2	565.7	565.2	565.2	567.1	567.5	568.4
32.5°	597.4	584.1	572.4	561.9	555.1	552.0	553.7	553.7	555.2	556.3	557.9
35°	567.5	555.8	546.7	537.8	531.9	533.2	534.2	535.0	537.3	540.0	541.8
37.5°	538.9	528.7	519.4	512.3	509.6	512.0	514.2	516.1	518.8	520.8	522.6
40°	518.3	510.7	501.7	495.3	496.3	497.7	499.5	501.7	503.9	505.3	507.1
42.5°	499.2	491.2	484.4	479.1	480.4	482.2	483.2	484.4	487.0	489.4	490.5
45°	470.1	463.8	457.5	454.3	455.3	456.2	457.0	458.4	460.6	462.4	463.0
47.5°	437.4	433.0	428.8	425.7	427.1	426.8	427.9	430.8	431.5	432.7	435.1
50°	416.5	412.4	407.5	406.6	406.6	406.6	407.0	410.6	410.6	412.4	414.2
52.5°	393.4	390.8	387.6	386.0	385.3	385.3	387.2	389.0	389.7	392.3	394.1
55°	359.2	356.5	353.9	352.5	351.5	352.5	356.1	357.0	359.2	360.6	362.0
57.5°	323.6	321.6	319.4	318.7	318.5	319.7	321.7	324.3	324.9	329.1	331.1
60°	300.2	297.0	295.2	295.2	294.4	298.4	297.5	302.0	302.9	305.6	308.8
62.5°	276.0	271.8	271.0	271.0	272.3	273.5	274.7	276.7	279.1	282.5	285.0
65°	237.1	234.9	238.0	237.5	236.6	239.4	239.4	241.6	244.3	247.5	252.4
67.5°	200.2	199.1	199.3	199.3	200.7	202.2	203.5	205.4	208.7	212.1	215.2
70°	175.3	176.7	174.4	176.2	177.6	178.1	178.9	181.7	185.3	187.5	191.1
72.5°	151.2	151.1	151.4	152.1	153.4	154.2	155.2	158.3	162.2	164.1	166.9
75°	116.3	115.8	117.2	117.2	119.4	120.4	121.2	122.6	126.2	128.9	131.1
77.5°	84.9	85.5	85.2	86.7	86.1	86.3	89.0	90.4	90.7	96.1	97.3
80°	64.0	64.9	65.3	65.8	66.3	65.3	68.5	69.8	69.8	73.0	75.3
82.5°	46.0	46.5	47.7	48.1	48.2	49.2	49.4	50.4	51.5	52.9	55.8
85°	23.0	24.4	24.8	24.4	24.8	23.8	25.2	25.7	26.2	26.2	26.2
87.5°	9.4	10.2	10.4	11.4	11.6	12.6	12.4	11.9	12.1	13.3	12.3
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	29.0
92.5°	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2	66.8	59.0	53.8
95°	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2	244.1	191.1	155.1
97.5°	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7	719.0	590.0	470.4
100°	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4	1098.4	981.4	839.3
102.5°	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1	1270.4	1202.2	1112.2
105°	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5	1400.5	1419.5	1393.5
107.5°	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6	1384.1	1471.7	1507.4
110°	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4	1330.5	1456.6	1526.6



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9	1260.1	1401.3	1491.3
115°	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4	1147.4	1294.4	1403.5
117.5°	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9	1052.1	1184.2	1294.9
120°	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3	999.4	1119.4	1220.5
122.5°	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7	956.9	1068.2	1162.0
125°	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3	904.3	1000.3	1080.4
127.5°	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9	858.1	944.7	1017.5
130°	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3	829.3	910.3	978.4
132.5°	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3	802.1	877.5	942.4
135°	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2	763.3	828.3	885.3
137.5°	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6	725.8	781.9	831.3
140°	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2	704.2	752.3	795.3
142.5°	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6	683.5	725.0	762.5
145°	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2	656.3	688.3	717.2
147.5°	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8	636.0	661.9	682.4
150°	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2	623.2	644.2	663.2
152.5°	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4	611.2	629.8	645.7
155°	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2	594.2	609.2	621.2
157.5°	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2	577.6	589.2	598.6
160°	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2	567.2	577.2	584.2
162.5°	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6	556.0	565.2	571.4
165°	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2	540.2	547.2	552.2
167.5°	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4	528.0	532.0	535.6
170°	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2	519.2	523.1	525.2
172.5°	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8	512.0	515.2	516.3
175°	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2	502.1	504.2	504.2
177.5°	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8	496.5	497.4	497.4
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	889.6	889.2	891.7	889.9	891.7	889.2	889.6	892.1	892.9	893.2	893.2
5°	828.0	829.4	824.8	824.8	824.8	829.4	828.0	830.7	833.0	834.8	837.5
7.5°	773.2	771.2	771.4	769.0	771.4	771.2	773.2	775.4	778.3	782.2	785.9
10°	739.7	737.0	736.1	736.5	736.1	737.0	739.7	745.1	746.9	750.5	754.6
12.5°	711.9	711.4	705.4	705.5	705.4	711.4	711.9	713.3	717.3	724.9	729.7
15°	679.2	670.7	669.8	672.5	669.8	670.7	679.2	679.2	681.1	686.9	689.7
17.5°	646.5	642.0	642.3	640.9	642.3	642.0	646.5	647.3	648.7	653.5	657.1
20°	629.2	626.5	626.1	622.9	626.1	626.5	629.2	629.2	631.0	633.3	636.9
22.5°	613.4	612.5	612.8	609.2	612.8	612.5	613.4	614.5	616.3	617.8	620.4
25°	593.7	595.9	594.1	594.1	594.1	595.9	593.7	594.1	594.5	596.8	598.6
27.5°	580.3	580.2	579.3	579.3	579.3	580.2	580.3	579.2	578.7	577.9	577.5
30°	570.2	569.7	570.7	570.7	570.7	569.7	570.2	568.4	567.5	567.1	565.2
32.5°	560.1	560.8	560.9	561.3	560.9	560.8	560.1	557.9	556.3	555.2	553.7
35°	544.5	544.9	546.3	545.4	546.3	544.9	544.5	541.8	540.0	537.3	535.0
37.5°	523.4	525.5	525.0	525.7	525.0	525.5	523.4	522.6	520.8	518.8	516.1
40°	507.6	508.9	508.4	508.4	508.4	508.9	507.6	507.1	505.3	503.9	501.7
42.5°	491.3	492.3	491.1	490.4	491.1	492.3	491.3	490.5	489.4	487.0	484.4
45°	464.7	463.8	465.2	463.4	465.2	463.8	464.7	463.0	462.4	460.6	458.4
47.5°	435.0	435.8	436.3	437.6	436.3	435.8	435.0	435.1	432.7	431.5	430.8
50°	415.2	417.8	417.8	417.4	417.8	417.8	415.2	414.2	412.4	410.6	410.6
52.5°	395.6	396.9	398.7	398.6	398.7	396.9	395.6	394.1	392.3	389.7	389.0
55°	365.6	366.4	367.4	367.8	367.4	366.4	365.6	362.0	360.6	359.2	357.0
57.5°	334.3	334.0	336.1	336.8	336.1	334.0	334.3	331.1	329.1	324.9	324.3
60°	312.4	312.4	316.0	317.4	316.0	312.4	312.4	308.8	305.6	302.9	302.0
62.5°	289.0	290.4	293.9	292.1	293.9	290.4	289.0	285.0	282.5	279.1	276.7
65°	254.7	258.3	257.9	259.6	257.9	258.3	254.7	252.4	247.5	244.3	241.6
67.5°	218.9	221.1	224.4	224.6	224.4	221.1	218.9	215.2	212.1	208.7	205.4
70°	194.8	197.0	198.8	200.1	198.8	197.0	194.8	191.1	187.5	185.3	181.7
72.5°	171.3	172.5	176.8	174.9	176.8	172.5	171.3	166.9	164.1	162.2	158.3
75°	134.3	137.5	140.2	138.8	140.2	137.5	134.3	131.1	128.9	126.2	122.6
77.5°	99.4	102.5	103.8	102.6	103.8	102.5	99.4	97.3	96.1	90.7	90.4
80°	78.4	78.0	80.7	80.2	80.7	78.0	78.4	75.3	73.0	69.8	69.8
82.5°	57.5	57.1	58.3	58.6	58.3	57.1	57.5	55.8	52.9	51.5	50.4
85°	28.0	29.3	27.5	27.0	27.5	29.3	28.0	26.2	26.2	26.2	25.7
87.5°	12.1	12.3	12.1	11.5	12.1	12.3	12.1	12.3	13.3	12.1	11.9
90°	28.0	29.0	30.0	29.0	30.0	29.0	28.0	29.0	27.0	26.0	25.0
92.5°	52.0	49.0	50.0	48.2	50.0	49.0	52.0	53.8	59.0	66.8	84.2
95°	136.0	127.1	120.0	116.1	120.0	127.1	136.0	155.1	191.1	244.1	360.2
97.5°	396.6	351.5	324.5	315.9	324.5	351.5	396.6	470.4	590.0	719.0	897.7
100°	738.2	665.2	626.2	627.2	626.2	665.2	738.2	839.3	981.4	1098.4	1179.4
102.5°	1033.5	975.8	943.1	920.2	943.1	975.8	1033.5	1112.2	1202.2	1270.4	1273.1
105°	1347.5	1309.5	1277.5	1272.5	1277.5	1309.5	1347.5	1393.5	1419.5	1400.5	1300.5
107.5°	1508.1	1495.3	1484.5	1475.3	1484.5	1495.3	1508.1	1507.4	1471.7	1384.1	1221.6
110°	1554.5	1562.5	1560.6	1558.6	1560.6	1562.5	1554.5	1526.6	1456.6	1330.5	1146.4



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1542.6	1567.4	1574.9	1575.4	1574.9	1567.4	1542.6	1491.3	1401.3	1260.1	1071.9
115°	1478.5	1522.5	1542.6	1547.6	1542.6	1522.5	1478.5	1403.5	1294.4	1147.4	973.4
117.5°	1373.1	1423.5	1452.3	1459.1	1452.3	1423.5	1373.1	1294.9	1184.2	1052.1	901.9
120°	1299.4	1355.5	1379.5	1385.5	1379.5	1355.5	1299.4	1220.5	1119.4	999.4	864.3
122.5°	1232.3	1282.6	1309.1	1316.6	1309.1	1282.6	1232.3	1162.0	1068.2	956.9	834.7
125°	1144.4	1188.4	1213.4	1220.5	1213.4	1188.4	1144.4	1080.4	1000.3	904.3	795.3
127.5°	1074.6	1112.2	1134.8	1141.2	1134.8	1112.2	1074.6	1017.5	944.7	858.1	760.9
130°	1031.4	1067.4	1088.4	1096.4	1088.4	1067.4	1031.4	978.4	910.3	829.3	739.3
132.5°	992.1	1028.1	1046.8	1052.4	1046.8	1028.1	992.1	942.4	877.5	802.1	719.3
135°	934.4	964.3	982.3	989.4	982.3	964.3	934.4	885.3	828.3	763.3	692.2
137.5°	872.5	902.9	918.1	922.7	918.1	902.9	872.5	831.3	781.9	725.8	667.6
140°	833.3	861.3	877.3	876.3	877.3	861.3	833.3	795.3	752.3	704.2	653.2
142.5°	794.9	819.7	834.1	833.1	834.1	819.7	794.9	762.5	725.0	683.5	639.6
145°	742.3	763.3	771.3	773.3	771.3	763.3	742.3	717.2	688.3	656.3	623.2
147.5°	701.5	715.7	723.2	724.0	723.2	715.7	701.5	682.4	661.9	636.0	609.8
150°	678.2	689.2	695.3	695.3	695.3	689.2	678.2	663.2	644.2	623.2	600.2
152.5°	657.5	667.6	671.2	671.2	671.2	667.6	657.5	645.7	629.8	611.2	591.4
155°	630.3	638.3	640.2	641.2	640.2	638.3	630.3	621.2	609.2	594.2	578.2
157.5°	606.4	612.4	614.0	613.8	614.0	612.4	606.4	598.6	589.2	577.6	564.2
160°	591.2	597.2	597.2	596.2	597.2	597.2	591.2	584.2	577.2	567.2	556.2
162.5°	576.0	581.2	581.2	580.2	581.2	581.2	576.0	571.4	565.2	556.0	546.6
165°	556.2	560.2	559.2	559.2	559.2	560.2	556.2	552.2	547.2	540.2	534.2
167.5°	537.4	540.2	539.2	539.2	539.2	540.2	537.4	535.6	532.0	528.0	523.4
170°	526.2	528.2	527.2	527.2	527.2	528.2	526.2	525.2	523.1	519.2	516.2
172.5°	516.6	518.6	516.8	516.0	516.8	518.6	516.6	516.3	515.2	512.0	509.8
175°	504.2	505.1	504.2	503.2	504.2	505.1	504.2	504.2	504.2	502.1	501.2
177.5°	496.5	497.4	495.8	495.8	495.8	497.4	496.5	497.4	497.4	496.5	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	892.1	892.1	899.0	903.3	908.7	912.3	914.8	917.4	921.7	927.5	933.9
5°	841.1	842.9	852.8	862.7	872.2	880.3	887.1	895.2	905.1	917.3	930.8
7.5°	791.7	798.7	808.7	820.7	834.0	845.8	857.8	871.2	885.1	903.0	922.0
10°	760.0	767.7	779.8	795.1	809.1	823.0	837.9	852.4	870.0	891.1	915.5
12.5°	732.2	739.5	752.0	768.8	782.0	797.5	814.5	833.3	853.0	878.5	906.1
15°	693.7	702.2	717.6	725.7	746.0	764.5	780.2	807.3	832.5	858.7	890.7
17.5°	662.1	666.9	679.3	694.4	709.6	730.3	751.0	773.5	798.7	830.6	870.6
20°	640.5	644.5	658.1	673.9	690.1	709.0	727.5	750.0	778.4	812.3	855.5
22.5°	624.3	628.7	637.6	654.4	669.5	685.3	703.7	730.6	760.8	793.8	840.8
25°	600.8	603.6	609.4	622.9	636.5	654.0	670.3	695.5	726.6	765.3	812.3
27.5°	578.6	581.2	586.1	595.8	608.4	622.7	640.3	661.8	693.4	735.5	785.2
30°	565.2	565.7	570.2	579.2	590.0	601.8	617.9	642.3	672.1	714.9	767.2
32.5°	553.7	552.0	555.1	561.9	572.4	584.1	597.4	621.4	650.1	692.2	745.9
35°	534.2	533.2	531.9	537.8	546.7	555.8	567.5	585.6	617.9	657.2	713.5
37.5°	514.2	512.0	509.6	512.3	519.4	528.7	538.9	555.0	582.9	626.1	680.0
40°	499.5	497.7	496.3	495.3	501.7	510.7	518.3	533.6	559.8	600.8	654.0
42.5°	483.2	482.2	480.4	479.1	484.4	491.2	499.2	512.8	538.9	577.4	627.8
45°	457.0	456.2	455.3	454.3	457.5	463.8	470.1	480.0	502.6	540.0	585.6
47.5°	427.9	426.8	427.1	425.7	428.8	433.0	437.4	448.1	469.7	499.9	533.1
50°	407.0	406.6	406.6	406.6	407.5	412.4	416.5	424.6	444.4	474.7	498.5
52.5°	387.2	385.3	385.3	386.0	387.6	390.8	393.4	402.3	419.6	444.4	466.1
55°	356.1	352.5	351.5	352.5	353.9	356.5	359.2	366.4	381.3	399.8	412.4
57.5°	321.7	319.7	318.5	318.7	319.4	321.6	323.6	331.5	343.2	352.8	360.9
60°	297.5	298.4	294.4	295.2	295.2	297.0	300.2	305.1	315.0	321.8	329.9
62.5°	274.7	273.5	272.3	271.0	271.0	271.8	276.0	279.9	288.3	291.9	298.3
65°	239.4	239.4	236.6	237.5	238.0	234.9	237.1	241.6	247.0	248.4	254.3
67.5°	203.5	202.2	200.7	199.3	199.3	199.1	200.2	202.5	206.6	207.0	211.5
70°	178.9	178.1	177.6	176.2	174.4	176.7	175.3	177.6	179.9	180.3	183.0
72.5°	155.2	154.2	153.4	152.1	151.4	151.1	151.2	153.8	155.3	154.7	157.7
75°	121.2	120.4	119.4	117.2	117.2	115.8	116.3	118.1	119.9	118.6	121.2
77.5°	89.0	86.3	86.1	86.7	85.2	85.5	84.9	84.6	85.5	85.6	88.0
80°	68.5	65.3	66.3	65.8	65.3	64.9	64.0	64.5	64.9	65.3	66.7
82.5°	49.4	49.2	48.2	48.1	47.7	46.5	46.0	46.8	47.3	47.0	48.0
85°	25.2	23.8	24.8	24.4	24.8	24.4	23.0	23.0	23.8	23.4	24.4
87.5°	12.4	12.6	11.6	11.4	10.4	10.2	9.4	9.4	9.1	8.7	9.0
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	116.1	153.9	169.3	127.1	84.0	57.9	43.0	34.6	26.8	18.4	12.4
95°	481.1	593.2	528.2	364.1	215.1	130.0	91.0	65.0	48.0	37.0	34.0
97.5°	983.5	919.3	673.0	399.5	231.5	150.2	108.1	82.4	67.6	59.0	58.0
100°	1144.4	947.4	640.2	377.1	229.1	159.0	120.0	96.0	82.1	75.0	74.0
102.5°	1152.4	895.4	592.2	357.9	232.3	169.4	133.6	112.0	98.8	92.6	90.8
105°	1091.4	804.3	533.2	344.1	241.1	187.1	156.0	137.1	125.0	119.1	116.1
107.5°	984.6	723.8	495.6	343.1	257.5	210.1	181.2	163.4	151.6	145.9	142.8
110°	917.3	678.2	481.1	347.2	271.1	226.1	198.0	181.1	170.0	165.1	162.0



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	858.9	647.8	473.2	355.2	284.7	242.9	215.7	198.6	187.7	182.7	179.7
115°	788.2	615.2	470.2	368.2	307.1	269.1	242.1	225.1	215.1	209.1	205.1
117.5°	745.6	596.0	472.0	385.3	330.9	293.3	268.3	249.3	240.0	235.1	230.5
120°	723.2	587.2	475.2	398.1	346.1	310.1	285.1	266.1	256.1	251.1	248.1
122.5°	704.8	581.6	480.8	410.2	362.1	326.9	300.3	282.1	271.3	266.3	263.3
125°	681.2	574.2	489.1	429.1	385.1	350.1	323.1	304.1	293.1	287.1	285.1
127.5°	660.5	570.6	498.8	444.8	405.1	371.3	344.3	323.3	312.1	304.7	301.7
130°	649.2	568.2	505.1	455.1	417.2	384.1	357.1	336.1	324.1	315.1	312.1
132.5°	638.9	567.4	510.0	464.8	427.6	395.4	369.1	348.1	333.7	323.9	320.1
135°	625.3	566.2	517.2	477.2	443.2	412.2	385.1	364.1	349.1	338.1	334.2
137.5°	613.4	564.0	522.0	486.4	453.9	424.1	399.2	378.3	362.3	351.5	347.3
140°	606.2	563.2	525.2	491.2	461.2	432.1	407.2	387.1	371.1	361.1	356.1
142.5°	599.8	561.6	527.6	495.9	466.7	438.6	415.2	395.1	380.7	370.0	365.8
145°	591.2	559.2	529.2	501.2	474.2	448.2	425.2	408.1	393.1	384.1	381.2
147.5°	582.8	555.4	529.2	504.4	480.2	456.3	436.8	420.3	407.3	398.6	396.7
150°	577.2	552.2	529.2	505.1	484.1	461.2	443.2	429.1	416.1	408.1	407.2
152.5°	570.8	548.2	526.8	506.8	486.6	466.7	449.5	437.1	425.8	417.8	417.6
155°	561.2	541.2	524.2	507.2	491.2	474.2	460.1	449.2	439.2	433.2	433.2
157.5°	550.4	535.0	520.8	508.2	493.8	480.2	469.3	459.9	451.2	446.3	445.6
160°	543.2	530.2	519.2	508.2	496.2	484.1	474.2	467.2	459.2	455.1	455.1
162.5°	536.0	525.4	516.0	507.4	497.0	486.6	478.2	472.0	465.5	462.4	462.4
165°	526.2	518.1	511.2	505.1	498.2	490.2	483.2	479.1	474.2	472.2	473.2
167.5°	516.8	511.0	506.4	503.6	498.0	492.1	487.8	485.0	481.1	480.2	481.4
170°	511.2	506.2	503.2	501.2	497.1	492.1	490.2	488.2	485.2	484.1	486.2
172.5°	505.6	502.1	500.8	500.4	497.1	493.0	491.8	490.6	488.4	488.2	489.4
175°	499.2	497.1	497.1	498.2	496.2	494.2	493.2	493.2	491.2	492.1	493.2
177.5°	495.0	494.2	495.0	496.5	495.0	494.2	494.2	494.2	493.4	494.2	495.0
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	936.1	937.9	944.1	948.4	953.4	956.3	959.2	961.4	964.2	964.9	975.4
5°	940.3	949.3	965.1	976.8	991.2	1006.9	1017.8	1022.8	1035.8	1046.6	1068.2
7.5°	939.1	958.3	982.1	1006.8	1033.3	1057.8	1079.1	1104.3	1122.3	1149.3	1175.8
10°	938.0	963.7	994.4	1025.9	1062.9	1097.1	1127.7	1162.0	1190.4	1227.9	1259.8
12.5°	934.8	965.9	1008.4	1045.8	1090.6	1137.9	1183.3	1227.3	1252.4	1314.7	1344.2
15°	926.8	963.7	1016.9	1073.7	1135.4	1191.4	1249.1	1295.0	1369.3	1423.9	1458.6
17.5°	911.5	963.2	1026.2	1094.8	1169.8	1243.5	1308.9	1378.6	1457.5	1523.5	1593.9
20°	904.2	961.0	1031.3	1107.1	1185.0	1268.4	1342.8	1426.6	1512.7	1577.6	1667.8
22.5°	890.9	955.2	1031.0	1115.3	1198.7	1285.0	1372.0	1456.6	1556.0	1645.5	1731.2
25°	869.0	941.2	1019.6	1113.8	1211.6	1298.1	1402.3	1514.5	1618.2	1733.1	1818.8
27.5°	846.1	923.2	1001.8	1089.3	1194.6	1297.3	1428.2	1555.1	1681.9	1781.1	1844.4
30°	828.5	903.3	984.5	1072.8	1176.9	1299.1	1445.5	1583.9	1707.4	1792.6	1828.2
32.5°	809.3	885.3	957.0	1049.7	1160.7	1298.0	1456.4	1600.9	1708.9	1765.6	1758.7
35°	779.4	842.9	912.7	1002.0	1132.7	1290.0	1462.7	1602.4	1668.7	1656.5	1564.5
37.5°	736.1	789.5	858.3	956.1	1100.3	1273.3	1450.1	1554.9	1550.6	1451.5	1318.3
40°	709.0	754.6	820.8	923.6	1075.0	1262.6	1430.2	1498.3	1440.6	1302.2	1142.6
42.5°	673.7	715.6	781.9	887.5	1047.2	1240.5	1392.3	1412.1	1299.2	1140.0	993.7
45°	618.9	655.8	724.4	833.4	1005.6	1192.7	1299.9	1251.7	1099.8	935.3	824.0
47.5°	560.0	598.4	664.3	776.4	945.4	1120.7	1171.7	1069.2	913.2	779.8	677.6
50°	522.9	559.8	624.3	737.4	904.7	1061.5	1082.7	950.2	806.8	689.7	605.8
52.5°	485.3	520.1	583.5	697.1	857.0	993.0	979.9	844.9	713.1	613.2	547.4
55°	429.6	462.4	522.9	629.2	774.8	882.5	835.3	706.4	597.3	519.7	469.7
57.5°	379.6	411.2	463.3	559.4	686.0	760.0	699.7	591.1	504.4	444.7	407.4
60°	345.7	373.7	423.3	512.5	622.5	678.8	619.3	523.3	450.3	402.5	369.2
62.5°	313.7	337.9	383.9	464.9	560.4	607.8	547.6	466.3	404.2	361.8	333.5
65°	265.0	287.1	327.7	390.8	469.2	500.8	448.9	383.1	334.9	303.3	284.4
67.5°	220.7	239.4	274.5	324.2	381.9	404.8	365.4	314.4	278.1	252.8	237.7
70°	191.1	207.3	234.9	277.7	329.9	347.5	310.6	268.6	242.0	221.8	207.8
72.5°	166.3	178.1	203.1	236.2	279.8	293.8	268.0	231.2	206.4	191.1	180.0
75°	126.7	136.6	152.8	179.4	209.6	217.7	198.3	175.3	158.7	147.8	139.3
77.5°	91.4	98.6	110.4	126.7	147.7	155.0	142.7	127.3	115.2	107.9	103.1
80°	69.0	74.8	84.7	98.2	110.9	114.9	107.7	96.0	87.5	83.4	79.3
82.5°	51.0	54.2	60.2	69.4	78.1	82.8	76.7	69.7	65.1	61.4	59.8
85°	25.7	27.5	30.2	33.8	39.2	41.0	38.7	36.9	34.3	32.0	32.0
87.5°	10.2	10.6	12.2	13.3	15.2	16.9	17.1	17.0	17.2	16.7	16.5
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.6	43.0	57.9	84.0	127.1	169.3	153.9	116.1	84.2
95°	37.0	48.0	65.0	91.0	130.0	215.1	364.1	528.2	593.2	481.1	360.2
97.5°	59.0	67.6	82.4	108.1	150.2	231.5	399.5	673.0	919.3	983.5	897.7
100°	75.0	82.1	96.0	120.0	159.0	229.1	377.1	640.2	947.4	1144.4	1179.4
102.5°	92.6	98.8	112.0	133.6	169.4	232.3	357.9	592.2	895.4	1152.4	1273.1
105°	119.1	125.0	137.1	156.0	187.1	241.1	344.1	533.2	804.3	1091.4	1300.5
107.5°	145.9	151.6	163.4	181.2	210.1	257.5	343.1	495.6	723.8	984.6	1221.6
110°	165.1	170.0	181.1	198.0	226.1	271.1	347.2	481.1	678.2	917.3	1146.4



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.7	187.7	198.6	215.7	242.9	284.7	355.2	473.2	647.8	858.9	1071.9
115°	209.1	215.1	225.1	242.1	269.1	307.1	368.2	470.2	615.2	788.2	973.4
117.5°	235.1	240.0	249.3	268.3	293.3	330.9	385.3	472.0	596.0	745.6	901.9
120°	251.1	256.1	266.1	285.1	310.1	346.1	398.1	475.2	587.2	723.2	864.3
122.5°	266.3	271.3	282.1	300.3	326.9	362.1	410.2	480.8	581.6	704.8	834.7
125°	287.1	293.1	304.1	323.1	350.1	385.1	429.1	489.1	574.2	681.2	795.3
127.5°	304.7	312.1	323.3	344.3	371.3	405.1	444.8	498.8	570.6	660.5	760.9
130°	315.1	324.1	336.1	357.1	384.1	417.2	455.1	505.1	568.2	649.2	739.3
132.5°	323.9	333.7	348.1	369.1	395.4	427.6	464.8	510.0	567.4	638.9	719.3
135°	338.1	349.1	364.1	385.1	412.2	443.2	477.2	517.2	566.2	625.3	692.2
137.5°	351.5	362.3	378.3	399.2	424.1	453.9	486.4	522.0	564.0	613.4	667.6
140°	361.1	371.1	387.1	407.2	432.1	461.2	491.2	525.2	563.2	606.2	653.2
142.5°	370.0	380.7	395.1	415.2	438.6	466.7	495.9	527.6	561.6	599.8	639.6
145°	384.1	393.1	408.1	425.2	448.2	474.2	501.2	529.2	559.2	591.2	623.2
147.5°	398.6	407.3	420.3	436.8	456.3	480.2	504.4	529.2	555.4	582.8	609.8
150°	408.1	416.1	429.1	443.2	461.2	484.1	505.1	529.2	552.2	577.2	600.2
152.5°	417.8	425.8	437.1	449.5	466.7	486.6	506.8	526.8	548.2	570.8	591.4
155°	433.2	439.2	449.2	460.1	474.2	491.2	507.2	524.2	541.2	561.2	578.2
157.5°	446.3	451.2	459.9	469.3	480.2	493.8	508.2	520.8	535.0	550.4	564.2
160°	455.1	459.2	467.2	474.2	484.1	496.2	508.2	519.2	530.2	543.2	556.2
162.5°	462.4	465.5	472.0	478.2	486.6	497.0	507.4	516.0	525.4	536.0	546.6
165°	472.2	474.2	479.1	483.2	490.2	498.2	505.1	511.2	518.1	526.2	534.2
167.5°	480.2	481.1	485.0	487.8	492.1	498.0	503.6	506.4	511.0	516.8	523.4
170°	484.1	485.2	488.2	490.2	492.1	497.1	501.2	503.2	506.2	511.2	516.2
172.5°	488.2	488.4	490.6	491.8	493.0	497.1	500.4	500.8	502.1	505.6	509.8
175°	492.1	491.2	493.2	493.2	494.2	496.2	498.2	497.1	497.1	499.2	501.2
177.5°	494.2	493.4	494.2	494.2	494.2	495.0	496.5	495.0	494.2	495.0	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2	494.2



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	930.3	930.3	930.3	930.3	930.3	930.3	930.3
2.5°	979.0	979.4	983.3	986.3	984.8	986.6	987.3
5°	1069.6	1085.9	1094.4	1100.7	1101.2	1101.6	1105.3
7.5°	1198.1	1215.5	1228.2	1247.5	1253.3	1259.8	1257.9
10°	1291.8	1317.5	1339.6	1351.3	1364.0	1382.4	1367.6
12.5°	1379.5	1425.0	1458.6	1476.9	1488.8	1492.5	1485.1
15°	1524.0	1583.5	1615.5	1614.5	1655.2	1672.8	1645.2
17.5°	1656.5	1711.4	1755.4	1778.0	1811.7	1819.2	1815.8
20°	1737.7	1797.6	1831.9	1870.6	1888.2	1903.9	1906.7
22.5°	1807.6	1861.4	1898.2	1930.4	1945.2	1952.7	1957.1
25°	1879.6	1922.0	1944.1	1955.3	1959.4	1958.5	1952.7
27.5°	1874.7	1877.9	1853.6	1829.7	1808.4	1784.3	1776.0
30°	1826.0	1788.1	1720.5	1682.2	1625.8	1581.2	1599.2
32.5°	1698.0	1622.6	1546.7	1462.9	1393.6	1373.9	1354.0
35°	1449.1	1316.6	1239.2	1148.9	1112.9	1076.9	1052.1
37.5°	1172.4	1069.9	977.9	918.9	882.9	860.1	847.7
40°	1013.7	921.4	845.6	797.8	770.3	744.7	741.1
42.5°	887.2	801.2	744.2	706.2	679.8	668.9	661.0
45°	726.6	666.7	628.4	601.3	583.8	577.0	567.9
47.5°	615.0	572.7	543.9	525.5	512.2	507.2	506.4
50°	552.6	517.5	496.3	481.8	471.5	469.7	462.4
52.5°	505.8	475.3	458.7	446.2	438.7	433.6	431.4
55°	439.0	418.7	403.9	396.7	390.8	385.8	385.8
57.5°	384.1	367.2	357.3	351.2	349.4	345.9	343.6
60°	350.3	335.8	328.1	322.7	319.2	319.6	315.6
62.5°	317.0	307.7	300.4	295.0	290.7	290.8	291.0
65°	270.0	262.8	257.4	255.5	252.9	249.7	250.6
67.5°	228.8	222.1	217.8	214.7	213.9	212.2	214.7
70°	199.2	194.2	191.1	188.4	187.5	188.0	190.2
72.5°	172.2	168.7	166.6	165.3	163.3	163.4	165.0
75°	135.3	132.5	130.7	129.3	128.9	128.9	128.9
77.5°	99.4	98.8	97.9	95.9	96.0	96.5	96.6
80°	78.4	77.1	76.6	75.8	74.4	73.4	75.8
82.5°	58.6	57.3	56.8	56.7	54.5	54.3	56.2
85°	31.5	30.2	30.7	30.2	30.2	29.8	29.8
87.5°	16.4	16.2	16.3	16.4	16.3	16.1	16.6
90°	26.0	27.0	29.0	28.0	29.0	30.0	29.0
92.5°	66.8	59.0	53.8	52.0	49.0	50.0	48.2
95°	244.1	191.1	155.1	136.0	127.1	120.0	116.1
97.5°	719.0	590.0	470.4	396.6	351.5	324.5	315.9
100°	1098.4	981.4	839.3	738.2	665.2	626.2	627.2
102.5°	1270.4	1202.2	1112.2	1033.5	975.8	943.1	920.2
105°	1400.5	1419.5	1393.5	1347.5	1309.5	1277.5	1272.5
107.5°	1384.1	1471.7	1507.4	1508.1	1495.3	1484.5	1475.3
110°	1330.5	1456.6	1526.6	1554.5	1562.5	1560.6	1558.6



TEST NUMBER: P331993-935

CATALOG NUMBER: S123DIP-S775D1195U935-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1260.1	1401.3	1491.3	1542.6	1567.4	1574.9	1575.4
115°	1147.4	1294.4	1403.5	1478.5	1522.5	1542.6	1547.6
117.5°	1052.1	1184.2	1294.9	1373.1	1423.5	1452.3	1459.1
120°	999.4	1119.4	1220.5	1299.4	1355.5	1379.5	1385.5
122.5°	956.9	1068.2	1162.0	1232.3	1282.6	1309.1	1316.6
125°	904.3	1000.3	1080.4	1144.4	1188.4	1213.4	1220.5
127.5°	858.1	944.7	1017.5	1074.6	1112.2	1134.8	1141.2
130°	829.3	910.3	978.4	1031.4	1067.4	1088.4	1096.4
132.5°	802.1	877.5	942.4	992.1	1028.1	1046.8	1052.4
135°	763.3	828.3	885.3	934.4	964.3	982.3	989.4
137.5°	725.8	781.9	831.3	872.5	902.9	918.1	922.7
140°	704.2	752.3	795.3	833.3	861.3	877.3	876.3
142.5°	683.5	725.0	762.5	794.9	819.7	834.1	833.1
145°	656.3	688.3	717.2	742.3	763.3	771.3	773.3
147.5°	636.0	661.9	682.4	701.5	715.7	723.2	724.0
150°	623.2	644.2	663.2	678.2	689.2	695.3	695.3
152.5°	611.2	629.8	645.7	657.5	667.6	671.2	671.2
155°	594.2	609.2	621.2	630.3	638.3	640.2	641.2
157.5°	577.6	589.2	598.6	606.4	612.4	614.0	613.8
160°	567.2	577.2	584.2	591.2	597.2	597.2	596.2
162.5°	556.0	565.2	571.4	576.0	581.2	581.2	580.2
165°	540.2	547.2	552.2	556.2	560.2	559.2	559.2
167.5°	528.0	532.0	535.6	537.4	540.2	539.2	539.2
170°	519.2	523.1	525.2	526.2	528.2	527.2	527.2
172.5°	512.0	515.2	516.3	516.6	518.6	516.8	516.0
175°	502.1	504.2	504.2	504.2	505.1	504.2	503.2
177.5°	496.5	497.4	497.4	496.5	497.4	495.8	495.8
180°	494.2	494.2	494.2	494.2	494.2	494.2	494.2

(END OF REPORT)