

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831527

Luminaire Tested: S123DIP-S560D365U940-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831527
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U940-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3485.6 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 29.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	77	70	64	81	73	66	61	65	60	56	58	54	51	51	49	46	43				
4	79	69	61	55	74	65	58	53	59	53	49	52	48	44	47	43	40	37				
5	73	62	54	48	69	59	52	46	53	47	43	48	43	39	43	39	36	33				
6	68	56	48	42	64	53	46	41	48	42	38	43	39	35	39	35	32	30				
7	63	51	43	38	59	49	42	36	44	38	34	40	35	32	36	32	29	27				
8	59	47	39	34	56	45	38	33	41	35	31	37	32	29	33	29	27	24				
9	55	43	36	31	52	41	34	30	38	32	28	34	30	26	31	27	24	22				
10	52	40	33	28	49	38	32	27	35	29	26	32	27	24	29	25	22	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	15493	15493	15493	15493	15493
5°	19594	18493	15632	12597	11575
10°	19783	20382	15527	10041	8775
15°	14900	18923	15422	8504	7421
20°	10381	15313	15224	7436	6740
25°	7917	11776	14890	6842	6322
30°	6848	9355	14353	6421	5986
35°	6355	7899	13736	6117	5749
40°	6015	7086	12867	5828	5668
45°	5815	6558	11764	5602	5632
50°	5715	6141	10458	5397	5603
55°	5502	5834	9175	5202	5628
60°	5307	5507	7907	5018	5535
65°	4984	5196	6821	4824	5428
70°	4604	4803	5800	4497	5108
75°	4167	4304	4974	4180	4666
80°	3434	3769	3936	3645	3936
85°	2717	3051	2890	3088	3137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 13431 cd/sqm



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	3.9
10°-20°	338.5	9.7
20°-30°	400.8	11.5
30°-40°	403.0	11.6
40°-50°	369.8	10.6
50°-60°	305.2	8.8
60°-70°	215.9	6.2
70°-80°	115.2	3.3
80°-90°	30.1	0.9
90°-100°	84.5	2.4
100°-110°	247.3	7.1
110°-120°	241.5	6.9
120°-130°	192.3	5.5
130°-140°	151.7	4.4
140°-150°	113.2	3.2
150°-160°	78.9	2.3
160°-170°	46.4	1.3
170°-180°	15.1	0.4
0°-30°	875.4	25.1
0°-40°	1278.4	36.7
0°-60°	1953.4	56.0
0°-90°	2314.6	66.4
90°-120°	573.3	16.4
90°-150°	1030.6	29.6
90°-180°	1171.0	33.6
0°-180°	3485.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1439	1439	1439	1439	1439	
5°	1813	1712	1447	1166	1071	173
15°	1337	1698	1384	763	666	369
25°	667	992	1254	576	532	315
35°	484	601	1045	466	438	304
45°	382	431	773	368	370	296
55°	293	311	489	277	300	262
65°	196	204	268	189	213	194
75°	100	104	120	100	112	105
85°	22	25	23	25	25	25
90°	9	8	1	8	9	6
95°	37	187	11	187	37	59
105°	401	253	37	253	401	400
115°	488	194	65	194	488	475
125°	384	181	90	181	384	348
135°	312	178	105	178	312	242
145°	244	176	120	176	244	155
155°	202	170	136	170	202	94
165°	176	163	149	163	176	50
175°	158	157	155	157	158	15
180°	156	156	156	156	156	



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1622.3	1620.7	1619.0	1610.6	1602.3	1598.3	1594.3	1582.3	1570.2	1556.9	1543.5
5°	1813.4	1818.0	1822.7	1817.4	1812.0	1795.7	1779.3	1757.6	1735.9	1711.5	1687.1
7.5°	1901.5	1904.2	1906.9	1903.5	1900.2	1895.8	1891.5	1872.1	1852.8	1827.7	1802.7
10°	1810.0	1816.0	1822.0	1835.1	1848.1	1862.8	1877.5	1874.8	1872.1	1864.8	1857.4
12.5°	1609.0	1616.3	1623.7	1649.7	1675.8	1709.2	1742.6	1771.3	1800.0	1820.0	1840.1
15°	1337.1	1357.5	1377.9	1401.6	1425.3	1474.4	1523.5	1583.9	1644.4	1698.1	1751.9
17.5°	1101.4	1109.1	1116.7	1142.1	1167.5	1229.3	1291.1	1360.8	1430.6	1519.8	1609.0
20°	906.3	913.4	920.4	953.8	987.2	1035.6	1084.0	1162.5	1241.0	1336.8	1432.6
22.5°	761.4	772.4	783.4	802.1	820.9	867.3	913.7	983.5	1053.3	1159.1	1265.0
25°	666.6	674.6	682.6	693.9	705.3	742.4	779.4	836.9	894.3	991.5	1088.7
27.5°	601.8	605.1	608.5	619.8	631.2	655.2	679.3	728.7	778.1	860.6	943.1
30°	551.0	553.4	555.7	565.7	575.7	592.1	608.5	644.2	679.9	752.7	825.5
32.5°	515.6	517.3	519.0	526.6	534.3	546.0	557.7	583.7	609.8	669.9	730.0
35°	483.6	484.6	485.6	491.2	496.9	505.6	514.3	534.0	553.7	601.1	648.5
37.5°	455.5	456.8	458.2	461.5	464.9	472.5	480.2	495.9	511.6	548.0	584.4
40°	428.1	430.5	432.8	435.1	437.5	443.8	450.2	462.2	474.2	504.3	534.3
42.5°	404.7	407.1	409.4	410.4	411.4	415.1	418.8	429.8	440.8	463.2	485.6
45°	382.0	383.0	384.0	385.0	386.0	389.1	392.1	401.7	411.4	430.8	450.2
47.5°	361.3	361.3	361.3	362.0	362.7	365.3	368.0	375.0	382.0	397.1	412.1
50°	341.3	341.3	341.3	340.3	339.3	341.0	342.6	348.0	353.3	366.7	380.0
52.5°	317.3	317.3	317.3	317.6	317.9	317.9	317.9	322.6	327.3	339.3	351.3
55°	293.2	294.5	295.9	294.9	293.9	294.5	295.2	298.2	301.2	310.9	320.6
57.5°	269.2	269.8	270.5	270.2	269.8	270.2	270.5	273.2	275.8	283.2	290.5
60°	246.5	246.5	246.5	245.8	245.1	245.8	246.5	247.8	249.1	255.8	262.5
62.5°	221.1	221.4	221.7	222.1	222.4	221.7	221.1	222.7	224.4	229.4	234.4
65°	195.7	196.0	196.4	197.4	198.4	197.7	197.0	198.7	200.4	204.0	207.7
67.5°	173.0	172.3	171.7	172.0	172.3	173.3	174.3	174.7	175.0	179.0	183.0
70°	146.3	146.9	147.6	147.3	146.9	147.3	147.6	148.6	149.6	152.6	155.6
72.5°	122.2	122.6	122.9	122.9	122.9	123.6	124.2	125.2	126.2	127.9	129.6
75°	100.2	100.2	100.2	100.9	101.5	101.9	102.2	102.2	102.2	103.5	104.9
77.5°	76.1	77.8	79.5	79.1	78.8	79.5	80.1	81.2	82.2	82.8	83.5
80°	55.4	55.4	55.4	55.8	56.1	57.1	58.1	58.8	59.4	60.8	62.1
82.5°	35.4	35.7	36.1	37.1	38.1	38.7	39.4	40.4	41.4	41.4	41.4
85°	22.0	21.4	20.7	21.4	22.0	22.7	23.4	23.7	24.0	24.7	25.4
87.5°	10.7	10.7	10.7	10.7	10.7	11.0	11.4	11.4	11.4	11.4	11.4
90°	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.9	7.6	7.9	6.9
92.5°	16.7	17.3	17.0	18.3	18.9	21.1	24.3	31.2	43.8	58.6	64.9
95°	36.6	37.8	40.0	42.9	48.8	60.2	76.9	113.4	151.6	186.9	166.4
97.5°	75.0	78.5	86.0	98.0	119.1	155.0	196.6	260.6	297.2	287.4	214.6
100°	197.6	197.3	209.6	232.6	264.4	309.1	346.0	371.5	360.5	298.4	201.7
102.5°	312.9	322.0	331.8	348.8	371.8	396.1	413.7	408.4	363.6	277.9	182.8
105°	400.8	402.4	412.5	424.5	439.0	447.1	441.2	409.6	343.8	253.4	168.0
107.5°	458.2	461.6	465.7	471.4	473.3	464.8	440.2	390.7	315.4	231.6	157.2
110°	490.9	491.6	492.2	489.7	480.9	458.8	419.1	361.1	289.0	213.6	151.6



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	497.6	497.2	494.1	485.0	467.0	437.1	391.4	331.8	266.0	201.7	148.4
115°	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6	248.3	193.8	148.1
117.5°	465.4	463.2	453.8	438.3	413.7	378.1	335.6	287.1	236.7	188.4	148.4
120°	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.3	227.8	185.0	149.7
122.5°	409.3	406.8	398.3	382.9	361.4	332.4	298.1	260.6	220.6	182.8	151.9
125°	384.4	382.2	374.4	360.5	340.3	315.1	284.9	250.5	214.6	180.9	154.1
127.5°	363.0	361.1	353.9	341.9	323.6	300.3	272.6	241.4	208.9	179.9	156.6
130°	345.4	342.8	336.2	324.9	308.2	286.8	261.2	232.9	204.5	179.0	159.1
132.5°	328.0	326.5	320.8	309.4	294.0	273.8	250.5	225.0	200.4	178.7	161.0
135°	311.6	309.4	303.8	294.3	278.9	260.9	240.4	218.1	196.9	178.4	162.9
137.5°	294.3	292.4	287.7	277.9	264.7	248.6	230.3	211.4	193.8	177.7	164.2
140°	276.0	276.4	271.3	262.5	250.5	237.0	221.8	205.8	191.0	177.4	165.4
142.5°	259.0	259.3	254.9	247.4	237.6	226.3	213.6	200.4	188.4	176.8	166.4
145°	243.6	243.0	240.4	233.8	225.9	216.8	206.7	196.3	186.2	176.1	166.7
147.5°	230.3	230.0	227.5	222.8	216.5	209.9	201.4	192.8	184.0	175.2	166.7
150°	219.0	219.0	217.1	213.6	208.9	202.9	196.3	189.1	181.8	173.9	166.7
152.5°	209.6	209.6	208.6	205.5	202.0	197.3	191.6	185.6	179.3	172.4	165.7
155°	202.0	201.7	201.0	198.5	195.7	191.9	187.2	182.1	176.8	170.5	165.1
157.5°	194.7	194.7	194.1	192.2	189.7	186.5	182.8	178.4	173.9	168.9	164.2
160°	187.8	188.1	188.1	186.2	184.0	181.8	178.7	175.2	171.1	167.0	163.5
162.5°	181.5	181.8	181.8	180.2	179.0	177.1	174.3	171.4	168.3	165.1	162.3
165°	176.1	176.1	176.5	175.2	173.9	172.4	170.2	168.3	165.7	163.2	161.0
167.5°	170.8	170.8	171.1	170.2	169.5	168.3	167.0	165.4	163.2	161.3	159.8
170°	166.1	166.1	166.4	165.7	165.4	164.8	163.5	162.6	161.0	159.4	158.5
172.5°	161.7	162.0	162.6	162.0	162.0	161.7	160.7	160.1	158.8	157.9	157.6
175°	158.5	158.8	159.1	158.8	158.8	158.8	158.2	157.9	157.2	156.6	156.6
177.5°	156.3	156.3	156.9	156.6	156.9	156.9	156.6	156.3	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1539.5	1535.5	1520.8	1506.1	1489.4	1472.7	1460.4	1448.0	1429.6	1411.3	1396.2
5°	1668.4	1649.7	1618.7	1587.6	1545.5	1503.4	1475.1	1446.7	1408.6	1370.5	1340.1
7.5°	1770.6	1738.5	1695.1	1651.7	1596.6	1541.5	1489.4	1437.3	1379.2	1321.1	1273.7
10°	1835.7	1814.0	1763.9	1713.8	1640.0	1566.2	1493.4	1420.6	1345.8	1271.0	1208.2
12.5°	1842.1	1844.1	1798.0	1751.9	1668.4	1584.9	1496.4	1407.9	1313.8	1219.6	1146.5
15°	1786.3	1820.7	1795.3	1769.9	1685.8	1601.6	1492.8	1383.9	1275.4	1166.8	1082.3
17.5°	1682.8	1756.6	1760.3	1763.9	1679.8	1595.6	1475.1	1354.5	1231.6	1108.7	1019.9
20°	1541.5	1650.4	1687.8	1725.2	1656.7	1588.3	1458.7	1329.1	1191.5	1053.9	960.8
22.5°	1397.3	1529.5	1598.0	1666.4	1615.7	1564.9	1427.0	1289.1	1143.8	998.5	904.0
25°	1232.9	1377.2	1482.4	1587.6	1556.5	1525.5	1389.6	1253.7	1099.0	944.4	847.9
27.5°	1089.7	1236.3	1363.2	1490.1	1483.4	1476.7	1341.8	1206.9	1048.6	890.3	797.1
30°	962.1	1098.7	1240.6	1382.6	1398.9	1415.3	1285.0	1154.8	996.2	837.5	747.7
32.5°	849.2	968.5	1120.7	1273.0	1305.1	1337.1	1219.6	1102.0	945.1	788.1	701.6
35°	756.7	864.9	1017.2	1169.5	1209.6	1249.6	1147.5	1045.3	892.3	739.4	656.9
37.5°	674.9	765.4	914.0	1062.6	1111.7	1160.8	1069.3	977.8	834.5	691.3	615.5
40°	607.1	679.9	816.5	953.1	1009.9	1066.6	991.2	915.7	779.8	643.9	574.1
42.5°	550.4	615.1	739.0	862.9	917.4	971.8	908.0	844.2	723.3	602.4	538.7
45°	501.9	553.7	666.2	778.8	830.5	882.3	827.5	772.8	666.2	559.7	500.3
47.5°	456.5	500.9	597.1	693.3	739.4	785.5	742.7	700.0	609.8	519.6	465.9
50°	415.8	451.5	535.7	619.8	659.9	700.0	662.2	624.5	550.4	476.2	429.5
52.5°	380.4	409.4	479.9	550.4	584.7	619.1	586.8	554.4	495.6	436.8	396.1
55°	345.3	370.0	431.1	492.2	515.6	539.0	514.0	488.9	441.5	394.1	359.7
57.5°	312.6	334.6	384.7	434.8	452.8	470.9	448.2	425.5	389.7	354.0	325.3
60°	280.5	298.6	340.3	382.0	393.1	404.1	385.7	367.3	342.3	317.3	291.5
62.5°	250.8	267.2	298.2	329.3	336.6	344.0	329.9	315.9	296.9	277.8	257.8
65°	220.1	232.4	257.8	283.2	287.9	292.5	280.2	267.8	253.5	239.1	224.4
67.5°	191.7	200.4	221.1	241.8	242.1	242.4	232.4	222.4	214.4	206.4	194.7
70°	164.0	172.3	186.0	199.7	200.0	200.4	192.4	184.3	178.3	172.3	163.6
72.5°	135.6	141.6	151.9	162.3	161.6	161.0	156.0	150.9	146.3	141.6	135.3
75°	109.9	114.9	121.9	128.9	126.9	124.9	122.2	119.6	115.5	111.5	107.5
77.5°	86.5	89.5	93.5	97.5	96.2	94.8	92.5	90.2	87.2	84.2	82.5
80°	63.5	64.8	67.5	70.1	69.5	68.8	66.1	63.5	62.8	62.1	59.8
82.5°	43.1	44.7	45.4	46.1	45.8	45.4	43.4	41.4	40.7	40.1	39.7
85°	25.7	26.0	26.4	26.7	25.7	24.7	24.0	23.4	23.4	23.4	23.0
87.5°	11.7	12.0	12.0	12.0	11.7	11.4	10.7	10.0	10.4	10.7	10.7
90°	6.0	5.0	4.1	3.5	2.8	1.9	1.3	0.6	1.3	1.9	2.8
92.5°	48.5	31.8	21.7	16.1	12.9	10.1	6.9	4.7	6.9	10.1	12.9
95°	114.7	67.7	41.0	28.7	20.5	15.1	11.7	10.7	11.7	15.1	20.5
97.5°	127.6	73.1	46.6	33.1	24.9	20.2	17.3	17.0	17.3	20.2	24.9
100°	118.8	72.2	50.1	37.8	30.3	25.8	23.6	23.3	23.6	25.8	30.3
102.5°	111.2	73.4	54.2	43.2	36.6	32.5	30.6	29.9	30.6	32.5	36.6
105°	108.4	75.9	58.9	49.2	43.2	39.4	37.5	36.6	37.5	39.4	43.2
107.5°	107.8	80.0	64.9	55.8	50.1	46.3	44.4	43.5	44.4	46.3	50.1
110°	109.3	85.4	71.2	62.4	57.0	53.6	52.0	51.0	52.0	53.6	57.0



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	112.5	90.8	77.8	69.3	64.0	60.5	58.9	58.0	58.9	60.5	64.0
115°	116.0	96.7	84.8	76.3	70.9	67.7	65.9	64.6	65.9	67.7	70.9
117.5°	120.4	103.0	91.1	83.2	77.2	74.4	72.8	71.2	72.8	74.4	77.2
120°	125.4	109.0	97.7	89.8	83.8	80.7	79.1	78.1	79.1	80.7	83.8
122.5°	130.1	115.3	104.3	95.8	90.1	86.7	85.1	84.1	85.1	86.7	90.1
125°	135.2	121.3	110.3	101.8	95.8	92.3	90.4	89.8	90.4	92.3	95.8
127.5°	139.3	126.7	116.0	107.5	100.8	97.4	95.2	94.2	95.2	97.4	100.8
130°	143.4	131.4	121.0	112.5	105.9	102.1	99.3	98.3	99.3	102.1	105.9
132.5°	147.2	135.5	125.4	117.2	110.6	105.9	102.7	101.5	102.7	105.9	110.6
135°	150.3	139.6	129.8	121.3	114.7	110.0	106.5	105.2	106.5	110.0	114.7
137.5°	152.8	142.4	133.0	125.1	118.5	113.4	110.0	108.7	110.0	113.4	118.5
140°	154.7	145.3	136.1	128.3	121.9	116.9	113.8	112.2	113.8	116.9	121.9
142.5°	156.6	147.5	138.6	131.4	125.1	120.7	117.2	116.0	117.2	120.7	125.1
145°	157.9	149.4	141.2	133.9	128.6	123.8	121.0	120.1	121.0	123.8	128.6
147.5°	158.8	150.9	143.4	137.1	131.7	127.6	124.8	124.2	124.8	127.6	131.7
150°	159.1	152.5	145.3	139.6	135.2	131.1	128.6	128.3	128.6	131.1	135.2
152.5°	159.8	153.5	147.5	142.1	138.3	134.9	132.3	132.3	132.3	134.9	138.3
155°	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4	136.4	138.3	141.5
157.5°	160.1	155.4	150.9	147.5	144.3	141.5	139.9	139.6	139.9	141.5	144.3
160°	160.1	156.3	152.5	149.4	147.2	144.6	143.4	143.4	143.4	144.6	147.2
162.5°	159.8	156.6	153.5	150.9	149.0	147.2	146.2	146.2	146.2	147.2	149.0
165°	159.1	156.9	154.4	152.2	150.9	149.4	148.7	149.0	148.7	149.4	150.9
167.5°	158.8	156.9	155.0	153.5	152.5	151.3	150.9	151.3	150.9	151.3	152.5
170°	157.9	156.6	155.0	154.4	153.8	152.8	152.5	153.1	152.5	152.8	153.8
172.5°	157.6	156.6	155.4	155.0	154.7	154.1	154.1	154.4	154.1	154.1	154.7
175°	156.9	156.3	155.7	155.4	155.4	154.7	155.0	155.4	155.0	154.7	155.4
177.5°	156.6	156.0	155.7	155.7	155.7	155.4	155.7	156.0	155.7	155.4	155.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1381.2	1368.2	1355.2	1345.2	1335.1	1318.1	1301.1	1297.1	1293.1	1287.4	1281.7
5°	1309.8	1277.7	1245.6	1216.9	1188.2	1165.8	1143.4	1128.8	1114.1	1103.4	1092.7
7.5°	1226.3	1178.2	1130.1	1096.0	1062.0	1029.6	997.2	986.8	976.5	962.4	948.4
10°	1145.5	1092.4	1039.3	994.8	950.4	918.7	887.0	874.3	861.6	843.9	826.2
12.5°	1073.3	1015.2	957.1	912.4	867.6	836.9	806.2	787.8	769.4	759.4	749.4
15°	997.8	935.7	873.6	832.2	790.8	763.1	735.4	719.3	703.3	693.6	683.9
17.5°	931.1	869.6	808.2	768.4	728.7	703.3	677.9	663.9	649.9	642.5	635.2
20°	867.6	807.5	747.4	708.6	669.9	649.2	628.5	619.5	610.5	604.5	598.4
22.5°	809.5	750.4	691.3	658.2	625.2	608.5	591.8	585.4	579.1	574.1	569.1
25°	751.4	698.6	645.9	617.8	589.8	576.1	562.4	556.0	549.7	544.7	539.7
27.5°	704.0	653.5	603.1	579.1	555.0	544.3	533.7	528.6	523.6	519.0	514.3
30°	657.9	612.8	567.7	547.0	526.3	516.6	506.9	501.9	496.9	492.6	488.2
32.5°	615.1	576.4	537.7	518.6	499.6	491.6	483.6	477.5	471.5	468.2	464.9
35°	574.4	539.7	504.9	489.2	473.5	465.5	457.5	452.5	447.5	444.8	442.2
37.5°	539.7	508.6	477.5	462.5	447.5	439.8	432.1	427.8	423.4	422.4	421.4
40°	504.3	477.5	450.8	436.1	421.4	414.8	408.1	405.4	402.7	402.1	401.4
42.5°	474.9	448.8	422.8	409.4	396.1	390.4	384.7	383.4	382.0	383.0	384.0
45°	440.8	419.1	397.4	385.0	372.7	368.0	363.3	362.3	361.3	363.3	365.3
47.5°	412.1	392.1	372.0	360.3	348.6	345.3	342.0	341.6	341.3	344.0	346.6
50°	382.7	363.3	344.0	334.6	325.3	322.3	319.3	320.3	321.3	325.6	329.9
52.5°	355.3	337.3	319.3	310.6	301.9	299.9	297.9	300.2	302.6	307.2	311.9
55°	325.3	308.9	292.5	285.9	279.2	277.2	275.2	279.9	284.5	288.9	293.2
57.5°	296.5	282.2	267.8	261.8	255.8	255.5	255.1	259.5	263.8	268.5	273.2
60°	265.8	253.8	241.8	237.1	232.4	233.1	233.8	238.8	243.8	247.5	251.1
62.5°	237.8	227.8	217.7	213.4	209.1	210.7	212.4	217.4	222.4	226.8	231.1
65°	209.7	201.4	193.0	190.0	187.0	189.4	191.7	196.0	200.4	203.4	206.4
67.5°	183.0	176.0	169.0	166.6	164.3	166.6	169.0	173.3	177.7	180.7	183.7
70°	155.0	149.3	143.6	141.9	140.3	142.9	145.6	149.3	152.9	156.0	159.0
72.5°	128.9	124.6	120.2	119.9	119.6	121.9	124.2	127.9	131.6	133.6	135.6
75°	103.5	101.2	98.8	98.5	98.2	100.5	102.9	104.9	106.9	108.5	110.2
77.5°	80.8	78.8	76.8	77.1	77.5	79.1	80.8	82.8	84.8	85.8	86.8
80°	57.4	56.8	56.1	56.8	57.4	58.8	60.1	61.4	62.8	63.5	64.1
82.5°	39.4	38.7	38.1	39.1	40.1	41.1	42.1	43.1	44.1	44.4	44.7
85°	22.7	23.7	24.7	24.7	24.7	25.0	25.4	25.7	26.0	25.7	25.4
87.5°	10.7	11.0	11.4	11.4	11.4	11.7	12.0	12.0	12.0	11.7	11.4
90°	3.5	4.1	5.0	6.0	6.9	7.9	7.6	7.9	8.2	8.5	9.1
92.5°	16.1	21.7	31.8	48.5	64.9	58.6	43.8	31.2	24.3	21.1	18.9
95°	28.7	41.0	67.7	114.7	166.4	186.9	151.6	113.4	76.9	60.2	48.8
97.5°	33.1	46.6	73.1	127.6	214.6	287.4	297.2	260.6	196.6	155.0	119.1
100°	37.8	50.1	72.2	118.8	201.7	298.4	360.5	371.5	346.0	309.1	264.4
102.5°	43.2	54.2	73.4	111.2	182.8	277.9	363.6	408.4	413.7	396.1	371.8
105°	49.2	58.9	75.9	108.4	168.0	253.4	343.8	409.6	441.2	447.1	439.0
107.5°	55.8	64.9	80.0	107.8	157.2	231.6	315.4	390.7	440.2	464.8	473.3
110°	62.4	71.2	85.4	109.3	151.6	213.6	289.0	361.1	419.1	458.8	480.9



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	69.3	77.8	90.8	112.5	148.4	201.7	266.0	331.8	391.4	437.1	467.0
115°	76.3	84.8	96.7	116.0	148.1	193.8	248.3	306.6	361.4	407.8	442.1
117.5°	83.2	91.1	103.0	120.4	148.4	188.4	236.7	287.1	335.6	378.1	413.7
120°	89.8	97.7	109.0	125.4	149.7	185.0	227.8	272.3	314.8	352.6	384.4
122.5°	95.8	104.3	115.3	130.1	151.9	182.8	220.6	260.6	298.1	332.4	361.4
125°	101.8	110.3	121.3	135.2	154.1	180.9	214.6	250.5	284.9	315.1	340.3
127.5°	107.5	116.0	126.7	139.3	156.6	179.9	208.9	241.4	272.6	300.3	323.6
130°	112.5	121.0	131.4	143.4	159.1	179.0	204.5	232.9	261.2	286.8	308.2
132.5°	117.2	125.4	135.5	147.2	161.0	178.7	200.4	225.0	250.5	273.8	294.0
135°	121.3	129.8	139.6	150.3	162.9	178.4	196.9	218.1	240.4	260.9	278.9
137.5°	125.1	133.0	142.4	152.8	164.2	177.7	193.8	211.4	230.3	248.6	264.7
140°	128.3	136.1	145.3	154.7	165.4	177.4	191.0	205.8	221.8	237.0	250.5
142.5°	131.4	138.6	147.5	156.6	166.4	176.8	188.4	200.4	213.6	226.3	237.6
145°	133.9	141.2	149.4	157.9	166.7	176.1	186.2	196.3	206.7	216.8	225.9
147.5°	137.1	143.4	150.9	158.8	166.7	175.2	184.0	192.8	201.4	209.9	216.5
150°	139.6	145.3	152.5	159.1	166.7	173.9	181.8	189.1	196.3	202.9	208.9
152.5°	142.1	147.5	153.5	159.8	165.7	172.4	179.3	185.6	191.6	197.3	202.0
155°	145.0	149.4	154.7	159.8	165.1	170.5	176.8	182.1	187.2	191.9	195.7
157.5°	147.5	150.9	155.4	160.1	164.2	168.9	173.9	178.4	182.8	186.5	189.7
160°	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2	178.7	181.8	184.0
162.5°	150.9	153.5	156.6	159.8	162.3	165.1	168.3	171.4	174.3	177.1	179.0
165°	152.2	154.4	156.9	159.1	161.0	163.2	165.7	168.3	170.2	172.4	173.9
167.5°	153.5	155.0	156.9	158.8	159.8	161.3	163.2	165.4	167.0	168.3	169.5
170°	154.4	155.0	156.6	157.9	158.5	159.4	161.0	162.6	163.5	164.8	165.4
172.5°	155.0	155.4	156.6	157.6	157.6	157.9	158.8	160.1	160.7	161.7	162.0
175°	155.4	155.7	156.3	156.9	156.6	156.6	157.2	157.9	158.2	158.8	158.8
177.5°	155.7	155.7	156.0	156.6	156.0	155.7	156.0	156.3	156.6	156.9	156.9
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1439.3	1439.3	1439.3	1439.3
2.5°	1279.4	1277.0	1267.7	1258.3
5°	1084.7	1076.7	1074.0	1071.3
7.5°	947.8	947.1	933.1	919.0
10°	827.2	828.2	815.5	802.8
12.5°	741.0	732.7	731.7	730.7
15°	676.3	668.6	667.2	665.9
17.5°	630.5	625.8	624.5	623.2
20°	595.8	593.1	590.8	588.4
22.5°	565.7	562.4	560.4	558.4
25°	536.7	533.7	533.0	532.3
27.5°	510.6	506.9	506.9	506.9
30°	485.9	483.6	482.6	481.6
32.5°	462.9	460.9	460.9	460.9
35°	441.1	440.1	438.8	437.5
37.5°	421.4	421.4	420.8	420.1
40°	402.4	403.4	403.4	403.4
42.5°	385.0	386.0	386.0	386.0
45°	367.0	368.7	369.3	370.0
47.5°	349.3	352.0	352.7	353.3
50°	331.9	334.0	334.3	334.6
52.5°	314.2	316.6	318.3	319.9
55°	295.5	297.9	298.9	299.9
57.5°	275.5	277.8	278.2	278.5
60°	253.5	255.8	256.5	257.1
62.5°	232.4	233.8	234.4	235.1
65°	208.4	210.4	211.7	213.1
67.5°	185.3	187.0	187.0	187.0
70°	159.6	160.3	161.3	162.3
72.5°	135.9	136.3	136.3	136.3
75°	110.9	111.5	111.9	112.2
77.5°	87.2	87.5	87.5	87.5
80°	63.8	63.5	63.5	63.5
82.5°	43.7	42.7	42.7	42.7
85°	25.0	24.7	25.0	25.4
87.5°	11.4	11.4	11.4	11.4
90°	8.8	9.1	9.5	9.1
92.5°	18.3	17.0	17.3	16.7
95°	42.9	40.0	37.8	36.6
97.5°	98.0	86.0	78.5	75.0
100°	232.6	209.6	197.3	197.6
102.5°	348.8	331.8	322.0	312.9
105°	424.5	412.5	402.4	400.8
107.5°	471.4	465.7	461.6	458.2
110°	489.7	492.2	491.6	490.9



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	485.0	494.1	497.2	497.6
115°	465.7	479.6	485.9	487.5
117.5°	438.3	453.8	463.2	465.4
120°	409.3	427.0	434.5	436.4
122.5°	382.9	398.3	406.8	409.3
125°	360.5	374.4	382.2	384.4
127.5°	341.9	353.9	361.1	363.0
130°	324.9	336.2	342.8	345.4
132.5°	309.4	320.8	326.5	328.0
135°	294.3	303.8	309.4	311.6
137.5°	277.9	287.7	292.4	294.3
140°	262.5	271.3	276.4	276.0
142.5°	247.4	254.9	259.3	259.0
145°	233.8	240.4	243.0	243.6
147.5°	222.8	227.5	230.0	230.3
150°	213.6	217.1	219.0	219.0
152.5°	205.5	208.6	209.6	209.6
155°	198.5	201.0	201.7	202.0
157.5°	192.2	194.1	194.7	194.7
160°	186.2	188.1	188.1	187.8
162.5°	180.2	181.8	181.8	181.5
165°	175.2	176.5	176.1	176.1
167.5°	170.2	171.1	170.8	170.8
170°	165.7	166.4	166.1	166.1
172.5°	162.0	162.6	162.0	161.7
175°	158.8	159.1	158.8	158.5
177.5°	156.6	156.9	156.3	156.3
180°	155.7	155.7	155.7	155.7



TEST NUMBER: P831527

CATALOG NUMBER: S123DIP-S560D365U940-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.50	15.48	15.31	16.31	17.33	16.74	17.72	17.55	18.54	19.56
	3H	16.16	17.03	16.98	17.87	18.92	18.17	19.05	18.99	19.88	20.93
	4H	16.74	17.57	17.58	18.41	19.47	18.63	19.45	19.47	20.30	21.36
	6H	17.12	17.88	17.97	18.73	19.80	18.91	19.67	19.76	20.52	21.59
	8H	17.22	17.94	18.08	18.81	19.88	18.97	19.70	19.84	20.57	21.64
	12H	17.26	17.95	18.13	18.82	19.92	19.00	19.69	19.86	20.55	21.65
4H	2H	15.09	15.92	15.93	16.76	17.82	16.91	17.74	17.76	18.59	19.64
	3H	16.93	17.62	17.78	18.49	19.57	18.54	19.23	19.40	20.11	21.18
	4H	17.63	18.26	18.50	19.13	20.23	19.13	19.76	20.00	20.63	21.73
	6H	18.11	18.65	19.00	19.55	20.66	19.54	20.08	20.43	20.98	22.09
	8H	18.25	18.76	19.14	19.65	20.77	19.66	20.16	20.54	21.05	22.17
	12H	18.32	18.78	19.23	19.69	20.81	19.71	20.16	20.61	21.07	22.19
8H	4H	17.91	18.41	18.79	19.30	20.42	19.25	19.75	20.13	20.64	21.76
	6H	18.50	18.92	19.41	19.85	20.97	19.75	20.17	20.67	21.10	22.22
	8H	18.71	19.08	19.63	20.00	21.14	19.93	20.30	20.86	21.23	22.36
	12H	18.84	19.16	19.76	20.08	21.27	20.04	20.36	20.97	21.28	22.47
12H	4H	17.91	18.37	18.82	19.28	20.40	19.23	19.68	20.13	20.59	21.71
	6H	18.55	18.92	19.47	19.85	20.98	19.77	20.14	20.69	21.06	22.20
	8H	18.79	19.11	19.72	20.03	21.22	19.97	20.30	20.90	21.22	22.40