

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331972-935

Luminaire Tested: **S123DIP-S775D585U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331972-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4555.3 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	30	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11286	11286	11286
5°	11339	11182	11261
10°	11262	11086	11154
15°	11131	10961	10981
20°	10977	10781	10791
25°	10772	10568	10546
30°	10544	10331	10253
35°	10307	10081	9950
40°	10058	9805	9653
45°	9785	9552	9319
50°	9512	9239	8982
55°	9154	8916	8646
60°	8792	8540	8269
65°	8474	8130	7875
70°	8003	7660	7320
75°	7311	7049	6750
80°	6595	6316	6261
85°	5780	5570	5348



TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.8	2.2
10°-20°	278.9	6.1
20°-30°	411.9	9.0
30°-40°	481.2	10.6
40°-50°	483.8	10.6
50°-60°	425.0	9.3
60°-70°	316.6	6.9
70°-80°	180.4	4.0
80°-90°	53.7	1.2
90°-100°	135.0	3.0
100°-110°	382.3	8.4
110°-120°	376.1	8.3
120°-130°	300.0	6.6
130°-140°	236.5	5.2
140°-150°	176.5	3.9
150°-160°	123.0	2.7
160°-170°	72.3	1.6
170°-180°	23.5	0.5
0°-30°	789.6	17.3
0°-40°	1270.8	27.9
0°-60°	2179.5	47.8
0°-90°	2730.1	59.9
90°-120°	893.4	19.6
90°-150°	1606.4	35.3
90°-180°	1825.0	40.1
0°-180°	4555.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1049	1045	1035	1043	1042	99
15°	999	995	984	990	985	281
25°	907	901	890	890	888	418
35°	784	779	767	762	757	490
45°	643	639	628	617	612	496
55°	488	486	475	466	461	437
65°	333	328	319	312	309	328
75°	176	172	170	165	162	188
85°	47	45	45	43	43	51
90°	1	6	12	14	14	4
95°	17	54	291	85	57	18
105°	57	84	395	690	625	61
115°	101	125	302	662	760	100
125°	140	165	282	511	599	124
135°	164	196	278	421	486	127
145°	187	214	274	345	380	117
155°	213	229	266	302	315	98
165°	232	239	254	270	274	65
175°	242	242	244	248	247	23
180°	243	243	243	243	243	



TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1052.1	1051.5	1050.9	1050.2	1049.6	1048.4	1046.5	1044.8	1043.0	1041.3	1042.8
5°	1049.4	1048.4	1047.4	1046.4	1045.3	1043.8	1041.6	1039.4	1037.2	1034.9	1037.0
7.5°	1039.1	1038.1	1037.1	1036.1	1035.1	1033.5	1031.1	1028.9	1026.6	1024.3	1026.1
10°	1030.4	1029.4	1028.5	1027.4	1026.5	1024.7	1022.0	1019.4	1016.8	1014.3	1016.1
12.5°	1018.9	1018.0	1017.3	1016.4	1015.5	1013.9	1011.5	1009.0	1006.6	1004.1	1005.5
15°	998.9	998.1	997.3	996.5	995.7	994.0	991.4	988.8	986.2	983.6	985.2
17.5°	975.6	974.6	973.5	972.5	971.5	969.7	967.1	964.4	961.8	959.2	960.4
20°	958.3	957.1	956.0	954.8	953.6	951.6	949.0	946.4	943.8	941.2	942.0
22.5°	938.8	937.6	936.4	935.2	934.0	932.1	929.5	927.0	924.4	921.7	922.4
25°	907.0	905.8	904.6	903.4	902.2	900.3	897.6	895.0	892.4	889.8	890.0
27.5°	872.9	871.7	870.6	869.4	868.2	866.3	863.4	860.7	857.8	855.0	855.1
30°	848.3	847.3	846.4	845.3	844.3	842.4	839.6	836.8	834.1	831.2	831.2
32.5°	823.8	822.5	821.1	819.8	818.6	816.8	814.6	812.4	810.3	808.1	807.0
35°	784.4	783.2	782.0	780.8	779.5	777.7	775.0	772.4	769.8	767.2	766.0
37.5°	743.9	742.4	740.9	739.3	737.9	735.8	733.1	730.5	727.8	725.2	723.8
40°	715.8	714.6	713.4	712.2	711.0	709.0	706.2	703.4	700.6	697.8	696.2
42.5°	687.7	686.3	684.9	683.6	682.3	680.2	677.3	674.5	671.8	668.9	667.4
45°	642.8	642.0	641.2	640.4	639.6	637.9	635.2	632.7	630.1	627.5	625.1
47.5°	598.2	597.1	595.9	594.8	593.6	591.8	589.4	586.9	584.4	582.0	579.6
50°	568.0	567.0	565.9	565.0	564.0	562.1	559.6	557.0	554.3	551.7	549.6
52.5°	536.2	535.5	534.9	534.2	533.5	531.8	529.0	526.2	523.5	520.7	518.8
55°	487.8	487.5	487.3	487.2	486.9	485.5	482.9	480.4	477.7	475.1	472.9
57.5°	441.6	440.9	440.2	439.5	438.9	437.5	435.4	433.3	431.2	429.1	427.1
60°	408.4	408.2	408.0	407.8	407.6	406.3	403.9	401.5	399.1	396.7	394.9
62.5°	378.8	378.3	377.8	377.3	376.8	375.3	372.9	370.5	368.1	365.7	363.9
65°	332.7	331.7	330.6	329.7	328.6	327.2	325.1	323.1	321.2	319.2	317.5
67.5°	283.8	282.9	282.1	281.1	280.3	279.1	277.6	276.0	274.5	273.0	271.6
70°	254.3	253.0	251.8	250.6	249.4	248.2	247.0	245.8	244.6	243.4	242.0
72.5°	223.3	222.3	221.4	220.6	219.7	218.6	217.2	215.9	214.5	213.1	211.9
75°	175.8	175.0	174.2	173.4	172.6	171.9	171.3	170.7	170.0	169.5	168.5
77.5°	133.8	133.4	132.9	132.5	132.0	131.5	130.7	130.0	129.3	128.5	127.9
80°	106.4	105.8	105.2	104.6	104.0	103.5	103.1	102.7	102.3	101.9	101.7
82.5°	79.7	79.6	79.5	79.3	79.2	79.1	79.0	79.0	78.9	78.8	78.4
85°	46.8	46.5	46.1	45.7	45.3	45.1	45.1	45.1	45.1	45.1	44.7
87.5°	18.9	18.7	18.3	18.2	17.9	17.8	17.9	18.1	18.2	18.3	18.1
90°	0.9	2.0	2.9	4.4	5.4	6.4	7.8	9.3	10.8	12.3	11.8
92.5°	6.1	9.0	13.2	17.0	21.1	28.4	41.2	62.3	83.1	75.5	57.0
95°	16.7	18.2	23.6	31.9	44.7	63.8	105.6	178.7	259.3	291.2	236.2
97.5°	28.5	29.0	33.2	40.5	53.0	73.8	113.7	196.1	330.4	451.3	482.8
100°	36.3	36.9	40.3	47.2	58.9	78.1	112.4	185.1	314.3	465.0	561.8
102.5°	44.6	45.5	48.6	55.0	65.6	83.2	114.0	175.7	290.8	439.5	565.8
105°	57.0	58.5	61.4	67.2	76.6	91.9	118.4	168.9	261.7	394.9	535.8
107.5°	70.1	71.6	74.5	80.2	89.0	103.1	126.4	168.4	243.3	355.3	483.4
110°	79.6	81.0	83.5	88.9	97.2	111.0	133.1	170.4	236.2	332.9	450.3



TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	88.2	89.7	92.1	97.6	105.9	119.2	139.7	174.4	232.3	318.1	421.6
115°	100.7	102.6	105.6	110.5	118.8	132.1	150.8	180.7	230.8	302.0	387.0
117.5°	113.1	115.4	117.9	122.3	131.7	144.0	162.5	189.2	231.7	292.6	366.1
120°	121.8	123.3	125.7	130.6	140.0	152.2	169.9	195.4	233.2	288.3	355.1
122.5°	129.2	130.7	133.2	138.4	147.4	160.5	177.8	201.4	236.0	285.5	346.0
125°	140.0	140.9	143.9	149.3	158.6	171.9	189.1	210.7	240.1	281.9	334.4
127.5°	148.1	149.6	153.3	158.7	169.0	182.3	198.9	218.3	244.9	280.1	324.3
130°	153.3	154.7	159.1	165.0	175.3	188.6	204.7	223.4	248.0	279.0	318.7
132.5°	157.1	159.0	163.8	170.9	181.2	194.1	209.9	228.2	250.4	278.5	313.6
135°	164.0	166.0	171.4	178.7	189.1	202.3	217.6	234.3	253.9	277.9	306.9
137.5°	170.5	172.5	177.9	185.7	196.0	208.2	222.8	238.8	256.2	276.9	301.2
140°	174.9	177.3	182.2	190.0	199.8	212.2	226.4	241.2	257.8	276.5	297.6
142.5°	179.5	181.6	186.9	194.0	203.8	215.3	229.1	243.5	259.0	275.7	294.5
145°	187.1	188.6	193.0	200.4	208.7	220.0	232.8	246.1	259.8	274.5	290.2
147.5°	194.8	195.6	200.0	206.4	214.4	224.0	235.7	247.6	259.8	272.7	286.1
150°	199.8	200.4	204.3	210.7	217.6	226.4	237.7	248.0	259.8	271.0	283.4
152.5°	205.0	205.1	209.1	214.6	220.7	229.1	238.8	248.8	258.6	269.1	280.3
155°	212.7	212.7	215.6	220.5	225.9	232.8	241.2	249.0	257.4	265.7	275.5
157.5°	218.7	219.1	221.4	225.8	230.4	235.7	242.4	249.5	255.6	262.6	270.2
160°	223.4	223.4	225.4	229.4	232.8	237.7	243.6	249.5	254.9	260.3	266.7
162.5°	227.0	227.0	228.6	231.7	234.7	238.8	244.0	249.1	253.3	258.0	263.1
165°	232.3	231.8	232.8	235.2	237.2	240.6	244.5	248.0	251.0	254.4	258.3
167.5°	236.3	235.7	236.2	238.1	239.4	241.6	244.4	247.2	248.6	250.8	253.7
170°	238.7	237.7	238.2	239.6	240.6	241.6	244.1	246.1	247.0	248.5	251.0
172.5°	240.2	239.6	239.8	240.8	241.4	242.0	244.1	245.6	245.8	246.5	248.2
175°	242.1	241.6	241.2	242.1	242.1	242.6	243.6	244.5	244.1	244.1	245.0
177.5°	243.0	242.6	242.2	242.6	242.6	242.6	243.0	243.7	243.0	242.6	243.0
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6



TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1044.5	1046.1	1047.7	1048.4	1048.3	1048.1	1047.9	1047.8
5°	1039.0	1040.9	1043.0	1043.8	1043.4	1043.0	1042.6	1042.2
7.5°	1027.9	1029.8	1031.6	1032.3	1032.1	1031.8	1031.6	1031.4
10°	1017.9	1019.6	1021.4	1022.2	1021.7	1021.3	1021.0	1020.5
12.5°	1006.8	1008.1	1009.4	1010.0	1009.7	1009.4	1009.3	1009.0
15°	986.8	988.3	990.0	990.2	988.9	987.7	986.6	985.4
17.5°	961.5	962.6	963.7	964.1	963.6	963.2	962.8	962.3
20°	942.8	943.6	944.4	944.5	943.9	943.3	942.7	942.1
22.5°	923.0	923.7	924.3	924.2	923.5	922.7	922.0	921.2
25°	890.2	890.4	890.6	890.4	889.8	889.2	888.6	888.0
27.5°	855.3	855.5	855.7	855.3	854.6	853.9	853.1	852.3
30°	831.2	831.2	831.2	830.5	829.1	827.7	826.3	824.9
32.5°	805.9	804.8	803.7	802.7	801.9	801.2	800.4	799.7
35°	764.8	763.6	762.4	761.3	760.3	759.3	758.3	757.2
37.5°	722.3	720.8	719.5	718.4	717.7	717.1	716.4	715.8
40°	694.6	693.0	691.4	690.2	689.4	688.5	687.8	687.0
42.5°	665.7	664.1	662.5	661.3	660.6	659.7	658.9	658.1
45°	622.7	620.3	617.9	616.1	615.2	614.2	613.1	612.2
47.5°	577.3	575.0	572.6	570.9	570.1	569.2	568.3	567.4
50°	547.3	545.1	542.9	541.2	540.0	538.8	537.6	536.4
52.5°	516.9	515.1	513.2	511.7	510.5	509.3	508.1	506.9
55°	470.7	468.5	466.3	464.7	463.6	462.7	461.7	460.7
57.5°	425.2	423.3	421.3	419.7	418.5	417.4	416.2	415.1
60°	393.0	391.2	389.4	388.1	387.0	386.1	385.0	384.1
62.5°	362.1	360.2	358.4	357.2	356.5	355.9	355.2	354.5
65°	315.9	314.4	312.7	311.6	311.0	310.4	309.8	309.2
67.5°	270.2	268.8	267.3	266.2	265.4	264.6	263.7	262.9
70°	240.6	239.2	237.8	236.6	235.6	234.6	233.6	232.6
72.5°	210.6	209.4	208.2	207.2	206.7	206.2	205.7	205.2
75°	167.5	166.5	165.5	164.7	164.1	163.5	162.9	162.3
77.5°	127.2	126.5	125.8	125.5	125.5	125.5	125.5	125.5
80°	101.5	101.3	101.1	101.0	101.0	101.0	101.0	101.0
82.5°	78.1	77.7	77.3	77.1	77.0	76.8	76.6	76.5
85°	44.3	43.9	43.5	43.3	43.3	43.3	43.3	43.3
87.5°	18.0	17.9	17.9	18.0	17.9	18.0	18.1	18.0
90°	12.3	12.7	13.3	14.2	13.8	14.2	14.7	14.2
92.5°	41.3	32.8	29.0	26.4	25.6	24.0	24.5	23.7
95°	176.8	119.9	93.8	76.1	66.8	62.3	58.9	57.0
97.5°	440.7	353.0	289.6	230.9	194.7	172.5	159.3	155.1
100°	579.0	539.2	481.7	412.0	362.4	326.6	307.5	307.9
102.5°	625.0	623.7	590.2	546.0	507.4	479.0	463.0	451.7
105°	638.4	687.5	696.9	684.1	661.5	642.8	627.2	624.7
107.5°	599.7	679.5	722.5	739.9	740.4	734.1	728.8	724.3
110°	562.7	653.2	715.1	749.4	763.2	767.1	766.1	765.1





TEST NUMBER: P331972-935

CATALOG NUMBER: S123DIP-S775D585U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	526.2	618.5	687.9	732.1	757.2	769.5	773.2	773.4
115°	477.9	563.3	635.5	689.0	725.8	747.4	757.2	759.7
117.5°	442.7	516.5	581.3	635.7	674.1	698.8	713.0	716.3
120°	424.3	490.6	549.5	599.2	637.9	665.5	677.2	680.2
122.5°	409.7	469.8	524.3	570.4	604.9	629.6	642.7	646.4
125°	390.4	443.9	491.1	530.4	561.8	583.4	595.7	599.2
127.5°	373.5	421.3	463.8	499.6	527.5	546.0	557.1	560.3
130°	362.9	407.1	446.9	480.3	506.4	524.0	534.3	538.2
132.5°	353.1	393.7	430.8	462.6	487.1	504.7	513.8	516.6
135°	339.8	374.7	406.7	434.6	458.7	473.4	482.2	485.7
137.5°	327.8	356.4	383.8	408.1	428.3	443.2	450.7	453.0
140°	320.7	345.7	369.3	390.4	409.1	422.8	430.7	430.2
142.5°	314.0	335.5	355.9	374.3	390.2	402.4	409.5	409.0
145°	305.9	322.2	337.9	352.1	364.4	374.7	378.7	379.6
147.5°	299.4	312.2	324.9	335.0	344.3	351.3	355.1	355.4
150°	294.6	305.9	316.2	325.6	332.9	338.4	341.3	341.3
152.5°	290.3	300.1	309.2	316.9	322.7	327.8	329.5	329.5
155°	283.9	291.7	299.1	305.0	309.4	313.3	314.3	314.8
157.5°	277.0	283.5	289.3	293.9	297.7	300.7	301.4	301.4
160°	273.0	278.4	283.4	286.8	290.2	293.2	293.2	292.7
162.5°	268.4	272.9	277.5	280.5	282.8	285.3	285.3	284.8
165°	262.3	265.2	268.6	271.0	273.0	275.0	274.5	274.5
167.5°	256.9	259.2	261.1	262.9	263.8	265.2	264.7	264.7
170°	253.4	254.9	256.8	257.8	258.3	259.3	258.8	258.8
172.5°	250.3	251.3	252.9	253.5	253.6	254.6	253.7	253.3
175°	246.1	246.5	247.5	247.5	247.5	248.0	247.5	247.0
177.5°	243.4	243.7	244.2	244.2	243.7	244.2	243.4	243.4
180°	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

(END OF REPORT)