

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331930-940

Luminaire Tested: **S123DIP-S560D805U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331930-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D805U940-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4721.3 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33				33
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				28
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	27	24	21				21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				18
7	58	46	38	32	53	42	35	31	36	31	27	30	26	23	24	21	19	16				16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15				15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7587	7587	7587	7587
5°	9048	7621	6753	7621
10°	11326	7582	6099	7582
15°	13891	7520	5678	7520
20°	16549	7425	5407	7425
25°	17570	7310	5346	7310
30°	15060	7225	5374	7225
35°	10474	7104	5430	7104
40°	7888	6962	5413	6962
45°	6550	6753	5345	6753
50°	5868	6325	5297	6325
55°	5485	5864	5230	5864
60°	5147	5382	5175	5382
65°	4834	4905	5010	4905
70°	4535	4365	4771	4365
75°	4059	3818	4375	3818
80°	3552	3137	3769	3137
85°	2791	2285	2532	2285



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.4	1.5
10°-20°	222.7	4.7
20°-30°	373.7	7.9
30°-40°	423.1	9.0
40°-50°	379.5	8.0
50°-60°	306.2	6.5
60°-70°	213.4	4.5
70°-80°	112.2	2.4
80°-90°	30.1	0.6
90°-100°	191.7	4.1
100°-110°	542.7	11.5
110°-120°	533.9	11.3
120°-130°	425.8	9.0
130°-140°	335.7	7.1
140°-150°	250.6	5.3
150°-160°	174.7	3.7
160°-170°	102.6	2.2
170°-180°	33.4	0.7
0°-30°	665.8	14.1
0°-40°	1088.9	23.1
0°-60°	1774.6	37.6
0°-90°	2130.2	45.1
90°-120°	1268.2	26.9
90°-150°	2280.4	48.3
90°-180°	2591.0	54.9
0°-180°	4721.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	705	705	705	705	705	
5°	837	705	625	705	837	87
15°	1246	675	510	675	1246	360
25°	1479	616	450	616	1479	649
35°	797	541	413	541	797	518
45°	430	444	351	444	430	340
55°	292	312	279	312	292	262
65°	190	193	197	193	190	189
75°	98	92	105	92	98	105
85°	23	18	20	18	23	27
90°	20	1	20	1	20	12
95°	81	24	81	24	81	146
105°	887	81	887	81	887	875
115°	1078	143	1078	143	1078	1048
125°	850	199	850	199	850	771
135°	690	233	690	233	690	535
145°	539	266	539	266	539	343
155°	447	302	447	302	447	208
165°	390	330	390	330	390	111
175°	351	344	351	344	351	34
180°	344	344	344	344	344	



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	748.1	747.5	746.2	747.3	745.0	742.1	741.8	739.0	731.1	730.6	728.4
5°	837.4	834.6	834.4	834.0	829.2	822.7	810.4	809.4	793.0	784.8	774.9
7.5°	953.1	954.6	949.6	945.2	930.6	921.0	907.8	890.9	870.8	850.3	836.7
10°	1036.2	1047.4	1033.4	1023.9	1015.0	998.3	978.8	954.6	930.3	902.0	880.5
12.5°	1125.2	1130.8	1128.0	1118.9	1105.2	1079.7	1045.2	1018.5	996.1	949.0	929.9
15°	1246.5	1267.4	1254.1	1223.3	1224.1	1199.8	1154.7	1105.2	1078.9	1037.5	981.1
17.5°	1375.8	1378.4	1372.7	1347.1	1330.0	1296.7	1255.1	1207.6	1154.3	1104.4	1044.6
20°	1444.7	1442.6	1430.7	1417.3	1387.9	1362.0	1316.5	1263.6	1195.3	1146.1	1080.9
22.5°	1482.9	1479.4	1473.8	1462.7	1438.2	1410.3	1369.6	1311.7	1246.7	1178.9	1103.6
25°	1479.4	1483.9	1484.6	1481.5	1473.0	1456.3	1424.2	1378.0	1313.1	1226.1	1147.5
27.5°	1345.6	1351.8	1370.1	1386.3	1404.4	1422.8	1420.4	1397.5	1349.5	1274.3	1178.2
30°	1211.7	1198.0	1231.9	1274.5	1303.6	1354.8	1383.5	1385.2	1358.3	1293.7	1200.1
32.5°	1025.9	1041.0	1055.9	1108.4	1171.9	1229.4	1286.5	1332.5	1337.7	1294.8	1212.9
35°	797.1	815.9	843.2	870.6	938.9	997.6	1098.0	1185.4	1255.1	1264.3	1214.1
37.5°	642.3	651.7	668.9	696.2	740.9	810.7	888.3	998.8	1099.7	1174.8	1178.1
40°	561.4	564.2	583.6	604.5	640.7	698.0	768.1	865.8	986.7	1091.5	1135.2
42.5°	500.8	506.8	515.1	535.1	563.9	607.1	672.2	753.0	863.7	984.4	1069.9
45°	430.3	437.1	442.3	455.6	476.1	505.1	550.5	624.3	708.6	833.3	948.4
47.5°	383.7	384.2	388.1	398.1	412.1	433.9	466.0	513.4	590.8	691.9	810.1
50°	350.4	355.9	357.2	365.1	376.0	392.1	418.7	459.0	522.5	611.4	720.0
52.5°	326.9	328.5	332.3	338.0	347.6	360.1	383.2	414.7	464.6	540.3	640.2
55°	292.3	292.3	296.1	300.5	306.0	317.3	332.6	355.9	393.8	452.5	535.2
57.5°	260.4	262.1	264.7	266.1	270.7	278.2	291.1	308.7	337.0	382.2	447.9
60°	239.1	242.1	241.8	244.5	248.6	254.4	265.4	279.7	305.0	341.2	396.5
62.5°	220.5	220.3	220.3	223.5	227.6	233.1	240.2	252.6	274.1	306.2	353.3
65°	189.8	189.2	191.6	193.7	195.0	199.1	204.6	215.5	229.9	253.8	290.3
67.5°	162.7	160.7	162.0	162.7	165.1	168.3	173.3	180.1	191.5	210.7	238.3
70°	144.1	142.4	142.0	142.8	144.8	147.2	151.0	157.5	168.0	183.4	203.6
72.5°	125.0	123.9	123.8	125.3	126.3	127.8	130.5	136.4	144.8	156.3	175.1
75°	97.6	97.6	97.6	98.0	99.1	100.4	102.5	105.5	112.0	120.2	132.9
77.5°	73.2	73.1	72.8	72.7	74.2	74.8	75.3	78.1	81.8	87.3	96.5
80°	57.3	55.6	56.4	57.3	58.1	58.4	59.4	60.1	63.2	66.3	72.8
82.5°	42.6	41.2	41.3	42.9	43.1	43.3	44.4	45.4	46.5	49.3	52.8
85°	22.6	22.6	22.9	22.9	23.2	22.9	23.9	24.3	24.3	25.9	28.0
87.5°	12.2	11.9	11.9	12.1	11.9	11.9	12.1	12.2	12.4	12.8	12.7
90°	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4	16.8	17.4	15.3
92.5°	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7	80.9	107.2	118.0
95°	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0	335.4	413.4	368.1
97.5°	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6	685.5	640.7	469.0
100°	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0	797.5	660.2	446.2
102.5°	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2	803.2	623.9	412.7
105°	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3	760.6	560.5	371.6
107.5°	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4	686.2	504.4	345.4
110°	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0	639.3	472.7	335.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1	598.6	451.5	329.8
115°	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3	549.4	428.7	327.7
117.5°	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6	519.7	415.4	329.0
120°	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4	504.1	409.2	331.2
122.5°	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8	491.2	405.4	335.0
125°	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2	474.7	400.2	340.9
127.5°	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3	460.3	397.7	347.6
130°	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2	452.5	396.0	352.0
132.5°	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2	445.2	395.4	355.4
135°	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4	435.7	394.6	360.4
137.5°	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3	427.5	393.1	363.8
140°	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2	422.5	392.5	366.0
142.5°	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8	418.0	391.4	367.7
145°	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4	412.1	389.7	368.8
147.5°	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0	406.2	387.1	368.8
150°	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3	402.3	384.9	368.8
152.5°	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1	397.8	382.0	367.1
155°	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0	391.1	377.2	365.3
157.5°	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2	383.6	372.8	362.9
160°	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6	378.5	369.5	361.9
162.5°	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9	373.5	366.1	359.6
165°	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3	366.7	361.1	356.2
167.5°	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7	360.2	356.1	352.9
170°	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7	356.2	352.8	350.7
172.5°	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3	352.3	350.0	349.0
175°	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3	347.9	346.5	346.5
177.5°	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	726.7	724.6	722.4	718.5	715.2	710.6	709.3	707.7	702.8	698.3	695.1
5°	771.2	762.9	751.0	740.0	731.2	719.3	712.4	705.3	695.0	685.8	678.2
7.5°	817.6	801.5	782.9	762.9	744.1	726.0	711.5	698.6	684.2	670.6	660.0
10°	854.5	831.3	805.3	777.3	753.4	730.1	710.7	693.7	675.2	659.2	645.8
12.5°	896.5	862.1	826.3	792.3	764.0	731.8	708.3	686.5	665.7	646.3	631.3
15°	946.4	902.7	860.3	813.5	770.4	730.1	702.1	674.8	650.6	630.8	611.6
17.5°	991.7	942.2	886.4	829.5	777.6	729.8	690.5	659.7	629.4	605.1	586.0
20°	1017.4	961.0	897.9	838.7	781.4	728.1	685.1	648.2	615.5	589.8	568.3
22.5°	1039.6	973.6	908.2	845.1	781.1	723.7	675.0	637.0	601.5	576.4	553.6
25°	1062.5	983.6	918.0	843.9	772.5	713.1	658.4	615.5	579.9	550.5	527.0
27.5°	1082.2	982.9	905.1	825.4	759.0	699.5	641.1	594.9	557.2	525.3	501.4
30°	1095.3	984.3	891.7	812.8	745.9	684.4	627.7	581.3	541.6	509.2	486.7
32.5°	1103.5	983.5	879.4	795.3	725.1	670.7	613.2	565.2	524.4	492.6	470.8
35°	1108.2	977.4	858.3	759.2	691.6	638.6	590.5	540.6	497.9	468.2	443.6
37.5°	1098.7	964.8	833.7	724.3	650.3	598.2	557.7	515.2	474.4	441.7	420.4
40°	1083.6	956.6	814.5	699.8	621.9	571.7	537.3	495.5	455.2	424.2	404.4
42.5°	1055.0	940.0	793.5	672.4	592.4	542.2	510.4	475.6	437.5	408.3	388.5
45°	985.0	903.7	762.0	631.5	548.8	497.0	469.0	443.6	409.1	380.8	363.7
47.5°	887.8	849.1	716.3	588.3	503.4	453.4	424.3	403.9	378.7	355.9	339.5
50°	820.4	804.3	685.5	558.7	473.0	424.2	396.2	377.7	359.6	336.7	321.7
52.5°	742.4	752.3	649.3	528.2	442.1	394.1	367.7	353.1	336.7	317.9	304.8
55°	632.8	668.7	587.1	476.8	396.2	350.4	325.5	312.5	302.9	288.9	277.7
57.5°	530.2	575.8	519.7	423.8	351.0	311.6	287.7	273.5	267.3	260.0	251.2
60°	469.2	514.3	471.6	388.3	320.7	283.1	262.0	250.0	243.9	238.7	231.2
62.5°	414.9	460.5	424.6	352.2	290.9	256.1	237.6	226.0	221.1	218.5	212.0
65°	340.2	379.4	355.5	296.1	248.3	217.6	200.8	192.6	188.2	187.2	183.1
67.5°	276.9	306.7	289.4	245.6	207.9	181.4	167.2	160.2	156.9	156.5	153.4
70°	235.3	263.3	250.0	210.4	177.9	157.1	144.8	138.7	136.6	136.3	134.6
72.5°	203.0	222.6	212.0	179.0	153.9	135.0	125.9	119.5	117.2	117.7	116.5
75°	150.3	165.0	158.8	135.9	115.7	103.4	95.9	91.8	89.8	90.9	89.4
77.5°	108.2	117.4	111.9	96.0	83.6	74.7	69.2	66.7	64.8	64.7	64.1
80°	81.6	87.1	84.0	74.5	64.2	56.7	52.3	50.6	49.5	49.2	48.9
82.5°	58.1	62.8	59.1	52.6	45.7	41.1	38.6	36.4	35.6	35.8	35.5
85°	29.3	31.1	29.7	25.6	22.9	20.9	19.4	18.5	17.7	18.1	17.4
87.5°	12.8	12.6	11.4	10.0	9.2	7.9	7.7	6.9	6.6	6.9	7.0
90°	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4	2.8	4.2	6.2
92.5°	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6	12.8	18.7	24.2
95°	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7	25.8	33.4	45.3
97.5°	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4	41.1	47.2	57.4
100°	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6	52.3	57.2	67.0
102.5°	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3	64.6	68.8	78.1
105°	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9	82.9	87.1	95.5
107.5°	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5	101.7	105.7	113.9
110°	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0	115.0	118.5	126.2





TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2	127.3	130.8	138.5
115°	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9	145.7	149.9	156.9
117.5°	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6	163.8	167.3	173.7
120°	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9	175.0	178.4	185.5
122.5°	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5	185.6	189.0	196.6
125°	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7	200.1	204.3	212.0
127.5°	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3	212.3	217.5	225.3
130°	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5	219.6	225.9	234.3
132.5°	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1	225.8	232.6	242.6
135°	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8	235.7	243.3	253.8
137.5°	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0	245.0	252.5	263.7
140°	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2	251.6	258.7	269.8
142.5°	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9	257.8	265.4	275.4
145°	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6	267.7	274.0	284.5
147.5°	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5	277.8	283.9	292.9
150°	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7	284.5	290.0	299.1
152.5°	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0	291.1	296.7	304.7
155°	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8	301.8	306.0	313.0
157.5°	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5	311.0	314.4	320.6
160°	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2	317.2	320.0	325.6
162.5°	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3	322.3	324.5	329.0
165°	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8	329.0	330.5	333.9
167.5°	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5	334.7	335.4	338.0
170°	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9	337.4	338.1	340.2
172.5°	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1	340.2	340.4	341.9
175°	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7	343.0	342.3	343.7
177.5°	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9	344.4	343.8	344.4
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	693.1	691.3	688.5	684.4	681.1	675.9	675.9	676.7	676.7	676.5	675.9
5°	672.1	667.0	660.8	653.7	646.1	638.6	637.3	634.5	632.5	631.2	629.5
7.5°	649.9	640.9	631.9	621.9	612.7	605.1	599.9	595.5	592.6	589.7	587.5
10°	634.9	623.6	613.1	602.4	590.8	581.6	575.8	571.7	568.6	565.9	564.5
12.5°	617.2	604.2	592.5	582.5	569.8	560.3	554.7	552.9	549.2	543.5	540.5
15°	591.2	579.3	565.3	549.8	543.7	532.1	525.6	522.5	520.5	516.0	514.7
17.5°	569.0	553.3	537.6	526.1	514.7	505.3	501.7	497.8	495.2	491.5	490.4
20°	551.3	537.3	522.9	510.6	498.6	488.4	485.3	482.6	479.8	478.1	476.8
22.5°	533.2	519.2	507.3	495.8	483.0	476.4	473.0	470.0	468.1	466.9	465.6
25°	507.8	495.5	482.2	472.0	461.7	457.3	455.2	453.5	452.2	450.5	450.1
27.5°	485.2	471.8	461.0	451.4	444.1	440.3	438.4	437.6	437.8	438.5	438.8
30°	468.2	455.9	447.0	438.8	432.0	428.6	428.3	428.3	429.6	430.0	430.7
32.5°	452.6	442.6	433.6	425.7	420.5	418.2	419.5	419.5	420.6	421.5	422.8
35°	430.0	421.1	414.3	407.4	403.0	404.0	404.7	405.4	407.1	409.1	410.5
37.5°	408.3	400.6	393.5	388.2	386.1	388.0	389.6	391.0	393.1	394.6	395.9
40°	392.7	386.9	380.1	375.3	376.0	377.0	378.4	380.1	381.8	382.8	384.2
42.5°	378.3	372.2	367.0	363.0	364.0	365.3	366.1	367.0	369.0	370.9	371.7
45°	356.2	351.4	346.6	344.3	344.9	345.6	346.3	347.3	349.0	350.4	350.7
47.5°	331.4	328.1	324.9	322.5	323.6	323.3	324.2	326.5	327.0	327.8	329.7
50°	315.6	312.5	308.7	308.1	308.1	308.1	308.4	311.1	311.1	312.5	313.9
52.5°	298.1	296.1	293.7	292.5	291.9	291.9	293.4	294.7	295.2	297.2	298.5
55°	272.2	270.1	268.1	267.1	266.4	267.1	269.8	270.5	272.2	273.2	274.2
57.5°	245.2	243.6	242.0	241.5	241.3	242.2	243.7	245.8	246.2	249.3	250.8
60°	227.5	225.1	223.7	223.7	223.0	226.0	225.4	228.8	229.5	231.6	234.0
62.5°	209.1	205.9	205.4	205.4	206.3	207.2	208.2	209.7	211.5	214.1	215.9
65°	179.7	177.9	180.3	179.9	179.3	181.4	181.4	183.1	185.1	187.5	191.3
67.5°	151.7	150.8	151.1	151.1	152.0	153.2	154.2	155.7	158.1	160.7	163.1
70°	132.9	133.8	132.2	133.6	134.6	134.9	135.5	137.6	140.4	142.0	144.8
72.5°	114.6	114.5	114.7	115.2	116.3	116.9	117.5	119.8	122.9	124.3	126.5
75°	88.1	87.7	88.8	88.8	90.5	91.2	91.8	92.9	95.6	97.6	99.4
77.5°	64.4	64.7	64.6	65.7	65.3	65.4	67.5	68.5	68.8	72.9	73.7
80°	48.5	49.2	49.5	49.8	50.2	49.5	51.9	53.0	53.0	55.3	57.1
82.5°	34.9	35.2	36.1	36.5	36.6	37.2	37.5	38.2	39.0	40.0	42.3
85°	17.4	18.5	18.8	18.5	18.8	18.1	19.1	19.4	19.8	19.8	19.8
87.5°	7.0	7.6	7.7	8.4	8.6	9.2	9.1	8.6	8.8	9.8	8.9
90°	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4	18.1	18.8	20.2
92.5°	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7	46.5	41.1	37.5
95°	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0	170.1	133.1	108.1
97.5°	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6	501.1	411.2	327.8
100°	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0	765.4	683.9	584.9
102.5°	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2	885.4	837.9	775.1
105°	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3	976.0	989.3	971.2
107.5°	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4	964.6	1025.6	1050.4
110°	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0	927.2	1015.0	1063.9



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1	878.2	976.6	1039.3
115°	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3	799.6	902.1	978.1
117.5°	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6	733.3	825.3	902.4
120°	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4	696.4	780.2	850.5
122.5°	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8	666.9	744.4	809.9
125°	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2	630.3	697.1	753.0
127.5°	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3	598.0	658.4	709.2
130°	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2	577.9	634.5	681.8
132.5°	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2	559.0	611.5	656.7
135°	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4	531.9	577.2	617.0
137.5°	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3	505.9	544.9	579.3
140°	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2	490.8	524.2	554.2
142.5°	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8	476.3	505.3	531.4
145°	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4	457.4	479.7	499.9
147.5°	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0	443.3	461.3	475.6
150°	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3	434.4	449.0	462.2
152.5°	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1	426.0	438.9	450.0
155°	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0	414.1	424.5	432.9
157.5°	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2	402.5	410.6	417.1
160°	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6	395.3	402.3	407.2
162.5°	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9	387.4	393.9	398.2
165°	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3	376.5	381.4	384.9
167.5°	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7	367.9	370.8	373.3
170°	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7	361.9	364.6	366.0
172.5°	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3	356.8	359.0	359.9
175°	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3	350.0	351.3	351.3
177.5°	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5	346.1	346.6	346.6
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	674.0	673.8	675.6	674.3	675.6	673.8	674.0	675.9	676.5	676.7	676.7
5°	627.4	628.4	625.0	625.0	625.0	628.4	627.4	629.5	631.2	632.5	634.5
7.5°	585.9	584.3	584.5	582.6	584.5	584.3	585.9	587.5	589.7	592.6	595.5
10°	560.4	558.4	557.7	558.0	557.7	558.4	560.4	564.5	565.9	568.6	571.7
12.5°	539.4	539.0	534.5	534.6	534.5	539.0	539.4	540.5	543.5	549.2	552.9
15°	514.7	508.2	507.5	509.5	507.5	508.2	514.7	514.7	516.0	520.5	522.5
17.5°	489.9	486.4	486.7	485.6	486.7	486.4	489.9	490.4	491.5	495.2	497.8
20°	476.8	474.7	474.4	472.0	474.4	474.7	476.8	476.8	478.1	479.8	482.6
22.5°	464.8	464.0	464.2	461.6	464.2	464.0	464.8	465.6	466.9	468.1	470.0
25°	449.8	451.5	450.1	450.1	450.1	451.5	449.8	450.1	450.5	452.2	453.5
27.5°	439.7	439.6	438.9	438.9	438.9	439.6	439.7	438.8	438.5	437.8	437.6
30°	432.0	431.7	432.4	432.4	432.4	431.7	432.0	430.7	430.0	429.6	428.3
32.5°	424.4	424.8	425.0	425.3	425.0	424.8	424.4	422.8	421.5	420.6	419.5
35°	412.6	412.9	413.9	413.2	413.9	412.9	412.6	410.5	409.1	407.1	405.4
37.5°	396.5	398.1	397.8	398.3	397.8	398.1	396.5	395.9	394.6	393.1	391.0
40°	384.6	385.6	385.2	385.2	385.2	385.6	384.6	384.2	382.8	381.8	380.1
42.5°	372.3	373.0	372.1	371.6	372.1	373.0	372.3	371.7	370.9	369.0	367.0
45°	352.1	351.4	352.5	351.1	352.5	351.4	352.1	350.7	350.4	349.0	347.3
47.5°	329.6	330.3	330.6	331.5	330.6	330.3	329.6	329.7	327.8	327.0	326.5
50°	314.5	316.6	316.6	316.3	316.6	316.6	314.5	313.9	312.5	311.1	311.1
52.5°	299.8	300.8	302.1	302.0	302.1	300.8	299.8	298.5	297.2	295.2	294.7
55°	277.0	277.7	278.3	278.7	278.3	277.7	277.0	274.2	273.2	272.2	270.5
57.5°	253.3	253.1	254.7	255.2	254.7	253.1	253.3	250.8	249.3	246.2	245.8
60°	236.7	236.7	239.4	240.4	239.4	236.7	236.7	234.0	231.6	229.5	228.8
62.5°	218.9	220.0	222.7	221.3	222.7	220.0	218.9	215.9	214.1	211.5	209.7
65°	193.0	195.7	195.4	196.7	195.4	195.7	193.0	191.3	187.5	185.1	183.1
67.5°	165.9	167.6	170.0	170.2	170.0	167.6	165.9	163.1	160.7	158.1	155.7
70°	147.6	149.3	150.6	151.6	150.6	149.3	147.6	144.8	142.0	140.4	137.6
72.5°	129.7	130.6	133.9	132.5	133.9	130.6	129.7	126.5	124.3	122.9	119.8
75°	101.7	104.2	106.2	105.2	106.2	104.2	101.7	99.4	97.6	95.6	92.9
77.5°	75.3	77.7	78.6	77.8	78.6	77.7	75.3	73.7	72.9	68.8	68.5
80°	59.4	59.1	61.2	60.8	61.2	59.1	59.4	57.1	55.3	53.0	53.0
82.5°	43.6	43.2	44.2	44.4	44.2	43.2	43.6	42.3	40.0	39.0	38.2
85°	21.1	22.2	20.9	20.5	20.9	22.2	21.1	19.8	19.8	19.8	19.4
87.5°	8.8	8.9	8.8	8.4	8.8	8.9	8.8	8.9	9.8	8.8	8.6
90°	19.5	20.2	21.0	20.2	21.0	20.2	19.5	20.2	18.8	18.1	17.4
92.5°	36.3	34.2	34.9	33.6	34.9	34.2	36.3	37.5	41.1	46.5	58.7
95°	94.8	88.5	83.6	80.9	83.6	88.5	94.8	108.1	133.1	170.1	251.0
97.5°	276.3	245.0	226.1	220.2	226.1	245.0	276.3	327.8	411.2	501.1	625.6
100°	514.5	463.6	436.4	437.1	436.4	463.6	514.5	584.9	683.9	765.4	822.0
102.5°	720.3	680.0	657.3	641.2	657.3	680.0	720.3	775.1	837.9	885.4	887.2
105°	939.1	912.6	890.3	886.8	890.3	912.6	939.1	971.2	989.3	976.0	906.3
107.5°	1051.1	1042.1	1034.6	1028.1	1034.6	1042.1	1051.1	1050.4	1025.6	964.6	851.4
110°	1083.3	1089.0	1087.5	1086.2	1087.5	1089.0	1083.3	1063.9	1015.0	927.2	799.0



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1075.0	1092.3	1097.6	1097.9	1097.6	1092.3	1075.0	1039.3	976.6	878.2	747.1
115°	1030.4	1061.0	1075.0	1078.5	1075.0	1061.0	1030.4	978.1	902.1	799.6	678.3
117.5°	956.9	992.0	1012.1	1016.9	1012.1	992.0	956.9	902.4	825.3	733.3	628.6
120°	905.6	944.7	961.4	965.5	961.4	944.7	905.6	850.5	780.2	696.4	602.4
122.5°	858.7	893.9	912.3	917.6	912.3	893.9	858.7	809.9	744.4	666.9	581.8
125°	797.5	828.2	845.6	850.5	845.6	828.2	797.5	753.0	697.1	630.3	554.2
127.5°	748.9	775.1	790.9	795.3	790.9	775.1	748.9	709.2	658.4	598.0	530.3
130°	718.8	743.9	758.5	764.1	758.5	743.9	718.8	681.8	634.5	577.9	515.2
132.5°	691.4	716.6	729.5	733.4	729.5	716.6	691.4	656.7	611.5	559.0	501.2
135°	651.1	672.1	684.6	689.5	684.6	672.1	651.1	617.0	577.2	531.9	482.4
137.5°	608.1	629.3	639.9	643.1	639.9	629.3	608.1	579.3	544.9	505.9	465.3
140°	580.8	600.2	611.4	610.7	611.4	600.2	580.8	554.2	524.2	490.8	455.2
142.5°	553.9	571.2	581.3	580.6	581.3	571.2	553.9	531.4	505.3	476.3	445.8
145°	517.3	531.9	537.5	538.9	537.5	531.9	517.3	499.9	479.7	457.4	434.4
147.5°	488.8	498.7	504.1	504.6	504.1	498.7	488.8	475.6	461.3	443.3	425.0
150°	472.7	480.4	484.6	484.6	484.6	480.4	472.7	462.2	449.0	434.4	418.3
152.5°	458.2	465.3	467.8	467.8	467.8	465.3	458.2	450.0	438.9	426.0	412.1
155°	439.2	444.8	446.2	446.8	446.2	444.8	439.2	432.9	424.5	414.1	403.0
157.5°	422.6	426.8	427.9	427.8	427.9	426.8	422.6	417.1	410.6	402.5	393.2
160°	412.1	416.2	416.2	415.5	416.2	416.2	412.1	407.2	402.3	395.3	387.6
162.5°	401.4	405.0	405.0	404.4	405.0	405.0	401.4	398.2	393.9	387.4	380.9
165°	387.6	390.4	389.7	389.7	389.7	390.4	387.6	384.9	381.4	376.5	372.3
167.5°	374.5	376.5	375.8	375.8	375.8	376.5	374.5	373.3	370.8	367.9	364.7
170°	366.7	368.1	367.4	367.4	367.4	368.1	366.7	366.0	364.6	361.9	359.7
172.5°	360.0	361.4	360.2	359.6	360.2	361.4	360.0	359.9	359.0	356.8	355.3
175°	351.3	352.0	351.3	350.7	351.3	352.0	351.3	351.3	351.3	350.0	349.3
177.5°	346.1	346.6	345.5	345.5	345.5	346.6	346.1	346.6	346.6	346.1	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	675.9	675.9	681.1	684.4	688.5	691.3	693.1	695.1	698.3	702.8	707.7
5°	637.3	638.6	646.1	653.7	660.8	667.0	672.1	678.2	685.8	695.0	705.3
7.5°	599.9	605.1	612.7	621.9	631.9	640.9	649.9	660.0	670.6	684.2	698.6
10°	575.8	581.6	590.8	602.4	613.1	623.6	634.9	645.8	659.2	675.2	693.7
12.5°	554.7	560.3	569.8	582.5	592.5	604.2	617.2	631.3	646.3	665.7	686.5
15°	525.6	532.1	543.7	549.8	565.3	579.3	591.2	611.6	630.8	650.6	674.8
17.5°	501.7	505.3	514.7	526.1	537.6	553.3	569.0	586.0	605.1	629.4	659.7
20°	485.3	488.4	498.6	510.6	522.9	537.3	551.3	568.3	589.8	615.5	648.2
22.5°	473.0	476.4	483.0	495.8	507.3	519.2	533.2	553.6	576.4	601.5	637.0
25°	455.2	457.3	461.7	472.0	482.2	495.5	507.8	527.0	550.5	579.9	615.5
27.5°	438.4	440.3	444.1	451.4	461.0	471.8	485.2	501.4	525.3	557.2	594.9
30°	428.3	428.6	432.0	438.8	447.0	455.9	468.2	486.7	509.2	541.6	581.3
32.5°	419.5	418.2	420.5	425.7	433.6	442.6	452.6	470.8	492.6	524.4	565.2
35°	404.7	404.0	403.0	407.4	414.3	421.1	430.0	443.6	468.2	497.9	540.6
37.5°	389.6	388.0	386.1	388.2	393.5	400.6	408.3	420.4	441.7	474.4	515.2
40°	378.4	377.0	376.0	375.3	380.1	386.9	392.7	404.4	424.2	455.2	495.5
42.5°	366.1	365.3	364.0	363.0	367.0	372.2	378.3	388.5	408.3	437.5	475.6
45°	346.3	345.6	344.9	344.3	346.6	351.4	356.2	363.7	380.8	409.1	443.6
47.5°	324.2	323.3	323.6	322.5	324.9	328.1	331.4	339.5	355.9	378.7	403.9
50°	308.4	308.1	308.1	308.1	308.7	312.5	315.6	321.7	336.7	359.6	377.7
52.5°	293.4	291.9	291.9	292.5	293.7	296.1	298.1	304.8	317.9	336.7	353.1
55°	269.8	267.1	266.4	267.1	268.1	270.1	272.2	277.7	288.9	302.9	312.5
57.5°	243.7	242.2	241.3	241.5	242.0	243.6	245.2	251.2	260.0	267.3	273.5
60°	225.4	226.0	223.0	223.7	223.7	225.1	227.5	231.2	238.7	243.9	250.0
62.5°	208.2	207.2	206.3	205.4	205.4	205.9	209.1	212.0	218.5	221.1	226.0
65°	181.4	181.4	179.3	179.9	180.3	177.9	179.7	183.1	187.2	188.2	192.6
67.5°	154.2	153.2	152.0	151.1	151.1	150.8	151.7	153.4	156.5	156.9	160.2
70°	135.5	134.9	134.6	133.6	132.2	133.8	132.9	134.6	136.3	136.6	138.7
72.5°	117.5	116.9	116.3	115.2	114.7	114.5	114.6	116.5	117.7	117.2	119.5
75°	91.8	91.2	90.5	88.8	88.8	87.7	88.1	89.4	90.9	89.8	91.8
77.5°	67.5	65.4	65.3	65.7	64.6	64.7	64.4	64.1	64.7	64.8	66.7
80°	51.9	49.5	50.2	49.8	49.5	49.2	48.5	48.9	49.2	49.5	50.6
82.5°	37.5	37.2	36.6	36.5	36.1	35.2	34.9	35.5	35.8	35.6	36.4
85°	19.1	18.1	18.8	18.5	18.8	18.5	17.4	17.4	18.1	17.7	18.5
87.5°	9.1	9.2	8.6	8.4	7.7	7.6	7.0	7.0	6.9	6.6	6.9
90°	16.8	17.4	15.3	13.3	11.1	9.1	7.7	6.2	4.2	2.8	1.4
92.5°	80.9	107.2	118.0	88.5	58.6	40.3	30.0	24.2	18.7	12.8	8.6
95°	335.4	413.4	368.1	253.8	149.9	90.6	63.4	45.3	33.4	25.8	23.7
97.5°	685.5	640.7	469.0	278.5	161.3	104.7	75.3	57.4	47.2	41.1	40.4
100°	797.5	660.2	446.2	262.8	159.6	110.8	83.6	67.0	57.2	52.3	51.6
102.5°	803.2	623.9	412.7	249.4	161.8	118.1	93.2	78.1	68.8	64.6	63.3
105°	760.6	560.5	371.6	239.8	168.0	130.4	108.8	95.5	87.1	82.9	80.9
107.5°	686.2	504.4	345.4	239.2	179.4	146.4	126.4	113.9	105.7	101.7	99.5
110°	639.3	472.7	335.4	241.9	189.0	157.6	138.0	126.2	118.5	115.0	113.0



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	598.6	451.5	329.8	247.4	198.4	169.2	150.3	138.5	130.8	127.3	125.2
115°	549.4	428.7	327.7	256.5	214.0	187.5	168.7	156.9	149.9	145.7	142.9
117.5°	519.7	415.4	329.0	268.6	230.6	204.4	187.0	173.7	167.3	163.8	160.6
120°	504.1	409.2	331.2	277.5	241.2	216.2	198.7	185.5	178.4	175.0	172.9
122.5°	491.2	405.4	335.0	285.8	252.4	227.8	209.3	196.6	189.0	185.6	183.5
125°	474.7	400.2	340.9	299.1	268.4	244.0	225.2	212.0	204.3	200.1	198.7
127.5°	460.3	397.7	347.6	310.0	282.3	258.8	240.0	225.3	217.5	212.3	210.3
130°	452.5	396.0	352.0	317.2	290.7	267.7	248.9	234.3	225.9	219.6	217.5
132.5°	445.2	395.4	355.4	323.9	297.9	275.5	257.3	242.6	232.6	225.8	223.1
135°	435.7	394.6	360.4	332.5	308.8	287.2	268.4	253.8	243.3	235.7	232.8
137.5°	427.5	393.1	363.8	338.9	316.4	295.6	278.1	263.7	252.5	245.0	242.0
140°	422.5	392.5	366.0	342.3	321.4	301.1	283.7	269.8	258.7	251.6	248.2
142.5°	418.0	391.4	367.7	345.6	325.3	305.6	289.4	275.4	265.4	257.8	254.9
145°	412.1	389.7	368.8	349.3	330.5	312.4	296.3	284.5	274.0	267.7	265.6
147.5°	406.2	387.1	368.8	351.5	334.7	318.1	304.3	292.9	283.9	277.8	276.5
150°	402.3	384.9	368.8	352.0	337.4	321.4	308.8	299.1	290.0	284.5	283.7
152.5°	397.8	382.0	367.1	353.2	339.1	325.3	313.3	304.7	296.7	291.1	291.0
155°	391.1	377.2	365.3	353.5	342.3	330.5	320.7	313.0	306.0	301.8	301.8
157.5°	383.6	372.8	362.9	354.2	344.1	334.7	327.1	320.6	314.4	311.0	310.5
160°	378.5	369.5	361.9	354.2	345.8	337.4	330.5	325.6	320.0	317.2	317.2
162.5°	373.5	366.1	359.6	353.6	346.3	339.1	333.2	329.0	324.5	322.3	322.3
165°	366.7	361.1	356.2	352.0	347.1	341.6	336.7	333.9	330.5	329.0	329.8
167.5°	360.2	356.1	352.9	351.0	347.1	343.0	339.9	338.0	335.4	334.7	335.5
170°	356.2	352.8	350.7	349.3	346.5	343.0	341.6	340.2	338.1	337.4	338.9
172.5°	352.3	350.0	349.0	348.7	346.5	343.6	342.7	341.9	340.4	340.2	341.1
175°	347.9	346.5	346.5	347.1	345.8	344.4	343.7	343.7	342.3	343.0	343.7
177.5°	344.9	344.4	344.9	346.1	344.9	344.4	344.4	344.4	343.8	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	709.3	710.6	715.2	718.5	722.4	724.6	726.7	728.4	730.6	731.1	739.0
5°	712.4	719.3	731.2	740.0	751.0	762.9	771.2	774.9	784.8	793.0	809.4
7.5°	711.5	726.0	744.1	762.9	782.9	801.5	817.6	836.7	850.3	870.8	890.9
10°	710.7	730.1	753.4	777.3	805.3	831.3	854.5	880.5	902.0	930.3	954.6
12.5°	708.3	731.8	764.0	792.3	826.3	862.1	896.5	929.9	949.0	996.1	1018.5
15°	702.1	730.1	770.4	813.5	860.3	902.7	946.4	981.1	1037.5	1078.9	1105.2
17.5°	690.5	729.8	777.6	829.5	886.4	942.2	991.7	1044.6	1104.4	1154.3	1207.6
20°	685.1	728.1	781.4	838.7	897.9	961.0	1017.4	1080.9	1146.1	1195.3	1263.6
22.5°	675.0	723.7	781.1	845.1	908.2	973.6	1039.6	1103.6	1178.9	1246.7	1311.7
25°	658.4	713.1	772.5	843.9	918.0	983.6	1062.5	1147.5	1226.1	1313.1	1378.0
27.5°	641.1	699.5	759.0	825.4	905.1	982.9	1082.2	1178.2	1274.3	1349.5	1397.5
30°	627.7	684.4	745.9	812.8	891.7	984.3	1095.3	1200.1	1293.7	1358.3	1385.2
32.5°	613.2	670.7	725.1	795.3	879.4	983.5	1103.5	1212.9	1294.8	1337.7	1332.5
35°	590.5	638.6	691.6	759.2	858.3	977.4	1108.2	1214.1	1264.3	1255.1	1185.4
37.5°	557.7	598.2	650.3	724.3	833.7	964.8	1098.7	1178.1	1174.8	1099.7	998.8
40°	537.3	571.7	621.9	699.8	814.5	956.6	1083.6	1135.2	1091.5	986.7	865.8
42.5°	510.4	542.2	592.4	672.4	793.5	940.0	1055.0	1069.9	984.4	863.7	753.0
45°	469.0	497.0	548.8	631.5	762.0	903.7	985.0	948.4	833.3	708.6	624.3
47.5°	424.3	453.4	503.4	588.3	716.3	849.1	887.8	810.1	691.9	590.8	513.4
50°	396.2	424.2	473.0	558.7	685.5	804.3	820.4	720.0	611.4	522.5	459.0
52.5°	367.7	394.1	442.1	528.2	649.3	752.3	742.4	640.2	540.3	464.6	414.7
55°	325.5	350.4	396.2	476.8	587.1	668.7	632.8	535.2	452.5	393.8	355.9
57.5°	287.7	311.6	351.0	423.8	519.7	575.8	530.2	447.9	382.2	337.0	308.7
60°	262.0	283.1	320.7	388.3	471.6	514.3	469.2	396.5	341.2	305.0	279.7
62.5°	237.6	256.1	290.9	352.2	424.6	460.5	414.9	353.3	306.2	274.1	252.6
65°	200.8	217.6	248.3	296.1	355.5	379.4	340.2	290.3	253.8	229.9	215.5
67.5°	167.2	181.4	207.9	245.6	289.4	306.7	276.9	238.3	210.7	191.5	180.1
70°	144.8	157.1	177.9	210.4	250.0	263.3	235.3	203.6	183.4	168.0	157.5
72.5°	125.9	135.0	153.9	179.0	212.0	222.6	203.0	175.1	156.3	144.8	136.4
75°	95.9	103.4	115.7	135.9	158.8	165.0	150.3	132.9	120.2	112.0	105.5
77.5°	69.2	74.7	83.6	96.0	111.9	117.4	108.2	96.5	87.3	81.8	78.1
80°	52.3	56.7	64.2	74.5	84.0	87.1	81.6	72.8	66.3	63.2	60.1
82.5°	38.6	41.1	45.7	52.6	59.1	62.8	58.1	52.8	49.3	46.5	45.4
85°	19.4	20.9	22.9	25.6	29.7	31.1	29.3	28.0	25.9	24.3	24.3
87.5°	7.7	7.9	9.2	10.0	11.4	12.6	12.8	12.7	12.8	12.4	12.2
90°	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8	17.4
92.5°	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9	58.7
95°	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4	251.0
97.5°	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5	625.6
100°	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5	822.0
102.5°	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2	887.2
105°	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6	906.3
107.5°	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2	851.4
110°	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3	799.0





TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6	747.1
115°	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4	678.3
117.5°	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7	628.6
120°	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1	602.4
122.5°	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2	581.8
125°	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7	554.2
127.5°	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3	530.3
130°	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5	515.2
132.5°	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2	501.2
135°	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7	482.4
137.5°	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5	465.3
140°	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5	455.2
142.5°	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0	445.8
145°	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1	434.4
147.5°	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2	425.0
150°	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3	418.3
152.5°	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8	412.1
155°	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1	403.0
157.5°	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6	393.2
160°	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5	387.6
162.5°	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5	380.9
165°	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7	372.3
167.5°	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2	364.7
170°	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2	359.7
172.5°	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3	355.3
175°	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9	349.3
177.5°	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	704.9	704.9	704.9	704.9	704.9	704.9	704.9
2.5°	741.8	742.1	745.0	747.3	746.2	747.5	748.1
5°	810.4	822.7	829.2	834.0	834.4	834.6	837.4
7.5°	907.8	921.0	930.6	945.2	949.6	954.6	953.1
10°	978.8	998.3	1015.0	1023.9	1033.4	1047.4	1036.2
12.5°	1045.2	1079.7	1105.2	1118.9	1128.0	1130.8	1125.2
15°	1154.7	1199.8	1224.1	1223.3	1254.1	1267.4	1246.5
17.5°	1255.1	1296.7	1330.0	1347.1	1372.7	1378.4	1375.8
20°	1316.5	1362.0	1387.9	1417.3	1430.7	1442.6	1444.7
22.5°	1369.6	1410.3	1438.2	1462.7	1473.8	1479.4	1482.9
25°	1424.2	1456.3	1473.0	1481.5	1484.6	1483.9	1479.4
27.5°	1420.4	1422.8	1404.4	1386.3	1370.1	1351.8	1345.6
30°	1383.5	1354.8	1303.6	1274.5	1231.9	1198.0	1211.7
32.5°	1286.5	1229.4	1171.9	1108.4	1055.9	1041.0	1025.9
35°	1098.0	997.6	938.9	870.6	843.2	815.9	797.1
37.5°	888.3	810.7	740.9	696.2	668.9	651.7	642.3
40°	768.1	698.0	640.7	604.5	583.6	564.2	561.4
42.5°	672.2	607.1	563.9	535.1	515.1	506.8	500.8
45°	550.5	505.1	476.1	455.6	442.3	437.1	430.3
47.5°	466.0	433.9	412.1	398.1	388.1	384.2	383.7
50°	418.7	392.1	376.0	365.1	357.2	355.9	350.4
52.5°	383.2	360.1	347.6	338.0	332.3	328.5	326.9
55°	332.6	317.3	306.0	300.5	296.1	292.3	292.3
57.5°	291.1	278.2	270.7	266.1	264.7	262.1	260.4
60°	265.4	254.4	248.6	244.5	241.8	242.1	239.1
62.5°	240.2	233.1	227.6	223.5	220.3	220.3	220.5
65°	204.6	199.1	195.0	193.7	191.6	189.2	189.8
67.5°	173.3	168.3	165.1	162.7	162.0	160.7	162.7
70°	151.0	147.2	144.8	142.8	142.0	142.4	144.1
72.5°	130.5	127.8	126.3	125.3	123.8	123.9	125.0
75°	102.5	100.4	99.1	98.0	97.6	97.6	97.6
77.5°	75.3	74.8	74.2	72.7	72.8	73.1	73.2
80°	59.4	58.4	58.1	57.3	56.4	55.6	57.3
82.5°	44.4	43.3	43.1	42.9	41.3	41.2	42.6
85°	23.9	22.9	23.2	22.9	22.9	22.6	22.6
87.5°	12.1	11.9	11.9	12.1	11.9	11.9	12.2
90°	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P331930-940

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)