

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831580

Luminaire Tested: S123DIP-S560D805U940-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831580
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U940-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4774.7 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

Luminous Intensity Polar Plot



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47	42				
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	39	37	35	31				
4	75	65	58	52	69	60	54	49	52	47	43	43	40	37	36	33	31	27				
5	70	58	51	45	64	54	47	42	47	41	37	39	35	32	33	30	27	24				
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22				
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	24	22	20				
8	56	44	36	31	51	41	34	29	35	30	26	30	26	23	25	22	20	18				
9	52	40	33	28	48	38	31	27	33	27	24	28	24	21	24	21	18	16				
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	22	19	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	15493	15493	15493	15493	15493
5°	19594	18493	15632	12597	11575
10°	19783	20382	15527	10041	8775
15°	14900	18923	15422	8504	7421
20°	10381	15313	15224	7436	6740
25°	7917	11776	14890	6842	6322
30°	6848	9355	14353	6421	5986
35°	6355	7899	13736	6117	5749
40°	6015	7086	12867	5828	5668
45°	5815	6558	11764	5602	5632
50°	5715	6141	10458	5397	5603
55°	5502	5834	9175	5202	5628
60°	5307	5507	7907	5018	5535
65°	4984	5196	6821	4824	5428
70°	4604	4803	5800	4497	5108
75°	4167	4304	4974	4180	4666
80°	3434	3769	3936	3645	3936
85°	2717	3051	2890	3088	3137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 13431 cd/sqm



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.1	2.8
10°-20°	338.5	7.1
20°-30°	400.8	8.4
30°-40°	403.0	8.4
40°-50°	369.8	7.7
50°-60°	305.2	6.4
60°-70°	215.9	4.5
70°-80°	115.2	2.4
80°-90°	31.1	0.7
90°-100°	57.1	1.2
100°-110°	172.9	3.6
110°-120°	294.4	6.2
120°-130°	387.3	8.1
130°-140°	435.3	9.1
140°-150°	428.0	9.0
150°-160°	360.3	7.5
160°-170°	239.9	5.0
170°-180°	84.0	1.8
0°-30°	875.4	18.3
0°-40°	1278.4	26.8
0°-60°	1953.4	40.9
0°-90°	2315.6	48.5
90°-120°	524.4	11.0
90°-150°	1774.9	37.2
90°-180°	2459.0	51.5
0°-180°	4774.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1439	1439	1439	1439	1439	
5°	1813	1712	1447	1166	1071	173
15°	1337	1698	1384	763	666	369
25°	667	992	1254	576	532	315
35°	484	601	1045	466	438	304
45°	382	431	773	368	370	296
55°	293	311	489	277	300	262
65°	196	204	268	189	213	194
75°	100	104	120	100	112	105
85°	22	25	23	25	25	25
90°	21	17	1	17	21	11
95°	54	52	41	52	54	55
105°	166	164	157	164	166	176
115°	297	297	296	297	297	294
125°	429	434	434	434	429	383
135°	562	566	563	566	562	432
145°	682	686	682	686	682	426
155°	780	782	782	782	780	359
165°	848	849	851	849	848	239
175°	882	883	885	883	882	84
180°	888	888	888	888	888	



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1622.3	1620.7	1619.0	1610.6	1602.3	1598.3	1594.3	1582.3	1570.2	1556.9	1543.5
5°	1813.4	1818.0	1822.7	1817.4	1812.0	1795.7	1779.3	1757.6	1735.9	1711.5	1687.1
7.5°	1901.5	1904.2	1906.9	1903.5	1900.2	1895.8	1891.5	1872.1	1852.8	1827.7	1802.7
10°	1810.0	1816.0	1822.0	1835.1	1848.1	1862.8	1877.5	1874.8	1872.1	1864.8	1857.4
12.5°	1609.0	1616.3	1623.7	1649.7	1675.8	1709.2	1742.6	1771.3	1800.0	1820.0	1840.1
15°	1337.1	1357.5	1377.9	1401.6	1425.3	1474.4	1523.5	1583.9	1644.4	1698.1	1751.9
17.5°	1101.4	1109.1	1116.7	1142.1	1167.5	1229.3	1291.1	1360.8	1430.6	1519.8	1609.0
20°	906.3	913.4	920.4	953.8	987.2	1035.6	1084.0	1162.5	1241.0	1336.8	1432.6
22.5°	761.4	772.4	783.4	802.1	820.9	867.3	913.7	983.5	1053.3	1159.1	1265.0
25°	666.6	674.6	682.6	693.9	705.3	742.4	779.4	836.9	894.3	991.5	1088.7
27.5°	601.8	605.1	608.5	619.8	631.2	655.2	679.3	728.7	778.1	860.6	943.1
30°	551.0	553.4	555.7	565.7	575.7	592.1	608.5	644.2	679.9	752.7	825.5
32.5°	515.6	517.3	519.0	526.6	534.3	546.0	557.7	583.7	609.8	669.9	730.0
35°	483.6	484.6	485.6	491.2	496.9	505.6	514.3	534.0	553.7	601.1	648.5
37.5°	455.5	456.8	458.2	461.5	464.9	472.5	480.2	495.9	511.6	548.0	584.4
40°	428.1	430.5	432.8	435.1	437.5	443.8	450.2	462.2	474.2	504.3	534.3
42.5°	404.7	407.1	409.4	410.4	411.4	415.1	418.8	429.8	440.8	463.2	485.6
45°	382.0	383.0	384.0	385.0	386.0	389.1	392.1	401.7	411.4	430.8	450.2
47.5°	361.3	361.3	361.3	362.0	362.7	365.3	368.0	375.0	382.0	397.1	412.1
50°	341.3	341.3	341.3	340.3	339.3	341.0	342.6	348.0	353.3	366.7	380.0
52.5°	317.3	317.3	317.3	317.6	317.9	317.9	317.9	322.6	327.3	339.3	351.3
55°	293.2	294.5	295.9	294.9	293.9	294.5	295.2	298.2	301.2	310.9	320.6
57.5°	269.2	269.8	270.5	270.2	269.8	270.2	270.5	273.2	275.8	283.2	290.5
60°	246.5	246.5	246.5	245.8	245.1	245.8	246.5	247.8	249.1	255.8	262.5
62.5°	221.1	221.4	221.7	222.1	222.4	221.7	221.1	222.7	224.4	229.4	234.4
65°	195.7	196.0	196.4	197.4	198.4	197.7	197.0	198.7	200.4	204.0	207.7
67.5°	173.0	172.3	171.7	172.0	172.3	173.3	174.3	174.7	175.0	179.0	183.0
70°	146.3	146.9	147.6	147.3	146.9	147.3	147.6	148.6	149.6	152.6	155.6
72.5°	122.2	122.6	122.9	122.9	122.9	123.6	124.2	125.2	126.2	127.9	129.6
75°	100.2	100.2	100.2	100.9	101.5	101.9	102.2	102.2	102.2	103.5	104.9
77.5°	76.1	77.8	79.5	79.1	78.8	79.5	80.1	81.2	82.2	82.8	83.5
80°	55.4	55.4	55.4	55.8	56.1	57.1	58.1	58.8	59.4	60.8	62.1
82.5°	35.4	35.7	36.1	37.1	38.1	38.7	39.4	40.4	41.4	41.4	41.4
85°	22.0	21.4	20.7	21.4	22.0	22.7	23.4	23.7	24.0	24.7	25.4
87.5°	10.7	10.7	10.7	10.7	10.7	11.0	11.4	11.4	11.4	11.4	11.4
90°	20.9	20.6	20.3	20.0	19.7	19.2	18.6	18.0	17.4	16.7	14.7
92.5°	30.0	30.3	30.6	30.9	31.2	31.1	30.7	30.2	29.7	29.3	28.4
95°	54.4	54.4	54.4	54.4	54.4	54.1	53.5	52.8	52.2	51.6	50.4
97.5°	78.1	78.2	78.4	78.5	78.7	78.4	77.6	76.8	76.1	75.3	74.4
100°	106.0	105.7	105.4	105.0	104.7	104.3	103.9	103.4	102.9	102.5	101.7
102.5°	134.6	134.7	134.9	135.0	135.2	135.0	134.6	134.1	133.6	133.2	132.1
105°	165.9	165.6	165.3	165.0	164.7	164.5	164.5	164.5	164.5	164.5	163.1
107.5°	198.0	198.2	198.3	198.5	198.6	198.5	198.0	197.5	197.1	196.6	196.0
110°	230.8	231.1	231.4	231.7	232.0	231.9	231.2	230.6	230.0	229.4	229.1



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	265.6	265.6	265.6	265.6	265.6	265.2	264.5	263.7	262.9	262.1	262.1
115°	297.0	297.2	297.3	297.5	297.6	297.6	297.5	297.3	297.2	297.0	297.3
117.5°	329.1	329.5	330.0	330.5	330.9	331.2	331.2	331.2	331.2	331.2	331.5
120°	363.2	363.5	363.8	364.2	364.5	364.7	364.9	365.0	365.2	365.3	366.1
122.5°	396.0	396.5	396.9	397.4	397.9	398.3	398.8	399.3	399.7	400.2	400.5
125°	428.8	429.4	430.0	430.6	431.2	431.9	432.5	433.1	433.7	434.3	434.7
127.5°	461.5	462.2	462.8	463.4	464.0	464.8	465.7	466.6	467.6	468.5	468.8
130°	493.6	494.7	495.8	496.9	497.9	498.8	499.4	500.0	500.7	501.3	501.7
132.5°	527.1	527.8	528.6	529.4	530.2	530.9	531.7	532.5	533.3	534.0	534.3
135°	561.9	562.2	562.5	562.9	563.2	563.6	564.2	564.9	565.5	566.1	566.3
137.5°	592.6	593.1	593.5	594.0	594.5	595.1	595.9	596.6	597.4	598.2	597.7
140°	622.6	623.7	624.7	625.8	626.9	627.5	627.7	627.8	628.0	628.2	628.0
142.5°	653.3	654.0	654.8	655.6	656.4	656.8	657.0	657.1	657.3	657.4	657.1
145°	682.5	683.2	683.8	684.4	685.0	685.4	685.6	685.7	685.9	686.0	685.6
147.5°	709.0	710.0	710.9	711.8	712.7	713.2	713.2	713.2	713.2	713.2	712.7
150°	734.1	735.1	736.0	736.9	737.8	738.3	738.3	738.3	738.3	738.3	738.0
152.5°	758.5	759.3	760.1	760.9	761.6	761.9	761.5	761.2	760.9	760.6	760.5
155°	780.1	781.2	782.3	783.4	784.5	784.7	784.1	783.5	782.9	782.2	782.1
157.5°	800.4	801.3	802.2	803.1	804.1	804.2	803.6	803.0	802.4	801.8	801.6
160°	819.9	820.5	821.1	821.7	822.4	822.3	821.5	820.7	820.0	819.2	819.2
162.5°	834.5	835.6	836.7	837.8	838.9	839.0	838.2	837.5	836.7	835.9	835.8
165°	848.5	849.5	850.6	851.7	852.8	852.9	852.0	851.0	850.1	849.2	849.2
167.5°	861.0	861.9	862.9	863.8	864.7	864.7	863.8	862.9	861.9	861.0	860.9
170°	870.1	871.2	872.2	873.3	874.4	874.4	873.3	872.2	871.2	870.1	870.1
172.5°	877.0	878.1	879.2	880.3	881.4	881.5	880.5	879.6	878.7	877.7	877.7
175°	881.9	883.0	884.1	885.2	886.3	886.3	885.4	884.5	883.6	882.6	882.6
177.5°	884.7	885.8	886.9	888.0	889.1	889.1	888.2	887.3	886.3	885.4	885.4
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1539.5	1535.5	1520.8	1506.1	1489.4	1472.7	1460.4	1448.0	1429.6	1411.3	1396.2
5°	1668.4	1649.7	1618.7	1587.6	1545.5	1503.4	1475.1	1446.7	1408.6	1370.5	1340.1
7.5°	1770.6	1738.5	1695.1	1651.7	1596.6	1541.5	1489.4	1437.3	1379.2	1321.1	1273.7
10°	1835.7	1814.0	1763.9	1713.8	1640.0	1566.2	1493.4	1420.6	1345.8	1271.0	1208.2
12.5°	1842.1	1844.1	1798.0	1751.9	1668.4	1584.9	1496.4	1407.9	1313.8	1219.6	1146.5
15°	1786.3	1820.7	1795.3	1769.9	1685.8	1601.6	1492.8	1383.9	1275.4	1166.8	1082.3
17.5°	1682.8	1756.6	1760.3	1763.9	1679.8	1595.6	1475.1	1354.5	1231.6	1108.7	1019.9
20°	1541.5	1650.4	1687.8	1725.2	1656.7	1588.3	1458.7	1329.1	1191.5	1053.9	960.8
22.5°	1397.3	1529.5	1598.0	1666.4	1615.7	1564.9	1427.0	1289.1	1143.8	998.5	904.0
25°	1232.9	1377.2	1482.4	1587.6	1556.5	1525.5	1389.6	1253.7	1099.0	944.4	847.9
27.5°	1089.7	1236.3	1363.2	1490.1	1483.4	1476.7	1341.8	1206.9	1048.6	890.3	797.1
30°	962.1	1098.7	1240.6	1382.6	1398.9	1415.3	1285.0	1154.8	996.2	837.5	747.7
32.5°	849.2	968.5	1120.7	1273.0	1305.1	1337.1	1219.6	1102.0	945.1	788.1	701.6
35°	756.7	864.9	1017.2	1169.5	1209.6	1249.6	1147.5	1045.3	892.3	739.4	656.9
37.5°	674.9	765.4	914.0	1062.6	1111.7	1160.8	1069.3	977.8	834.5	691.3	615.5
40°	607.1	679.9	816.5	953.1	1009.9	1066.6	991.2	915.7	779.8	643.9	574.1
42.5°	550.4	615.1	739.0	862.9	917.4	971.8	908.0	844.2	723.3	602.4	538.7
45°	501.9	553.7	666.2	778.8	830.5	882.3	827.5	772.8	666.2	559.7	500.3
47.5°	456.5	500.9	597.1	693.3	739.4	785.5	742.7	700.0	609.8	519.6	465.9
50°	415.8	451.5	535.7	619.8	659.9	700.0	662.2	624.5	550.4	476.2	429.5
52.5°	380.4	409.4	479.9	550.4	584.7	619.1	586.8	554.4	495.6	436.8	396.1
55°	345.3	370.0	431.1	492.2	515.6	539.0	514.0	488.9	441.5	394.1	359.7
57.5°	312.6	334.6	384.7	434.8	452.8	470.9	448.2	425.5	389.7	354.0	325.3
60°	280.5	298.6	340.3	382.0	393.1	404.1	385.7	367.3	342.3	317.3	291.5
62.5°	250.8	267.2	298.2	329.3	336.6	344.0	329.9	315.9	296.9	277.8	257.8
65°	220.1	232.4	257.8	283.2	287.9	292.5	280.2	267.8	253.5	239.1	224.4
67.5°	191.7	200.4	221.1	241.8	242.1	242.4	232.4	222.4	214.4	206.4	194.7
70°	164.0	172.3	186.0	199.7	200.0	200.4	192.4	184.3	178.3	172.3	163.6
72.5°	135.6	141.6	151.9	162.3	161.6	161.0	156.0	150.9	146.3	141.6	135.3
75°	109.9	114.9	121.9	128.9	126.9	124.9	122.2	119.6	115.5	111.5	107.5
77.5°	86.5	89.5	93.5	97.5	96.2	94.8	92.5	90.2	87.2	84.2	82.5
80°	63.5	64.8	67.5	70.1	69.5	68.8	66.1	63.5	62.8	62.1	59.8
82.5°	43.1	44.7	45.4	46.1	45.8	45.4	43.4	41.4	40.7	40.1	39.7
85°	25.7	26.0	26.4	26.7	25.7	24.7	24.0	23.4	23.4	23.4	23.0
87.5°	11.7	12.0	12.0	12.0	11.7	11.4	10.7	10.0	10.4	10.7	10.7
90°	12.7	10.7	8.7	6.9	5.3	3.8	2.2	0.7	2.2	3.8	5.3
92.5°	27.4	26.5	25.6	24.6	23.7	22.8	21.8	20.9	21.8	22.8	23.7
95°	49.1	47.9	46.6	45.5	44.4	43.3	42.2	41.1	42.2	43.3	44.4
97.5°	73.4	72.5	71.6	70.7	70.0	69.2	68.4	67.6	68.4	69.2	70.0
100°	100.9	100.2	99.4	98.5	97.6	96.7	95.7	94.8	95.7	96.7	97.6
102.5°	131.0	129.9	128.8	128.0	127.6	127.1	126.7	126.2	126.7	127.1	127.6
105°	161.7	160.4	159.0	158.1	157.8	157.5	157.2	156.9	157.2	157.5	157.8
107.5°	195.4	194.7	194.1	193.7	193.6	193.4	193.3	193.1	193.3	193.4	193.6
110°	228.8	228.4	228.1	227.8	227.5	227.2	226.9	226.6	226.9	227.2	227.5



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.1	262.1	262.1	262.1	261.9	261.8	261.6	261.4	261.6	261.8	261.9
115°	297.6	297.9	298.2	298.2	297.7	297.2	296.8	296.3	296.8	297.2	297.7
117.5°	331.8	332.1	332.4	332.5	332.3	332.2	332.0	331.9	332.0	332.2	332.3
120°	366.9	367.6	368.4	368.3	367.4	366.5	365.6	364.6	365.6	366.5	367.4
122.5°	400.8	401.1	401.4	401.3	400.6	400.0	399.4	398.8	399.4	400.0	400.6
125°	435.0	435.3	435.6	435.5	435.0	434.6	434.1	433.6	434.1	434.6	435.0
127.5°	469.1	469.4	469.7	469.4	468.5	467.6	466.6	465.7	466.6	467.6	468.5
130°	502.2	502.7	503.1	502.7	501.5	500.3	499.0	497.8	499.0	500.3	501.5
132.5°	534.7	535.0	535.3	534.8	533.6	532.3	531.1	529.9	531.1	532.3	533.6
135°	566.4	566.6	566.7	566.3	565.4	564.5	563.6	562.6	563.6	564.5	565.4
137.5°	597.2	596.8	596.3	595.7	594.9	594.1	593.4	592.6	593.4	594.1	594.9
140°	627.8	627.7	627.5	627.1	626.3	625.5	624.7	624.0	624.7	625.5	626.3
142.5°	656.8	656.5	656.2	655.7	654.9	654.1	653.3	652.6	653.3	654.1	654.9
145°	685.1	684.6	684.2	683.8	683.5	683.2	682.8	682.5	682.8	683.2	683.5
147.5°	712.3	711.8	711.4	710.8	710.2	709.6	709.0	708.3	709.0	709.6	710.2
150°	737.7	737.4	737.1	736.8	736.5	736.1	735.8	735.5	735.8	736.1	736.5
152.5°	760.3	760.2	760.0	759.7	759.2	758.8	758.3	757.8	758.3	758.8	759.2
155°	781.9	781.8	781.6	781.5	781.5	781.5	781.5	781.5	781.5	781.5	781.5
157.5°	801.4	801.3	801.1	801.1	801.3	801.4	801.6	801.8	801.6	801.4	801.3
160°	819.2	819.2	819.2	819.3	819.6	820.0	820.3	820.6	820.3	820.0	819.6
162.5°	835.6	835.5	835.3	835.5	835.9	836.4	836.8	837.3	836.8	836.4	835.9
165°	849.2	849.2	849.2	849.4	849.9	850.3	850.8	851.3	850.8	850.3	849.9
167.5°	860.7	860.5	860.4	860.6	861.2	861.9	862.5	863.1	862.5	861.9	861.2
170°	870.1	870.1	870.1	870.4	871.0	871.6	872.2	872.9	872.2	871.6	871.0
172.5°	877.7	877.7	877.7	878.1	878.7	879.3	879.9	880.5	879.9	879.3	878.7
175°	882.6	882.6	882.6	882.9	883.6	884.2	884.8	885.4	884.8	884.2	883.6
177.5°	885.4	885.4	885.4	885.7	886.3	887.0	887.6	888.2	887.6	887.0	886.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3	1439.3
2.5°	1381.2	1368.2	1355.2	1345.2	1335.1	1318.1	1301.1	1297.1	1293.1	1287.4	1281.7
5°	1309.8	1277.7	1245.6	1216.9	1188.2	1165.8	1143.4	1128.8	1114.1	1103.4	1092.7
7.5°	1226.3	1178.2	1130.1	1096.0	1062.0	1029.6	997.2	986.8	976.5	962.4	948.4
10°	1145.5	1092.4	1039.3	994.8	950.4	918.7	887.0	874.3	861.6	843.9	826.2
12.5°	1073.3	1015.2	957.1	912.4	867.6	836.9	806.2	787.8	769.4	759.4	749.4
15°	997.8	935.7	873.6	832.2	790.8	763.1	735.4	719.3	703.3	693.6	683.9
17.5°	931.1	869.6	808.2	768.4	728.7	703.3	677.9	663.9	649.9	642.5	635.2
20°	867.6	807.5	747.4	708.6	669.9	649.2	628.5	619.5	610.5	604.5	598.4
22.5°	809.5	750.4	691.3	658.2	625.2	608.5	591.8	585.4	579.1	574.1	569.1
25°	751.4	698.6	645.9	617.8	589.8	576.1	562.4	556.0	549.7	544.7	539.7
27.5°	704.0	653.5	603.1	579.1	555.0	544.3	533.7	528.6	523.6	519.0	514.3
30°	657.9	612.8	567.7	547.0	526.3	516.6	506.9	501.9	496.9	492.6	488.2
32.5°	615.1	576.4	537.7	518.6	499.6	491.6	483.6	477.5	471.5	468.2	464.9
35°	574.4	539.7	504.9	489.2	473.5	465.5	457.5	452.5	447.5	444.8	442.2
37.5°	539.7	508.6	477.5	462.5	447.5	439.8	432.1	427.8	423.4	422.4	421.4
40°	504.3	477.5	450.8	436.1	421.4	414.8	408.1	405.4	402.7	402.1	401.4
42.5°	474.9	448.8	422.8	409.4	396.1	390.4	384.7	383.4	382.0	383.0	384.0
45°	440.8	419.1	397.4	385.0	372.7	368.0	363.3	362.3	361.3	363.3	365.3
47.5°	412.1	392.1	372.0	360.3	348.6	345.3	342.0	341.6	341.3	344.0	346.6
50°	382.7	363.3	344.0	334.6	325.3	322.3	319.3	320.3	321.3	325.6	329.9
52.5°	355.3	337.3	319.3	310.6	301.9	299.9	297.9	300.2	302.6	307.2	311.9
55°	325.3	308.9	292.5	285.9	279.2	277.2	275.2	279.9	284.5	288.9	293.2
57.5°	296.5	282.2	267.8	261.8	255.8	255.5	255.1	259.5	263.8	268.5	273.2
60°	265.8	253.8	241.8	237.1	232.4	233.1	233.8	238.8	243.8	247.5	251.1
62.5°	237.8	227.8	217.7	213.4	209.1	210.7	212.4	217.4	222.4	226.8	231.1
65°	209.7	201.4	193.0	190.0	187.0	189.4	191.7	196.0	200.4	203.4	206.4
67.5°	183.0	176.0	169.0	166.6	164.3	166.6	169.0	173.3	177.7	180.7	183.7
70°	155.0	149.3	143.6	141.9	140.3	142.9	145.6	149.3	152.9	156.0	159.0
72.5°	128.9	124.6	120.2	119.9	119.6	121.9	124.2	127.9	131.6	133.6	135.6
75°	103.5	101.2	98.8	98.5	98.2	100.5	102.9	104.9	106.9	108.5	110.2
77.5°	80.8	78.8	76.8	77.1	77.5	79.1	80.8	82.8	84.8	85.8	86.8
80°	57.4	56.8	56.1	56.8	57.4	58.8	60.1	61.4	62.8	63.5	64.1
82.5°	39.4	38.7	38.1	39.1	40.1	41.1	42.1	43.1	44.1	44.4	44.7
85°	22.7	23.7	24.7	24.7	24.7	25.0	25.4	25.7	26.0	25.7	25.4
87.5°	10.7	11.0	11.4	11.4	11.4	11.7	12.0	12.0	12.0	11.7	11.4
90°	6.9	8.7	10.7	12.7	14.7	16.7	17.4	18.0	18.6	19.2	19.7
92.5°	24.6	25.6	26.5	27.4	28.4	29.3	29.7	30.2	30.7	31.1	31.2
95°	45.5	46.6	47.9	49.1	50.4	51.6	52.2	52.8	53.5	54.1	54.4
97.5°	70.7	71.6	72.5	73.4	74.4	75.3	76.1	76.8	77.6	78.4	78.7
100°	98.5	99.4	100.2	100.9	101.7	102.5	102.9	103.4	103.9	104.3	104.7
102.5°	128.0	128.8	129.9	131.0	132.1	133.2	133.6	134.1	134.6	135.0	135.2
105°	158.1	159.0	160.4	161.7	163.1	164.5	164.5	164.5	164.5	164.5	164.7
107.5°	193.7	194.1	194.7	195.4	196.0	196.6	197.1	197.5	198.0	198.5	198.6
110°	227.8	228.1	228.4	228.8	229.1	229.4	230.0	230.6	231.2	231.9	232.0



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	262.1	262.1	262.1	262.1	262.1	262.1	262.9	263.7	264.5	265.2	265.6
115°	298.2	298.2	297.9	297.6	297.3	297.0	297.2	297.3	297.5	297.6	297.6
117.5°	332.5	332.4	332.1	331.8	331.5	331.2	331.2	331.2	331.2	331.2	330.9
120°	368.3	368.4	367.6	366.9	366.1	365.3	365.2	365.0	364.9	364.7	364.5
122.5°	401.3	401.4	401.1	400.8	400.5	400.2	399.7	399.3	398.8	398.3	397.9
125°	435.5	435.6	435.3	435.0	434.7	434.3	433.7	433.1	432.5	431.9	431.2
127.5°	469.4	469.7	469.4	469.1	468.8	468.5	467.6	466.6	465.7	464.8	464.0
130°	502.7	503.1	502.7	502.2	501.7	501.3	500.7	500.0	499.4	498.8	497.9
132.5°	534.8	535.3	535.0	534.7	534.3	534.0	533.3	532.5	531.7	530.9	530.2
135°	566.3	566.7	566.6	566.4	566.3	566.1	565.5	564.9	564.2	563.6	563.2
137.5°	595.7	596.3	596.8	597.2	597.7	598.2	597.4	596.6	595.9	595.1	594.5
140°	627.1	627.5	627.7	627.8	628.0	628.2	628.0	627.8	627.7	627.5	626.9
142.5°	655.7	656.2	656.5	656.8	657.1	657.4	657.3	657.1	657.0	656.8	656.4
145°	683.8	684.2	684.6	685.1	685.6	686.0	685.9	685.7	685.6	685.4	685.0
147.5°	710.8	711.4	711.8	712.3	712.7	713.2	713.2	713.2	713.2	713.2	712.7
150°	736.8	737.1	737.4	737.7	738.0	738.3	738.3	738.3	738.3	738.3	737.8
152.5°	759.7	760.0	760.2	760.3	760.5	760.6	760.9	761.2	761.5	761.9	761.6
155°	781.5	781.6	781.8	781.9	782.1	782.2	782.9	783.5	784.1	784.7	784.5
157.5°	801.1	801.1	801.3	801.4	801.6	801.8	802.4	803.0	803.6	804.2	804.1
160°	819.3	819.2	819.2	819.2	819.2	819.2	820.0	820.7	821.5	822.3	822.4
162.5°	835.5	835.3	835.5	835.6	835.8	835.9	836.7	837.5	838.2	839.0	838.9
165°	849.4	849.2	849.2	849.2	849.2	849.2	850.1	851.0	852.0	852.9	852.8
167.5°	860.6	860.4	860.5	860.7	860.9	861.0	861.9	862.9	863.8	864.7	864.7
170°	870.4	870.1	870.1	870.1	870.1	870.1	871.2	872.2	873.3	874.4	874.4
172.5°	878.1	877.7	877.7	877.7	877.7	877.7	878.7	879.6	880.5	881.5	881.4
175°	882.9	882.6	882.6	882.6	882.6	882.6	883.6	884.5	885.4	886.3	886.3
177.5°	885.7	885.4	885.4	885.4	885.4	885.4	886.3	887.3	888.2	889.1	889.1
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	1439.3	1439.3	1439.3	1439.3
2.5°	1279.4	1277.0	1267.7	1258.3
5°	1084.7	1076.7	1074.0	1071.3
7.5°	947.8	947.1	933.1	919.0
10°	827.2	828.2	815.5	802.8
12.5°	741.0	732.7	731.7	730.7
15°	676.3	668.6	667.2	665.9
17.5°	630.5	625.8	624.5	623.2
20°	595.8	593.1	590.8	588.4
22.5°	565.7	562.4	560.4	558.4
25°	536.7	533.7	533.0	532.3
27.5°	510.6	506.9	506.9	506.9
30°	485.9	483.6	482.6	481.6
32.5°	462.9	460.9	460.9	460.9
35°	441.1	440.1	438.8	437.5
37.5°	421.4	421.4	420.8	420.1
40°	402.4	403.4	403.4	403.4
42.5°	385.0	386.0	386.0	386.0
45°	367.0	368.7	369.3	370.0
47.5°	349.3	352.0	352.7	353.3
50°	331.9	334.0	334.3	334.6
52.5°	314.2	316.6	318.3	319.9
55°	295.5	297.9	298.9	299.9
57.5°	275.5	277.8	278.2	278.5
60°	253.5	255.8	256.5	257.1
62.5°	232.4	233.8	234.4	235.1
65°	208.4	210.4	211.7	213.1
67.5°	185.3	187.0	187.0	187.0
70°	159.6	160.3	161.3	162.3
72.5°	135.9	136.3	136.3	136.3
75°	110.9	111.5	111.9	112.2
77.5°	87.2	87.5	87.5	87.5
80°	63.8	63.5	63.5	63.5
82.5°	43.7	42.7	42.7	42.7
85°	25.0	24.7	25.0	25.4
87.5°	11.4	11.4	11.4	11.4
90°	20.0	20.3	20.6	20.9
92.5°	30.9	30.6	30.3	30.0
95°	54.4	54.4	54.4	54.4
97.5°	78.5	78.4	78.2	78.1
100°	105.0	105.4	105.7	106.0
102.5°	135.0	134.9	134.7	134.6
105°	165.0	165.3	165.6	165.9
107.5°	198.5	198.3	198.2	198.0
110°	231.7	231.4	231.1	230.8



TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	265.6	265.6	265.6	265.6
115°	297.5	297.3	297.2	297.0
117.5°	330.5	330.0	329.5	329.1
120°	364.2	363.8	363.5	363.2
122.5°	397.4	396.9	396.5	396.0
125°	430.6	430.0	429.4	428.8
127.5°	463.4	462.8	462.2	461.5
130°	496.9	495.8	494.7	493.6
132.5°	529.4	528.6	527.8	527.1
135°	562.9	562.5	562.2	561.9
137.5°	594.0	593.5	593.1	592.6
140°	625.8	624.7	623.7	622.6
142.5°	655.6	654.8	654.0	653.3
145°	684.4	683.8	683.2	682.5
147.5°	711.8	710.9	710.0	709.0
150°	736.9	736.0	735.1	734.1
152.5°	760.9	760.1	759.3	758.5
155°	783.4	782.3	781.2	780.1
157.5°	803.1	802.2	801.3	800.4
160°	821.7	821.1	820.5	819.9
162.5°	837.8	836.7	835.6	834.5
165°	851.7	850.6	849.5	848.5
167.5°	863.8	862.9	861.9	861.0
170°	873.3	872.2	871.2	870.1
172.5°	880.3	879.2	878.1	877.0
175°	885.2	884.1	883.0	881.9
177.5°	888.0	886.9	885.8	884.7
180°	887.5	887.5	887.5	887.5

TEST NUMBER: P831580

CATALOG NUMBER: S123DIP-S560D805U940-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.95	13.76	13.92	14.75	16.04	15.18	16.00	16.16	16.98	18.28
	3H	14.59	15.32	15.58	16.31	17.63	16.60	17.33	17.59	18.33	19.64
	4H	15.17	15.85	16.17	16.85	18.18	17.05	17.74	18.05	18.74	20.06
	6H	15.53	16.17	16.55	17.17	18.51	17.33	17.96	18.34	18.96	20.30
	8H	15.63	16.23	16.65	17.25	18.59	17.39	17.99	18.40	19.01	20.34
	12H	15.67	16.25	16.69	17.26	18.62	17.40	17.98	18.43	18.99	20.35
4H	2H	13.51	14.20	14.52	15.20	16.53	15.34	16.03	16.35	17.03	18.35
	3H	15.34	15.91	16.36	16.94	18.28	16.95	17.53	17.97	18.56	19.89
	4H	16.04	16.56	17.06	17.58	18.94	17.54	18.06	18.56	19.08	20.44
	6H	16.51	16.96	17.54	18.00	19.36	17.94	18.39	18.97	19.43	20.79
	8H	16.65	17.07	17.68	18.10	19.47	18.05	18.47	19.08	19.51	20.88
	12H	16.71	17.09	17.76	18.14	19.52	18.09	18.47	19.15	19.52	20.90
8H	4H	16.30	16.72	17.33	17.76	19.13	17.64	18.06	18.67	19.10	20.47
	6H	16.89	17.23	17.94	18.31	19.68	18.14	18.49	19.20	19.56	20.94
	8H	17.09	17.40	18.16	18.46	19.85	18.32	18.62	19.39	19.69	21.08
	12H	17.22	17.48	18.28	18.54	19.97	18.42	18.69	19.49	19.74	21.18
12H	4H	16.30	16.68	17.35	17.73	19.11	17.61	17.99	18.66	19.04	20.42
	6H	16.94	17.24	18.00	18.30	19.69	18.15	18.46	19.22	19.52	20.91
	8H	17.17	17.44	18.24	18.49	19.93	18.35	18.62	19.42	19.68	21.11