

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331983-940

Luminaire Tested: **S123DIP-S775D1025U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331983-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6051.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	48	47	46	41	41	41	41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26	26	26	26	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	31	31	28	26	22	22	22	22	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16	16	16	16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10371	10371	10371	10371
5°	12369	10416	9231	10416
10°	15481	10364	8337	10364
15°	18988	10280	7762	10280
20°	22620	10149	7391	10149
25°	24018	9991	7308	9991
30°	20586	9875	7346	9875
35°	14318	9711	7423	9711
40°	10784	9517	7399	9517
45°	8954	9232	7305	9232
50°	8020	8646	7239	8646
55°	7499	8015	7148	8015
60°	7035	7356	7076	7356
65°	6612	6706	6849	6706
70°	6200	5964	6521	5964
75°	5552	5224	5976	5224
80°	4866	4283	5151	4283
85°	3816	3112	3458	3112



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.9	1.6
10°-20°	304.3	5.0
20°-30°	510.8	8.4
30°-40°	578.4	9.6
40°-50°	518.7	8.6
50°-60°	418.6	6.9
60°-70°	291.7	4.8
70°-80°	153.3	2.5
80°-90°	40.8	0.7
90°-100°	73.8	1.2
100°-110°	220.9	3.7
110°-120°	375.8	6.2
120°-130°	494.3	8.2
130°-140°	555.6	9.2
140°-150°	546.1	9.0
150°-160°	459.7	7.6
160°-170°	306.0	5.1
170°-180°	107.2	1.8
0°-30°	910.1	15.0
0°-40°	1488.4	24.6
0°-60°	2425.7	40.1
0°-90°	2911.5	48.1
90°-120°	670.6	11.1
90°-150°	2266.5	37.5
90°-180°	3139.0	51.9
0°-180°	6051.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	964	964	964	964	964	
5°	1145	964	854	964	1145	119
15°	1704	922	696	922	1704	492
25°	2022	841	615	841	2022	887
35°	1090	739	565	739	1090	708
45°	588	606	480	606	588	465
55°	400	427	381	427	400	359
65°	260	263	269	263	260	259
75°	134	126	144	126	134	143
85°	31	25	28	25	31	37
90°	27	1	27	1	27	15
95°	70	52	70	52	70	71
105°	212	200	212	200	212	225
115°	379	378	379	378	379	375
125°	547	554	547	554	547	489
135°	718	718	718	718	718	552
145°	871	871	871	871	871	544
155°	996	998	996	998	996	459
165°	1083	1087	1083	1087	1083	306
175°	1126	1130	1126	1130	1126	107
180°	1133	1133	1133	1133	1133	



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1022.5	1021.8	1019.9	1021.5	1018.4	1014.3	1014.0	1010.2	999.3	998.6	995.7
5°	1144.7	1140.9	1140.5	1140.0	1133.5	1124.6	1107.8	1106.3	1084.0	1072.7	1059.3
7.5°	1302.8	1304.8	1298.0	1292.0	1272.0	1258.8	1240.8	1217.7	1190.3	1162.3	1143.7
10°	1416.4	1431.7	1412.6	1399.5	1387.4	1364.5	1337.9	1304.8	1271.7	1232.9	1203.5
12.5°	1538.1	1545.7	1541.9	1529.6	1510.6	1475.9	1428.7	1392.1	1361.6	1297.1	1271.0
15°	1703.9	1732.4	1714.2	1672.1	1673.1	1639.9	1578.3	1510.6	1474.7	1418.2	1341.2
17.5°	1880.5	1884.1	1876.3	1841.4	1818.0	1772.5	1715.6	1650.7	1577.9	1509.5	1427.8
20°	1974.7	1971.8	1955.5	1937.3	1897.2	1861.7	1799.7	1727.2	1633.9	1566.6	1477.5
22.5°	2026.9	2022.3	2014.6	1999.3	1965.9	1927.8	1872.1	1793.0	1704.1	1611.5	1508.5
25°	2022.3	2028.4	2029.3	2025.1	2013.4	1990.6	1946.7	1883.6	1794.9	1675.9	1568.5
27.5°	1839.3	1847.9	1872.9	1895.0	1919.7	1944.9	1941.5	1910.2	1844.6	1741.9	1610.5
30°	1656.3	1637.6	1683.8	1742.2	1781.9	1851.9	1891.1	1893.5	1856.5	1768.4	1640.4
32.5°	1402.3	1422.9	1443.3	1515.1	1601.9	1680.5	1758.5	1821.4	1828.5	1769.9	1658.0
35°	1089.6	1115.3	1152.6	1189.9	1283.4	1363.6	1500.8	1620.3	1715.6	1728.2	1659.6
37.5°	878.0	890.7	914.4	951.7	1012.8	1108.0	1214.2	1365.3	1503.2	1605.9	1610.3
40°	767.5	771.2	797.8	826.3	875.7	954.2	1049.9	1183.4	1348.6	1492.0	1551.8
42.5°	684.6	692.8	704.1	731.4	770.8	829.8	918.8	1029.1	1180.6	1345.6	1462.5
45°	588.2	597.5	604.6	622.8	650.8	690.5	752.5	853.4	968.7	1139.1	1296.4
47.5°	524.5	525.3	530.5	544.2	563.3	593.1	636.9	701.8	807.6	945.7	1107.3
50°	478.9	486.4	488.3	499.0	514.0	535.9	572.3	627.4	714.3	835.6	984.1
52.5°	446.8	449.1	454.3	462.1	475.1	492.2	523.8	566.9	635.1	738.5	875.0
55°	399.6	399.6	404.7	410.8	418.3	433.6	454.7	486.4	538.2	618.6	731.6
57.5°	355.9	358.2	361.9	363.7	370.1	380.3	397.8	422.0	460.6	522.4	612.2
60°	326.8	331.0	330.6	334.2	339.8	347.8	362.7	382.4	416.9	466.4	542.0
62.5°	301.4	301.1	301.0	305.5	311.1	318.7	328.3	345.4	374.7	418.6	483.0
65°	259.6	258.6	261.9	264.7	266.5	272.2	279.6	294.5	314.1	346.9	396.8
67.5°	222.4	219.7	221.5	222.4	225.6	230.0	236.9	246.2	261.8	288.0	325.7
70°	197.0	194.7	194.2	195.1	198.0	201.2	206.3	215.2	229.7	250.7	278.2
72.5°	170.9	169.2	169.2	171.2	172.5	174.7	178.3	186.5	198.0	213.7	239.4
75°	133.5	133.5	133.5	133.9	135.4	137.2	140.1	144.3	153.1	164.3	181.6
77.5°	100.0	100.0	99.4	99.3	101.4	102.3	102.9	106.8	111.7	119.3	131.9
80°	78.5	76.1	77.0	78.5	79.4	79.8	81.2	82.1	86.4	90.6	99.4
82.5°	58.2	56.3	56.4	58.7	58.9	59.3	60.7	62.0	63.6	67.4	72.1
85°	30.9	30.9	31.3	31.3	31.7	31.3	32.6	33.2	33.2	35.5	38.3
87.5°	16.6	15.7	16.1	16.3	15.9	16.1	16.3	16.5	16.8	16.9	16.9
90°	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9	22.1	21.4	18.8
92.5°	35.9	36.2	36.5	36.6	36.9	36.7	36.1	35.5	34.8	34.2	32.7
95°	69.5	69.5	69.5	69.5	69.5	69.0	68.2	67.4	66.7	65.9	64.3
97.5°	106.8	106.9	107.0	107.1	107.1	106.7	105.8	104.9	104.0	103.1	101.9
100°	135.3	134.9	134.5	134.1	133.8	133.2	132.6	132.1	131.4	130.8	129.8
102.5°	164.5	164.6	164.6	164.7	164.8	164.5	164.0	163.4	162.7	162.2	160.9
105°	211.9	211.4	211.1	210.6	210.3	210.1	210.1	210.1	210.1	210.1	208.3
107.5°	261.2	261.4	261.6	261.9	262.1	261.9	261.3	260.6	260.0	259.4	258.7
110°	294.6	295.1	295.4	295.8	296.2	296.0	295.2	294.4	293.6	292.8	292.5



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	330.2	330.3	330.4	330.5	330.6	330.1	329.1	328.2	327.3	326.3	326.3
115°	379.2	379.4	379.6	379.8	380.0	380.0	379.8	379.6	379.4	379.2	379.6
117.5°	428.8	429.4	430.0	430.5	431.1	431.4	431.4	431.4	431.5	431.5	432.0
120°	463.8	464.1	464.6	464.9	465.3	465.7	465.8	466.0	466.2	466.5	467.4
122.5°	497.2	497.8	498.3	498.9	499.4	500.0	500.5	501.0	501.5	502.0	502.6
125°	547.4	548.2	549.0	549.8	550.5	551.3	552.1	552.9	553.8	554.6	554.9
127.5°	597.4	598.3	599.2	600.2	601.1	602.1	603.2	604.3	605.4	606.5	607.0
130°	630.2	631.6	632.9	634.4	635.7	636.9	637.6	638.4	639.2	640.0	640.6
132.5°	664.4	665.5	666.6	667.6	668.7	669.7	670.7	671.5	672.5	673.4	673.9
135°	717.5	717.8	718.2	718.6	719.0	719.6	720.4	721.2	722.0	722.7	723.0
137.5°	764.3	765.0	765.7	766.5	767.2	768.0	768.9	769.7	770.5	771.3	770.9
140°	794.9	796.3	797.6	799.1	800.4	801.2	801.4	801.6	801.8	802.0	801.8
142.5°	826.2	827.2	828.3	829.4	830.5	831.1	831.3	831.5	831.7	831.9	831.5
145°	871.4	872.2	873.0	873.8	874.6	875.0	875.3	875.5	875.7	875.8	875.3
147.5°	911.7	912.8	914.0	915.3	916.4	917.0	917.0	917.0	917.0	917.0	916.4
150°	937.3	938.4	939.7	940.8	942.0	942.6	942.6	942.6	942.6	942.6	942.3
152.5°	962.2	963.2	964.3	965.3	966.3	966.7	966.3	966.1	965.7	965.5	965.2
155°	996.0	997.4	998.8	1000.2	1001.6	1001.8	1001.1	1000.3	999.5	998.7	998.5
157.5°	1026.8	1028.0	1029.0	1030.2	1031.3	1031.4	1030.6	1029.7	1028.9	1028.1	1028.0
160°	1046.8	1047.6	1048.4	1049.2	1049.9	1049.8	1048.8	1047.8	1046.9	1045.9	1045.9
162.5°	1061.8	1063.0	1064.3	1065.5	1066.8	1066.9	1066.0	1065.0	1064.0	1063.0	1062.8
165°	1083.3	1084.7	1086.0	1087.4	1088.8	1088.9	1087.7	1086.5	1085.3	1084.1	1084.1
167.5°	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6	1101.4
170°	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9	1110.9
172.5°	1117.9	1119.4	1120.8	1122.1	1123.6	1123.6	1122.4	1121.1	1119.9	1118.7	1118.7
175°	1126.0	1127.4	1128.7	1130.2	1131.5	1131.7	1130.4	1129.3	1128.1	1126.9	1126.9
177.5°	1130.2	1131.4	1132.5	1133.6	1134.7	1134.8	1133.8	1132.9	1131.9	1131.0	1131.0
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	993.4	990.4	987.4	982.2	977.8	971.3	969.5	967.2	960.6	954.6	950.1
5°	1054.1	1042.9	1026.5	1011.6	999.5	983.1	973.8	964.0	950.0	937.4	927.1
7.5°	1117.6	1095.6	1070.1	1042.7	1017.1	992.5	972.6	954.8	935.2	916.7	902.2
10°	1168.0	1136.2	1100.8	1062.5	1029.8	998.1	971.4	948.2	922.9	901.0	882.8
12.5°	1225.5	1178.5	1129.5	1083.1	1044.4	1000.3	968.1	938.4	909.8	883.4	863.0
15°	1293.6	1233.9	1175.9	1112.0	1053.2	998.1	959.8	922.5	889.3	862.2	836.1
17.5°	1355.6	1287.9	1211.6	1133.8	1062.8	997.6	944.0	901.7	860.2	827.2	801.1
20°	1390.7	1313.7	1227.3	1146.6	1068.1	995.2	936.5	886.0	841.2	806.2	776.8
22.5°	1420.9	1330.8	1241.4	1155.1	1067.7	989.3	922.7	870.8	822.2	787.9	756.6
25°	1452.3	1344.4	1254.8	1153.5	1056.0	974.7	900.0	841.2	792.6	752.5	720.3
27.5°	1479.2	1343.5	1237.2	1128.2	1037.5	956.1	876.3	813.2	761.7	718.1	685.4
30°	1497.1	1345.4	1218.9	1111.1	1019.6	935.5	858.0	794.5	740.4	696.1	665.2
32.5°	1508.3	1344.3	1202.1	1087.2	991.1	916.9	838.2	772.5	716.8	673.2	643.5
35°	1514.8	1336.1	1173.1	1037.8	945.3	873.0	807.2	739.0	680.6	640.0	606.5
37.5°	1501.8	1318.8	1139.5	990.2	888.9	817.7	762.3	704.3	648.5	603.7	574.8
40°	1481.2	1307.6	1113.4	956.5	850.1	781.5	734.3	677.3	622.2	579.8	552.7
42.5°	1442.0	1284.8	1084.6	919.2	809.8	741.1	697.8	650.1	598.0	558.1	531.1
45°	1346.3	1235.2	1041.5	863.2	750.2	679.2	641.0	606.5	559.3	520.5	497.1
47.5°	1213.5	1160.7	979.1	804.1	688.0	619.7	580.0	552.1	517.7	486.4	464.0
50°	1121.3	1099.4	936.9	763.8	646.6	579.8	541.5	516.3	491.6	460.3	439.8
52.5°	1014.9	1028.4	887.6	721.9	604.3	538.7	502.7	482.7	460.2	434.5	416.6
55°	865.0	914.0	802.5	651.7	541.5	478.9	444.9	427.1	414.1	394.9	379.5
57.5°	724.7	787.1	710.4	579.3	479.8	425.9	393.2	373.8	365.4	355.4	343.3
60°	641.4	703.0	644.7	530.7	438.4	387.0	358.0	341.7	333.3	326.3	316.0
62.5°	567.1	629.5	580.4	481.5	397.6	350.0	324.9	308.9	302.3	298.6	289.9
65°	464.9	518.6	486.0	404.7	339.4	297.4	274.5	263.3	257.3	255.8	250.2
67.5°	378.4	419.3	395.5	335.7	284.3	248.0	228.5	219.0	214.4	213.9	209.7
70°	321.6	359.9	341.7	287.6	243.3	214.7	198.0	189.5	186.7	186.3	184.0
72.5°	277.6	304.3	289.8	244.6	210.4	184.5	172.2	163.4	160.2	160.9	159.3
75°	205.4	225.5	217.0	185.8	158.3	141.4	131.2	125.6	122.8	124.2	122.3
77.5°	147.8	160.5	152.9	131.3	114.3	102.1	94.6	91.1	88.6	88.5	87.7
80°	111.6	119.0	114.9	101.7	87.7	77.5	71.4	69.1	67.7	67.2	66.8
82.5°	79.5	85.8	80.9	71.9	62.3	56.2	52.8	49.7	48.7	49.0	48.4
85°	40.1	42.4	40.6	35.0	31.3	28.4	26.6	25.2	24.3	24.7	23.8
87.5°	17.0	16.9	15.2	13.4	12.2	10.7	10.3	9.2	8.8	9.2	9.2
90°	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9	2.9	4.8	6.9
92.5°	31.2	29.8	28.4	26.9	25.6	24.3	22.9	21.6	22.9	24.3	25.6
95°	62.7	61.1	59.6	58.1	56.7	55.3	53.9	52.5	53.9	55.3	56.7
97.5°	100.8	99.6	98.4	97.4	96.4	95.3	94.3	93.3	94.3	95.3	96.4
100°	128.9	127.9	126.9	125.8	124.6	123.4	122.3	121.1	122.3	123.4	124.6
102.5°	159.5	158.3	156.9	156.0	155.2	154.5	153.8	153.1	153.8	154.5	155.2
105°	206.5	204.7	203.0	201.9	201.4	201.1	200.6	200.3	200.6	201.1	201.4
107.5°	258.0	257.3	256.5	256.1	255.8	255.6	255.4	255.1	255.4	255.6	255.8
110°	292.0	291.7	291.2	290.9	290.4	290.1	289.7	289.3	289.7	290.1	290.4



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	326.2	326.1	326.0	325.8	325.6	325.4	325.1	324.9	325.1	325.4	325.6
115°	380.0	380.4	380.8	380.7	380.0	379.5	378.9	378.3	378.9	379.5	380.0
117.5°	432.6	433.1	433.5	433.6	433.3	432.8	432.5	432.0	432.5	432.8	433.3
120°	468.4	469.4	470.4	470.3	469.1	467.9	466.7	465.6	466.7	467.9	469.1
122.5°	503.0	503.5	504.1	503.9	503.0	502.1	501.3	500.4	501.3	502.1	503.0
125°	555.4	555.7	556.2	556.0	555.4	554.8	554.3	553.7	554.3	554.8	555.4
127.5°	607.4	607.8	608.2	607.9	606.5	605.3	604.0	602.8	604.0	605.3	606.5
130°	641.1	641.8	642.4	641.9	640.2	638.7	637.1	635.5	637.1	638.7	640.2
132.5°	674.3	674.8	675.2	674.7	673.1	671.5	669.9	668.3	669.9	671.5	673.1
135°	723.2	723.4	723.5	723.1	721.8	720.7	719.5	718.4	719.5	720.7	721.8
137.5°	770.3	769.8	769.3	768.6	767.6	766.6	765.6	764.6	765.6	766.6	767.6
140°	801.6	801.4	801.2	800.6	799.6	798.6	797.6	796.7	797.6	798.6	799.6
142.5°	831.2	830.8	830.5	829.8	828.8	827.9	826.8	825.8	826.8	827.9	828.8
145°	874.7	874.1	873.5	873.0	872.6	872.2	871.8	871.4	871.8	872.2	872.6
147.5°	915.9	915.3	914.8	914.2	913.5	912.8	912.0	911.3	912.0	912.8	913.5
150°	941.8	941.5	941.0	940.7	940.2	939.9	939.5	939.1	939.5	939.9	940.2
152.5°	964.9	964.7	964.5	964.0	963.5	963.0	962.4	961.9	962.4	963.0	963.5
155°	998.3	998.1	997.9	997.8	997.8	997.8	997.8	997.8	997.8	997.8	997.8
157.5°	1027.8	1027.6	1027.4	1027.5	1027.7	1028.0	1028.2	1028.4	1028.2	1028.0	1027.7
160°	1045.9	1045.9	1045.9	1046.1	1046.5	1046.9	1047.2	1047.7	1047.2	1046.9	1046.5
162.5°	1062.7	1062.5	1062.4	1062.6	1063.1	1063.6	1064.2	1064.8	1064.2	1063.6	1063.1
165°	1084.1	1084.1	1084.1	1084.5	1085.0	1085.7	1086.2	1086.8	1086.2	1085.7	1085.0
167.5°	1101.3	1101.2	1101.0	1101.3	1102.1	1102.9	1103.7	1104.5	1103.7	1102.9	1102.1
170°	1110.9	1110.9	1110.9	1111.3	1112.1	1112.9	1113.7	1114.5	1113.7	1112.9	1112.1
172.5°	1118.7	1118.7	1118.7	1119.1	1119.9	1120.7	1121.5	1122.2	1121.5	1120.7	1119.9
175°	1126.9	1126.9	1126.9	1127.3	1128.1	1128.8	1129.6	1130.4	1129.6	1128.8	1128.1
177.5°	1131.0	1131.0	1131.0	1131.3	1131.9	1132.6	1133.2	1133.8	1133.2	1132.6	1131.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	947.4	944.9	941.1	935.5	931.0	923.9	923.9	925.1	925.1	924.7	923.9
5°	918.7	911.7	903.3	893.5	883.2	873.0	871.1	867.4	864.6	862.7	860.3
7.5°	888.4	875.9	863.7	850.0	837.5	827.2	819.9	814.0	810.1	806.0	803.1
10°	867.8	852.4	837.9	823.5	807.6	795.0	787.1	781.5	777.3	773.6	771.7
12.5°	843.6	825.9	809.9	796.2	778.8	765.9	758.3	755.7	750.7	742.9	738.8
15°	808.1	791.8	772.6	751.6	743.2	727.3	718.5	714.3	711.4	705.3	703.5
17.5°	777.8	756.3	734.9	719.2	703.6	690.7	685.7	680.6	676.8	671.8	670.4
20°	753.5	734.3	714.7	697.9	681.5	667.5	663.3	659.6	655.9	653.5	651.7
22.5°	728.8	709.7	693.4	677.7	660.3	651.1	646.6	642.5	639.8	638.3	636.4
25°	694.2	677.3	659.2	645.2	631.2	625.1	622.2	619.9	618.0	615.7	615.3
27.5°	663.2	644.9	630.1	617.1	607.0	601.9	599.2	598.1	598.5	599.3	599.9
30°	640.0	623.2	611.1	599.9	590.6	585.9	585.4	585.4	587.3	587.7	588.7
32.5°	618.8	604.9	592.8	581.9	574.9	571.7	573.5	573.5	575.0	576.1	577.8
35°	587.7	575.6	566.2	557.0	550.9	552.2	553.2	554.1	556.4	559.3	561.2
37.5°	558.1	547.6	537.9	530.6	527.8	530.3	532.5	534.5	537.3	539.4	541.3
40°	536.8	528.9	519.6	513.0	514.0	515.4	517.3	519.6	521.9	523.3	525.2
42.5°	517.0	508.7	501.7	496.2	497.6	499.4	500.4	501.7	504.4	506.8	508.0
45°	486.9	480.4	473.9	470.6	471.5	472.4	473.3	474.7	477.1	478.9	479.5
47.5°	453.0	448.4	444.1	440.9	442.4	442.0	443.2	446.2	446.9	448.1	450.7
50°	431.3	427.1	422.0	421.1	421.1	421.1	421.5	425.3	425.3	427.1	429.0
52.5°	407.4	404.7	401.4	399.8	399.0	399.0	401.0	402.9	403.6	406.3	408.1
55°	372.0	369.3	366.5	365.1	364.1	365.1	368.8	369.7	372.0	373.4	374.9
57.5°	335.2	333.1	330.8	330.0	329.8	331.1	333.1	335.9	336.5	340.8	343.0
60°	310.9	307.6	305.8	305.8	304.9	309.1	308.1	312.8	313.7	316.5	319.8
62.5°	285.9	281.5	280.7	280.7	282.0	283.3	284.5	286.6	289.1	292.6	295.2
65°	245.6	243.3	246.5	246.0	245.0	247.9	247.9	250.2	253.0	256.3	261.4
67.5°	207.3	206.2	206.4	206.4	207.9	209.5	210.7	212.8	216.2	219.6	222.9
70°	181.6	183.0	180.7	182.5	184.0	184.4	185.3	188.2	191.9	194.2	198.0
72.5°	156.6	156.5	156.8	157.5	158.9	159.7	160.7	163.9	168.0	170.0	172.9
75°	120.5	119.9	121.4	121.4	123.7	124.7	125.6	127.0	130.7	133.5	135.8
77.5°	87.9	88.5	88.2	89.8	89.2	89.3	92.2	93.6	94.0	99.5	100.8
80°	66.3	67.2	67.7	68.1	68.7	67.7	71.0	72.3	72.3	75.6	77.9
82.5°	47.6	48.2	49.4	49.8	49.9	50.9	51.2	52.2	53.3	54.8	57.8
85°	23.8	25.2	25.7	25.2	25.7	24.7	26.1	26.6	27.1	27.1	27.1
87.5°	9.3	10.1	10.2	11.1	11.2	12.1	12.3	11.7	11.9	13.1	11.8
90°	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9	23.7	24.5	25.1
92.5°	26.9	28.4	29.8	31.2	32.7	34.2	34.8	35.5	36.1	36.7	36.9
95°	58.1	59.6	61.1	62.7	64.3	65.9	66.7	67.4	68.2	69.0	69.5
97.5°	97.4	98.4	99.6	100.8	101.9	103.1	104.0	104.9	105.8	106.7	107.1
100°	125.8	126.9	127.9	128.9	129.8	130.8	131.4	132.1	132.6	133.2	133.8
102.5°	156.0	156.9	158.3	159.5	160.9	162.2	162.7	163.4	164.0	164.5	164.8
105°	201.9	203.0	204.7	206.5	208.3	210.1	210.1	210.1	210.1	210.1	210.3
107.5°	256.1	256.5	257.3	258.0	258.7	259.4	260.0	260.6	261.3	261.9	262.1
110°	290.9	291.2	291.7	292.0	292.5	292.8	293.6	294.4	295.2	296.0	296.2



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	325.8	326.0	326.1	326.2	326.3	326.3	327.3	328.2	329.1	330.1	330.6
115°	380.7	380.8	380.4	380.0	379.6	379.2	379.4	379.6	379.8	380.0	380.0
117.5°	433.6	433.5	433.1	432.6	432.0	431.5	431.5	431.4	431.4	431.4	431.1
120°	470.3	470.4	469.4	468.4	467.4	466.5	466.2	466.0	465.8	465.7	465.3
122.5°	503.9	504.1	503.5	503.0	502.6	502.0	501.5	501.0	500.5	500.0	499.4
125°	556.0	556.2	555.7	555.4	554.9	554.6	553.8	552.9	552.1	551.3	550.5
127.5°	607.9	608.2	607.8	607.4	607.0	606.5	605.4	604.3	603.2	602.1	601.1
130°	641.9	642.4	641.8	641.1	640.6	640.0	639.2	638.4	637.6	636.9	635.7
132.5°	674.7	675.2	674.8	674.3	673.9	673.4	672.5	671.5	670.7	669.7	668.7
135°	723.1	723.5	723.4	723.2	723.0	722.7	722.0	721.2	720.4	719.6	719.0
137.5°	768.6	769.3	769.8	770.3	770.9	771.3	770.5	769.7	768.9	768.0	767.2
140°	800.6	801.2	801.4	801.6	801.8	802.0	801.8	801.6	801.4	801.2	800.4
142.5°	829.8	830.5	830.8	831.2	831.5	831.9	831.7	831.5	831.3	831.1	830.5
145°	873.0	873.5	874.1	874.7	875.3	875.8	875.7	875.5	875.3	875.0	874.6
147.5°	914.2	914.8	915.3	915.9	916.4	917.0	917.0	917.0	917.0	917.0	916.4
150°	940.7	941.0	941.5	941.8	942.3	942.6	942.6	942.6	942.6	942.6	942.0
152.5°	964.0	964.5	964.7	964.9	965.2	965.5	965.7	966.1	966.3	966.7	966.3
155°	997.8	997.9	998.1	998.3	998.5	998.7	999.5	1000.3	1001.1	1001.8	1001.6
157.5°	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9	1029.7	1030.6	1031.4	1031.3
160°	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9	1047.8	1048.8	1049.8	1049.9
162.5°	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0	1065.0	1066.0	1066.9	1066.8
165°	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3	1086.5	1087.7	1088.9	1088.8
167.5°	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5
170°	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4
172.5°	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9	1121.1	1122.4	1123.6	1123.6
175°	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1	1129.3	1130.4	1131.7	1131.5
177.5°	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9	1132.9	1133.8	1134.8	1134.7
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	921.3	921.0	923.5	921.7	923.5	921.0	921.3	923.9	924.7	925.1	925.1
5°	857.6	859.0	854.3	854.3	854.3	859.0	857.6	860.3	862.7	864.6	867.4
7.5°	800.8	798.7	798.9	796.4	798.9	798.7	800.8	803.1	806.0	810.1	814.0
10°	766.1	763.3	762.3	762.8	762.3	763.3	766.1	771.7	773.6	777.3	781.5
12.5°	737.3	736.7	730.6	730.7	730.6	736.7	737.3	738.8	742.9	750.7	755.7
15°	703.5	694.6	693.7	696.5	693.7	694.6	703.5	703.5	705.3	711.4	714.3
17.5°	669.6	664.9	665.2	663.8	665.2	664.9	669.6	670.4	671.8	676.8	680.6
20°	651.7	648.9	648.5	645.2	648.5	648.9	651.7	651.7	653.5	655.9	659.6
22.5°	635.3	634.4	634.6	631.0	634.6	634.4	635.3	636.4	638.3	639.8	642.5
25°	614.8	617.2	615.3	615.3	615.3	617.2	614.8	615.3	615.7	618.0	619.9
27.5°	601.0	600.9	599.9	599.9	599.9	600.9	601.0	599.9	599.3	598.5	598.1
30°	590.6	590.0	591.0	591.0	591.0	590.0	590.6	588.7	587.7	587.3	585.4
32.5°	580.1	580.8	580.9	581.3	580.9	580.8	580.1	577.8	576.1	575.0	573.5
35°	563.9	564.4	565.8	564.9	565.8	564.4	563.9	561.2	559.3	556.4	554.1
37.5°	542.1	544.2	543.8	544.5	543.8	544.2	542.1	541.3	539.4	537.3	534.5
40°	525.7	527.1	526.6	526.6	526.6	527.1	525.7	525.2	523.3	521.9	519.6
42.5°	508.8	509.9	508.6	507.9	508.6	509.9	508.8	508.0	506.8	504.4	501.7
45°	481.3	480.4	481.8	479.9	481.8	480.4	481.3	479.5	478.9	477.1	474.7
47.5°	450.5	451.4	451.8	453.2	451.8	451.4	450.5	450.7	448.1	446.9	446.2
50°	430.0	432.7	432.7	432.3	432.7	432.7	430.0	429.0	427.1	425.3	425.3
52.5°	409.7	411.1	413.0	412.9	413.0	411.1	409.7	408.1	406.3	403.6	402.9
55°	378.6	379.5	380.5	380.9	380.5	379.5	378.6	374.9	373.4	372.0	369.7
57.5°	346.3	345.9	348.1	348.8	348.1	345.9	346.3	343.0	340.8	336.5	335.9
60°	323.5	323.5	327.3	328.7	327.3	323.5	323.5	319.8	316.5	313.7	312.8
62.5°	299.3	300.8	304.4	302.5	304.4	300.8	299.3	295.2	292.6	289.1	286.6
65°	263.8	267.5	267.1	268.9	267.1	267.5	263.8	261.4	256.3	253.0	250.2
67.5°	226.7	229.0	232.4	232.6	232.4	229.0	226.7	222.9	219.6	216.2	212.8
70°	201.7	204.0	205.9	207.2	205.9	204.0	201.7	198.0	194.2	191.9	188.2
72.5°	177.4	178.6	183.1	181.1	183.1	178.6	177.4	172.9	170.0	168.0	163.9
75°	139.1	142.4	145.2	143.7	145.2	142.4	139.1	135.8	133.5	130.7	127.0
77.5°	102.9	106.1	107.5	106.3	107.5	106.1	102.9	100.8	99.5	94.0	93.6
80°	81.2	80.8	83.6	83.1	83.6	80.8	81.2	77.9	75.6	72.3	72.3
82.5°	59.6	59.1	60.4	60.7	60.4	59.1	59.6	57.8	54.8	53.3	52.2
85°	29.0	30.3	28.4	28.0	28.4	30.3	29.0	27.1	27.1	27.1	26.6
87.5°	11.9	11.9	11.6	11.3	11.6	11.9	11.9	11.8	13.1	11.9	11.7
90°	25.5	25.9	26.3	26.7	26.3	25.9	25.5	25.1	24.5	23.7	22.9
92.5°	36.6	36.5	36.2	35.9	36.2	36.5	36.6	36.9	36.7	36.1	35.5
95°	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.5	69.0	68.2	67.4
97.5°	107.1	107.0	106.9	106.8	106.9	107.0	107.1	107.1	106.7	105.8	104.9
100°	134.1	134.5	134.9	135.3	134.9	134.5	134.1	133.8	133.2	132.6	132.1
102.5°	164.7	164.6	164.6	164.5	164.6	164.6	164.7	164.8	164.5	164.0	163.4
105°	210.6	211.1	211.4	211.9	211.4	211.1	210.6	210.3	210.1	210.1	210.1
107.5°	261.9	261.6	261.4	261.2	261.4	261.6	261.9	262.1	261.9	261.3	260.6
110°	295.8	295.4	295.1	294.6	295.1	295.4	295.8	296.2	296.0	295.2	294.4



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	330.5	330.4	330.3	330.2	330.3	330.4	330.5	330.6	330.1	329.1	328.2
115°	379.8	379.6	379.4	379.2	379.4	379.6	379.8	380.0	380.0	379.8	379.6
117.5°	430.5	430.0	429.4	428.8	429.4	430.0	430.5	431.1	431.4	431.4	431.4
120°	464.9	464.6	464.1	463.8	464.1	464.6	464.9	465.3	465.7	465.8	466.0
122.5°	498.9	498.3	497.8	497.2	497.8	498.3	498.9	499.4	500.0	500.5	501.0
125°	549.8	549.0	548.2	547.4	548.2	549.0	549.8	550.5	551.3	552.1	552.9
127.5°	600.2	599.2	598.3	597.4	598.3	599.2	600.2	601.1	602.1	603.2	604.3
130°	634.4	632.9	631.6	630.2	631.6	632.9	634.4	635.7	636.9	637.6	638.4
132.5°	667.6	666.6	665.5	664.4	665.5	666.6	667.6	668.7	669.7	670.7	671.5
135°	718.6	718.2	717.8	717.5	717.8	718.2	718.6	719.0	719.6	720.4	721.2
137.5°	766.5	765.7	765.0	764.3	765.0	765.7	766.5	767.2	768.0	768.9	769.7
140°	799.1	797.6	796.3	794.9	796.3	797.6	799.1	800.4	801.2	801.4	801.6
142.5°	829.4	828.3	827.2	826.2	827.2	828.3	829.4	830.5	831.1	831.3	831.5
145°	873.8	873.0	872.2	871.4	872.2	873.0	873.8	874.6	875.0	875.3	875.5
147.5°	915.3	914.0	912.8	911.7	912.8	914.0	915.3	916.4	917.0	917.0	917.0
150°	940.8	939.7	938.4	937.3	938.4	939.7	940.8	942.0	942.6	942.6	942.6
152.5°	965.3	964.3	963.2	962.2	963.2	964.3	965.3	966.3	966.7	966.3	966.1
155°	1000.2	998.8	997.4	996.0	997.4	998.8	1000.2	1001.6	1001.8	1001.1	1000.3
157.5°	1030.2	1029.0	1028.0	1026.8	1028.0	1029.0	1030.2	1031.3	1031.4	1030.6	1029.7
160°	1049.2	1048.4	1047.6	1046.8	1047.6	1048.4	1049.2	1049.9	1049.8	1048.8	1047.8
162.5°	1065.5	1064.3	1063.0	1061.8	1063.0	1064.3	1065.5	1066.8	1066.9	1066.0	1065.0
165°	1087.4	1086.0	1084.7	1083.3	1084.7	1086.0	1087.4	1088.8	1088.9	1087.7	1086.5
167.5°	1105.3	1104.0	1102.9	1101.6	1102.9	1104.0	1105.3	1106.5	1106.5	1105.3	1104.0
170°	1115.0	1113.7	1112.2	1110.9	1112.2	1113.7	1115.0	1116.4	1116.4	1115.0	1113.7
172.5°	1122.1	1120.8	1119.4	1117.9	1119.4	1120.8	1122.1	1123.6	1123.6	1122.4	1121.1
175°	1130.2	1128.7	1127.4	1126.0	1127.4	1128.7	1130.2	1131.5	1131.7	1130.4	1129.3
177.5°	1133.6	1132.5	1131.4	1130.2	1131.4	1132.5	1133.6	1134.7	1134.8	1133.8	1132.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	923.9	923.9	931.0	935.5	941.1	944.9	947.4	950.1	954.6	960.6	967.2
5°	871.1	873.0	883.2	893.5	903.3	911.7	918.7	927.1	937.4	950.0	964.0
7.5°	819.9	827.2	837.5	850.0	863.7	875.9	888.4	902.2	916.7	935.2	954.8
10°	787.1	795.0	807.6	823.5	837.9	852.4	867.8	882.8	901.0	922.9	948.2
12.5°	758.3	765.9	778.8	796.2	809.9	825.9	843.6	863.0	883.4	909.8	938.4
15°	718.5	727.3	743.2	751.6	772.6	791.8	808.1	836.1	862.2	889.3	922.5
17.5°	685.7	690.7	703.6	719.2	734.9	756.3	777.8	801.1	827.2	860.2	901.7
20°	663.3	667.5	681.5	697.9	714.7	734.3	753.5	776.8	806.2	841.2	886.0
22.5°	646.6	651.1	660.3	677.7	693.4	709.7	728.8	756.6	787.9	822.2	870.8
25°	622.2	625.1	631.2	645.2	659.2	677.3	694.2	720.3	752.5	792.6	841.2
27.5°	599.2	601.9	607.0	617.1	630.1	644.9	663.2	685.4	718.1	761.7	813.2
30°	585.4	585.9	590.6	599.9	611.1	623.2	640.0	665.2	696.1	740.4	794.5
32.5°	573.5	571.7	574.9	581.9	592.8	604.9	618.8	643.5	673.2	716.8	772.5
35°	553.2	552.2	550.9	557.0	566.2	575.6	587.7	606.5	640.0	680.6	739.0
37.5°	532.5	530.3	527.8	530.6	537.9	547.6	558.1	574.8	603.7	648.5	704.3
40°	517.3	515.4	514.0	513.0	519.6	528.9	536.8	552.7	579.8	622.2	677.3
42.5°	500.4	499.4	497.6	496.2	501.7	508.7	517.0	531.1	558.1	598.0	650.1
45°	473.3	472.4	471.5	470.6	473.9	480.4	486.9	497.1	520.5	559.3	606.5
47.5°	443.2	442.0	442.4	440.9	444.1	448.4	453.0	464.0	486.4	517.7	552.1
50°	421.5	421.1	421.1	421.1	422.0	427.1	431.3	439.8	460.3	491.6	516.3
52.5°	401.0	399.0	399.0	399.8	401.4	404.7	407.4	416.6	434.5	460.2	482.7
55°	368.8	365.1	364.1	365.1	366.5	369.3	372.0	379.5	394.9	414.1	427.1
57.5°	333.1	331.1	329.8	330.0	330.8	333.1	335.2	343.3	355.4	365.4	373.8
60°	308.1	309.1	304.9	305.8	305.8	307.6	310.9	316.0	326.3	333.3	341.7
62.5°	284.5	283.3	282.0	280.7	280.7	281.5	285.9	289.9	298.6	302.3	308.9
65°	247.9	247.9	245.0	246.0	246.5	243.3	245.6	250.2	255.8	257.3	263.3
67.5°	210.7	209.5	207.9	206.4	206.4	206.2	207.3	209.7	213.9	214.4	219.0
70°	185.3	184.4	184.0	182.5	180.7	183.0	181.6	184.0	186.3	186.7	189.5
72.5°	160.7	159.7	158.9	157.5	156.8	156.5	156.6	159.3	160.9	160.2	163.4
75°	125.6	124.7	123.7	121.4	121.4	119.9	120.5	122.3	124.2	122.8	125.6
77.5°	92.2	89.3	89.2	89.8	88.2	88.5	87.9	87.7	88.5	88.6	91.1
80°	71.0	67.7	68.7	68.1	67.7	67.2	66.3	66.8	67.2	67.7	69.1
82.5°	51.2	50.9	49.9	49.8	49.4	48.2	47.6	48.4	49.0	48.7	49.7
85°	26.1	24.7	25.7	25.2	25.7	25.2	23.8	23.8	24.7	24.3	25.2
87.5°	12.3	12.1	11.2	11.1	10.2	10.1	9.3	9.2	9.2	8.8	9.2
90°	22.1	21.4	18.8	16.2	13.6	11.1	8.8	6.9	4.8	2.9	0.9
92.5°	34.8	34.2	32.7	31.2	29.8	28.4	26.9	25.6	24.3	22.9	21.6
95°	66.7	65.9	64.3	62.7	61.1	59.6	58.1	56.7	55.3	53.9	52.5
97.5°	104.0	103.1	101.9	100.8	99.6	98.4	97.4	96.4	95.3	94.3	93.3
100°	131.4	130.8	129.8	128.9	127.9	126.9	125.8	124.6	123.4	122.3	121.1
102.5°	162.7	162.2	160.9	159.5	158.3	156.9	156.0	155.2	154.5	153.8	153.1
105°	210.1	210.1	208.3	206.5	204.7	203.0	201.9	201.4	201.1	200.6	200.3
107.5°	260.0	259.4	258.7	258.0	257.3	256.5	256.1	255.8	255.6	255.4	255.1
110°	293.6	292.8	292.5	292.0	291.7	291.2	290.9	290.4	290.1	289.7	289.3



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	327.3	326.3	326.3	326.2	326.1	326.0	325.8	325.6	325.4	325.1	324.9
115°	379.4	379.2	379.6	380.0	380.4	380.8	380.7	380.0	379.5	378.9	378.3
117.5°	431.5	431.5	432.0	432.6	433.1	433.5	433.6	433.3	432.8	432.5	432.0
120°	466.2	466.5	467.4	468.4	469.4	470.4	470.3	469.1	467.9	466.7	465.6
122.5°	501.5	502.0	502.6	503.0	503.5	504.1	503.9	503.0	502.1	501.3	500.4
125°	553.8	554.6	554.9	555.4	555.7	556.2	556.0	555.4	554.8	554.3	553.7
127.5°	605.4	606.5	607.0	607.4	607.8	608.2	607.9	606.5	605.3	604.0	602.8
130°	639.2	640.0	640.6	641.1	641.8	642.4	641.9	640.2	638.7	637.1	635.5
132.5°	672.5	673.4	673.9	674.3	674.8	675.2	674.7	673.1	671.5	669.9	668.3
135°	722.0	722.7	723.0	723.2	723.4	723.5	723.1	721.8	720.7	719.5	718.4
137.5°	770.5	771.3	770.9	770.3	769.8	769.3	768.6	767.6	766.6	765.6	764.6
140°	801.8	802.0	801.8	801.6	801.4	801.2	800.6	799.6	798.6	797.6	796.7
142.5°	831.7	831.9	831.5	831.2	830.8	830.5	829.8	828.8	827.9	826.8	825.8
145°	875.7	875.8	875.3	874.7	874.1	873.5	873.0	872.6	872.2	871.8	871.4
147.5°	917.0	917.0	916.4	915.9	915.3	914.8	914.2	913.5	912.8	912.0	911.3
150°	942.6	942.6	942.3	941.8	941.5	941.0	940.7	940.2	939.9	939.5	939.1
152.5°	965.7	965.5	965.2	964.9	964.7	964.5	964.0	963.5	963.0	962.4	961.9
155°	999.5	998.7	998.5	998.3	998.1	997.9	997.8	997.8	997.8	997.8	997.8
157.5°	1028.9	1028.1	1028.0	1027.8	1027.6	1027.4	1027.5	1027.7	1028.0	1028.2	1028.4
160°	1046.9	1045.9	1045.9	1045.9	1045.9	1045.9	1046.1	1046.5	1046.9	1047.2	1047.7
162.5°	1064.0	1063.0	1062.8	1062.7	1062.5	1062.4	1062.6	1063.1	1063.6	1064.2	1064.8
165°	1085.3	1084.1	1084.1	1084.1	1084.1	1084.1	1084.5	1085.0	1085.7	1086.2	1086.8
167.5°	1102.9	1101.6	1101.4	1101.3	1101.2	1101.0	1101.3	1102.1	1102.9	1103.7	1104.5
170°	1112.2	1110.9	1110.9	1110.9	1110.9	1110.9	1111.3	1112.1	1112.9	1113.7	1114.5
172.5°	1119.9	1118.7	1118.7	1118.7	1118.7	1118.7	1119.1	1119.9	1120.7	1121.5	1122.2
175°	1128.1	1126.9	1126.9	1126.9	1126.9	1126.9	1127.3	1128.1	1128.8	1129.6	1130.4
177.5°	1131.9	1131.0	1131.0	1131.0	1131.0	1131.0	1131.3	1131.9	1132.6	1133.2	1133.8
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	969.5	971.3	977.8	982.2	987.4	990.4	993.4	995.7	998.6	999.3	1010.2
5°	973.8	983.1	999.5	1011.6	1026.5	1042.9	1054.1	1059.3	1072.7	1084.0	1106.3
7.5°	972.6	992.5	1017.1	1042.7	1070.1	1095.6	1117.6	1143.7	1162.3	1190.3	1217.7
10°	971.4	998.1	1029.8	1062.5	1100.8	1136.2	1168.0	1203.5	1232.9	1271.7	1304.8
12.5°	968.1	1000.3	1044.4	1083.1	1129.5	1178.5	1225.5	1271.0	1297.1	1361.6	1392.1
15°	959.8	998.1	1053.2	1112.0	1175.9	1233.9	1293.6	1341.2	1418.2	1474.7	1510.6
17.5°	944.0	997.6	1062.8	1133.8	1211.6	1287.9	1355.6	1427.8	1509.5	1577.9	1650.7
20°	936.5	995.2	1068.1	1146.6	1227.3	1313.7	1390.7	1477.5	1566.6	1633.9	1727.2
22.5°	922.7	989.3	1067.7	1155.1	1241.4	1330.8	1420.9	1508.5	1611.5	1704.1	1793.0
25°	900.0	974.7	1056.0	1153.5	1254.8	1344.4	1452.3	1568.5	1675.9	1794.9	1883.6
27.5°	876.3	956.1	1037.5	1128.2	1237.2	1343.5	1479.2	1610.5	1741.9	1844.6	1910.2
30°	858.0	935.5	1019.6	1111.1	1218.9	1345.4	1497.1	1640.4	1768.4	1856.5	1893.5
32.5°	838.2	916.9	991.1	1087.2	1202.1	1344.3	1508.3	1658.0	1769.9	1828.5	1821.4
35°	807.2	873.0	945.3	1037.8	1173.1	1336.1	1514.8	1659.6	1728.2	1715.6	1620.3
37.5°	762.3	817.7	888.9	990.2	1139.5	1318.8	1501.8	1610.3	1605.9	1503.2	1365.3
40°	734.3	781.5	850.1	956.5	1113.4	1307.6	1481.2	1551.8	1492.0	1348.6	1183.4
42.5°	697.8	741.1	809.8	919.2	1084.6	1284.8	1442.0	1462.5	1345.6	1180.6	1029.1
45°	641.0	679.2	750.2	863.2	1041.5	1235.2	1346.3	1296.4	1139.1	968.7	853.4
47.5°	580.0	619.7	688.0	804.1	979.1	1160.7	1213.5	1107.3	945.7	807.6	701.8
50°	541.5	579.8	646.6	763.8	936.9	1099.4	1121.3	984.1	835.6	714.3	627.4
52.5°	502.7	538.7	604.3	721.9	887.6	1028.4	1014.9	875.0	738.5	635.1	566.9
55°	444.9	478.9	541.5	651.7	802.5	914.0	865.0	731.6	618.6	538.2	486.4
57.5°	393.2	425.9	479.8	579.3	710.4	787.1	724.7	612.2	522.4	460.6	422.0
60°	358.0	387.0	438.4	530.7	644.7	703.0	641.4	542.0	466.4	416.9	382.4
62.5°	324.9	350.0	397.6	481.5	580.4	629.5	567.1	483.0	418.6	374.7	345.4
65°	274.5	297.4	339.4	404.7	486.0	518.6	464.9	396.8	346.9	314.1	294.5
67.5°	228.5	248.0	284.3	335.7	395.5	419.3	378.4	325.7	288.0	261.8	246.2
70°	198.0	214.7	243.3	287.6	341.7	359.9	321.6	278.2	250.7	229.7	215.2
72.5°	172.2	184.5	210.4	244.6	289.8	304.3	277.6	239.4	213.7	198.0	186.5
75°	131.2	141.4	158.3	185.8	217.0	225.5	205.4	181.6	164.3	153.1	144.3
77.5°	94.6	102.1	114.3	131.3	152.9	160.5	147.8	131.9	119.3	111.7	106.8
80°	71.4	77.5	87.7	101.7	114.9	119.0	111.6	99.4	90.6	86.4	82.1
82.5°	52.8	56.2	62.3	71.9	80.9	85.8	79.5	72.1	67.4	63.6	62.0
85°	26.6	28.4	31.3	35.0	40.6	42.4	40.1	38.3	35.5	33.2	33.2
87.5°	10.3	10.7	12.2	13.4	15.2	16.9	17.0	16.9	16.9	16.8	16.5
90°	2.9	4.8	6.9	8.8	11.1	13.6	16.2	18.8	21.4	22.1	22.9
92.5°	22.9	24.3	25.6	26.9	28.4	29.8	31.2	32.7	34.2	34.8	35.5
95°	53.9	55.3	56.7	58.1	59.6	61.1	62.7	64.3	65.9	66.7	67.4
97.5°	94.3	95.3	96.4	97.4	98.4	99.6	100.8	101.9	103.1	104.0	104.9
100°	122.3	123.4	124.6	125.8	126.9	127.9	128.9	129.8	130.8	131.4	132.1
102.5°	153.8	154.5	155.2	156.0	156.9	158.3	159.5	160.9	162.2	162.7	163.4
105°	200.6	201.1	201.4	201.9	203.0	204.7	206.5	208.3	210.1	210.1	210.1
107.5°	255.4	255.6	255.8	256.1	256.5	257.3	258.0	258.7	259.4	260.0	260.6
110°	289.7	290.1	290.4	290.9	291.2	291.7	292.0	292.5	292.8	293.6	294.4



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	325.1	325.4	325.6	325.8	326.0	326.1	326.2	326.3	326.3	327.3	328.2
115°	378.9	379.5	380.0	380.7	380.8	380.4	380.0	379.6	379.2	379.4	379.6
117.5°	432.5	432.8	433.3	433.6	433.5	433.1	432.6	432.0	431.5	431.5	431.4
120°	466.7	467.9	469.1	470.3	470.4	469.4	468.4	467.4	466.5	466.2	466.0
122.5°	501.3	502.1	503.0	503.9	504.1	503.5	503.0	502.6	502.0	501.5	501.0
125°	554.3	554.8	555.4	556.0	556.2	555.7	555.4	554.9	554.6	553.8	552.9
127.5°	604.0	605.3	606.5	607.9	608.2	607.8	607.4	607.0	606.5	605.4	604.3
130°	637.1	638.7	640.2	641.9	642.4	641.8	641.1	640.6	640.0	639.2	638.4
132.5°	669.9	671.5	673.1	674.7	675.2	674.8	674.3	673.9	673.4	672.5	671.5
135°	719.5	720.7	721.8	723.1	723.5	723.4	723.2	723.0	722.7	722.0	721.2
137.5°	765.6	766.6	767.6	768.6	769.3	769.8	770.3	770.9	771.3	770.5	769.7
140°	797.6	798.6	799.6	800.6	801.2	801.4	801.6	801.8	802.0	801.8	801.6
142.5°	826.8	827.9	828.8	829.8	830.5	830.8	831.2	831.5	831.9	831.7	831.5
145°	871.8	872.2	872.6	873.0	873.5	874.1	874.7	875.3	875.8	875.7	875.5
147.5°	912.0	912.8	913.5	914.2	914.8	915.3	915.9	916.4	917.0	917.0	917.0
150°	939.5	939.9	940.2	940.7	941.0	941.5	941.8	942.3	942.6	942.6	942.6
152.5°	962.4	963.0	963.5	964.0	964.5	964.7	964.9	965.2	965.5	965.7	966.1
155°	997.8	997.8	997.8	997.8	997.9	998.1	998.3	998.5	998.7	999.5	1000.3
157.5°	1028.2	1028.0	1027.7	1027.5	1027.4	1027.6	1027.8	1028.0	1028.1	1028.9	1029.7
160°	1047.2	1046.9	1046.5	1046.1	1045.9	1045.9	1045.9	1045.9	1045.9	1046.9	1047.8
162.5°	1064.2	1063.6	1063.1	1062.6	1062.4	1062.5	1062.7	1062.8	1063.0	1064.0	1065.0
165°	1086.2	1085.7	1085.0	1084.5	1084.1	1084.1	1084.1	1084.1	1084.1	1085.3	1086.5
167.5°	1103.7	1102.9	1102.1	1101.3	1101.0	1101.2	1101.3	1101.4	1101.6	1102.9	1104.0
170°	1113.7	1112.9	1112.1	1111.3	1110.9	1110.9	1110.9	1110.9	1110.9	1112.2	1113.7
172.5°	1121.5	1120.7	1119.9	1119.1	1118.7	1118.7	1118.7	1118.7	1118.7	1119.9	1121.1
175°	1129.6	1128.8	1128.1	1127.3	1126.9	1126.9	1126.9	1126.9	1126.9	1128.1	1129.3
177.5°	1133.2	1132.6	1131.9	1131.3	1131.0	1131.0	1131.0	1131.0	1131.0	1131.9	1132.9
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	963.5	963.5	963.5	963.5	963.5	963.5	963.5
2.5°	1014.0	1014.3	1018.4	1021.5	1019.9	1021.8	1022.5
5°	1107.8	1124.6	1133.5	1140.0	1140.5	1140.9	1144.7
7.5°	1240.8	1258.8	1272.0	1292.0	1298.0	1304.8	1302.8
10°	1337.9	1364.5	1387.4	1399.5	1412.6	1431.7	1416.4
12.5°	1428.7	1475.9	1510.6	1529.6	1541.9	1545.7	1538.1
15°	1578.3	1639.9	1673.1	1672.1	1714.2	1732.4	1703.9
17.5°	1715.6	1772.5	1818.0	1841.4	1876.3	1884.1	1880.5
20°	1799.7	1861.7	1897.2	1937.3	1955.5	1971.8	1974.7
22.5°	1872.1	1927.8	1965.9	1999.3	2014.6	2022.3	2026.9
25°	1946.7	1990.6	2013.4	2025.1	2029.3	2028.4	2022.3
27.5°	1941.5	1944.9	1919.7	1895.0	1872.9	1847.9	1839.3
30°	1891.1	1851.9	1781.9	1742.2	1683.8	1637.6	1656.3
32.5°	1758.5	1680.5	1601.9	1515.1	1443.3	1422.9	1402.3
35°	1500.8	1363.6	1283.4	1189.9	1152.6	1115.3	1089.6
37.5°	1214.2	1108.0	1012.8	951.7	914.4	890.7	878.0
40°	1049.9	954.2	875.7	826.3	797.8	771.2	767.5
42.5°	918.8	829.8	770.8	731.4	704.1	692.8	684.6
45°	752.5	690.5	650.8	622.8	604.6	597.5	588.2
47.5°	636.9	593.1	563.3	544.2	530.5	525.3	524.5
50°	572.3	535.9	514.0	499.0	488.3	486.4	478.9
52.5°	523.8	492.2	475.1	462.1	454.3	449.1	446.8
55°	454.7	433.6	418.3	410.8	404.7	399.6	399.6
57.5°	397.8	380.3	370.1	363.7	361.9	358.2	355.9
60°	362.7	347.8	339.8	334.2	330.6	331.0	326.8
62.5°	328.3	318.7	311.1	305.5	301.0	301.1	301.4
65°	279.6	272.2	266.5	264.7	261.9	258.6	259.6
67.5°	236.9	230.0	225.6	222.4	221.5	219.7	222.4
70°	206.3	201.2	198.0	195.1	194.2	194.7	197.0
72.5°	178.3	174.7	172.5	171.2	169.2	169.2	170.9
75°	140.1	137.2	135.4	133.9	133.5	133.5	133.5
77.5°	102.9	102.3	101.4	99.3	99.4	100.0	100.0
80°	81.2	79.8	79.4	78.5	77.0	76.1	78.5
82.5°	60.7	59.3	58.9	58.7	56.4	56.3	58.2
85°	32.6	31.3	31.7	31.3	31.3	30.9	30.9
87.5°	16.3	16.1	15.9	16.3	16.1	15.7	16.6
90°	23.7	24.5	25.1	25.5	25.9	26.3	26.7
92.5°	36.1	36.7	36.9	36.6	36.5	36.2	35.9
95°	68.2	69.0	69.5	69.5	69.5	69.5	69.5
97.5°	105.8	106.7	107.1	107.1	107.0	106.9	106.8
100°	132.6	133.2	133.8	134.1	134.5	134.9	135.3
102.5°	164.0	164.5	164.8	164.7	164.6	164.6	164.5
105°	210.1	210.1	210.3	210.6	211.1	211.4	211.9
107.5°	261.3	261.9	262.1	261.9	261.6	261.4	261.2
110°	295.2	296.0	296.2	295.8	295.4	295.1	294.6



TEST NUMBER: P331983-940

CATALOG NUMBER: S123DIP-S775D1025U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	329.1	330.1	330.6	330.5	330.4	330.3	330.2
115°	379.8	380.0	380.0	379.8	379.6	379.4	379.2
117.5°	431.4	431.4	431.1	430.5	430.0	429.4	428.8
120°	465.8	465.7	465.3	464.9	464.6	464.1	463.8
122.5°	500.5	500.0	499.4	498.9	498.3	497.8	497.2
125°	552.1	551.3	550.5	549.8	549.0	548.2	547.4
127.5°	603.2	602.1	601.1	600.2	599.2	598.3	597.4
130°	637.6	636.9	635.7	634.4	632.9	631.6	630.2
132.5°	670.7	669.7	668.7	667.6	666.6	665.5	664.4
135°	720.4	719.6	719.0	718.6	718.2	717.8	717.5
137.5°	768.9	768.0	767.2	766.5	765.7	765.0	764.3
140°	801.4	801.2	800.4	799.1	797.6	796.3	794.9
142.5°	831.3	831.1	830.5	829.4	828.3	827.2	826.2
145°	875.3	875.0	874.6	873.8	873.0	872.2	871.4
147.5°	917.0	917.0	916.4	915.3	914.0	912.8	911.7
150°	942.6	942.6	942.0	940.8	939.7	938.4	937.3
152.5°	966.3	966.7	966.3	965.3	964.3	963.2	962.2
155°	1001.1	1001.8	1001.6	1000.2	998.8	997.4	996.0
157.5°	1030.6	1031.4	1031.3	1030.2	1029.0	1028.0	1026.8
160°	1048.8	1049.8	1049.9	1049.2	1048.4	1047.6	1046.8
162.5°	1066.0	1066.9	1066.8	1065.5	1064.3	1063.0	1061.8
165°	1087.7	1088.9	1088.8	1087.4	1086.0	1084.7	1083.3
167.5°	1105.3	1106.5	1106.5	1105.3	1104.0	1102.9	1101.6
170°	1115.0	1116.4	1116.4	1115.0	1113.7	1112.2	1110.9
172.5°	1122.4	1123.6	1123.6	1122.1	1120.8	1119.4	1117.9
175°	1130.4	1131.7	1131.5	1130.2	1128.7	1127.4	1126.0
177.5°	1133.8	1134.8	1134.7	1133.6	1132.5	1131.4	1130.2
180°	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1	1133.1

(END OF REPORT)