

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332350-935

Luminaire Tested: **S123RDIP-S1000D1025U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332350-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6605.4 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	52	51	50	45
2	90	83	78	73	83	77	72	68	66	62	59	56	53	51	46	45	43	38
3	83	74	67	61	76	69	63	58	59	54	51	50	47	44	42	39	37	33
4	76	66	58	52	70	61	55	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	26
6	65	53	45	39	60	50	43	37	43	37	33	37	33	29	31	28	26	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	26	23	21	18
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	24	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14733	14733	14733	14733
5°	17562	14795	13029	14795
10°	21928	14711	11770	14711
15°	25740	14561	10735	14561
20°	28726	14336	9852	14336
25°	28268	14099	9311	14099
30°	20319	13881	8754	13881
35°	13566	13596	8393	13596
40°	9996	13256	8019	13256
45°	8385	12657	7652	12657
50°	7398	11871	7142	11871
55°	6488	10975	6444	10975
60°	5778	10116	5903	10116
65°	5074	9192	5491	9192
70°	3984	8371	5017	8371
75°	3510	7311	4579	7311
80°	3050	6211	4506	6211
85°	2458	5002	4780	5002



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.6	2.0
10°-20°	420.5	6.4
20°-30°	660.6	10.0
30°-40°	689.3	10.4
40°-50°	589.9	8.9
50°-60°	449.6	6.8
60°-70°	288.2	4.4
70°-80°	138.6	2.1
80°-90°	40.0	0.6
90°-100°	236.3	3.6
100°-110°	669.0	10.1
110°-120°	658.1	10.0
120°-130°	525.0	7.9
130°-140°	413.9	6.3
140°-150°	308.9	4.7
150°-160°	215.3	3.3
160°-170°	126.5	1.9
170°-180°	41.2	0.6
0°-30°	1215.8	18.4
0°-40°	1905.0	28.8
0°-60°	2944.5	44.6
0°-90°	3411.3	51.6
90°-120°	1563.5	23.7
90°-150°	2811.2	42.6
90°-180°	3194.0	48.4
0°-180°	6605.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1625	1369	1206	1369	1625	168
15°	2310	1307	963	1307	2310	655
25°	2380	1187	784	1187	2380	1023
35°	1032	1035	639	1035	1032	677
45°	551	832	503	832	551	433
55°	346	585	343	585	346	313
65°	199	361	216	361	199	196
75°	84	176	110	176	84	90
85°	20	40	39	40	20	23
90°	25	2	25	2	25	14
95°	100	29	100	29	100	180
105°	1093	100	1093	100	1093	1078
115°	1330	176	1330	176	1330	1292
125°	1048	245	1048	245	1048	950
135°	850	287	850	287	850	659
145°	664	327	664	327	664	423
155°	551	372	551	372	551	257
165°	480	406	480	406	480	137
175°	432	424	432	424	432	42
180°	425	425	425	425	425	



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1457.8	1459.7	1453.6	1452.7	1445.6	1443.7	1443.7	1433.9	1427.8	1419.9	1415.1
5°	1625.4	1634.8	1630.0	1619.5	1602.0	1597.8	1586.7	1569.2	1549.2	1524.6	1512.9
7.5°	1834.7	1847.4	1842.5	1826.3	1807.8	1792.9	1761.6	1732.4	1691.5	1655.6	1625.0
10°	2006.2	1992.8	1982.2	1966.4	1949.4	1921.8	1889.0	1843.9	1791.8	1750.8	1705.1
12.5°	2134.7	2132.4	2119.1	2102.8	2078.8	2052.6	2012.3	1957.4	1896.8	1837.5	1785.2
15°	2309.8	2313.2	2304.5	2287.5	2253.5	2207.3	2146.3	2123.5	2036.7	1972.3	1907.8
17.5°	2430.9	2430.3	2429.1	2405.5	2370.8	2337.9	2281.4	2221.3	2142.8	2051.9	1965.1
20°	2507.8	2502.0	2503.1	2476.8	2451.0	2412.9	2357.8	2270.5	2206.1	2101.2	2011.6
22.5°	2505.9	2504.7	2509.2	2500.2	2481.5	2452.3	2408.9	2335.2	2252.9	2147.1	2046.3
25°	2380.1	2375.4	2403.0	2410.5	2440.4	2445.7	2432.8	2392.4	2314.5	2205.5	2080.7
27.5°	1991.9	1989.3	2040.5	2104.5	2185.6	2248.6	2309.5	2339.0	2314.5	2236.4	2111.3
30°	1634.8	1689.9	1715.6	1808.2	1911.3	2034.4	2142.2	2244.7	2269.9	2235.9	2133.4
32.5°	1357.3	1405.3	1426.8	1506.3	1602.4	1746.5	1908.3	2053.5	2156.0	2182.0	2120.3
35°	1032.4	1033.0	1082.2	1117.4	1206.4	1354.7	1511.7	1706.2	1899.6	2046.1	2061.3
37.5°	823.8	826.7	856.5	891.6	958.4	1036.7	1175.0	1336.8	1560.1	1785.0	1916.8
40°	711.4	716.6	738.9	773.4	821.5	880.6	988.5	1140.8	1327.1	1577.4	1781.8
42.5°	639.1	647.7	659.2	685.8	715.6	770.9	858.2	975.9	1145.3	1381.9	1617.8
45°	550.8	555.4	564.3	576.5	603.5	642.2	700.8	779.9	920.5	1110.9	1347.0
47.5°	485.9	483.4	492.7	502.7	520.6	546.9	586.2	650.7	751.1	903.9	1104.1
50°	441.8	441.2	447.6	455.3	472.3	491.6	523.8	572.5	652.1	778.7	962.1
52.5°	400.5	402.8	407.3	416.8	429.1	444.7	473.6	508.7	577.1	686.4	839.3
55°	345.7	347.5	353.9	359.2	368.0	383.7	401.9	431.3	478.1	554.3	680.3
57.5°	299.3	298.5	304.7	306.0	315.9	328.8	342.9	365.7	399.6	456.2	541.1
60°	268.4	266.6	271.9	276.0	281.3	291.8	303.5	325.8	352.8	394.3	467.0
62.5°	240.2	239.4	243.3	247.4	251.8	261.3	271.2	288.3	309.6	344.7	402.3
65°	199.2	201.0	202.8	204.5	206.8	212.7	222.1	233.8	248.4	273.0	314.6
67.5°	156.5	158.3	158.9	162.6	167.6	171.3	176.9	187.4	197.6	218.3	242.0
70°	126.6	126.0	126.6	128.3	134.7	141.2	148.9	156.4	162.9	177.5	197.4
72.5°	108.7	107.7	109.3	109.6	112.7	114.5	119.3	126.5	134.7	144.7	159.0
75°	84.4	84.4	84.4	84.4	86.7	87.9	89.6	91.4	94.4	99.0	109.6
77.5°	62.3	62.4	63.3	63.9	64.3	65.0	66.1	67.8	68.9	71.4	75.9
80°	49.2	49.8	49.2	49.8	49.8	51.0	51.6	53.3	53.9	56.8	58.6
82.5°	37.0	36.7	37.0	37.6	37.6	38.8	38.9	40.2	40.3	41.8	43.6
85°	19.9	18.8	19.9	19.4	20.5	19.4	19.9	21.1	21.1	21.7	24.0
87.5°	9.6	10.8	9.6	10.0	10.2	10.2	10.1	9.9	10.7	10.4	10.3
90°	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5	20.7	21.5	18.9
92.5°	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3	99.7	132.2	145.4
95°	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4	413.4	509.6	453.7
97.5°	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3	845.0	789.8	578.2
100°	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3	983.2	813.9	550.0
102.5°	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7	990.1	769.2	508.8
105°	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2	937.6	691.0	458.1
107.5°	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6	845.8	621.9	425.8
110°	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9	788.1	582.7	413.4



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9	737.9	556.6	406.5
115°	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2	677.3	528.6	403.9
117.5°	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9	640.6	512.0	405.4
120°	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5	621.4	504.5	408.2
122.5°	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1	605.5	499.6	413.0
125°	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3	585.3	493.4	420.3
127.5°	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7	567.4	490.3	428.5
130°	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2	557.8	488.2	434.0
132.5°	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9	548.8	487.5	438.2
135°	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7	537.2	486.5	444.4
137.5°	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6	527.0	484.6	448.4
140°	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2	520.8	483.9	451.2
142.5°	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5	515.3	482.5	453.2
145°	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5	507.9	480.4	454.6
147.5°	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9	500.7	477.2	454.6
150°	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7	495.8	474.4	454.6
152.5°	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1	490.4	471.0	452.5
155°	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7	482.2	464.9	450.3
157.5°	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7	472.9	459.6	447.5
160°	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9	466.7	455.5	446.1
162.5°	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6	460.5	451.3	443.3
165°	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9	452.0	445.2	439.2
167.5°	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6	444.0	439.0	435.1
170°	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5	439.2	434.9	432.3
172.5°	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0	434.4	431.4	430.2
175°	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6	428.9	427.1	427.1
177.5°	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1413.2	1411.9	1405.3	1397.8	1387.9	1381.4	1376.2	1373.5	1365.0	1354.7	1347.6
5°	1500.6	1483.0	1464.3	1441.4	1420.3	1398.6	1385.2	1369.3	1350.0	1328.4	1313.1
7.5°	1594.1	1559.6	1522.5	1484.2	1446.3	1412.4	1382.3	1356.7	1325.9	1294.8	1273.0
10°	1665.9	1615.4	1563.3	1509.9	1461.3	1415.7	1380.4	1345.9	1309.0	1273.2	1246.3
12.5°	1731.0	1664.7	1604.6	1539.0	1476.8	1422.2	1371.6	1330.9	1286.5	1248.4	1217.7
15°	1813.4	1745.5	1672.8	1573.2	1490.6	1421.5	1359.9	1306.7	1252.8	1205.8	1176.0
17.5°	1890.6	1788.3	1690.7	1607.6	1500.2	1413.8	1338.8	1275.0	1215.8	1166.1	1129.4
20°	1922.4	1823.4	1717.4	1611.4	1505.9	1409.2	1321.9	1251.5	1190.1	1133.8	1099.8
22.5°	1941.6	1829.5	1717.9	1603.9	1491.8	1391.4	1305.0	1227.7	1161.0	1107.5	1065.6
25°	1964.0	1830.5	1707.4	1594.9	1480.7	1371.7	1269.1	1187.1	1115.1	1058.2	1013.7
27.5°	1978.8	1821.7	1676.3	1551.2	1435.3	1326.8	1232.8	1145.8	1072.7	1012.6	964.8
30°	1981.7	1814.6	1652.3	1517.0	1399.2	1299.6	1200.0	1116.8	1039.5	975.6	931.1
32.5°	1985.4	1797.3	1620.0	1476.2	1355.6	1257.0	1166.7	1087.3	1008.1	945.1	899.7
35°	1970.0	1787.7	1570.9	1405.7	1285.0	1189.5	1108.0	1034.7	956.8	895.9	849.6
37.5°	1903.3	1749.6	1520.0	1326.2	1200.0	1111.6	1045.2	981.4	909.8	844.1	800.5
40°	1836.3	1712.1	1480.7	1277.9	1146.1	1055.2	995.5	943.4	874.3	812.7	765.9
42.5°	1736.5	1661.0	1443.2	1227.3	1085.1	997.6	947.2	898.4	837.7	775.2	731.2
45°	1553.3	1563.3	1366.4	1146.7	1000.7	912.9	865.4	831.5	777.6	726.0	680.9
47.5°	1323.6	1416.8	1276.3	1060.8	911.8	829.3	787.8	758.2	721.9	671.2	630.1
50°	1173.6	1306.7	1204.1	1003.2	856.1	774.0	733.0	708.9	677.3	637.5	598.2
52.5°	1035.4	1178.2	1116.9	938.9	795.6	720.6	680.5	660.7	635.6	598.1	562.6
55°	844.3	989.0	975.0	842.0	704.9	637.5	607.0	584.8	567.7	539.7	511.5
57.5°	682.9	820.2	827.4	734.2	625.0	558.4	532.2	515.4	504.3	483.0	457.0
60°	581.3	707.2	731.8	661.5	567.7	509.2	483.4	469.9	461.2	444.1	424.2
62.5°	496.9	604.1	632.0	581.3	512.9	458.1	437.9	424.9	419.0	404.3	386.8
65°	380.3	469.3	496.3	468.1	432.4	388.5	372.0	360.9	355.7	347.5	334.6
67.5°	285.9	350.9	380.4	360.6	347.7	319.9	309.5	303.5	298.9	293.2	282.4
70°	229.7	277.8	308.2	302.9	292.4	277.8	270.1	266.0	261.3	256.7	247.3
72.5°	184.7	217.7	246.3	249.0	240.4	237.5	230.7	229.0	226.2	220.6	215.4
75°	122.4	145.3	165.2	172.9	176.3	179.3	176.3	175.8	175.2	170.5	167.6
77.5°	80.2	92.6	105.1	118.1	123.6	127.6	128.5	130.7	129.2	126.7	125.3
80°	61.6	64.5	73.3	84.4	93.2	96.7	99.0	100.2	99.6	99.0	96.7
82.5°	44.7	47.1	51.2	59.1	66.5	72.3	73.7	73.4	74.7	75.1	73.3
85°	24.0	24.6	25.7	26.9	31.1	37.5	39.3	40.5	41.6	41.6	38.1
87.5°	10.8	9.8	10.2	9.9	10.9	10.8	13.3	15.3	16.2	14.6	15.2
90°	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7	3.4	5.2	7.7
92.5°	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7	15.8	23.1	29.7
95°	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2	31.8	41.2	55.9
97.5°	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9	50.7	58.1	70.8
100°	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6	64.5	70.5	82.5
102.5°	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0	79.6	84.9	96.3
105°	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7	102.3	107.5	117.8
107.5°	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7	125.3	130.3	140.4
110°	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2	141.8	146.1	155.6





TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4	157.0	161.3	170.7
115°	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2	179.6	184.8	193.4
117.5°	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0	202.0	206.3	214.1
120°	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1	215.7	220.0	228.6
122.5°	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2	228.8	233.1	242.4
125°	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0	246.7	251.8	261.2
127.5°	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2	261.7	268.1	277.8
130°	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1	270.7	278.4	288.8
132.5°	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0	278.3	286.7	299.1
135°	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1	290.5	300.0	312.8
137.5°	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4	302.0	311.3	325.0
140°	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0	310.2	318.8	332.6
142.5°	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2	317.8	327.1	339.5
145°	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4	330.0	337.8	350.7
147.5°	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9	342.4	350.0	361.1
150°	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8	350.7	357.5	368.7
152.5°	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7	358.9	365.8	375.6
155°	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1	372.1	377.3	385.9
157.5°	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8	383.5	387.6	395.2
160°	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1	391.1	394.5	401.3
162.5°	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3	397.3	400.0	405.4
165°	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5	405.6	407.3	411.6
167.5°	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5	412.5	413.4	416.6
170°	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7	415.9	416.8	419.4
172.5°	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4	419.4	419.6	421.5
175°	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7	422.8	422.0	423.7
177.5°	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2	424.6	423.9	424.6
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1345.3	1339.2	1335.0	1325.6	1319.6	1312.9	1306.4	1310.6	1310.2	1309.7	1309.7
5°	1300.2	1286.7	1274.5	1258.6	1248.6	1236.3	1226.9	1225.8	1228.1	1220.0	1215.2
7.5°	1255.4	1237.0	1219.6	1202.1	1183.6	1168.8	1159.6	1155.2	1149.3	1144.2	1138.9
10°	1224.0	1202.4	1185.3	1163.6	1143.8	1126.2	1115.1	1107.4	1103.3	1099.2	1091.6
12.5°	1191.7	1170.4	1148.8	1124.3	1105.4	1084.9	1076.6	1068.1	1060.2	1055.6	1045.2
15°	1144.4	1116.8	1094.0	1068.2	1047.1	1027.2	1015.5	998.4	996.1	990.2	979.7
17.5°	1096.9	1067.0	1035.4	1016.4	992.6	971.8	954.0	948.3	931.5	925.2	916.0
20°	1059.4	1031.8	1007.8	982.7	948.0	928.7	914.6	907.1	893.5	885.4	879.5
22.5°	1027.0	999.0	971.3	941.8	913.3	891.7	881.4	869.5	862.1	850.7	844.3
25°	980.9	950.4	917.0	885.4	864.9	848.4	832.1	821.5	811.0	805.6	793.9
27.5°	927.2	895.4	864.1	840.1	814.9	798.7	783.9	774.5	761.8	752.9	746.5
30°	897.7	860.1	833.2	811.5	779.3	764.1	752.9	741.2	731.8	722.5	716.0
32.5°	863.4	829.2	803.7	776.9	752.1	735.5	721.1	710.8	702.7	693.9	687.4
35°	809.8	781.1	754.7	727.7	709.6	692.6	675.6	666.8	659.2	651.0	645.1
37.5°	761.2	734.4	709.4	683.8	661.2	647.5	633.8	627.1	616.7	611.2	605.3
40°	731.2	704.9	678.0	653.3	629.9	619.3	607.0	597.1	587.7	583.6	577.1
42.5°	698.4	672.1	649.4	622.8	603.6	589.4	578.0	567.1	560.1	554.1	550.4
45°	649.8	626.4	604.1	577.7	559.6	547.3	534.3	524.4	518.0	513.8	507.4
47.5°	602.6	579.1	556.6	533.6	516.0	501.9	489.0	482.1	473.6	468.6	464.2
50°	568.3	547.3	523.2	502.1	484.6	470.5	459.9	451.2	443.6	437.1	434.2
52.5°	536.9	514.4	493.7	474.1	455.5	439.5	430.0	420.7	415.0	407.6	404.2
55°	485.2	463.5	445.9	426.5	408.4	394.9	383.2	375.0	369.1	360.9	356.3
57.5°	436.5	417.1	396.1	379.4	360.6	349.2	339.5	328.4	321.2	314.8	310.2
60°	403.7	381.4	363.3	347.5	331.1	316.4	307.6	298.9	291.2	284.7	280.7
62.5°	369.5	350.1	332.8	315.6	300.6	287.8	277.6	270.3	263.6	259.4	255.4
65°	317.0	301.8	284.2	270.1	256.1	246.7	238.5	232.0	227.3	224.4	220.9
67.5°	268.7	253.9	238.6	224.8	215.4	208.3	202.9	197.3	195.0	191.2	188.9
70°	237.3	222.1	208.6	198.0	188.6	183.4	179.9	175.8	173.4	168.8	166.4
72.5°	203.1	192.1	182.4	173.7	166.2	161.4	156.9	151.9	148.1	142.9	140.6
75°	160.0	150.0	142.4	136.6	131.8	125.4	118.9	113.7	111.9	110.1	109.6
77.5°	118.5	112.2	106.7	101.7	95.8	91.2	89.8	88.6	88.3	87.3	87.3
80°	93.2	87.3	83.2	77.3	73.8	73.8	73.8	72.7	73.3	73.3	73.3
82.5°	69.2	63.9	61.6	59.5	58.8	59.3	59.3	59.5	59.2	60.1	59.7
85°	35.7	36.3	37.5	36.9	37.5	37.5	38.7	38.1	38.7	37.5	38.7
87.5°	15.0	16.8	17.7	18.8	19.7	19.8	20.1	20.2	20.8	21.0	21.4
90°	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5	22.4	23.2	24.9
92.5°	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3	57.4	50.7	46.2
95°	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4	209.7	164.2	133.2
97.5°	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3	617.8	506.9	404.1
100°	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3	943.7	843.1	721.1
102.5°	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7	1091.5	1032.9	955.5
105°	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2	1203.2	1219.5	1197.2
107.5°	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6	1189.1	1264.4	1295.0
110°	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9	1143.1	1251.3	1311.5



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9	1082.5	1203.9	1281.3
115°	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2	985.8	1112.1	1205.7
117.5°	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9	904.0	1017.4	1112.4
120°	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5	858.6	961.7	1048.5
122.5°	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1	822.2	917.7	998.3
125°	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3	777.0	859.5	928.2
127.5°	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7	737.2	811.7	874.2
130°	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2	712.5	782.0	840.5
132.5°	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9	689.1	753.9	809.6
135°	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7	655.7	711.6	760.6
137.5°	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6	623.6	671.8	714.2
140°	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2	605.0	646.3	683.3
142.5°	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5	587.2	622.9	655.0
145°	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5	563.8	591.2	616.2
147.5°	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9	546.4	568.6	586.3
150°	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7	535.5	553.5	569.8
152.5°	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1	525.1	541.1	554.7
155°	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7	510.5	523.4	533.7
157.5°	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7	496.2	506.2	514.3
160°	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9	487.3	495.8	501.9
162.5°	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6	477.7	485.6	490.9
165°	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9	464.1	470.1	474.4
167.5°	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6	453.6	457.0	460.1
170°	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5	446.1	449.4	451.2
172.5°	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0	439.9	442.6	443.7
175°	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6	431.4	433.2	433.2
177.5°	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9	426.6	427.3	427.3
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1304.1	1303.6	1304.1	1302.2	1304.1	1303.6	1304.1	1309.7	1309.7	1310.2	1310.6
5°	1213.5	1212.9	1211.2	1205.8	1211.2	1212.9	1213.5	1215.2	1220.0	1228.1	1225.8
7.5°	1134.4	1133.6	1128.4	1128.5	1128.4	1133.6	1134.4	1138.9	1144.2	1149.3	1155.2
10°	1087.5	1088.0	1081.1	1076.9	1081.1	1088.0	1087.5	1091.6	1099.2	1103.3	1107.4
12.5°	1042.1	1039.3	1033.7	1029.2	1033.7	1039.3	1042.1	1045.2	1055.6	1060.2	1068.1
15°	982.1	976.2	962.1	963.3	962.1	976.2	982.1	979.7	990.2	996.1	998.4
17.5°	911.4	907.1	906.8	898.6	906.8	907.1	911.4	916.0	925.2	931.5	948.3
20°	870.1	867.2	868.3	860.1	868.3	867.2	870.1	879.5	885.4	893.5	907.1
22.5°	837.8	834.8	829.9	827.3	829.9	834.8	837.8	844.3	850.7	862.1	869.5
25°	790.4	785.7	781.1	784.0	781.1	785.7	790.4	793.9	805.6	811.0	821.5
27.5°	743.1	739.6	734.9	734.3	734.9	739.6	743.1	746.5	752.9	761.8	774.5
30°	713.1	709.6	707.2	704.3	707.2	709.6	713.1	716.0	722.5	731.8	741.2
32.5°	682.6	681.9	677.7	677.1	677.7	681.9	682.6	687.4	693.9	702.7	710.8
35°	642.7	639.3	638.1	638.7	638.1	639.3	642.7	645.1	651.0	659.2	666.8
37.5°	604.9	600.2	598.1	596.0	598.1	600.2	604.9	605.3	611.2	616.7	627.1
40°	577.7	573.1	571.9	570.7	571.9	573.1	577.7	577.1	583.6	587.7	597.1
42.5°	547.3	545.4	544.7	542.6	544.7	545.4	547.3	550.4	554.1	560.1	567.1
45°	505.7	505.1	501.5	502.7	501.5	505.1	505.7	507.4	513.8	518.0	524.4
47.5°	461.8	459.3	456.8	458.4	456.8	459.3	461.8	464.2	468.6	473.6	482.1
50°	431.9	430.7	425.4	426.5	425.4	430.7	431.9	434.2	437.1	443.6	451.2
52.5°	401.8	397.4	395.4	394.7	395.4	397.4	401.8	404.2	407.6	415.0	420.7
55°	352.1	346.9	344.6	343.4	344.6	346.9	352.1	356.3	360.9	369.1	375.0
57.5°	303.4	302.0	300.1	301.4	300.1	302.0	303.4	310.2	314.8	321.2	328.4
60°	274.8	274.8	274.8	274.2	274.8	274.8	274.8	280.7	284.7	291.2	298.9
62.5°	252.8	251.3	250.9	251.8	250.9	251.3	252.8	255.4	259.4	263.6	270.3
65°	219.1	218.5	216.2	215.6	216.2	218.5	219.1	220.9	224.4	227.3	232.0
67.5°	187.4	185.3	184.6	183.7	184.6	185.3	187.4	188.9	191.2	195.0	197.3
70°	163.5	162.3	158.8	159.4	158.8	162.3	163.5	166.4	168.8	173.4	175.8
72.5°	137.7	136.6	135.8	135.0	135.8	136.6	137.7	140.6	142.9	148.1	151.9
75°	109.0	108.4	107.8	110.1	107.8	108.4	109.0	109.6	110.1	111.9	113.7
77.5°	87.3	87.3	87.6	86.7	87.6	87.3	87.3	87.3	87.3	88.3	88.6
80°	73.3	73.3	72.7	72.7	72.7	73.3	73.3	73.3	73.3	73.3	72.7
82.5°	58.7	59.2	59.5	58.6	59.5	59.2	58.7	59.7	60.1	59.2	59.5
85°	38.7	38.1	39.3	38.7	39.3	38.1	38.7	38.7	37.5	38.7	38.1
87.5°	22.1	21.4	21.5	21.9	21.5	21.4	22.1	21.4	21.0	20.8	20.2
90°	24.0	24.9	25.7	24.9	25.7	24.9	24.0	24.9	23.2	22.4	21.5
92.5°	44.7	42.1	43.0	41.4	43.0	42.1	44.7	46.2	50.7	57.4	72.3
95°	116.9	109.2	103.1	99.7	103.1	109.2	116.9	133.2	164.2	209.7	309.4
97.5°	340.7	302.0	278.8	271.4	278.8	302.0	340.7	404.1	506.9	617.8	771.3
100°	634.3	571.5	538.0	538.9	538.0	571.5	634.3	721.1	843.1	943.7	1013.3
102.5°	887.9	838.3	810.3	790.5	810.3	838.3	887.9	955.5	1032.9	1091.5	1093.7
105°	1157.6	1125.0	1097.5	1093.2	1097.5	1125.0	1157.6	1197.2	1219.5	1203.2	1117.2
107.5°	1295.7	1284.7	1275.4	1267.5	1275.4	1284.7	1295.7	1295.0	1264.4	1189.1	1049.6
110°	1335.6	1342.5	1340.7	1339.0	1340.7	1342.5	1335.6	1311.5	1251.3	1143.1	984.9



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1325.3	1346.5	1353.1	1353.4	1353.1	1346.5	1325.3	1281.3	1203.9	1082.5	920.9
115°	1270.2	1308.0	1325.3	1329.6	1325.3	1308.0	1270.2	1205.7	1112.1	985.8	836.2
117.5°	1179.7	1223.0	1247.8	1253.5	1247.8	1223.0	1179.7	1112.4	1017.4	904.0	774.9
120°	1116.4	1164.5	1185.2	1190.3	1185.2	1164.5	1116.4	1048.5	961.7	858.6	742.5
122.5°	1058.7	1102.0	1124.6	1131.2	1124.6	1102.0	1058.7	998.3	917.7	822.2	717.1
125°	983.2	1021.0	1042.5	1048.5	1042.5	1021.0	983.2	928.2	859.5	777.0	683.3
127.5°	923.2	955.5	974.9	980.4	974.9	955.5	923.2	874.2	811.7	737.2	653.7
130°	886.1	917.1	935.0	941.9	935.0	917.1	886.1	840.5	782.0	712.5	635.2
132.5°	852.4	883.3	899.3	904.1	899.3	883.3	852.4	809.6	753.9	689.1	617.9
135°	802.7	828.5	844.0	850.0	844.0	828.5	802.7	760.6	711.6	655.7	594.7
137.5°	749.6	775.8	788.8	792.7	788.8	775.8	749.6	714.2	671.8	623.6	573.6
140°	715.9	739.9	753.7	752.9	753.7	739.9	715.9	683.3	646.3	605.0	561.2
142.5°	682.9	704.2	716.6	715.7	716.6	704.2	682.9	655.0	622.9	587.2	549.5
145°	637.7	655.7	662.6	664.3	662.6	655.7	637.7	616.2	591.2	563.8	535.5
147.5°	602.6	614.8	621.4	622.1	621.4	614.8	602.6	586.3	568.6	546.4	523.9
150°	582.7	592.1	597.3	597.3	597.3	592.1	582.7	569.8	553.5	535.5	515.7
152.5°	564.8	573.6	576.7	576.7	576.7	573.6	564.8	554.7	541.1	525.1	508.1
155°	541.5	548.3	550.0	550.9	550.0	548.3	541.5	533.7	523.4	510.5	496.7
157.5°	521.0	526.2	527.5	527.4	527.5	526.2	521.0	514.3	506.2	496.2	484.7
160°	507.9	513.1	513.1	512.2	513.1	513.1	507.9	501.9	495.8	487.3	477.9
162.5°	494.9	499.3	499.3	498.4	499.3	499.3	494.9	490.9	485.6	477.7	469.6
165°	477.9	481.3	480.4	480.4	480.4	481.3	477.9	474.4	470.1	464.1	458.9
167.5°	461.7	464.1	463.2	463.2	463.2	464.1	461.7	460.1	457.0	453.6	449.6
170°	452.0	453.7	452.9	452.9	452.9	453.7	452.0	451.2	449.4	446.1	443.5
172.5°	443.8	445.6	444.0	443.3	444.0	445.6	443.8	443.7	442.6	439.9	438.0
175°	433.2	434.0	433.2	432.3	433.2	434.0	433.2	433.2	433.2	431.4	430.6
177.5°	426.6	427.3	425.9	425.9	425.9	427.3	426.6	427.3	427.3	426.6	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1306.4	1312.9	1319.6	1325.6	1335.0	1339.2	1345.3	1347.6	1354.7	1365.0	1373.5
5°	1226.9	1236.3	1248.6	1258.6	1274.5	1286.7	1300.2	1313.1	1328.4	1350.0	1369.3
7.5°	1159.6	1168.8	1183.6	1202.1	1219.6	1237.0	1255.4	1273.0	1294.8	1325.9	1356.7
10°	1115.1	1126.2	1143.8	1163.6	1185.3	1202.4	1224.0	1246.3	1273.2	1309.0	1345.9
12.5°	1076.6	1084.9	1105.4	1124.3	1148.8	1170.4	1191.7	1217.7	1248.4	1286.5	1330.9
15°	1015.5	1027.2	1047.1	1068.2	1094.0	1116.8	1144.4	1176.0	1205.8	1252.8	1306.7
17.5°	954.0	971.8	992.6	1016.4	1035.4	1067.0	1096.9	1129.4	1166.1	1215.8	1275.0
20°	914.6	928.7	948.0	982.7	1007.8	1031.8	1059.4	1099.8	1133.8	1190.1	1251.5
22.5°	881.4	891.7	913.3	941.8	971.3	999.0	1027.0	1065.6	1107.5	1161.0	1227.7
25°	832.1	848.4	864.9	885.4	917.0	950.4	980.9	1013.7	1058.2	1115.1	1187.1
27.5°	783.9	798.7	814.9	840.1	864.1	895.4	927.2	964.8	1012.6	1072.7	1145.8
30°	752.9	764.1	779.3	811.5	833.2	860.1	897.7	931.1	975.6	1039.5	1116.8
32.5°	721.1	735.5	752.1	776.9	803.7	829.2	863.4	899.7	945.1	1008.1	1087.3
35°	675.6	692.6	709.6	727.7	754.7	781.1	809.8	849.6	895.9	956.8	1034.7
37.5°	633.8	647.5	661.2	683.8	709.4	734.4	761.2	800.5	844.1	909.8	981.4
40°	607.0	619.3	629.9	653.3	678.0	704.9	731.2	765.9	812.7	874.3	943.4
42.5°	578.0	589.4	603.6	622.8	649.4	672.1	698.4	731.2	775.2	837.7	898.4
45°	534.3	547.3	559.6	577.7	604.1	626.4	649.8	680.9	726.0	777.6	831.5
47.5°	489.0	501.9	516.0	533.6	556.6	579.1	602.6	630.1	671.2	721.9	758.2
50°	459.9	470.5	484.6	502.1	523.2	547.3	568.3	598.2	637.5	677.3	708.9
52.5°	430.0	439.5	455.5	474.1	493.7	514.4	536.9	562.6	598.1	635.6	660.7
55°	383.2	394.9	408.4	426.5	445.9	463.5	485.2	511.5	539.7	567.7	584.8
57.5°	339.5	349.2	360.6	379.4	396.1	417.1	436.5	457.0	483.0	504.3	515.4
60°	307.6	316.4	331.1	347.5	363.3	381.4	403.7	424.2	444.1	461.2	469.9
62.5°	277.6	287.8	300.6	315.6	332.8	350.1	369.5	386.8	404.3	419.0	424.9
65°	238.5	246.7	256.1	270.1	284.2	301.8	317.0	334.6	347.5	355.7	360.9
67.5°	202.9	208.3	215.4	224.8	238.6	253.9	268.7	282.4	293.2	298.9	303.5
70°	179.9	183.4	188.6	198.0	208.6	222.1	237.3	247.3	256.7	261.3	266.0
72.5°	156.9	161.4	166.2	173.7	182.4	192.1	203.1	215.4	220.6	226.2	229.0
75°	118.9	125.4	131.8	136.6	142.4	150.0	160.0	167.6	170.5	175.2	175.8
77.5°	89.8	91.2	95.8	101.7	106.7	112.2	118.5	125.3	126.7	129.2	130.7
80°	73.8	73.8	73.8	77.3	83.2	87.3	93.2	96.7	99.0	99.6	100.2
82.5°	59.3	59.3	58.8	59.5	61.6	63.9	69.2	73.3	75.1	74.7	73.4
85°	38.7	37.5	37.5	36.9	37.5	36.3	35.7	38.1	41.6	41.6	40.5
87.5°	20.1	19.8	19.7	18.8	17.7	16.8	15.0	15.2	14.6	16.2	15.3
90°	20.7	21.5	18.9	16.4	13.8	11.2	9.5	7.7	5.2	3.4	1.7
92.5°	99.7	132.2	145.4	109.2	72.2	49.7	36.9	29.7	23.1	15.8	10.7
95°	413.4	509.6	453.7	312.8	184.8	111.8	78.2	55.9	41.2	31.8	29.2
97.5°	845.0	789.8	578.2	343.3	198.9	129.1	92.8	70.8	58.1	50.7	49.9
100°	983.2	813.9	550.0	324.0	196.8	136.6	103.1	82.5	70.5	64.5	63.6
102.5°	990.1	769.2	508.8	307.5	199.6	145.6	114.9	96.3	84.9	79.6	78.0
105°	937.6	691.0	458.1	295.7	207.2	160.7	134.1	117.8	107.5	102.3	99.7
107.5°	845.8	621.9	425.8	294.8	221.2	180.5	155.8	140.4	130.3	125.3	122.7
110°	788.1	582.7	413.4	298.3	232.9	194.2	170.1	155.6	146.1	141.8	139.2



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	737.9	556.6	406.5	305.1	244.6	208.7	185.3	170.7	161.3	157.0	154.4
115°	677.3	528.6	403.9	316.2	263.8	231.2	208.0	193.4	184.8	179.6	176.2
117.5°	640.6	512.0	405.4	331.1	284.3	252.0	230.5	214.1	206.3	202.0	198.0
120°	621.4	504.5	408.2	342.1	297.4	266.4	245.0	228.6	220.0	215.7	213.1
122.5°	605.5	499.6	413.0	352.4	311.1	280.9	258.0	242.4	233.1	228.8	226.2
125°	585.3	493.4	420.3	368.7	330.9	300.8	277.6	261.2	251.8	246.7	245.0
127.5°	567.4	490.3	428.5	382.1	348.1	319.0	295.8	277.8	268.1	261.7	259.2
130°	557.8	488.2	434.0	391.1	358.3	330.0	306.8	288.8	278.4	270.7	268.1
132.5°	548.8	487.5	438.2	399.3	367.3	339.7	317.1	299.1	286.7	278.3	275.0
135°	537.2	486.5	444.4	409.9	380.7	354.0	330.9	312.8	300.0	290.5	287.1
137.5°	527.0	484.6	448.4	417.8	390.0	364.4	342.9	325.0	311.3	302.0	298.4
140°	520.8	483.9	451.2	422.0	396.2	371.3	349.8	332.6	318.8	310.2	306.0
142.5°	515.3	482.5	453.2	426.1	401.1	376.8	356.6	339.5	327.1	317.8	314.2
145°	507.9	480.4	454.6	430.6	407.3	385.0	365.2	350.7	337.8	330.0	327.4
147.5°	500.7	477.2	454.6	433.3	412.5	392.1	375.2	361.1	350.0	342.4	340.9
150°	495.8	474.4	454.6	434.0	415.9	396.2	380.7	368.7	357.5	350.7	349.8
152.5°	490.4	471.0	452.5	435.4	418.0	401.1	386.2	375.6	365.8	358.9	358.7
155°	482.2	464.9	450.3	435.8	422.0	407.3	395.4	385.9	377.3	372.1	372.1
157.5°	472.9	459.6	447.5	436.6	424.2	412.5	403.2	395.2	387.6	383.5	382.8
160°	466.7	455.5	446.1	436.6	426.3	415.9	407.3	401.3	394.5	391.1	391.1
162.5°	460.5	451.3	443.3	435.9	427.0	418.0	410.8	405.4	400.0	397.3	397.3
165°	452.0	445.2	439.2	434.0	428.0	421.1	415.1	411.6	407.3	405.6	406.5
167.5°	444.0	439.0	435.1	432.7	427.8	422.8	419.0	416.6	413.4	412.5	413.5
170°	439.2	434.9	432.3	430.6	427.1	422.8	421.1	419.4	416.8	415.9	417.7
172.5°	434.4	431.4	430.2	429.9	427.1	423.5	422.5	421.5	419.6	419.4	420.4
175°	428.9	427.1	427.1	428.0	426.3	424.6	423.7	423.7	422.0	422.8	423.7
177.5°	425.2	424.6	425.2	426.6	425.2	424.6	424.6	424.6	423.9	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1376.2	1381.4	1387.9	1397.8	1405.3	1411.9	1413.2	1415.1	1419.9	1427.8	1433.9
5°	1385.2	1398.6	1420.3	1441.4	1464.3	1483.0	1500.6	1512.9	1524.6	1549.2	1569.2
7.5°	1382.3	1412.4	1446.3	1484.2	1522.5	1559.6	1594.1	1625.0	1655.6	1691.5	1732.4
10°	1380.4	1415.7	1461.3	1509.9	1563.3	1615.4	1665.9	1705.1	1750.8	1791.8	1843.9
12.5°	1371.6	1422.2	1476.8	1539.0	1604.6	1664.7	1731.0	1785.2	1837.5	1896.8	1957.4
15°	1359.9	1421.5	1490.6	1573.2	1672.8	1745.5	1813.4	1907.8	1972.3	2036.7	2123.5
17.5°	1338.8	1413.8	1500.2	1607.6	1690.7	1788.3	1890.6	1965.1	2051.9	2142.8	2221.3
20°	1321.9	1409.2	1505.9	1611.4	1717.4	1823.4	1922.4	2011.6	2101.2	2206.1	2270.5
22.5°	1305.0	1391.4	1491.8	1603.9	1717.9	1829.5	1941.6	2046.3	2147.1	2252.9	2335.2
25°	1269.1	1371.7	1480.7	1594.9	1707.4	1830.5	1964.0	2080.7	2205.5	2314.5	2392.4
27.5°	1232.8	1326.8	1435.3	1551.2	1676.3	1821.7	1978.8	2111.3	2236.4	2314.5	2339.0
30°	1200.0	1299.6	1399.2	1517.0	1652.3	1814.6	1981.7	2133.4	2235.9	2269.9	2244.7
32.5°	1166.7	1257.0	1355.6	1476.2	1620.0	1797.3	1985.4	2120.3	2182.0	2156.0	2053.5
35°	1108.0	1189.5	1285.0	1405.7	1570.9	1787.7	1970.0	2061.3	2046.1	1899.6	1706.2
37.5°	1045.2	1111.6	1200.0	1326.2	1520.0	1749.6	1903.3	1916.8	1785.0	1560.1	1336.8
40°	995.5	1055.2	1146.1	1277.9	1480.7	1712.1	1836.3	1781.8	1577.4	1327.1	1140.8
42.5°	947.2	997.6	1085.1	1227.3	1443.2	1661.0	1736.5	1617.8	1381.9	1145.3	975.9
45°	865.4	912.9	1000.7	1146.7	1366.4	1563.3	1553.3	1347.0	1110.9	920.5	779.9
47.5°	787.8	829.3	911.8	1060.8	1276.3	1416.8	1323.6	1104.1	903.9	751.1	650.7
50°	733.0	774.0	856.1	1003.2	1204.1	1306.7	1173.6	962.1	778.7	652.1	572.5
52.5°	680.5	720.6	795.6	938.9	1116.9	1178.2	1035.4	839.3	686.4	577.1	508.7
55°	607.0	637.5	704.9	842.0	975.0	989.0	844.3	680.3	554.3	478.1	431.3
57.5°	532.2	558.4	625.0	734.2	827.4	820.2	682.9	541.1	456.2	399.6	365.7
60°	483.4	509.2	567.7	661.5	731.8	707.2	581.3	467.0	394.3	352.8	325.8
62.5°	437.9	458.1	512.9	581.3	632.0	604.1	496.9	402.3	344.7	309.6	288.3
65°	372.0	388.5	432.4	468.1	496.3	469.3	380.3	314.6	273.0	248.4	233.8
67.5°	309.5	319.9	347.7	360.6	380.4	350.9	285.9	242.0	218.3	197.6	187.4
70°	270.1	277.8	292.4	302.9	308.2	277.8	229.7	197.4	177.5	162.9	156.4
72.5°	230.7	237.5	240.4	249.0	246.3	217.7	184.7	159.0	144.7	134.7	126.5
75°	176.3	179.3	176.3	172.9	165.2	145.3	122.4	109.6	99.0	94.4	91.4
77.5°	128.5	127.6	123.6	118.1	105.1	92.6	80.2	75.9	71.4	68.9	67.8
80°	99.0	96.7	93.2	84.4	73.3	64.5	61.6	58.6	56.8	53.9	53.3
82.5°	73.7	72.3	66.5	59.1	51.2	47.1	44.7	43.6	41.8	40.3	40.2
85°	39.3	37.5	31.1	26.9	25.7	24.6	24.0	24.0	21.7	21.1	21.1
87.5°	13.3	10.8	10.9	9.9	10.2	9.8	10.8	10.3	10.4	10.7	9.9
90°	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7	21.5
92.5°	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7	72.3
95°	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4	309.4
97.5°	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0	771.3
100°	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2	1013.3
102.5°	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1	1093.7
105°	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6	1117.2
107.5°	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8	1049.6
110°	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1	984.9





TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9	920.9
115°	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3	836.2
117.5°	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6	774.9
120°	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4	742.5
122.5°	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5	717.1
125°	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3	683.3
127.5°	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4	653.7
130°	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8	635.2
132.5°	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8	617.9
135°	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2	594.7
137.5°	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0	573.6
140°	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8	561.2
142.5°	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3	549.5
145°	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9	535.5
147.5°	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7	523.9
150°	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8	515.7
152.5°	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4	508.1
155°	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2	496.7
157.5°	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9	484.7
160°	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7	477.9
162.5°	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5	469.6
165°	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0	458.9
167.5°	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0	449.6
170°	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2	443.5
172.5°	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4	438.0
175°	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9	430.6
177.5°	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1443.7	1443.7	1445.6	1452.7	1453.6	1459.7	1457.8
5°	1586.7	1597.8	1602.0	1619.5	1630.0	1634.8	1625.4
7.5°	1761.6	1792.9	1807.8	1826.3	1842.5	1847.4	1834.7
10°	1889.0	1921.8	1949.4	1966.4	1982.2	1992.8	2006.2
12.5°	2012.3	2052.6	2078.8	2102.8	2119.1	2132.4	2134.7
15°	2146.3	2207.3	2253.5	2287.5	2304.5	2313.2	2309.8
17.5°	2281.4	2337.9	2370.8	2405.5	2429.1	2430.3	2430.9
20°	2357.8	2412.9	2451.0	2476.8	2503.1	2502.0	2507.8
22.5°	2408.9	2452.3	2481.5	2500.2	2509.2	2504.7	2505.9
25°	2432.8	2445.7	2440.4	2410.5	2403.0	2375.4	2380.1
27.5°	2309.5	2248.6	2185.6	2104.5	2040.5	1989.3	1991.9
30°	2142.2	2034.4	1911.3	1808.2	1715.6	1689.9	1634.8
32.5°	1908.3	1746.5	1602.4	1506.3	1426.8	1405.3	1357.3
35°	1511.7	1354.7	1206.4	1117.4	1082.2	1033.0	1032.4
37.5°	1175.0	1036.7	958.4	891.6	856.5	826.7	823.8
40°	988.5	880.6	821.5	773.4	738.9	716.6	711.4
42.5°	858.2	770.9	715.6	685.8	659.2	647.7	639.1
45°	700.8	642.2	603.5	576.5	564.3	555.4	550.8
47.5°	586.2	546.9	520.6	502.7	492.7	483.4	485.9
50°	523.8	491.6	472.3	455.3	447.6	441.2	441.8
52.5°	473.6	444.7	429.1	416.8	407.3	402.8	400.5
55°	401.9	383.7	368.0	359.2	353.9	347.5	345.7
57.5°	342.9	328.8	315.9	306.0	304.7	298.5	299.3
60°	303.5	291.8	281.3	276.0	271.9	266.6	268.4
62.5°	271.2	261.3	251.8	247.4	243.3	239.4	240.2
65°	222.1	212.7	206.8	204.5	202.8	201.0	199.2
67.5°	176.9	171.3	167.6	162.6	158.9	158.3	156.5
70°	148.9	141.2	134.7	128.3	126.6	126.0	126.6
72.5°	119.3	114.5	112.7	109.6	109.3	107.7	108.7
75°	89.6	87.9	86.7	84.4	84.4	84.4	84.4
77.5°	66.1	65.0	64.3	63.9	63.3	62.4	62.3
80°	51.6	51.0	49.8	49.8	49.2	49.8	49.2
82.5°	38.9	38.8	37.6	37.6	37.0	36.7	37.0
85°	19.9	19.4	20.5	19.4	19.9	18.8	19.9
87.5°	10.1	10.2	10.2	10.0	9.6	10.8	9.6
90°	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P332350-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)