

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332353-935

Luminaire Tested: **S123RDIP-S1000D1025U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332353-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6461.6 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	49	48	43
2	90	82	77	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36	31
4	75	65	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	2.1
10°-20°	377.5	5.8
20°-30°	543.6	8.4
30°-40°	612.3	9.5
40°-50°	585.8	9.1
50°-60°	479.7	7.4
60°-70°	323.7	5.0
70°-80°	162.8	2.5
80°-90°	46.4	0.7
90°-100°	236.3	3.7
100°-110°	669.0	10.4
110°-120°	658.1	10.2
120°-130°	525.0	8.1
130°-140°	413.9	6.4
140°-150°	308.9	4.8
150°-160°	215.3	3.3
160°-170°	126.5	2.0
170°-180°	41.2	0.6
0°-30°	1056.8	16.4
0°-40°	1669.1	25.8
0°-60°	2734.6	42.3
0°-90°	3267.4	50.6
90°-120°	1563.5	24.2
90°-150°	2811.2	43.5
90°-180°	3194.0	49.4
0°-180°	6461.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	2	10	22	24	25	5
95°	29	95	510	149	100	32
105°	100	147	691	1208	1093	106
115°	176	220	529	1159	1330	174
125°	245	289	493	894	1048	217
135°	287	342	486	736	850	222
145°	327	375	480	604	664	205
155°	372	401	465	529	551	171
165°	406	418	445	472	480	115
175°	424	424	427	433	432	40
180°	425	425	425	425	425	



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.8	20.9	18.9	17.1	15.2	14.5	14.9	15.4	15.9	16.4	16.1
90°	1.7	3.4	5.2	7.7	9.5	11.2	13.8	16.4	18.9	21.5	20.7
92.5°	10.7	15.8	23.1	29.7	36.9	49.7	72.2	109.2	145.4	132.2	99.7
95°	29.2	31.8	41.2	55.9	78.2	111.8	184.8	312.8	453.7	509.6	413.4
97.5°	49.9	50.7	58.1	70.8	92.8	129.1	198.9	343.3	578.2	789.8	845.0
100°	63.6	64.5	70.5	82.5	103.1	136.6	196.8	324.0	550.0	813.9	983.2
102.5°	78.0	79.6	84.9	96.3	114.9	145.6	199.6	307.5	508.8	769.2	990.1
105°	99.7	102.3	107.5	117.8	134.1	160.7	207.2	295.7	458.1	691.0	937.6
107.5°	122.7	125.3	130.3	140.4	155.8	180.5	221.2	294.8	425.8	621.9	845.8
110°	139.2	141.8	146.1	155.6	170.1	194.2	232.9	298.3	413.4	582.7	788.1



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	154.4	157.0	161.3	170.7	185.3	208.7	244.6	305.1	406.5	556.6	737.9
115°	176.2	179.6	184.8	193.4	208.0	231.2	263.8	316.2	403.9	528.6	677.3
117.5°	198.0	202.0	206.3	214.1	230.5	252.0	284.3	331.1	405.4	512.0	640.6
120°	213.1	215.7	220.0	228.6	245.0	266.4	297.4	342.1	408.2	504.5	621.4
122.5°	226.2	228.8	233.1	242.4	258.0	280.9	311.1	352.4	413.0	499.6	605.5
125°	245.0	246.7	251.8	261.2	277.6	300.8	330.9	368.7	420.3	493.4	585.3
127.5°	259.2	261.7	268.1	277.8	295.8	319.0	348.1	382.1	428.5	490.3	567.4
130°	268.1	270.7	278.4	288.8	306.8	330.0	358.3	391.1	434.0	488.2	557.8
132.5°	275.0	278.3	286.7	299.1	317.1	339.7	367.3	399.3	438.2	487.5	548.8
135°	287.1	290.5	300.0	312.8	330.9	354.0	380.7	409.9	444.4	486.5	537.2
137.5°	298.4	302.0	311.3	325.0	342.9	364.4	390.0	417.8	448.4	484.6	527.0
140°	306.0	310.2	318.8	332.6	349.8	371.3	396.2	422.0	451.2	483.9	520.8
142.5°	314.2	317.8	327.1	339.5	356.6	376.8	401.1	426.1	453.2	482.5	515.3
145°	327.4	330.0	337.8	350.7	365.2	385.0	407.3	430.6	454.6	480.4	507.9
147.5°	340.9	342.4	350.0	361.1	375.2	392.1	412.5	433.3	454.6	477.2	500.7
150°	349.8	350.7	357.5	368.7	380.7	396.2	415.9	434.0	454.6	474.4	495.8
152.5°	358.7	358.9	365.8	375.6	386.2	401.1	418.0	435.4	452.5	471.0	490.4
155°	372.1	372.1	377.3	385.9	395.4	407.3	422.0	435.8	450.3	464.9	482.2
157.5°	382.8	383.5	387.6	395.2	403.2	412.5	424.2	436.6	447.5	459.6	472.9
160°	391.1	391.1	394.5	401.3	407.3	415.9	426.3	436.6	446.1	455.5	466.7
162.5°	397.3	397.3	400.0	405.4	410.8	418.0	427.0	435.9	443.3	451.3	460.5
165°	406.5	405.6	407.3	411.6	415.1	421.1	428.0	434.0	439.2	445.2	452.0
167.5°	413.5	412.5	413.4	416.6	419.0	422.8	427.8	432.7	435.1	439.0	444.0
170°	417.7	415.9	416.8	419.4	421.1	422.8	427.1	430.6	432.3	434.9	439.2
172.5°	420.4	419.4	419.6	421.5	422.5	423.5	427.1	429.9	430.2	431.4	434.4
175°	423.7	422.8	422.0	423.7	423.7	424.6	426.3	428.0	427.1	427.1	428.9
177.5°	425.2	424.6	423.9	424.6	424.6	424.6	425.2	426.6	425.2	424.6	425.2
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	16.1	16.0	16.0	16.1	15.8	15.8	15.7	15.3
90°	21.5	22.4	23.2	24.9	24.0	24.9	25.7	24.9
92.5°	72.3	57.4	50.7	46.2	44.7	42.1	43.0	41.4
95°	309.4	209.7	164.2	133.2	116.9	109.2	103.1	99.7
97.5°	771.3	617.8	506.9	404.1	340.7	302.0	278.8	271.4
100°	1013.3	943.7	843.1	721.1	634.3	571.5	538.0	538.9
102.5°	1093.7	1091.5	1032.9	955.5	887.9	838.3	810.3	790.5
105°	1117.2	1203.2	1219.5	1197.2	1157.6	1125.0	1097.5	1093.2
107.5°	1049.6	1189.1	1264.4	1295.0	1295.7	1284.7	1275.4	1267.5
110°	984.9	1143.1	1251.3	1311.5	1335.6	1342.5	1340.7	1339.0



TEST NUMBER: P332353-935

CATALOG NUMBER: S123RDIP-S1000D1025U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	920.9	1082.5	1203.9	1281.3	1325.3	1346.5	1353.1	1353.4
115°	836.2	985.8	1112.1	1205.7	1270.2	1308.0	1325.3	1329.6
117.5°	774.9	904.0	1017.4	1112.4	1179.7	1223.0	1247.8	1253.5
120°	742.5	858.6	961.7	1048.5	1116.4	1164.5	1185.2	1190.3
122.5°	717.1	822.2	917.7	998.3	1058.7	1102.0	1124.6	1131.2
125°	683.3	777.0	859.5	928.2	983.2	1021.0	1042.5	1048.5
127.5°	653.7	737.2	811.7	874.2	923.2	955.5	974.9	980.4
130°	635.2	712.5	782.0	840.5	886.1	917.1	935.0	941.9
132.5°	617.9	689.1	753.9	809.6	852.4	883.3	899.3	904.1
135°	594.7	655.7	711.6	760.6	802.7	828.5	844.0	850.0
137.5°	573.6	623.6	671.8	714.2	749.6	775.8	788.8	792.7
140°	561.2	605.0	646.3	683.3	715.9	739.9	753.7	752.9
142.5°	549.5	587.2	622.9	655.0	682.9	704.2	716.6	715.7
145°	535.5	563.8	591.2	616.2	637.7	655.7	662.6	664.3
147.5°	523.9	546.4	568.6	586.3	602.6	614.8	621.4	622.1
150°	515.7	535.5	553.5	569.8	582.7	592.1	597.3	597.3
152.5°	508.1	525.1	541.1	554.7	564.8	573.6	576.7	576.7
155°	496.7	510.5	523.4	533.7	541.5	548.3	550.0	550.9
157.5°	484.7	496.2	506.2	514.3	521.0	526.2	527.5	527.4
160°	477.9	487.3	495.8	501.9	507.9	513.1	513.1	512.2
162.5°	469.6	477.7	485.6	490.9	494.9	499.3	499.3	498.4
165°	458.9	464.1	470.1	474.4	477.9	481.3	480.4	480.4
167.5°	449.6	453.6	457.0	460.1	461.7	464.1	463.2	463.2
170°	443.5	446.1	449.4	451.2	452.0	453.7	452.9	452.9
172.5°	438.0	439.9	442.6	443.7	443.8	445.6	444.0	443.3
175°	430.6	431.4	433.2	433.2	433.2	434.0	433.2	432.3
177.5°	425.9	426.6	427.3	427.3	426.6	427.3	425.9	425.9
180°	424.6	424.6	424.6	424.6	424.6	424.6	424.6	424.6

(END OF REPORT)