

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331979-940

Luminaire Tested: **S123DIP-S775D805U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331979-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5689.7 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50					50			
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42					42			
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	40	35					35			
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	30					30			
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25					25			
5	68	56	48	42	62	52	45	40	45	39	35	38	33	30	31	28	25	22					22			
6	63	51	42	37	58	47	40	34	40	35	30	34	30	26	28	25	22	19					19			
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17					17			
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15					15			
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14					14			
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	13					13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.8
10°-20°	288.8	5.1
20°-30°	426.6	7.5
30°-40°	498.4	8.8
40°-50°	501.0	8.8
50°-60°	440.1	7.7
60°-70°	327.9	5.8
70°-80°	186.8	3.3
80°-90°	56.3	1.0
90°-100°	34.1	0.6
100°-110°	162.6	2.9
110°-120°	390.6	6.9
120°-130°	497.3	8.7
130°-140°	531.4	9.3
140°-150°	496.9	8.7
150°-160°	400.8	7.0
160°-170°	258.7	4.5
170°-180°	89.2	1.6
0°-30°	817.7	14.4
0°-40°	1316.1	23.1
0°-60°	2257.3	39.7
0°-90°	2828.2	49.7
90°-120°	587.3	10.3
90°-150°	2112.9	37.1
90°-180°	2862.0	50.3
0°-180°	5689.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	8	17	19	21	5
95°	42	16	22	26	26	53
105°	208	212	153	36	31	220
115°	390	394	400	407	410	385
125°	549	555	558	559	560	490
135°	684	688	691	693	691	526
145°	789	794	795	797	797	494
155°	869	868	869	872	868	400
165°	917	915	914	919	915	259
175°	938	935	936	940	935	89
180°	938	938	938	938	938	



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.5	19.4	19.2	19.0	18.8	18.8	19.1	19.4	19.5	19.8	19.7
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	12.9	12.6	12.1	11.7	11.2	11.8	13.3	14.8	16.3	17.8	18.8
95°	42.5	36.2	29.8	23.5	17.1	14.8	16.5	18.2	19.9	21.6	22.7
97.5°	85.4	82.7	79.8	77.0	74.1	67.1	55.9	44.8	33.6	22.5	23.7
100°	117.8	120.9	124.0	127.1	130.2	119.7	95.5	71.3	47.2	23.0	24.3
102.5°	154.6	156.9	159.1	161.3	163.5	151.5	125.1	98.6	72.2	45.8	42.0
105°	207.8	209.5	211.2	212.9	214.5	208.5	194.5	180.6	166.6	152.7	125.3
107.5°	263.8	265.2	266.5	267.9	269.2	271.0	273.2	275.4	277.6	279.8	259.8
110°	301.1	302.4	303.6	304.9	306.1	307.6	309.3	311.0	312.7	314.4	309.3



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	338.0	339.1	340.2	341.3	342.7	344.5	346.2	347.9	349.6	349.6
115°	389.7	390.7	391.6	392.5	393.4	394.6	396.0	397.3	398.8	400.2	401.7
117.5°	440.9	442.0	443.2	444.3	445.4	446.4	447.1	447.8	448.5	449.2	450.5
120°	472.7	474.0	475.5	476.8	478.2	479.2	479.7	480.1	480.5	481.0	482.2
122.5°	505.0	506.1	507.3	508.5	509.6	510.4	511.0	511.7	512.2	512.8	513.7
125°	549.4	550.5	551.8	553.0	554.3	555.3	555.9	556.4	557.1	557.7	558.0
127.5°	592.3	593.5	594.8	596.0	597.3	598.2	599.0	599.8	600.5	601.2	601.7
130°	619.0	620.3	621.5	622.8	624.0	624.9	625.5	626.2	626.8	627.4	628.0
132.5°	644.7	646.0	647.2	648.5	649.7	650.5	651.0	651.5	652.0	652.6	653.2
135°	683.9	684.8	685.7	686.7	687.6	688.4	689.0	689.6	690.3	690.9	691.3
137.5°	717.4	718.5	719.7	720.9	722.0	722.8	723.2	723.5	723.8	724.2	725.0
140°	739.7	740.6	741.5	742.4	743.4	744.0	744.6	745.0	745.5	745.9	746.5
142.5°	760.3	761.3	762.1	763.1	764.0	764.7	765.2	765.6	766.1	766.6	767.0
145°	789.2	790.2	791.3	792.4	793.5	794.2	794.5	794.8	795.1	795.4	795.8
147.5°	816.4	817.1	817.8	818.5	819.2	819.7	820.0	820.3	820.6	820.9	821.3
150°	833.0	833.6	834.0	834.5	834.9	835.4	835.6	836.0	836.2	836.6	836.9
152.5°	848.1	848.4	848.6	848.8	849.0	849.2	849.4	849.5	849.8	850.0	850.5
155°	869.3	869.1	868.7	868.4	868.1	868.0	868.2	868.3	868.4	868.6	869.4
157.5°	885.7	885.7	885.7	885.6	885.6	885.6	885.4	885.3	885.1	884.9	885.9
160°	895.8	895.6	895.5	895.4	895.2	895.0	894.9	894.7	894.6	894.4	895.4
162.5°	905.3	904.9	904.5	904.1	903.7	903.4	903.2	903.1	902.9	902.8	903.8
165°	916.8	916.2	915.8	915.3	914.9	914.5	914.4	914.3	914.1	913.9	915.2
167.5°	925.7	925.1	924.4	923.8	923.2	922.8	922.8	922.8	922.8	922.8	924.1
170°	930.7	930.1	929.4	928.8	928.2	927.9	927.9	927.9	927.9	927.9	929.2
172.5°	934.0	933.3	932.6	931.7	931.0	930.8	930.9	930.9	931.1	931.2	932.5
175°	938.3	937.5	936.8	936.0	935.2	935.0	935.0	935.2	935.4	935.6	936.7
177.5°	939.4	938.9	938.3	937.6	937.0	936.7	936.8	937.0	937.1	937.2	938.3
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	19.7	19.6	19.6	19.6	19.7	19.7	19.8	19.9
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	19.8	20.8	21.8	22.4	22.6	22.7	22.9	23.2
95°	23.8	24.9	25.9	26.5	26.5	26.5	26.5	26.5
97.5°	25.0	26.1	27.4	28.1	28.3	28.4	28.5	28.7
100°	25.5	26.8	28.0	28.6	28.8	29.0	29.2	29.2
102.5°	38.2	34.3	30.5	28.7	29.0	29.2	29.5	29.9
105°	97.8	70.4	43.0	29.4	29.8	30.1	30.4	30.7
107.5°	239.6	219.5	199.4	179.0	158.4	137.7	117.0	96.3
110°	304.2	299.1	294.0	280.4	258.2	236.0	213.8	191.7



TEST NUMBER: P331979-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	349.7	349.8	349.9	347.6	343.0	338.2	333.6	329.0
115°	403.2	404.8	406.4	407.4	408.0	408.7	409.3	409.9
117.5°	451.7	453.0	454.1	454.9	455.0	455.1	455.2	455.4
120°	483.5	484.7	486.0	486.6	486.6	486.6	486.6	486.6
122.5°	514.5	515.4	516.3	516.7	516.9	517.0	517.2	517.3
125°	558.3	558.7	558.9	559.3	559.5	559.9	560.2	560.5
127.5°	602.2	602.7	603.2	603.2	603.0	602.7	602.4	602.1
130°	628.7	629.3	629.9	630.1	629.7	629.5	629.1	628.8
132.5°	653.7	654.3	655.0	655.1	654.7	654.2	653.8	653.4
135°	691.8	692.2	692.7	692.7	692.2	691.8	691.3	690.9
137.5°	725.7	726.4	727.2	727.4	727.1	726.7	726.5	726.1
140°	747.2	747.8	748.4	748.6	748.2	748.0	747.6	747.3
142.5°	767.6	768.0	768.6	768.6	768.1	767.7	767.3	766.9
145°	796.0	796.4	796.7	796.8	796.8	796.8	796.8	796.8
147.5°	821.5	821.9	822.2	822.0	821.3	820.6	819.8	819.1
150°	837.1	837.5	837.8	837.8	837.2	836.8	836.3	835.9
152.5°	851.0	851.6	852.2	852.1	851.4	850.7	850.0	849.3
155°	870.2	870.9	871.7	871.6	870.8	869.8	868.9	867.9
157.5°	886.8	887.7	888.7	888.5	887.3	886.1	884.9	883.7
160°	896.3	897.2	898.1	898.0	897.0	895.9	894.8	893.8
162.5°	904.9	906.0	907.0	907.0	906.1	905.1	904.2	903.2
165°	916.4	917.7	918.9	919.0	917.9	916.8	915.7	914.6
167.5°	925.3	926.6	927.8	927.8	926.6	925.3	924.1	922.8
170°	930.3	931.6	932.8	932.8	931.6	930.3	929.2	927.9
172.5°	933.7	935.0	936.2	936.1	934.8	933.4	932.0	930.7
175°	937.7	938.8	939.9	939.8	938.6	937.4	936.1	934.9
177.5°	939.2	940.2	941.2	941.1	939.9	938.6	937.4	936.1
180°	938.3	938.3	938.3	938.3	938.3	938.3	938.3	938.3

(END OF REPORT)