

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831811

Luminaire Tested: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831811
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7235.6 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

Luminous Intensity Polar Plot



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				51
1	99	95	91	88	91	88	85	82	75	73	71	63	61	60	52	51	50				45	
2	91	84	78	73	84	78	73	69	67	63	60	56	54	51	47	45	43				39	
3	83	75	68	62	77	69	63	59	60	55	51	51	47	45	42	40	38				34	
4	77	67	59	54	71	62	56	51	54	49	45	46	42	39	38	36	34				30	
5	71	60	52	47	66	56	49	44	49	43	39	42	38	35	35	32	30				27	
6	66	54	47	41	61	51	44	39	44	39	35	38	34	31	32	29	27				24	
7	61	49	42	37	57	46	40	35	41	35	31	35	31	28	30	27	25				22	
8	57	45	38	33	53	42	36	31	37	32	28	32	28	25	28	25	22				20	
9	53	42	34	30	49	39	33	28	34	29	26	30	26	23	26	23	21				19	
10	50	38	32	27	46	36	30	26	32	27	23	28	24	21	24	21	19				17	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	30074	30074	30074	30074	30074
5°	35710	34571	30263	24464	22713
10°	32354	35114	30112	19601	16816
15°	22276	30107	29795	16020	13301
20°	15497	23180	29196	13509	11692
25°	11809	17667	28326	12006	10776
30°	10280	14124	27237	11149	9981
35°	9437	11914	25695	10424	9257
40°	8612	10640	23678	9714	8595
45°	7777	9730	21500	9042	7934
50°	7060	8977	18933	8383	7117
55°	6384	8244	16467	7739	6105
60°	5722	7496	14303	7029	5772
65°	5280	6653	12312	6316	5456
70°	4290	5750	10744	5715	4434
75°	3764	4575	9100	4741	3905
80°	3409	3868	7457	3973	3694
85°	3112	3396	5656	3606	3396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 22686 cd/sqm



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.7	3.5
10°-20°	589.3	8.1
20°-30°	676.1	9.3
30°-40°	666.4	9.2
40°-50°	587.7	8.1
50°-60°	452.1	6.2
60°-70°	297.3	4.1
70°-80°	144.4	2.0
80°-90°	39.1	0.5
90°-100°	82.0	1.1
100°-110°	248.1	3.4
110°-120°	422.4	5.8
120°-130°	555.7	7.7
130°-140°	624.6	8.6
140°-150°	614.1	8.5
150°-160°	517.0	7.1
160°-170°	344.2	4.8
170°-180°	120.5	1.7
0°-30°	1520.1	21.0
0°-40°	2186.5	30.2
0°-60°	3226.4	44.6
0°-90°	3707.1	51.2
90°-120°	752.5	10.4
90°-150°	2546.9	35.2
90°-180°	3529.0	48.8
0°-180°	7235.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2794	2794	2794	2794	2794	
5°	3305	3200	2801	2264	2102	302
15°	1999	2702	2674	1438	1194	564
25°	994	1488	2385	1011	907	470
35°	718	907	1955	793	704	448
45°	511	639	1412	594	521	397
55°	340	439	878	412	325	305
65°	207	261	483	248	214	203
75°	90	110	219	114	94	97
85°	25	28	46	29	28	27
90°	30	24	1	24	30	16
95°	78	74	59	74	78	78
105°	238	236	225	236	238	252
115°	426	426	425	426	426	422
125°	615	623	622	623	615	550
135°	806	812	807	812	806	620
145°	979	984	979	984	979	612
155°	1119	1122	1121	1122	1119	516
165°	1218	1218	1222	1218	1218	344
175°	1266	1266	1270	1266	1266	120
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	3096.4	3086.6	3076.9	3074.0	3071.2	3062.0	3052.8	3032.2	3011.6	2990.4	2969.2
5°	3304.9	3306.0	3307.2	3304.3	3301.4	3289.4	3277.4	3252.2	3227.0	3199.5	3172.0
7.5°	3240.7	3259.0	3277.4	3280.8	3284.2	3293.4	3302.6	3296.8	3291.1	3280.8	3270.5
10°	2960.1	2958.9	2957.8	2978.4	2999.0	3060.3	3121.6	3153.1	3184.6	3212.6	3240.7
12.5°	2501.8	2503.6	2505.3	2572.9	2640.5	2698.3	2756.2	2836.3	2916.5	3003.0	3089.5
15°	1999.0	2027.0	2055.1	2115.2	2175.4	2262.4	2349.5	2457.2	2564.8	2701.7	2838.6
17.5°	1641.5	1653.6	1665.6	1723.5	1781.3	1863.8	1946.3	2068.3	2190.3	2366.7	2543.1
20°	1352.9	1363.8	1374.6	1416.5	1458.3	1537.3	1616.3	1732.6	1848.9	2023.6	2198.3
22.5°	1129.5	1150.7	1171.9	1199.9	1228.0	1285.3	1342.6	1461.1	1579.7	1738.9	1898.1
25°	994.3	1004.1	1013.8	1037.9	1061.9	1116.9	1171.9	1250.3	1328.8	1487.5	1646.1
27.5°	902.7	905.5	908.4	926.2	943.9	979.4	1014.9	1087.7	1160.4	1291.0	1421.6
30°	827.1	832.2	837.4	851.1	864.9	890.7	916.4	968.0	1019.5	1136.4	1253.2
32.5°	768.7	771.5	774.4	785.8	797.3	816.2	835.1	875.8	916.4	1005.8	1095.1
35°	718.2	718.8	719.4	728.0	736.6	754.9	773.2	807.0	840.8	906.7	972.6
37.5°	661.0	665.0	669.0	675.3	681.6	697.6	713.7	741.2	768.7	823.1	877.5
40°	612.9	616.3	619.7	627.2	634.6	647.2	659.8	685.0	710.2	757.2	804.2
42.5°	564.7	567.0	569.3	576.8	584.2	599.7	615.2	635.2	655.2	694.2	733.1
45°	510.9	516.6	522.4	530.4	538.4	551.6	564.7	585.4	606.0	639.2	672.4
47.5°	466.2	469.1	472.0	478.8	485.7	501.7	517.8	536.1	554.4	585.4	616.3
50°	421.6	422.7	423.8	430.1	436.4	450.8	465.1	486.3	507.5	536.1	564.7
52.5°	379.2	382.0	384.9	391.2	397.5	407.2	417.0	438.7	460.5	488.6	516.6
55°	340.2	341.9	343.7	348.2	352.8	364.3	375.7	394.6	413.5	439.3	465.1
57.5°	303.6	305.9	308.1	311.6	315.0	325.3	335.6	352.3	368.9	394.6	420.4
60°	265.8	268.6	271.5	275.5	279.5	287.5	295.5	310.4	325.3	348.2	371.2
62.5°	238.3	238.8	239.4	242.9	246.3	252.0	257.7	269.8	281.8	304.7	327.6
65°	207.3	209.1	210.8	212.5	214.2	218.8	223.4	233.7	244.0	261.2	278.4
67.5°	175.3	177.0	178.7	181.6	184.4	188.4	192.4	199.3	206.2	222.2	238.3
70°	136.3	136.3	136.3	140.9	145.5	152.4	159.2	164.4	169.5	182.7	195.9
72.5°	111.1	111.7	112.3	112.8	113.4	117.4	121.4	130.0	138.6	146.6	154.6
75°	90.5	91.1	91.6	92.2	92.8	93.9	95.1	97.9	100.8	110.0	119.1
77.5°	72.2	72.7	73.3	73.9	74.5	75.6	76.8	77.9	79.0	82.5	85.9
80°	55.0	55.6	56.1	56.7	57.3	57.8	58.4	59.6	60.7	62.4	64.1
82.5°	40.1	40.1	40.1	40.1	40.1	41.2	42.4	42.4	42.4	43.5	44.7
85°	25.2	25.2	25.2	25.8	26.3	26.3	26.3	26.9	27.5	27.5	27.5
87.5°	11.5	10.9	10.3	10.9	11.5	11.5	11.5	12.0	12.6	12.6	12.6
90°	30.0	29.6	29.1	28.7	28.2	27.6	26.7	25.8	24.9	24.0	21.1
92.5°	43.0	43.5	43.9	44.4	44.8	44.7	44.0	43.3	42.7	42.0	40.7
95°	78.0	78.0	78.0	78.0	78.0	77.6	76.7	75.8	74.9	74.0	72.2
97.5°	112.0	112.3	112.5	112.7	112.9	112.5	111.4	110.3	109.2	108.0	106.7
100°	152.1	151.6	151.2	150.7	150.3	149.7	149.1	148.4	147.7	147.1	145.9
102.5°	193.1	193.3	193.5	193.7	194.0	193.7	193.1	192.4	191.7	191.1	189.5
105°	238.1	237.6	237.2	236.8	236.3	236.1	236.1	236.1	236.1	236.1	234.1
107.5°	284.1	284.3	284.6	284.8	285.0	284.8	284.1	283.4	282.8	282.1	281.2
110°	331.1	331.6	332.0	332.5	332.9	332.7	331.8	330.9	330.0	329.1	328.7



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.1	381.1	381.1	381.1	381.1	380.6	379.5	378.4	377.3	376.1	376.1
115°	426.2	426.4	426.6	426.8	427.1	427.1	426.8	426.6	426.4	426.2	426.6
117.5°	472.2	472.8	473.5	474.2	474.8	475.2	475.2	475.2	475.2	475.2	475.6
120°	521.2	521.6	522.1	522.5	523.0	523.3	523.5	523.8	524.0	524.2	525.3
122.5°	568.2	568.9	569.5	570.2	570.9	571.5	572.2	572.9	573.5	574.2	574.7
125°	615.2	616.1	617.0	617.9	618.8	619.7	620.6	621.5	622.3	623.2	623.7
127.5°	662.2	663.1	664.0	664.9	665.8	666.9	668.3	669.6	670.9	672.3	672.7
130°	708.3	709.8	711.4	712.9	714.5	715.7	716.6	717.5	718.4	719.3	719.9
132.5°	756.3	757.4	758.5	759.6	760.7	761.8	763.0	764.1	765.2	766.3	766.7
135°	806.3	806.7	807.2	807.6	808.1	808.7	809.6	810.5	811.4	812.3	812.5
137.5°	850.3	851.0	851.7	852.3	853.0	853.9	855.0	856.1	857.2	858.3	857.7
140°	893.3	894.9	896.4	898.0	899.6	900.5	900.7	900.9	901.1	901.3	901.1
142.5°	937.4	938.5	939.6	940.7	941.8	942.5	942.7	942.9	943.1	943.4	942.9
145°	979.4	980.3	981.1	982.0	982.9	983.5	983.7	983.9	984.1	984.4	983.7
147.5°	1017.4	1018.7	1020.1	1021.4	1022.7	1023.4	1023.4	1023.4	1023.4	1023.4	1022.7
150°	1053.4	1054.7	1056.1	1057.4	1058.7	1059.4	1059.4	1059.4	1059.4	1059.4	1059.0
152.5°	1088.4	1089.5	1090.6	1091.7	1092.9	1093.2	1092.7	1092.3	1091.9	1091.4	1091.2
155°	1119.4	1121.0	1122.5	1124.1	1125.6	1126.0	1125.1	1124.2	1123.3	1122.4	1122.2
157.5°	1148.4	1149.8	1151.1	1152.4	1153.8	1154.0	1153.1	1152.2	1151.3	1150.4	1150.2
160°	1176.4	1177.3	1178.2	1179.1	1180.0	1179.9	1178.8	1177.7	1176.6	1175.4	1175.4
162.5°	1197.5	1199.0	1200.6	1202.1	1203.7	1203.9	1202.8	1201.7	1200.6	1199.5	1199.2
165°	1217.5	1219.0	1220.6	1222.1	1223.7	1223.8	1222.5	1221.1	1219.8	1218.5	1218.5
167.5°	1235.5	1236.8	1238.1	1239.5	1240.8	1240.8	1239.5	1238.1	1236.8	1235.5	1235.2
170°	1248.5	1250.0	1251.6	1253.1	1254.7	1254.7	1253.1	1251.6	1250.0	1248.5	1248.5
172.5°	1258.5	1260.0	1261.6	1263.1	1264.7	1264.8	1263.5	1262.1	1260.8	1259.5	1259.5
175°	1265.5	1267.0	1268.6	1270.1	1271.7	1271.8	1270.5	1269.1	1267.8	1266.5	1266.5
177.5°	1269.5	1271.0	1272.6	1274.1	1275.7	1275.8	1274.5	1273.1	1271.8	1270.5	1270.5
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	2966.4	2963.5	2936.0	2908.5	2881.6	2854.7	2834.6	2814.6	2780.8	2747.0	2725.8
5°	3150.2	3128.5	3084.9	3041.4	2976.1	2910.8	2855.8	2800.8	2731.0	2661.1	2602.7
7.5°	3252.7	3235.0	3182.3	3129.6	3043.1	2956.6	2870.7	2784.8	2681.7	2578.6	2490.4
10°	3255.6	3270.5	3227.0	3183.4	3086.1	2988.7	2871.9	2755.0	2616.4	2477.8	2363.8
12.5°	3153.7	3217.8	3208.6	3199.5	3100.4	3001.3	2859.3	2717.2	2547.1	2377.0	2234.4
15°	2962.9	3087.2	3123.9	3160.5	3078.6	2996.7	2835.2	2673.7	2473.8	2273.9	2110.1
17.5°	2717.2	2891.3	2988.1	3084.9	3025.4	2965.8	2788.8	2611.8	2386.7	2161.6	1983.5
20°	2426.2	2654.2	2806.0	2957.8	2936.0	2914.2	2731.5	2548.8	2306.0	2063.1	1870.1
22.5°	2138.7	2379.3	2588.9	2798.5	2820.9	2843.2	2658.8	2474.4	2208.6	1942.8	1746.4
25°	1890.7	2135.3	2385.0	2634.7	2685.1	2735.5	2560.3	2385.0	2109.5	1834.0	1638.7
27.5°	1654.2	1886.7	2161.6	2436.5	2528.2	2619.8	2459.5	2299.1	2012.1	1725.2	1530.4
30°	1461.1	1669.0	1949.7	2230.4	2358.1	2485.8	2338.6	2191.4	1906.7	1622.1	1431.3
32.5°	1281.3	1467.4	1749.2	2031.0	2179.4	2327.7	2200.6	2073.4	1799.6	1525.9	1337.4
35°	1139.2	1305.9	1568.8	1831.7	1997.8	2163.9	2059.7	1955.4	1687.9	1420.5	1242.3
37.5°	1017.2	1157.0	1403.9	1650.7	1827.1	2003.5	1916.5	1829.4	1578.0	1326.5	1158.1
40°	916.4	1028.7	1258.4	1488.0	1661.0	1834.0	1759.5	1685.1	1460.0	1234.9	1077.4
42.5°	829.9	926.7	1132.9	1339.1	1497.8	1656.4	1607.2	1557.9	1354.0	1150.1	1004.1
45°	753.8	835.1	1016.7	1198.2	1344.3	1490.3	1451.4	1412.4	1236.6	1060.8	926.7
47.5°	686.2	756.1	918.1	1080.2	1211.4	1342.6	1306.5	1270.4	1124.9	979.4	857.4
50°	624.3	683.9	819.1	954.2	1072.2	1190.2	1160.4	1130.6	1010.4	890.1	784.7
52.5°	565.9	615.2	736.6	858.0	953.1	1048.2	1025.3	1002.3	909.6	816.8	721.1
55°	510.3	555.6	658.1	760.6	842.0	923.3	900.4	877.5	805.3	733.1	648.9
57.5°	459.9	499.5	582.5	665.6	730.3	795.0	784.1	773.2	713.1	653.0	583.6
60°	406.7	442.2	513.8	585.4	637.5	689.6	677.0	664.4	621.5	578.5	518.9
62.5°	359.1	390.6	447.9	505.2	547.6	589.9	580.8	571.6	539.0	506.3	457.1
65°	309.3	340.2	386.6	433.0	466.2	499.5	491.4	483.4	458.8	434.2	394.6
67.5°	264.0	289.8	329.9	370.0	392.3	414.7	410.1	405.5	386.6	367.7	336.8
70°	218.2	240.6	273.8	307.0	322.5	337.9	339.7	341.4	324.2	307.0	284.1
72.5°	172.4	190.2	221.1	252.0	264.0	276.1	275.5	274.9	264.6	254.3	233.7
75°	132.3	145.5	169.5	193.6	203.9	214.2	216.5	218.8	209.1	199.3	187.9
77.5°	95.1	104.2	122.6	140.9	152.4	163.8	165.0	166.1	161.5	156.9	146.1
80°	67.0	69.9	81.3	92.8	104.8	116.8	118.6	120.3	115.7	111.1	104.2
82.5°	46.4	48.1	52.1	56.1	65.9	75.6	77.9	80.2	77.9	75.6	68.2
85°	28.1	28.6	30.4	32.1	36.7	41.2	43.5	45.8	44.7	43.5	39.5
87.5°	12.6	12.6	13.2	13.7	14.9	16.0	18.9	21.8	20.0	18.3	16.6
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	39.3	38.0	36.7	35.3	34.0	32.7	31.3	30.0	31.3	32.7	34.0
95°	70.5	68.7	66.9	65.2	63.7	62.1	60.6	59.0	60.6	62.1	63.7
97.5°	105.4	104.0	102.7	101.5	100.4	99.3	98.1	97.0	98.1	99.3	100.4
100°	144.8	143.7	142.6	141.4	140.1	138.7	137.4	136.1	137.4	138.7	140.1
102.5°	188.0	186.4	184.8	183.7	183.1	182.4	181.7	181.1	181.7	182.4	183.1
105°	232.1	230.1	228.1	226.9	226.4	226.0	225.5	225.1	225.5	226.0	226.4
107.5°	280.3	279.4	278.5	278.0	277.8	277.5	277.3	277.1	277.3	277.5	277.8
110°	328.2	327.8	327.3	326.9	326.5	326.0	325.6	325.1	325.6	326.0	326.5



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	376.1	376.1	376.1	376.0	375.8	375.6	375.4	375.1	375.4	375.6	375.8
115°	427.1	427.5	427.9	427.8	427.2	426.5	425.8	425.2	425.8	426.5	427.2
117.5°	476.1	476.5	477.0	477.1	476.8	476.6	476.4	476.2	476.4	476.6	476.8
120°	526.4	527.5	528.6	528.5	527.2	525.9	524.5	523.2	524.5	525.9	527.2
122.5°	575.1	575.6	576.0	575.8	574.9	574.0	573.1	572.2	573.1	574.0	574.9
125°	624.1	624.6	625.0	624.9	624.2	623.6	622.9	622.2	622.9	623.6	624.2
127.5°	673.1	673.6	674.0	673.6	672.3	670.9	669.6	668.3	669.6	670.9	672.3
130°	720.6	721.3	721.9	721.4	719.6	717.8	716.0	714.3	716.0	717.8	719.6
132.5°	767.2	767.6	768.1	767.4	765.6	763.8	762.1	760.3	762.1	763.8	765.6
135°	812.8	813.0	813.2	812.6	811.3	810.0	808.6	807.3	808.6	810.0	811.3
137.5°	857.0	856.3	855.7	854.8	853.7	852.5	851.4	850.3	851.4	852.5	853.7
140°	900.9	900.7	900.5	899.8	898.7	897.6	896.4	895.3	896.4	897.6	898.7
142.5°	942.5	942.0	941.6	940.8	939.7	938.6	937.5	936.4	937.5	938.6	939.7
145°	983.0	982.4	981.7	981.1	980.7	980.3	979.8	979.4	979.8	980.3	980.7
147.5°	1022.1	1021.4	1020.7	1019.9	1019.1	1018.2	1017.3	1016.4	1017.3	1018.2	1019.1
150°	1058.5	1058.1	1057.6	1057.2	1056.7	1056.3	1055.8	1055.4	1055.8	1056.3	1056.7
152.5°	1091.0	1090.7	1090.5	1090.1	1089.4	1088.7	1088.1	1087.4	1088.1	1088.7	1089.4
155°	1122.0	1121.8	1121.5	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4	1121.4
157.5°	1150.0	1149.8	1149.5	1149.5	1149.8	1150.0	1150.2	1150.4	1150.2	1150.0	1149.8
160°	1175.4	1175.4	1175.4	1175.7	1176.1	1176.6	1177.0	1177.4	1177.0	1176.6	1176.1
162.5°	1199.0	1198.8	1198.6	1198.8	1199.5	1200.1	1200.8	1201.5	1200.8	1200.1	1199.5
165°	1218.5	1218.5	1218.5	1218.8	1219.5	1220.1	1220.8	1221.5	1220.8	1220.1	1219.5
167.5°	1235.0	1234.8	1234.6	1234.9	1235.8	1236.7	1237.6	1238.5	1237.6	1236.7	1235.8
170°	1248.5	1248.5	1248.5	1248.9	1249.8	1250.7	1251.6	1252.5	1251.6	1250.7	1249.8
172.5°	1259.5	1259.5	1259.5	1259.9	1260.8	1261.7	1262.6	1263.5	1262.6	1261.7	1260.8
175°	1266.5	1266.5	1266.5	1266.9	1267.8	1268.7	1269.6	1270.5	1269.6	1268.7	1267.8
177.5°	1270.5	1270.5	1270.5	1270.9	1271.8	1272.7	1273.6	1274.5	1273.6	1272.7	1271.8
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0	2794.0
2.5°	2704.6	2672.0	2639.3	2615.8	2592.3	2563.1	2533.9	2532.8	2531.6	2509.9	2488.1
5°	2544.2	2487.5	2430.8	2375.3	2319.7	2264.1	2208.6	2196.0	2183.4	2164.5	2145.6
7.5°	2402.2	2311.7	2221.2	2150.2	2079.1	2023.6	1968.0	1930.2	1892.4	1863.2	1834.0
10°	2249.8	2137.6	2025.3	1939.4	1853.5	1793.3	1733.2	1689.7	1646.1	1625.5	1604.9
12.5°	2091.7	1969.7	1847.7	1763.5	1679.4	1607.2	1535.0	1495.5	1456.0	1427.3	1398.7
15°	1946.3	1815.1	1683.9	1594.6	1505.2	1437.6	1370.1	1330.5	1291.0	1262.4	1233.7
17.5°	1805.4	1673.1	1540.7	1450.2	1359.7	1298.5	1237.2	1198.8	1160.4	1142.7	1124.9
20°	1677.1	1543.6	1410.2	1324.8	1239.5	1179.3	1119.2	1098.6	1077.9	1061.3	1044.7
22.5°	1549.9	1421.6	1293.3	1211.4	1129.5	1086.0	1042.4	1025.8	1009.2	996.6	984.0
25°	1443.4	1315.6	1187.9	1116.3	1044.7	1010.9	977.1	966.3	955.4	942.8	930.2
27.5°	1335.7	1214.3	1092.8	1035.6	978.3	950.8	923.3	909.6	895.8	885.5	875.2
30°	1240.6	1128.4	1016.1	968.5	921.0	897.0	872.9	858.0	843.1	833.4	823.6
32.5°	1149.0	1049.3	949.6	909.0	868.3	844.8	821.3	807.0	792.7	781.3	769.8
35°	1064.2	977.7	891.2	854.0	816.8	793.3	769.8	755.5	741.2	729.7	718.2
37.5°	989.7	911.3	832.8	797.9	762.9	742.3	721.7	706.8	691.9	679.9	667.8
40°	919.9	850.6	781.3	747.5	713.7	691.3	669.0	655.8	642.6	631.8	620.9
42.5°	858.0	794.4	730.9	697.6	664.4	643.2	622.0	606.6	591.1	584.8	578.5
45°	792.7	736.6	680.4	648.4	616.3	594.0	571.6	558.4	545.3	539.5	533.8
47.5°	735.4	683.3	631.2	599.7	568.2	548.1	528.1	517.8	507.5	499.5	491.4
50°	679.3	628.9	578.5	548.1	517.8	500.6	483.4	470.8	458.2	452.5	446.8
52.5°	625.5	579.6	533.8	502.9	472.0	455.3	438.7	427.9	417.0	404.9	392.9
55°	564.7	524.7	484.6	457.1	429.6	412.4	395.2	382.6	370.0	357.4	344.8
57.5°	514.3	474.8	435.3	410.7	386.0	369.4	352.8	339.1	325.3	315.0	304.7
60°	459.4	425.0	390.6	366.6	342.5	326.5	310.4	297.3	284.1	278.9	273.8
62.5°	407.8	375.7	343.7	322.5	301.3	285.8	270.3	261.8	253.2	249.7	246.3
65°	355.1	327.6	300.1	280.7	261.2	248.0	234.8	230.8	226.8	224.0	221.1
67.5°	305.9	282.4	258.9	241.7	224.5	215.4	206.2	201.6	197.0	193.6	190.2
70°	261.2	240.6	219.9	205.1	190.2	181.6	173.0	169.0	165.0	158.7	152.4
72.5°	213.1	197.0	181.0	169.5	158.1	150.6	143.2	135.2	127.2	121.4	115.7
75°	176.4	160.4	144.3	133.5	122.6	114.0	105.4	102.5	99.7	97.9	96.2
77.5°	135.2	121.4	107.7	99.1	90.5	86.5	82.5	80.8	79.0	78.5	77.9
80°	97.4	85.9	74.5	69.9	65.3	64.1	63.0	61.9	60.7	60.1	59.6
82.5°	60.7	55.0	49.3	48.1	47.0	46.4	45.8	45.2	44.7	44.1	43.5
85°	35.5	33.2	30.9	30.4	29.8	29.2	28.6	28.6	28.6	28.6	28.6
87.5°	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.3	13.7
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.9	25.8	26.7	27.6	28.2
92.5°	35.3	36.7	38.0	39.3	40.7	42.0	42.7	43.3	44.0	44.7	44.8
95°	65.2	66.9	68.7	70.5	72.2	74.0	74.9	75.8	76.7	77.6	78.0
97.5°	101.5	102.7	104.0	105.4	106.7	108.0	109.2	110.3	111.4	112.5	112.9
100°	141.4	142.6	143.7	144.8	145.9	147.1	147.7	148.4	149.1	149.7	150.3
102.5°	183.7	184.8	186.4	188.0	189.5	191.1	191.7	192.4	193.1	193.7	194.0
105°	226.9	228.1	230.1	232.1	234.1	236.1	236.1	236.1	236.1	236.1	236.3
107.5°	278.0	278.5	279.4	280.3	281.2	282.1	282.8	283.4	284.1	284.8	285.0
110°	326.9	327.3	327.8	328.2	328.7	329.1	330.0	330.9	331.8	332.7	332.9



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	376.0	376.1	376.1	376.1	376.1	376.1	377.3	378.4	379.5	380.6	381.1
115°	427.8	427.9	427.5	427.1	426.6	426.2	426.4	426.6	426.8	427.1	427.1
117.5°	477.1	477.0	476.5	476.1	475.6	475.2	475.2	475.2	475.2	475.2	474.8
120°	528.5	528.6	527.5	526.4	525.3	524.2	524.0	523.8	523.5	523.3	523.0
122.5°	575.8	576.0	575.6	575.1	574.7	574.2	573.5	572.9	572.2	571.5	570.9
125°	624.9	625.0	624.6	624.1	623.7	623.2	622.3	621.5	620.6	619.7	618.8
127.5°	673.6	674.0	673.6	673.1	672.7	672.3	670.9	669.6	668.3	666.9	665.8
130°	721.4	721.9	721.3	720.6	719.9	719.3	718.4	717.5	716.6	715.7	714.5
132.5°	767.4	768.1	767.6	767.2	766.7	766.3	765.2	764.1	763.0	761.8	760.7
135°	812.6	813.2	813.0	812.8	812.5	812.3	811.4	810.5	809.6	808.7	808.1
137.5°	854.8	855.7	856.3	857.0	857.7	858.3	857.2	856.1	855.0	853.9	853.0
140°	899.8	900.5	900.7	900.9	901.1	901.3	901.1	900.9	900.7	900.5	899.6
142.5°	940.8	941.6	942.0	942.5	942.9	943.4	943.1	942.9	942.7	942.5	941.8
145°	981.1	981.7	982.4	983.0	983.7	984.4	984.1	983.9	983.7	983.5	982.9
147.5°	1019.9	1020.7	1021.4	1022.1	1022.7	1023.4	1023.4	1023.4	1023.4	1023.4	1022.7
150°	1057.2	1057.6	1058.1	1058.5	1059.0	1059.4	1059.4	1059.4	1059.4	1059.4	1058.7
152.5°	1090.1	1090.5	1090.7	1091.0	1091.2	1091.4	1091.9	1092.3	1092.7	1093.2	1092.9
155°	1121.4	1121.5	1121.8	1122.0	1122.2	1122.4	1123.3	1124.2	1125.1	1126.0	1125.6
157.5°	1149.5	1149.5	1149.8	1150.0	1150.2	1150.4	1151.3	1152.2	1153.1	1154.0	1153.8
160°	1175.7	1175.4	1175.4	1175.4	1175.4	1175.4	1176.6	1177.7	1178.8	1179.9	1180.0
162.5°	1198.8	1198.6	1198.8	1199.0	1199.2	1199.5	1200.6	1201.7	1202.8	1203.9	1203.7
165°	1218.8	1218.5	1218.5	1218.5	1218.5	1218.5	1219.8	1221.1	1222.5	1223.8	1223.7
167.5°	1234.9	1234.6	1234.8	1235.0	1235.2	1235.5	1236.8	1238.1	1239.5	1240.8	1240.8
170°	1248.9	1248.5	1248.5	1248.5	1248.5	1248.5	1250.0	1251.6	1253.1	1254.7	1254.7
172.5°	1259.9	1259.5	1259.5	1259.5	1259.5	1259.5	1260.8	1262.1	1263.5	1264.8	1264.7
175°	1266.9	1266.5	1266.5	1266.5	1266.5	1266.5	1267.8	1269.1	1270.5	1271.8	1271.7
177.5°	1270.9	1270.5	1270.5	1270.5	1270.5	1270.5	1271.8	1273.1	1274.5	1275.8	1275.7
180°	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2794.0	2794.0	2794.0	2794.0
2.5°	2482.4	2476.6	2474.4	2472.1
5°	2127.8	2110.1	2106.1	2102.1
7.5°	1826.6	1819.1	1794.5	1769.8
10°	1582.0	1559.1	1548.8	1538.5
12.5°	1377.5	1356.3	1352.9	1349.4
15°	1218.8	1204.0	1198.8	1193.6
17.5°	1114.6	1104.3	1098.0	1091.7
20°	1037.3	1029.8	1025.3	1020.7
22.5°	978.3	972.6	969.1	965.7
25°	921.6	913.0	910.1	907.3
27.5°	867.7	860.3	857.4	854.6
30°	817.3	811.0	807.0	803.0
32.5°	762.4	754.9	752.6	750.3
35°	713.7	709.1	706.8	704.5
37.5°	662.1	656.4	653.0	649.5
40°	618.0	615.2	613.4	611.7
42.5°	573.3	568.2	567.6	567.0
45°	528.7	523.5	522.4	521.2
47.5°	486.9	482.3	481.7	481.1
50°	440.5	434.2	429.6	425.0
52.5°	387.2	381.5	377.5	373.4
55°	338.5	332.2	328.8	325.3
57.5°	301.8	299.0	297.3	295.5
60°	272.1	270.3	269.2	268.1
62.5°	244.6	242.9	242.9	242.9
65°	219.4	217.7	215.9	214.2
67.5°	186.7	183.3	182.7	182.1
70°	147.2	142.0	141.5	140.9
72.5°	115.1	114.6	113.4	112.3
75°	95.1	93.9	93.9	93.9
77.5°	76.8	75.6	75.6	75.6
80°	59.0	58.4	59.0	59.6
82.5°	43.5	43.5	43.0	42.4
85°	28.1	27.5	27.5	27.5
87.5°	13.7	13.7	13.7	13.7
90°	28.7	29.1	29.6	30.0
92.5°	44.4	43.9	43.5	43.0
95°	78.0	78.0	78.0	78.0
97.5°	112.7	112.5	112.3	112.0
100°	150.7	151.2	151.6	152.1
102.5°	193.7	193.5	193.3	193.1
105°	236.8	237.2	237.6	238.1
107.5°	284.8	284.6	284.3	284.1
110°	332.5	332.0	331.6	331.1



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	381.1	381.1	381.1	381.1
115°	426.8	426.6	426.4	426.2
117.5°	474.2	473.5	472.8	472.2
120°	522.5	522.1	521.6	521.2
122.5°	570.2	569.5	568.9	568.2
125°	617.9	617.0	616.1	615.2
127.5°	664.9	664.0	663.1	662.2
130°	712.9	711.4	709.8	708.3
132.5°	759.6	758.5	757.4	756.3
135°	807.6	807.2	806.7	806.3
137.5°	852.3	851.7	851.0	850.3
140°	898.0	896.4	894.9	893.3
142.5°	940.7	939.6	938.5	937.4
145°	982.0	981.1	980.3	979.4
147.5°	1021.4	1020.1	1018.7	1017.4
150°	1057.4	1056.1	1054.7	1053.4
152.5°	1091.7	1090.6	1089.5	1088.4
155°	1124.1	1122.5	1121.0	1119.4
157.5°	1152.4	1151.1	1149.8	1148.4
160°	1179.1	1178.2	1177.3	1176.4
162.5°	1202.1	1200.6	1199.0	1197.5
165°	1222.1	1220.6	1219.0	1217.5
167.5°	1239.5	1238.1	1236.8	1235.5
170°	1253.1	1251.6	1250.0	1248.5
172.5°	1263.1	1261.6	1260.0	1258.5
175°	1270.1	1268.6	1267.0	1265.5
177.5°	1274.1	1272.6	1271.0	1269.5
180°	1273.5	1273.5	1273.5	1273.5



TEST NUMBER: P831811

CATALOG NUMBER: S123RDIP-S1000D1195U935-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.69	13.50	13.64	14.47	15.73	17.35	18.17	18.31	19.13	20.39
	3H	13.91	14.64	14.88	15.61	16.89	18.85	19.58	19.82	20.55	21.83
	4H	14.29	14.98	15.27	15.96	17.25	19.34	20.03	20.32	21.01	22.30
	6H	14.57	15.20	15.56	16.19	17.49	19.65	20.28	20.64	21.27	22.57
	8H	14.66	15.26	15.66	16.26	17.56	19.73	20.33	20.73	21.33	22.63
	12H	14.71	15.28	15.71	16.27	17.60	19.76	20.33	20.76	21.33	22.65
4H	2H	13.41	14.10	14.40	15.08	16.37	17.34	18.03	18.33	19.01	20.30
	3H	14.78	15.35	15.77	16.36	17.66	19.00	19.57	20.00	20.58	21.88
	4H	15.23	15.75	16.24	16.75	18.08	19.61	20.13	20.61	21.13	22.46
	6H	15.60	16.05	16.61	17.07	18.40	20.04	20.49	21.06	21.52	22.84
	8H	15.72	16.14	16.74	17.16	18.50	20.18	20.59	21.19	21.61	22.95
	12H	15.80	16.18	16.83	17.21	18.55	20.24	20.61	21.27	21.65	22.99
8H	4H	15.54	15.96	16.56	16.98	18.32	19.57	19.99	20.59	21.01	22.35
	6H	16.01	16.35	17.05	17.41	18.75	20.07	20.41	21.11	21.47	22.81
	8H	16.20	16.50	17.25	17.55	18.90	20.26	20.56	21.30	21.60	22.96
	12H	16.34	16.61	17.39	17.65	19.05	20.37	20.64	21.42	21.68	23.08
12H	4H	15.55	15.93	16.59	16.97	18.31	19.52	19.90	20.56	20.93	22.28
	6H	16.07	16.37	17.12	17.42	18.77	20.04	20.35	21.09	21.39	22.75
	8H	16.28	16.55	17.34	17.59	18.99	20.24	20.50	21.29	21.54	22.94