

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331981-940

Luminaire Tested: **S123DIP-S775D805U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331981-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5419.3 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	80	74	72	69	62	60	59	51	50	49	44
2	89	82	76	70	82	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	41	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	68	57	49	43	63	53	46	40	45	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	24	21	18	16
9	50	38	31	25	47	36	29	24	31	26	22	27	22	19	23	19	17	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11689	11689	11689
5°	11743	11581	11662
10°	11664	11481	11552
15°	11529	11352	11373
20°	11369	11165	11176
25°	11156	10946	10923
30°	10920	10700	10618
35°	10674	10441	10306
40°	10418	10153	9997
45°	10135	9893	9651
50°	9851	9568	9302
55°	9481	9233	8955
60°	9104	8844	8564
65°	8777	8420	8155
70°	8286	7934	7582
75°	7573	7303	6991
80°	6831	6540	6484
85°	5990	5768	5545



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	1.9
10°-20°	288.8	5.3
20°-30°	426.6	7.9
30°-40°	498.4	9.2
40°-50°	501.0	9.2
50°-60°	440.1	8.1
60°-70°	327.9	6.1
70°-80°	186.8	3.4
80°-90°	56.3	1.0
90°-100°	191.7	3.5
100°-110°	542.7	10.0
110°-120°	533.9	9.9
120°-130°	425.8	7.9
130°-140°	335.7	6.2
140°-150°	250.6	4.6
150°-160°	174.7	3.2
160°-170°	102.6	1.9
170°-180°	33.4	0.6
0°-30°	817.7	15.1
0°-40°	1316.1	24.3
0°-60°	2257.3	41.7
0°-90°	2828.2	52.2
90°-120°	1268.2	23.4
90°-150°	2280.4	42.1
90°-180°	2591.0	47.8
0°-180°	5419.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1086	1086	1086	1086	1086	
5°	1087	1082	1072	1081	1079	103
15°	1035	1030	1019	1025	1021	292
25°	939	933	922	922	920	432
35°	812	806	795	789	784	508
45°	666	662	650	639	634	514
55°	505	504	492	482	477	452
65°	345	340	331	323	320	340
75°	182	178	176	171	168	195
85°	48	47	47	45	45	53
90°	1	8	17	20	20	4
95°	24	77	413	121	81	26
105°	81	120	560	980	887	86
115°	143	178	429	940	1078	141
125°	199	235	400	725	850	176
135°	233	278	395	597	690	180
145°	266	304	390	490	539	166
155°	302	326	377	429	447	139
165°	330	339	361	383	390	93
175°	344	344	346	351	351	33
180°	344	344	344	344	344	



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1089.6	1089.0	1088.3	1087.6	1087.0	1085.7	1083.9	1082.1	1080.2	1078.4	1080.0
5°	1086.8	1085.7	1084.8	1083.7	1082.6	1081.0	1078.7	1076.5	1074.2	1071.8	1074.0
7.5°	1076.2	1075.1	1074.1	1073.1	1072.0	1070.3	1067.9	1065.6	1063.2	1060.9	1062.7
10°	1067.2	1066.1	1065.1	1064.1	1063.1	1061.2	1058.5	1055.8	1053.1	1050.4	1052.3
12.5°	1055.3	1054.4	1053.6	1052.7	1051.8	1050.1	1047.6	1045.0	1042.5	1039.9	1041.3
15°	1034.6	1033.7	1032.9	1032.1	1031.2	1029.5	1026.7	1024.0	1021.4	1018.7	1020.3
17.5°	1010.4	1009.3	1008.3	1007.2	1006.1	1004.2	1001.6	998.8	996.1	993.5	994.6
20°	992.5	991.2	990.1	988.8	987.6	985.5	982.8	980.2	977.5	974.7	975.6
22.5°	972.3	971.1	969.8	968.6	967.3	965.4	962.7	960.0	957.3	954.6	955.3
25°	939.3	938.1	936.8	935.6	934.3	932.4	929.6	926.9	924.3	921.6	921.8
27.5°	904.0	902.8	901.6	900.4	899.2	897.2	894.2	891.4	888.4	885.5	885.6
30°	878.6	877.5	876.6	875.5	874.4	872.4	869.6	866.7	863.8	860.9	860.9
32.5°	853.2	851.9	850.4	849.1	847.7	846.0	843.6	841.4	839.2	837.0	835.8
35°	812.3	811.1	809.9	808.6	807.4	805.4	802.6	800.0	797.3	794.6	793.4
37.5°	770.4	768.9	767.3	765.7	764.2	762.1	759.3	756.5	753.8	751.1	749.6
40°	741.4	740.1	738.9	737.6	736.4	734.3	731.4	728.5	725.6	722.6	721.0
42.5°	712.2	710.8	709.4	708.0	706.6	704.5	701.5	698.6	695.7	692.8	691.2
45°	665.8	664.9	664.1	663.3	662.4	660.7	657.9	655.2	652.6	649.9	647.4
47.5°	619.6	618.4	617.2	616.0	614.7	612.9	610.4	607.9	605.3	602.8	600.3
50°	588.3	587.2	586.1	585.1	584.1	582.2	579.5	576.8	574.1	571.4	569.2
52.5°	555.4	554.6	553.9	553.2	552.5	550.7	547.9	545.0	542.2	539.3	537.3
55°	505.2	504.9	504.7	504.5	504.3	502.8	500.2	497.5	494.7	492.0	489.8
57.5°	457.4	456.6	455.9	455.2	454.5	453.1	450.9	448.7	446.6	444.4	442.4
60°	422.9	422.8	422.6	422.3	422.1	420.8	418.3	415.8	413.3	410.8	408.9
62.5°	392.4	391.8	391.3	390.7	390.2	388.7	386.2	383.7	381.2	378.7	376.8
65°	344.6	343.5	342.4	341.4	340.4	338.9	336.7	334.7	332.6	330.6	328.9
67.5°	293.9	293.0	292.1	291.1	290.3	289.0	287.5	285.9	284.3	282.8	281.2
70°	263.3	262.1	260.8	259.6	258.3	257.1	255.8	254.6	253.3	252.1	250.7
72.5°	231.2	230.2	229.3	228.5	227.6	226.4	225.0	223.6	222.1	220.7	219.5
75°	182.1	181.2	180.4	179.6	178.8	178.0	177.4	176.7	176.1	175.6	174.5
77.5°	138.6	138.1	137.7	137.2	136.7	136.2	135.4	134.6	133.9	133.1	132.4
80°	110.2	109.6	109.0	108.3	107.7	107.2	106.7	106.4	105.9	105.5	105.3
82.5°	82.6	82.4	82.3	82.1	82.0	81.9	81.9	81.8	81.7	81.6	81.2
85°	48.5	48.2	47.7	47.3	46.9	46.7	46.7	46.7	46.7	46.7	46.3
87.5°	19.7	19.4	19.3	19.2	19.0	18.9	19.2	19.4	19.7	19.9	19.6
90°	1.4	2.8	4.2	6.2	7.7	9.1	11.1	13.3	15.3	17.4	16.8
92.5°	8.6	12.8	18.7	24.2	30.0	40.3	58.6	88.5	118.0	107.2	80.9
95°	23.7	25.8	33.4	45.3	63.4	90.6	149.9	253.8	368.1	413.4	335.4
97.5°	40.4	41.1	47.2	57.4	75.3	104.7	161.3	278.5	469.0	640.7	685.5
100°	51.6	52.3	57.2	67.0	83.6	110.8	159.6	262.8	446.2	660.2	797.5
102.5°	63.3	64.6	68.8	78.1	93.2	118.1	161.8	249.4	412.7	623.9	803.2
105°	80.9	82.9	87.1	95.5	108.8	130.4	168.0	239.8	371.6	560.5	760.6
107.5°	99.5	101.7	105.7	113.9	126.4	146.4	179.4	239.2	345.4	504.4	686.2
110°	113.0	115.0	118.5	126.2	138.0	157.6	189.0	241.9	335.4	472.7	639.3



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	125.2	127.3	130.8	138.5	150.3	169.2	198.4	247.4	329.8	451.5	598.6
115°	142.9	145.7	149.9	156.9	168.7	187.5	214.0	256.5	327.7	428.7	549.4
117.5°	160.6	163.8	167.3	173.7	187.0	204.4	230.6	268.6	329.0	415.4	519.7
120°	172.9	175.0	178.4	185.5	198.7	216.2	241.2	277.5	331.2	409.2	504.1
122.5°	183.5	185.6	189.0	196.6	209.3	227.8	252.4	285.8	335.0	405.4	491.2
125°	198.7	200.1	204.3	212.0	225.2	244.0	268.4	299.1	340.9	400.2	474.7
127.5°	210.3	212.3	217.5	225.3	240.0	258.8	282.3	310.0	347.6	397.7	460.3
130°	217.5	219.6	225.9	234.3	248.9	267.7	290.7	317.2	352.0	396.0	452.5
132.5°	223.1	225.8	232.6	242.6	257.3	275.5	297.9	323.9	355.4	395.4	445.2
135°	232.8	235.7	243.3	253.8	268.4	287.2	308.8	332.5	360.4	394.6	435.7
137.5°	242.0	245.0	252.5	263.7	278.1	295.6	316.4	338.9	363.8	393.1	427.5
140°	248.2	251.6	258.7	269.8	283.7	301.1	321.4	342.3	366.0	392.5	422.5
142.5°	254.9	257.8	265.4	275.4	289.4	305.6	325.3	345.6	367.7	391.4	418.0
145°	265.6	267.7	274.0	284.5	296.3	312.4	330.5	349.3	368.8	389.7	412.1
147.5°	276.5	277.8	283.9	292.9	304.3	318.1	334.7	351.5	368.8	387.1	406.2
150°	283.7	284.5	290.0	299.1	308.8	321.4	337.4	352.0	368.8	384.9	402.3
152.5°	291.0	291.1	296.7	304.7	313.3	325.3	339.1	353.2	367.1	382.0	397.8
155°	301.8	301.8	306.0	313.0	320.7	330.5	342.3	353.5	365.3	377.2	391.1
157.5°	310.5	311.0	314.4	320.6	327.1	334.7	344.1	354.2	362.9	372.8	383.6
160°	317.2	317.2	320.0	325.6	330.5	337.4	345.8	354.2	361.9	369.5	378.5
162.5°	322.3	322.3	324.5	329.0	333.2	339.1	346.3	353.6	359.6	366.1	373.5
165°	329.8	329.0	330.5	333.9	336.7	341.6	347.1	352.0	356.2	361.1	366.7
167.5°	335.5	334.7	335.4	338.0	339.9	343.0	347.1	351.0	352.9	356.1	360.2
170°	338.9	337.4	338.1	340.2	341.6	343.0	346.5	349.3	350.7	352.8	356.2
172.5°	341.1	340.2	340.4	341.9	342.7	343.6	346.5	348.7	349.0	350.0	352.3
175°	343.7	343.0	342.3	343.7	343.7	344.4	345.8	347.1	346.5	346.5	347.9
177.5°	344.9	344.4	343.8	344.4	344.4	344.4	344.9	346.1	344.9	344.4	344.9
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9	1085.9
2.5°	1081.7	1083.4	1085.0	1085.8	1085.7	1085.5	1085.3	1085.1
5°	1076.0	1078.1	1080.2	1081.0	1080.6	1080.2	1079.8	1079.3
7.5°	1064.6	1066.5	1068.4	1069.2	1068.9	1068.6	1068.4	1068.2
10°	1054.2	1056.0	1057.8	1058.6	1058.2	1057.7	1057.4	1056.9
12.5°	1042.7	1044.0	1045.4	1046.0	1045.7	1045.4	1045.3	1045.0
15°	1022.0	1023.6	1025.3	1025.5	1024.2	1023.0	1021.8	1020.6
17.5°	995.8	996.9	998.1	998.4	998.0	997.6	997.1	996.7
20°	976.4	977.2	978.1	978.2	977.6	977.0	976.3	975.7
22.5°	955.9	956.6	957.3	957.2	956.4	955.6	954.8	954.0
25°	921.9	922.2	922.4	922.2	921.6	921.0	920.3	919.7
27.5°	885.8	886.0	886.2	885.8	885.1	884.3	883.5	882.7
30°	860.9	860.9	860.9	860.1	858.7	857.2	855.8	854.3
32.5°	834.6	833.5	832.3	831.3	830.5	829.7	828.9	828.2
35°	792.1	790.9	789.6	788.5	787.4	786.4	785.3	784.3
37.5°	748.1	746.5	745.1	744.0	743.3	742.7	742.0	741.4
40°	719.3	717.7	716.0	714.8	714.0	713.1	712.3	711.5
42.5°	689.5	687.8	686.2	684.9	684.1	683.2	682.4	681.6
45°	644.9	642.4	639.9	638.1	637.1	636.1	635.0	634.0
47.5°	597.9	595.5	593.0	591.3	590.4	589.5	588.6	587.6
50°	566.9	564.5	562.3	560.5	559.3	558.0	556.8	555.5
52.5°	535.4	533.4	531.5	529.9	528.7	527.4	526.2	525.0
55°	487.5	485.2	483.0	481.3	480.2	479.2	478.1	477.2
57.5°	440.3	438.4	436.3	434.7	433.5	432.3	431.1	429.9
60°	407.1	405.2	403.3	401.9	400.8	399.8	398.8	397.8
62.5°	375.0	373.1	371.2	370.0	369.3	368.5	367.8	367.1
65°	327.2	325.6	323.9	322.7	322.1	321.5	320.8	320.2
67.5°	279.8	278.4	276.9	275.7	274.9	274.0	273.1	272.2
70°	249.2	247.7	246.3	245.0	244.0	243.0	241.9	240.9
72.5°	218.1	216.9	215.6	214.6	214.1	213.6	213.0	212.5
75°	173.4	172.5	171.4	170.6	170.0	169.3	168.7	168.1
77.5°	131.7	131.0	130.3	130.0	130.0	130.0	130.0	130.0
80°	105.1	104.9	104.7	104.6	104.6	104.6	104.6	104.6
82.5°	80.9	80.5	80.1	79.8	79.7	79.5	79.4	79.2
85°	45.8	45.5	45.0	44.9	44.9	44.9	44.9	44.9
87.5°	19.6	19.5	19.5	19.7	19.6	19.7	19.9	19.7
90°	17.4	18.1	18.8	20.2	19.5	20.2	21.0	20.2
92.5°	58.7	46.5	41.1	37.5	36.3	34.2	34.9	33.6
95°	251.0	170.1	133.1	108.1	94.8	88.5	83.6	80.9
97.5°	625.6	501.1	411.2	327.8	276.3	245.0	226.1	220.2
100°	822.0	765.4	683.9	584.9	514.5	463.6	436.4	437.1
102.5°	887.2	885.4	837.9	775.1	720.3	680.0	657.3	641.2
105°	906.3	976.0	989.3	971.2	939.1	912.6	890.3	886.8
107.5°	851.4	964.6	1025.6	1050.4	1051.1	1042.1	1034.6	1028.1
110°	799.0	927.2	1015.0	1063.9	1083.3	1089.0	1087.5	1086.2



TEST NUMBER: P331981-940

CATALOG NUMBER: S123DIP-S775D805U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	747.1	878.2	976.6	1039.3	1075.0	1092.3	1097.6	1097.9
115°	678.3	799.6	902.1	978.1	1030.4	1061.0	1075.0	1078.5
117.5°	628.6	733.3	825.3	902.4	956.9	992.0	1012.1	1016.9
120°	602.4	696.4	780.2	850.5	905.6	944.7	961.4	965.5
122.5°	581.8	666.9	744.4	809.9	858.7	893.9	912.3	917.6
125°	554.2	630.3	697.1	753.0	797.5	828.2	845.6	850.5
127.5°	530.3	598.0	658.4	709.2	748.9	775.1	790.9	795.3
130°	515.2	577.9	634.5	681.8	718.8	743.9	758.5	764.1
132.5°	501.2	559.0	611.5	656.7	691.4	716.6	729.5	733.4
135°	482.4	531.9	577.2	617.0	651.1	672.1	684.6	689.5
137.5°	465.3	505.9	544.9	579.3	608.1	629.3	639.9	643.1
140°	455.2	490.8	524.2	554.2	580.8	600.2	611.4	610.7
142.5°	445.8	476.3	505.3	531.4	553.9	571.2	581.3	580.6
145°	434.4	457.4	479.7	499.9	517.3	531.9	537.5	538.9
147.5°	425.0	443.3	461.3	475.6	488.8	498.7	504.1	504.6
150°	418.3	434.4	449.0	462.2	472.7	480.4	484.6	484.6
152.5°	412.1	426.0	438.9	450.0	458.2	465.3	467.8	467.8
155°	403.0	414.1	424.5	432.9	439.2	444.8	446.2	446.8
157.5°	393.2	402.5	410.6	417.1	422.6	426.8	427.9	427.8
160°	387.6	395.3	402.3	407.2	412.1	416.2	416.2	415.5
162.5°	380.9	387.4	393.9	398.2	401.4	405.0	405.0	404.4
165°	372.3	376.5	381.4	384.9	387.6	390.4	389.7	389.7
167.5°	364.7	367.9	370.8	373.3	374.5	376.5	375.8	375.8
170°	359.7	361.9	364.6	366.0	366.7	368.1	367.4	367.4
172.5°	355.3	356.8	359.0	359.9	360.0	361.4	360.2	359.6
175°	349.3	350.0	351.3	351.3	351.3	352.0	351.3	350.7
177.5°	345.5	346.1	346.6	346.6	346.1	346.6	345.5	345.5
180°	344.4	344.4	344.4	344.4	344.4	344.4	344.4	344.4

(END OF REPORT)