

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332384-935

Luminaire Tested: **S123RDIP-S1165D1195U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P332384-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8045.7 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	44	43	41	36
3	82	73	66	61	76	68	62	57	58	53	50	48	45	42	40	38	36	32
4	76	65	58	52	69	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	58	50	45	64	54	47	42	47	41	37	39	35	32	33	30	27	24
6	64	53	45	39	59	49	42	37	42	37	33	36	32	28	30	27	24	22
7	59	48	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17016	17016	17016	17016
5°	20283	17088	15048	17088
10°	25326	16990	13595	16990
15°	29727	16817	12397	16817
20°	33176	16557	11379	16557
25°	32647	16284	10753	16284
30°	23467	16032	10110	16032
35°	15669	15704	9692	15704
40°	11545	15309	9261	15309
45°	9683	14618	8840	14618
50°	8544	13711	8251	13711
55°	7492	12675	7443	12675
60°	6674	11683	6818	11683
65°	5861	10618	6342	10618
70°	4601	9668	5794	9668
75°	4055	8442	5294	8442
80°	3521	7172	5201	7172
85°	2841	5768	5521	5768



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	1.9
10°-20°	485.7	6.0
20°-30°	763.0	9.5
30°-40°	796.1	9.9
40°-50°	681.2	8.5
50°-60°	519.2	6.5
60°-70°	332.8	4.1
70°-80°	160.1	2.0
80°-90°	46.1	0.6
90°-100°	48.9	0.6
100°-110°	233.3	2.9
110°-120°	560.4	7.0
120°-130°	713.6	8.9
130°-140°	762.5	9.5
140°-150°	713.0	8.9
150°-160°	575.1	7.1
160°-170°	371.2	4.6
170°-180°	127.9	1.6
0°-30°	1404.1	17.5
0°-40°	2200.2	27.3
0°-60°	3400.7	42.3
0°-90°	3939.7	49.0
90°-120°	842.6	10.5
90°-150°	3031.7	37.7
90°-180°	4106.0	51.0
0°-180°	8045.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1877	1582	1393	1582	1877	194
15°	2668	1509	1112	1509	2668	756
25°	2749	1371	905	1371	2749	1181
35°	1192	1195	738	1195	1192	782
45°	636	960	581	960	636	500
55°	399	675	397	675	399	361
65°	230	417	249	417	230	226
75°	98	203	127	203	98	105
85°	23	47	45	47	23	27
90°	30	1	30	1	30	14
95°	38	61	38	61	38	32
105°	44	298	44	298	44	101
115°	588	559	588	559	588	543
125°	804	788	804	788	804	718
135°	991	981	991	981	991	764
145°	1143	1132	1143	1132	1143	714
155°	1245	1247	1245	1247	1245	574
165°	1312	1315	1312	1315	1312	371
175°	1341	1346	1341	1346	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1683.7	1685.8	1678.8	1677.7	1669.6	1667.4	1667.4	1656.0	1649.0	1639.9	1634.4
5°	1877.2	1888.1	1882.7	1870.4	1850.1	1845.4	1832.6	1812.2	1789.2	1760.8	1747.3
7.5°	2118.9	2133.7	2128.0	2109.2	2087.9	2070.8	2034.5	2000.8	1953.5	1912.1	1876.6
10°	2317.1	2301.5	2289.3	2271.1	2251.4	2219.7	2181.8	2129.6	2069.4	2022.1	1969.3
12.5°	2465.4	2462.9	2447.4	2428.6	2400.9	2370.7	2324.1	2260.6	2190.6	2122.2	2061.8
15°	2667.6	2671.7	2661.5	2641.9	2602.6	2549.2	2478.8	2452.5	2352.3	2277.9	2203.4
17.5°	2807.5	2806.8	2805.4	2778.2	2738.2	2700.1	2634.8	2565.4	2474.8	2369.9	2269.6
20°	2896.3	2889.6	2891.0	2860.5	2830.7	2786.7	2723.1	2622.3	2547.9	2426.7	2323.2
22.5°	2894.2	2892.9	2898.0	2887.5	2865.9	2832.2	2782.1	2697.0	2602.0	2479.8	2363.3
25°	2748.8	2743.4	2775.3	2784.0	2818.6	2824.6	2809.7	2763.0	2673.1	2547.2	2403.1
27.5°	2300.6	2297.6	2356.6	2430.5	2524.2	2596.9	2667.4	2701.3	2673.1	2582.9	2438.5
30°	1888.1	1951.6	1981.4	2088.4	2207.4	2349.6	2474.1	2592.5	2621.6	2582.4	2463.9
32.5°	1567.5	1623.1	1648.0	1739.7	1850.7	2017.2	2203.9	2371.6	2490.1	2520.1	2448.8
35°	1192.4	1193.1	1249.9	1290.5	1393.4	1564.6	1745.9	1970.6	2193.9	2363.1	2380.7
37.5°	951.5	954.8	989.2	1029.7	1106.8	1197.4	1357.1	1543.9	1801.8	2061.6	2213.8
40°	821.6	827.6	853.3	893.3	948.7	1017.1	1141.6	1317.6	1532.8	1821.7	2057.9
42.5°	738.1	748.0	761.3	792.0	826.4	890.4	991.1	1127.0	1322.8	1595.9	1868.5
45°	636.1	641.5	651.7	665.9	697.0	741.7	809.3	900.7	1063.2	1283.1	1555.7
47.5°	561.1	558.3	568.9	580.5	601.2	631.6	677.0	751.6	867.5	1043.9	1275.2
50°	510.2	509.5	517.0	525.8	545.4	567.7	605.0	661.2	753.2	899.4	1111.2
52.5°	462.6	465.2	470.5	481.4	495.6	513.7	547.1	587.5	666.6	792.7	969.3
55°	399.2	401.3	408.7	414.8	425.0	443.2	464.3	498.1	552.2	640.2	785.7
57.5°	345.7	344.7	351.9	353.4	364.9	379.8	396.0	422.2	461.5	526.9	624.9
60°	310.0	307.9	314.0	318.7	324.9	337.0	350.5	376.3	407.4	455.5	539.3
62.5°	277.4	276.5	280.9	285.7	290.8	301.8	313.1	332.9	357.6	398.0	464.6
65°	230.1	232.1	234.1	236.2	238.8	245.6	256.5	270.0	287.0	315.4	363.4
67.5°	180.8	182.9	183.6	187.7	193.6	197.8	204.4	216.5	228.2	252.2	279.5
70°	146.2	145.5	146.2	148.2	155.7	163.1	171.9	180.7	188.1	205.0	228.1
72.5°	125.6	124.4	126.1	126.6	130.2	132.2	137.8	146.0	155.7	167.1	183.7
75°	97.5	97.5	97.5	97.5	100.1	101.5	103.6	105.6	108.9	114.3	126.6
77.5°	72.0	72.2	73.1	73.8	74.3	75.1	76.4	78.4	79.6	82.4	87.7
80°	56.8	57.5	56.8	57.5	57.5	58.9	59.6	61.6	62.3	65.6	67.7
82.5°	42.8	42.4	42.8	43.5	43.5	44.8	44.9	46.4	46.6	48.3	50.4
85°	23.0	21.7	23.0	22.3	23.7	22.3	23.0	24.4	24.4	25.1	27.7
87.5°	11.5	12.4	11.3	11.7	11.6	12.0	11.8	11.6	12.6	11.9	11.8
90°	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7	24.9	24.0	21.1
92.5°	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4	27.0	25.6	23.4
95°	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1	32.5	31.0	28.6
97.5°	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7	34.0	32.2	48.2
100°	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6	34.8	33.0	67.7
102.5°	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8	60.3	65.8	103.7
105°	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3	179.7	219.0	239.1
107.5°	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8	372.6	401.6	398.4
110°	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4	443.8	451.2	448.7



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8	501.7	501.5	499.1
115°	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6	576.4	574.2	572.2
117.5°	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2	646.4	644.6	643.6
120°	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8	692.0	690.2	689.6
122.5°	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3	737.1	735.8	734.9
125°	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2	800.7	800.2	799.4
127.5°	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1	863.4	862.6	861.6
130°	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1	901.2	900.3	899.4
132.5°	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1	937.2	936.3	935.6
135°	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4	990.4
137.5°	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3	1040.2	1039.1	1038.6
140°	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1	1071.3	1070.3	1069.7
142.5°	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4	1100.7	1099.9	1099.3
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3	1141.8	1141.3	1140.9
147.5°	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9	1178.5	1177.9	1177.5
150°	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3	1200.8	1200.4	1200.0
152.5°	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2	1220.4	1219.6	1219.3
155°	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6	1247.5	1246.4	1246.2
157.5°	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5	1271.2	1269.8	1270.1
160°	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1	1284.8	1283.4	1283.7
162.5°	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5	1296.9	1295.4	1295.6
165°	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0	1313.2	1311.4	1311.6
167.5°	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2	1324.2
170°	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5	1331.5
172.5°	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8	1338.0	1336.2	1336.0
175°	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6	1344.0	1342.4	1342.2
177.5°	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6	1346.3	1344.8	1344.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1632.3	1630.6	1623.1	1614.4	1603.0	1595.4	1589.5	1586.2	1576.5	1564.6	1556.4
5°	1733.1	1712.8	1691.1	1664.7	1640.4	1615.3	1599.7	1581.5	1559.2	1534.1	1516.6
7.5°	1841.1	1801.3	1758.4	1714.2	1670.4	1631.2	1596.6	1566.8	1531.3	1495.4	1470.2
10°	1923.9	1865.7	1805.5	1743.9	1687.7	1635.0	1594.3	1554.4	1511.8	1470.5	1439.4
12.5°	1999.2	1922.5	1853.1	1777.4	1705.6	1642.5	1584.1	1537.1	1485.8	1441.8	1406.4
15°	2094.5	2015.9	1932.0	1817.0	1721.6	1641.8	1570.6	1509.1	1446.8	1392.7	1358.1
17.5°	2183.5	2065.4	1952.6	1856.7	1732.7	1632.9	1546.2	1472.6	1404.2	1346.8	1304.3
20°	2220.3	2105.9	1983.5	1861.0	1739.1	1627.5	1526.6	1445.4	1374.4	1309.4	1270.2
22.5°	2242.5	2113.0	1984.0	1852.4	1722.9	1607.0	1507.2	1417.9	1340.8	1279.1	1230.7
25°	2268.4	2114.1	1971.9	1842.0	1710.0	1584.2	1465.8	1371.1	1287.8	1222.2	1170.7
27.5°	2285.4	2103.9	1936.0	1791.6	1657.7	1532.3	1423.8	1323.4	1239.0	1169.5	1114.3
30°	2288.6	2095.8	1908.3	1752.0	1616.0	1501.0	1386.0	1289.9	1200.5	1126.7	1075.3
32.5°	2293.0	2075.8	1871.0	1705.0	1565.6	1451.7	1347.5	1255.7	1164.2	1091.6	1039.1
35°	2275.1	2064.7	1814.3	1623.4	1484.0	1373.7	1279.7	1195.1	1105.1	1034.7	981.3
37.5°	2198.2	2020.7	1755.6	1531.7	1386.0	1283.8	1207.1	1133.3	1050.9	974.9	924.5
40°	2120.8	1977.4	1710.0	1475.9	1323.7	1218.7	1149.8	1089.5	1009.7	938.6	884.5
42.5°	2005.5	1918.4	1666.7	1417.5	1253.3	1152.2	1094.0	1037.5	967.4	895.3	844.4
45°	1794.0	1805.5	1578.1	1324.3	1155.8	1054.3	999.5	960.3	898.0	838.4	786.4
47.5°	1528.7	1636.3	1474.0	1225.1	1053.1	957.9	909.9	875.6	833.7	775.2	727.7
50°	1355.5	1509.1	1390.7	1158.6	988.7	894.0	846.5	818.8	782.3	736.2	691.0
52.5°	1195.8	1360.7	1290.0	1084.3	918.9	832.2	785.9	763.1	734.1	690.8	649.8
55°	975.2	1142.3	1126.1	972.4	814.1	736.2	701.1	675.4	655.7	623.3	590.8
57.5°	788.8	947.3	955.6	847.9	721.8	644.9	614.6	595.2	582.4	557.9	527.9
60°	671.3	816.8	845.2	764.1	655.7	588.1	558.3	542.7	532.6	513.0	489.9
62.5°	573.9	697.7	729.9	671.4	592.4	529.1	505.8	490.8	483.9	466.9	446.6
65°	439.2	542.1	573.2	540.7	499.4	448.7	429.7	416.9	410.8	401.3	386.4
67.5°	330.3	405.2	439.4	416.5	401.6	369.5	357.4	350.5	345.1	338.6	326.1
70°	265.3	320.7	355.9	349.8	337.7	320.7	311.9	307.2	301.8	296.4	285.6
72.5°	213.3	251.5	284.5	287.6	277.6	274.2	266.5	264.5	261.2	254.7	248.7
75°	141.5	167.8	190.8	199.7	203.7	207.1	203.7	203.0	202.3	196.9	193.6
77.5°	92.7	106.9	121.4	136.5	142.8	147.4	148.4	150.9	149.1	146.3	144.6
80°	71.0	74.5	84.6	97.5	107.6	111.7	114.3	115.7	115.0	114.3	111.7
82.5°	51.6	54.4	59.2	68.2	76.7	83.5	85.2	84.9	86.4	86.8	84.6
85°	27.7	28.4	29.8	31.2	35.9	43.3	45.4	46.7	48.0	48.0	44.0
87.5°	12.3	11.2	11.7	11.2	12.4	12.5	15.2	17.6	18.5	16.8	17.2
90°	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6	18.0	17.4	16.7
95°	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0	51.9	42.8	33.7
97.5°	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6	118.6	114.4	110.4
100°	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0	173.5	178.0	182.4
102.5°	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9	225.1	228.3	231.4
105°	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1	300.6	303.0	305.4
107.5°	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5	380.5	382.5	384.4
110°	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1	433.9	435.7	437.5



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4	484.9	486.6	488.2
115°	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2	560.5	561.8	563.2
117.5°	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6	634.2	635.8	637.6
120°	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2	680.2	682.3	684.2
122.5°	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6	726.3	727.9	729.5
125°	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2	790.1	791.8	793.6
127.5°	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9	851.6	853.4	855.2
130°	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3	890.1	891.8	893.6
132.5°	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1	926.9	928.7	930.4
135°	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3	982.7	984.0	985.3
137.5°	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3	1031.0	1032.7	1034.4
140°	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4	1062.6	1064.0	1065.3
142.5°	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0	1092.3	1093.6	1094.9
145°	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4	1133.9	1135.5	1137.0
147.5°	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4	1172.4	1173.5	1174.4
150°	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4	1196.0	1196.7	1197.4
152.5°	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0	1217.3	1217.6	1217.9
155°	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4	1247.0	1246.5	1246.0
157.5°	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0	1270.9	1270.9	1270.8
160°	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4	1285.2	1285.0	1284.8
162.5°	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0	1298.5	1297.9	1297.3
165°	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4	1314.7	1314.1	1313.5
167.5°	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3	1327.3	1326.5	1325.6
170°	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4	1334.6	1333.7	1332.7
172.5°	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2	1339.2	1338.1	1337.0
175°	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4	1345.3	1344.2	1343.1
177.5°	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1	1347.1	1346.3	1345.4
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1553.8	1546.7	1541.9	1531.0	1524.0	1516.4	1508.8	1513.7	1513.1	1512.6	1512.6
5°	1501.7	1486.1	1471.9	1453.6	1442.1	1427.9	1417.0	1415.7	1418.4	1408.9	1403.5
7.5°	1449.9	1428.7	1408.5	1388.4	1367.0	1350.0	1339.2	1334.2	1327.3	1321.5	1315.4
10°	1413.7	1388.6	1369.0	1343.9	1320.9	1300.6	1287.8	1279.0	1274.3	1269.5	1260.8
12.5°	1376.3	1351.9	1326.8	1298.5	1276.6	1253.0	1243.4	1233.6	1224.4	1219.2	1207.1
15°	1321.6	1289.9	1263.4	1233.6	1209.3	1186.3	1172.8	1153.1	1150.4	1143.7	1131.4
17.5°	1266.8	1232.3	1195.9	1173.8	1146.3	1122.4	1101.8	1095.2	1075.8	1068.5	1058.0
20°	1223.5	1191.7	1164.0	1134.9	1094.9	1072.6	1056.4	1047.6	1032.0	1022.5	1015.7
22.5°	1186.1	1153.8	1121.7	1087.8	1054.9	1029.8	1018.0	1004.3	995.7	982.5	975.2
25°	1132.8	1097.6	1059.0	1022.5	998.8	979.9	961.0	948.7	936.6	930.5	917.0
27.5°	1070.8	1034.1	998.0	970.3	941.2	922.5	905.3	894.5	879.9	869.6	862.1
30°	1036.7	993.4	962.3	937.3	900.0	882.4	869.6	856.1	845.2	834.4	827.0
32.5°	997.2	957.7	928.2	897.2	868.7	849.4	832.8	820.9	811.7	801.3	793.9
35°	935.2	902.1	871.6	840.5	819.5	799.9	780.2	770.1	761.3	751.8	745.1
37.5°	879.2	848.2	819.2	789.7	763.7	747.8	731.9	724.2	712.3	705.9	699.0
40°	844.6	814.1	783.0	754.6	727.5	715.3	701.1	689.6	678.7	674.0	666.6
42.5°	806.7	776.2	749.9	719.4	697.2	680.6	667.5	655.0	646.8	639.9	635.7
45°	750.4	723.4	697.7	667.3	646.3	632.1	617.2	605.6	598.2	593.5	586.0
47.5°	695.9	668.9	642.7	616.2	595.9	579.7	564.8	556.8	546.9	541.1	536.1
50°	656.4	632.1	604.3	580.0	559.6	543.4	531.2	521.1	512.3	504.8	501.4
52.5°	620.2	594.2	570.2	547.4	526.1	507.6	496.5	485.9	479.2	470.7	466.8
55°	560.3	535.3	515.0	492.7	471.7	456.1	442.6	433.1	426.4	416.9	411.5
57.5°	504.1	481.7	457.4	438.1	416.5	403.3	392.1	379.3	371.0	363.5	358.3
60°	466.2	440.6	419.6	401.3	382.4	365.4	355.2	345.1	336.3	328.9	324.2
62.5°	426.7	404.2	384.4	364.5	347.2	332.4	320.6	312.1	304.4	299.6	294.9
65°	366.1	348.5	328.2	311.9	295.8	284.9	275.4	267.9	262.6	259.2	255.1
67.5°	310.3	293.3	275.5	259.6	248.7	240.5	234.3	227.9	225.2	220.8	218.2
70°	274.1	256.5	240.9	228.8	217.9	211.8	207.8	203.0	200.3	194.9	192.2
72.5°	234.5	221.8	210.6	200.6	191.9	186.4	181.2	175.4	171.1	165.1	162.4
75°	184.8	173.2	164.5	157.6	152.2	144.8	137.4	131.3	129.2	127.3	126.6
77.5°	136.8	129.5	123.1	117.4	110.7	105.3	103.7	102.3	101.9	100.8	100.8
80°	107.6	100.8	96.1	89.3	85.2	85.2	85.2	83.9	84.6	84.6	84.6
82.5°	80.0	73.8	71.2	68.8	67.9	68.4	68.4	68.8	68.4	69.4	68.9
85°	41.2	41.9	43.3	42.6	43.3	43.3	44.7	44.0	44.7	43.3	44.7
87.5°	17.1	19.3	20.4	21.5	22.6	22.6	23.4	23.6	24.3	24.5	24.6
90°	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7	26.7	27.6	28.2
92.5°	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4	29.9	31.3	32.1
95°	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1	35.6	37.2	38.0
97.5°	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7	37.5	39.3	40.3
100°	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6	38.3	40.1	41.2
102.5°	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8	49.2	43.7	41.2
105°	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3	101.0	61.6	42.3
107.5°	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8	315.0	286.1	256.8
110°	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4	429.1	421.8	402.3



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8	502.0	502.1	498.8
115°	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6	580.8	583.1	584.6
117.5°	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2	650.0	651.7	652.7
120°	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8	695.5	697.3	698.2
122.5°	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3	739.6	740.8	741.5
125°	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2	801.6	802.0	802.5
127.5°	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1	864.8	865.5	865.6
130°	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1	902.9	903.9	904.0
132.5°	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1	939.0	939.9	940.0
135°	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6	993.3	994.0	994.0
137.5°	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3	1042.3	1043.4	1043.7
140°	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1	1073.0	1073.9	1074.1
142.5°	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4	1102.1	1102.8	1102.9
145°	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3	1142.7	1143.1	1143.3
147.5°	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9	1179.3	1179.7	1179.5
150°	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3	1201.7	1202.1	1202.0
152.5°	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2	1222.0	1222.8	1222.7
155°	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6	1249.7	1250.9	1250.7
157.5°	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5	1273.8	1275.1	1275.0
160°	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1	1287.4	1288.7	1288.7
162.5°	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5	1299.9	1301.5	1301.5
165°	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0	1316.7	1318.5	1318.6
167.5°	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4
170°	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5
172.5°	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8	1341.5	1343.3	1343.2
175°	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6	1347.1	1348.7	1348.5
177.5°	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6	1349.1	1350.5	1350.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1506.1	1505.5	1506.1	1503.9	1506.1	1505.5	1506.1	1512.6	1512.6	1513.1	1513.7
5°	1401.4	1400.8	1398.8	1392.7	1398.8	1400.8	1401.4	1403.5	1408.9	1418.4	1415.7
7.5°	1310.1	1309.2	1303.2	1303.4	1303.2	1309.2	1310.1	1315.4	1321.5	1327.3	1334.2
10°	1256.0	1256.6	1248.5	1243.8	1248.5	1256.6	1256.0	1260.8	1269.5	1274.3	1279.0
12.5°	1203.5	1200.4	1193.9	1188.6	1193.9	1200.4	1203.5	1207.1	1219.2	1224.4	1233.6
15°	1134.2	1127.4	1111.2	1112.5	1111.2	1127.4	1134.2	1131.4	1143.7	1150.4	1153.1
17.5°	1052.6	1047.6	1047.3	1037.8	1047.3	1047.6	1052.6	1058.0	1068.5	1075.8	1095.2
20°	1005.0	1001.5	1002.9	993.4	1002.9	1001.5	1005.0	1015.7	1022.5	1032.0	1047.6
22.5°	967.6	964.1	958.5	955.5	958.5	964.1	967.6	975.2	982.5	995.7	1004.3
25°	912.9	907.5	902.1	905.4	902.1	907.5	912.9	917.0	930.5	936.6	948.7
27.5°	858.2	854.2	848.8	848.1	848.8	854.2	858.2	862.1	869.6	879.9	894.5
30°	823.5	819.5	816.8	813.4	816.8	819.5	823.5	827.0	834.4	845.2	856.1
32.5°	788.4	787.6	782.7	782.0	782.7	787.6	788.4	793.9	801.3	811.7	820.9
35°	742.4	738.3	736.9	737.6	736.9	738.3	742.4	745.1	751.8	761.3	770.1
37.5°	698.6	693.2	690.8	688.4	690.8	693.2	698.6	699.0	705.9	712.3	724.2
40°	667.3	661.9	660.5	659.1	660.5	661.9	667.3	666.6	674.0	678.7	689.6
42.5°	632.1	629.9	629.0	626.6	629.0	629.9	632.1	635.7	639.9	646.8	655.0
45°	584.0	583.3	579.3	580.7	579.3	583.3	584.0	586.0	593.5	598.2	605.6
47.5°	533.4	530.4	527.5	529.4	527.5	530.4	533.4	536.1	541.1	546.9	556.8
50°	498.8	497.4	491.3	492.7	491.3	497.4	498.8	501.4	504.8	512.3	521.1
52.5°	464.1	458.9	456.7	455.8	456.7	458.9	464.1	466.8	470.7	479.2	485.9
55°	406.7	400.6	397.9	396.6	397.9	400.6	406.7	411.5	416.9	426.4	433.1
57.5°	350.4	348.8	346.6	348.1	346.6	348.8	350.4	358.3	363.5	371.0	379.3
60°	317.4	317.4	317.4	316.7	317.4	317.4	317.4	324.2	328.9	336.3	345.1
62.5°	292.0	290.3	289.8	290.8	289.8	290.3	292.0	294.9	299.6	304.4	312.1
65°	253.1	252.4	249.7	249.0	249.7	252.4	253.1	255.1	259.2	262.6	267.9
67.5°	216.5	214.0	213.2	212.2	213.2	214.0	216.5	218.2	220.8	225.2	227.9
70°	188.8	187.4	183.4	184.1	183.4	187.4	188.8	192.2	194.9	200.3	203.0
72.5°	159.0	157.6	156.9	155.9	156.9	157.6	159.0	162.4	165.1	171.1	175.4
75°	125.9	125.2	124.5	127.3	124.5	125.2	125.9	126.6	127.3	129.2	131.3
77.5°	100.8	100.8	101.3	100.1	101.3	100.8	100.8	100.8	100.8	101.9	102.3
80°	84.6	84.6	83.9	83.9	83.9	84.6	84.6	84.6	84.6	84.6	83.9
82.5°	67.8	68.4	68.8	67.7	68.8	68.4	67.8	68.9	69.4	68.4	68.8
85°	44.7	44.0	45.4	44.7	45.4	44.0	44.7	44.7	43.3	44.7	44.0
87.5°	25.7	24.8	24.9	25.5	24.9	24.8	25.7	24.6	24.5	24.3	23.6
90°	28.7	29.1	29.5	30.0	29.5	29.1	28.7	28.2	27.6	26.7	25.7
92.5°	32.4	32.7	33.0	33.2	33.0	32.7	32.4	32.1	31.3	29.9	28.4
95°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.2	35.6	34.1
97.5°	40.6	40.8	41.0	41.2	41.0	40.8	40.6	40.3	39.3	37.5	35.7
100°	41.3	41.6	41.8	42.0	41.8	41.6	41.3	41.2	40.1	38.3	36.6
102.5°	41.6	42.0	42.4	42.8	42.4	42.0	41.6	41.2	43.7	49.2	54.8
105°	42.7	43.1	43.6	44.0	43.6	43.1	42.7	42.3	61.6	101.0	140.3
107.5°	227.2	197.5	167.9	138.3	167.9	197.5	227.2	256.8	286.1	315.0	343.8
110°	370.5	338.6	306.9	275.1	306.9	338.6	370.5	402.3	421.8	429.1	436.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.1	485.3	478.6	471.9	478.6	485.3	492.1	498.8	502.1	502.0	501.8
115°	585.5	586.4	587.3	588.1	587.3	586.4	585.5	584.6	583.1	580.8	578.6
117.5°	652.9	653.1	653.2	653.4	653.2	653.1	652.9	652.7	651.7	650.0	648.2
120°	698.2	698.2	698.2	698.2	698.2	698.2	698.2	698.2	697.3	695.5	693.8
122.5°	741.7	741.8	742.1	742.3	742.1	741.8	741.7	741.5	740.8	739.6	738.3
125°	802.9	803.4	803.8	804.3	803.8	803.4	802.9	802.5	802.0	801.6	801.2
127.5°	865.2	864.8	864.4	863.8	864.4	864.8	865.2	865.6	865.5	864.8	864.1
130°	903.6	903.2	902.8	902.3	902.8	903.2	903.6	904.0	903.9	902.9	902.1
132.5°	939.4	938.7	938.1	937.5	938.1	938.7	939.4	940.0	939.9	939.0	938.1
135°	993.3	992.6	992.0	991.4	992.0	992.6	993.3	994.0	994.0	993.3	992.6
137.5°	1043.3	1042.8	1042.4	1041.9	1042.4	1042.8	1043.3	1043.7	1043.4	1042.3	1041.3
140°	1073.7	1073.2	1072.8	1072.4	1072.8	1073.2	1073.7	1074.1	1073.9	1073.0	1072.1
142.5°	1102.3	1101.6	1101.0	1100.4	1101.0	1101.6	1102.3	1102.9	1102.8	1102.1	1101.4
145°	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.3	1143.1	1142.7	1142.3
147.5°	1178.5	1177.4	1176.4	1175.4	1176.4	1177.4	1178.5	1179.5	1179.7	1179.3	1178.9
150°	1201.4	1200.8	1200.1	1199.4	1200.1	1200.8	1201.4	1202.0	1202.1	1201.7	1201.3
152.5°	1221.7	1220.6	1219.6	1218.6	1219.6	1220.6	1221.7	1222.7	1222.8	1222.0	1221.2
155°	1249.4	1248.1	1246.7	1245.4	1246.7	1248.1	1249.4	1250.7	1250.9	1249.7	1248.6
157.5°	1273.2	1271.4	1269.7	1268.0	1269.7	1271.4	1273.2	1275.0	1275.1	1273.8	1272.5
160°	1287.1	1285.6	1283.9	1282.4	1283.9	1285.6	1287.1	1288.7	1288.7	1287.4	1286.1
162.5°	1300.1	1298.7	1297.4	1296.0	1297.4	1298.7	1300.1	1301.5	1301.5	1299.9	1298.5
165°	1317.1	1315.5	1314.0	1312.4	1314.0	1315.5	1317.1	1318.6	1318.5	1316.7	1315.0
167.5°	1329.6	1327.7	1326.0	1324.2	1326.0	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7
170°	1336.8	1335.0	1333.2	1331.5	1333.2	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0
172.5°	1341.3	1339.4	1337.4	1335.4	1337.4	1339.4	1341.3	1343.2	1343.3	1341.5	1339.8
175°	1346.8	1345.0	1343.2	1341.4	1343.2	1345.0	1346.8	1348.5	1348.7	1347.1	1345.6
177.5°	1348.6	1346.8	1345.0	1343.2	1345.0	1346.8	1348.6	1350.3	1350.5	1349.1	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1508.8	1516.4	1524.0	1531.0	1541.9	1546.7	1553.8	1556.4	1564.6	1576.5	1586.2
5°	1417.0	1427.9	1442.1	1453.6	1471.9	1486.1	1501.7	1516.6	1534.1	1559.2	1581.5
7.5°	1339.2	1350.0	1367.0	1388.4	1408.5	1428.7	1449.9	1470.2	1495.4	1531.3	1566.8
10°	1287.8	1300.6	1320.9	1343.9	1369.0	1388.6	1413.7	1439.4	1470.5	1511.8	1554.4
12.5°	1243.4	1253.0	1276.6	1298.5	1326.8	1351.9	1376.3	1406.4	1441.8	1485.8	1537.1
15°	1172.8	1186.3	1209.3	1233.6	1263.4	1289.9	1321.6	1358.1	1392.7	1446.8	1509.1
17.5°	1101.8	1122.4	1146.3	1173.8	1195.9	1232.3	1266.8	1304.3	1346.8	1404.2	1472.6
20°	1056.4	1072.6	1094.9	1134.9	1164.0	1191.7	1223.5	1270.2	1309.4	1374.4	1445.4
22.5°	1018.0	1029.8	1054.9	1087.8	1121.7	1153.8	1186.1	1230.7	1279.1	1340.8	1417.9
25°	961.0	979.9	998.8	1022.5	1059.0	1097.6	1132.8	1170.7	1222.2	1287.8	1371.1
27.5°	905.3	922.5	941.2	970.3	998.0	1034.1	1070.8	1114.3	1169.5	1239.0	1323.4
30°	869.6	882.4	900.0	937.3	962.3	993.4	1036.7	1075.3	1126.7	1200.5	1289.9
32.5°	832.8	849.4	868.7	897.2	928.2	957.7	997.2	1039.1	1091.6	1164.2	1255.7
35°	780.2	799.9	819.5	840.5	871.6	902.1	935.2	981.3	1034.7	1105.1	1195.1
37.5°	731.9	747.8	763.7	789.7	819.2	848.2	879.2	924.5	974.9	1050.9	1133.3
40°	701.1	715.3	727.5	754.6	783.0	814.1	844.6	884.5	938.6	1009.7	1089.5
42.5°	667.5	680.6	697.2	719.4	749.9	776.2	806.7	844.4	895.3	967.4	1037.5
45°	617.2	632.1	646.3	667.3	697.7	723.4	750.4	786.4	838.4	898.0	960.3
47.5°	564.8	579.7	595.9	616.2	642.7	668.9	695.9	727.7	775.2	833.7	875.6
50°	531.2	543.4	559.6	580.0	604.3	632.1	656.4	691.0	736.2	782.3	818.8
52.5°	496.5	507.6	526.1	547.4	570.2	594.2	620.2	649.8	690.8	734.1	763.1
55°	442.6	456.1	471.7	492.7	515.0	535.3	560.3	590.8	623.3	655.7	675.4
57.5°	392.1	403.3	416.5	438.1	457.4	481.7	504.1	527.9	557.9	582.4	595.2
60°	355.2	365.4	382.4	401.3	419.6	440.6	466.2	489.9	513.0	532.6	542.7
62.5°	320.6	332.4	347.2	364.5	384.4	404.2	426.7	446.6	466.9	483.9	490.8
65°	275.4	284.9	295.8	311.9	328.2	348.5	366.1	386.4	401.3	410.8	416.9
67.5°	234.3	240.5	248.7	259.6	275.5	293.3	310.3	326.1	338.6	345.1	350.5
70°	207.8	211.8	217.9	228.8	240.9	256.5	274.1	285.6	296.4	301.8	307.2
72.5°	181.2	186.4	191.9	200.6	210.6	221.8	234.5	248.7	254.7	261.2	264.5
75°	137.4	144.8	152.2	157.6	164.5	173.2	184.8	193.6	196.9	202.3	203.0
77.5°	103.7	105.3	110.7	117.4	123.1	129.5	136.8	144.6	146.3	149.1	150.9
80°	85.2	85.2	85.2	89.3	96.1	100.8	107.6	111.7	114.3	115.0	115.7
82.5°	68.4	68.4	67.9	68.8	71.2	73.8	80.0	84.6	86.8	86.4	84.9
85°	44.7	43.3	43.3	42.6	43.3	41.9	41.2	44.0	48.0	48.0	46.7
87.5°	23.4	22.6	22.6	21.5	20.4	19.3	17.1	17.2	16.8	18.5	17.6
90°	24.9	24.0	21.1	18.3	15.3	12.5	9.9	7.7	5.4	3.2	1.0
92.5°	27.0	25.6	23.4	21.3	19.1	16.9	16.1	16.7	17.4	18.0	18.6
95°	32.5	31.0	28.6	26.1	23.7	21.3	24.5	33.7	42.8	51.9	61.0
97.5°	34.0	32.2	48.2	64.2	80.2	96.3	106.2	110.4	114.4	118.6	122.6
100°	34.8	33.0	67.7	102.4	137.1	171.7	186.8	182.4	178.0	173.5	169.0
102.5°	60.3	65.8	103.7	141.5	179.4	217.3	234.7	231.4	228.3	225.1	221.9
105°	179.7	219.0	239.1	259.1	279.1	299.1	307.9	305.4	303.0	300.6	298.1
107.5°	372.6	401.6	398.4	395.2	392.1	388.9	386.3	384.4	382.5	380.5	378.5
110°	443.8	451.2	448.7	446.3	443.8	441.3	439.3	437.5	435.7	433.9	432.1



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	501.7	501.5	499.1	496.7	494.2	491.8	489.7	488.2	486.6	484.9	483.4
115°	576.4	574.2	572.2	570.2	568.2	566.2	564.5	563.2	561.8	560.5	559.2
117.5°	646.4	644.6	643.6	642.6	641.5	640.5	639.2	637.6	635.8	634.2	632.6
120°	692.0	690.2	689.6	688.9	688.2	687.6	686.2	684.2	682.3	680.2	678.2
122.5°	737.1	735.8	734.9	734.2	733.3	732.5	731.2	729.5	727.9	726.3	724.6
125°	800.7	800.2	799.4	798.5	797.5	796.7	795.4	793.6	791.8	790.1	788.2
127.5°	863.4	862.6	861.6	860.6	859.5	858.4	857.0	855.2	853.4	851.6	849.9
130°	901.2	900.3	899.4	898.5	897.6	896.7	895.4	893.6	891.8	890.1	888.3
132.5°	937.2	936.3	935.6	934.9	934.2	933.4	932.2	930.4	928.7	926.9	925.1
135°	992.0	991.4	990.4	989.5	988.7	987.7	986.6	985.3	984.0	982.7	981.3
137.5°	1040.2	1039.1	1038.6	1038.2	1037.7	1037.2	1036.1	1034.4	1032.7	1031.0	1029.3
140°	1071.3	1070.3	1069.7	1069.0	1068.3	1067.6	1066.7	1065.3	1064.0	1062.6	1061.4
142.5°	1100.7	1099.9	1099.3	1098.6	1097.9	1097.3	1096.3	1094.9	1093.6	1092.3	1091.0
145°	1141.8	1141.3	1140.9	1140.5	1140.1	1139.6	1138.6	1137.0	1135.5	1133.9	1132.4
147.5°	1178.5	1177.9	1177.5	1177.1	1176.6	1176.2	1175.4	1174.4	1173.5	1172.4	1171.4
150°	1200.8	1200.4	1200.0	1199.5	1199.0	1198.6	1198.1	1197.4	1196.7	1196.0	1195.4
152.5°	1220.4	1219.6	1219.3	1219.1	1218.7	1218.5	1218.2	1217.9	1217.6	1217.3	1217.0
155°	1247.5	1246.4	1246.2	1246.0	1245.7	1245.5	1245.6	1246.0	1246.5	1247.0	1247.4
157.5°	1271.2	1269.8	1270.1	1270.2	1270.5	1270.7	1270.8	1270.8	1270.9	1270.9	1271.0
160°	1284.8	1283.4	1283.7	1283.8	1284.1	1284.3	1284.5	1284.8	1285.0	1285.2	1285.4
162.5°	1296.9	1295.4	1295.6	1295.9	1296.1	1296.3	1296.7	1297.3	1297.9	1298.5	1299.0
165°	1313.2	1311.4	1311.6	1311.8	1312.1	1312.3	1312.8	1313.5	1314.1	1314.7	1315.4
167.5°	1326.0	1324.2	1324.2	1324.2	1324.2	1324.2	1324.6	1325.6	1326.5	1327.3	1328.3
170°	1333.2	1331.5	1331.5	1331.5	1331.5	1331.5	1331.9	1332.7	1333.7	1334.6	1335.4
172.5°	1338.0	1336.2	1336.0	1335.8	1335.7	1335.5	1335.9	1337.0	1338.1	1339.2	1340.2
175°	1344.0	1342.4	1342.2	1342.0	1341.8	1341.5	1342.0	1343.1	1344.2	1345.3	1346.4
177.5°	1346.3	1344.8	1344.6	1344.5	1344.3	1344.1	1344.5	1345.4	1346.3	1347.1	1348.1
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1589.5	1595.4	1603.0	1614.4	1623.1	1630.6	1632.3	1634.4	1639.9	1649.0	1656.0
5°	1599.7	1615.3	1640.4	1664.7	1691.1	1712.8	1733.1	1747.3	1760.8	1789.2	1812.2
7.5°	1596.6	1631.2	1670.4	1714.2	1758.4	1801.3	1841.1	1876.6	1912.1	1953.5	2000.8
10°	1594.3	1635.0	1687.7	1743.9	1805.5	1865.7	1923.9	1969.3	2022.1	2069.4	2129.6
12.5°	1584.1	1642.5	1705.6	1777.4	1853.1	1922.5	1999.2	2061.8	2122.2	2190.6	2260.6
15°	1570.6	1641.8	1721.6	1817.0	1932.0	2015.9	2094.5	2203.4	2277.9	2352.3	2452.5
17.5°	1546.2	1632.9	1732.7	1856.7	1952.6	2065.4	2183.5	2269.6	2369.9	2474.8	2565.4
20°	1526.6	1627.5	1739.1	1861.0	1983.5	2105.9	2220.3	2323.2	2426.7	2547.9	2622.3
22.5°	1507.2	1607.0	1722.9	1852.4	1984.0	2113.0	2242.5	2363.3	2479.8	2602.0	2697.0
25°	1465.8	1584.2	1710.0	1842.0	1971.9	2114.1	2268.4	2403.1	2547.2	2673.1	2763.0
27.5°	1423.8	1532.3	1657.7	1791.6	1936.0	2103.9	2285.4	2438.5	2582.9	2673.1	2701.3
30°	1386.0	1501.0	1616.0	1752.0	1908.3	2095.8	2288.6	2463.9	2582.4	2621.6	2592.5
32.5°	1347.5	1451.7	1565.6	1705.0	1871.0	2075.8	2293.0	2448.8	2520.1	2490.1	2371.6
35°	1279.7	1373.7	1484.0	1623.4	1814.3	2064.7	2275.1	2380.7	2363.1	2193.9	1970.6
37.5°	1207.1	1283.8	1386.0	1531.7	1755.6	2020.7	2198.2	2213.8	2061.6	1801.8	1543.9
40°	1149.8	1218.7	1323.7	1475.9	1710.0	1977.4	2120.8	2057.9	1821.7	1532.8	1317.6
42.5°	1094.0	1152.2	1253.3	1417.5	1666.7	1918.4	2005.5	1868.5	1595.9	1322.8	1127.0
45°	999.5	1054.3	1155.8	1324.3	1578.1	1805.5	1794.0	1555.7	1283.1	1063.2	900.7
47.5°	909.9	957.9	1053.1	1225.1	1474.0	1636.3	1528.7	1275.2	1043.9	867.5	751.6
50°	846.5	894.0	988.7	1158.6	1390.7	1509.1	1355.5	1111.2	899.4	753.2	661.2
52.5°	785.9	832.2	918.9	1084.3	1290.0	1360.7	1195.8	969.3	792.7	666.6	587.5
55°	701.1	736.2	814.1	972.4	1126.1	1142.3	975.2	785.7	640.2	552.2	498.1
57.5°	614.6	644.9	721.8	847.9	955.6	947.3	788.8	624.9	526.9	461.5	422.2
60°	558.3	588.1	655.7	764.1	845.2	816.8	671.3	539.3	455.5	407.4	376.3
62.5°	505.8	529.1	592.4	671.4	729.9	697.7	573.9	464.6	398.0	357.6	332.9
65°	429.7	448.7	499.4	540.7	573.2	542.1	439.2	363.4	315.4	287.0	270.0
67.5°	357.4	369.5	401.6	416.5	439.4	405.2	330.3	279.5	252.2	228.2	216.5
70°	311.9	320.7	337.7	349.8	355.9	320.7	265.3	228.1	205.0	188.1	180.7
72.5°	266.5	274.2	277.6	287.6	284.5	251.5	213.3	183.7	167.1	155.7	146.0
75°	203.7	207.1	203.7	199.7	190.8	167.8	141.5	126.6	114.3	108.9	105.6
77.5°	148.4	147.4	142.8	136.5	121.4	106.9	92.7	87.7	82.4	79.6	78.4
80°	114.3	111.7	107.6	97.5	84.6	74.5	71.0	67.7	65.6	62.3	61.6
82.5°	85.2	83.5	76.7	68.2	59.2	54.4	51.6	50.4	48.3	46.6	46.4
85°	45.4	43.3	35.9	31.2	29.8	28.4	27.7	27.7	25.1	24.4	24.4
87.5°	15.2	12.5	12.4	11.2	11.7	11.2	12.3	11.8	11.9	12.6	11.6
90°	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9	25.7
92.5°	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0	28.4
95°	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5	34.1
97.5°	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0	35.7
100°	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8	36.6
102.5°	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3	54.8
105°	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7	140.3
107.5°	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6	343.8
110°	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8	436.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7	501.8
115°	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4	578.6
117.5°	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4	648.2
120°	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0	693.8
122.5°	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1	738.3
125°	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7	801.2
127.5°	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4	864.1
130°	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2	902.1
132.5°	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2	938.1
135°	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0	992.6
137.5°	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2	1041.3
140°	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3	1072.1
142.5°	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7	1101.4
145°	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8	1142.3
147.5°	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5	1178.9
150°	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8	1201.3
152.5°	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4	1221.2
155°	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5	1248.6
157.5°	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2	1272.5
160°	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8	1286.1
162.5°	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9	1298.5
165°	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2	1315.0
167.5°	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0	1327.7
170°	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2	1335.0
172.5°	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0	1339.8
175°	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0	1345.6
177.5°	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3	1347.6
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1667.4	1667.4	1669.6	1677.7	1678.8	1685.8	1683.7
5°	1832.6	1845.4	1850.1	1870.4	1882.7	1888.1	1877.2
7.5°	2034.5	2070.8	2087.9	2109.2	2128.0	2133.7	2118.9
10°	2181.8	2219.7	2251.4	2271.1	2289.3	2301.5	2317.1
12.5°	2324.1	2370.7	2400.9	2428.6	2447.4	2462.9	2465.4
15°	2478.8	2549.2	2602.6	2641.9	2661.5	2671.7	2667.6
17.5°	2634.8	2700.1	2738.2	2778.2	2805.4	2806.8	2807.5
20°	2723.1	2786.7	2830.7	2860.5	2891.0	2889.6	2896.3
22.5°	2782.1	2832.2	2865.9	2887.5	2898.0	2892.9	2894.2
25°	2809.7	2824.6	2818.6	2784.0	2775.3	2743.4	2748.8
27.5°	2667.4	2596.9	2524.2	2430.5	2356.6	2297.6	2300.6
30°	2474.1	2349.6	2207.4	2088.4	1981.4	1951.6	1888.1
32.5°	2203.9	2017.2	1850.7	1739.7	1648.0	1623.1	1567.5
35°	1745.9	1564.6	1393.4	1290.5	1249.9	1193.1	1192.4
37.5°	1357.1	1197.4	1106.8	1029.7	989.2	954.8	951.5
40°	1141.6	1017.1	948.7	893.3	853.3	827.6	821.6
42.5°	991.1	890.4	826.4	792.0	761.3	748.0	738.1
45°	809.3	741.7	697.0	665.9	651.7	641.5	636.1
47.5°	677.0	631.6	601.2	580.5	568.9	558.3	561.1
50°	605.0	567.7	545.4	525.8	517.0	509.5	510.2
52.5°	547.1	513.7	495.6	481.4	470.5	465.2	462.6
55°	464.3	443.2	425.0	414.8	408.7	401.3	399.2
57.5°	396.0	379.8	364.9	353.4	351.9	344.7	345.7
60°	350.5	337.0	324.9	318.7	314.0	307.9	310.0
62.5°	313.1	301.8	290.8	285.7	280.9	276.5	277.4
65°	256.5	245.6	238.8	236.2	234.1	232.1	230.1
67.5°	204.4	197.8	193.6	187.7	183.6	182.9	180.8
70°	171.9	163.1	155.7	148.2	146.2	145.5	146.2
72.5°	137.8	132.2	130.2	126.6	126.1	124.4	125.6
75°	103.6	101.5	100.1	97.5	97.5	97.5	97.5
77.5°	76.4	75.1	74.3	73.8	73.1	72.2	72.0
80°	59.6	58.9	57.5	57.5	56.8	57.5	56.8
82.5°	44.9	44.8	43.5	43.5	42.8	42.4	42.8
85°	23.0	22.3	23.7	22.3	23.0	21.7	23.0
87.5°	11.8	12.0	11.6	11.7	11.3	12.4	11.5
90°	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332384-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)