

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332353-940

Luminaire Tested: **S123RDIP-S1000D1025U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332353-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6692.1 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	71	69		62	60	59		51	49	48	43
2	90	82	77	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	66	60	76	68	61	56	58	53	49		49	45	42		40	38	36	31
4	75	65	57	51	69	60	53	48	51	46	42		43	40	36		36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36		39	35	32		33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32		35	31	28		30	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28		32	28	25		27	24	21	19
8	55	43	35	30	51	40	33	28	35	29	25		30	25	22		25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23		27	23	20		23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20		25	21	18		21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.1
10°-20°	391.0	5.8
20°-30°	563.0	8.4
30°-40°	634.1	9.5
40°-50°	606.7	9.1
50°-60°	496.8	7.4
60°-70°	335.2	5.0
70°-80°	168.6	2.5
80°-90°	48.0	0.7
90°-100°	244.7	3.7
100°-110°	692.9	10.4
110°-120°	681.6	10.2
120°-130°	543.7	8.1
130°-140°	428.7	6.4
140°-150°	319.9	4.8
150°-160°	223.0	3.3
160°-170°	131.0	2.0
170°-180°	42.6	0.6
0°-30°	1094.5	16.4
0°-40°	1728.6	25.8
0°-60°	2832.1	42.3
0°-90°	3384.0	50.6
90°-120°	1619.2	24.2
90°-150°	2911.5	43.5
90°-180°	3308.0	49.4
0°-180°	6692.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	2	11	22	25	26	5
95°	30	98	528	154	103	33
105°	103	153	716	1251	1132	110
115°	182	227	547	1200	1377	181
125°	254	300	511	926	1086	225
135°	297	355	504	762	880	230
145°	339	389	498	625	688	213
155°	385	416	482	547	570	177
165°	421	433	461	489	498	119
175°	439	439	442	449	448	42
180°	440	440	440	440	440	



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.6	21.7	19.6	17.7	15.8	15.0	15.4	16.0	16.5	17.0	16.7
90°	1.8	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4
92.5°	11.1	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3
95°	30.2	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1
97.5°	51.6	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1
100°	65.9	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2
102.5°	80.8	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4
105°	103.3	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1
107.5°	127.1	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0
110°	144.2	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.9	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2
115°	182.4	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4
117.5°	205.1	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4
120°	220.7	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5
122.5°	234.3	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1
125°	253.7	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2
127.5°	268.5	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6
130°	277.7	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7
132.5°	284.8	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4
135°	297.3	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3
137.5°	309.1	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8
140°	316.9	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4
142.5°	325.4	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7
145°	339.1	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0
147.5°	353.0	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5
150°	362.3	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5
152.5°	371.5	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9
155°	385.4	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4
157.5°	396.5	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7
160°	405.0	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3
162.5°	411.4	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9
165°	421.0	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1
167.5°	428.3	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9
170°	432.6	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9
172.5°	435.4	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9
175°	438.8	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2
177.5°	440.4	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	16.7	16.6	16.6	16.7	16.3	16.3	16.2	15.9
90°	22.3	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	74.9	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	320.4	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	798.8	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	1049.5	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1132.7	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1157.1	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1087.0	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1020.0	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P332353-940

CATALOG NUMBER: S123RDIP-S1000D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	953.8	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	866.0	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	802.5	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	769.0	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	742.7	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	707.7	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	677.0	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	657.8	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	640.0	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	615.9	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	594.1	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	581.2	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	569.1	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	554.6	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	542.6	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	534.0	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	526.2	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	514.4	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	502.0	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	494.9	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	486.3	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	475.3	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	465.7	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	459.3	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	453.6	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	445.9	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.1	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)