

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332387-935

Luminaire Tested: **S123RDIP-S1165D1195U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332387-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1195U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7879.6 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.0
10°-20°	436.0	5.5
20°-30°	627.8	8.0
30°-40°	707.2	9.0
40°-50°	676.5	8.6
50°-60°	554.0	7.0
60°-70°	373.8	4.7
70°-80°	188.1	2.4
80°-90°	53.5	0.7
90°-100°	48.9	0.6
100°-110°	233.3	3.0
110°-120°	560.4	7.1
120°-130°	713.6	9.1
130°-140°	762.5	9.7
140°-150°	713.0	9.0
150°-160°	575.1	7.3
160°-170°	371.2	4.7
170°-180°	127.9	1.6
0°-30°	1220.5	15.5
0°-40°	1927.7	24.5
0°-60°	3158.3	40.1
0°-90°	3773.6	47.9
90°-120°	842.6	10.7
90°-150°	3031.7	38.5
90°-180°	4106.0	52.1
0°-180°	7879.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	1	11	24	28	30	6
95°	61	23	31	38	38	75
105°	298	304	219	52	44	316
115°	559	565	574	584	588	552
125°	788	796	800	802	804	704
135°	981	987	991	994	991	755
145°	1132	1139	1141	1143	1143	709
155°	1247	1246	1246	1251	1245	574
165°	1315	1313	1311	1319	1312	371
175°	1346	1342	1342	1349	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.2	24.0	21.8	19.5	17.4	16.5	17.1	17.7	18.3	18.9	18.9
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	18.6	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0
95°	61.0	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5
97.5°	122.6	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0
100°	169.0	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8
102.5°	221.9	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3
105°	298.1	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7
107.5°	378.5	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6
110°	432.1	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.4	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7
115°	559.2	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4
117.5°	632.6	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4
120°	678.2	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0
122.5°	724.6	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1
125°	788.2	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7
127.5°	849.9	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4
130°	888.3	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2
132.5°	925.1	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2
135°	981.3	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0
137.5°	1029.3	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2
140°	1061.4	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3
142.5°	1091.0	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7
145°	1132.4	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8
147.5°	1171.4	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5
150°	1195.4	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8
152.5°	1217.0	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4
155°	1247.4	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5
157.5°	1271.0	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2
160°	1285.4	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8
162.5°	1299.0	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9
165°	1315.4	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2
167.5°	1328.3	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0
170°	1335.4	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2
172.5°	1340.2	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0
175°	1346.4	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0
177.5°	1348.1	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	18.8	18.7	18.6	18.5	18.3	18.3	18.1	17.9
90°	25.7	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	28.4	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	34.1	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	35.7	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	36.6	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	54.8	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	140.3	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	343.8	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	436.4	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332387-935

CATALOG NUMBER: S123RDIP-S1165D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	501.8	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	578.6	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	648.2	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	693.8	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	738.3	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.2	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.1	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.1	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	938.1	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1041.3	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1072.1	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1101.4	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.3	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1178.9	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.3	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1221.2	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1248.6	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1272.5	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1286.1	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1298.5	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1315.0	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1339.8	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1345.6	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1347.6	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)