

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332332-940

Luminaire Tested: **S123RDIP-S1000D365U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332332-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D365U940-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4701.9 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	93	99	95	92	89	87	84	82	79	77	75	71	70	69	65
2	96	89	83	78	91	85	79	75	77	73	69	70	67	64	64	61	59	56
3	88	79	71	66	83	75	69	64	69	64	59	63	59	55	57	54	51	48
4	81	70	62	57	77	67	60	55	62	56	51	57	52	48	52	48	45	42
5	75	63	55	49	71	61	53	48	56	50	45	51	46	42	47	43	40	37
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	43	39	35	33
7	64	52	44	38	61	50	43	37	46	40	36	43	38	34	40	35	32	30
8	60	48	40	34	57	46	39	34	43	36	32	39	34	30	37	32	29	27
9	56	44	36	31	53	42	35	30	39	33	29	36	31	28	34	29	26	24
10	52	40	33	28	50	39	32	28	36	30	26	34	29	25	31	27	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	3.0
10°-20°	435.5	9.3
20°-30°	684.2	14.6
30°-40°	713.8	15.2
40°-50°	610.9	13.0
50°-60°	465.6	9.9
60°-70°	298.4	6.3
70°-80°	143.6	3.1
80°-90°	39.2	0.8
90°-100°	86.6	1.8
100°-110°	245.3	5.2
110°-120°	241.3	5.1
120°-130°	192.5	4.1
130°-140°	151.8	3.2
140°-150°	113.3	2.4
150°-160°	78.9	1.7
160°-170°	46.4	1.0
170°-180°	15.1	0.3
0°-30°	1259.1	26.8
0°-40°	1973.0	42.0
0°-60°	3049.5	64.9
0°-90°	3530.7	75.1
90°-120°	573.2	12.2
90°-150°	1030.7	21.9
90°-180°	1171.0	24.9
0°-180°	4701.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	9	1	9	1	9	5
95°	37	11	37	11	37	66
105°	401	37	401	37	401	395
115°	488	65	488	65	488	474
125°	384	90	384	90	384	348
135°	312	105	312	105	312	242
145°	244	120	244	120	244	155
155°	202	136	202	136	202	94
165°	176	149	176	149	176	50
175°	158	155	158	155	158	15
180°	156	156	156	156	156	



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	6.7	7.8	6.7	7.1	7.1	7.5	7.5	7.4	8.3	7.8	8.2
90°	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8	7.6	7.8	7.0
92.5°	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6	36.6	48.4	53.3
95°	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4	151.6	186.9	166.4
97.5°	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8	309.8	289.6	212.0
100°	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5	360.5	298.5	201.7
102.5°	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0	363.0	282.0	186.5
105°	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7	343.8	253.3	168.0
107.5°	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8	310.1	228.0	156.1
110°	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1	289.0	213.7	151.6



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7	270.5	204.0	149.0
115°	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6	248.3	193.8	148.1
117.5°	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1	234.9	187.7	148.6
120°	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2	227.8	184.9	149.7
122.5°	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0	222.0	183.2	151.4
125°	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5	214.6	180.8	154.1
127.5°	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7	208.0	179.8	157.1
130°	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8	204.5	179.0	159.2
132.5°	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6	201.3	178.7	160.7
135°	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0	197.0	178.3	162.9
137.5°	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3	193.2	177.6	164.4
140°	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8	190.9	177.5	165.4
142.5°	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5	189.0	176.9	166.2
145°	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4	186.2	176.1	166.7
147.5°	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1	183.6	175.0	166.7
150°	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0	181.8	174.0	166.7
152.5°	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3	179.8	172.7	165.9
155°	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2	176.7	170.5	165.1
157.5°	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7	173.3	168.5	164.1
160°	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2	171.1	167.0	163.5
162.5°	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2	168.8	165.5	162.6
165°	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3	165.8	163.3	161.0
167.5°	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9	162.8	161.0	159.5
170°	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6	161.0	159.4	158.5
172.5°	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6	159.3	158.2	157.7
175°	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8	157.2	156.6	156.6
177.5°	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	9.0	8.3	9.1	8.9	10.3	10.6	13.4	15.7	16.2	14.4	14.6
90°	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6	1.2	1.9	2.9
92.5°	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9	5.8	8.5	10.9
95°	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7	11.7	15.2	20.5
97.5°	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3	18.5	21.3	25.9
100°	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4	23.6	25.9	30.2
102.5°	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6	29.2	31.1	35.3
105°	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6	37.5	39.4	43.2
107.5°	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0	45.9	47.8	51.5
110°	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0	52.0	53.6	57.1





TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6	57.5	59.1	62.6
115°	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6	65.9	67.8	70.9
117.5°	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6	74.0	75.6	78.6
120°	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1	79.1	80.7	83.8
122.5°	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9	83.9	85.4	88.9
125°	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8	90.4	92.3	95.8
127.5°	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1	95.9	98.4	101.8
130°	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4	99.2	102.1	105.8
132.5°	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9	102.0	105.1	109.7
135°	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2	106.5	109.9	114.7
137.5°	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4	110.8	114.1	119.1
140°	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2	113.8	116.9	122.0
142.5°	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2	116.5	119.9	124.5
145°	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0	121.0	123.9	128.6
147.5°	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0	125.6	128.3	132.4
150°	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2	128.6	131.1	135.2
152.5°	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5	131.6	134.1	137.7
155°	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4	136.4	138.3	141.5
157.5°	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4	140.6	142.1	144.9
160°	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4	143.4	144.6	147.1
162.5°	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6	145.6	146.7	148.6
165°	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0	148.7	149.4	151.0
167.5°	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6	151.2	151.6	152.8
170°	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1	152.5	152.8	153.7
172.5°	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2	153.7	153.8	154.5
175°	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3	155.1	154.7	155.3
177.5°	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0	155.7	155.4	155.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	14.3	15.9	16.6	17.2	17.9	17.6	18.0	18.1	18.6	18.7	18.8
90°	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8	8.2	8.5	9.1
92.5°	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6	21.0	18.5	16.9
95°	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4	76.9	60.2	48.9
97.5°	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8	226.5	185.8	148.2
100°	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5	346.0	309.2	264.4
102.5°	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0	400.2	378.7	350.4
105°	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7	441.1	447.1	439.0
107.5°	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8	436.0	463.6	474.8
110°	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1	419.1	458.8	480.9



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7	396.9	441.4	469.8
115°	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6	361.4	407.8	442.1
117.5°	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1	331.4	373.0	407.9
120°	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2	314.8	352.6	384.4
122.5°	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0	301.4	336.4	366.0
125°	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5	284.9	315.1	340.4
127.5°	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7	270.3	297.6	320.6
130°	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8	261.3	286.8	308.2
132.5°	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6	252.6	276.4	296.9
135°	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0	240.4	260.9	278.8
137.5°	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3	228.6	246.3	261.9
140°	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8	221.9	236.9	250.5
142.5°	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5	215.3	228.4	240.1
145°	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4	206.7	216.8	226.0
147.5°	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1	200.4	208.5	215.0
150°	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0	196.4	203.0	208.9
152.5°	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3	192.5	198.4	203.4
155°	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2	187.2	191.9	195.6
157.5°	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7	181.9	185.6	188.6
160°	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2	178.7	181.8	184.0
162.5°	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2	175.1	178.1	180.0
165°	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3	170.1	172.4	174.0
167.5°	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9	166.3	167.6	168.7
170°	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6	163.5	164.8	165.4
172.5°	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6	161.3	162.3	162.6
175°	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8	158.2	158.8	158.8
177.5°	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1	156.4	156.7	156.7
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	19.7	18.8	18.9	19.3	18.9	18.8	19.7	18.8	18.7	18.6	18.1
90°	8.8	9.1	9.5	9.1	9.5	9.1	8.8	9.1	8.5	8.2	7.8
92.5°	16.4	15.4	15.8	15.2	15.8	15.4	16.4	16.9	18.5	21.0	26.6
95°	42.9	40.0	37.8	36.6	37.8	40.0	42.9	48.9	60.2	76.9	113.4
97.5°	124.9	110.8	102.2	99.5	102.2	110.8	124.9	148.2	185.8	226.5	282.8
100°	232.6	209.6	197.2	197.6	197.2	209.6	232.6	264.4	309.2	346.0	371.5
102.5°	325.6	307.4	297.1	289.8	297.1	307.4	325.6	350.4	378.7	400.2	401.0
105°	424.5	412.5	402.4	400.8	402.4	412.5	424.5	439.0	447.1	441.1	409.7
107.5°	475.1	471.0	467.6	464.8	467.6	471.0	475.1	474.8	463.6	436.0	384.8
110°	489.7	492.2	491.6	491.0	491.6	492.2	489.7	480.9	458.8	419.1	361.1



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	485.9	493.7	496.1	496.2	496.1	493.7	485.9	469.8	441.4	396.9	337.7
115°	465.7	479.6	485.9	487.5	485.9	479.6	465.7	442.1	407.8	361.4	306.6
117.5°	432.6	448.4	457.4	459.6	457.4	448.4	432.6	407.9	373.0	331.4	284.1
120°	409.3	427.0	434.5	436.4	434.5	427.0	409.3	384.4	352.6	314.8	272.2
122.5°	388.2	404.0	412.3	414.7	412.3	404.0	388.2	366.0	336.4	301.4	263.0
125°	360.5	374.3	382.3	384.4	382.3	374.3	360.5	340.4	315.1	284.9	250.5
127.5°	338.5	350.4	357.5	359.4	357.5	350.4	338.5	320.6	297.6	270.3	239.7
130°	324.9	336.3	342.9	345.4	342.9	336.3	324.9	308.2	286.8	261.3	232.8
132.5°	312.5	323.9	329.8	331.5	329.8	323.9	312.5	296.9	276.4	252.6	226.6
135°	294.4	303.8	309.4	311.7	309.4	303.8	294.4	278.8	260.9	240.4	218.0
137.5°	274.8	284.5	289.2	290.7	289.2	284.5	274.8	261.9	246.3	228.6	210.3
140°	262.5	271.3	276.3	276.1	276.3	271.3	262.5	250.5	236.9	221.9	205.8
142.5°	250.4	258.2	262.7	262.4	262.7	258.2	250.4	240.1	228.4	215.3	201.5
145°	233.8	240.4	243.0	243.6	243.0	240.4	233.8	226.0	216.8	206.7	196.4
147.5°	221.0	225.4	227.8	228.1	227.8	225.4	221.0	215.0	208.5	200.4	192.1
150°	213.7	217.1	219.0	219.0	219.0	217.1	213.7	208.9	203.0	196.4	189.0
152.5°	207.1	210.3	211.4	211.4	211.4	210.3	207.1	203.4	198.4	192.5	186.3
155°	198.5	201.1	201.7	202.0	201.7	201.1	198.5	195.6	191.9	187.2	182.2
157.5°	191.0	192.9	193.4	193.3	193.4	192.9	191.0	188.6	185.6	181.9	177.7
160°	186.2	188.2	188.2	187.8	188.2	188.2	186.2	184.0	181.8	178.7	175.2
162.5°	181.5	183.1	183.1	182.8	183.1	183.1	181.5	180.0	178.1	175.1	172.2
165°	175.2	176.5	176.1	176.1	176.1	176.5	175.2	174.0	172.4	170.1	168.3
167.5°	169.2	170.1	169.9	169.9	169.9	170.1	169.2	168.7	167.6	166.3	164.9
170°	165.8	166.4	166.0	166.0	166.0	166.4	165.8	165.4	164.8	163.5	162.6
172.5°	162.7	163.4	162.8	162.6	162.8	163.4	162.7	162.6	162.3	161.3	160.6
175°	158.8	159.2	158.8	158.5	158.8	159.2	158.8	158.8	158.8	158.2	157.8
177.5°	156.4	156.7	156.1	156.1	156.1	156.7	156.4	156.7	156.7	156.4	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	18.0	17.6	17.9	17.2	16.6	15.9	14.3	14.6	14.4	16.2	15.7
90°	7.6	7.8	7.0	6.0	5.1	4.1	3.5	2.9	1.9	1.2	0.6
92.5°	36.6	48.4	53.3	40.0	26.5	18.2	13.6	10.9	8.5	5.8	3.9
95°	151.6	186.9	166.4	114.7	67.8	40.9	28.7	20.5	15.2	11.7	10.7
97.5°	309.8	289.6	212.0	125.8	72.9	47.3	34.1	25.9	21.3	18.5	18.3
100°	360.5	298.5	201.7	118.8	72.1	50.1	37.8	30.2	25.9	23.6	23.4
102.5°	363.0	282.0	186.5	112.7	73.2	53.4	42.1	35.3	31.1	29.2	28.6
105°	343.8	253.3	168.0	108.4	76.0	58.9	49.1	43.2	39.4	37.5	36.6
107.5°	310.1	228.0	156.1	108.1	81.1	66.2	57.1	51.5	47.8	45.9	45.0
110°	289.0	213.7	151.6	109.3	85.4	71.2	62.4	57.1	53.6	52.0	51.0



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	270.5	204.0	149.0	111.9	89.7	76.5	67.9	62.6	59.1	57.5	56.6
115°	248.3	193.8	148.1	115.9	96.8	84.8	76.2	70.9	67.8	65.9	64.6
117.5°	234.9	187.7	148.6	121.4	104.2	92.4	84.5	78.6	75.6	74.0	72.6
120°	227.8	184.9	149.7	125.4	109.1	97.6	89.8	83.8	80.7	79.1	78.1
122.5°	222.0	183.2	151.4	129.2	114.0	103.0	94.6	88.9	85.4	83.9	82.9
125°	214.6	180.8	154.1	135.2	121.4	110.3	101.7	95.8	92.3	90.4	89.8
127.5°	208.0	179.8	157.1	140.1	127.6	117.0	108.4	101.8	98.4	95.9	95.1
130°	204.5	179.0	159.2	143.4	131.4	121.0	112.5	105.8	102.1	99.2	98.4
132.5°	201.3	178.7	160.7	146.4	134.6	124.6	116.3	109.7	105.1	102.0	100.9
135°	197.0	178.3	162.9	150.3	139.6	129.8	121.4	114.7	109.9	106.5	105.2
137.5°	193.2	177.6	164.4	153.2	143.0	133.6	125.7	119.1	114.1	110.8	109.4
140°	190.9	177.5	165.4	154.7	145.3	136.2	128.2	122.0	116.9	113.8	112.2
142.5°	189.0	176.9	166.2	156.2	147.0	138.1	130.8	124.5	119.9	116.5	115.2
145°	186.2	176.1	166.7	157.8	149.4	141.2	133.9	128.6	123.9	121.0	120.0
147.5°	183.6	175.0	166.7	158.9	151.2	143.7	137.6	132.4	128.3	125.6	125.0
150°	181.8	174.0	166.7	159.2	152.5	145.3	139.6	135.2	131.1	128.6	128.2
152.5°	179.8	172.7	165.9	159.6	153.3	147.0	141.6	137.7	134.1	131.6	131.5
155°	176.7	170.5	165.1	159.8	154.7	149.4	145.0	141.5	138.3	136.4	136.4
157.5°	173.3	168.5	164.1	160.1	155.5	151.2	147.8	144.9	142.1	140.6	140.4
160°	171.1	167.0	163.5	160.1	156.3	152.5	149.4	147.1	144.6	143.4	143.4
162.5°	168.8	165.5	162.6	159.8	156.6	153.3	150.6	148.6	146.7	145.6	145.6
165°	165.8	163.3	161.0	159.2	156.9	154.4	152.2	151.0	149.4	148.7	149.0
167.5°	162.8	161.0	159.5	158.6	156.9	155.1	153.6	152.8	151.6	151.2	151.6
170°	161.0	159.4	158.5	157.8	156.6	155.1	154.4	153.7	152.8	152.5	153.1
172.5°	159.3	158.2	157.7	157.7	156.6	155.2	154.9	154.5	153.8	153.7	154.2
175°	157.2	156.6	156.6	156.9	156.3	155.7	155.3	155.3	154.7	155.1	155.3
177.5°	156.0	155.7	156.0	156.4	156.0	155.7	155.7	155.7	155.4	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.4	10.6	10.3	8.9	9.1	8.3	9.0	8.2	7.8	8.3	7.4
90°	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6	7.8
92.5°	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6	26.6
95°	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6	113.4
97.5°	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8	282.8
100°	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5	371.5
102.5°	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0	401.0
105°	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8	409.7
107.5°	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1	384.8
110°	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0	361.1





TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5	337.7
115°	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3	306.6
117.5°	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9	284.1
120°	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8	272.2
122.5°	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0	263.0
125°	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6	250.5
127.5°	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0	239.7
130°	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5	232.8
132.5°	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3	226.6
135°	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0	218.0
137.5°	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2	210.3
140°	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9	205.8
142.5°	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0	201.5
145°	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2	196.4
147.5°	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6	192.1
150°	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8	189.0
152.5°	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8	186.3
155°	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7	182.2
157.5°	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3	177.7
160°	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1	175.2
162.5°	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8	172.2
165°	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8	168.3
167.5°	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8	164.9
170°	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0	162.6
172.5°	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3	160.6
175°	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2	157.8
177.5°	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	7.5	7.5	7.1	7.1	6.7	7.8	6.7
90°	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	419.1	458.8	480.9	489.7	492.2	491.6	491.0



TEST NUMBER: P332332-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)