

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332334-940

Luminaire Tested: **S123RDIP-S1000D365U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332334-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D365U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4493.2 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75
1	104	100	96	92	99	95	92	89	86	84	81	78	76	74	71	69	68	64
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47
4	80	69	61	55	76	66	59	53	61	55	50	55	51	47	51	47	43	41
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	36
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31
7	63	51	43	37	60	49	41	36	45	39	34	42	36	32	38	34	30	28
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25
9	55	42	35	30	52	41	34	29	38	32	28	35	30	26	33	28	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	3.1
10°-20°	391.0	8.7
20°-30°	563.0	12.5
30°-40°	634.1	14.1
40°-50°	606.7	13.5
50°-60°	496.8	11.1
60°-70°	335.2	7.5
70°-80°	168.6	3.8
80°-90°	45.8	1.0
90°-100°	26.1	0.6
100°-110°	78.2	1.7
110°-120°	133.0	3.0
120°-130°	175.0	3.9
130°-140°	196.7	4.4
140°-150°	193.3	4.3
150°-160°	162.8	3.6
160°-170°	108.3	2.4
170°-180°	37.9	0.8
0°-30°	1094.5	24.4
0°-40°	1728.6	38.5
0°-60°	2832.1	63.0
0°-90°	3381.8	75.3
90°-120°	237.4	5.3
90°-150°	802.4	17.9
90°-180°	1111.0	24.7
0°-180°	4493.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	0	4	8	9	10	4
95°	19	21	23	24	25	21
105°	71	72	74	74	75	76
115°	134	135	134	135	134	132
125°	196	197	196	195	194	175
135°	254	256	256	255	254	196
145°	308	309	310	310	308	193
155°	353	353	354	355	353	163
165°	385	384	384	386	384	108
175°	400	399	399	401	399	38
180°	401	401	401	401	401	



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.4	21.1	18.9	16.7	14.4	13.4	13.6	13.7	13.9	14.2	14.0
90°	0.4	1.0	1.7	2.4	3.1	3.9	4.8	5.7	6.7	7.6	7.8
92.5°	7.7	8.1	8.6	9.1	9.5	10.0	10.5	11.1	11.6	12.1	12.3
95°	18.6	19.1	19.5	20.1	20.5	21.0	21.7	22.2	22.7	23.4	23.6
97.5°	33.0	33.3	33.8	34.2	34.5	34.9	35.3	35.7	36.1	36.5	36.8
100°	42.9	43.2	43.7	44.1	44.5	44.9	45.3	45.7	46.0	46.3	46.5
102.5°	54.2	54.5	54.7	54.9	55.2	55.6	56.0	56.5	57.0	57.4	57.6
105°	70.9	71.1	71.2	71.3	71.4	71.9	72.5	73.1	73.7	74.4	74.4
107.5°	90.3	90.4	90.5	90.6	90.7	90.8	91.0	91.3	91.6	91.8	92.0
110°	102.5	102.5	102.7	102.8	103.0	103.1	103.3	103.4	103.5	103.7	104.0



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	115.0	115.1	115.2	115.3	115.4	115.4	115.5	115.5	115.5	115.6	115.8
115°	133.9	134.1	134.4	134.6	134.7	134.8	134.6	134.6	134.4	134.2	134.3
117.5°	152.9	153.1	153.3	153.4	153.6	153.5	153.3	153.1	152.9	152.8	152.8
120°	164.8	165.2	165.7	166.0	166.5	166.5	166.2	165.9	165.5	165.1	165.1
122.5°	177.2	177.5	177.8	178.1	178.4	178.4	178.3	178.1	177.9	177.7	177.5
125°	196.0	196.2	196.4	196.6	196.9	196.9	196.7	196.6	196.4	196.4	196.0
127.5°	213.4	213.8	214.3	214.7	215.2	215.3	215.2	215.0	214.9	214.7	214.4
130°	225.0	225.5	226.1	226.7	227.2	227.4	227.2	227.0	226.8	226.6	226.3
132.5°	236.6	237.2	237.7	238.3	238.8	239.1	238.9	238.7	238.5	238.4	238.1
135°	254.3	254.8	255.1	255.6	256.0	256.2	256.1	256.0	255.9	255.9	255.6
137.5°	270.7	271.1	271.3	271.7	272.1	272.3	272.5	272.7	272.9	273.0	272.8
140°	282.0	282.4	282.8	283.1	283.5	283.7	283.7	283.7	283.8	283.9	283.8
142.5°	292.4	292.7	293.1	293.5	293.7	294.0	294.2	294.3	294.4	294.5	294.4
145°	308.5	308.6	308.8	308.9	309.1	309.2	309.4	309.7	309.9	310.0	310.0
147.5°	322.6	322.9	323.2	323.4	323.6	323.9	324.0	324.2	324.4	324.7	324.7
150°	332.4	332.6	332.7	332.9	333.1	333.1	333.3	333.4	333.6	333.7	333.7
152.5°	340.5	340.7	340.9	341.1	341.3	341.4	341.5	341.6	341.7	341.8	341.9
155°	353.3	353.3	353.3	353.3	353.3	353.3	353.4	353.4	353.5	353.6	353.8
157.5°	364.1	364.0	363.9	363.8	363.7	363.7	363.8	363.8	363.9	364.0	364.3
160°	370.9	370.8	370.6	370.5	370.3	370.2	370.2	370.2	370.2	370.2	370.6
162.5°	376.9	376.7	376.6	376.4	376.1	376.1	376.1	376.2	376.3	376.3	376.7
165°	384.8	384.6	384.3	384.1	383.9	383.8	383.8	383.8	383.8	383.8	384.2
167.5°	391.0	390.7	390.5	390.1	389.9	389.8	389.9	389.9	389.9	390.0	390.4
170°	394.5	394.2	394.0	393.7	393.4	393.2	393.2	393.2	393.2	393.2	393.8
172.5°	397.3	397.0	396.7	396.5	396.2	396.0	396.0	396.0	396.0	396.0	396.5
175°	400.2	399.9	399.7	399.4	399.1	399.0	399.0	399.0	399.0	399.0	399.4
177.5°	401.4	401.2	400.9	400.7	400.5	400.4	400.4	400.4	400.4	400.4	400.7
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	13.8	13.6	13.5	13.3	13.1	12.9	12.8	12.6
90°	8.1	8.4	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	12.6	12.8	13.0	13.1	13.0	12.9	12.8	12.8
95°	23.9	24.2	24.4	24.6	24.6	24.6	24.6	24.6
97.5°	37.1	37.5	37.8	37.9	37.9	37.9	37.8	37.8
100°	46.7	47.0	47.2	47.3	47.4	47.6	47.8	47.9
102.5°	57.9	58.1	58.2	58.3	58.3	58.3	58.2	58.2
105°	74.4	74.4	74.4	74.5	74.5	74.7	74.9	75.0
107.5°	92.3	92.5	92.7	92.8	92.7	92.6	92.6	92.5
110°	104.2	104.5	104.8	104.9	104.7	104.6	104.4	104.3



TEST NUMBER: P332334-940

CATALOG NUMBER: S123RDIP-S1000D365U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	116.2	116.5	116.9	117.0	117.0	117.0	116.9	116.9
115°	134.4	134.5	134.6	134.6	134.5	134.4	134.3	134.2
117.5°	152.8	152.8	152.8	152.6	152.4	152.2	152.0	151.9
120°	165.0	164.9	164.9	164.7	164.6	164.4	164.3	164.2
122.5°	177.4	177.2	177.0	176.8	176.6	176.4	176.2	176.0
125°	195.7	195.5	195.2	194.9	194.7	194.4	194.0	193.8
127.5°	213.9	213.6	213.1	212.8	212.5	212.1	211.9	211.5
130°	226.0	225.7	225.4	225.1	224.6	224.1	223.6	223.1
132.5°	237.7	237.4	237.1	236.7	236.3	235.9	235.6	235.2
135°	255.3	255.0	254.8	254.6	254.4	254.2	254.1	254.0
137.5°	272.5	272.2	271.9	271.6	271.3	271.1	270.8	270.5
140°	283.7	283.7	283.7	283.4	282.9	282.4	281.9	281.4
142.5°	294.4	294.3	294.3	294.0	293.6	293.3	292.8	292.5
145°	310.0	309.9	309.8	309.6	309.3	309.1	308.8	308.5
147.5°	324.7	324.7	324.7	324.4	324.0	323.6	323.2	322.7
150°	333.7	333.7	333.7	333.5	333.1	332.7	332.3	331.8
152.5°	342.0	342.1	342.2	342.1	341.7	341.3	341.0	340.6
155°	354.1	354.4	354.7	354.5	354.1	353.6	353.1	352.6
157.5°	364.5	364.9	365.2	365.1	364.7	364.4	363.9	363.6
160°	371.0	371.3	371.7	371.7	371.4	371.1	370.9	370.6
162.5°	377.0	377.4	377.7	377.6	377.2	376.7	376.3	375.9
165°	384.7	385.0	385.5	385.5	385.0	384.5	384.0	383.5
167.5°	390.8	391.3	391.7	391.7	391.3	390.8	390.4	390.0
170°	394.2	394.8	395.2	395.2	394.8	394.2	393.8	393.2
172.5°	396.9	397.3	397.8	397.8	397.3	396.8	396.3	395.8
175°	399.8	400.2	400.6	400.6	400.1	399.6	399.1	398.6
177.5°	401.1	401.4	401.7	401.7	401.4	400.9	400.6	400.1
180°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2

(END OF REPORT)