

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332374-935

Luminaire Tested: **S123RDIP-S1165D805U935-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332374-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D805U935-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6440.4 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66	61
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	57	53
2	93	85	80	75	86	80	75	71	71	67	63	62	59	56	53	51	50	46
3	85	76	69	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39
4	78	68	60	54	73	64	57	52	56	51	47	50	45	42	43	40	38	34
5	72	61	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	30
6	67	55	47	41	62	52	45	39	46	40	36	41	36	33	36	32	30	27
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24
8	57	45	38	32	54	43	36	31	39	33	29	34	30	26	30	27	24	22
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17016	17016	17016	17016
5°	20283	17088	15048	17088
10°	25326	16990	13595	16990
15°	29727	16817	12397	16817
20°	33176	16557	11379	16557
25°	32647	16284	10753	16284
30°	23467	16032	10110	16032
35°	15669	15704	9692	15704
40°	11545	15309	9261	15309
45°	9683	14618	8840	14618
50°	8544	13711	8251	13711
55°	7492	12675	7443	12675
60°	6674	11683	6818	11683
65°	5861	10618	6342	10618
70°	4601	9668	5794	9668
75°	4055	8442	5294	8442
80°	3521	7172	5201	7172
85°	2841	5768	5521	5768



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.5	2.4
10°-20°	485.7	7.5
20°-30°	763.0	11.8
30°-40°	796.1	12.4
40°-50°	681.2	10.6
50°-60°	519.2	8.1
60°-70°	332.8	5.2
70°-80°	160.1	2.5
80°-90°	44.9	0.7
90°-100°	185.1	2.9
100°-110°	524.0	8.1
110°-120°	515.5	8.0
120°-130°	411.2	6.4
130°-140°	324.2	5.0
140°-150°	242.0	3.8
150°-160°	168.6	2.6
160°-170°	99.1	1.5
170°-180°	32.2	0.5
0°-30°	1404.1	21.8
0°-40°	2200.2	34.2
0°-60°	3400.7	52.8
0°-90°	3938.5	61.2
90°-120°	1224.6	19.0
90°-150°	2201.9	34.2
90°-180°	2502.0	38.8
0°-180°	6440.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1877	1582	1393	1582	1877	194
15°	2668	1509	1112	1509	2668	756
25°	2749	1371	905	1371	2749	1181
35°	1192	1195	738	1195	1192	782
45°	636	960	581	960	636	500
55°	399	675	397	675	399	361
65°	230	417	249	417	230	226
75°	98	203	127	203	98	105
85°	23	47	45	47	23	27
90°	20	1	20	1	20	11
95°	78	23	78	23	78	141
105°	856	78	856	78	856	845
115°	1041	138	1041	138	1041	1012
125°	821	192	821	192	821	744
135°	666	225	666	225	666	516
145°	520	256	520	256	520	331
155°	431	291	431	291	431	201
165°	376	318	376	318	376	108
175°	339	332	339	332	339	33
180°	332	332	332	332	332	



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1683.7	1685.8	1678.8	1677.7	1669.6	1667.4	1667.4	1656.0	1649.0	1639.9	1634.4
5°	1877.2	1888.1	1882.7	1870.4	1850.1	1845.4	1832.6	1812.2	1789.2	1760.8	1747.3
7.5°	2118.9	2133.7	2128.0	2109.2	2087.9	2070.8	2034.5	2000.8	1953.5	1912.1	1876.6
10°	2317.1	2301.5	2289.3	2271.1	2251.4	2219.7	2181.8	2129.6	2069.4	2022.1	1969.3
12.5°	2465.4	2462.9	2447.4	2428.6	2400.9	2370.7	2324.1	2260.6	2190.6	2122.2	2061.8
15°	2667.6	2671.7	2661.5	2641.9	2602.6	2549.2	2478.8	2452.5	2352.3	2277.9	2203.4
17.5°	2807.5	2806.8	2805.4	2778.2	2738.2	2700.1	2634.8	2565.4	2474.8	2369.9	2269.6
20°	2896.3	2889.6	2891.0	2860.5	2830.7	2786.7	2723.1	2622.3	2547.9	2426.7	2323.2
22.5°	2894.2	2892.9	2898.0	2887.5	2865.9	2832.2	2782.1	2697.0	2602.0	2479.8	2363.3
25°	2748.8	2743.4	2775.3	2784.0	2818.6	2824.6	2809.7	2763.0	2673.1	2547.2	2403.1
27.5°	2300.6	2297.6	2356.6	2430.5	2524.2	2596.9	2667.4	2701.3	2673.1	2582.9	2438.5
30°	1888.1	1951.6	1981.4	2088.4	2207.4	2349.6	2474.1	2592.5	2621.6	2582.4	2463.9
32.5°	1567.5	1623.1	1648.0	1739.7	1850.7	2017.2	2203.9	2371.6	2490.1	2520.1	2448.8
35°	1192.4	1193.1	1249.9	1290.5	1393.4	1564.6	1745.9	1970.6	2193.9	2363.1	2380.7
37.5°	951.5	954.8	989.2	1029.7	1106.8	1197.4	1357.1	1543.9	1801.8	2061.6	2213.8
40°	821.6	827.6	853.3	893.3	948.7	1017.1	1141.6	1317.6	1532.8	1821.7	2057.9
42.5°	738.1	748.0	761.3	792.0	826.4	890.4	991.1	1127.0	1322.8	1595.9	1868.5
45°	636.1	641.5	651.7	665.9	697.0	741.7	809.3	900.7	1063.2	1283.1	1555.7
47.5°	561.1	558.3	568.9	580.5	601.2	631.6	677.0	751.6	867.5	1043.9	1275.2
50°	510.2	509.5	517.0	525.8	545.4	567.7	605.0	661.2	753.2	899.4	1111.2
52.5°	462.6	465.2	470.5	481.4	495.6	513.7	547.1	587.5	666.6	792.7	969.3
55°	399.2	401.3	408.7	414.8	425.0	443.2	464.3	498.1	552.2	640.2	785.7
57.5°	345.7	344.7	351.9	353.4	364.9	379.8	396.0	422.2	461.5	526.9	624.9
60°	310.0	307.9	314.0	318.7	324.9	337.0	350.5	376.3	407.4	455.5	539.3
62.5°	277.4	276.5	280.9	285.7	290.8	301.8	313.1	332.9	357.6	398.0	464.6
65°	230.1	232.1	234.1	236.2	238.8	245.6	256.5	270.0	287.0	315.4	363.4
67.5°	180.8	182.9	183.6	187.7	193.6	197.8	204.4	216.5	228.2	252.2	279.5
70°	146.2	145.5	146.2	148.2	155.7	163.1	171.9	180.7	188.1	205.0	228.1
72.5°	125.6	124.4	126.1	126.6	130.2	132.2	137.8	146.0	155.7	167.1	183.7
75°	97.5	97.5	97.5	97.5	100.1	101.5	103.6	105.6	108.9	114.3	126.6
77.5°	72.0	72.2	73.1	73.8	74.3	75.1	76.4	78.4	79.6	82.4	87.7
80°	56.8	57.5	56.8	57.5	57.5	58.9	59.6	61.6	62.3	65.6	67.7
82.5°	42.8	42.4	42.8	43.5	43.5	44.8	44.9	46.4	46.6	48.3	50.4
85°	23.0	21.7	23.0	22.3	23.7	22.3	23.0	24.4	24.4	25.1	27.7
87.5°	9.3	10.5	9.3	9.7	9.9	10.2	10.0	9.9	10.8	10.4	10.5
90°	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8	16.2	16.8	14.8
92.5°	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7	78.1	103.5	113.9
95°	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4	323.8	399.2	355.4
97.5°	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1	661.9	618.6	452.9
100°	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7	770.1	637.5	430.8
102.5°	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6	775.5	602.4	398.5
105°	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1	734.4	541.2	358.8
107.5°	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1	662.5	487.1	333.5
110°	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5	617.3	456.4	323.8



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3	578.0	435.9	318.4
115°	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0	530.5	414.0	316.4
117.5°	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9	501.8	401.1	317.6
120°	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6	486.7	395.1	319.8
122.5°	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7	474.3	391.4	323.5
125°	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1	458.4	386.4	329.2
127.5°	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0	444.4	384.0	335.6
130°	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5	436.9	382.4	339.9
132.5°	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0	429.9	381.8	343.2
135°	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8	420.7	381.0	348.0
137.5°	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3	412.8	379.5	351.3
140°	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5	407.9	379.0	353.4
142.5°	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4	403.6	377.9	355.0
145°	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4	397.9	376.3	356.1
147.5°	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4	392.2	373.8	356.1
150°	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9	388.4	371.6	356.1
152.5°	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0	384.1	368.9	354.5
155°	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1	377.6	364.2	352.8
157.5°	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6	370.4	360.0	350.4
160°	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3	365.5	356.8	349.4
162.5°	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8	360.7	353.5	347.2
165°	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5	354.0	348.7	344.0
167.5°	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1	347.8	343.9	340.8
170°	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3	344.0	340.6	338.6
172.5°	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0	340.2	337.9	337.0
175°	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3	335.9	334.6	334.6
177.5°	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1632.3	1630.6	1623.1	1614.4	1603.0	1595.4	1589.5	1586.2	1576.5	1564.6	1556.4
5°	1733.1	1712.8	1691.1	1664.7	1640.4	1615.3	1599.7	1581.5	1559.2	1534.1	1516.6
7.5°	1841.1	1801.3	1758.4	1714.2	1670.4	1631.2	1596.6	1566.8	1531.3	1495.4	1470.2
10°	1923.9	1865.7	1805.5	1743.9	1687.7	1635.0	1594.3	1554.4	1511.8	1470.5	1439.4
12.5°	1999.2	1922.5	1853.1	1777.4	1705.6	1642.5	1584.1	1537.1	1485.8	1441.8	1406.4
15°	2094.5	2015.9	1932.0	1817.0	1721.6	1641.8	1570.6	1509.1	1446.8	1392.7	1358.1
17.5°	2183.5	2065.4	1952.6	1856.7	1732.7	1632.9	1546.2	1472.6	1404.2	1346.8	1304.3
20°	2220.3	2105.9	1983.5	1861.0	1739.1	1627.5	1526.6	1445.4	1374.4	1309.4	1270.2
22.5°	2242.5	2113.0	1984.0	1852.4	1722.9	1607.0	1507.2	1417.9	1340.8	1279.1	1230.7
25°	2268.4	2114.1	1971.9	1842.0	1710.0	1584.2	1465.8	1371.1	1287.8	1222.2	1170.7
27.5°	2285.4	2103.9	1936.0	1791.6	1657.7	1532.3	1423.8	1323.4	1239.0	1169.5	1114.3
30°	2288.6	2095.8	1908.3	1752.0	1616.0	1501.0	1386.0	1289.9	1200.5	1126.7	1075.3
32.5°	2293.0	2075.8	1871.0	1705.0	1565.6	1451.7	1347.5	1255.7	1164.2	1091.6	1039.1
35°	2275.1	2064.7	1814.3	1623.4	1484.0	1373.7	1279.7	1195.1	1105.1	1034.7	981.3
37.5°	2198.2	2020.7	1755.6	1531.7	1386.0	1283.8	1207.1	1133.3	1050.9	974.9	924.5
40°	2120.8	1977.4	1710.0	1475.9	1323.7	1218.7	1149.8	1089.5	1009.7	938.6	884.5
42.5°	2005.5	1918.4	1666.7	1417.5	1253.3	1152.2	1094.0	1037.5	967.4	895.3	844.4
45°	1794.0	1805.5	1578.1	1324.3	1155.8	1054.3	999.5	960.3	898.0	838.4	786.4
47.5°	1528.7	1636.3	1474.0	1225.1	1053.1	957.9	909.9	875.6	833.7	775.2	727.7
50°	1355.5	1509.1	1390.7	1158.6	988.7	894.0	846.5	818.8	782.3	736.2	691.0
52.5°	1195.8	1360.7	1290.0	1084.3	918.9	832.2	785.9	763.1	734.1	690.8	649.8
55°	975.2	1142.3	1126.1	972.4	814.1	736.2	701.1	675.4	655.7	623.3	590.8
57.5°	788.8	947.3	955.6	847.9	721.8	644.9	614.6	595.2	582.4	557.9	527.9
60°	671.3	816.8	845.2	764.1	655.7	588.1	558.3	542.7	532.6	513.0	489.9
62.5°	573.9	697.7	729.9	671.4	592.4	529.1	505.8	490.8	483.9	466.9	446.6
65°	439.2	542.1	573.2	540.7	499.4	448.7	429.7	416.9	410.8	401.3	386.4
67.5°	330.3	405.2	439.4	416.5	401.6	369.5	357.4	350.5	345.1	338.6	326.1
70°	265.3	320.7	355.9	349.8	337.7	320.7	311.9	307.2	301.8	296.4	285.6
72.5°	213.3	251.5	284.5	287.6	277.6	274.2	266.5	264.5	261.2	254.7	248.7
75°	141.5	167.8	190.8	199.7	203.7	207.1	203.7	203.0	202.3	196.9	193.6
77.5°	92.7	106.9	121.4	136.5	142.8	147.4	148.4	150.9	149.1	146.3	144.6
80°	71.0	74.5	84.6	97.5	107.6	111.7	114.3	115.7	115.0	114.3	111.7
82.5°	51.6	54.4	59.2	68.2	76.7	83.5	85.2	84.9	86.4	86.8	84.6
85°	27.7	28.4	29.8	31.2	35.9	43.3	45.4	46.7	48.0	48.0	44.0
87.5°	11.2	10.2	10.9	10.7	12.1	12.1	15.2	17.6	18.4	16.5	16.9
90°	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4	2.7	4.0	6.0
92.5°	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4	12.4	18.1	23.3
95°	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9	24.9	32.3	43.7
97.5°	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0	39.7	45.5	55.4
100°	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9	50.5	55.2	64.7
102.5°	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1	62.3	66.5	75.4
105°	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1	80.1	84.1	92.2
107.5°	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1	98.2	102.0	109.9
110°	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1	111.1	114.4	121.8





TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9	123.0	126.3	133.7
115°	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0	140.7	144.7	151.4
117.5°	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1	158.2	161.5	167.7
120°	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9	168.9	172.3	179.1
122.5°	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2	179.2	182.5	189.9
125°	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8	193.2	197.3	204.7
127.5°	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0	205.0	210.0	217.6
130°	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0	212.1	218.1	226.2
132.5°	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4	218.0	224.5	234.3
135°	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8	227.6	235.0	245.0
137.5°	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7	236.5	243.8	254.6
140°	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6	243.0	249.8	260.5
142.5°	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1	248.9	256.2	265.9
145°	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5	258.5	264.6	274.7
147.5°	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0	268.2	274.1	282.8
150°	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0	274.7	280.0	288.8
152.5°	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9	281.1	286.5	294.2
155°	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4	291.4	295.5	302.2
157.5°	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8	300.3	303.6	309.5
160°	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3	306.3	309.0	314.4
162.5°	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2	311.2	313.3	317.6
165°	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4	317.7	319.1	322.4
167.5°	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9	323.1	323.8	326.3
170°	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2	325.8	326.5	328.5
172.5°	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3	328.5	328.6	330.1
175°	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8	331.2	330.5	331.8
177.5°	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0	332.5	332.0	332.5
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1553.8	1546.7	1541.9	1531.0	1524.0	1516.4	1508.8	1513.7	1513.1	1512.6	1512.6
5°	1501.7	1486.1	1471.9	1453.6	1442.1	1427.9	1417.0	1415.7	1418.4	1408.9	1403.5
7.5°	1449.9	1428.7	1408.5	1388.4	1367.0	1350.0	1339.2	1334.2	1327.3	1321.5	1315.4
10°	1413.7	1388.6	1369.0	1343.9	1320.9	1300.6	1287.8	1279.0	1274.3	1269.5	1260.8
12.5°	1376.3	1351.9	1326.8	1298.5	1276.6	1253.0	1243.4	1233.6	1224.4	1219.2	1207.1
15°	1321.6	1289.9	1263.4	1233.6	1209.3	1186.3	1172.8	1153.1	1150.4	1143.7	1131.4
17.5°	1266.8	1232.3	1195.9	1173.8	1146.3	1122.4	1101.8	1095.2	1075.8	1068.5	1058.0
20°	1223.5	1191.7	1164.0	1134.9	1094.9	1072.6	1056.4	1047.6	1032.0	1022.5	1015.7
22.5°	1186.1	1153.8	1121.7	1087.8	1054.9	1029.8	1018.0	1004.3	995.7	982.5	975.2
25°	1132.8	1097.6	1059.0	1022.5	998.8	979.9	961.0	948.7	936.6	930.5	917.0
27.5°	1070.8	1034.1	998.0	970.3	941.2	922.5	905.3	894.5	879.9	869.6	862.1
30°	1036.7	993.4	962.3	937.3	900.0	882.4	869.6	856.1	845.2	834.4	827.0
32.5°	997.2	957.7	928.2	897.2	868.7	849.4	832.8	820.9	811.7	801.3	793.9
35°	935.2	902.1	871.6	840.5	819.5	799.9	780.2	770.1	761.3	751.8	745.1
37.5°	879.2	848.2	819.2	789.7	763.7	747.8	731.9	724.2	712.3	705.9	699.0
40°	844.6	814.1	783.0	754.6	727.5	715.3	701.1	689.6	678.7	674.0	666.6
42.5°	806.7	776.2	749.9	719.4	697.2	680.6	667.5	655.0	646.8	639.9	635.7
45°	750.4	723.4	697.7	667.3	646.3	632.1	617.2	605.6	598.2	593.5	586.0
47.5°	695.9	668.9	642.7	616.2	595.9	579.7	564.8	556.8	546.9	541.1	536.1
50°	656.4	632.1	604.3	580.0	559.6	543.4	531.2	521.1	512.3	504.8	501.4
52.5°	620.2	594.2	570.2	547.4	526.1	507.6	496.5	485.9	479.2	470.7	466.8
55°	560.3	535.3	515.0	492.7	471.7	456.1	442.6	433.1	426.4	416.9	411.5
57.5°	504.1	481.7	457.4	438.1	416.5	403.3	392.1	379.3	371.0	363.5	358.3
60°	466.2	440.6	419.6	401.3	382.4	365.4	355.2	345.1	336.3	328.9	324.2
62.5°	426.7	404.2	384.4	364.5	347.2	332.4	320.6	312.1	304.4	299.6	294.9
65°	366.1	348.5	328.2	311.9	295.8	284.9	275.4	267.9	262.6	259.2	255.1
67.5°	310.3	293.3	275.5	259.6	248.7	240.5	234.3	227.9	225.2	220.8	218.2
70°	274.1	256.5	240.9	228.8	217.9	211.8	207.8	203.0	200.3	194.9	192.2
72.5°	234.5	221.8	210.6	200.6	191.9	186.4	181.2	175.4	171.1	165.1	162.4
75°	184.8	173.2	164.5	157.6	152.2	144.8	137.4	131.3	129.2	127.3	126.6
77.5°	136.8	129.5	123.1	117.4	110.7	105.3	103.7	102.3	101.9	100.8	100.8
80°	107.6	100.8	96.1	89.3	85.2	85.2	85.2	83.9	84.6	84.6	84.6
82.5°	80.0	73.8	71.2	68.8	67.9	68.4	68.4	68.8	68.4	69.4	68.9
85°	41.2	41.9	43.3	42.6	43.3	43.3	44.7	44.0	44.7	43.3	44.7
87.5°	16.6	18.5	19.5	20.4	21.4	21.3	21.6	21.8	22.5	22.6	22.8
90°	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8	17.5	18.2	19.5
92.5°	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7	44.9	39.7	36.2
95°	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4	164.3	128.5	104.4
97.5°	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1	483.9	397.0	316.5
100°	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7	739.1	660.4	564.7
102.5°	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6	854.9	809.0	748.4
105°	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1	942.4	955.2	937.7
107.5°	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1	931.3	990.3	1014.3
110°	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5	895.3	980.1	1027.3



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3	847.9	943.0	1003.5
115°	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0	772.1	871.1	944.4
117.5°	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9	708.0	796.9	871.3
120°	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6	672.4	753.3	821.2
122.5°	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7	643.9	718.8	782.0
125°	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1	608.6	673.1	727.0
127.5°	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0	577.4	635.8	684.8
130°	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5	558.0	612.6	658.3
132.5°	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0	539.8	590.5	634.1
135°	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8	513.6	557.3	595.7
137.5°	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3	488.4	526.2	559.4
140°	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5	473.9	506.2	535.1
142.5°	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4	459.9	487.9	513.1
145°	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4	441.6	463.1	482.7
147.5°	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4	428.0	445.4	459.3
150°	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9	419.4	433.5	446.3
152.5°	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0	411.3	423.8	434.5
155°	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1	399.8	409.9	418.0
157.5°	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6	388.7	396.5	402.8
160°	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3	381.7	388.4	393.1
162.5°	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8	374.1	380.3	384.5
165°	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5	363.5	368.2	371.6
167.5°	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1	355.2	358.0	360.4
170°	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3	349.4	352.1	353.4
172.5°	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0	344.5	346.6	347.5
175°	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3	337.9	339.2	339.2
177.5°	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6	334.2	334.7	334.7
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1506.1	1505.5	1506.1	1503.9	1506.1	1505.5	1506.1	1512.6	1512.6	1513.1	1513.7
5°	1401.4	1400.8	1398.8	1392.7	1398.8	1400.8	1401.4	1403.5	1408.9	1418.4	1415.7
7.5°	1310.1	1309.2	1303.2	1303.4	1303.2	1309.2	1310.1	1315.4	1321.5	1327.3	1334.2
10°	1256.0	1256.6	1248.5	1243.8	1248.5	1256.6	1256.0	1260.8	1269.5	1274.3	1279.0
12.5°	1203.5	1200.4	1193.9	1188.6	1193.9	1200.4	1203.5	1207.1	1219.2	1224.4	1233.6
15°	1134.2	1127.4	1111.2	1112.5	1111.2	1127.4	1134.2	1131.4	1143.7	1150.4	1153.1
17.5°	1052.6	1047.6	1047.3	1037.8	1047.3	1047.6	1052.6	1058.0	1068.5	1075.8	1095.2
20°	1005.0	1001.5	1002.9	993.4	1002.9	1001.5	1005.0	1015.7	1022.5	1032.0	1047.6
22.5°	967.6	964.1	958.5	955.5	958.5	964.1	967.6	975.2	982.5	995.7	1004.3
25°	912.9	907.5	902.1	905.4	902.1	907.5	912.9	917.0	930.5	936.6	948.7
27.5°	858.2	854.2	848.8	848.1	848.8	854.2	858.2	862.1	869.6	879.9	894.5
30°	823.5	819.5	816.8	813.4	816.8	819.5	823.5	827.0	834.4	845.2	856.1
32.5°	788.4	787.6	782.7	782.0	782.7	787.6	788.4	793.9	801.3	811.7	820.9
35°	742.4	738.3	736.9	737.6	736.9	738.3	742.4	745.1	751.8	761.3	770.1
37.5°	698.6	693.2	690.8	688.4	690.8	693.2	698.6	699.0	705.9	712.3	724.2
40°	667.3	661.9	660.5	659.1	660.5	661.9	667.3	666.6	674.0	678.7	689.6
42.5°	632.1	629.9	629.0	626.6	629.0	629.9	632.1	635.7	639.9	646.8	655.0
45°	584.0	583.3	579.3	580.7	579.3	583.3	584.0	586.0	593.5	598.2	605.6
47.5°	533.4	530.4	527.5	529.4	527.5	530.4	533.4	536.1	541.1	546.9	556.8
50°	498.8	497.4	491.3	492.7	491.3	497.4	498.8	501.4	504.8	512.3	521.1
52.5°	464.1	458.9	456.7	455.8	456.7	458.9	464.1	466.8	470.7	479.2	485.9
55°	406.7	400.6	397.9	396.6	397.9	400.6	406.7	411.5	416.9	426.4	433.1
57.5°	350.4	348.8	346.6	348.1	346.6	348.8	350.4	358.3	363.5	371.0	379.3
60°	317.4	317.4	317.4	316.7	317.4	317.4	317.4	324.2	328.9	336.3	345.1
62.5°	292.0	290.3	289.8	290.8	289.8	290.3	292.0	294.9	299.6	304.4	312.1
65°	253.1	252.4	249.7	249.0	249.7	252.4	253.1	255.1	259.2	262.6	267.9
67.5°	216.5	214.0	213.2	212.2	213.2	214.0	216.5	218.2	220.8	225.2	227.9
70°	188.8	187.4	183.4	184.1	183.4	187.4	188.8	192.2	194.9	200.3	203.0
72.5°	159.0	157.6	156.9	155.9	156.9	157.6	159.0	162.4	165.1	171.1	175.4
75°	125.9	125.2	124.5	127.3	124.5	125.2	125.9	126.6	127.3	129.2	131.3
77.5°	100.8	100.8	101.3	100.1	101.3	100.8	100.8	100.8	100.8	101.9	102.3
80°	84.6	84.6	83.9	83.9	83.9	84.6	84.6	84.6	84.6	84.6	83.9
82.5°	67.8	68.4	68.8	67.7	68.8	68.4	67.8	68.9	69.4	68.4	68.8
85°	44.7	44.0	45.4	44.7	45.4	44.0	44.7	44.7	43.3	44.7	44.0
87.5°	23.8	22.8	23.0	23.4	23.0	22.8	23.8	22.8	22.6	22.5	21.8
90°	18.9	19.5	20.2	19.5	20.2	19.5	18.9	19.5	18.2	17.5	16.8
92.5°	35.0	33.0	33.7	32.5	33.7	33.0	35.0	36.2	39.7	44.9	56.7
95°	91.5	85.5	80.8	78.1	80.8	85.5	91.5	104.4	128.5	164.3	242.4
97.5°	266.8	236.5	218.3	212.6	218.3	236.5	266.8	316.5	397.0	483.9	604.1
100°	496.8	447.6	421.4	422.1	421.4	447.6	496.8	564.7	660.4	739.1	793.7
102.5°	695.5	656.6	634.6	619.1	634.6	656.6	695.5	748.4	809.0	854.9	856.6
105°	906.7	881.1	859.6	856.3	859.6	881.1	906.7	937.7	955.2	942.4	875.1
107.5°	1014.9	1006.3	998.9	992.7	998.9	1006.3	1014.9	1014.3	990.3	931.3	822.1
110°	1046.0	1051.5	1050.1	1048.8	1050.1	1051.5	1046.0	1027.3	980.1	895.3	771.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1038.0	1054.7	1059.8	1060.1	1059.8	1054.7	1038.0	1003.5	943.0	847.9	721.3
115°	994.9	1024.5	1038.0	1041.4	1038.0	1024.5	994.9	944.4	871.1	772.1	655.0
117.5°	923.9	957.9	977.2	981.9	977.2	957.9	923.9	871.3	796.9	708.0	606.9
120°	874.4	912.1	928.2	932.3	928.2	912.1	874.4	821.2	753.3	672.4	581.6
122.5°	829.1	863.1	880.9	886.0	880.9	863.1	829.1	782.0	718.8	643.9	561.7
125°	770.1	799.7	816.5	821.2	816.5	799.7	770.1	727.0	673.1	608.6	535.1
127.5°	723.1	748.4	763.6	767.9	763.6	748.4	723.1	684.8	635.8	577.4	512.0
130°	694.1	718.2	732.4	737.8	732.4	718.2	694.1	658.3	612.6	558.0	497.5
132.5°	667.6	691.9	704.4	708.2	704.4	691.9	667.6	634.1	590.5	539.8	484.0
135°	628.7	648.9	661.0	665.7	661.0	648.9	628.7	595.7	557.3	513.6	465.8
137.5°	587.1	607.6	617.9	621.0	617.9	607.6	587.1	559.4	526.2	488.4	449.3
140°	560.8	579.5	590.4	589.7	590.4	579.5	560.8	535.1	506.2	473.9	439.5
142.5°	534.9	551.6	561.3	560.6	561.3	551.6	534.9	513.1	487.9	459.9	430.4
145°	499.5	513.6	519.0	520.3	519.0	513.6	499.5	482.7	463.1	441.6	419.4
147.5°	472.0	481.6	486.7	487.2	486.7	481.6	472.0	459.3	445.4	428.0	410.4
150°	456.4	463.8	467.9	467.9	467.9	463.8	456.4	446.3	433.5	419.4	403.9
152.5°	442.4	449.3	451.7	451.7	451.7	449.3	442.4	434.5	423.8	411.3	398.0
155°	424.0	429.5	430.8	431.4	430.8	429.5	424.0	418.0	409.9	399.8	389.1
157.5°	408.0	412.1	413.2	413.0	413.2	412.1	408.0	402.8	396.5	388.7	379.6
160°	397.9	401.8	401.8	401.2	401.8	401.8	397.9	393.1	388.4	381.7	374.3
162.5°	387.6	391.1	391.1	390.5	391.1	391.1	387.6	384.5	380.3	374.1	367.8
165°	374.3	376.9	376.3	376.3	376.3	376.9	374.3	371.6	368.2	363.5	359.5
167.5°	361.6	363.5	362.8	362.8	362.8	363.5	361.6	360.4	358.0	355.2	352.1
170°	354.0	355.4	354.7	354.7	354.7	355.4	354.0	353.4	352.1	349.4	347.3
172.5°	347.6	349.0	347.8	347.2	347.8	349.0	347.6	347.5	346.6	344.5	343.0
175°	339.2	339.9	339.2	338.6	339.2	339.9	339.2	339.2	339.2	337.9	337.3
177.5°	334.2	334.7	333.6	333.6	333.6	334.7	334.2	334.7	334.7	334.2	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1508.8	1516.4	1524.0	1531.0	1541.9	1546.7	1553.8	1556.4	1564.6	1576.5	1586.2
5°	1417.0	1427.9	1442.1	1453.6	1471.9	1486.1	1501.7	1516.6	1534.1	1559.2	1581.5
7.5°	1339.2	1350.0	1367.0	1388.4	1408.5	1428.7	1449.9	1470.2	1495.4	1531.3	1566.8
10°	1287.8	1300.6	1320.9	1343.9	1369.0	1388.6	1413.7	1439.4	1470.5	1511.8	1554.4
12.5°	1243.4	1253.0	1276.6	1298.5	1326.8	1351.9	1376.3	1406.4	1441.8	1485.8	1537.1
15°	1172.8	1186.3	1209.3	1233.6	1263.4	1289.9	1321.6	1358.1	1392.7	1446.8	1509.1
17.5°	1101.8	1122.4	1146.3	1173.8	1195.9	1232.3	1266.8	1304.3	1346.8	1404.2	1472.6
20°	1056.4	1072.6	1094.9	1134.9	1164.0	1191.7	1223.5	1270.2	1309.4	1374.4	1445.4
22.5°	1018.0	1029.8	1054.9	1087.8	1121.7	1153.8	1186.1	1230.7	1279.1	1340.8	1417.9
25°	961.0	979.9	998.8	1022.5	1059.0	1097.6	1132.8	1170.7	1222.2	1287.8	1371.1
27.5°	905.3	922.5	941.2	970.3	998.0	1034.1	1070.8	1114.3	1169.5	1239.0	1323.4
30°	869.6	882.4	900.0	937.3	962.3	993.4	1036.7	1075.3	1126.7	1200.5	1289.9
32.5°	832.8	849.4	868.7	897.2	928.2	957.7	997.2	1039.1	1091.6	1164.2	1255.7
35°	780.2	799.9	819.5	840.5	871.6	902.1	935.2	981.3	1034.7	1105.1	1195.1
37.5°	731.9	747.8	763.7	789.7	819.2	848.2	879.2	924.5	974.9	1050.9	1133.3
40°	701.1	715.3	727.5	754.6	783.0	814.1	844.6	884.5	938.6	1009.7	1089.5
42.5°	667.5	680.6	697.2	719.4	749.9	776.2	806.7	844.4	895.3	967.4	1037.5
45°	617.2	632.1	646.3	667.3	697.7	723.4	750.4	786.4	838.4	898.0	960.3
47.5°	564.8	579.7	595.9	616.2	642.7	668.9	695.9	727.7	775.2	833.7	875.6
50°	531.2	543.4	559.6	580.0	604.3	632.1	656.4	691.0	736.2	782.3	818.8
52.5°	496.5	507.6	526.1	547.4	570.2	594.2	620.2	649.8	690.8	734.1	763.1
55°	442.6	456.1	471.7	492.7	515.0	535.3	560.3	590.8	623.3	655.7	675.4
57.5°	392.1	403.3	416.5	438.1	457.4	481.7	504.1	527.9	557.9	582.4	595.2
60°	355.2	365.4	382.4	401.3	419.6	440.6	466.2	489.9	513.0	532.6	542.7
62.5°	320.6	332.4	347.2	364.5	384.4	404.2	426.7	446.6	466.9	483.9	490.8
65°	275.4	284.9	295.8	311.9	328.2	348.5	366.1	386.4	401.3	410.8	416.9
67.5°	234.3	240.5	248.7	259.6	275.5	293.3	310.3	326.1	338.6	345.1	350.5
70°	207.8	211.8	217.9	228.8	240.9	256.5	274.1	285.6	296.4	301.8	307.2
72.5°	181.2	186.4	191.9	200.6	210.6	221.8	234.5	248.7	254.7	261.2	264.5
75°	137.4	144.8	152.2	157.6	164.5	173.2	184.8	193.6	196.9	202.3	203.0
77.5°	103.7	105.3	110.7	117.4	123.1	129.5	136.8	144.6	146.3	149.1	150.9
80°	85.2	85.2	85.2	89.3	96.1	100.8	107.6	111.7	114.3	115.0	115.7
82.5°	68.4	68.4	67.9	68.8	71.2	73.8	80.0	84.6	86.8	86.4	84.9
85°	44.7	43.3	43.3	42.6	43.3	41.9	41.2	44.0	48.0	48.0	46.7
87.5°	21.6	21.3	21.4	20.4	19.5	18.5	16.6	16.9	16.5	18.4	17.6
90°	16.2	16.8	14.8	12.8	10.8	8.8	7.4	6.0	4.0	2.7	1.4
92.5°	78.1	103.5	113.9	85.5	56.6	38.9	28.9	23.3	18.1	12.4	8.4
95°	323.8	399.2	355.4	245.0	144.7	87.5	61.2	43.7	32.3	24.9	22.9
97.5°	661.9	618.6	452.9	268.9	155.8	101.1	72.7	55.4	45.5	39.7	39.0
100°	770.1	637.5	430.8	253.7	154.1	107.0	80.8	64.7	55.2	50.5	49.9
102.5°	775.5	602.4	398.5	240.8	156.3	114.0	90.0	75.4	66.5	62.3	61.1
105°	734.4	541.2	358.8	231.5	162.2	125.9	105.0	92.2	84.1	80.1	78.1
107.5°	662.5	487.1	333.5	230.9	173.2	141.4	122.0	109.9	102.0	98.2	96.1
110°	617.3	456.4	323.8	233.6	182.4	152.1	133.3	121.8	114.4	111.1	109.1



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	578.0	435.9	318.4	238.9	191.6	163.4	145.2	133.7	126.3	123.0	120.9
115°	530.5	414.0	316.4	247.7	206.6	181.1	162.9	151.4	144.7	140.7	138.0
117.5°	501.8	401.1	317.6	259.3	222.7	197.3	180.6	167.7	161.5	158.2	155.1
120°	486.7	395.1	319.8	267.9	232.9	208.7	191.8	179.1	172.3	168.9	166.9
122.5°	474.3	391.4	323.5	276.0	243.7	220.0	202.1	189.9	182.5	179.2	177.2
125°	458.4	386.4	329.2	288.8	259.2	235.6	217.4	204.7	197.3	193.2	191.8
127.5°	444.4	384.0	335.6	299.3	272.6	249.9	231.7	217.6	210.0	205.0	203.0
130°	436.9	382.4	339.9	306.3	280.7	258.5	240.3	226.2	218.1	212.1	210.0
132.5°	429.9	381.8	343.2	312.7	287.7	266.0	248.4	234.3	224.5	218.0	215.4
135°	420.7	381.0	348.0	321.1	298.2	277.3	259.2	245.0	235.0	227.6	224.8
137.5°	412.8	379.5	351.3	327.3	305.5	285.4	268.5	254.6	243.8	236.5	233.7
140°	407.9	379.0	353.4	330.5	310.3	290.8	274.0	260.5	249.8	243.0	239.6
142.5°	403.6	377.9	355.0	333.7	314.1	295.1	279.4	265.9	256.2	248.9	246.1
145°	397.9	376.3	356.1	337.3	319.1	301.6	286.1	274.7	264.6	258.5	256.5
147.5°	392.2	373.8	356.1	339.4	323.1	307.1	293.9	282.8	274.1	268.2	267.0
150°	388.4	371.6	356.1	339.9	325.8	310.3	298.2	288.8	280.0	274.7	274.0
152.5°	384.1	368.9	354.5	341.0	327.4	314.1	302.5	294.2	286.5	281.1	280.9
155°	377.6	364.2	352.8	341.3	330.5	319.1	309.6	302.2	295.5	291.4	291.4
157.5°	370.4	360.0	350.4	342.0	332.3	323.1	315.8	309.5	303.6	300.3	299.8
160°	365.5	356.8	349.4	342.0	333.9	325.8	319.1	314.4	309.0	306.3	306.3
162.5°	360.7	353.5	347.2	341.4	334.4	327.4	321.8	317.6	313.3	311.2	311.2
165°	354.0	348.7	344.0	339.9	335.2	329.8	325.1	322.4	319.1	317.7	318.4
167.5°	347.8	343.9	340.8	338.9	335.1	331.2	328.2	326.3	323.8	323.1	323.9
170°	344.0	340.6	338.6	337.3	334.6	331.2	329.8	328.5	326.5	325.8	327.2
172.5°	340.2	337.9	337.0	336.7	334.6	331.7	330.9	330.1	328.6	328.5	329.3
175°	335.9	334.6	334.6	335.2	333.9	332.5	331.8	331.8	330.5	331.2	331.8
177.5°	333.0	332.5	333.0	334.2	333.0	332.5	332.5	332.5	332.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1589.5	1595.4	1603.0	1614.4	1623.1	1630.6	1632.3	1634.4	1639.9	1649.0	1656.0
5°	1599.7	1615.3	1640.4	1664.7	1691.1	1712.8	1733.1	1747.3	1760.8	1789.2	1812.2
7.5°	1596.6	1631.2	1670.4	1714.2	1758.4	1801.3	1841.1	1876.6	1912.1	1953.5	2000.8
10°	1594.3	1635.0	1687.7	1743.9	1805.5	1865.7	1923.9	1969.3	2022.1	2069.4	2129.6
12.5°	1584.1	1642.5	1705.6	1777.4	1853.1	1922.5	1999.2	2061.8	2122.2	2190.6	2260.6
15°	1570.6	1641.8	1721.6	1817.0	1932.0	2015.9	2094.5	2203.4	2277.9	2352.3	2452.5
17.5°	1546.2	1632.9	1732.7	1856.7	1952.6	2065.4	2183.5	2269.6	2369.9	2474.8	2565.4
20°	1526.6	1627.5	1739.1	1861.0	1983.5	2105.9	2220.3	2323.2	2426.7	2547.9	2622.3
22.5°	1507.2	1607.0	1722.9	1852.4	1984.0	2113.0	2242.5	2363.3	2479.8	2602.0	2697.0
25°	1465.8	1584.2	1710.0	1842.0	1971.9	2114.1	2268.4	2403.1	2547.2	2673.1	2763.0
27.5°	1423.8	1532.3	1657.7	1791.6	1936.0	2103.9	2285.4	2438.5	2582.9	2673.1	2701.3
30°	1386.0	1501.0	1616.0	1752.0	1908.3	2095.8	2288.6	2463.9	2582.4	2621.6	2592.5
32.5°	1347.5	1451.7	1565.6	1705.0	1871.0	2075.8	2293.0	2448.8	2520.1	2490.1	2371.6
35°	1279.7	1373.7	1484.0	1623.4	1814.3	2064.7	2275.1	2380.7	2363.1	2193.9	1970.6
37.5°	1207.1	1283.8	1386.0	1531.7	1755.6	2020.7	2198.2	2213.8	2061.6	1801.8	1543.9
40°	1149.8	1218.7	1323.7	1475.9	1710.0	1977.4	2120.8	2057.9	1821.7	1532.8	1317.6
42.5°	1094.0	1152.2	1253.3	1417.5	1666.7	1918.4	2005.5	1868.5	1595.9	1322.8	1127.0
45°	999.5	1054.3	1155.8	1324.3	1578.1	1805.5	1794.0	1555.7	1283.1	1063.2	900.7
47.5°	909.9	957.9	1053.1	1225.1	1474.0	1636.3	1528.7	1275.2	1043.9	867.5	751.6
50°	846.5	894.0	988.7	1158.6	1390.7	1509.1	1355.5	1111.2	899.4	753.2	661.2
52.5°	785.9	832.2	918.9	1084.3	1290.0	1360.7	1195.8	969.3	792.7	666.6	587.5
55°	701.1	736.2	814.1	972.4	1126.1	1142.3	975.2	785.7	640.2	552.2	498.1
57.5°	614.6	644.9	721.8	847.9	955.6	947.3	788.8	624.9	526.9	461.5	422.2
60°	558.3	588.1	655.7	764.1	845.2	816.8	671.3	539.3	455.5	407.4	376.3
62.5°	505.8	529.1	592.4	671.4	729.9	697.7	573.9	464.6	398.0	357.6	332.9
65°	429.7	448.7	499.4	540.7	573.2	542.1	439.2	363.4	315.4	287.0	270.0
67.5°	357.4	369.5	401.6	416.5	439.4	405.2	330.3	279.5	252.2	228.2	216.5
70°	311.9	320.7	337.7	349.8	355.9	320.7	265.3	228.1	205.0	188.1	180.7
72.5°	266.5	274.2	277.6	287.6	284.5	251.5	213.3	183.7	167.1	155.7	146.0
75°	203.7	207.1	203.7	199.7	190.8	167.8	141.5	126.6	114.3	108.9	105.6
77.5°	148.4	147.4	142.8	136.5	121.4	106.9	92.7	87.7	82.4	79.6	78.4
80°	114.3	111.7	107.6	97.5	84.6	74.5	71.0	67.7	65.6	62.3	61.6
82.5°	85.2	83.5	76.7	68.2	59.2	54.4	51.6	50.4	48.3	46.6	46.4
85°	45.4	43.3	35.9	31.2	29.8	28.4	27.7	27.7	25.1	24.4	24.4
87.5°	15.2	12.1	12.1	10.7	10.9	10.2	11.2	10.5	10.4	10.8	9.9
90°	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2	16.8
92.5°	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1	56.7
95°	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8	242.4
97.5°	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9	604.1
100°	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1	793.7
102.5°	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5	856.6
105°	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4	875.1
107.5°	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5	822.1
110°	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3	771.5





TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0	721.3
115°	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5	655.0
117.5°	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8	606.9
120°	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7	581.6
122.5°	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3	561.7
125°	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4	535.1
127.5°	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4	512.0
130°	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9	497.5
132.5°	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9	484.0
135°	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7	465.8
137.5°	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8	449.3
140°	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9	439.5
142.5°	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6	430.4
145°	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9	419.4
147.5°	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2	410.4
150°	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4	403.9
152.5°	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1	398.0
155°	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6	389.1
157.5°	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4	379.6
160°	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5	374.3
162.5°	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7	367.8
165°	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0	359.5
167.5°	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8	352.1
170°	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0	347.3
172.5°	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2	343.0
175°	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9	337.3
177.5°	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1667.4	1667.4	1669.6	1677.7	1678.8	1685.8	1683.7
5°	1832.6	1845.4	1850.1	1870.4	1882.7	1888.1	1877.2
7.5°	2034.5	2070.8	2087.9	2109.2	2128.0	2133.7	2118.9
10°	2181.8	2219.7	2251.4	2271.1	2289.3	2301.5	2317.1
12.5°	2324.1	2370.7	2400.9	2428.6	2447.4	2462.9	2465.4
15°	2478.8	2549.2	2602.6	2641.9	2661.5	2671.7	2667.6
17.5°	2634.8	2700.1	2738.2	2778.2	2805.4	2806.8	2807.5
20°	2723.1	2786.7	2830.7	2860.5	2891.0	2889.6	2896.3
22.5°	2782.1	2832.2	2865.9	2887.5	2898.0	2892.9	2894.2
25°	2809.7	2824.6	2818.6	2784.0	2775.3	2743.4	2748.8
27.5°	2667.4	2596.9	2524.2	2430.5	2356.6	2297.6	2300.6
30°	2474.1	2349.6	2207.4	2088.4	1981.4	1951.6	1888.1
32.5°	2203.9	2017.2	1850.7	1739.7	1648.0	1623.1	1567.5
35°	1745.9	1564.6	1393.4	1290.5	1249.9	1193.1	1192.4
37.5°	1357.1	1197.4	1106.8	1029.7	989.2	954.8	951.5
40°	1141.6	1017.1	948.7	893.3	853.3	827.6	821.6
42.5°	991.1	890.4	826.4	792.0	761.3	748.0	738.1
45°	809.3	741.7	697.0	665.9	651.7	641.5	636.1
47.5°	677.0	631.6	601.2	580.5	568.9	558.3	561.1
50°	605.0	567.7	545.4	525.8	517.0	509.5	510.2
52.5°	547.1	513.7	495.6	481.4	470.5	465.2	462.6
55°	464.3	443.2	425.0	414.8	408.7	401.3	399.2
57.5°	396.0	379.8	364.9	353.4	351.9	344.7	345.7
60°	350.5	337.0	324.9	318.7	314.0	307.9	310.0
62.5°	313.1	301.8	290.8	285.7	280.9	276.5	277.4
65°	256.5	245.6	238.8	236.2	234.1	232.1	230.1
67.5°	204.4	197.8	193.6	187.7	183.6	182.9	180.8
70°	171.9	163.1	155.7	148.2	146.2	145.5	146.2
72.5°	137.8	132.2	130.2	126.6	126.1	124.4	125.6
75°	103.6	101.5	100.1	97.5	97.5	97.5	97.5
77.5°	76.4	75.1	74.3	73.8	73.1	72.2	72.0
80°	59.6	58.9	57.5	57.5	56.8	57.5	56.8
82.5°	44.9	44.8	43.5	43.5	42.8	42.4	42.8
85°	23.0	22.3	23.7	22.3	23.0	21.7	23.0
87.5°	10.0	10.2	9.9	9.7	9.3	10.5	9.3
90°	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8



TEST NUMBER: P332374-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)