

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332377-935

Luminaire Tested: **S123RDIP-S1165D805U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332377-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D805U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6274.3 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	75	67	62	78	70	64	58	62	57	52	54	50	47	46	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	40	33	28	49	38	31	27	34	29	25	30	26	22	27	23	20
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.7	2.5
10°-20°	436.0	6.9
20°-30°	627.8	10.0
30°-40°	707.2	11.3
40°-50°	676.5	10.8
50°-60°	554.0	8.8
60°-70°	373.8	6.0
70°-80°	188.1	3.0
80°-90°	52.3	0.8
90°-100°	185.1	2.9
100°-110°	524.0	8.4
110°-120°	515.5	8.2
120°-130°	411.2	6.6
130°-140°	324.2	5.2
140°-150°	242.0	3.9
150°-160°	168.6	2.7
160°-170°	99.1	1.6
170°-180°	32.2	0.5
0°-30°	1220.5	19.5
0°-40°	1927.7	30.7
0°-60°	3158.3	50.3
0°-90°	3772.4	60.1
90°-120°	1224.6	19.5
90°-150°	2201.9	35.1
90°-180°	2502.0	39.9
0°-180°	6274.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	1	8	17	19	20	5
95°	23	74	399	116	78	25
105°	78	115	541	946	856	83
115°	138	172	414	908	1041	137
125°	192	226	386	700	821	170
135°	225	268	381	576	666	174
145°	256	294	376	473	520	161
155°	291	314	364	414	431	134
165°	318	327	349	370	376	90
175°	332	332	335	339	339	32
180°	332	332	332	332	332	



TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.3	23.8	21.5	19.3	16.9	15.8	16.2	16.6	17.0	17.5	17.0
90°	1.4	2.7	4.0	6.0	7.4	8.8	10.8	12.8	14.8	16.8	16.2
92.5°	8.4	12.4	18.1	23.3	28.9	38.9	56.6	85.5	113.9	103.5	78.1
95°	22.9	24.9	32.3	43.7	61.2	87.5	144.7	245.0	355.4	399.2	323.8
97.5°	39.0	39.7	45.5	55.4	72.7	101.1	155.8	268.9	452.9	618.6	661.9
100°	49.9	50.5	55.2	64.7	80.8	107.0	154.1	253.7	430.8	637.5	770.1
102.5°	61.1	62.3	66.5	75.4	90.0	114.0	156.3	240.8	398.5	602.4	775.5
105°	78.1	80.1	84.1	92.2	105.0	125.9	162.2	231.5	358.8	541.2	734.4
107.5°	96.1	98.2	102.0	109.9	122.0	141.4	173.2	230.9	333.5	487.1	662.5
110°	109.1	111.1	114.4	121.8	133.3	152.1	182.4	233.6	323.8	456.4	617.3



TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	120.9	123.0	126.3	133.7	145.2	163.4	191.6	238.9	318.4	435.9	578.0
115°	138.0	140.7	144.7	151.4	162.9	181.1	206.6	247.7	316.4	414.0	530.5
117.5°	155.1	158.2	161.5	167.7	180.6	197.3	222.7	259.3	317.6	401.1	501.8
120°	166.9	168.9	172.3	179.1	191.8	208.7	232.9	267.9	319.8	395.1	486.7
122.5°	177.2	179.2	182.5	189.9	202.1	220.0	243.7	276.0	323.5	391.4	474.3
125°	191.8	193.2	197.3	204.7	217.4	235.6	259.2	288.8	329.2	386.4	458.4
127.5°	203.0	205.0	210.0	217.6	231.7	249.9	272.6	299.3	335.6	384.0	444.4
130°	210.0	212.1	218.1	226.2	240.3	258.5	280.7	306.3	339.9	382.4	436.9
132.5°	215.4	218.0	224.5	234.3	248.4	266.0	287.7	312.7	343.2	381.8	429.9
135°	224.8	227.6	235.0	245.0	259.2	277.3	298.2	321.1	348.0	381.0	420.7
137.5°	233.7	236.5	243.8	254.6	268.5	285.4	305.5	327.3	351.3	379.5	412.8
140°	239.6	243.0	249.8	260.5	274.0	290.8	310.3	330.5	353.4	379.0	407.9
142.5°	246.1	248.9	256.2	265.9	279.4	295.1	314.1	333.7	355.0	377.9	403.6
145°	256.5	258.5	264.6	274.7	286.1	301.6	319.1	337.3	356.1	376.3	397.9
147.5°	267.0	268.2	274.1	282.8	293.9	307.1	323.1	339.4	356.1	373.8	392.2
150°	274.0	274.7	280.0	288.8	298.2	310.3	325.8	339.9	356.1	371.6	388.4
152.5°	280.9	281.1	286.5	294.2	302.5	314.1	327.4	341.0	354.5	368.9	384.1
155°	291.4	291.4	295.5	302.2	309.6	319.1	330.5	341.3	352.8	364.2	377.6
157.5°	299.8	300.3	303.6	309.5	315.8	323.1	332.3	342.0	350.4	360.0	370.4
160°	306.3	306.3	309.0	314.4	319.1	325.8	333.9	342.0	349.4	356.8	365.5
162.5°	311.2	311.2	313.3	317.6	321.8	327.4	334.4	341.4	347.2	353.5	360.7
165°	318.4	317.7	319.1	322.4	325.1	329.8	335.2	339.9	344.0	348.7	354.0
167.5°	323.9	323.1	323.8	326.3	328.2	331.2	335.1	338.9	340.8	343.9	347.8
170°	327.2	325.8	326.5	328.5	329.8	331.2	334.6	337.3	338.6	340.6	344.0
172.5°	329.3	328.5	328.6	330.1	330.9	331.7	334.6	336.7	337.0	337.9	340.2
175°	331.8	331.2	330.5	331.8	331.8	332.5	333.9	335.2	334.6	334.6	335.9
177.5°	333.0	332.5	332.0	332.5	332.5	332.5	333.0	334.2	333.0	332.5	333.0
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5



TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	17.0	16.9	16.8	16.8	16.4	16.3	16.2	15.8
90°	16.8	17.5	18.2	19.5	18.9	19.5	20.2	19.5
92.5°	56.7	44.9	39.7	36.2	35.0	33.0	33.7	32.5
95°	242.4	164.3	128.5	104.4	91.5	85.5	80.8	78.1
97.5°	604.1	483.9	397.0	316.5	266.8	236.5	218.3	212.6
100°	793.7	739.1	660.4	564.7	496.8	447.6	421.4	422.1
102.5°	856.6	854.9	809.0	748.4	695.5	656.6	634.6	619.1
105°	875.1	942.4	955.2	937.7	906.7	881.1	859.6	856.3
107.5°	822.1	931.3	990.3	1014.3	1014.9	1006.3	998.9	992.7
110°	771.5	895.3	980.1	1027.3	1046.0	1051.5	1050.1	1048.8





TEST NUMBER: P332377-935

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.3	847.9	943.0	1003.5	1038.0	1054.7	1059.8	1060.1
115°	655.0	772.1	871.1	944.4	994.9	1024.5	1038.0	1041.4
117.5°	606.9	708.0	796.9	871.3	923.9	957.9	977.2	981.9
120°	581.6	672.4	753.3	821.2	874.4	912.1	928.2	932.3
122.5°	561.7	643.9	718.8	782.0	829.1	863.1	880.9	886.0
125°	535.1	608.6	673.1	727.0	770.1	799.7	816.5	821.2
127.5°	512.0	577.4	635.8	684.8	723.1	748.4	763.6	767.9
130°	497.5	558.0	612.6	658.3	694.1	718.2	732.4	737.8
132.5°	484.0	539.8	590.5	634.1	667.6	691.9	704.4	708.2
135°	465.8	513.6	557.3	595.7	628.7	648.9	661.0	665.7
137.5°	449.3	488.4	526.2	559.4	587.1	607.6	617.9	621.0
140°	439.5	473.9	506.2	535.1	560.8	579.5	590.4	589.7
142.5°	430.4	459.9	487.9	513.1	534.9	551.6	561.3	560.6
145°	419.4	441.6	463.1	482.7	499.5	513.6	519.0	520.3
147.5°	410.4	428.0	445.4	459.3	472.0	481.6	486.7	487.2
150°	403.9	419.4	433.5	446.3	456.4	463.8	467.9	467.9
152.5°	398.0	411.3	423.8	434.5	442.4	449.3	451.7	451.7
155°	389.1	399.8	409.9	418.0	424.0	429.5	430.8	431.4
157.5°	379.6	388.7	396.5	402.8	408.0	412.1	413.2	413.0
160°	374.3	381.7	388.4	393.1	397.9	401.8	401.8	401.2
162.5°	367.8	374.1	380.3	384.5	387.6	391.1	391.1	390.5
165°	359.5	363.5	368.2	371.6	374.3	376.9	376.3	376.3
167.5°	352.1	355.2	358.0	360.4	361.6	363.5	362.8	362.8
170°	347.3	349.4	352.1	353.4	354.0	355.4	354.7	354.7
172.5°	343.0	344.5	346.6	347.5	347.6	349.0	347.8	347.2
175°	337.3	337.9	339.2	339.2	339.2	339.9	339.2	338.6
177.5°	333.6	334.2	334.7	334.7	334.2	334.7	333.6	333.6
180°	332.5	332.5	332.5	332.5	332.5	332.5	332.5	332.5

(END OF REPORT)