

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332346-940

Luminaire Tested: **S123RDIP-S1000D805U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332346-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5842.2 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	55	54	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	66	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	61	50	43	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.4
10°-20°	391.0	6.7
20°-30°	563.0	9.6
30°-40°	634.1	10.9
40°-50°	606.7	10.4
50°-60°	496.8	8.5
60°-70°	335.2	5.7
70°-80°	168.6	2.9
80°-90°	47.2	0.8
90°-100°	57.8	1.0
100°-110°	173.1	3.0
110°-120°	294.3	5.0
120°-130°	387.1	6.6
130°-140°	435.1	7.4
140°-150°	427.7	7.3
150°-160°	360.1	6.2
160°-170°	239.7	4.1
170°-180°	83.9	1.4
0°-30°	1094.5	18.7
0°-40°	1728.6	29.6
0°-60°	2832.1	48.5
0°-90°	3383.2	57.9
90°-120°	525.2	9.0
90°-150°	1775.2	30.4
90°-180°	2459.0	42.1
0°-180°	5842.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	8	17	19	21	6
95°	41	46	52	54	54	46
105°	157	159	164	165	166	168
115°	296	298	297	298	297	293
125°	434	436	434	432	429	387
135°	563	567	566	563	562	433
145°	682	684	686	685	682	426
155°	782	782	782	785	780	360
165°	851	849	849	853	848	240
175°	885	883	883	886	882	84
180°	888	888	888	888	888	



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.4	19.4	17.2	15.2	14.4	14.8	15.2	15.6	16.0	15.9
90°	0.7	2.2	3.8	5.4	6.9	8.6	10.7	12.7	14.7	16.8	17.4
92.5°	16.9	17.9	19.0	20.1	21.0	22.2	23.4	24.5	25.6	26.8	27.3
95°	41.1	42.2	43.3	44.4	45.5	46.6	47.9	49.1	50.4	51.6	52.3
97.5°	73.0	73.8	74.6	75.4	76.3	77.1	78.0	78.9	79.8	80.7	81.4
100°	94.8	95.8	96.7	97.6	98.5	99.4	100.1	100.9	101.7	102.5	103.0
102.5°	119.9	120.5	121.0	121.6	122.2	123.0	123.9	125.0	126.0	127.1	127.5
105°	156.9	157.2	157.5	157.8	158.1	159.0	160.3	161.8	163.2	164.5	164.5
107.5°	199.8	200.0	200.2	200.4	200.5	200.9	201.5	202.1	202.6	203.1	203.7
110°	226.6	226.9	227.2	227.5	227.8	228.1	228.5	228.7	229.1	229.3	230.0



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	254.5	254.7	254.9	255.0	255.2	255.3	255.4	255.5	255.6	255.6	256.4
115°	296.3	296.8	297.2	297.7	298.2	298.3	297.9	297.7	297.3	297.0	297.1
117.5°	338.4	338.8	339.0	339.3	339.7	339.6	339.2	338.8	338.4	338.0	338.0
120°	364.6	365.5	366.5	367.4	368.4	368.5	367.7	366.8	366.1	365.3	365.2
122.5°	392.0	392.6	393.3	394.0	394.7	394.8	394.4	394.0	393.6	393.2	392.8
125°	433.6	434.1	434.5	435.1	435.5	435.6	435.2	435.0	434.6	434.4	433.7
127.5°	472.2	473.1	474.1	475.1	476.1	476.4	476.1	475.7	475.4	475.0	474.2
130°	497.8	499.0	500.2	501.5	502.7	503.1	502.7	502.2	501.8	501.2	500.6
132.5°	523.4	524.7	525.9	527.2	528.4	528.9	528.5	528.2	527.8	527.4	526.7
135°	562.6	563.6	564.5	565.4	566.3	566.8	566.6	566.4	566.2	566.1	565.5
137.5°	598.9	599.7	600.4	601.2	602.0	602.5	603.0	603.3	603.8	604.1	603.5
140°	623.9	624.7	625.5	626.3	627.1	627.5	627.7	627.9	628.0	628.1	628.0
142.5°	646.8	647.6	648.4	649.2	650.0	650.5	650.8	651.0	651.3	651.6	651.4
145°	682.5	682.9	683.1	683.5	683.8	684.1	684.7	685.1	685.5	686.0	685.9
147.5°	713.8	714.3	714.9	715.4	716.0	716.5	716.9	717.4	717.8	718.3	718.3
150°	735.5	735.8	736.1	736.5	736.7	737.1	737.4	737.7	738.0	738.3	738.3
152.5°	753.4	753.8	754.2	754.7	755.1	755.5	755.6	755.8	756.0	756.2	756.4
155°	781.5	781.5	781.5	781.5	781.5	781.6	781.8	781.9	782.1	782.2	782.8
157.5°	805.5	805.3	805.1	804.9	804.8	804.8	804.9	805.0	805.1	805.2	805.9
160°	820.6	820.3	819.9	819.7	819.3	819.2	819.2	819.2	819.2	819.2	819.9
162.5°	833.9	833.6	833.1	832.7	832.2	832.1	832.2	832.3	832.4	832.6	833.3
165°	851.2	850.8	850.3	849.9	849.4	849.2	849.2	849.2	849.2	849.2	850.1
167.5°	865.0	864.4	863.8	863.2	862.6	862.4	862.5	862.6	862.7	862.8	863.8
170°	872.9	872.3	871.6	871.0	870.4	870.0	870.0	870.0	870.0	870.0	871.2
172.5°	879.0	878.4	877.8	877.2	876.6	876.2	876.2	876.2	876.2	876.2	877.2
175°	885.4	884.8	884.2	883.6	883.0	882.6	882.6	882.6	882.6	882.6	883.6
177.5°	888.1	887.6	887.1	886.5	886.1	885.8	885.8	885.8	885.8	885.8	886.5
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	15.8	15.7	15.6	15.5	15.3	15.2	15.0	14.9
90°	18.0	18.5	19.2	19.7	20.0	20.3	20.6	21.0
92.5°	27.7	28.3	28.7	28.9	28.7	28.5	28.4	28.2
95°	52.8	53.4	54.0	54.4	54.4	54.4	54.4	54.4
97.5°	82.1	82.8	83.6	83.9	83.8	83.8	83.7	83.6
100°	103.4	103.9	104.3	104.8	105.0	105.3	105.7	105.9
102.5°	128.0	128.4	128.9	129.1	129.0	128.9	128.9	128.9
105°	164.5	164.5	164.5	164.7	165.0	165.3	165.6	165.9
107.5°	204.1	204.6	205.2	205.3	205.1	204.9	204.7	204.6
110°	230.6	231.2	231.8	232.0	231.7	231.4	231.0	230.8



TEST NUMBER: P332346-940

CATALOG NUMBER: S123RDIP-S1000D805U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.1	257.8	258.6	258.9	258.9	258.8	258.7	258.7
115°	297.3	297.5	297.7	297.7	297.5	297.3	297.1	297.0
117.5°	338.0	337.9	337.9	337.6	337.2	336.8	336.4	335.9
120°	365.0	364.9	364.7	364.4	364.2	363.8	363.6	363.2
122.5°	392.4	392.0	391.6	391.2	390.7	390.3	389.9	389.4
125°	433.1	432.5	431.9	431.2	430.6	430.0	429.4	428.7
127.5°	473.3	472.4	471.6	470.8	470.1	469.4	468.7	468.0
130°	500.1	499.4	498.8	497.9	496.9	495.8	494.7	493.6
132.5°	526.0	525.2	524.5	523.7	522.9	522.0	521.2	520.4
135°	564.9	564.3	563.7	563.2	562.8	562.6	562.2	562.0
137.5°	602.9	602.3	601.5	600.9	600.4	599.8	599.2	598.6
140°	627.9	627.7	627.5	627.0	625.8	624.7	623.7	622.6
142.5°	651.3	651.1	650.9	650.5	649.6	648.8	647.9	647.1
145°	685.7	685.5	685.4	685.0	684.4	683.8	683.1	682.5
147.5°	718.3	718.3	718.3	717.7	716.8	715.9	715.0	714.1
150°	738.3	738.3	738.3	737.9	736.9	736.0	735.0	734.1
152.5°	756.6	756.9	757.2	756.9	756.1	755.3	754.5	753.7
155°	783.5	784.1	784.7	784.4	783.4	782.3	781.2	780.2
157.5°	806.6	807.2	807.8	807.7	806.9	806.0	805.1	804.2
160°	820.7	821.5	822.2	822.3	821.7	821.1	820.5	819.8
162.5°	834.1	834.9	835.7	835.5	834.6	833.6	832.6	831.6
165°	851.0	851.9	852.9	852.8	851.8	850.6	849.5	848.5
167.5°	864.8	865.7	866.7	866.7	865.7	864.8	863.8	862.8
170°	872.3	873.3	874.4	874.4	873.3	872.3	871.2	870.0
172.5°	878.2	879.1	880.0	880.0	878.9	877.8	876.7	875.7
175°	884.5	885.4	886.4	886.3	885.2	884.1	883.0	881.9
177.5°	887.3	888.1	888.8	888.8	887.9	887.0	886.2	885.3
180°	887.5	887.5	887.5	887.5	887.5	887.5	887.5	887.5

(END OF REPORT)