

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832026

Luminaire Tested: S123RDIP-S1165D805U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P832026
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D805U935-4F0-1E-UDD-G
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7042.1 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

Luminous Intensity Polar Plot





TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	61	
1	101	97	94	90	95	91	88	85	80	78	75	69	68	66	60	59	58	58	58	58	53	
2	93	86	80	75	87	81	76	72	71	67	64	62	59	57	54	52	50	50	50	50	46	
3	86	77	70	64	80	72	66	61	64	59	55	56	52	50	49	46	44	44	44	44	40	
4	79	69	61	56	74	65	58	53	58	52	48	51	47	44	44	41	39	39	39	39	36	
5	73	62	54	49	68	59	52	47	52	47	43	46	42	39	41	37	35	35	35	35	32	
6	68	56	48	43	63	53	46	41	48	42	38	42	38	35	37	34	31	31	31	31	29	
7	63	51	44	38	59	49	42	37	44	38	34	39	35	31	35	31	28	28	28	28	26	
8	59	47	40	35	55	45	38	33	40	35	31	36	32	28	32	29	26	26	26	26	24	
9	55	43	36	31	52	41	35	30	37	32	28	34	29	26	30	27	24	24	24	24	22	
10	52	40	33	29	49	38	32	28	35	29	26	31	27	24	28	25	22	22	22	22	20	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	34733	34733	34733	34733	34733
5°	41242	39927	34952	28254	26231
10°	37366	40555	34777	22638	19420
15°	25727	34771	34410	18503	15363
20°	17898	26771	33719	15601	13503
25°	13639	20403	32714	13867	12444
30°	11872	16312	31457	12875	11527
35°	10900	13761	29676	12039	10692
40°	9946	12288	27347	11219	9927
45°	8983	11237	24832	10443	9164
50°	8153	10369	21867	9682	8219
55°	7373	9522	19018	8938	7051
60°	6607	8658	16518	8118	6665
65°	6100	7682	14220	7294	6301
70°	4954	6641	12409	6600	5120
75°	4346	5282	10509	5473	4512
80°	3936	4469	8610	4593	4265
85°	3594	3927	6533	4162	3927

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 26201 cd/sqm



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.1	4.2
10°-20°	680.6	9.7
20°-30°	780.9	11.1
30°-40°	769.7	10.9
40°-50°	678.8	9.6
50°-60°	522.2	7.4
60°-70°	343.3	4.9
70°-80°	166.7	2.4
80°-90°	43.9	0.6
90°-100°	31.9	0.5
100°-110°	154.4	2.2
110°-120°	378.5	5.4
120°-130°	480.5	6.8
130°-140°	513.3	7.3
140°-150°	480.0	6.8
150°-160°	387.2	5.5
160°-170°	249.9	3.5
170°-180°	86.1	1.2
0°-30°	1755.6	24.9
0°-40°	2525.3	35.9
0°-60°	3726.2	52.9
0°-90°	4280.1	60.8
90°-120°	564.9	8.0
90°-150°	2038.8	29.0
90°-180°	2762.0	39.2
0°-180°	7042.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3227	3227	3227	3227	3227	
5°	3817	3695	3235	2615	2428	349
15°	2309	3120	3088	1660	1379	652
25°	1148	1718	2754	1168	1048	542
35°	830	1047	2258	916	814	517
45°	590	738	1631	686	602	458
55°	393	507	1013	476	376	352
65°	240	302	558	286	247	235
75°	104	127	253	132	108	112
85°	29	32	53	34	32	31
90°	20	16	1	16	20	10
95°	26	21	41	21	26	21
105°	30	147	201	147	30	62
115°	396	386	376	386	396	372
125°	541	538	530	538	541	484
135°	667	667	660	667	667	515
145°	769	768	762	768	769	480
155°	838	839	839	839	838	387
165°	883	882	885	882	883	249
175°	903	903	906	903	903	86
180°	906	906	906	906	906	



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3576.1	3564.9	3553.6	3550.3	3547.0	3536.4	3525.8	3502.0	3478.2	3453.7	3429.3
5°	3816.9	3818.2	3819.5	3816.2	3812.9	3799.0	3785.1	3756.0	3726.9	3695.2	3663.4
7.5°	3742.8	3764.0	3785.1	3789.1	3793.1	3803.7	3814.2	3807.6	3801.0	3789.1	3777.2
10°	3418.7	3417.3	3416.0	3439.8	3463.6	3534.4	3605.2	3641.6	3678.0	3710.4	3742.8
12.5°	2889.5	2891.4	2893.4	2971.5	3049.5	3116.4	3183.2	3275.8	3368.4	3468.3	3568.2
15°	2308.7	2341.1	2373.5	2442.9	2512.4	2613.0	2713.5	2837.9	2962.2	3120.3	3278.4
17.5°	1895.9	1909.8	1923.7	1990.5	2057.3	2152.5	2247.8	2388.7	2529.6	2733.3	2937.1
20°	1562.5	1575.0	1587.6	1635.9	1684.2	1775.5	1866.8	2001.1	2135.3	2337.1	2538.9
22.5°	1304.5	1329.0	1353.4	1385.9	1418.3	1484.4	1550.6	1687.5	1824.4	2008.3	2192.2
25°	1148.4	1159.6	1170.9	1198.6	1226.4	1289.9	1353.4	1444.1	1534.7	1717.9	1901.2
27.5°	1042.5	1045.8	1049.1	1069.7	1090.2	1131.2	1172.2	1256.2	1340.2	1491.0	1641.9
30°	955.2	961.2	967.1	983.0	998.9	1028.6	1058.4	1117.9	1177.5	1312.4	1447.4
32.5°	887.7	891.0	894.4	907.6	920.8	942.6	964.5	1011.4	1058.4	1161.6	1264.8
35°	829.5	830.2	830.9	840.8	850.7	871.9	893.0	932.1	971.1	1047.2	1123.2
37.5°	763.4	768.0	772.6	779.9	787.2	805.7	824.2	856.0	887.7	950.6	1013.4
40°	707.8	711.8	715.8	724.3	732.9	747.5	762.1	791.2	820.3	874.5	928.8
42.5°	652.2	654.9	657.5	666.1	674.7	692.6	710.5	733.6	756.8	801.7	846.7
45°	590.1	596.7	603.3	612.6	621.8	637.0	652.2	676.1	699.9	738.2	776.6
47.5°	538.5	541.8	545.1	553.0	561.0	579.5	598.0	619.2	640.3	676.1	711.8
50°	486.9	488.2	489.5	496.8	504.1	520.6	537.1	561.6	586.1	619.2	652.2
52.5°	437.9	441.2	444.5	451.8	459.1	470.3	481.6	506.7	531.9	564.3	596.7
55°	392.9	394.9	396.9	402.2	407.5	420.7	433.9	455.8	477.6	507.4	537.1
57.5°	350.6	353.2	355.9	359.9	363.8	375.7	387.6	406.8	426.0	455.8	485.5
60°	306.9	310.2	313.6	318.2	322.8	332.1	341.3	358.5	375.7	402.2	428.7
62.5°	275.2	275.8	276.5	280.5	284.4	291.1	297.7	311.6	325.5	351.9	378.4
65°	239.5	241.4	243.4	245.4	247.4	252.7	258.0	269.9	281.8	301.6	321.5
67.5°	202.4	204.4	206.4	209.7	213.0	217.6	222.3	230.2	238.1	256.7	275.2
70°	157.4	157.4	157.4	162.7	168.0	176.0	183.9	189.9	195.8	211.0	226.2
72.5°	128.3	129.0	129.7	130.3	131.0	135.6	140.2	150.2	160.1	169.3	178.6
75°	104.5	105.2	105.8	106.5	107.2	108.5	109.8	113.1	116.4	127.0	137.6
77.5°	83.3	84.0	84.7	85.3	86.0	87.3	88.6	90.0	91.3	95.3	99.2
80°	63.5	64.2	64.8	65.5	66.2	66.8	67.5	68.8	70.1	72.1	74.1
82.5°	46.3	46.3	46.3	46.3	46.3	47.6	49.0	49.0	49.0	50.3	51.6
85°	29.1	29.1	29.1	29.8	30.4	30.4	30.4	31.1	31.8	31.8	31.8
87.5°	13.2	12.6	11.9	12.6	13.2	13.2	13.2	13.9	14.6	14.6	14.6
90°	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4	16.8	16.2	14.2
92.5°	22.9	22.7	22.6	22.4	22.3	21.7	20.6	19.6	18.5	17.5	16.2
95°	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0	21.9	20.9	19.2
97.5°	27.6	27.4	27.3	27.1	27.0	26.3	25.1	23.9	22.7	21.5	20.2
100°	28.3	28.1	28.0	27.8	27.7	27.0	25.8	24.6	23.4	22.2	20.9
102.5°	28.9	28.6	28.3	28.0	27.7	30.1	35.0	39.9	44.9	49.8	54.7
105°	29.6	29.3	29.0	28.7	28.4	41.5	68.0	94.5	120.9	147.4	160.9
107.5°	70.0	89.6	109.2	128.8	148.4	169.7	192.7	215.8	238.8	261.8	259.6
110°	185.1	206.5	227.9	249.3	270.7	283.8	288.8	293.7	298.6	303.6	301.9



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	350.7	351.0	351.3	351.6	351.9	351.4	350.0	348.7	347.3	346.0	344.3
115°	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.4	387.9	386.4	385.0
117.5°	432.1	432.0	431.8	431.7	431.5	430.9	429.7	428.5	427.3	426.1	425.3
120°	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8	465.7	464.5	464.0
122.5°	506.9	506.7	506.6	506.4	506.3	505.8	505.1	504.3	503.6	502.8	502.2
125°	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1	538.8	538.5	537.9
127.5°	574.8	575.1	575.4	575.7	576.0	576.0	575.5	575.1	574.6	574.2	573.4
130°	607.2	607.5	607.8	608.1	608.4	608.2	607.6	607.0	606.4	605.8	605.2
132.5°	636.8	637.2	637.7	638.1	638.6	638.5	637.9	637.3	636.7	636.1	635.7
135°	667.1	667.5	668.0	668.4	668.9	668.9	668.4	668.0	667.5	667.1	666.5
137.5°	696.0	696.3	696.6	696.9	697.2	697.0	696.2	695.5	694.7	694.0	693.7
140°	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4	720.8	720.2	719.8
142.5°	745.1	745.6	746.0	746.5	746.9	746.9	746.5	746.0	745.6	745.1	744.7
145°	769.4	769.4	769.4	769.4	769.4	769.2	768.9	768.6	768.3	768.0	767.7
147.5°	786.9	787.6	788.4	789.1	789.9	790.1	789.8	789.5	789.2	788.9	788.6
150°	807.1	807.5	808.0	808.4	808.9	808.9	808.6	808.3	808.0	807.7	807.4
152.5°	823.2	824.0	824.7	825.5	826.2	826.3	825.7	825.1	824.5	823.9	823.8
155°	838.0	838.9	839.8	840.7	841.6	841.7	841.0	840.2	839.5	838.7	838.6
157.5°	850.8	852.0	853.2	854.4	855.6	855.8	854.9	854.0	853.1	852.2	852.3
160°	862.9	864.0	865.0	866.1	867.1	867.2	866.3	865.4	864.5	863.6	863.8
162.5°	874.4	875.3	876.2	877.1	878.0	877.9	876.9	875.8	874.8	873.7	873.9
165°	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.9	883.7	882.5	882.6
167.5°	889.9	891.1	892.3	893.5	894.7	894.7	893.5	892.3	891.1	889.9	889.9
170°	895.9	897.1	898.3	899.5	900.7	900.7	899.5	898.3	897.1	895.9	895.9
172.5°	899.3	900.6	902.0	903.3	904.7	904.8	903.6	902.4	901.2	900.0	899.8
175°	902.7	903.9	905.1	906.2	907.4	907.5	906.5	905.4	904.4	903.3	903.2
177.5°	903.3	904.8	906.3	907.8	909.3	909.5	908.3	907.1	905.9	904.7	904.5
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3425.9	3422.6	3390.9	3359.1	3328.0	3296.9	3273.8	3250.6	3211.6	3172.6	3148.1
5°	3638.3	3613.1	3562.9	3512.6	3437.2	3361.8	3298.3	3234.8	3154.1	3073.4	3005.9
7.5°	3756.7	3736.2	3675.3	3614.5	3514.6	3414.7	3315.5	3216.2	3097.2	2978.1	2876.2
10°	3760.0	3777.2	3726.9	3676.7	3564.2	3451.7	3316.8	3181.8	3021.8	2861.7	2730.0
12.5°	3642.3	3716.3	3705.8	3695.2	3580.7	3466.3	3302.2	3138.2	2941.7	2745.3	2580.5
15°	3422.0	3565.5	3607.9	3650.2	3555.6	3461.0	3274.5	3087.9	2857.0	2626.2	2437.0
17.5°	3138.2	3339.3	3451.1	3562.9	3494.1	3425.3	3220.9	3016.5	2756.5	2496.5	2290.8
20°	2802.1	3065.4	3240.7	3416.0	3390.9	3365.7	3154.7	2943.7	2663.2	2382.7	2159.8
22.5°	2470.1	2747.9	2990.0	3232.1	3257.9	3283.7	3070.7	2857.7	2550.8	2243.8	2016.9
25°	2183.6	2466.1	2754.5	3042.9	3101.1	3159.4	2956.9	2754.5	2436.3	2118.1	1892.6
27.5°	1910.4	2179.0	2496.5	2814.0	2919.9	3025.7	2840.5	2655.3	2323.9	1992.5	1767.5
30°	1687.5	1927.6	2251.8	2575.9	2723.4	2870.9	2700.9	2530.9	2202.2	1873.4	1653.1
32.5°	1479.8	1694.8	2020.2	2345.7	2517.0	2688.4	2541.5	2394.7	2078.5	1762.3	1544.6
35°	1315.7	1508.2	1811.9	2115.5	2307.3	2499.2	2378.8	2258.4	1949.5	1640.5	1434.8
37.5°	1174.8	1336.2	1621.4	1906.5	2110.2	2314.0	2213.4	2112.9	1822.5	1532.0	1337.6
40°	1058.4	1188.1	1453.3	1718.6	1918.4	2118.1	2032.1	1946.2	1686.2	1426.2	1244.3
42.5°	958.5	1070.3	1308.5	1546.6	1729.8	1913.1	1856.2	1799.3	1563.8	1328.3	1159.6
45°	870.5	964.5	1174.2	1383.9	1552.6	1721.2	1676.3	1631.3	1428.2	1225.1	1070.3
47.5°	792.5	873.2	1060.4	1247.6	1399.1	1550.6	1508.9	1467.2	1299.2	1131.2	990.3
50°	721.0	789.8	946.0	1102.1	1238.3	1374.6	1340.2	1305.8	1166.9	1028.0	906.3
52.5°	653.6	710.5	850.7	990.9	1100.7	1210.6	1184.1	1157.6	1050.5	943.3	832.8
55°	589.4	641.7	760.1	878.5	972.4	1066.3	1039.9	1013.4	930.1	846.7	749.5
57.5°	531.2	576.8	672.8	768.7	843.4	918.2	905.6	893.0	823.6	754.1	674.1
60°	469.7	510.7	593.4	676.1	736.3	796.5	781.9	767.3	717.7	668.1	599.3
62.5°	414.8	451.1	517.3	583.4	632.4	681.4	670.8	660.2	622.5	584.8	527.9
65°	357.2	392.9	446.5	500.1	538.5	576.8	567.6	558.3	529.9	501.4	455.8
67.5°	305.0	334.7	381.0	427.3	453.1	478.9	473.6	468.3	446.5	424.7	389.0
70°	252.0	277.8	316.2	354.6	372.4	390.3	392.3	394.3	374.4	354.6	328.1
72.5°	199.1	219.6	255.3	291.1	305.0	318.8	318.2	317.5	305.6	293.7	269.9
75°	152.8	168.0	195.8	223.6	235.5	247.4	250.0	252.7	241.4	230.2	217.0
77.5°	109.8	120.4	141.6	162.7	176.0	189.2	190.5	191.8	186.5	181.3	168.7
80°	77.4	80.7	93.9	107.2	121.1	134.9	136.9	138.9	133.6	128.3	120.4
82.5°	53.6	55.6	60.2	64.8	76.1	87.3	90.0	92.6	90.0	87.3	78.7
85°	32.4	33.1	35.1	37.0	42.3	47.6	50.3	52.9	51.6	50.3	45.6
87.5°	14.6	14.6	15.2	15.9	17.2	18.5	21.8	25.1	23.2	21.2	19.2
90°	12.3	10.3	8.4	6.7	5.2	3.7	2.2	0.7	2.2	3.7	5.2
92.5°	14.8	13.5	12.1	11.9	12.8	13.7	14.6	15.5	14.6	13.7	12.8
95°	17.6	15.9	14.3	16.5	22.7	28.8	34.9	41.1	34.9	28.8	22.7
97.5°	36.8	44.4	52.1	58.0	62.2	66.3	70.5	74.7	70.5	66.3	62.2
100°	68.9	92.2	115.6	125.7	122.7	119.7	116.7	113.8	116.7	119.7	122.7
102.5°	101.9	127.9	153.9	166.0	164.0	162.1	160.1	158.2	160.1	162.1	164.0
105°	174.3	187.8	201.3	207.2	205.5	203.9	202.2	200.6	202.2	203.9	205.5
107.5°	257.4	255.1	252.9	251.1	249.7	248.4	247.0	245.7	247.0	248.4	249.7
110°	300.3	298.6	297.0	295.6	294.4	293.2	292.0	290.8	292.0	293.2	294.4



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.7	341.0	339.4	338.1	337.0	336.0	334.9	333.9	334.9	336.0	337.0
115°	383.7	382.3	381.0	379.9	379.0	378.1	377.2	376.3	377.2	378.1	379.0
117.5°	424.6	423.8	423.1	422.2	421.2	420.1	419.1	418.0	419.1	420.1	421.2
120°	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4	457.7	459.1	460.4
122.5°	501.6	501.0	500.4	499.6	498.6	497.5	496.5	495.4	496.5	497.5	498.6
125°	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.4	531.6	532.8	534.0
127.5°	572.7	571.9	571.2	570.2	569.0	567.8	566.6	565.4	566.6	567.8	569.0
130°	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7	598.9	600.1	601.3
132.5°	635.2	634.8	634.3	633.5	632.3	631.1	629.9	628.7	629.9	631.1	632.3
135°	665.9	665.3	664.7	663.9	663.0	662.1	661.2	660.3	661.2	662.1	663.0
137.5°	693.4	693.1	692.8	692.0	690.8	689.7	688.5	687.3	688.5	689.7	690.8
140°	719.3	718.9	718.4	717.8	716.9	716.0	715.1	714.2	715.1	716.0	716.9
142.5°	744.3	743.8	743.4	742.7	741.8	740.9	740.0	739.1	740.0	740.9	741.8
145°	767.4	767.1	766.8	766.2	765.1	764.1	763.0	762.0	763.0	764.1	765.1
147.5°	788.3	788.0	787.7	787.2	786.4	785.7	784.9	784.2	784.9	785.7	786.4
150°	807.1	806.9	806.6	806.2	805.7	805.3	804.8	804.4	804.8	805.3	805.7
152.5°	823.6	823.5	823.3	823.2	823.0	822.9	822.7	822.6	822.7	822.9	823.0
155°	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4	839.1	838.8	838.5
157.5°	852.5	852.6	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8
160°	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0	864.8	864.7	864.5
162.5°	874.0	874.2	874.3	874.6	875.1	875.5	876.0	876.4	876.0	875.5	875.1
165°	882.8	882.9	883.1	883.4	883.8	884.3	884.7	885.2	884.7	884.3	883.8
167.5°	889.9	889.9	889.9	890.2	890.8	891.4	892.0	892.6	892.0	891.4	890.8
170°	895.9	895.9	895.9	896.2	896.8	897.4	898.0	898.6	898.0	897.4	896.8
172.5°	899.7	899.5	899.4	899.7	900.4	901.2	901.9	902.7	901.9	901.2	900.4
175°	903.0	902.9	902.7	903.0	903.8	904.5	905.3	906.0	905.3	904.5	903.8
177.5°	904.4	904.2	904.1	904.4	905.1	905.9	906.6	907.4	906.6	905.9	905.1
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8	3226.8
2.5°	3123.6	3085.9	3048.2	3021.1	2994.0	2960.2	2926.5	2925.2	2923.9	2898.7	2873.6
5°	2938.4	2872.9	2807.4	2743.3	2679.1	2614.9	2550.8	2536.2	2521.7	2499.8	2478.0
7.5°	2774.4	2669.8	2565.3	2483.3	2401.3	2337.1	2272.9	2229.3	2185.6	2151.9	2118.1
10°	2598.4	2468.7	2339.1	2239.9	2140.6	2071.2	2001.7	1951.4	1901.2	1877.4	1853.5
12.5°	2415.8	2274.9	2134.0	2036.8	1939.5	1856.2	1772.8	1727.2	1681.5	1648.5	1615.4
15°	2247.8	2096.3	1944.8	1841.6	1738.4	1660.4	1582.3	1536.7	1491.0	1458.0	1424.9
17.5°	2085.1	1932.3	1779.5	1674.9	1570.4	1499.6	1428.9	1384.5	1340.2	1319.7	1299.2
20°	1936.9	1782.8	1628.6	1530.1	1431.5	1362.0	1292.6	1268.8	1245.0	1225.8	1206.6
22.5°	1790.0	1641.9	1493.7	1399.1	1304.5	1254.2	1203.9	1184.8	1165.6	1151.0	1136.5
25°	1667.0	1519.5	1372.0	1289.3	1206.6	1167.6	1128.5	1116.0	1103.4	1088.8	1074.3
27.5°	1542.6	1402.4	1262.2	1196.0	1129.9	1098.1	1066.3	1050.5	1034.6	1022.7	1010.8
30°	1432.8	1303.2	1173.5	1118.6	1063.7	1035.9	1008.1	990.9	973.7	962.5	951.2
32.5°	1327.0	1211.9	1096.8	1049.8	1002.8	975.7	948.6	932.1	915.5	902.3	889.1
35°	1229.1	1129.2	1029.3	986.3	943.3	916.2	889.1	872.5	856.0	842.8	829.5
37.5°	1143.1	1052.5	961.8	921.5	881.1	857.3	833.5	816.3	799.1	785.2	771.3
40°	1062.4	982.3	902.3	863.3	824.2	798.4	772.6	757.4	742.2	729.6	717.1
42.5°	990.9	917.5	844.1	805.7	767.3	742.9	718.4	700.5	682.7	675.4	668.1
45°	915.5	850.7	785.9	748.8	711.8	686.0	660.2	645.0	629.8	623.1	616.5
47.5°	849.4	789.2	729.0	692.6	656.2	633.1	609.9	598.0	586.1	576.8	567.6
50°	784.5	726.3	668.1	633.1	598.0	578.2	558.3	543.8	529.2	522.6	516.0
52.5°	722.4	669.4	616.5	580.8	545.1	525.9	506.7	494.1	481.6	467.7	453.8
55°	652.2	605.9	559.6	527.9	496.1	476.3	456.4	441.9	427.3	412.8	398.2
57.5°	594.0	548.4	502.7	474.3	445.9	426.7	407.5	391.6	375.7	363.8	351.9
60°	530.5	490.8	451.1	423.4	395.6	377.1	358.5	343.3	328.1	322.2	316.2
62.5°	471.0	433.9	396.9	372.4	348.0	330.1	312.2	302.3	292.4	288.4	284.4
65°	410.1	378.4	346.6	324.1	301.6	286.4	271.2	266.6	262.0	258.6	255.3
67.5°	353.2	326.1	299.0	279.2	259.3	248.7	238.1	232.9	227.6	223.6	219.6
70°	301.6	277.8	254.0	236.8	219.6	209.7	199.8	195.1	190.5	183.2	176.0
72.5°	246.1	227.6	209.0	195.8	182.6	174.0	165.4	156.1	146.9	140.2	133.6
75°	203.7	185.2	166.7	154.1	141.6	131.6	121.7	118.4	115.1	113.1	111.1
77.5°	156.1	140.2	124.4	114.4	104.5	99.9	95.3	93.3	91.3	90.6	90.0
80°	112.5	99.2	86.0	80.7	75.4	74.1	72.8	71.4	70.1	69.5	68.8
82.5°	70.1	63.5	56.9	55.6	54.2	53.6	52.9	52.3	51.6	50.9	50.3
85°	41.0	38.4	35.7	35.1	34.4	33.7	33.1	33.1	33.1	33.1	33.1
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	16.5	15.9
90°	6.7	8.4	10.3	12.3	14.2	16.2	16.8	17.4	17.9	18.5	19.0
92.5°	11.9	12.1	13.5	14.8	16.2	17.5	18.5	19.6	20.6	21.7	22.3
95°	16.5	14.3	15.9	17.6	19.2	20.9	21.9	23.0	24.0	25.1	25.6
97.5°	58.0	52.1	44.4	36.8	29.2	21.5	22.7	23.9	25.1	26.3	27.0
100°	125.7	115.6	92.2	68.9	45.5	22.2	23.4	24.6	25.8	27.0	27.7
102.5°	166.0	153.9	127.9	101.9	75.8	49.8	44.9	39.9	35.0	30.1	27.7
105°	207.2	201.3	187.8	174.3	160.9	147.4	120.9	94.5	68.0	41.5	28.4
107.5°	251.1	252.9	255.1	257.4	259.6	261.8	238.8	215.8	192.7	169.7	148.4
110°	295.6	297.0	298.6	300.3	301.9	303.6	298.6	293.7	288.8	283.8	270.7



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	338.1	339.4	341.0	342.7	344.3	346.0	347.3	348.7	350.0	351.4	351.9
115°	379.9	381.0	382.3	383.7	385.0	386.4	387.9	389.4	390.9	392.4	393.4
117.5°	422.2	423.1	423.8	424.6	425.3	426.1	427.3	428.5	429.7	430.9	431.5
120°	461.8	462.7	463.1	463.6	464.0	464.5	465.7	466.8	468.0	469.2	469.8
122.5°	499.6	500.4	501.0	501.6	502.2	502.8	503.6	504.3	505.1	505.8	506.3
125°	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1	539.4	539.7	540.0
127.5°	570.2	571.2	571.9	572.7	573.4	574.2	574.6	575.1	575.5	576.0	576.0
130°	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0	607.6	608.2	608.4
132.5°	633.5	634.3	634.8	635.2	635.7	636.1	636.7	637.3	637.9	638.5	638.6
135°	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0	668.4	668.9	668.9
137.5°	692.0	692.8	693.1	693.4	693.7	694.0	694.7	695.5	696.2	697.0	697.2
140°	717.8	718.4	718.9	719.3	719.8	720.2	720.8	721.4	722.0	722.6	722.8
142.5°	742.7	743.4	743.8	744.3	744.7	745.1	745.6	746.0	746.5	746.9	746.9
145°	766.2	766.8	767.1	767.4	767.7	768.0	768.3	768.6	768.9	769.2	769.4
147.5°	787.2	787.7	788.0	788.3	788.6	788.9	789.2	789.5	789.8	790.1	789.9
150°	806.2	806.6	806.9	807.1	807.4	807.7	808.0	808.3	808.6	808.9	808.9
152.5°	823.2	823.3	823.5	823.6	823.8	823.9	824.5	825.1	825.7	826.3	826.2
155°	838.2	838.1	838.3	838.4	838.6	838.7	839.5	840.2	841.0	841.7	841.6
157.5°	852.8	852.8	852.6	852.5	852.3	852.2	853.1	854.0	854.9	855.8	855.6
160°	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4	866.3	867.2	867.1
162.5°	874.6	874.3	874.2	874.0	873.9	873.7	874.8	875.8	876.9	877.9	878.0
165°	883.4	883.1	882.9	882.8	882.6	882.5	883.7	884.9	886.1	887.3	887.3
167.5°	890.2	889.9	889.9	889.9	889.9	889.9	891.1	892.3	893.5	894.7	894.7
170°	896.2	895.9	895.9	895.9	895.9	895.9	897.1	898.3	899.5	900.7	900.7
172.5°	899.7	899.4	899.5	899.7	899.8	900.0	901.2	902.4	903.6	904.8	904.7
175°	903.0	902.7	902.9	903.0	903.2	903.3	904.4	905.4	906.5	907.5	907.4
177.5°	904.4	904.1	904.2	904.4	904.5	904.7	905.9	907.1	908.3	909.5	909.3
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3226.8	3226.8	3226.8	3226.8
2.5°	2867.0	2860.4	2857.7	2855.1
5°	2457.5	2437.0	2432.4	2427.7
7.5°	2109.5	2100.9	2072.5	2044.1
10°	1827.1	1800.6	1788.7	1776.8
12.5°	1590.9	1566.4	1562.5	1558.5
15°	1407.7	1390.5	1384.5	1378.6
17.5°	1287.3	1275.4	1268.1	1260.8
20°	1198.0	1189.4	1184.1	1178.8
22.5°	1129.9	1123.2	1119.3	1115.3
25°	1064.4	1054.4	1051.1	1047.8
27.5°	1002.2	993.6	990.3	987.0
30°	944.0	936.7	932.1	927.4
32.5°	880.5	871.9	869.2	866.6
35°	824.2	818.9	816.3	813.7
37.5°	764.7	758.1	754.1	750.1
40°	713.8	710.5	708.5	706.5
42.5°	662.2	656.2	655.6	654.9
45°	610.6	604.6	603.3	602.0
47.5°	562.3	557.0	556.3	555.7
50°	508.7	501.4	496.1	490.8
52.5°	447.2	440.6	435.9	431.3
55°	391.0	383.7	379.7	375.7
57.5°	348.6	345.3	343.3	341.3
60°	314.2	312.2	310.9	309.6
62.5°	282.5	280.5	280.5	280.5
65°	253.4	251.4	249.4	247.4
67.5°	215.7	211.7	211.0	210.4
70°	170.0	164.1	163.4	162.7
72.5°	133.0	132.3	131.0	129.7
75°	109.8	108.5	108.5	108.5
77.5°	88.6	87.3	87.3	87.3
80°	68.1	67.5	68.1	68.8
82.5°	50.3	50.3	49.6	49.0
85°	32.4	31.8	31.8	31.8
87.5°	15.9	15.9	15.9	15.9
90°	19.3	19.6	19.9	20.2
92.5°	22.4	22.6	22.7	22.9
95°	25.6	25.6	25.6	25.6
97.5°	27.1	27.3	27.4	27.6
100°	27.8	28.0	28.1	28.3
102.5°	28.0	28.3	28.6	28.9
105°	28.7	29.0	29.3	29.6
107.5°	128.8	109.2	89.6	70.0
110°	249.3	227.9	206.5	185.1



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	351.6	351.3	351.0	350.7
115°	394.0	394.6	395.2	395.8
117.5°	431.7	431.8	432.0	432.1
120°	469.8	469.8	469.8	469.8
122.5°	506.4	506.6	506.7	506.9
125°	540.3	540.6	540.9	541.2
127.5°	575.7	575.4	575.1	574.8
130°	608.1	607.8	607.5	607.2
132.5°	638.1	637.7	637.2	636.8
135°	668.4	668.0	667.5	667.1
137.5°	696.9	696.6	696.3	696.0
140°	722.5	722.2	721.9	721.6
142.5°	746.5	746.0	745.6	745.1
145°	769.4	769.4	769.4	769.4
147.5°	789.1	788.4	787.6	786.9
150°	808.4	808.0	807.5	807.1
152.5°	825.5	824.7	824.0	823.2
155°	840.7	839.8	838.9	838.0
157.5°	854.4	853.2	852.0	850.8
160°	866.1	865.0	864.0	862.9
162.5°	877.1	876.2	875.3	874.4
165°	886.3	885.2	884.2	883.1
167.5°	893.5	892.3	891.1	889.9
170°	899.5	898.3	897.1	895.9
172.5°	903.3	902.0	900.6	899.3
175°	906.2	905.1	903.9	902.7
177.5°	907.8	906.3	904.8	903.3
180°	906.0	906.0	906.0	906.0



TEST NUMBER: P832026

CATALOG NUMBER: S123RDIP-S1165D805U935-4F0-1E-UDD-G

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.03	14.93	14.90	15.81	16.93	18.69	19.59	19.57	20.48	21.59
	3H	15.26	16.06	16.14	16.95	18.09	20.20	21.00	21.08	21.89	23.03
	4H	15.64	16.40	16.54	17.30	18.45	20.69	21.45	21.59	22.35	23.50
	6H	15.93	16.62	16.84	17.53	18.69	21.01	21.70	21.92	22.61	23.77
	8H	16.02	16.68	16.93	17.60	18.76	21.09	21.75	22.01	22.67	23.83
	12H	16.07	16.70	16.99	17.61	18.80	21.12	21.75	22.05	22.67	23.85
4H	2H	14.76	15.52	15.67	16.42	17.57	18.70	19.45	19.60	20.35	21.50
	3H	16.14	16.76	17.05	17.69	18.86	20.36	20.99	21.28	21.92	23.08
	4H	16.59	17.17	17.52	18.09	19.28	20.97	21.54	21.90	22.47	23.66
	6H	16.97	17.46	17.90	18.41	19.60	21.41	21.90	22.35	22.85	24.05
	8H	17.09	17.55	18.03	18.49	19.70	21.54	22.00	22.49	22.95	24.15
	12H	17.17	17.58	18.13	18.54	19.75	21.61	22.02	22.57	22.98	24.19
8H	4H	16.91	17.37	17.85	18.32	19.52	20.94	21.40	21.88	22.34	23.55
	6H	17.38	17.76	18.35	18.74	19.95	21.44	21.82	22.41	22.80	24.01
	8H	17.57	17.91	18.55	18.88	20.10	21.63	21.96	22.60	22.94	24.16
	12H	17.72	18.01	18.69	18.98	20.25	21.75	22.04	22.72	23.01	24.28
12H	4H	16.93	17.34	17.89	18.30	19.51	20.90	21.31	21.86	22.27	23.48
	6H	17.44	17.77	18.41	18.75	19.97	21.42	21.75	22.39	22.73	23.95
	8H	17.66	17.95	18.64	18.92	20.19	21.61	21.90	22.59	22.87	24.14