

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332383-940

Luminaire Tested: **S123RDIP-S1165D1025U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332383-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7215.9 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	54	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	61	77	68	62	57	59	54	50	50	47	44	42	40	38	34
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	30	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.2
10°-20°	451.6	6.3
20°-30°	650.2	9.0
30°-40°	732.4	10.1
40°-50°	700.7	9.7
50°-60°	573.8	8.0
60°-70°	387.1	5.4
70°-80°	194.8	2.7
80°-90°	54.9	0.8
90°-100°	244.7	3.4
100°-110°	692.9	9.6
110°-120°	681.6	9.4
120°-130°	543.7	7.5
130°-140°	428.7	5.9
140°-150°	319.9	4.4
150°-160°	223.0	3.1
160°-170°	131.0	1.8
170°-180°	42.6	0.6
0°-30°	1264.1	17.5
0°-40°	1996.5	27.7
0°-60°	3270.9	45.3
0°-90°	3907.7	54.2
90°-120°	1619.2	22.4
90°-150°	2911.5	40.3
90°-180°	3308.0	45.8
0°-180°	7215.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	2	11	22	25	26	6
95°	30	98	528	154	103	33
105°	103	153	716	1251	1132	110
115°	182	227	547	1200	1377	181
125°	254	300	511	926	1086	225
135°	297	355	504	762	880	230
145°	339	389	498	625	688	213
155°	385	416	482	547	570	177
165°	421	433	461	489	498	119
175°	439	439	442	449	448	42
180°	440	440	440	440	440	



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.3	24.9	22.5	20.3	17.9	16.9	17.4	17.9	18.5	19.0	18.6
90°	1.8	3.6	5.4	8.0	9.8	11.6	14.3	16.9	19.6	22.3	21.4
92.5°	11.1	16.4	23.9	30.8	38.3	51.5	74.7	113.1	150.6	136.9	103.3
95°	30.2	32.9	42.7	57.9	81.0	115.7	191.4	324.0	469.9	527.8	428.1
97.5°	51.6	52.5	60.2	73.3	96.1	133.7	206.0	355.5	598.9	818.0	875.1
100°	65.9	66.8	73.0	85.4	106.8	141.5	203.8	335.6	569.6	842.9	1018.2
102.5°	80.8	82.4	87.9	99.7	119.0	150.8	206.7	318.4	526.9	796.7	1025.4
105°	103.3	105.9	111.3	122.0	138.8	166.5	214.5	306.2	474.4	715.6	971.1
107.5°	127.1	129.7	134.9	145.4	161.3	186.9	229.1	305.3	441.0	644.1	876.0
110°	144.2	146.9	151.3	161.1	176.2	201.2	241.2	308.9	428.1	603.5	816.2



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.9	162.6	167.0	176.7	191.9	216.2	253.3	316.0	421.0	576.4	764.2
115°	182.4	186.0	191.4	200.3	215.4	239.4	273.2	327.5	418.3	547.4	701.4
117.5°	205.1	209.2	213.7	221.8	238.7	261.0	294.4	342.9	419.9	530.3	663.4
120°	220.7	223.4	227.8	236.7	253.7	275.9	308.0	354.3	422.8	522.5	643.5
122.5°	234.3	236.9	241.4	251.0	267.2	290.9	322.2	365.0	427.8	517.5	627.1
125°	253.7	255.5	260.8	270.5	287.5	311.6	342.7	381.8	435.2	511.0	606.2
127.5°	268.5	271.1	277.7	287.7	306.4	330.4	360.5	395.7	443.8	507.7	587.6
130°	277.7	280.4	288.4	299.1	317.7	341.8	371.1	405.0	449.5	505.6	577.7
132.5°	284.8	288.2	296.9	309.8	328.4	351.8	380.4	413.6	453.8	504.9	568.4
135°	297.3	300.9	310.7	324.0	342.7	366.7	394.3	424.5	460.2	503.8	556.3
137.5°	309.1	312.8	322.4	336.6	355.2	377.4	403.9	432.7	464.4	501.9	545.8
140°	316.9	321.3	330.2	344.5	362.3	384.5	410.4	437.0	467.3	501.1	539.4
142.5°	325.4	329.1	338.8	351.6	369.3	390.2	415.4	441.3	469.4	499.7	533.7
145°	339.1	341.8	349.8	363.2	378.3	398.8	421.9	445.9	470.8	497.6	526.0
147.5°	353.0	354.6	362.5	374.0	388.6	406.1	427.2	448.8	470.8	494.2	518.5
150°	362.3	363.2	370.2	381.8	394.3	410.4	430.8	449.5	470.8	491.3	513.5
152.5°	371.5	371.7	378.8	389.0	400.0	415.4	432.9	450.9	468.7	487.8	507.9
155°	385.4	385.4	390.7	399.7	409.5	421.9	437.0	451.3	466.4	481.5	499.4
157.5°	396.5	397.2	401.4	409.3	417.6	427.2	439.3	452.2	463.4	476.0	489.7
160°	405.0	405.0	408.6	415.6	421.9	430.8	441.5	452.2	462.0	471.7	483.3
162.5°	411.4	411.4	414.3	419.9	425.4	432.9	442.2	451.5	459.1	467.4	476.9
165°	421.0	420.1	421.9	426.3	429.9	436.1	443.3	449.5	454.9	461.1	468.1
167.5°	428.3	427.2	428.1	431.5	434.0	437.9	443.1	448.1	450.6	454.7	459.9
170°	432.6	430.8	431.7	434.4	436.1	437.9	442.4	445.9	447.7	450.4	454.9
172.5°	435.4	434.4	434.5	436.5	437.6	438.6	442.4	445.2	445.6	446.8	449.9
175°	438.8	437.9	437.0	438.8	438.8	439.7	441.5	443.3	442.4	442.4	444.2
177.5°	440.4	439.7	439.0	439.7	439.7	439.7	440.4	441.8	440.4	439.7	440.4
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	18.5	18.5	18.4	18.5	18.1	18.0	17.9	17.5
90°	22.3	23.2	24.1	25.8	24.9	25.8	26.7	25.8
92.5°	74.9	59.5	52.5	47.9	46.3	43.6	44.5	42.9
95°	320.4	217.2	170.0	137.9	121.1	113.1	106.8	103.3
97.5°	798.8	639.8	525.0	418.5	352.8	312.8	288.7	281.1
100°	1049.5	977.3	873.2	746.8	656.9	591.9	557.2	558.1
102.5°	1132.7	1130.4	1069.7	989.6	919.6	868.2	839.2	818.7
105°	1157.1	1246.2	1263.0	1239.9	1198.9	1165.1	1136.7	1132.2
107.5°	1087.0	1231.5	1309.5	1341.2	1341.9	1330.5	1320.9	1312.7
110°	1020.0	1183.8	1295.9	1358.3	1383.2	1390.4	1388.6	1386.8



TEST NUMBER: P332383-940

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	953.8	1121.1	1246.8	1327.0	1372.5	1394.5	1401.3	1401.7
115°	866.0	1020.9	1151.7	1248.8	1315.5	1354.7	1372.5	1377.0
117.5°	802.5	936.2	1053.6	1152.1	1221.7	1266.6	1292.3	1298.2
120°	769.0	889.2	996.0	1085.9	1156.2	1206.0	1227.4	1232.8
122.5°	742.7	851.5	950.5	1033.9	1096.4	1141.3	1164.8	1171.5
125°	707.7	804.7	890.1	961.3	1018.2	1057.4	1079.7	1085.9
127.5°	677.0	763.5	840.6	905.4	956.1	989.6	1009.7	1015.4
130°	657.8	737.9	809.9	870.5	917.7	949.8	968.4	975.5
132.5°	640.0	713.6	780.8	838.5	882.8	914.8	931.4	936.4
135°	615.9	679.1	737.0	787.7	831.3	858.0	874.1	880.3
137.5°	594.1	645.9	695.7	739.7	776.3	803.4	816.9	821.0
140°	581.2	626.6	669.3	707.7	741.5	766.3	780.6	779.7
142.5°	569.1	608.1	645.2	678.4	707.3	729.3	742.2	741.3
145°	554.6	583.9	612.3	638.2	660.4	679.1	686.3	688.0
147.5°	542.6	565.9	588.9	607.3	624.1	636.8	643.5	644.3
150°	534.0	554.6	573.2	590.1	603.5	613.2	618.6	618.6
152.5°	526.2	543.9	560.4	574.4	585.0	594.1	597.3	597.3
155°	514.4	528.7	542.1	552.8	560.8	567.8	569.6	570.5
157.5°	502.0	513.9	524.2	532.6	539.6	544.9	546.4	546.2
160°	494.9	504.7	513.5	519.8	526.0	531.4	531.4	530.5
162.5°	486.3	494.7	502.9	508.5	512.6	517.1	517.1	516.2
165°	475.3	480.6	486.9	491.3	494.9	498.5	497.6	497.6
167.5°	465.7	469.8	473.3	476.5	478.1	480.6	479.7	479.7
170°	459.3	462.0	465.5	467.3	468.1	469.9	469.0	469.0
172.5°	453.6	455.6	458.4	459.5	459.7	461.5	459.9	459.1
175°	445.9	446.8	448.6	448.6	448.6	449.5	448.6	447.7
177.5°	441.1	441.8	442.6	442.6	441.8	442.6	441.1	441.1
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7

(END OF REPORT)