

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332267-935

Luminaire Tested: **S123RDIP-S340D1195U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332267-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1195U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5227.2 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21				
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	24	22	22	16				
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	20	18	13				
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9				
7	54	42	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	29	23	19	22	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	0.9
10°-20°	129.2	2.5
20°-30°	186.1	3.6
30°-40°	209.6	4.0
40°-50°	200.5	3.8
50°-60°	164.2	3.1
60°-70°	110.8	2.1
70°-80°	55.7	1.1
80°-90°	18.5	0.4
90°-100°	48.9	0.9
100°-110°	233.3	4.5
110°-120°	560.4	10.7
120°-130°	713.6	13.7
130°-140°	762.5	14.6
140°-150°	713.0	13.6
150°-160°	575.1	11.0
160°-170°	371.2	7.1
170°-180°	127.9	2.4
0°-30°	361.8	6.9
0°-40°	571.4	10.9
0°-60°	936.2	17.9
0°-90°	1121.2	21.4
90°-120°	842.6	16.1
90°-150°	3031.7	58.0
90°-180°	4106.0	78.6
0°-180°	5227.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	11	24	28	30	4
95°	61	23	31	38	38	75
105°	298	304	219	52	44	316
115°	559	565	574	584	588	552
125°	788	796	800	802	804	704
135°	981	987	991	994	991	755
145°	1132	1139	1141	1143	1143	709
155°	1247	1246	1246	1251	1245	574
165°	1315	1313	1311	1319	1312	371
175°	1346	1342	1342	1349	1341	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.9	7.6	7.2	6.9	6.5	6.6	7.2	7.8	8.4	9.0	9.0
90°	1.0	3.2	5.4	7.7	9.9	12.5	15.3	18.3	21.1	24.0	24.9
92.5°	18.6	18.0	17.4	16.7	16.1	16.9	19.1	21.3	23.4	25.6	27.0
95°	61.0	51.9	42.8	33.7	24.5	21.3	23.7	26.1	28.6	31.0	32.5
97.5°	122.6	118.6	114.4	110.4	106.2	96.3	80.2	64.2	48.2	32.2	34.0
100°	169.0	173.5	178.0	182.4	186.8	171.7	137.1	102.4	67.7	33.0	34.8
102.5°	221.9	225.1	228.3	231.4	234.7	217.3	179.4	141.5	103.7	65.8	60.3
105°	298.1	300.6	303.0	305.4	307.9	299.1	279.1	259.1	239.1	219.0	179.7
107.5°	378.5	380.5	382.5	384.4	386.3	388.9	392.1	395.2	398.4	401.6	372.6
110°	432.1	433.9	435.7	437.5	439.3	441.3	443.8	446.3	448.7	451.2	443.8



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.4	484.9	486.6	488.2	489.7	491.8	494.2	496.7	499.1	501.5	501.7
115°	559.2	560.5	561.8	563.2	564.5	566.2	568.2	570.2	572.2	574.2	576.4
117.5°	632.6	634.2	635.8	637.6	639.2	640.5	641.5	642.6	643.6	644.6	646.4
120°	678.2	680.2	682.3	684.2	686.2	687.6	688.2	688.9	689.6	690.2	692.0
122.5°	724.6	726.3	727.9	729.5	731.2	732.5	733.3	734.2	734.9	735.8	737.1
125°	788.2	790.1	791.8	793.6	795.4	796.7	797.5	798.5	799.4	800.2	800.7
127.5°	849.9	851.6	853.4	855.2	857.0	858.4	859.5	860.6	861.6	862.6	863.4
130°	888.3	890.1	891.8	893.6	895.4	896.7	897.6	898.5	899.4	900.3	901.2
132.5°	925.1	926.9	928.7	930.4	932.2	933.4	934.2	934.9	935.6	936.3	937.2
135°	981.3	982.7	984.0	985.3	986.6	987.7	988.7	989.5	990.4	991.4	992.0
137.5°	1029.3	1031.0	1032.7	1034.4	1036.1	1037.2	1037.7	1038.2	1038.6	1039.1	1040.2
140°	1061.4	1062.6	1064.0	1065.3	1066.7	1067.6	1068.3	1069.0	1069.7	1070.3	1071.3
142.5°	1091.0	1092.3	1093.6	1094.9	1096.3	1097.3	1097.9	1098.6	1099.3	1099.9	1100.7
145°	1132.4	1133.9	1135.5	1137.0	1138.6	1139.6	1140.1	1140.5	1140.9	1141.3	1141.8
147.5°	1171.4	1172.4	1173.5	1174.4	1175.4	1176.2	1176.6	1177.1	1177.5	1177.9	1178.5
150°	1195.4	1196.0	1196.7	1197.4	1198.1	1198.6	1199.0	1199.5	1200.0	1200.4	1200.8
152.5°	1217.0	1217.3	1217.6	1217.9	1218.2	1218.5	1218.7	1219.1	1219.3	1219.6	1220.4
155°	1247.4	1247.0	1246.5	1246.0	1245.6	1245.5	1245.7	1246.0	1246.2	1246.4	1247.5
157.5°	1271.0	1270.9	1270.9	1270.8	1270.8	1270.7	1270.5	1270.2	1270.1	1269.8	1271.2
160°	1285.4	1285.2	1285.0	1284.8	1284.5	1284.3	1284.1	1283.8	1283.7	1283.4	1284.8
162.5°	1299.0	1298.5	1297.9	1297.3	1296.7	1296.3	1296.1	1295.9	1295.6	1295.4	1296.9
165°	1315.4	1314.7	1314.1	1313.5	1312.8	1312.3	1312.1	1311.8	1311.6	1311.4	1313.2
167.5°	1328.3	1327.3	1326.5	1325.6	1324.6	1324.2	1324.2	1324.2	1324.2	1324.2	1326.0
170°	1335.4	1334.6	1333.7	1332.7	1331.9	1331.5	1331.5	1331.5	1331.5	1331.5	1333.2
172.5°	1340.2	1339.2	1338.1	1337.0	1335.9	1335.5	1335.7	1335.8	1336.0	1336.2	1338.0
175°	1346.4	1345.3	1344.2	1343.1	1342.0	1341.5	1341.8	1342.0	1342.2	1342.4	1344.0
177.5°	1348.1	1347.1	1346.3	1345.4	1344.5	1344.1	1344.3	1344.5	1344.6	1344.8	1346.3
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	9.2	9.3	9.4	9.5	9.5	9.5	9.6	9.6
90°	25.7	26.7	27.6	28.2	28.7	29.1	29.5	30.0
92.5°	28.4	29.9	31.3	32.1	32.4	32.7	33.0	33.2
95°	34.1	35.6	37.2	38.0	38.0	38.0	38.0	38.0
97.5°	35.7	37.5	39.3	40.3	40.6	40.8	41.0	41.2
100°	36.6	38.3	40.1	41.2	41.3	41.6	41.8	42.0
102.5°	54.8	49.2	43.7	41.2	41.6	42.0	42.4	42.8
105°	140.3	101.0	61.6	42.3	42.7	43.1	43.6	44.0
107.5°	343.8	315.0	286.1	256.8	227.2	197.5	167.9	138.3
110°	436.4	429.1	421.8	402.3	370.5	338.6	306.9	275.1



TEST NUMBER: P332267-935

CATALOG NUMBER: S123RDIP-S340D1195U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	501.8	502.0	502.1	498.8	492.1	485.3	478.6	471.9
115°	578.6	580.8	583.1	584.6	585.5	586.4	587.3	588.1
117.5°	648.2	650.0	651.7	652.7	652.9	653.1	653.2	653.4
120°	693.8	695.5	697.3	698.2	698.2	698.2	698.2	698.2
122.5°	738.3	739.6	740.8	741.5	741.7	741.8	742.1	742.3
125°	801.2	801.6	802.0	802.5	802.9	803.4	803.8	804.3
127.5°	864.1	864.8	865.5	865.6	865.2	864.8	864.4	863.8
130°	902.1	902.9	903.9	904.0	903.6	903.2	902.8	902.3
132.5°	938.1	939.0	939.9	940.0	939.4	938.7	938.1	937.5
135°	992.6	993.3	994.0	994.0	993.3	992.6	992.0	991.4
137.5°	1041.3	1042.3	1043.4	1043.7	1043.3	1042.8	1042.4	1041.9
140°	1072.1	1073.0	1073.9	1074.1	1073.7	1073.2	1072.8	1072.4
142.5°	1101.4	1102.1	1102.8	1102.9	1102.3	1101.6	1101.0	1100.4
145°	1142.3	1142.7	1143.1	1143.3	1143.3	1143.3	1143.3	1143.3
147.5°	1178.9	1179.3	1179.7	1179.5	1178.5	1177.4	1176.4	1175.4
150°	1201.3	1201.7	1202.1	1202.0	1201.4	1200.8	1200.1	1199.4
152.5°	1221.2	1222.0	1222.8	1222.7	1221.7	1220.6	1219.6	1218.6
155°	1248.6	1249.7	1250.9	1250.7	1249.4	1248.1	1246.7	1245.4
157.5°	1272.5	1273.8	1275.1	1275.0	1273.2	1271.4	1269.7	1268.0
160°	1286.1	1287.4	1288.7	1288.7	1287.1	1285.6	1283.9	1282.4
162.5°	1298.5	1299.9	1301.5	1301.5	1300.1	1298.7	1297.4	1296.0
165°	1315.0	1316.7	1318.5	1318.6	1317.1	1315.5	1314.0	1312.4
167.5°	1327.7	1329.6	1331.4	1331.4	1329.6	1327.7	1326.0	1324.2
170°	1335.0	1336.8	1338.5	1338.5	1336.8	1335.0	1333.2	1331.5
172.5°	1339.8	1341.5	1343.3	1343.2	1341.3	1339.4	1337.4	1335.4
175°	1345.6	1347.1	1348.7	1348.5	1346.8	1345.0	1343.2	1341.4
177.5°	1347.6	1349.1	1350.5	1350.3	1348.6	1346.8	1345.0	1343.2
180°	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4	1346.4

(END OF REPORT)