

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332243-935

Luminaire Tested: **S123RDIP-S340D365U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332243-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2367.5 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47																				
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40																				
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	42	41	39	34																				
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34	29																				
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25																				
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	22																				
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20																				
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18																				
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	24	20	18	16																				
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	16	14																				
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	2.0
10°-20°	129.2	5.5
20°-30°	186.1	7.9
30°-40°	209.6	8.9
40°-50°	200.5	8.5
50°-60°	164.2	6.9
60°-70°	110.8	4.7
70°-80°	55.7	2.4
80°-90°	15.9	0.7
90°-100°	14.9	0.6
100°-110°	71.0	3.0
110°-120°	170.4	7.2
120°-130°	217.0	9.2
130°-140°	231.9	9.8
140°-150°	216.9	9.2
150°-160°	174.9	7.4
160°-170°	112.9	4.8
170°-180°	38.9	1.6
0°-30°	361.8	15.3
0°-40°	571.4	24.1
0°-60°	936.2	39.5
0°-90°	1118.6	47.2
90°-120°	256.3	10.8
90°-150°	922.1	38.9
90°-180°	1249.0	52.8
0°-180°	2367.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	0	3	7	8	9	2
95°	19	7	10	11	12	23
105°	91	92	67	16	13	96
115°	170	172	175	178	179	168
125°	240	242	243	244	245	214
135°	298	300	302	302	302	230
145°	344	346	347	348	348	216
155°	379	379	379	380	379	175
165°	400	399	399	401	399	113
175°	410	408	408	410	408	39
180°	410	410	410	410	410	



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.7	7.1	6.5	5.9	5.2	4.9	5.1	5.3	5.4	5.6	5.6
90°	0.3	0.9	1.6	2.3	3.0	3.8	4.6	5.5	6.5	7.3	7.6
92.5°	5.7	5.5	5.3	5.1	4.9	5.2	5.8	6.5	7.1	7.7	8.2
95°	18.6	15.8	13.0	10.2	7.5	6.5	7.2	7.9	8.7	9.5	9.9
97.5°	37.3	36.1	34.8	33.6	32.3	29.3	24.4	19.5	14.6	9.8	10.3
100°	51.4	52.8	54.2	55.4	56.8	52.3	41.7	31.2	20.6	10.1	10.6
102.5°	67.5	68.4	69.4	70.4	71.4	66.1	54.6	43.0	31.5	20.1	18.3
105°	90.7	91.4	92.1	92.9	93.7	91.0	84.9	78.8	72.8	66.6	54.7
107.5°	115.1	115.7	116.3	116.9	117.5	118.3	119.2	120.2	121.1	122.1	113.3
110°	131.5	132.0	132.5	133.0	133.6	134.2	135.0	135.7	136.5	137.2	135.0



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	147.0	147.5	148.0	148.4	149.0	149.6	150.3	151.1	151.8	152.6	152.6
115°	170.0	170.5	170.9	171.3	171.7	172.2	172.8	173.4	174.0	174.6	175.3
117.5°	192.4	193.0	193.4	193.9	194.4	194.8	195.1	195.4	195.8	196.0	196.6
120°	206.3	206.9	207.5	208.1	208.7	209.1	209.3	209.6	209.7	209.9	210.5
122.5°	220.4	220.9	221.4	221.9	222.4	222.7	223.0	223.3	223.5	223.8	224.2
125°	239.8	240.3	240.8	241.3	241.9	242.3	242.6	242.9	243.1	243.4	243.6
127.5°	258.5	259.1	259.6	260.1	260.6	261.1	261.4	261.7	262.1	262.3	262.6
130°	270.2	270.7	271.2	271.8	272.3	272.8	273.0	273.3	273.5	273.8	274.1
132.5°	281.4	281.9	282.5	283.0	283.5	283.9	284.1	284.4	284.6	284.8	285.1
135°	298.5	298.9	299.3	299.7	300.1	300.4	300.7	301.0	301.3	301.5	301.7
137.5°	313.1	313.6	314.1	314.6	315.1	315.5	315.6	315.7	315.9	316.1	316.4
140°	322.8	323.2	323.6	324.0	324.4	324.8	324.9	325.1	325.4	325.5	325.8
142.5°	331.8	332.3	332.6	333.0	333.5	333.7	334.0	334.2	334.3	334.6	334.8
145°	344.4	344.9	345.3	345.9	346.3	346.6	346.7	346.9	347.0	347.2	347.3
147.5°	356.3	356.6	356.9	357.2	357.5	357.7	357.9	358.0	358.2	358.3	358.4
150°	363.6	363.8	363.9	364.2	364.4	364.5	364.7	364.8	365.0	365.1	365.2
152.5°	370.1	370.2	370.3	370.4	370.5	370.7	370.7	370.7	370.8	370.9	371.2
155°	379.4	379.3	379.1	379.0	378.8	378.8	378.9	378.9	379.0	379.1	379.4
157.5°	386.6	386.6	386.6	386.5	386.5	386.5	386.4	386.3	386.2	386.2	386.6
160°	391.0	390.9	390.8	390.7	390.7	390.6	390.5	390.5	390.5	390.4	390.7
162.5°	395.1	394.9	394.8	394.6	394.4	394.3	394.2	394.2	394.1	394.0	394.4
165°	400.1	399.8	399.7	399.5	399.2	399.2	399.1	399.0	398.9	398.9	399.4
167.5°	404.0	403.7	403.5	403.2	402.9	402.8	402.8	402.8	402.8	402.8	403.3
170°	406.1	405.9	405.6	405.4	405.1	404.9	404.9	404.9	404.9	404.9	405.5
172.5°	407.6	407.3	407.0	406.7	406.3	406.2	406.2	406.3	406.4	406.4	407.0
175°	409.5	409.1	408.8	408.5	408.2	408.0	408.1	408.2	408.2	408.3	408.8
177.5°	410.0	409.7	409.5	409.2	408.9	408.8	408.9	408.9	409.0	409.1	409.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	5.6	5.6	5.6	5.5	5.5	5.4	5.4	5.3
90°	7.8	8.1	8.4	8.6	8.7	8.9	9.0	9.1
92.5°	8.7	9.1	9.6	9.8	9.8	9.9	10.0	10.1
95°	10.4	10.8	11.4	11.5	11.5	11.5	11.5	11.5
97.5°	10.8	11.5	12.0	12.2	12.3	12.4	12.5	12.6
100°	11.1	11.6	12.2	12.5	12.6	12.7	12.7	12.7
102.5°	16.7	15.0	13.3	12.6	12.7	12.7	12.9	13.0
105°	42.7	30.7	18.8	12.8	13.0	13.1	13.3	13.3
107.5°	104.6	95.8	87.0	78.1	69.1	60.1	51.1	42.0
110°	132.8	130.5	128.3	122.3	112.7	103.0	93.3	83.7



TEST NUMBER: P332243-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	152.7	152.7	152.7	151.7	149.6	147.7	145.6	143.5
115°	176.0	176.7	177.4	177.8	178.1	178.4	178.7	178.9
117.5°	197.2	197.7	198.2	198.5	198.5	198.6	198.7	198.7
120°	211.0	211.5	212.1	212.4	212.4	212.4	212.4	212.4
122.5°	224.5	225.0	225.3	225.5	225.6	225.7	225.7	225.8
125°	243.7	243.8	243.9	244.1	244.2	244.4	244.5	244.6
127.5°	262.8	263.0	263.3	263.3	263.1	263.0	262.9	262.8
130°	274.4	274.7	274.9	275.0	274.8	274.7	274.6	274.4
132.5°	285.3	285.6	285.9	285.9	285.7	285.5	285.3	285.2
135°	302.0	302.1	302.3	302.3	302.1	302.0	301.7	301.5
137.5°	316.7	317.0	317.4	317.5	317.3	317.2	317.0	316.9
140°	326.1	326.3	326.7	326.7	326.6	326.4	326.3	326.1
142.5°	335.0	335.2	335.4	335.4	335.3	335.0	334.8	334.7
145°	347.4	347.6	347.7	347.8	347.8	347.8	347.8	347.8
147.5°	358.5	358.7	358.9	358.8	358.4	358.1	357.8	357.5
150°	365.4	365.5	365.7	365.6	365.4	365.2	365.0	364.8
152.5°	371.4	371.7	372.0	371.9	371.6	371.3	370.9	370.7
155°	379.8	380.1	380.5	380.4	380.0	379.6	379.2	378.8
157.5°	387.0	387.4	387.9	387.8	387.3	386.8	386.2	385.6
160°	391.2	391.6	392.0	391.9	391.5	391.0	390.5	390.0
162.5°	394.9	395.4	395.8	395.9	395.5	395.0	394.6	394.2
165°	399.9	400.5	401.1	401.1	400.6	400.1	399.7	399.2
167.5°	403.8	404.4	404.9	404.9	404.4	403.8	403.3	402.8
170°	406.0	406.6	407.1	407.1	406.6	406.0	405.5	404.9
172.5°	407.5	408.0	408.5	408.5	407.9	407.3	406.7	406.1
175°	409.2	409.7	410.2	410.2	409.7	409.1	408.5	408.0
177.5°	409.9	410.4	410.8	410.7	410.2	409.7	409.1	408.5
180°	409.5	409.5	409.5	409.5	409.5	409.5	409.5	409.5

(END OF REPORT)