

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831923

Luminaire Tested: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831923  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7740.8 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	0	
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50	50	50	0	
2	92	85	79	75	86	80	75	71	69	66	63	60	57	55	51	49	48	43	43	43	0	
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38	38	38	0	
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34	34	34	0	
5	72	61	54	48	67	58	51	46	51	45	41	45	40	37	39	36	33	30	30	30	0	
6	67	55	48	42	62	52	45	40	46	41	37	41	37	33	36	32	30	27	27	27	0	
7	62	51	43	38	58	48	41	36	43	37	33	38	33	30	33	30	27	25	25	25	0	
8	58	46	39	34	54	44	37	33	39	34	30	35	30	27	31	27	25	22	22	22	0	
9	54	43	36	31	51	41	34	30	36	31	27	32	28	25	29	25	23	21	21	21	0	
10	51	40	33	28	48	38	31	27	34	29	25	30	26	23	27	23	21	19	19	19	0	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	35972	35972	35972	35972	35972
5°	42712	41351	36199	29262	27167
10°	38699	42001	36018	23446	20113
15°	26644	36012	35638	19163	15911
20°	18536	27726	34922	16158	13985
25°	14125	21131	33882	14361	12889
30°	12296	16894	32579	13335	11938
35°	11289	14251	30734	12469	11073
40°	10301	12726	28322	11619	10281
45°	9302	11639	25718	10816	9490
50°	8443	10739	22647	10027	8512
55°	7638	9862	19697	9257	7302
60°	6844	8966	17108	8407	6902
65°	6316	7957	14727	7554	6525
70°	5133	6877	12850	6836	5303
75°	4500	5469	10884	5669	4675
80°	4079	4630	8920	4754	4420
85°	3717	4063	6768	4310	4063

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 27136 cd/sqm



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	304.6	3.9
10°-20°	704.9	9.1
20°-30°	808.7	10.4
30°-40°	797.1	10.3
40°-50°	703.0	9.1
50°-60°	540.8	7.0
60°-70°	355.6	4.6
70°-80°	172.7	2.2
80°-90°	46.0	0.6
90°-100°	238.6	3.1
100°-110°	698.6	9.0
110°-120°	682.2	8.8
120°-130°	543.3	7.0
130°-140°	428.6	5.5
140°-150°	319.8	4.1
150°-160°	222.9	2.9
160°-170°	131.0	1.7
170°-180°	42.6	0.6
0°-30°	1818.2	23.5
0°-40°	2615.4	33.8
0°-60°	3859.1	49.9
0°-90°	4433.3	57.3
90°-120°	1619.3	20.9
90°-150°	2911.0	37.6
90°-180°	3308.0	42.7
0°-180°	7740.8	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3342	3342	3342	3342	3342	
5°	3953	3827	3350	2708	2514	361
15°	2391	3232	3198	1720	1428	675
25°	1189	1779	2853	1209	1085	562
35°	859	1084	2339	949	843	536
45°	611	765	1690	710	623	474
55°	407	526	1050	493	389	365
65°	248	312	578	297	256	243
75°	108	132	262	136	112	116
85°	30	33	55	35	33	32
90°	26	22	2	22	26	15
95°	103	528	30	528	103	168
105°	1132	716	103	716	1132	1130
115°	1377	547	182	547	1377	1343
125°	1086	511	254	511	1086	983
135°	880	504	297	504	880	683
145°	688	498	339	498	688	437
155°	570	482	385	482	570	266
165°	498	461	421	461	498	142
175°	448	442	439	442	448	43
180°	440	440	440	440	440	



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3703.7	3692.0	3680.4	3676.9	3673.5	3662.6	3651.6	3626.9	3602.3	3576.9	3551.6
5°	3953.0	3954.4	3955.8	3952.4	3948.9	3934.5	3920.2	3890.0	3859.9	3827.0	3794.1
7.5°	3876.3	3898.2	3920.2	3924.3	3928.4	3939.3	3950.3	3943.5	3936.6	3924.3	3911.9
10°	3540.6	3539.2	3537.9	3562.5	3587.2	3660.5	3733.8	3771.5	3809.2	3842.7	3876.3
12.5°	2992.5	2994.6	2996.6	3077.5	3158.3	3227.5	3296.7	3392.6	3488.5	3592.0	3695.4
15°	2391.0	2424.6	2458.1	2530.1	2602.0	2706.2	2810.3	2939.1	3067.9	3231.6	3395.4
17.5°	1963.5	1977.9	1992.3	2061.5	2130.7	2229.3	2328.0	2473.9	2619.8	2830.8	3041.9
20°	1618.2	1631.2	1644.2	1694.3	1744.3	1838.8	1933.4	2072.4	2211.5	2420.5	2629.4
22.5°	1351.0	1376.4	1401.7	1435.3	1468.9	1537.4	1605.9	1747.7	1889.5	2080.0	2270.4
25°	1189.3	1201.0	1212.6	1241.4	1270.2	1336.0	1401.7	1495.6	1589.4	1779.2	1969.0
27.5°	1079.7	1083.1	1086.6	1107.8	1129.0	1171.5	1214.0	1301.0	1388.0	1544.2	1700.4
30°	989.3	995.5	1001.6	1018.1	1034.5	1065.3	1096.2	1157.8	1219.5	1359.2	1499.0
32.5°	919.4	922.8	926.3	940.0	953.7	976.3	998.9	1047.5	1096.2	1203.0	1309.9
35°	859.1	859.8	860.5	870.8	881.0	903.0	924.9	965.3	1005.7	1084.5	1163.3
37.5°	790.6	795.4	800.2	807.7	815.3	834.5	853.6	886.5	919.4	984.5	1049.6
40°	733.1	737.2	741.3	750.2	759.1	774.2	789.2	819.4	849.5	905.7	961.9
42.5°	675.5	678.3	681.0	689.9	698.8	717.3	735.8	759.8	783.8	830.3	876.9
45°	611.1	618.0	624.8	634.4	644.0	659.8	675.5	700.2	724.8	764.6	804.3
47.5°	557.7	561.1	564.5	572.7	581.0	600.2	619.3	641.3	663.2	700.2	737.2
50°	504.2	505.6	507.0	514.5	522.0	539.2	556.3	581.7	607.0	641.3	675.5
52.5°	453.5	457.0	460.4	467.9	475.5	487.1	498.8	524.8	550.8	584.4	618.0
55°	407.0	409.0	411.1	416.5	422.0	435.7	449.4	472.0	494.6	525.5	556.3
57.5°	363.1	365.8	368.6	372.7	376.8	389.1	401.5	421.3	441.2	472.0	502.9
60°	317.9	321.3	324.7	329.5	334.3	343.9	353.5	371.3	389.1	416.5	443.9
62.5°	285.0	285.7	286.4	290.5	294.6	301.4	308.3	322.7	337.1	364.5	391.9
65°	248.0	250.1	252.1	254.2	256.2	261.7	267.2	279.5	291.9	312.4	333.0
67.5°	209.6	211.7	213.8	217.2	220.6	225.4	230.2	238.4	246.6	265.8	285.0
70°	163.1	163.1	163.1	168.5	174.0	182.2	190.5	196.6	202.8	218.5	234.3
72.5°	132.9	133.6	134.3	135.0	135.7	140.4	145.2	155.5	165.8	175.4	185.0
75°	108.2	108.9	109.6	110.3	111.0	112.4	113.7	117.2	120.6	131.5	142.5
77.5°	86.3	87.0	87.7	88.4	89.1	90.4	91.8	93.2	94.5	98.7	102.8
80°	65.8	66.5	67.1	67.8	68.5	69.2	69.9	71.3	72.6	74.7	76.7
82.5°	48.0	48.0	48.0	48.0	48.0	49.3	50.7	50.7	50.7	52.1	53.4
85°	30.1	30.1	30.1	30.8	31.5	31.5	31.5	32.2	32.9	32.9	32.9
87.5°	13.7	13.0	12.3	13.0	13.7	13.7	13.7	14.4	15.1	15.1	15.1
90°	25.8	26.7	25.8	24.9	25.8	24.0	23.1	22.3	21.4	22.3	19.6
92.5°	47.2	49.0	48.1	51.6	53.4	59.6	68.5	88.1	123.7	165.6	183.4
95°	103.3	106.8	113.0	121.1	138.0	170.0	217.2	320.4	428.1	527.8	470.0
97.5°	211.8	221.6	243.0	276.8	336.5	437.9	555.4	736.1	839.4	811.8	606.1
100°	558.1	557.2	591.9	656.9	746.8	873.2	977.3	1049.4	1018.3	842.9	569.7
102.5°	883.9	909.7	937.3	985.3	1050.3	1118.8	1168.7	1153.6	1027.2	785.1	516.3
105°	1132.2	1136.6	1165.1	1198.9	1239.9	1263.0	1246.1	1157.1	971.1	715.6	474.4
107.5°	1294.2	1304.0	1315.5	1331.6	1336.9	1312.9	1243.5	1103.7	891.0	654.2	444.2
110°	1386.8	1388.5	1390.3	1383.2	1358.3	1296.0	1183.8	1020.0	816.2	603.5	428.1



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1405.4	1404.6	1395.7	1369.8	1319.1	1234.6	1105.5	937.3	751.2	569.7	419.2
115°	1377.0	1372.5	1354.7	1315.5	1248.8	1151.8	1020.9	866.1	701.4	547.4	418.3
117.5°	1314.7	1308.4	1281.7	1238.1	1168.7	1068.1	947.9	810.9	668.5	532.3	419.2
120°	1232.8	1227.4	1206.1	1156.2	1085.9	996.0	889.2	769.0	643.5	522.5	422.8
122.5°	1156.2	1149.1	1125.1	1081.5	1020.9	939.0	842.0	736.1	623.1	516.3	429.0
125°	1085.9	1079.7	1057.4	1018.3	961.3	890.1	804.6	707.6	606.1	510.9	435.3
127.5°	1025.4	1020.0	999.6	965.7	914.1	848.3	769.9	681.8	590.1	508.2	442.4
130°	975.5	968.4	949.7	917.7	870.5	810.0	737.9	657.8	577.7	505.6	449.5
132.5°	926.6	922.1	906.1	874.1	830.5	773.5	707.6	635.5	566.1	504.7	454.8
135°	880.3	874.1	858.0	831.3	787.7	737.0	679.1	615.9	556.3	503.8	460.2
137.5°	831.3	826.0	812.6	785.1	747.7	702.3	650.7	597.2	547.4	502.0	463.7
140°	779.7	780.6	766.4	741.4	707.6	669.3	626.6	581.2	539.4	501.1	467.3
142.5°	731.7	732.5	720.1	698.7	671.1	639.1	603.5	566.1	532.3	499.3	470.0
145°	688.0	686.3	679.1	660.4	638.2	612.4	583.9	554.5	526.0	497.6	470.9
147.5°	650.7	649.8	642.6	629.3	611.5	592.8	568.8	544.7	519.8	494.9	470.9
150°	618.6	618.6	613.3	603.5	590.1	573.2	554.5	534.1	513.6	491.3	470.9
152.5°	591.9	591.9	589.2	580.3	570.5	557.2	541.2	524.3	506.5	486.9	468.2
155°	570.5	569.7	567.9	560.8	552.7	542.1	528.7	514.5	499.3	481.5	466.4
157.5°	550.1	550.1	548.3	543.0	535.8	526.9	516.3	503.8	491.3	477.1	463.7
160°	530.5	531.4	531.4	526.0	519.8	513.6	504.7	494.9	483.3	471.7	462.0
162.5°	512.7	513.6	513.6	509.1	505.6	500.2	492.2	484.2	475.3	466.4	458.4
165°	497.6	497.6	498.4	494.9	491.3	486.9	480.6	475.3	468.2	461.1	454.8
167.5°	482.4	482.4	483.3	480.6	478.9	475.3	471.7	467.3	461.1	455.7	451.3
170°	469.1	469.1	470.0	468.2	467.3	465.5	462.0	459.3	454.8	450.4	447.7
172.5°	456.6	457.5	459.3	457.5	457.5	456.6	453.9	452.2	448.6	445.9	445.0
175°	447.7	448.6	449.5	448.6	448.6	448.6	446.8	445.9	444.2	442.4	442.4
177.5°	441.5	441.5	443.3	442.4	443.3	443.3	442.4	441.5	440.6	439.7	440.6
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3548.1	3544.7	3511.8	3479.0	3446.8	3414.6	3390.6	3366.6	3326.2	3285.8	3260.4
5°	3768.1	3742.0	3690.0	3637.9	3559.8	3481.7	3415.9	3350.2	3266.6	3183.0	3113.1
7.5°	3890.7	3869.5	3806.4	3743.4	3640.0	3536.5	3433.7	3331.0	3207.7	3084.3	2978.8
10°	3894.1	3911.9	3859.9	3807.8	3691.3	3574.9	3435.1	3295.3	3129.6	2963.8	2827.4
12.5°	3772.2	3848.9	3837.9	3827.0	3708.5	3589.9	3420.0	3250.1	3046.7	2843.2	2672.6
15°	3544.0	3692.7	3736.6	3780.4	3682.4	3584.5	3391.3	3198.1	2959.0	2719.9	2523.9
17.5°	3250.1	3458.4	3574.2	3690.0	3618.7	3547.5	3335.8	3124.1	2854.8	2585.6	2372.5
20°	2902.1	3174.8	3356.3	3537.9	3511.8	3485.8	3267.3	3048.7	2758.2	2467.7	2236.9
22.5°	2558.2	2845.9	3096.7	3347.4	3374.1	3400.9	3180.2	2959.6	2641.8	2323.9	2088.9
25°	2261.5	2554.1	2852.8	3151.5	3211.8	3272.1	3062.4	2852.8	2523.2	2193.7	1960.1
27.5°	1978.6	2256.7	2585.6	2914.4	3024.0	3133.7	2941.8	2750.0	2406.8	2063.5	1830.6
30°	1747.7	1996.4	2332.1	2667.8	2820.6	2973.3	2797.3	2621.2	2280.7	1940.2	1712.1
32.5°	1532.6	1755.2	2092.3	2429.4	2606.8	2784.3	2632.2	2480.1	2152.6	1825.1	1599.7
35°	1362.7	1562.0	1876.5	2191.0	2389.6	2588.3	2463.6	2338.9	2019.0	1699.1	1486.0
37.5°	1216.7	1383.9	1679.2	1974.5	2185.5	2396.5	2292.4	2188.2	1887.5	1586.7	1385.3
40°	1096.2	1230.4	1505.2	1779.9	1986.8	2193.7	2104.6	2015.6	1746.3	1477.1	1288.7
42.5°	992.7	1108.5	1355.1	1601.8	1791.5	1981.3	1922.4	1863.5	1619.6	1375.7	1201.0
45°	901.6	998.9	1216.1	1433.2	1607.9	1782.6	1736.1	1689.5	1479.1	1268.8	1108.5
47.5°	820.8	904.3	1098.2	1292.1	1449.0	1605.9	1562.7	1519.6	1345.5	1171.5	1025.6
50°	746.8	818.0	979.7	1141.4	1282.5	1423.6	1388.0	1352.4	1208.5	1064.7	938.6
52.5°	676.9	735.8	881.0	1026.3	1140.0	1253.7	1226.3	1198.9	1087.9	977.0	862.5
55°	610.4	664.5	787.2	909.8	1007.1	1104.4	1077.0	1049.6	963.3	876.9	776.2
57.5°	550.1	597.4	696.7	796.1	873.5	950.9	937.9	924.9	853.0	781.0	698.1
60°	486.4	528.9	614.5	700.2	762.5	824.9	809.8	794.7	743.3	692.0	620.7
62.5°	429.6	467.2	535.8	604.3	655.0	705.7	694.7	683.7	644.7	605.6	546.7
65°	370.0	407.0	462.4	517.9	557.7	597.4	587.8	578.2	548.8	519.3	472.0
67.5°	315.8	346.7	394.6	442.6	469.3	496.0	490.5	485.1	462.4	439.8	402.8
70°	261.0	287.7	327.5	367.2	385.7	404.2	406.3	408.3	387.8	367.2	339.8
72.5°	206.2	227.5	264.4	301.4	315.8	330.2	329.5	328.8	316.5	304.2	279.5
75°	158.3	174.0	202.8	231.6	243.9	256.2	259.0	261.7	250.1	238.4	224.7
77.5°	113.7	124.7	146.6	168.5	182.2	195.9	197.3	198.7	193.2	187.7	174.7
80°	80.2	83.6	97.3	111.0	125.4	139.8	141.8	143.9	138.4	132.9	124.7
82.5°	55.5	57.5	62.3	67.1	78.8	90.4	93.2	95.9	93.2	90.4	81.5
85°	33.6	34.3	36.3	38.4	43.8	49.3	52.1	54.8	53.4	52.1	47.3
87.5°	15.1	15.1	15.8	16.4	17.8	19.2	22.6	26.0	24.0	21.9	19.9
90°	16.9	14.2	11.6	9.8	8.0	5.3	3.6	1.8	3.6	5.3	8.0
92.5°	137.1	89.9	61.4	45.4	36.5	28.5	19.6	13.4	19.6	28.5	36.5
95°	324.0	191.4	115.7	81.0	57.9	42.7	32.9	30.3	32.9	42.7	57.9
97.5°	360.5	206.5	131.7	93.5	70.3	57.0	49.0	48.1	49.0	57.0	70.3
100°	335.6	203.8	141.5	106.8	85.4	73.0	66.8	65.9	66.8	73.0	85.4
102.5°	314.2	207.4	153.1	121.9	103.3	91.7	86.3	84.6	86.3	91.7	103.3
105°	306.2	214.5	166.4	138.9	121.9	111.3	105.9	103.3	105.9	111.3	121.9
107.5°	304.4	226.1	183.4	157.5	141.5	130.8	125.5	122.8	125.5	130.8	141.5
110°	308.9	241.2	201.2	176.2	161.1	151.3	146.9	144.2	146.9	151.3	161.1





TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	317.8	256.3	219.9	195.8	180.7	170.9	166.4	163.8	166.4	170.9	180.7
115°	327.6	273.3	239.4	215.4	200.3	191.4	186.0	182.5	186.0	191.4	200.3
117.5°	340.0	291.1	257.2	235.0	218.1	210.1	205.6	201.2	205.6	210.1	218.1
120°	354.3	308.0	275.9	253.7	236.8	227.9	223.4	220.7	223.4	227.9	236.8
122.5°	367.6	325.8	294.6	270.6	254.6	244.8	240.3	237.7	240.3	244.8	254.6
125°	381.8	342.7	311.5	287.5	270.6	260.8	255.5	253.7	255.5	260.8	270.6
127.5°	393.4	357.8	327.6	303.5	284.8	275.0	268.8	266.1	268.8	275.0	284.8
130°	405.0	371.2	341.8	317.8	299.1	288.4	280.4	277.7	280.4	288.4	299.1
132.5°	415.7	382.7	354.3	331.1	312.4	299.1	290.2	286.6	290.2	299.1	312.4
135°	424.6	394.3	366.7	342.7	324.0	310.6	300.8	297.3	300.8	310.6	324.0
137.5°	431.7	402.3	375.6	353.4	334.7	320.4	310.6	307.1	310.6	320.4	334.7
140°	437.0	410.3	384.5	362.3	344.5	330.2	321.3	316.9	321.3	330.2	344.5
142.5°	442.4	416.6	391.6	371.2	353.4	340.9	331.1	327.6	331.1	340.9	353.4
145°	445.9	421.9	398.8	378.3	363.2	349.8	341.8	339.1	341.8	349.8	363.2
147.5°	448.6	426.4	405.0	387.2	372.1	360.5	352.5	350.7	352.5	360.5	372.1
150°	449.5	430.8	410.3	394.3	381.8	370.3	363.2	362.3	363.2	370.3	381.8
152.5°	451.3	433.5	416.6	401.4	390.7	381.0	373.8	373.8	373.8	381.0	390.7
155°	451.3	437.0	421.9	409.4	399.6	390.7	385.4	385.4	385.4	390.7	399.6
157.5°	452.2	438.8	426.4	416.6	407.7	399.6	395.2	394.3	395.2	399.6	407.7
160°	452.2	441.5	430.8	421.9	415.7	408.5	405.0	405.0	405.0	408.5	415.7
162.5°	451.3	442.4	433.5	426.4	421.0	415.7	413.0	413.0	413.0	415.7	421.0
165°	449.5	443.3	436.1	429.9	426.4	421.9	420.1	421.0	420.1	421.9	426.4
167.5°	448.6	443.3	437.9	433.5	430.8	427.2	426.4	427.2	426.4	427.2	430.8
170°	445.9	442.4	437.9	436.1	434.4	431.7	430.8	432.6	430.8	431.7	434.4
172.5°	445.0	442.4	438.8	437.9	437.0	435.3	435.3	436.1	435.3	435.3	437.0
175°	443.3	441.5	439.7	438.8	438.8	437.0	437.9	438.8	437.9	437.0	438.8
177.5°	442.4	440.6	439.7	439.7	439.7	438.8	439.7	440.6	439.7	438.8	439.7
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9	3341.9
2.5°	3235.1	3196.0	3157.0	3128.9	3100.8	3065.8	3030.9	3029.5	3028.2	3002.1	2976.1
5°	3043.2	2975.4	2907.6	2841.1	2774.7	2708.2	2641.8	2626.7	2611.6	2589.0	2566.4
7.5°	2873.3	2765.1	2656.8	2571.9	2486.9	2420.5	2354.0	2308.8	2263.6	2228.6	2193.7
10°	2691.1	2556.8	2422.5	2319.8	2217.0	2145.1	2073.1	2021.1	1969.0	1944.3	1919.7
12.5°	2502.0	2356.1	2210.1	2109.4	2008.7	1922.4	1836.1	1788.8	1741.5	1707.3	1673.0
15°	2328.0	2171.1	2014.2	1907.3	1800.5	1719.6	1638.8	1591.5	1544.2	1510.0	1475.7
17.5°	2159.4	2001.2	1842.9	1734.7	1626.4	1553.1	1479.8	1433.9	1388.0	1366.8	1345.5
20°	2006.0	1846.4	1686.7	1584.6	1482.6	1410.6	1338.7	1314.0	1289.4	1269.5	1249.6
22.5°	1853.9	1700.4	1547.0	1449.0	1351.0	1299.0	1246.9	1227.0	1207.2	1192.1	1177.0
25°	1726.5	1573.7	1420.9	1335.3	1249.6	1209.2	1168.8	1155.8	1142.8	1127.7	1112.6
27.5°	1597.7	1452.4	1307.2	1238.7	1170.2	1137.3	1104.4	1087.9	1071.5	1059.2	1046.8
30°	1483.9	1349.7	1215.4	1158.5	1101.6	1072.9	1044.1	1026.3	1008.5	996.8	985.2
32.5°	1374.3	1255.1	1135.9	1087.3	1038.6	1010.5	982.4	965.3	948.2	934.5	920.8
35°	1272.9	1169.5	1066.0	1021.5	977.0	948.9	920.8	903.7	886.5	872.8	859.1
37.5°	1183.9	1090.0	996.1	954.3	912.6	887.9	863.2	845.4	827.6	813.2	798.8
40°	1100.3	1017.4	934.5	894.1	853.6	826.9	800.2	784.4	768.7	755.7	742.7
42.5°	1026.3	950.2	874.2	834.5	794.7	769.4	744.0	725.5	707.0	699.5	692.0
45°	948.2	881.0	813.9	775.5	737.2	710.5	683.7	668.0	652.2	645.4	638.5
47.5°	879.7	817.3	755.0	717.3	679.6	655.6	631.7	619.3	607.0	597.4	587.8
50°	812.5	752.2	692.0	655.6	619.3	598.8	578.2	563.2	548.1	541.2	534.4
52.5°	748.1	693.3	638.5	601.5	564.5	544.7	524.8	511.8	498.8	484.4	470.0
55°	675.5	627.6	579.6	546.7	513.8	493.3	472.7	457.6	442.6	427.5	412.4
57.5°	615.2	568.0	520.7	491.2	461.8	441.9	422.0	405.6	389.1	376.8	364.5
60°	549.5	508.3	467.2	438.5	409.7	390.5	371.3	355.6	339.8	333.6	327.5
62.5°	487.8	449.4	411.1	385.7	360.4	341.9	323.4	313.1	302.8	298.7	294.6
65°	424.8	391.9	359.0	335.7	312.4	296.6	280.9	276.1	271.3	267.9	264.4
67.5°	365.8	337.8	309.7	289.1	268.6	257.6	246.6	241.2	235.7	231.6	227.5
70°	312.4	287.7	263.1	245.3	227.5	217.2	206.9	202.1	197.3	189.8	182.2
72.5°	254.9	235.7	216.5	202.8	189.1	180.2	171.3	161.7	152.1	145.2	138.4
75°	211.0	191.8	172.6	159.6	146.6	136.3	126.1	122.6	119.2	117.2	115.1
77.5°	161.7	145.2	128.8	118.5	108.2	103.5	98.7	96.6	94.5	93.9	93.2
80°	116.5	102.8	89.1	83.6	78.1	76.7	75.4	74.0	72.6	71.9	71.3
82.5°	72.6	65.8	58.9	57.5	56.2	55.5	54.8	54.1	53.4	52.8	52.1
85°	42.5	39.7	37.0	36.3	35.6	34.9	34.3	34.3	34.3	34.3	34.3
87.5°	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.8	17.1	16.4
90°	9.8	11.6	14.2	16.9	19.6	22.3	21.4	22.3	23.1	24.0	25.8
92.5°	45.4	61.4	89.9	137.1	183.4	165.6	123.7	88.1	68.5	59.6	53.4
95°	81.0	115.7	191.4	324.0	470.0	527.8	428.1	320.4	217.2	170.0	138.0
97.5°	93.5	131.7	206.5	360.5	606.1	811.8	839.4	736.1	555.4	437.9	336.5
100°	106.8	141.5	203.8	335.6	569.7	842.9	1018.3	1049.4	977.3	873.2	746.8
102.5°	121.9	153.1	207.4	314.2	516.3	785.1	1027.2	1153.6	1168.7	1118.8	1050.3
105°	138.9	166.4	214.5	306.2	474.4	715.6	971.1	1157.1	1246.1	1263.0	1239.9
107.5°	157.5	183.4	226.1	304.4	444.2	654.2	891.0	1103.7	1243.5	1312.9	1336.9
110°	176.2	201.2	241.2	308.9	428.1	603.5	816.2	1020.0	1183.8	1296.0	1358.3



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	195.8	219.9	256.3	317.8	419.2	569.7	751.2	937.3	1105.5	1234.6	1319.1
115°	215.4	239.4	273.3	327.6	418.3	547.4	701.4	866.1	1020.9	1151.8	1248.8
117.5°	235.0	257.2	291.1	340.0	419.2	532.3	668.5	810.9	947.9	1068.1	1168.7
120°	253.7	275.9	308.0	354.3	422.8	522.5	643.5	769.0	889.2	996.0	1085.9
122.5°	270.6	294.6	325.8	367.6	429.0	516.3	623.1	736.1	842.0	939.0	1020.9
125°	287.5	311.5	342.7	381.8	435.3	510.9	606.1	707.6	804.6	890.1	961.3
127.5°	303.5	327.6	357.8	393.4	442.4	508.2	590.1	681.8	769.9	848.3	914.1
130°	317.8	341.8	371.2	405.0	449.5	505.6	577.7	657.8	737.9	810.0	870.5
132.5°	331.1	354.3	382.7	415.7	454.8	504.7	566.1	635.5	707.6	773.5	830.5
135°	342.7	366.7	394.3	424.6	460.2	503.8	556.3	615.9	679.1	737.0	787.7
137.5°	353.4	375.6	402.3	431.7	463.7	502.0	547.4	597.2	650.7	702.3	747.7
140°	362.3	384.5	410.3	437.0	467.3	501.1	539.4	581.2	626.6	669.3	707.6
142.5°	371.2	391.6	416.6	442.4	470.0	499.3	532.3	566.1	603.5	639.1	671.1
145°	378.3	398.8	421.9	445.9	470.9	497.6	526.0	554.5	583.9	612.4	638.2
147.5°	387.2	405.0	426.4	448.6	470.9	494.9	519.8	544.7	568.8	592.8	611.5
150°	394.3	410.3	430.8	449.5	470.9	491.3	513.6	534.1	554.5	573.2	590.1
152.5°	401.4	416.6	433.5	451.3	468.2	486.9	506.5	524.3	541.2	557.2	570.5
155°	409.4	421.9	437.0	451.3	466.4	481.5	499.3	514.5	528.7	542.1	552.7
157.5°	416.6	426.4	438.8	452.2	463.7	477.1	491.3	503.8	516.3	526.9	535.8
160°	421.9	430.8	441.5	452.2	462.0	471.7	483.3	494.9	504.7	513.6	519.8
162.5°	426.4	433.5	442.4	451.3	458.4	466.4	475.3	484.2	492.2	500.2	505.6
165°	429.9	436.1	443.3	449.5	454.8	461.1	468.2	475.3	480.6	486.9	491.3
167.5°	433.5	437.9	443.3	448.6	451.3	455.7	461.1	467.3	471.7	475.3	478.9
170°	436.1	437.9	442.4	445.9	447.7	450.4	454.8	459.3	462.0	465.5	467.3
172.5°	437.9	438.8	442.4	445.0	445.0	445.9	448.6	452.2	453.9	456.6	457.5
175°	438.8	439.7	441.5	443.3	442.4	442.4	444.2	445.9	446.8	448.6	448.6
177.5°	439.7	439.7	440.6	442.4	440.6	439.7	440.6	441.5	442.4	443.3	443.3
180°	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7	439.7



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3341.9	3341.9	3341.9	3341.9
2.5°	2969.2	2962.4	2959.6	2956.9
5°	2545.2	2523.9	2519.1	2514.3
7.5°	2184.8	2175.9	2146.4	2117.0
10°	1892.3	1864.9	1852.5	1840.2
12.5°	1647.7	1622.3	1618.2	1614.1
15°	1457.9	1440.1	1433.9	1427.8
17.5°	1333.2	1320.9	1313.3	1305.8
20°	1240.7	1231.8	1226.3	1220.9
22.5°	1170.2	1163.3	1159.2	1155.1
25°	1102.3	1092.1	1088.6	1085.2
27.5°	1037.9	1029.0	1025.6	1022.2
30°	977.6	970.1	965.3	960.5
32.5°	911.9	903.0	900.2	897.5
35°	853.6	848.2	845.4	842.7
37.5°	792.0	785.1	781.0	776.9
40°	739.2	735.8	733.7	731.7
42.5°	685.8	679.6	678.9	678.3
45°	632.4	626.2	624.8	623.4
47.5°	582.3	576.9	576.2	575.5
50°	526.8	519.3	513.8	508.3
52.5°	463.1	456.3	451.5	446.7
55°	404.9	397.4	393.2	389.1
57.5°	361.0	357.6	355.6	353.5
60°	325.4	323.4	322.0	320.6
62.5°	292.5	290.5	290.5	290.5
65°	262.4	260.3	258.3	256.2
67.5°	223.3	219.2	218.5	217.9
70°	176.1	169.9	169.2	168.5
72.5°	137.7	137.0	135.7	134.3
75°	113.7	112.4	112.4	112.4
77.5°	91.8	90.4	90.4	90.4
80°	70.6	69.9	70.6	71.3
82.5°	52.1	52.1	51.4	50.7
85°	33.6	32.9	32.9	32.9
87.5°	16.4	16.4	16.4	16.4
90°	24.9	25.8	26.7	25.8
92.5°	51.6	48.1	49.0	47.2
95°	121.1	113.0	106.8	103.3
97.5°	276.8	243.0	221.6	211.8
100°	656.9	591.9	557.2	558.1
102.5°	985.3	937.3	909.7	883.9
105°	1198.9	1165.1	1136.6	1132.2
107.5°	1331.6	1315.5	1304.0	1294.2
110°	1383.2	1390.3	1388.5	1386.8



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1369.8	1395.7	1404.6	1405.4
115°	1315.5	1354.7	1372.5	1377.0
117.5°	1238.1	1281.7	1308.4	1314.7
120°	1156.2	1206.1	1227.4	1232.8
122.5°	1081.5	1125.1	1149.1	1156.2
125°	1018.3	1057.4	1079.7	1085.9
127.5°	965.7	999.6	1020.0	1025.4
130°	917.7	949.7	968.4	975.5
132.5°	874.1	906.1	922.1	926.6
135°	831.3	858.0	874.1	880.3
137.5°	785.1	812.6	826.0	831.3
140°	741.4	766.4	780.6	779.7
142.5°	698.7	720.1	732.5	731.7
145°	660.4	679.1	686.3	688.0
147.5°	629.3	642.6	649.8	650.7
150°	603.5	613.3	618.6	618.6
152.5°	580.3	589.2	591.9	591.9
155°	560.8	567.9	569.7	570.5
157.5°	543.0	548.3	550.1	550.1
160°	526.0	531.4	531.4	530.5
162.5°	509.1	513.6	513.6	512.7
165°	494.9	498.4	497.6	497.6
167.5°	480.6	483.3	482.4	482.4
170°	468.2	470.0	469.1	469.1
172.5°	457.5	459.3	457.5	456.6
175°	448.6	449.5	448.6	447.7
177.5°	442.4	443.3	441.5	441.5
180°	439.7	439.7	439.7	439.7



TEST NUMBER: P831923

CATALOG NUMBER: S123RDIP-S1165D1025U940-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.85	14.72	14.76	15.63	16.80	18.52	19.38	19.42	20.30	21.47
	3H	15.08	15.85	15.99	16.77	17.97	20.02	20.79	20.93	21.72	22.91
	4H	15.46	16.19	16.39	17.12	18.32	20.51	21.24	21.44	22.17	23.37
	6H	15.74	16.41	16.68	17.35	18.57	20.82	21.50	21.77	22.43	23.65
	8H	15.83	16.47	16.78	17.42	18.64	20.90	21.54	21.85	22.49	23.71
	12H	15.88	16.49	16.84	17.44	18.67	20.94	21.54	21.89	22.49	23.73
4H	2H	14.58	15.31	15.52	16.24	17.44	18.52	19.25	19.45	20.18	21.38
	3H	15.95	16.56	16.90	17.52	18.74	20.18	20.78	21.12	21.74	22.96
	4H	16.41	16.96	17.36	17.92	19.16	20.78	21.34	21.74	22.29	23.53
	6H	16.78	17.25	17.75	18.23	19.47	21.22	21.70	22.19	22.68	23.92
	8H	16.90	17.35	17.87	18.32	19.57	21.36	21.80	22.33	22.77	24.03
	12H	16.98	17.38	17.97	18.37	19.63	21.42	21.82	22.41	22.81	24.07
8H	4H	16.72	17.17	17.70	18.14	19.39	20.75	21.20	21.72	22.17	23.42
	6H	17.19	17.55	18.18	18.57	19.82	21.25	21.62	22.25	22.63	23.88
	8H	17.38	17.70	18.39	18.71	19.98	21.44	21.76	22.44	22.76	24.03
	12H	17.52	17.81	18.53	18.80	20.12	21.56	21.84	22.56	22.83	24.15
12H	4H	16.74	17.14	17.73	18.13	19.39	20.71	21.10	21.69	22.09	23.35
	6H	17.25	17.57	18.25	18.57	19.85	21.23	21.55	22.23	22.55	23.82
	8H	17.47	17.75	18.47	18.75	20.07	21.42	21.70	22.43	22.70	24.02