

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332245-935

Luminaire Tested: **S123RDIP-S340D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332245-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D365U935-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2249.5 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	42	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	58	50	44	63	54	46	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	2.1
10°-20°	129.2	5.7
20°-30°	186.1	8.3
30°-40°	209.6	9.3
40°-50°	200.5	8.9
50°-60°	164.2	7.3
60°-70°	110.8	4.9
70°-80°	55.7	2.5
80°-90°	15.9	0.7
90°-100°	83.7	3.7
100°-110°	236.9	10.5
110°-120°	233.0	10.4
120°-130°	185.8	8.3
130°-140°	146.5	6.5
140°-150°	109.4	4.9
150°-160°	76.2	3.4
160°-170°	44.8	2.0
170°-180°	14.6	0.6
0°-30°	361.8	16.1
0°-40°	571.4	25.4
0°-60°	936.2	41.6
0°-90°	1118.6	49.7
90°-120°	553.5	24.6
90°-150°	995.3	44.2
90°-180°	1131.0	50.3
0°-180°	2249.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	4	8	8	9	2
95°	10	34	180	53	35	11
105°	35	52	245	428	387	38
115°	62	78	187	410	471	62
125°	87	102	175	316	371	77
135°	102	121	172	261	301	79
145°	116	133	170	214	235	73
155°	132	142	165	187	195	61
165°	144	148	158	167	170	41
175°	150	150	151	153	153	14
180°	150	150	150	150	150	



TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.1	6.5	5.9	5.3	5.0	5.2	5.3	5.5	5.7	5.6
90°	0.6	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3
92.5°	3.8	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3
95°	10.3	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4
97.5°	17.7	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1
100°	22.6	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1
102.5°	27.6	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5
105°	35.3	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9
107.5°	43.5	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5
110°	49.2	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1



TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.7	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2
115°	62.3	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8
117.5°	70.1	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8
120°	75.4	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0
122.5°	80.1	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4
125°	86.7	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2
127.5°	91.8	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9
130°	95.0	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4
132.5°	97.4	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3
135°	101.6	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2
137.5°	105.6	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6
140°	108.3	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3
142.5°	111.2	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4
145°	115.9	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8
147.5°	120.7	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3
150°	123.8	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6
152.5°	127.0	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6
155°	131.7	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7
157.5°	135.5	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4
160°	138.4	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2
162.5°	140.6	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0
165°	143.9	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1
167.5°	146.4	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2
170°	147.8	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5
172.5°	148.9	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8
175°	150.0	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8
177.5°	150.6	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	5.5	5.5	5.5	5.6	5.4	5.4	5.4	5.3
90°	7.6	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	25.7	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	109.5	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	273.0	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	358.7	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	387.2	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	395.5	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	371.5	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	348.7	404.7	443.0	464.3	472.9	475.3	474.7	474.1





TEST NUMBER: P332245-935

CATALOG NUMBER: S123RDIP-S340D365U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.1	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	296.0	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	274.3	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	262.9	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	253.9	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	241.9	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	231.4	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	224.8	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	218.8	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	210.5	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	203.0	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	198.7	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	194.6	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	189.6	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	185.5	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	182.5	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	179.9	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	175.9	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	171.6	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	169.2	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	166.3	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	162.5	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	159.2	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.0	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.1	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.4	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	150.8	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)