

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332252-935

Luminaire Tested: **S123RDIP-S340D805U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332252-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U935-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3932.2 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30																				
1	94	90	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	26																				
2	85	79	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28	22																				
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19																				
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17																				
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18	15																				
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13																				
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12																				
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11																				
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10																				
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11	9																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5044	5044	5044	5044
5°	6013	5065	4460	5065
10°	7507	5037	4030	5037
15°	8811	4985	3675	4985
20°	9835	4907	3373	4907
25°	9678	4827	3188	4827
30°	6955	4753	2997	4753
35°	4644	4654	2872	4654
40°	3421	4539	2746	4539
45°	2871	4332	2620	4332
50°	2534	4064	2445	4064
55°	2222	3757	2205	3757
60°	1978	3462	2019	3462
65°	1737	3148	1880	3148
70°	1363	2867	1718	2867
75°	1198	2504	1568	2504
80°	1048	2126	1543	2126
85°	840	1717	1643	1717



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.1	1.2
10°-20°	144.0	3.7
20°-30°	226.2	5.8
30°-40°	236.0	6.0
40°-50°	201.9	5.1
50°-60°	153.9	3.9
60°-70°	98.7	2.5
70°-80°	47.5	1.2
80°-90°	15.1	0.4
90°-100°	32.9	0.8
100°-110°	157.0	4.0
110°-120°	377.1	9.6
120°-130°	480.2	12.2
130°-140°	513.1	13.0
140°-150°	479.8	12.2
150°-160°	387.0	9.8
160°-170°	249.8	6.4
170°-180°	86.1	2.2
0°-30°	416.2	10.6
0°-40°	652.2	16.6
0°-60°	1008.0	25.6
0°-90°	1169.3	29.7
90°-120°	567.0	14.4
90°-150°	2040.1	51.9
90°-180°	2763.0	70.3
0°-180°	3932.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	469	469	469	469	469	
5°	556	469	413	469	556	57
15°	791	447	330	447	791	224
25°	815	406	268	406	815	350
35°	353	354	219	354	353	232
45°	189	285	172	285	189	148
55°	118	200	118	200	118	107
65°	68	124	74	124	68	67
75°	29	60	38	60	29	31
85°	7	14	13	14	7	8
90°	20	1	20	1	20	9
95°	26	41	26	41	26	21
105°	30	201	30	201	30	68
115°	396	376	396	376	396	366
125°	541	530	541	530	541	483
135°	667	660	667	660	667	514
145°	769	762	769	762	769	480
155°	838	839	838	839	838	386
165°	883	885	883	885	883	249
175°	903	906	903	906	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	499.1	499.7	497.7	497.3	494.9	494.3	494.3	490.9	488.8	486.1	484.5
5°	556.5	559.6	558.0	554.5	548.5	547.0	543.2	537.2	530.4	521.9	518.0
7.5°	628.1	632.5	630.8	625.3	618.9	613.8	603.0	593.1	579.1	566.8	556.3
10°	686.8	682.3	678.6	673.2	667.4	658.0	646.7	631.3	613.5	599.3	583.8
12.5°	730.8	730.0	725.5	719.9	711.7	702.7	688.9	670.1	649.4	629.0	611.1
15°	790.7	791.9	788.9	783.2	771.5	755.6	734.8	726.9	697.2	675.2	653.2
17.5°	832.2	832.0	831.6	823.5	811.7	800.4	781.0	760.4	733.6	702.5	672.8
20°	858.6	856.5	857.0	847.9	839.1	826.0	807.2	777.3	755.3	719.4	688.6
22.5°	857.9	857.5	859.0	855.9	849.5	839.6	824.7	799.4	771.3	735.0	700.5
25°	814.9	813.2	822.6	825.3	835.5	837.3	832.8	819.1	792.4	755.0	712.3
27.5°	681.9	681.1	698.5	720.5	748.2	769.8	790.7	800.7	792.4	765.6	722.8
30°	559.6	578.5	587.4	619.1	654.4	696.5	733.4	768.4	777.1	765.4	730.4
32.5°	464.7	481.1	488.5	515.7	548.6	598.0	653.3	703.0	738.1	747.0	725.9
35°	353.4	353.6	370.5	382.5	413.0	463.7	517.5	584.1	650.3	700.5	705.7
37.5°	282.1	283.0	293.3	305.2	328.1	354.9	402.3	457.6	534.1	611.1	656.3
40°	243.5	245.3	253.0	264.8	281.2	301.5	338.4	390.5	454.3	540.0	610.0
42.5°	218.8	221.7	225.7	234.8	245.0	264.0	293.8	334.1	392.1	473.1	553.9
45°	188.6	190.2	193.2	197.4	206.6	219.8	239.9	267.0	315.1	380.3	461.2
47.5°	166.3	165.5	168.7	172.0	178.2	187.3	200.7	222.7	257.1	309.4	378.0
50°	151.3	151.0	153.3	155.8	161.7	168.3	179.3	196.0	223.3	266.6	329.4
52.5°	137.2	137.8	139.5	142.7	146.9	152.2	162.1	174.2	197.6	235.0	287.3
55°	118.4	119.0	121.1	123.0	126.0	131.4	137.6	147.7	163.7	189.8	232.9
57.5°	102.5	102.2	104.3	104.8	108.1	112.5	117.4	125.2	136.8	156.2	185.2
60°	91.9	91.3	93.1	94.5	96.3	99.9	103.9	111.5	120.8	135.0	159.9
62.5°	82.2	82.0	83.3	84.7	86.2	89.5	92.8	98.7	106.0	118.0	137.8
65°	68.2	68.8	69.4	70.0	70.8	72.8	76.0	80.1	85.1	93.5	107.7
67.5°	53.6	54.2	54.4	55.6	57.3	58.6	60.6	64.1	67.7	74.7	82.8
70°	43.3	43.1	43.3	43.9	46.1	48.3	51.0	53.6	55.8	60.8	67.6
72.5°	37.2	36.9	37.4	37.5	38.6	39.2	40.8	43.3	46.1	49.5	54.4
75°	28.8	28.8	28.8	28.8	29.7	30.0	30.7	31.3	32.3	33.9	37.5
77.5°	21.4	21.4	21.7	21.9	22.0	22.3	22.6	23.2	23.6	24.5	26.0
80°	16.9	17.0	16.9	17.0	17.0	17.5	17.7	18.3	18.4	19.5	20.1
82.5°	12.7	12.6	12.7	12.9	12.9	13.3	13.3	13.8	13.8	14.3	14.9
85°	6.8	6.5	6.8	6.6	7.1	6.6	6.8	7.2	7.2	7.4	8.3
87.5°	5.7	5.9	5.5	5.6	5.6	5.6	5.5	5.4	5.6	5.3	5.1
90°	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4	16.8	16.2	14.2
92.5°	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1	18.2	17.2	15.8
95°	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0	22.0	20.8	19.2
97.5°	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1	22.9	21.7	32.5
100°	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6	23.4	22.2	45.5
102.5°	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9	40.6	44.3	69.7
105°	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5	121.0	147.4	160.8
107.5°	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4	250.8	270.2	268.0
110°	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7	298.7	303.6	302.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7	337.6	337.5	335.9
115°	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3	387.9	386.4	385.0
117.5°	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2	435.0	433.8	433.1
120°	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8	465.6	464.4	464.0
122.5°	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8	496.0	495.2	494.6
125°	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1	538.8	538.5	537.9
127.5°	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4	581.0	580.5	579.8
130°	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0	606.4	605.8	605.2
132.5°	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2	630.7	630.1	629.6
135°	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1	666.5
137.5°	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7	700.0	699.2	698.9
140°	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4	720.8	720.2	719.8
142.5°	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1	740.6	740.2	739.7
145°	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6	768.4	768.0	767.8
147.5°	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2	793.0	792.6	792.4
150°	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3	808.0	807.8	807.4
152.5°	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7	821.2	820.7	820.5
155°	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2	839.5	838.7	838.5
157.5°	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3	855.4	854.5	854.6
160°	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4	864.5	863.6	863.8
162.5°	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7	872.7	871.7	871.8
165°	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8	883.6	882.4	882.6
167.5°	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0	891.0
170°	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0	896.0
172.5°	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6	900.3	899.1	899.1
175°	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4	904.4	903.4	903.2
177.5°	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9	905.9	904.9	904.8
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	483.8	483.4	481.1	478.5	475.2	472.9	471.1	470.2	467.3	463.7	461.4
5°	513.8	507.7	501.3	493.4	486.2	478.8	474.2	468.8	462.2	454.8	449.5
7.5°	545.7	533.9	521.2	508.1	495.2	483.5	473.2	464.4	453.9	443.2	435.8
10°	570.3	553.0	535.2	516.9	500.3	484.7	472.6	460.8	448.2	435.9	426.6
12.5°	592.6	569.9	549.3	526.8	505.6	486.9	469.6	455.6	440.4	427.4	416.9
15°	620.9	597.5	572.7	538.6	510.3	486.6	465.5	447.3	428.9	412.8	402.6
17.5°	647.2	612.3	578.8	550.4	513.6	484.1	458.3	436.5	416.2	399.2	386.6
20°	658.1	624.2	588.0	551.6	515.6	482.4	452.5	428.4	407.4	388.1	376.5
22.5°	664.7	626.4	588.1	549.1	510.7	476.3	446.8	420.3	397.4	379.2	364.8
25°	672.4	626.6	584.5	546.0	506.9	469.6	434.5	406.4	381.8	362.3	347.1
27.5°	677.4	623.6	573.9	531.1	491.4	454.3	422.1	392.3	367.2	346.6	330.3
30°	678.4	621.2	565.7	519.4	479.1	444.9	410.8	382.4	355.9	334.0	318.7
32.5°	679.7	615.3	554.6	505.4	464.1	430.3	399.4	372.2	345.1	323.6	308.0
35°	674.4	612.0	537.8	481.2	439.9	407.2	379.4	354.2	327.6	306.7	290.8
37.5°	651.6	599.0	520.4	454.0	410.8	380.6	357.8	336.0	311.5	289.0	274.1
40°	628.7	586.2	506.9	437.5	392.4	361.3	340.8	323.0	299.3	278.2	262.2
42.5°	594.5	568.6	494.0	420.2	371.5	341.6	324.3	307.5	286.8	265.4	250.3
45°	531.8	535.2	467.8	392.5	342.6	312.5	296.3	284.6	266.2	248.6	233.1
47.5°	453.1	485.0	437.0	363.2	312.2	284.0	269.8	259.6	247.1	229.8	215.7
50°	401.8	447.3	412.2	343.5	293.1	265.0	251.0	242.7	231.9	218.3	204.8
52.5°	354.5	403.4	382.4	321.4	272.3	246.7	233.0	226.2	217.6	204.7	192.6
55°	289.0	338.6	333.8	288.3	241.3	218.3	207.8	200.2	194.4	184.8	175.1
57.5°	233.8	280.8	283.3	251.3	214.0	191.1	182.2	176.4	172.6	165.4	156.4
60°	199.0	242.1	250.6	226.4	194.4	174.4	165.5	160.8	157.9	152.1	145.3
62.5°	170.1	206.8	216.4	199.1	175.6	156.8	149.9	145.5	143.4	138.4	132.4
65°	130.2	160.7	169.9	160.3	148.0	133.0	127.3	123.6	121.7	119.0	114.5
67.5°	97.9	120.1	130.3	123.5	119.0	109.5	106.0	103.9	102.3	100.4	96.7
70°	78.6	95.1	105.5	103.8	100.1	95.1	92.5	91.1	89.5	87.8	84.6
72.5°	63.2	74.6	84.3	85.2	82.3	81.3	79.0	78.4	77.4	75.5	73.7
75°	41.9	49.8	56.6	59.2	60.4	61.4	60.4	60.2	60.0	58.4	57.3
77.5°	27.5	31.7	36.0	40.5	42.4	43.7	44.0	44.8	44.2	43.4	42.9
80°	21.1	22.0	25.1	28.8	31.9	33.1	33.9	34.3	34.1	33.9	33.1
82.5°	15.3	16.1	17.6	20.2	22.7	24.7	25.2	25.1	25.6	25.7	25.1
85°	8.3	8.4	8.9	9.2	10.6	12.8	13.4	13.9	14.2	14.2	13.0
87.5°	5.0	4.5	4.4	4.0	4.2	4.1	4.7	5.3	5.8	5.4	5.7
90°	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7	2.2	3.7	5.2
92.5°	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5	12.1	11.7	11.3
95°	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1	35.0	28.8	22.6
97.5°	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5	79.8	77.1	74.3
100°	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7	116.8	119.8	122.7
102.5°	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3	151.4	153.6	155.8
105°	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6	202.2	203.9	205.5
107.5°	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7	256.1	257.4	258.6
110°	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8	292.0	293.2	294.4



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3	326.3	327.4	328.5
115°	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3	377.2	378.1	379.0
117.5°	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7	426.8	427.9	429.0
120°	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4	457.7	459.1	460.4
122.5°	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6	488.7	489.8	490.9
125°	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5	531.6	532.8	534.0
127.5°	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9	573.1	574.3	575.5
130°	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7	598.9	600.1	601.3
132.5°	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5	623.7	624.9	626.1
135°	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3	661.2	662.1	663.1
137.5°	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7	693.8	694.9	696.0
140°	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2	715.1	716.0	716.9
142.5°	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1	735.0	735.9	736.8
145°	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0	763.0	764.1	765.1
147.5°	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2	788.9	789.6	790.3
150°	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3	804.9	805.3	805.7
152.5°	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9	819.2	819.3	819.6
155°	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4	839.1	838.8	838.5
157.5°	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2	855.2	855.2	855.1
160°	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0	864.8	864.7	864.5
162.5°	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1	873.7	873.3	873.0
165°	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2	884.7	884.2	883.8
167.5°	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8	893.2	892.6	892.0
170°	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6	898.0	897.4	896.8
172.5°	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8	901.1	900.4	899.7
175°	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0	905.3	904.6	903.8
177.5°	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1	906.5	905.9	905.3
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	460.5	458.5	457.0	453.8	451.8	449.5	447.3	448.7	448.5	448.4	448.4
5°	445.1	440.5	436.3	430.8	427.5	423.3	420.1	419.7	420.4	417.7	416.0
7.5°	429.8	423.5	417.5	411.6	405.2	400.1	397.0	395.5	393.5	391.8	389.9
10°	419.0	411.6	405.8	398.4	391.6	385.6	381.8	379.1	377.7	376.3	373.7
12.5°	407.9	400.7	393.3	384.9	378.4	371.4	368.6	365.7	363.0	361.4	357.8
15°	391.8	382.4	374.5	365.7	358.4	351.6	347.7	341.8	341.0	339.0	335.4
17.5°	375.5	365.3	354.5	347.9	339.8	332.7	326.6	324.7	318.9	316.8	313.6
20°	362.7	353.3	345.0	336.4	324.6	318.0	313.1	310.6	305.9	303.1	301.1
22.5°	351.6	342.0	332.5	322.4	312.7	305.2	301.7	297.6	295.2	291.2	289.0
25°	335.8	325.4	313.9	303.1	296.1	290.5	284.8	281.2	277.6	275.8	271.8
27.5°	317.5	306.5	295.8	287.6	279.0	273.5	268.4	265.2	260.8	257.8	255.5
30°	307.3	294.5	285.2	277.8	266.8	261.6	257.8	253.7	250.6	247.4	245.1
32.5°	295.6	283.9	275.2	266.0	257.5	251.8	246.8	243.3	240.6	237.5	235.3
35°	277.2	267.4	258.4	249.2	242.9	237.1	231.3	228.3	225.7	222.8	220.8
37.5°	260.6	251.4	242.8	234.1	226.4	221.6	217.0	214.6	211.1	209.2	207.2
40°	250.4	241.3	232.1	223.7	215.7	212.1	207.8	204.4	201.2	199.8	197.6
42.5°	239.1	230.1	222.3	213.3	206.6	201.7	197.9	194.2	191.7	189.7	188.5
45°	222.5	214.5	206.8	197.8	191.6	187.4	183.0	179.5	177.4	175.9	173.7
47.5°	206.3	198.3	190.5	182.7	176.7	171.9	167.4	165.1	162.1	160.4	158.9
50°	194.6	187.4	179.2	171.9	165.9	161.1	157.5	154.5	151.9	149.6	148.6
52.5°	183.8	176.2	169.0	162.3	155.9	150.5	147.2	144.0	142.1	139.6	138.4
55°	166.1	158.7	152.7	146.0	139.8	135.2	131.2	128.4	126.4	123.6	122.0
57.5°	149.5	142.8	135.6	129.8	123.5	119.6	116.2	112.4	109.9	107.8	106.2
60°	138.2	130.6	124.3	119.0	113.3	108.3	105.3	102.3	99.7	97.5	96.1
62.5°	126.5	119.9	113.9	108.1	102.9	98.5	95.1	92.6	90.2	88.9	87.4
65°	108.5	103.3	97.3	92.5	87.6	84.5	81.6	79.5	77.8	76.8	75.6
67.5°	92.0	87.0	81.7	77.0	73.7	71.3	69.5	67.6	66.7	65.4	64.7
70°	81.3	76.0	71.4	67.8	64.6	62.8	61.6	60.2	59.4	57.8	57.0
72.5°	69.6	65.8	62.4	59.5	56.9	55.3	53.7	52.0	50.7	48.9	48.1
75°	54.8	51.3	48.7	46.8	45.1	43.0	40.7	38.9	38.3	37.7	37.5
77.5°	40.6	38.4	36.5	34.8	32.8	31.3	30.7	30.3	30.2	29.9	29.9
80°	31.9	29.9	28.5	26.5	25.3	25.3	25.3	24.9	25.1	25.1	25.1
82.5°	23.7	21.9	21.1	20.4	20.1	20.3	20.3	20.4	20.2	20.6	20.4
85°	12.2	12.4	12.8	12.7	12.8	12.8	13.3	13.0	13.3	12.8	13.3
87.5°	5.9	6.6	7.2	7.7	8.3	8.5	8.8	9.0	9.2	9.3	9.4
90°	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4	17.9	18.5	19.0
92.5°	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1	20.1	21.1	21.6
95°	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0	24.0	25.1	25.6
97.5°	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1	25.2	26.4	27.1
100°	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6	25.8	27.0	27.6
102.5°	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9	33.1	29.4	27.7
105°	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5	68.0	41.5	28.4
107.5°	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4	212.0	192.5	172.8
110°	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7	288.8	283.9	270.7



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7	337.8	337.9	335.6
115°	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3	390.9	392.4	393.4
117.5°	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2	437.4	438.5	439.2
120°	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8	468.0	469.2	469.8
122.5°	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8	497.7	498.5	498.9
125°	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1	539.4	539.7	540.0
127.5°	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4	581.9	582.4	582.5
130°	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0	607.6	608.2	608.4
132.5°	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2	631.8	632.4	632.5
135°	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0	668.4	668.8	668.8
137.5°	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7	701.4	702.1	702.3
140°	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4	722.0	722.6	722.8
142.5°	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1	741.6	742.1	742.1
145°	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6	769.0	769.2	769.4
147.5°	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2	793.6	793.8	793.7
150°	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3	808.7	808.9	808.9
152.5°	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7	822.3	822.9	822.8
155°	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2	840.9	841.7	841.6
157.5°	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3	857.1	858.1	857.9
160°	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4	866.3	867.2	867.1
162.5°	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7	874.8	875.7	875.8
165°	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8	886.1	887.3	887.3
167.5°	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5	894.7	895.9	895.9
170°	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3	899.5	900.7	900.7
172.5°	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6	902.8	904.0	903.9
175°	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4	906.5	907.5	907.4
177.5°	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9	907.8	908.8	908.7
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	446.4	446.3	446.4	445.8	446.4	446.3	446.4	448.4	448.4	448.5	448.7
5°	415.4	415.3	414.7	412.8	414.7	415.3	415.4	416.0	417.7	420.4	419.7
7.5°	388.3	388.1	386.3	386.3	386.3	388.1	388.3	389.9	391.8	393.5	395.5
10°	372.3	372.5	370.1	368.7	370.1	372.5	372.3	373.7	376.3	377.7	379.1
12.5°	356.7	355.9	353.9	352.3	353.9	355.9	356.7	357.8	361.4	363.0	365.7
15°	336.2	334.2	329.4	329.8	329.4	334.2	336.2	335.4	339.0	341.0	341.8
17.5°	312.0	310.6	310.5	307.6	310.5	310.6	312.0	313.6	316.8	318.9	324.7
20°	297.9	296.9	297.3	294.5	297.3	296.9	297.9	301.1	303.1	305.9	310.6
22.5°	286.8	285.8	284.1	283.3	284.1	285.8	286.8	289.0	291.2	295.2	297.6
25°	270.6	269.0	267.4	268.4	267.4	269.0	270.6	271.8	275.8	277.6	281.2
27.5°	254.4	253.2	251.6	251.4	251.6	253.2	254.4	255.5	257.8	260.8	265.2
30°	244.1	242.9	242.1	241.1	242.1	242.9	244.1	245.1	247.4	250.6	253.7
32.5°	233.7	233.4	232.0	231.8	232.0	233.4	233.7	235.3	237.5	240.6	243.3
35°	220.1	218.9	218.4	218.6	218.4	218.9	220.1	220.8	222.8	225.7	228.3
37.5°	207.1	205.5	204.7	204.1	204.7	205.5	207.1	207.2	209.2	211.1	214.6
40°	197.8	196.2	195.8	195.4	195.8	196.2	197.8	197.6	199.8	201.2	204.4
42.5°	187.4	186.8	186.5	185.7	186.5	186.8	187.4	188.5	189.7	191.7	194.2
45°	173.1	172.9	171.7	172.1	171.7	172.9	173.1	173.7	175.9	177.4	179.5
47.5°	158.1	157.2	156.4	157.0	156.4	157.2	158.1	158.9	160.4	162.1	165.1
50°	147.8	147.4	145.6	146.0	145.6	147.4	147.8	148.6	149.6	151.9	154.5
52.5°	137.6	136.0	135.3	135.1	135.3	136.0	137.6	138.4	139.6	142.1	144.0
55°	120.5	118.7	118.0	117.5	118.0	118.7	120.5	122.0	123.6	126.4	128.4
57.5°	103.8	103.4	102.7	103.1	102.7	103.4	103.8	106.2	107.8	109.9	112.4
60°	94.1	94.1	94.1	93.8	94.1	94.1	94.1	96.1	97.5	99.7	102.3
62.5°	86.5	86.0	85.9	86.2	85.9	86.0	86.5	87.4	88.9	90.2	92.6
65°	75.0	74.8	74.0	73.8	74.0	74.8	75.0	75.6	76.8	77.8	79.5
67.5°	64.1	63.5	63.2	62.9	63.2	63.5	64.1	64.7	65.4	66.7	67.6
70°	56.0	55.5	54.3	54.6	54.3	55.5	56.0	57.0	57.8	59.4	60.2
72.5°	47.2	46.8	46.5	46.2	46.5	46.8	47.2	48.1	48.9	50.7	52.0
75°	37.3	37.1	36.9	37.7	36.9	37.1	37.3	37.5	37.7	38.3	38.9
77.5°	29.9	29.9	30.0	29.7	30.0	29.9	29.9	29.9	29.9	30.2	30.3
80°	25.1	25.1	24.9	24.9	24.9	25.1	25.1	25.1	25.1	25.1	24.9
82.5°	20.1	20.2	20.4	20.1	20.4	20.2	20.1	20.4	20.6	20.2	20.4
85°	13.3	13.0	13.4	13.3	13.4	13.0	13.3	13.3	12.8	13.3	13.0
87.5°	9.8	9.6	9.6	9.8	9.6	9.6	9.8	9.4	9.3	9.2	9.0
90°	19.3	19.6	19.9	20.2	19.9	19.6	19.3	19.0	18.5	17.9	17.4
92.5°	21.8	22.0	22.1	22.4	22.1	22.0	21.8	21.6	21.1	20.1	19.1
95°	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.6	25.1	24.0	23.0
97.5°	27.3	27.5	27.6	27.7	27.6	27.5	27.3	27.1	26.4	25.2	24.1
100°	27.8	28.0	28.2	28.2	28.2	28.0	27.8	27.6	27.0	25.8	24.6
102.5°	28.0	28.2	28.5	28.8	28.5	28.2	28.0	27.7	29.4	33.1	36.9
105°	28.8	29.0	29.4	29.6	29.4	29.0	28.8	28.4	41.5	68.0	94.5
107.5°	152.9	132.9	113.0	93.0	113.0	132.9	152.9	172.8	192.5	212.0	231.4
110°	249.3	227.9	206.5	185.1	206.5	227.9	249.3	270.7	283.9	288.8	293.7



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	331.1	326.6	322.1	317.6	322.1	326.6	331.1	335.6	337.9	337.8	337.7
115°	394.0	394.6	395.2	395.8	395.2	394.6	394.0	393.4	392.4	390.9	389.3
117.5°	439.4	439.5	439.5	439.7	439.5	439.5	439.4	439.2	438.5	437.4	436.2
120°	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.8	469.2	468.0	466.8
122.5°	499.1	499.2	499.4	499.5	499.4	499.2	499.1	498.9	498.5	497.7	496.8
125°	540.3	540.6	540.9	541.2	540.9	540.6	540.3	540.0	539.7	539.4	539.1
127.5°	582.2	581.9	581.6	581.3	581.6	581.9	582.2	582.5	582.4	581.9	581.4
130°	608.0	607.8	607.4	607.2	607.4	607.8	608.0	608.4	608.2	607.6	607.0
132.5°	632.1	631.7	631.3	630.9	631.3	631.7	632.1	632.5	632.4	631.8	631.2
135°	668.4	668.0	667.5	667.1	667.5	668.0	668.4	668.8	668.8	668.4	668.0
137.5°	702.1	701.7	701.5	701.1	701.5	701.7	702.1	702.3	702.1	701.4	700.7
140°	722.5	722.2	721.9	721.6	721.9	722.2	722.5	722.8	722.6	722.0	721.4
142.5°	741.7	741.2	740.9	740.5	740.9	741.2	741.7	742.1	742.1	741.6	741.1
145°	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.4	769.2	769.0	768.6
147.5°	793.0	792.3	791.6	790.9	791.6	792.3	793.0	793.7	793.8	793.6	793.2
150°	808.4	808.0	807.5	807.1	807.5	808.0	808.4	808.9	808.9	808.7	808.3
152.5°	822.1	821.4	820.7	820.0	820.7	821.4	822.1	822.8	822.9	822.3	821.7
155°	840.8	839.8	839.0	838.0	839.0	839.8	840.8	841.6	841.7	840.9	840.2
157.5°	856.8	855.6	854.5	853.3	854.5	855.6	856.8	857.9	858.1	857.1	856.3
160°	866.1	865.0	864.0	863.0	864.0	865.0	866.1	867.1	867.2	866.3	865.4
162.5°	874.9	873.9	873.1	872.1	873.1	873.9	874.9	875.8	875.7	874.8	873.7
165°	886.3	885.2	884.2	883.1	884.2	885.2	886.3	887.3	887.3	886.1	884.8
167.5°	894.7	893.5	892.3	891.0	892.3	893.5	894.7	895.9	895.9	894.7	893.5
170°	899.5	898.3	897.2	896.0	897.2	898.3	899.5	900.7	900.7	899.5	898.3
172.5°	902.6	901.3	899.9	898.6	899.9	901.3	902.6	903.9	904.0	902.8	901.6
175°	906.3	905.1	903.9	902.7	903.9	905.1	906.3	907.4	907.5	906.5	905.4
177.5°	907.5	906.3	905.1	903.9	905.1	906.3	907.5	908.7	908.8	907.8	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	447.3	449.5	451.8	453.8	457.0	458.5	460.5	461.4	463.7	467.3	470.2
5°	420.1	423.3	427.5	430.8	436.3	440.5	445.1	449.5	454.8	462.2	468.8
7.5°	397.0	400.1	405.2	411.6	417.5	423.5	429.8	435.8	443.2	453.9	464.4
10°	381.8	385.6	391.6	398.4	405.8	411.6	419.0	426.6	435.9	448.2	460.8
12.5°	368.6	371.4	378.4	384.9	393.3	400.7	407.9	416.9	427.4	440.4	455.6
15°	347.7	351.6	358.4	365.7	374.5	382.4	391.8	402.6	412.8	428.9	447.3
17.5°	326.6	332.7	339.8	347.9	354.5	365.3	375.5	386.6	399.2	416.2	436.5
20°	313.1	318.0	324.6	336.4	345.0	353.3	362.7	376.5	388.1	407.4	428.4
22.5°	301.7	305.2	312.7	322.4	332.5	342.0	351.6	364.8	379.2	397.4	420.3
25°	284.8	290.5	296.1	303.1	313.9	325.4	335.8	347.1	362.3	381.8	406.4
27.5°	268.4	273.5	279.0	287.6	295.8	306.5	317.5	330.3	346.6	367.2	392.3
30°	257.8	261.6	266.8	277.8	285.2	294.5	307.3	318.7	334.0	355.9	382.4
32.5°	246.8	251.8	257.5	266.0	275.2	283.9	295.6	308.0	323.6	345.1	372.2
35°	231.3	237.1	242.9	249.2	258.4	267.4	277.2	290.8	306.7	327.6	354.2
37.5°	217.0	221.6	226.4	234.1	242.8	251.4	260.6	274.1	289.0	311.5	336.0
40°	207.8	212.1	215.7	223.7	232.1	241.3	250.4	262.2	278.2	299.3	323.0
42.5°	197.9	201.7	206.6	213.3	222.3	230.1	239.1	250.3	265.4	286.8	307.5
45°	183.0	187.4	191.6	197.8	206.8	214.5	222.5	233.1	248.6	266.2	284.6
47.5°	167.4	171.9	176.7	182.7	190.5	198.3	206.3	215.7	229.8	247.1	259.6
50°	157.5	161.1	165.9	171.9	179.2	187.4	194.6	204.8	218.3	231.9	242.7
52.5°	147.2	150.5	155.9	162.3	169.0	176.2	183.8	192.6	204.7	217.6	226.2
55°	131.2	135.2	139.8	146.0	152.7	158.7	166.1	175.1	184.8	194.4	200.2
57.5°	116.2	119.6	123.5	129.8	135.6	142.8	149.5	156.4	165.4	172.6	176.4
60°	105.3	108.3	113.3	119.0	124.3	130.6	138.2	145.3	152.1	157.9	160.8
62.5°	95.1	98.5	102.9	108.1	113.9	119.9	126.5	132.4	138.4	143.4	145.5
65°	81.6	84.5	87.6	92.5	97.3	103.3	108.5	114.5	119.0	121.7	123.6
67.5°	69.5	71.3	73.7	77.0	81.7	87.0	92.0	96.7	100.4	102.3	103.9
70°	61.6	62.8	64.6	67.8	71.4	76.0	81.3	84.6	87.8	89.5	91.1
72.5°	53.7	55.3	56.9	59.5	62.4	65.8	69.6	73.7	75.5	77.4	78.4
75°	40.7	43.0	45.1	46.8	48.7	51.3	54.8	57.3	58.4	60.0	60.2
77.5°	30.7	31.3	32.8	34.8	36.5	38.4	40.6	42.9	43.4	44.2	44.8
80°	25.3	25.3	25.3	26.5	28.5	29.9	31.9	33.1	33.9	34.1	34.3
82.5°	20.3	20.3	20.1	20.4	21.1	21.9	23.7	25.1	25.7	25.6	25.1
85°	13.3	12.8	12.8	12.7	12.8	12.4	12.2	13.0	14.2	14.2	13.9
87.5°	8.8	8.5	8.3	7.7	7.2	6.6	5.9	5.7	5.4	5.8	5.3
90°	16.8	16.2	14.2	12.2	10.3	8.4	6.6	5.2	3.7	2.2	0.7
92.5°	18.2	17.2	15.8	14.3	12.8	11.4	10.8	11.3	11.7	12.1	12.5
95°	22.0	20.8	19.2	17.6	15.9	14.3	16.5	22.6	28.8	35.0	41.1
97.5°	22.9	21.7	32.5	43.2	54.0	64.7	71.5	74.3	77.1	79.8	82.5
100°	23.4	22.2	45.5	68.9	92.2	115.5	125.7	122.7	119.8	116.8	113.7
102.5°	40.6	44.3	69.7	95.2	120.8	146.3	157.9	155.8	153.6	151.4	149.3
105°	121.0	147.4	160.8	174.4	187.8	201.3	207.2	205.5	203.9	202.2	200.6
107.5°	250.8	270.2	268.0	266.0	263.8	261.7	259.9	258.6	257.4	256.1	254.7
110°	298.7	303.6	302.0	300.3	298.7	297.0	295.6	294.4	293.2	292.0	290.8



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	337.6	337.5	335.9	334.2	332.6	330.9	329.6	328.5	327.4	326.3	325.3
115°	387.9	386.4	385.0	383.7	382.4	381.0	379.9	379.0	378.1	377.2	376.3
117.5°	435.0	433.8	433.1	432.4	431.7	431.0	430.1	429.0	427.9	426.8	425.7
120°	465.6	464.4	464.0	463.6	463.1	462.7	461.8	460.4	459.1	457.7	456.4
122.5°	496.0	495.2	494.6	494.0	493.4	492.8	492.1	490.9	489.8	488.7	487.6
125°	538.8	538.5	537.9	537.3	536.7	536.1	535.2	534.0	532.8	531.6	530.5
127.5°	581.0	580.5	579.8	579.1	578.3	577.6	576.7	575.5	574.3	573.1	571.9
130°	606.4	605.8	605.2	604.6	604.0	603.4	602.5	601.3	600.1	598.9	597.7
132.5°	630.7	630.1	629.6	629.0	628.6	628.1	627.3	626.1	624.9	623.7	622.5
135°	667.5	667.1	666.5	665.9	665.3	664.7	663.9	663.1	662.1	661.2	660.3
137.5°	700.0	699.2	698.9	698.6	698.3	697.9	697.2	696.0	694.9	693.8	692.7
140°	720.8	720.2	719.8	719.4	718.9	718.4	717.8	716.9	716.0	715.1	714.2
142.5°	740.6	740.2	739.7	739.3	738.8	738.4	737.7	736.8	735.9	735.0	734.1
145°	768.4	768.0	767.8	767.4	767.2	766.8	766.2	765.1	764.1	763.0	762.0
147.5°	793.0	792.6	792.4	792.0	791.8	791.5	791.0	790.3	789.6	788.9	788.2
150°	808.0	807.8	807.4	807.2	806.8	806.6	806.2	805.7	805.3	804.9	804.3
152.5°	821.2	820.7	820.5	820.3	820.1	819.9	819.8	819.6	819.3	819.2	818.9
155°	839.5	838.7	838.5	838.4	838.3	838.1	838.2	838.5	838.8	839.1	839.4
157.5°	855.4	854.5	854.6	854.8	854.9	855.1	855.1	855.1	855.2	855.2	855.2
160°	864.5	863.6	863.8	863.9	864.1	864.2	864.4	864.5	864.7	864.8	865.0
162.5°	872.7	871.7	871.8	872.0	872.1	872.3	872.5	873.0	873.3	873.7	874.1
165°	883.6	882.4	882.6	882.8	883.0	883.0	883.4	883.8	884.2	884.7	885.2
167.5°	892.3	891.0	891.0	891.0	891.0	891.0	891.4	892.0	892.6	893.2	893.8
170°	897.2	896.0	896.0	896.0	896.0	896.0	896.2	896.8	897.4	898.0	898.6
172.5°	900.3	899.1	899.1	898.9	898.8	898.7	899.0	899.7	900.4	901.1	901.8
175°	904.4	903.4	903.2	903.0	902.8	902.8	903.0	903.8	904.6	905.3	906.0
177.5°	905.9	904.9	904.8	904.7	904.6	904.5	904.7	905.3	905.9	906.5	907.1
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	471.1	472.9	475.2	478.5	481.1	483.4	483.8	484.5	486.1	488.8	490.9
5°	474.2	478.8	486.2	493.4	501.3	507.7	513.8	518.0	521.9	530.4	537.2
7.5°	473.2	483.5	495.2	508.1	521.2	533.9	545.7	556.3	566.8	579.1	593.1
10°	472.6	484.7	500.3	516.9	535.2	553.0	570.3	583.8	599.3	613.5	631.3
12.5°	469.6	486.9	505.6	526.8	549.3	569.9	592.6	611.1	629.0	649.4	670.1
15°	465.5	486.6	510.3	538.6	572.7	597.5	620.9	653.2	675.2	697.2	726.9
17.5°	458.3	484.1	513.6	550.4	578.8	612.3	647.2	672.8	702.5	733.6	760.4
20°	452.5	482.4	515.6	551.6	588.0	624.2	658.1	688.6	719.4	755.3	777.3
22.5°	446.8	476.3	510.7	549.1	588.1	626.4	664.7	700.5	735.0	771.3	799.4
25°	434.5	469.6	506.9	546.0	584.5	626.6	672.4	712.3	755.0	792.4	819.1
27.5°	422.1	454.3	491.4	531.1	573.9	623.6	677.4	722.8	765.6	792.4	800.7
30°	410.8	444.9	479.1	519.4	565.7	621.2	678.4	730.4	765.4	777.1	768.4
32.5°	399.4	430.3	464.1	505.4	554.6	615.3	679.7	725.9	747.0	738.1	703.0
35°	379.4	407.2	439.9	481.2	537.8	612.0	674.4	705.7	700.5	650.3	584.1
37.5°	357.8	380.6	410.8	454.0	520.4	599.0	651.6	656.3	611.1	534.1	457.6
40°	340.8	361.3	392.4	437.5	506.9	586.2	628.7	610.0	540.0	454.3	390.5
42.5°	324.3	341.6	371.5	420.2	494.0	568.6	594.5	553.9	473.1	392.1	334.1
45°	296.3	312.5	342.6	392.5	467.8	535.2	531.8	461.2	380.3	315.1	267.0
47.5°	269.8	284.0	312.2	363.2	437.0	485.0	453.1	378.0	309.4	257.1	222.7
50°	251.0	265.0	293.1	343.5	412.2	447.3	401.8	329.4	266.6	223.3	196.0
52.5°	233.0	246.7	272.3	321.4	382.4	403.4	354.5	287.3	235.0	197.6	174.2
55°	207.8	218.3	241.3	288.3	333.8	338.6	289.0	232.9	189.8	163.7	147.7
57.5°	182.2	191.1	214.0	251.3	283.3	280.8	233.8	185.2	156.2	136.8	125.2
60°	165.5	174.4	194.4	226.4	250.6	242.1	199.0	159.9	135.0	120.8	111.5
62.5°	149.9	156.8	175.6	199.1	216.4	206.8	170.1	137.8	118.0	106.0	98.7
65°	127.3	133.0	148.0	160.3	169.9	160.7	130.2	107.7	93.5	85.1	80.1
67.5°	106.0	109.5	119.0	123.5	130.3	120.1	97.9	82.8	74.7	67.7	64.1
70°	92.5	95.1	100.1	103.8	105.5	95.1	78.6	67.6	60.8	55.8	53.6
72.5°	79.0	81.3	82.3	85.2	84.3	74.6	63.2	54.4	49.5	46.1	43.3
75°	60.4	61.4	60.4	59.2	56.6	49.8	41.9	37.5	33.9	32.3	31.3
77.5°	44.0	43.7	42.4	40.5	36.0	31.7	27.5	26.0	24.5	23.6	23.2
80°	33.9	33.1	31.9	28.8	25.1	22.0	21.1	20.1	19.5	18.4	18.3
82.5°	25.2	24.7	22.7	20.2	17.6	16.1	15.3	14.9	14.3	13.8	13.8
85°	13.4	12.8	10.6	9.2	8.9	8.4	8.3	8.3	7.4	7.2	7.2
87.5°	4.7	4.1	4.2	4.0	4.4	4.5	5.0	5.1	5.3	5.6	5.4
90°	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8	17.4
92.5°	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2	19.1
95°	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0	23.0
97.5°	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9	24.1
100°	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4	24.6
102.5°	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6	36.9
105°	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0	94.5
107.5°	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8	231.4
110°	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7	293.7



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6	337.7
115°	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9	389.3
117.5°	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0	436.2
120°	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6	466.8
122.5°	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0	496.8
125°	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8	539.1
127.5°	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0	581.4
130°	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4	607.0
132.5°	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7	631.2
135°	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5	668.0
137.5°	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0	700.7
140°	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8	721.4
142.5°	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6	741.1
145°	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4	768.6
147.5°	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0	793.2
150°	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0	808.3
152.5°	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2	821.7
155°	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5	840.2
157.5°	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4	856.3
160°	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5	865.4
162.5°	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7	873.7
165°	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6	884.8
167.5°	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3	893.5
170°	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2	898.3
172.5°	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3	901.6
175°	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4	905.4
177.5°	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9	906.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	468.6	468.6	468.6	468.6	468.6	468.6	468.6
2.5°	494.3	494.3	494.9	497.3	497.7	499.7	499.1
5°	543.2	547.0	548.5	554.5	558.0	559.6	556.5
7.5°	603.0	613.8	618.9	625.3	630.8	632.5	628.1
10°	646.7	658.0	667.4	673.2	678.6	682.3	686.8
12.5°	688.9	702.7	711.7	719.9	725.5	730.0	730.8
15°	734.8	755.6	771.5	783.2	788.9	791.9	790.7
17.5°	781.0	800.4	811.7	823.5	831.6	832.0	832.2
20°	807.2	826.0	839.1	847.9	857.0	856.5	858.6
22.5°	824.7	839.6	849.5	855.9	859.0	857.5	857.9
25°	832.8	837.3	835.5	825.3	822.6	813.2	814.9
27.5°	790.7	769.8	748.2	720.5	698.5	681.1	681.9
30°	733.4	696.5	654.4	619.1	587.4	578.5	559.6
32.5°	653.3	598.0	548.6	515.7	488.5	481.1	464.7
35°	517.5	463.7	413.0	382.5	370.5	353.6	353.4
37.5°	402.3	354.9	328.1	305.2	293.3	283.0	282.1
40°	338.4	301.5	281.2	264.8	253.0	245.3	243.5
42.5°	293.8	264.0	245.0	234.8	225.7	221.7	218.8
45°	239.9	219.8	206.6	197.4	193.2	190.2	188.6
47.5°	200.7	187.3	178.2	172.0	168.7	165.5	166.3
50°	179.3	168.3	161.7	155.8	153.3	151.0	151.3
52.5°	162.1	152.2	146.9	142.7	139.5	137.8	137.2
55°	137.6	131.4	126.0	123.0	121.1	119.0	118.4
57.5°	117.4	112.5	108.1	104.8	104.3	102.2	102.5
60°	103.9	99.9	96.3	94.5	93.1	91.3	91.9
62.5°	92.8	89.5	86.2	84.7	83.3	82.0	82.2
65°	76.0	72.8	70.8	70.0	69.4	68.8	68.2
67.5°	60.6	58.6	57.3	55.6	54.4	54.2	53.6
70°	51.0	48.3	46.1	43.9	43.3	43.1	43.3
72.5°	40.8	39.2	38.6	37.5	37.4	36.9	37.2
75°	30.7	30.0	29.7	28.8	28.8	28.8	28.8
77.5°	22.6	22.3	22.0	21.9	21.7	21.4	21.4
80°	17.7	17.5	17.0	17.0	16.9	17.0	16.9
82.5°	13.3	13.3	12.9	12.9	12.7	12.6	12.7
85°	6.8	6.6	7.1	6.6	6.8	6.5	6.8
87.5°	5.5	5.6	5.6	5.6	5.5	5.9	5.7
90°	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332252-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)