

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332255-935

Luminaire Tested: **S123RDIP-S340D805U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332255-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3883.0 lumens
Efficiency: N/A
Efficacy: 124.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5324	5324	5324
5°	5344	5271	5302
10°	5314	5205	5187
15°	5258	5084	5029
20°	5179	4931	4816
25°	5099	4760	4608
30°	4992	4561	4313
35°	4882	4365	4043
40°	4780	4131	3710
45°	4647	3902	3408
50°	4501	3641	3069
55°	4352	3342	2755
60°	4215	3023	2409
65°	4037	2677	2063
70°	3811	2247	1668
75°	3489	1768	1568
80°	3106	1568	1438
85°	2631	1383	1284



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	1.2
10°-20°	129.2	3.3
20°-30°	186.1	4.8
30°-40°	209.6	5.4
40°-50°	200.5	5.2
50°-60°	164.2	4.2
60°-70°	110.8	2.9
70°-80°	55.7	1.4
80°-90°	17.3	0.4
90°-100°	32.9	0.8
100°-110°	157.0	4.0
110°-120°	377.1	9.7
120°-130°	480.2	12.4
130°-140°	513.1	13.2
140°-150°	479.8	12.4
150°-160°	387.0	10.0
160°-170°	249.8	6.4
170°-180°	86.1	2.2
0°-30°	361.8	9.3
0°-40°	571.4	14.7
0°-60°	936.2	24.1
0°-90°	1120.0	28.8
90°-120°	567.0	14.6
90°-150°	2040.1	52.5
90°-180°	2763.0	71.2
0°-180°	3883.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	495	492	488	491	491	47
15°	472	467	456	454	451	133
25°	429	419	401	393	388	197
35°	372	356	332	315	308	232
45°	305	286	256	234	224	235
55°	232	211	178	156	147	208
65°	158	136	105	86	81	157
75°	84	64	42	39	38	89
85°	21	13	11	10	10	24
90°	1	8	16	19	20	3
95°	41	15	21	25	26	51
105°	201	204	147	35	30	213
115°	376	380	386	393	396	371
125°	530	536	538	540	541	474
135°	660	664	667	669	667	508
145°	762	766	768	769	769	477
155°	839	838	839	842	838	387
165°	885	883	882	887	883	250
175°	906	903	903	907	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	496.3	495.9	495.7	495.4	495.2	494.6	493.7	492.8	492.0	491.1	491.9
5°	494.6	494.2	493.8	493.4	492.8	492.1	491.0	490.0	488.9	487.8	488.6
7.5°	490.1	489.6	489.1	488.6	488.2	487.2	485.9	484.5	483.0	481.6	482.1
10°	486.2	485.6	485.0	484.4	483.7	482.6	481.0	479.4	477.8	476.2	476.3
12.5°	480.8	480.1	479.4	478.7	478.0	476.6	474.7	472.8	470.8	468.8	468.7
15°	471.8	470.8	469.8	468.8	467.9	466.1	463.6	461.2	458.7	456.2	455.7
17.5°	460.5	459.3	458.2	457.0	455.9	453.7	450.6	447.4	444.3	441.1	440.1
20°	452.1	450.7	449.3	447.9	446.4	444.0	440.7	437.2	433.9	430.5	429.3
22.5°	442.8	441.2	439.5	437.9	436.3	433.7	430.1	426.5	422.8	419.2	417.8
25°	429.3	427.1	424.8	422.6	420.3	417.2	413.1	409.0	404.8	400.8	398.9
27.5°	412.8	410.4	407.9	405.4	402.9	399.5	394.9	390.3	385.7	381.2	378.6
30°	401.6	398.9	396.2	393.6	390.9	387.0	382.0	377.0	372.0	367.0	364.0
32.5°	390.4	387.3	384.3	381.3	378.2	374.1	368.8	363.5	358.3	352.9	349.7
35°	371.5	368.2	365.1	361.9	358.7	354.3	348.8	343.2	337.7	332.2	328.4
37.5°	352.4	348.8	345.3	341.7	338.1	333.4	327.5	321.6	315.7	309.8	305.5
40°	340.2	336.3	332.3	328.5	324.5	319.3	313.1	306.7	300.4	294.0	289.5
42.5°	326.4	322.4	318.6	314.6	310.7	305.5	298.9	292.4	285.9	279.3	274.2
45°	305.3	301.3	297.3	293.3	289.2	283.8	277.0	270.1	263.2	256.3	251.2
47.5°	284.2	279.8	275.3	271.0	266.6	261.0	254.1	247.2	240.4	233.5	228.0
50°	268.8	264.6	260.5	256.2	252.0	246.3	239.1	231.9	224.6	217.4	211.9
52.5°	255.0	250.5	245.9	241.3	236.8	230.9	223.8	216.6	209.5	202.3	196.7
55°	231.9	227.5	223.2	218.8	214.4	208.4	200.9	193.3	185.7	178.1	173.0
57.5°	210.5	205.8	201.0	196.2	191.5	185.3	177.7	170.0	162.5	154.9	150.0
60°	195.8	190.9	186.0	181.1	176.2	170.0	162.6	155.2	147.8	140.4	135.6
62.5°	181.0	176.1	171.2	166.3	161.4	155.2	147.8	140.4	133.0	125.6	121.1
65°	158.5	153.6	148.7	143.8	138.9	132.9	126.0	119.0	112.1	105.1	100.7
67.5°	136.0	131.0	126.0	121.1	116.1	110.3	103.6	96.9	90.2	83.6	80.3
70°	121.1	116.3	111.5	106.7	101.9	96.3	90.1	83.9	77.7	71.4	68.3
72.5°	106.4	101.7	96.9	92.1	87.4	82.2	76.5	70.9	65.2	59.5	57.0
75°	83.9	79.6	75.3	71.0	66.7	62.2	57.3	52.3	47.4	42.5	41.7
77.5°	63.3	59.4	55.5	51.7	47.9	44.3	41.2	38.0	34.9	31.7	31.3
80°	50.1	46.5	42.9	39.2	35.6	32.8	30.9	29.0	27.1	25.3	25.0
82.5°	37.6	34.4	31.3	28.2	25.0	23.0	22.1	21.3	20.4	19.5	19.2
85°	21.3	19.3	17.3	15.4	13.4	12.3	12.1	11.8	11.5	11.2	11.0
87.5°	7.8	7.3	6.9	6.4	5.9	5.9	6.2	6.6	7.0	7.4	7.5
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	12.5	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2
95°	41.1	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0
97.5°	82.5	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9
100°	113.7	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4
102.5°	149.3	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6
105°	200.6	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0
107.5°	254.7	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8
110°	290.8	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6
115°	376.3	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9
117.5°	425.7	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0
120°	456.4	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6
122.5°	487.6	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0
125°	530.5	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8
127.5°	571.9	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0
130°	597.7	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4
132.5°	622.5	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7
135°	660.3	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5
137.5°	692.7	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0
140°	714.2	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8
142.5°	734.1	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6
145°	762.0	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4
147.5°	788.2	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0
150°	804.3	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0
152.5°	818.9	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2
155°	839.4	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5
157.5°	855.2	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4
160°	865.0	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5
162.5°	874.1	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7
165°	885.2	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6
167.5°	893.8	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3
170°	898.6	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2
172.5°	901.8	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3
175°	906.0	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4
177.5°	907.1	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	494.6	494.6	494.6	494.6	494.6	494.6	494.6	494.6
2.5°	492.7	493.4	494.3	494.6	494.5	494.3	494.1	494.0
5°	489.5	490.3	491.0	491.4	491.2	491.0	490.9	490.7
7.5°	482.6	483.0	483.5	483.5	483.2	482.9	482.6	482.3
10°	476.4	476.5	476.6	476.4	476.0	475.5	475.0	474.6
12.5°	468.7	468.6	468.6	468.3	467.8	467.3	466.7	466.2
15°	455.2	454.8	454.3	453.8	453.2	452.5	451.9	451.3
17.5°	439.2	438.2	437.3	436.4	435.4	434.5	433.6	432.7
20°	428.2	427.0	425.9	424.7	423.6	422.6	421.5	420.4
22.5°	416.4	414.9	413.5	412.2	411.2	410.3	409.2	408.3
25°	397.0	395.2	393.3	391.8	390.9	389.9	388.9	388.0
27.5°	376.0	373.4	370.8	368.8	367.2	365.8	364.3	362.7
30°	361.0	358.0	355.0	352.8	351.3	349.9	348.4	347.0
32.5°	346.3	343.0	339.7	337.3	335.8	334.3	332.8	331.3
35°	324.5	320.6	316.8	314.1	312.5	310.9	309.3	307.7
37.5°	301.1	296.7	292.4	289.2	287.2	285.2	283.3	281.3
40°	284.8	280.2	275.5	272.2	270.1	268.1	266.0	264.0
42.5°	269.1	264.2	259.1	255.6	253.7	251.9	250.1	248.2
45°	246.2	241.1	236.0	232.4	230.3	228.2	226.0	223.9
47.5°	222.4	216.9	211.4	207.7	205.8	203.9	201.9	200.0
50°	206.4	200.9	195.4	191.6	189.5	187.4	185.4	183.3
52.5°	190.9	185.1	179.4	175.6	173.7	171.9	170.1	168.2
55°	167.8	162.6	157.5	153.9	152.2	150.4	148.6	146.8
57.5°	145.1	140.2	135.3	132.1	130.6	129.1	127.6	126.1
60°	130.8	126.0	121.1	118.0	116.5	114.9	113.5	111.9
62.5°	116.6	112.1	107.5	104.4	102.9	101.3	99.7	98.2
65°	96.3	92.0	87.6	85.0	83.9	83.0	82.1	81.0
67.5°	77.1	73.8	70.5	68.4	67.3	66.3	65.3	64.2
70°	65.2	62.1	58.9	56.9	55.9	54.9	53.9	53.0
72.5°	54.4	51.9	49.3	47.9	47.4	47.0	46.7	46.2
75°	40.7	39.9	38.9	38.4	38.2	38.1	37.9	37.7
77.5°	30.7	30.2	29.8	29.4	29.3	29.1	28.9	28.8
80°	24.7	24.5	24.2	24.0	23.8	23.6	23.4	23.2
82.5°	18.9	18.7	18.4	18.3	18.3	18.2	18.2	18.2
85°	10.8	10.7	10.5	10.4	10.4	10.4	10.4	10.4
87.5°	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	19.1	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	23.0	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	24.1	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	24.6	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	36.9	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	94.5	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	231.4	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	293.7	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332255-935

CATALOG NUMBER: S123RDIP-S340D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	389.3	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	436.2	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	466.8	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	496.8	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.1	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.4	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.0	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.2	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	700.7	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	721.4	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.1	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	768.6	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.2	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.3	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	821.7	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.2	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	856.3	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	865.4	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	873.7	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	884.8	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	901.6	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	905.4	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	906.9	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)