

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332365-940

Luminaire Tested: **S123RDIP-S1165D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332365-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U940-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5076.7 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	93	99	96	92	89	87	84	82	79	77	76	72	71	69	66
2	95	88	82	77	91	84	79	74	77	73	69	70	67	64	64	62	59	56
3	87	78	70	64	83	75	68	62	68	63	58	63	58	55	57	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	44	42
5	74	62	54	48	70	60	52	46	55	49	44	51	45	41	47	42	39	36
6	68	56	48	42	65	54	46	41	50	43	39	46	41	37	43	38	35	32
7	64	51	43	37	60	49	42	36	45	39	34	42	37	33	39	34	31	29
8	59	47	39	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26
9	55	43	35	30	53	41	34	29	38	32	28	36	30	27	33	29	25	23
10	52	39	32	27	49	38	31	26	36	30	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	3.2
10°-20°	451.6	8.9
20°-30°	650.2	12.8
30°-40°	732.4	14.4
40°-50°	700.7	13.8
50°-60°	573.8	11.3
60°-70°	387.1	7.6
70°-80°	194.8	3.8
80°-90°	52.7	1.0
90°-100°	86.6	1.7
100°-110°	245.3	4.8
110°-120°	241.3	4.8
120°-130°	192.5	3.8
130°-140°	151.8	3.0
140°-150°	113.3	2.2
150°-160°	78.9	1.6
160°-170°	46.4	0.9
170°-180°	15.1	0.3
0°-30°	1264.1	24.9
0°-40°	1996.5	39.3
0°-60°	3270.9	64.4
0°-90°	3905.5	76.9
90°-120°	573.2	11.3
90°-150°	1030.7	20.3
90°-180°	1171.0	23.1
0°-180°	5076.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	1	4	8	9	9	4
95°	11	35	187	55	37	12
105°	37	54	253	443	401	39
115°	65	80	194	425	488	64
125°	90	106	181	328	384	80
135°	105	126	178	270	312	81
145°	120	138	176	221	244	75
155°	136	147	170	194	202	63
165°	149	153	163	173	176	42
175°	155	156	157	159	158	15
180°	156	156	156	156	156	



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.0	24.4	21.8	19.3	16.7	15.4	15.6	15.8	16.0	16.1	15.9
90°	0.6	1.2	1.9	2.9	3.5	4.1	5.1	6.0	7.0	7.8	7.6
92.5°	3.9	5.8	8.5	10.9	13.6	18.2	26.5	40.0	53.3	48.4	36.6
95°	10.7	11.7	15.2	20.5	28.7	40.9	67.8	114.7	166.4	186.9	151.6
97.5°	18.3	18.5	21.3	25.9	34.1	47.3	72.9	125.8	212.0	289.6	309.8
100°	23.4	23.6	25.9	30.2	37.8	50.1	72.1	118.8	201.7	298.5	360.5
102.5°	28.6	29.2	31.1	35.3	42.1	53.4	73.2	112.7	186.5	282.0	363.0
105°	36.6	37.5	39.4	43.2	49.1	58.9	76.0	108.4	168.0	253.3	343.8
107.5°	45.0	45.9	47.8	51.5	57.1	66.2	81.1	108.1	156.1	228.0	310.1
110°	51.0	52.0	53.6	57.1	62.4	71.2	85.4	109.3	151.6	213.7	289.0



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.6	57.5	59.1	62.6	67.9	76.5	89.7	111.9	149.0	204.0	270.5
115°	64.6	65.9	67.8	70.9	76.2	84.8	96.8	115.9	148.1	193.8	248.3
117.5°	72.6	74.0	75.6	78.6	84.5	92.4	104.2	121.4	148.6	187.7	234.9
120°	78.1	79.1	80.7	83.8	89.8	97.6	109.1	125.4	149.7	184.9	227.8
122.5°	82.9	83.9	85.4	88.9	94.6	103.0	114.0	129.2	151.4	183.2	222.0
125°	89.8	90.4	92.3	95.8	101.7	110.3	121.4	135.2	154.1	180.8	214.6
127.5°	95.1	95.9	98.4	101.8	108.4	117.0	127.6	140.1	157.1	179.8	208.0
130°	98.4	99.2	102.1	105.8	112.5	121.0	131.4	143.4	159.2	179.0	204.5
132.5°	100.9	102.0	105.1	109.7	116.3	124.6	134.6	146.4	160.7	178.7	201.3
135°	105.2	106.5	109.9	114.7	121.4	129.8	139.6	150.3	162.9	178.3	197.0
137.5°	109.4	110.8	114.1	119.1	125.7	133.6	143.0	153.2	164.4	177.6	193.2
140°	112.2	113.8	116.9	122.0	128.2	136.2	145.3	154.7	165.4	177.5	190.9
142.5°	115.2	116.5	119.9	124.5	130.8	138.1	147.0	156.2	166.2	176.9	189.0
145°	120.0	121.0	123.9	128.6	133.9	141.2	149.4	157.8	166.7	176.1	186.2
147.5°	125.0	125.6	128.3	132.4	137.6	143.7	151.2	158.9	166.7	175.0	183.6
150°	128.2	128.6	131.1	135.2	139.6	145.3	152.5	159.2	166.7	174.0	181.8
152.5°	131.5	131.6	134.1	137.7	141.6	147.0	153.3	159.6	165.9	172.7	179.8
155°	136.4	136.4	138.3	141.5	145.0	149.4	154.7	159.8	165.1	170.5	176.7
157.5°	140.4	140.6	142.1	144.9	147.8	151.2	155.5	160.1	164.1	168.5	173.3
160°	143.4	143.4	144.6	147.1	149.4	152.5	156.3	160.1	163.5	167.0	171.1
162.5°	145.6	145.6	146.7	148.6	150.6	153.3	156.6	159.8	162.6	165.5	168.8
165°	149.0	148.7	149.4	151.0	152.2	154.4	156.9	159.2	161.0	163.3	165.8
167.5°	151.6	151.2	151.6	152.8	153.6	155.1	156.9	158.6	159.5	161.0	162.8
170°	153.1	152.5	152.8	153.7	154.4	155.1	156.6	157.8	158.5	159.4	161.0
172.5°	154.2	153.7	153.8	154.5	154.9	155.2	156.6	157.7	157.7	158.2	159.3
175°	155.3	155.1	154.7	155.3	155.3	155.7	156.3	156.9	156.6	156.6	157.2
177.5°	156.0	155.7	155.4	155.7	155.7	155.7	156.0	156.4	156.0	155.7	156.0
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	15.7	15.4	15.2	15.2	14.9	14.6	14.4	14.2
90°	7.8	8.2	8.5	9.1	8.8	9.1	9.5	9.1
92.5°	26.6	21.0	18.5	16.9	16.4	15.4	15.8	15.2
95°	113.4	76.9	60.2	48.9	42.9	40.0	37.8	36.6
97.5°	282.8	226.5	185.8	148.2	124.9	110.8	102.2	99.5
100°	371.5	346.0	309.2	264.4	232.6	209.6	197.2	197.6
102.5°	401.0	400.2	378.7	350.4	325.6	307.4	297.1	289.8
105°	409.7	441.1	447.1	439.0	424.5	412.5	402.4	400.8
107.5°	384.8	436.0	463.6	474.8	475.1	471.0	467.6	464.8
110°	361.1	419.1	458.8	480.9	489.7	492.2	491.6	491.0



TEST NUMBER: P332365-940

CATALOG NUMBER: S123RDIP-S1165D365U940-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	396.9	441.4	469.8	485.9	493.7	496.1	496.2
115°	306.6	361.4	407.8	442.1	465.7	479.6	485.9	487.5
117.5°	284.1	331.4	373.0	407.9	432.6	448.4	457.4	459.6
120°	272.2	314.8	352.6	384.4	409.3	427.0	434.5	436.4
122.5°	263.0	301.4	336.4	366.0	388.2	404.0	412.3	414.7
125°	250.5	284.9	315.1	340.4	360.5	374.3	382.3	384.4
127.5°	239.7	270.3	297.6	320.6	338.5	350.4	357.5	359.4
130°	232.8	261.3	286.8	308.2	324.9	336.3	342.9	345.4
132.5°	226.6	252.6	276.4	296.9	312.5	323.9	329.8	331.5
135°	218.0	240.4	260.9	278.8	294.4	303.8	309.4	311.7
137.5°	210.3	228.6	246.3	261.9	274.8	284.5	289.2	290.7
140°	205.8	221.9	236.9	250.5	262.5	271.3	276.3	276.1
142.5°	201.5	215.3	228.4	240.1	250.4	258.2	262.7	262.4
145°	196.4	206.7	216.8	226.0	233.8	240.4	243.0	243.6
147.5°	192.1	200.4	208.5	215.0	221.0	225.4	227.8	228.1
150°	189.0	196.4	203.0	208.9	213.7	217.1	219.0	219.0
152.5°	186.3	192.5	198.4	203.4	207.1	210.3	211.4	211.4
155°	182.2	187.2	191.9	195.6	198.5	201.1	201.7	202.0
157.5°	177.7	181.9	185.6	188.6	191.0	192.9	193.4	193.3
160°	175.2	178.7	181.8	184.0	186.2	188.2	188.2	187.8
162.5°	172.2	175.1	178.1	180.0	181.5	183.1	183.1	182.8
165°	168.3	170.1	172.4	174.0	175.2	176.5	176.1	176.1
167.5°	164.9	166.3	167.6	168.7	169.2	170.1	169.9	169.9
170°	162.6	163.5	164.8	165.4	165.8	166.4	166.0	166.0
172.5°	160.6	161.3	162.3	162.6	162.7	163.4	162.8	162.6
175°	157.8	158.2	158.8	158.8	158.8	159.2	158.8	158.5
177.5°	156.1	156.4	156.7	156.7	156.4	156.7	156.1	156.1
180°	155.7	155.7	155.7	155.7	155.7	155.7	155.7	155.7

(END OF REPORT)