

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332367-940

Luminaire Tested: **S123RDIP-S1165D585U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332367-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D585U940-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5872.2 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	69
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	78	73	74	70	67	67	64	61	60	57	55	52
3	87	77	70	65	82	74	67	62	66	61	57	60	56	53	54	51	48	45
4	80	69	61	55	75	66	59	53	60	54	50	54	49	46	48	45	42	39
5	74	62	54	48	69	59	52	47	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	54	46	41	49	43	38	44	39	36	40	36	33	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	37	33	30	27
8	59	47	39	34	56	45	38	33	41	35	31	37	32	29	34	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	27	24	22
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17623	17623	17623	17623
5°	21007	17698	15584	17698
10°	26230	17596	14080	17596
15°	30788	17416	12840	17416
20°	34360	17148	11786	17148
25°	33812	16865	11137	16865
30°	24304	16604	10470	16604
35°	16227	16264	10038	16264
40°	11956	15855	9591	15855
45°	10029	15139	9155	15139
50°	8848	14200	8544	14200
55°	7760	13127	7707	13127
60°	6910	12099	7061	12099
65°	6069	10998	6569	10998
70°	4765	10014	5998	10014
75°	4196	8746	5481	8746
80°	3651	7426	5387	7426
85°	2939	5965	5718	5965



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.0	2.7
10°-20°	503.0	8.6
20°-30°	790.2	13.5
30°-40°	824.4	14.0
40°-50°	705.6	12.0
50°-60°	537.8	9.2
60°-70°	344.7	5.9
70°-80°	165.8	2.8
80°-90°	45.8	0.8
90°-100°	42.2	0.7
100°-110°	126.2	2.1
110°-120°	214.7	3.7
120°-130°	282.4	4.8
130°-140°	317.5	5.4
140°-150°	312.1	5.3
150°-160°	262.7	4.5
160°-170°	174.9	3.0
170°-180°	61.2	1.0
0°-30°	1454.2	24.8
0°-40°	2278.7	38.8
0°-60°	3522.0	60.0
0°-90°	4078.3	69.5
90°-120°	383.2	6.5
90°-150°	1295.1	22.1
90°-180°	1794.0	30.6
0°-180°	5872.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1637	1637	1637	1637	1637	
5°	1944	1638	1442	1638	1944	201
15°	2763	1563	1152	1563	2763	783
25°	2847	1420	938	1420	2847	1224
35°	1235	1238	764	1238	1235	810
45°	659	994	601	994	659	518
55°	414	700	411	700	414	374
65°	238	432	258	432	238	234
75°	101	210	132	210	101	108
85°	24	48	46	48	24	28
90°	15	0	15	0	15	8
95°	40	30	40	30	40	41
105°	121	114	121	114	121	128
115°	217	216	217	216	217	215
125°	313	316	313	316	313	280
135°	410	410	410	410	410	315
145°	498	498	498	498	498	311
155°	569	570	569	570	569	262
165°	619	621	619	621	619	175
175°	643	646	643	646	643	61
180°	648	648	648	648	648	



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1743.7	1746.0	1738.7	1737.6	1729.1	1726.9	1726.9	1715.1	1707.8	1698.4	1692.7
5°	1944.2	1955.4	1949.8	1937.2	1916.1	1911.2	1897.9	1876.9	1853.1	1823.6	1809.6
7.5°	2194.5	2209.8	2204.0	2184.4	2162.4	2144.7	2107.0	2072.2	2023.2	1980.3	1943.6
10°	2399.8	2383.6	2371.0	2352.1	2331.7	2298.8	2259.6	2205.6	2143.2	2094.2	2039.5
12.5°	2553.3	2550.7	2534.7	2515.2	2486.5	2455.2	2407.0	2341.3	2268.8	2197.9	2135.4
15°	2762.8	2767.0	2756.5	2736.1	2695.5	2640.1	2567.2	2539.9	2436.2	2359.1	2282.0
17.5°	2907.7	2906.9	2905.5	2877.3	2835.8	2796.4	2728.8	2656.9	2563.0	2454.4	2350.5
20°	2999.6	2992.7	2994.1	2962.5	2931.7	2886.1	2820.2	2715.8	2638.8	2513.3	2406.0
22.5°	2997.4	2996.1	3001.3	2990.5	2968.1	2933.2	2881.4	2793.2	2694.8	2568.2	2447.6
25°	2846.9	2841.3	2874.3	2883.3	2919.1	2925.3	2909.9	2861.6	2768.4	2638.0	2488.8
27.5°	2382.7	2379.5	2440.7	2517.2	2614.2	2689.6	2762.5	2797.7	2768.4	2675.0	2525.5
30°	1955.4	2021.2	2052.1	2162.8	2286.2	2433.4	2562.3	2684.9	2715.1	2674.5	2551.8
32.5°	1623.4	1681.0	1706.7	1801.8	1916.7	2089.1	2282.5	2456.2	2578.9	2609.9	2536.1
35°	1234.9	1235.6	1294.5	1336.5	1443.1	1620.4	1808.2	2040.9	2272.2	2447.4	2465.6
37.5°	985.4	988.9	1024.5	1066.4	1146.3	1240.1	1405.5	1598.9	1866.1	2135.1	2292.8
40°	850.9	857.1	883.8	925.1	982.6	1053.4	1182.3	1364.6	1587.4	1886.7	2131.3
42.5°	764.5	774.7	788.5	820.3	855.9	922.2	1026.4	1167.2	1369.9	1652.9	1935.1
45°	658.8	664.4	674.9	689.6	721.8	768.1	838.2	932.8	1101.1	1328.8	1611.2
47.5°	581.1	578.2	589.2	601.2	622.7	654.2	701.2	778.4	898.4	1081.1	1320.7
50°	528.4	527.7	535.5	544.6	564.9	588.0	626.6	684.7	780.1	931.5	1150.8
52.5°	479.1	481.8	487.2	498.6	513.3	532.0	566.6	608.5	690.4	821.0	1003.9
55°	413.5	415.6	423.3	429.6	440.1	459.1	480.8	515.9	571.9	663.0	813.7
57.5°	358.0	357.0	364.4	366.0	377.9	393.3	410.1	437.3	478.0	545.7	647.2
60°	321.0	318.9	325.2	330.1	336.4	349.0	363.0	389.7	422.0	471.7	558.6
62.5°	287.3	286.3	291.0	295.9	301.1	312.5	324.3	344.8	370.3	412.2	481.2
65°	238.3	240.4	242.5	244.6	247.4	254.4	265.6	279.6	297.2	326.6	376.4
67.5°	187.3	189.4	190.1	194.4	200.5	204.8	211.7	224.2	236.3	261.2	289.4
70°	151.4	150.7	151.4	153.5	161.2	168.9	178.0	187.2	194.8	212.3	236.2
72.5°	130.1	128.9	130.6	131.1	134.8	137.0	142.7	151.2	161.2	173.1	190.2
75°	100.9	100.9	100.9	100.9	103.7	105.1	107.3	109.3	112.8	118.4	131.1
77.5°	74.5	74.7	75.7	76.4	77.0	77.8	79.1	81.1	82.4	85.3	90.9
80°	58.9	59.6	58.9	59.6	59.6	61.0	61.7	63.8	64.5	67.9	70.1
82.5°	44.3	43.9	44.3	45.0	45.0	46.4	46.5	48.1	48.2	50.0	52.2
85°	23.8	22.5	23.8	23.1	24.5	23.1	23.8	25.2	25.2	25.9	28.7
87.5°	8.6	9.7	8.6	9.1	9.0	9.5	9.5	9.4	10.3	9.7	10.0
90°	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1	12.7	12.2	10.7
92.5°	20.5	20.7	20.8	21.0	21.1	21.0	20.6	20.2	19.9	19.5	18.7
95°	39.7	39.7	39.7	39.7	39.7	39.4	39.0	38.5	38.1	37.6	36.7
97.5°	61.0	61.1	61.1	61.2	61.2	61.0	60.5	59.9	59.4	58.9	58.2
100°	77.3	77.0	76.9	76.6	76.4	76.2	75.8	75.4	75.1	74.7	74.2
102.5°	94.0	94.1	94.1	94.2	94.2	94.0	93.7	93.4	93.0	92.6	91.9
105°	121.1	120.8	120.6	120.4	120.1	120.0	120.0	120.0	120.0	120.0	119.0
107.5°	149.3	149.4	149.5	149.6	149.8	149.6	149.3	148.9	148.6	148.2	147.8
110°	168.4	168.6	168.8	169.1	169.2	169.2	168.7	168.3	167.8	167.4	167.1



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	188.7	188.8	188.8	188.9	188.9	188.6	188.1	187.5	187.0	186.5	186.5
115°	216.7	216.8	216.9	217.0	217.1	217.1	217.0	216.9	216.8	216.7	216.9
117.5°	245.0	245.4	245.7	246.0	246.3	246.5	246.5	246.6	246.6	246.6	246.9
120°	265.0	265.2	265.5	265.6	265.9	266.1	266.2	266.3	266.4	266.5	267.1
122.5°	284.1	284.5	284.7	285.1	285.3	285.7	286.0	286.2	286.6	286.9	287.1
125°	312.8	313.3	313.7	314.1	314.6	315.0	315.5	315.9	316.4	316.9	317.1
127.5°	341.3	341.9	342.4	343.0	343.5	344.0	344.6	345.3	346.0	346.6	346.8
130°	360.1	360.9	361.7	362.5	363.3	363.9	364.4	364.8	365.2	365.7	366.0
132.5°	379.6	380.2	380.8	381.5	382.1	382.6	383.2	383.7	384.2	384.9	385.0
135°	409.9	410.2	410.4	410.6	410.8	411.2	411.6	412.1	412.6	413.0	413.1
137.5°	436.7	437.1	437.6	438.0	438.5	438.9	439.3	439.8	440.3	440.8	440.5
140°	454.2	455.0	455.8	456.6	457.4	457.8	457.9	458.1	458.2	458.3	458.2
142.5°	472.1	472.7	473.3	473.9	474.6	474.9	475.0	475.1	475.3	475.4	475.2
145°	497.9	498.4	498.8	499.3	499.7	500.1	500.2	500.2	500.3	500.5	500.2
147.5°	520.9	521.7	522.3	523.0	523.6	524.0	524.0	524.0	524.0	524.0	523.7
150°	535.6	536.3	536.9	537.6	538.3	538.6	538.6	538.6	538.6	538.6	538.4
152.5°	549.8	550.5	551.0	551.6	552.1	552.4	552.2	552.1	551.8	551.6	551.5
155°	569.2	570.0	570.7	571.5	572.3	572.5	572.0	571.6	571.1	570.7	570.6
157.5°	586.7	587.4	588.0	588.6	589.2	589.3	588.9	588.4	587.9	587.5	587.4
160°	598.2	598.6	599.1	599.5	599.9	599.9	599.3	598.8	598.2	597.6	597.6
162.5°	606.7	607.4	608.1	608.9	609.6	609.7	609.1	608.5	608.0	607.4	607.3
165°	619.0	619.8	620.5	621.3	622.1	622.2	621.5	620.9	620.2	619.5	619.5
167.5°	629.5	630.2	630.9	631.6	632.3	632.3	631.6	630.9	630.2	629.5	629.4
170°	634.7	635.5	636.3	637.1	637.9	637.9	637.1	636.3	635.5	634.7	634.7
172.5°	638.8	639.6	640.4	641.2	642.0	642.0	641.3	640.6	640.0	639.3	639.3
175°	643.4	644.2	645.0	645.8	646.6	646.7	646.0	645.2	644.6	643.9	643.9
177.5°	645.9	646.5	647.1	647.7	648.4	648.5	647.9	647.4	646.8	646.2	646.2
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1690.5	1688.8	1681.0	1672.0	1660.2	1652.3	1646.2	1642.8	1632.7	1620.4	1611.9
5°	1794.9	1773.9	1751.4	1724.1	1698.9	1672.9	1656.8	1637.9	1614.8	1588.9	1570.7
7.5°	1906.7	1865.5	1821.1	1775.3	1730.0	1689.3	1653.5	1622.7	1585.9	1548.7	1522.7
10°	1992.5	1932.2	1869.9	1806.1	1747.9	1693.3	1651.2	1609.9	1565.8	1523.0	1490.8
12.5°	2070.5	1991.1	1919.2	1840.8	1766.5	1701.1	1640.6	1591.9	1538.8	1493.3	1456.5
15°	2169.2	2087.9	2000.9	1881.8	1783.0	1700.3	1626.7	1562.9	1498.4	1442.3	1406.6
17.5°	2261.4	2139.0	2022.2	1922.9	1794.5	1691.1	1601.3	1525.1	1454.3	1394.8	1350.9
20°	2299.5	2181.0	2054.2	1927.3	1801.2	1685.6	1581.1	1497.0	1423.4	1356.1	1315.5
22.5°	2322.5	2188.3	2054.8	1918.4	1784.4	1664.3	1560.9	1468.5	1388.7	1324.7	1274.6
25°	2349.3	2189.5	2042.3	1907.7	1771.0	1640.7	1518.0	1420.0	1333.7	1265.8	1212.5
27.5°	2367.0	2179.0	2005.0	1855.5	1716.8	1587.0	1474.6	1370.6	1283.2	1211.2	1154.1
30°	2370.3	2170.5	1976.4	1814.5	1673.7	1554.5	1435.4	1335.9	1243.3	1166.9	1113.7
32.5°	2374.8	2149.8	1937.7	1765.8	1621.5	1503.5	1395.5	1300.5	1205.8	1130.5	1076.1
35°	2356.3	2138.3	1879.0	1681.3	1537.0	1422.7	1325.3	1237.7	1144.5	1071.6	1016.3
37.5°	2276.6	2092.8	1818.2	1586.4	1435.4	1329.5	1250.2	1173.8	1088.3	1009.7	957.5
40°	2196.5	2047.9	1771.0	1528.6	1370.9	1262.2	1190.8	1128.4	1045.7	972.1	916.1
42.5°	2077.1	1986.8	1726.2	1468.0	1298.0	1193.3	1133.0	1074.5	1001.9	927.2	874.5
45°	1858.0	1869.9	1634.4	1371.5	1197.0	1091.9	1035.2	994.5	930.1	868.3	814.4
47.5°	1583.2	1694.7	1526.6	1268.8	1090.7	992.0	942.4	906.9	863.4	802.9	753.7
50°	1403.8	1562.9	1440.3	1199.9	1024.0	925.9	876.7	848.0	810.2	762.5	715.6
52.5°	1238.4	1409.3	1336.0	1123.0	951.6	861.9	814.0	790.3	760.3	715.4	673.0
55°	1010.0	1183.0	1166.3	1007.1	843.1	762.5	726.1	699.5	679.1	645.5	611.9
57.5°	816.9	981.1	989.7	878.2	747.5	667.9	636.5	616.4	603.2	577.8	546.7
60°	695.3	846.0	875.4	791.3	679.1	609.0	578.2	562.0	551.6	531.3	507.4
62.5°	594.3	722.6	755.9	695.4	613.5	548.0	523.8	508.3	501.1	483.6	462.5
65°	454.9	561.4	593.6	560.0	517.2	464.7	445.1	431.8	425.4	415.6	400.2
67.5°	342.1	419.6	455.0	431.3	415.9	382.6	370.1	363.0	357.4	350.7	337.8
70°	274.7	332.2	368.6	362.3	349.7	332.2	323.1	318.2	312.5	307.0	295.8
72.5°	220.9	260.5	294.6	297.8	287.5	284.0	276.0	273.9	270.5	263.8	257.6
75°	146.5	173.8	197.6	206.8	211.0	214.5	211.0	210.3	209.6	203.9	200.5
77.5°	96.0	110.8	125.7	141.3	147.8	152.7	153.7	156.3	154.4	151.5	149.8
80°	73.6	77.1	87.6	100.9	111.5	115.7	118.4	119.8	119.1	118.4	115.7
82.5°	53.4	56.4	61.3	70.6	79.5	86.5	88.2	87.9	89.4	89.9	87.6
85°	28.7	29.4	30.9	32.3	37.2	44.9	47.0	48.3	49.8	49.8	45.6
87.5°	10.8	10.0	10.8	10.5	12.0	12.3	15.4	18.0	18.8	16.9	17.0
90°	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5	1.6	2.8	3.9
92.5°	17.8	17.0	16.2	15.4	14.6	13.8	13.1	12.3	13.1	13.8	14.6
95°	35.8	35.0	34.1	33.2	32.4	31.6	30.8	30.1	30.8	31.6	32.4
97.5°	57.6	56.9	56.3	55.6	55.1	54.5	53.9	53.3	53.9	54.5	55.1
100°	73.7	73.0	72.5	71.9	71.2	70.5	69.8	69.2	69.8	70.5	71.2
102.5°	91.2	90.4	89.7	89.1	88.7	88.3	87.9	87.5	87.9	88.3	88.7
105°	118.0	117.0	115.9	115.4	115.1	114.9	114.7	114.4	114.7	114.9	115.1
107.5°	147.4	147.0	146.6	146.3	146.2	146.1	145.9	145.8	145.9	146.1	146.2
110°	166.9	166.7	166.4	166.2	165.9	165.8	165.5	165.3	165.5	165.8	165.9





TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	186.4	186.4	186.3	186.2	186.0	185.9	185.7	185.7	185.7	185.9	186.0
115°	217.1	217.3	217.6	217.5	217.2	216.9	216.5	216.2	216.5	216.9	217.2
117.5°	247.2	247.4	247.7	247.8	247.5	247.4	247.1	246.9	247.1	247.4	247.5
120°	267.7	268.2	268.8	268.8	268.0	267.3	266.7	266.0	266.7	267.3	268.0
122.5°	287.5	287.8	288.0	287.9	287.4	287.0	286.4	286.0	286.4	287.0	287.4
125°	317.4	317.5	317.8	317.7	317.4	317.0	316.7	316.4	316.7	317.0	317.4
127.5°	347.1	347.3	347.6	347.3	346.6	345.9	345.2	344.5	345.2	345.9	346.6
130°	366.4	366.8	367.0	366.8	365.9	365.0	364.1	363.2	364.1	365.0	365.9
132.5°	385.3	385.6	385.8	385.5	384.6	383.7	382.8	381.8	382.8	383.7	384.6
135°	413.2	413.3	413.5	413.1	412.5	411.8	411.2	410.5	411.2	411.8	412.5
137.5°	440.1	439.9	439.6	439.2	438.6	438.0	437.5	436.9	437.5	438.0	438.6
140°	458.1	457.9	457.8	457.4	456.9	456.4	455.8	455.2	455.8	456.4	456.9
142.5°	474.9	474.7	474.6	474.1	473.6	473.1	472.4	471.9	472.4	473.1	473.6
145°	499.8	499.4	499.1	498.8	498.6	498.4	498.2	497.9	498.2	498.4	498.6
147.5°	523.3	523.1	522.7	522.4	521.9	521.6	521.1	520.8	521.1	521.6	521.9
150°	538.1	538.0	537.7	537.5	537.3	537.1	536.8	536.6	536.8	537.1	537.3
152.5°	551.3	551.3	551.1	550.9	550.5	550.3	549.9	549.7	549.9	550.3	550.5
155°	570.4	570.3	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
157.5°	587.3	587.2	587.1	587.1	587.3	587.4	587.5	587.6	587.5	587.4	587.3
160°	597.6	597.6	597.6	597.7	598.0	598.2	598.4	598.6	598.4	598.2	598.0
162.5°	607.3	607.2	607.1	607.2	607.4	607.8	608.1	608.4	608.1	607.8	607.4
165°	619.5	619.5	619.5	619.6	620.0	620.4	620.7	621.0	620.7	620.4	620.0
167.5°	629.3	629.2	629.1	629.3	629.7	630.2	630.6	631.1	630.6	630.2	629.7
170°	634.7	634.7	634.7	635.0	635.4	635.9	636.3	636.8	636.3	635.9	635.4
172.5°	639.3	639.3	639.3	639.4	639.9	640.3	640.8	641.2	640.8	640.3	639.9
175°	643.9	643.9	643.9	644.2	644.6	645.1	645.5	646.0	645.5	645.1	644.6
177.5°	646.2	646.2	646.2	646.4	646.8	647.2	647.6	647.9	647.6	647.2	646.8
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1609.2	1601.9	1596.9	1585.6	1578.3	1570.5	1562.6	1567.7	1567.1	1566.6	1566.6
5°	1555.2	1539.1	1524.4	1505.5	1493.5	1478.8	1467.6	1466.2	1469.0	1459.2	1453.6
7.5°	1501.6	1479.6	1458.7	1437.9	1415.8	1398.1	1387.0	1381.8	1374.7	1368.6	1362.4
10°	1464.1	1438.2	1417.8	1391.9	1368.1	1347.0	1333.7	1324.6	1319.7	1314.8	1305.7
12.5°	1425.4	1400.1	1374.1	1344.8	1322.1	1297.7	1287.7	1277.6	1268.1	1262.7	1250.2
15°	1368.8	1335.9	1308.5	1277.6	1252.4	1228.6	1214.6	1194.3	1191.4	1184.5	1171.8
17.5°	1312.0	1276.2	1238.6	1215.7	1187.2	1162.4	1141.1	1134.3	1114.2	1106.6	1095.7
20°	1267.1	1234.2	1205.5	1175.4	1134.0	1110.9	1094.0	1084.9	1068.8	1059.0	1052.0
22.5°	1228.4	1195.0	1161.7	1126.6	1092.5	1066.6	1054.3	1040.1	1031.3	1017.5	1010.0
25°	1173.2	1136.8	1096.8	1059.0	1034.5	1014.9	995.2	982.6	970.0	963.7	949.7
27.5°	1109.0	1070.9	1033.6	1004.9	974.7	955.4	937.6	926.4	911.2	900.6	892.9
30°	1073.7	1028.9	996.6	970.7	932.1	913.9	900.6	886.6	875.4	864.2	856.5
32.5°	1032.8	991.8	961.3	929.2	899.6	879.7	862.5	850.2	840.6	829.9	822.2
35°	968.6	934.2	902.7	870.5	848.7	828.4	808.1	797.5	788.5	778.6	771.7
37.5°	910.5	878.4	848.5	817.9	790.9	774.5	758.0	750.0	737.7	731.1	724.0
40°	874.7	843.1	810.9	781.5	753.4	740.8	726.1	714.2	702.9	698.0	690.4
42.5°	835.4	803.9	776.7	745.0	722.0	704.9	691.3	678.3	669.9	662.7	658.4
45°	777.2	749.2	722.6	691.1	669.3	654.6	639.2	627.2	619.6	614.7	606.9
47.5°	720.8	692.8	665.7	638.2	617.2	600.4	585.0	576.7	566.4	560.4	555.2
50°	679.8	654.6	625.9	600.7	579.6	562.8	550.2	539.7	530.6	522.8	519.3
52.5°	642.3	615.4	590.6	566.9	544.8	525.8	514.2	503.2	496.3	487.5	483.5
55°	580.3	554.4	533.3	510.2	488.5	472.3	458.3	448.5	441.6	431.8	426.1
57.5°	522.1	498.9	473.8	453.7	431.3	417.7	406.1	392.8	384.2	376.5	371.0
60°	482.9	456.3	434.5	415.6	396.0	378.4	367.9	357.4	348.3	340.6	335.7
62.5°	441.9	418.7	398.1	377.5	359.5	344.3	332.1	323.2	315.2	310.3	305.4
65°	379.2	361.0	339.9	323.1	306.3	295.1	285.3	277.5	272.0	268.4	264.2
67.5°	321.4	303.7	285.3	268.9	257.6	249.1	242.6	236.0	233.3	228.7	226.0
70°	283.8	265.6	249.5	236.9	225.7	219.4	215.2	210.3	207.4	201.9	199.0
72.5°	242.9	229.7	218.1	207.8	198.8	193.1	187.7	181.6	177.2	171.0	168.2
75°	191.4	179.4	170.3	163.3	157.7	150.0	142.3	136.0	133.8	131.8	131.1
77.5°	141.7	134.1	127.5	121.6	114.7	109.1	107.4	105.9	105.6	104.4	104.4
80°	111.5	104.4	99.5	92.5	88.3	88.3	88.3	86.9	87.6	87.6	87.6
82.5°	82.8	76.4	73.7	71.2	70.4	70.9	70.9	71.2	70.8	71.9	71.3
85°	42.7	43.4	44.9	44.1	44.9	44.9	46.3	45.6	46.3	44.9	46.3
87.5°	16.7	18.6	19.5	20.3	21.2	21.0	21.6	21.7	22.3	22.5	22.5
90°	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1	13.6	14.0	14.4
92.5°	15.4	16.2	17.0	17.8	18.7	19.5	19.9	20.2	20.6	21.0	21.1
95°	33.2	34.1	35.0	35.8	36.7	37.6	38.1	38.5	39.0	39.4	39.7
97.5°	55.6	56.3	56.9	57.6	58.2	58.9	59.4	59.9	60.5	61.0	61.2
100°	71.9	72.5	73.0	73.7	74.2	74.7	75.1	75.4	75.8	76.2	76.4
102.5°	89.1	89.7	90.4	91.2	91.9	92.6	93.0	93.4	93.7	94.0	94.2
105°	115.4	115.9	117.0	118.0	119.0	120.0	120.0	120.0	120.0	120.0	120.1
107.5°	146.3	146.6	147.0	147.4	147.8	148.2	148.6	148.9	149.3	149.6	149.8
110°	166.2	166.4	166.7	166.9	167.1	167.4	167.8	168.3	168.7	169.2	169.2



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	186.2	186.3	186.4	186.4	186.5	186.5	187.0	187.5	188.1	188.6	188.9
115°	217.5	217.6	217.3	217.1	216.9	216.7	216.8	216.9	217.0	217.1	217.1
117.5°	247.8	247.7	247.4	247.2	246.9	246.6	246.6	246.6	246.5	246.5	246.3
120°	268.8	268.8	268.2	267.7	267.1	266.5	266.4	266.3	266.2	266.1	265.9
122.5°	287.9	288.0	287.8	287.5	287.1	286.9	286.6	286.2	286.0	285.7	285.3
125°	317.7	317.8	317.5	317.4	317.1	316.9	316.4	315.9	315.5	315.0	314.6
127.5°	347.3	347.6	347.3	347.1	346.8	346.6	346.0	345.3	344.6	344.0	343.5
130°	366.8	367.0	366.8	366.4	366.0	365.7	365.2	364.8	364.4	363.9	363.3
132.5°	385.5	385.8	385.6	385.3	385.0	384.9	384.2	383.7	383.2	382.6	382.1
135°	413.1	413.5	413.3	413.2	413.1	413.0	412.6	412.1	411.6	411.2	410.8
137.5°	439.2	439.6	439.9	440.1	440.5	440.8	440.3	439.8	439.3	438.9	438.5
140°	457.4	457.8	457.9	458.1	458.2	458.3	458.2	458.1	457.9	457.8	457.4
142.5°	474.1	474.6	474.7	474.9	475.2	475.4	475.3	475.1	475.0	474.9	474.6
145°	498.8	499.1	499.4	499.8	500.2	500.5	500.3	500.2	500.2	500.1	499.7
147.5°	522.4	522.7	523.1	523.3	523.7	524.0	524.0	524.0	524.0	524.0	523.6
150°	537.5	537.7	538.0	538.1	538.4	538.6	538.6	538.6	538.6	538.6	538.3
152.5°	550.9	551.1	551.3	551.3	551.5	551.6	551.8	552.1	552.2	552.4	552.1
155°	570.2	570.2	570.3	570.4	570.6	570.7	571.1	571.6	572.0	572.5	572.3
157.5°	587.1	587.1	587.2	587.3	587.4	587.5	587.9	588.4	588.9	589.3	589.2
160°	597.7	597.6	597.6	597.6	597.6	597.6	598.2	598.8	599.3	599.9	599.9
162.5°	607.2	607.1	607.2	607.3	607.3	607.4	608.0	608.5	609.1	609.7	609.6
165°	619.6	619.5	619.5	619.5	619.5	619.5	620.2	620.9	621.5	622.2	622.1
167.5°	629.3	629.1	629.2	629.3	629.4	629.5	630.2	630.9	631.6	632.3	632.3
170°	635.0	634.7	634.7	634.7	634.7	634.7	635.5	636.3	637.1	637.9	637.9
172.5°	639.4	639.3	639.3	639.3	639.3	639.3	640.0	640.6	641.3	642.0	642.0
175°	644.2	643.9	643.9	643.9	643.9	643.9	644.6	645.2	646.0	646.7	646.6
177.5°	646.4	646.2	646.2	646.2	646.2	646.2	646.8	647.4	647.9	648.5	648.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1559.9	1559.2	1559.9	1557.6	1559.9	1559.2	1559.9	1566.6	1566.6	1567.1	1567.7
5°	1451.4	1450.8	1448.7	1442.3	1448.7	1450.8	1451.4	1453.6	1459.2	1469.0	1466.2
7.5°	1356.8	1355.8	1349.7	1349.9	1349.7	1355.8	1356.8	1362.4	1368.6	1374.7	1381.8
10°	1300.8	1301.5	1293.1	1288.2	1293.1	1301.5	1300.8	1305.7	1314.8	1319.7	1324.6
12.5°	1246.4	1243.2	1236.4	1231.0	1236.4	1243.2	1246.4	1250.2	1262.7	1268.1	1277.6
15°	1174.7	1167.6	1150.8	1152.2	1150.8	1167.6	1174.7	1171.8	1184.5	1191.4	1194.3
17.5°	1090.1	1084.9	1084.7	1074.9	1084.7	1084.9	1090.1	1095.7	1106.6	1114.2	1134.3
20°	1040.8	1037.2	1038.7	1028.9	1038.7	1037.2	1040.8	1052.0	1059.0	1068.8	1084.9
22.5°	1002.1	998.5	992.7	989.6	992.7	998.5	1002.1	1010.0	1017.5	1031.3	1040.1
25°	945.5	939.9	934.2	937.7	934.2	939.9	945.5	949.7	963.7	970.0	982.6
27.5°	888.9	884.7	879.0	878.3	879.0	884.7	888.9	892.9	900.6	911.2	926.4
30°	852.9	848.7	846.0	842.4	846.0	848.7	852.9	856.5	864.2	875.4	886.6
32.5°	816.5	815.6	810.7	809.9	810.7	815.6	816.5	822.2	829.9	840.6	850.2
35°	768.8	764.6	763.2	763.9	763.2	764.6	768.8	771.7	778.6	788.5	797.5
37.5°	723.5	717.9	715.4	712.9	715.4	717.9	723.5	724.0	731.1	737.7	750.0
40°	691.1	685.5	684.0	682.6	684.0	685.5	691.1	690.4	698.0	702.9	714.2
42.5°	654.6	652.4	651.5	649.0	651.5	652.4	654.6	658.4	662.7	669.9	678.3
45°	604.8	604.1	599.9	601.4	599.9	604.1	604.8	606.9	614.7	619.6	627.2
47.5°	552.4	549.3	546.4	548.3	546.4	549.3	552.4	555.2	560.4	566.4	576.7
50°	516.6	515.1	508.8	510.2	508.8	515.1	516.6	519.3	522.8	530.6	539.7
52.5°	480.6	475.3	473.0	472.1	473.0	475.3	480.6	483.5	487.5	496.3	503.2
55°	421.2	414.9	412.1	410.7	412.1	414.9	421.2	426.1	431.8	441.6	448.5
57.5°	362.9	361.2	359.0	360.5	359.0	361.2	362.9	371.0	376.5	384.2	392.8
60°	328.7	328.7	328.7	328.0	328.7	328.7	328.7	335.7	340.6	348.3	357.4
62.5°	302.4	300.7	300.1	301.1	300.1	300.7	302.4	305.4	310.3	315.2	323.2
65°	262.2	261.4	258.6	257.9	258.6	261.4	262.2	264.2	268.4	272.0	277.5
67.5°	224.2	221.6	220.8	219.8	220.8	221.6	224.2	226.0	228.7	233.3	236.0
70°	195.6	194.1	189.9	190.6	189.9	194.1	195.6	199.0	201.9	207.4	210.3
72.5°	164.7	163.3	162.5	161.5	162.5	163.3	164.7	168.2	171.0	177.2	181.6
75°	130.4	129.7	128.9	131.8	128.9	129.7	130.4	131.1	131.8	133.8	136.0
77.5°	104.4	104.4	104.9	103.7	104.9	104.4	104.4	104.4	104.4	105.6	105.9
80°	87.6	87.6	86.9	86.9	86.9	87.6	87.6	87.6	87.6	87.6	86.9
82.5°	70.3	70.8	71.2	70.1	71.2	70.8	70.3	71.3	71.9	70.8	71.2
85°	46.3	45.6	47.0	46.3	47.0	45.6	46.3	46.3	44.9	46.3	45.6
87.5°	23.6	22.6	22.6	23.3	22.6	22.6	23.6	22.5	22.5	22.3	21.7
90°	14.6	14.8	15.1	15.2	15.1	14.8	14.6	14.4	14.0	13.6	13.1
92.5°	21.0	20.8	20.7	20.5	20.7	20.8	21.0	21.1	21.0	20.6	20.2
95°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.4	39.0	38.5
97.5°	61.2	61.1	61.1	61.0	61.1	61.1	61.2	61.2	61.0	60.5	59.9
100°	76.6	76.9	77.0	77.3	77.0	76.9	76.6	76.4	76.2	75.8	75.4
102.5°	94.2	94.1	94.1	94.0	94.1	94.1	94.2	94.2	94.0	93.7	93.4
105°	120.4	120.6	120.8	121.1	120.8	120.6	120.4	120.1	120.0	120.0	120.0
107.5°	149.6	149.5	149.4	149.3	149.4	149.5	149.6	149.8	149.6	149.3	148.9
110°	169.1	168.8	168.6	168.4	168.6	168.8	169.1	169.2	169.2	168.7	168.3



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	188.9	188.8	188.8	188.7	188.8	188.8	188.9	188.9	188.6	188.1	187.5
115°	217.0	216.9	216.8	216.7	216.8	216.9	217.0	217.1	217.1	217.0	216.9
117.5°	246.0	245.7	245.4	245.0	245.4	245.7	246.0	246.3	246.5	246.5	246.6
120°	265.6	265.5	265.2	265.0	265.2	265.5	265.6	265.9	266.1	266.2	266.3
122.5°	285.1	284.7	284.5	284.1	284.5	284.7	285.1	285.3	285.7	286.0	286.2
125°	314.1	313.7	313.3	312.8	313.3	313.7	314.1	314.6	315.0	315.5	315.9
127.5°	343.0	342.4	341.9	341.3	341.9	342.4	343.0	343.5	344.0	344.6	345.3
130°	362.5	361.7	360.9	360.1	360.9	361.7	362.5	363.3	363.9	364.4	364.8
132.5°	381.5	380.8	380.2	379.6	380.2	380.8	381.5	382.1	382.6	383.2	383.7
135°	410.6	410.4	410.2	409.9	410.2	410.4	410.6	410.8	411.2	411.6	412.1
137.5°	438.0	437.6	437.1	436.7	437.1	437.6	438.0	438.5	438.9	439.3	439.8
140°	456.6	455.8	455.0	454.2	455.0	455.8	456.6	457.4	457.8	457.9	458.1
142.5°	473.9	473.3	472.7	472.1	472.7	473.3	473.9	474.6	474.9	475.0	475.1
145°	499.3	498.8	498.4	497.9	498.4	498.8	499.3	499.7	500.1	500.2	500.2
147.5°	523.0	522.3	521.7	520.9	521.7	522.3	523.0	523.6	524.0	524.0	524.0
150°	537.6	536.9	536.3	535.6	536.3	536.9	537.6	538.3	538.6	538.6	538.6
152.5°	551.6	551.0	550.5	549.8	550.5	551.0	551.6	552.1	552.4	552.2	552.1
155°	571.5	570.7	570.0	569.2	570.0	570.7	571.5	572.3	572.5	572.0	571.6
157.5°	588.6	588.0	587.4	586.7	587.4	588.0	588.6	589.2	589.3	588.9	588.4
160°	599.5	599.1	598.6	598.2	598.6	599.1	599.5	599.9	599.9	599.3	598.8
162.5°	608.9	608.1	607.4	606.7	607.4	608.1	608.9	609.6	609.7	609.1	608.5
165°	621.3	620.5	619.8	619.0	619.8	620.5	621.3	622.1	622.2	621.5	620.9
167.5°	631.6	630.9	630.2	629.5	630.2	630.9	631.6	632.3	632.3	631.6	630.9
170°	637.1	636.3	635.5	634.7	635.5	636.3	637.1	637.9	637.9	637.1	636.3
172.5°	641.2	640.4	639.6	638.8	639.6	640.4	641.2	642.0	642.0	641.3	640.6
175°	645.8	645.0	644.2	643.4	644.2	645.0	645.8	646.6	646.7	646.0	645.2
177.5°	647.7	647.1	646.5	645.9	646.5	647.1	647.7	648.4	648.5	647.9	647.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1562.6	1570.5	1578.3	1585.6	1596.9	1601.9	1609.2	1611.9	1620.4	1632.7	1642.8
5°	1467.6	1478.8	1493.5	1505.5	1524.4	1539.1	1555.2	1570.7	1588.9	1614.8	1637.9
7.5°	1387.0	1398.1	1415.8	1437.9	1458.7	1479.6	1501.6	1522.7	1548.7	1585.9	1622.7
10°	1333.7	1347.0	1368.1	1391.9	1417.8	1438.2	1464.1	1490.8	1523.0	1565.8	1609.9
12.5°	1287.7	1297.7	1322.1	1344.8	1374.1	1400.1	1425.4	1456.5	1493.3	1538.8	1591.9
15°	1214.6	1228.6	1252.4	1277.6	1308.5	1335.9	1368.8	1406.6	1442.3	1498.4	1562.9
17.5°	1141.1	1162.4	1187.2	1215.7	1238.6	1276.2	1312.0	1350.9	1394.8	1454.3	1525.1
20°	1094.0	1110.9	1134.0	1175.4	1205.5	1234.2	1267.1	1315.5	1356.1	1423.4	1497.0
22.5°	1054.3	1066.6	1092.5	1126.6	1161.7	1195.0	1228.4	1274.6	1324.7	1388.7	1468.5
25°	995.2	1014.9	1034.5	1059.0	1096.8	1136.8	1173.2	1212.5	1265.8	1333.7	1420.0
27.5°	937.6	955.4	974.7	1004.9	1033.6	1070.9	1109.0	1154.1	1211.2	1283.2	1370.6
30°	900.6	913.9	932.1	970.7	996.6	1028.9	1073.7	1113.7	1166.9	1243.3	1335.9
32.5°	862.5	879.7	899.6	929.2	961.3	991.8	1032.8	1076.1	1130.5	1205.8	1300.5
35°	808.1	828.4	848.7	870.5	902.7	934.2	968.6	1016.3	1071.6	1144.5	1237.7
37.5°	758.0	774.5	790.9	817.9	848.5	878.4	910.5	957.5	1009.7	1088.3	1173.8
40°	726.1	740.8	753.4	781.5	810.9	843.1	874.7	916.1	972.1	1045.7	1128.4
42.5°	691.3	704.9	722.0	745.0	776.7	803.9	835.4	874.5	927.2	1001.9	1074.5
45°	639.2	654.6	669.3	691.1	722.6	749.2	777.2	814.4	868.3	930.1	994.5
47.5°	585.0	600.4	617.2	638.2	665.7	692.8	720.8	753.7	802.9	863.4	906.9
50°	550.2	562.8	579.6	600.7	625.9	654.6	679.8	715.6	762.5	810.2	848.0
52.5°	514.2	525.8	544.8	566.9	590.6	615.4	642.3	673.0	715.4	760.3	790.3
55°	458.3	472.3	488.5	510.2	533.3	554.4	580.3	611.9	645.5	679.1	699.5
57.5°	406.1	417.7	431.3	453.7	473.8	498.9	522.1	546.7	577.8	603.2	616.4
60°	367.9	378.4	396.0	415.6	434.5	456.3	482.9	507.4	531.3	551.6	562.0
62.5°	332.1	344.3	359.5	377.5	398.1	418.7	441.9	462.5	483.6	501.1	508.3
65°	285.3	295.1	306.3	323.1	339.9	361.0	379.2	400.2	415.6	425.4	431.8
67.5°	242.6	249.1	257.6	268.9	285.3	303.7	321.4	337.8	350.7	357.4	363.0
70°	215.2	219.4	225.7	236.9	249.5	265.6	283.8	295.8	307.0	312.5	318.2
72.5°	187.7	193.1	198.8	207.8	218.1	229.7	242.9	257.6	263.8	270.5	273.9
75°	142.3	150.0	157.7	163.3	170.3	179.4	191.4	200.5	203.9	209.6	210.3
77.5°	107.4	109.1	114.7	121.6	127.5	134.1	141.7	149.8	151.5	154.4	156.3
80°	88.3	88.3	88.3	92.5	99.5	104.4	111.5	115.7	118.4	119.1	119.8
82.5°	70.9	70.9	70.4	71.2	73.7	76.4	82.8	87.6	89.9	89.4	87.9
85°	46.3	44.9	44.9	44.1	44.9	43.4	42.7	45.6	49.8	49.8	48.3
87.5°	21.6	21.0	21.2	20.3	19.5	18.6	16.7	17.0	16.9	18.8	18.0
90°	12.7	12.2	10.7	9.3	7.8	6.3	5.0	3.9	2.8	1.6	0.5
92.5°	19.9	19.5	18.7	17.8	17.0	16.2	15.4	14.6	13.8	13.1	12.3
95°	38.1	37.6	36.7	35.8	35.0	34.1	33.2	32.4	31.6	30.8	30.1
97.5°	59.4	58.9	58.2	57.6	56.9	56.3	55.6	55.1	54.5	53.9	53.3
100°	75.1	74.7	74.2	73.7	73.0	72.5	71.9	71.2	70.5	69.8	69.2
102.5°	93.0	92.6	91.9	91.2	90.4	89.7	89.1	88.7	88.3	87.9	87.5
105°	120.0	120.0	119.0	118.0	117.0	115.9	115.4	115.1	114.9	114.7	114.4
107.5°	148.6	148.2	147.8	147.4	147.0	146.6	146.3	146.2	146.1	145.9	145.8
110°	167.8	167.4	167.1	166.9	166.7	166.4	166.2	165.9	165.8	165.5	165.3



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	187.0	186.5	186.5	186.4	186.4	186.3	186.2	186.0	185.9	185.7	185.7
115°	216.8	216.7	216.9	217.1	217.3	217.6	217.5	217.2	216.9	216.5	216.2
117.5°	246.6	246.6	246.9	247.2	247.4	247.7	247.8	247.5	247.4	247.1	246.9
120°	266.4	266.5	267.1	267.7	268.2	268.8	268.8	268.0	267.3	266.7	266.0
122.5°	286.6	286.9	287.1	287.5	287.8	288.0	287.9	287.4	287.0	286.4	286.0
125°	316.4	316.9	317.1	317.4	317.5	317.8	317.7	317.4	317.0	316.7	316.4
127.5°	346.0	346.6	346.8	347.1	347.3	347.6	347.3	346.6	345.9	345.2	344.5
130°	365.2	365.7	366.0	366.4	366.8	367.0	366.8	365.9	365.0	364.1	363.2
132.5°	384.2	384.9	385.0	385.3	385.6	385.8	385.5	384.6	383.7	382.8	381.8
135°	412.6	413.0	413.1	413.2	413.3	413.5	413.1	412.5	411.8	411.2	410.5
137.5°	440.3	440.8	440.5	440.1	439.9	439.6	439.2	438.6	438.0	437.5	436.9
140°	458.2	458.3	458.2	458.1	457.9	457.8	457.4	456.9	456.4	455.8	455.2
142.5°	475.3	475.4	475.2	474.9	474.7	474.6	474.1	473.6	473.1	472.4	471.9
145°	500.3	500.5	500.2	499.8	499.4	499.1	498.8	498.6	498.4	498.2	497.9
147.5°	524.0	524.0	523.7	523.3	523.1	522.7	522.4	521.9	521.6	521.1	520.8
150°	538.6	538.6	538.4	538.1	538.0	537.7	537.5	537.3	537.1	536.8	536.6
152.5°	551.8	551.6	551.5	551.3	551.3	551.1	550.9	550.5	550.3	549.9	549.7
155°	571.1	570.7	570.6	570.4	570.3	570.2	570.2	570.2	570.2	570.2	570.2
157.5°	587.9	587.5	587.4	587.3	587.2	587.1	587.1	587.3	587.4	587.5	587.6
160°	598.2	597.6	597.6	597.6	597.6	597.6	597.7	598.0	598.2	598.4	598.6
162.5°	608.0	607.4	607.3	607.3	607.2	607.1	607.2	607.4	607.8	608.1	608.4
165°	620.2	619.5	619.5	619.5	619.5	619.5	619.6	620.0	620.4	620.7	621.0
167.5°	630.2	629.5	629.4	629.3	629.2	629.1	629.3	629.7	630.2	630.6	631.1
170°	635.5	634.7	634.7	634.7	634.7	634.7	635.0	635.4	635.9	636.3	636.8
172.5°	640.0	639.3	639.3	639.3	639.3	639.3	639.4	639.9	640.3	640.8	641.2
175°	644.6	643.9	643.9	643.9	643.9	643.9	644.2	644.6	645.1	645.5	646.0
177.5°	646.8	646.2	646.2	646.2	646.2	646.2	646.4	646.8	647.2	647.6	647.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1646.2	1652.3	1660.2	1672.0	1681.0	1688.8	1690.5	1692.7	1698.4	1707.8	1715.1
5°	1656.8	1672.9	1698.9	1724.1	1751.4	1773.9	1794.9	1809.6	1823.6	1853.1	1876.9
7.5°	1653.5	1689.3	1730.0	1775.3	1821.1	1865.5	1906.7	1943.6	1980.3	2023.2	2072.2
10°	1651.2	1693.3	1747.9	1806.1	1869.9	1932.2	1992.5	2039.5	2094.2	2143.2	2205.6
12.5°	1640.6	1701.1	1766.5	1840.8	1919.2	1991.1	2070.5	2135.4	2197.9	2268.8	2341.3
15°	1626.7	1700.3	1783.0	1881.8	2000.9	2087.9	2169.2	2282.0	2359.1	2436.2	2539.9
17.5°	1601.3	1691.1	1794.5	1922.9	2022.2	2139.0	2261.4	2350.5	2454.4	2563.0	2656.9
20°	1581.1	1685.6	1801.2	1927.3	2054.2	2181.0	2299.5	2406.0	2513.3	2638.8	2715.8
22.5°	1560.9	1664.3	1784.4	1918.4	2054.8	2188.3	2322.5	2447.6	2568.2	2694.8	2793.2
25°	1518.0	1640.7	1771.0	1907.7	2042.3	2189.5	2349.3	2488.8	2638.0	2768.4	2861.6
27.5°	1474.6	1587.0	1716.8	1855.5	2005.0	2179.0	2367.0	2525.5	2675.0	2768.4	2797.7
30°	1435.4	1554.5	1673.7	1814.5	1976.4	2170.5	2370.3	2551.8	2674.5	2715.1	2684.9
32.5°	1395.5	1503.5	1621.5	1765.8	1937.7	2149.8	2374.8	2536.1	2609.9	2578.9	2456.2
35°	1325.3	1422.7	1537.0	1681.3	1879.0	2138.3	2356.3	2465.6	2447.4	2272.2	2040.9
37.5°	1250.2	1329.5	1435.4	1586.4	1818.2	2092.8	2276.6	2292.8	2135.1	1866.1	1598.9
40°	1190.8	1262.2	1370.9	1528.6	1771.0	2047.9	2196.5	2131.3	1886.7	1587.4	1364.6
42.5°	1133.0	1193.3	1298.0	1468.0	1726.2	1986.8	2077.1	1935.1	1652.9	1369.9	1167.2
45°	1035.2	1091.9	1197.0	1371.5	1634.4	1869.9	1858.0	1611.2	1328.8	1101.1	932.8
47.5°	942.4	992.0	1090.7	1268.8	1526.6	1694.7	1583.2	1320.7	1081.1	898.4	778.4
50°	876.7	925.9	1024.0	1199.9	1440.3	1562.9	1403.8	1150.8	931.5	780.1	684.7
52.5°	814.0	861.9	951.6	1123.0	1336.0	1409.3	1238.4	1003.9	821.0	690.4	608.5
55°	726.1	762.5	843.1	1007.1	1166.3	1183.0	1010.0	813.7	663.0	571.9	515.9
57.5°	636.5	667.9	747.5	878.2	989.7	981.1	816.9	647.2	545.7	478.0	437.3
60°	578.2	609.0	679.1	791.3	875.4	846.0	695.3	558.6	471.7	422.0	389.7
62.5°	523.8	548.0	613.5	695.4	755.9	722.6	594.3	481.2	412.2	370.3	344.8
65°	445.1	464.7	517.2	560.0	593.6	561.4	454.9	376.4	326.6	297.2	279.6
67.5°	370.1	382.6	415.9	431.3	455.0	419.6	342.1	289.4	261.2	236.3	224.2
70°	323.1	332.2	349.7	362.3	368.6	332.2	274.7	236.2	212.3	194.8	187.2
72.5°	276.0	284.0	287.5	297.8	294.6	260.5	220.9	190.2	173.1	161.2	151.2
75°	211.0	214.5	211.0	206.8	197.6	173.8	146.5	131.1	118.4	112.8	109.3
77.5°	153.7	152.7	147.8	141.3	125.7	110.8	96.0	90.9	85.3	82.4	81.1
80°	118.4	115.7	111.5	100.9	87.6	77.1	73.6	70.1	67.9	64.5	63.8
82.5°	88.2	86.5	79.5	70.6	61.3	56.4	53.4	52.2	50.0	48.2	48.1
85°	47.0	44.9	37.2	32.3	30.9	29.4	28.7	28.7	25.9	25.2	25.2
87.5°	15.4	12.3	12.0	10.5	10.8	10.0	10.8	10.0	9.7	10.3	9.4
90°	1.6	2.8	3.9	5.0	6.3	7.8	9.3	10.7	12.2	12.7	13.1
92.5°	13.1	13.8	14.6	15.4	16.2	17.0	17.8	18.7	19.5	19.9	20.2
95°	30.8	31.6	32.4	33.2	34.1	35.0	35.8	36.7	37.6	38.1	38.5
97.5°	53.9	54.5	55.1	55.6	56.3	56.9	57.6	58.2	58.9	59.4	59.9
100°	69.8	70.5	71.2	71.9	72.5	73.0	73.7	74.2	74.7	75.1	75.4
102.5°	87.9	88.3	88.7	89.1	89.7	90.4	91.2	91.9	92.6	93.0	93.4
105°	114.7	114.9	115.1	115.4	115.9	117.0	118.0	119.0	120.0	120.0	120.0
107.5°	145.9	146.1	146.2	146.3	146.6	147.0	147.4	147.8	148.2	148.6	148.9
110°	165.5	165.8	165.9	166.2	166.4	166.7	166.9	167.1	167.4	167.8	168.3





TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	185.7	185.9	186.0	186.2	186.3	186.4	186.4	186.5	186.5	187.0	187.5
115°	216.5	216.9	217.2	217.5	217.6	217.3	217.1	216.9	216.7	216.8	216.9
117.5°	247.1	247.4	247.5	247.8	247.7	247.4	247.2	246.9	246.6	246.6	246.6
120°	266.7	267.3	268.0	268.8	268.8	268.2	267.7	267.1	266.5	266.4	266.3
122.5°	286.4	287.0	287.4	287.9	288.0	287.8	287.5	287.1	286.9	286.6	286.2
125°	316.7	317.0	317.4	317.7	317.8	317.5	317.4	317.1	316.9	316.4	315.9
127.5°	345.2	345.9	346.6	347.3	347.6	347.3	347.1	346.8	346.6	346.0	345.3
130°	364.1	365.0	365.9	366.8	367.0	366.8	366.4	366.0	365.7	365.2	364.8
132.5°	382.8	383.7	384.6	385.5	385.8	385.6	385.3	385.0	384.9	384.2	383.7
135°	411.2	411.8	412.5	413.1	413.5	413.3	413.2	413.1	413.0	412.6	412.1
137.5°	437.5	438.0	438.6	439.2	439.6	439.9	440.1	440.5	440.8	440.3	439.8
140°	455.8	456.4	456.9	457.4	457.8	457.9	458.1	458.2	458.3	458.2	458.1
142.5°	472.4	473.1	473.6	474.1	474.6	474.7	474.9	475.2	475.4	475.3	475.1
145°	498.2	498.4	498.6	498.8	499.1	499.4	499.8	500.2	500.5	500.3	500.2
147.5°	521.1	521.6	521.9	522.4	522.7	523.1	523.3	523.7	524.0	524.0	524.0
150°	536.8	537.1	537.3	537.5	537.7	538.0	538.1	538.4	538.6	538.6	538.6
152.5°	549.9	550.3	550.5	550.9	551.1	551.3	551.3	551.5	551.6	551.8	552.1
155°	570.2	570.2	570.2	570.2	570.2	570.3	570.4	570.6	570.7	571.1	571.6
157.5°	587.5	587.4	587.3	587.1	587.1	587.2	587.3	587.4	587.5	587.9	588.4
160°	598.4	598.2	598.0	597.7	597.6	597.6	597.6	597.6	597.6	598.2	598.8
162.5°	608.1	607.8	607.4	607.2	607.1	607.2	607.3	607.3	607.4	608.0	608.5
165°	620.7	620.4	620.0	619.6	619.5	619.5	619.5	619.5	619.5	620.2	620.9
167.5°	630.6	630.2	629.7	629.3	629.1	629.2	629.3	629.4	629.5	630.2	630.9
170°	636.3	635.9	635.4	635.0	634.7	634.7	634.7	634.7	634.7	635.5	636.3
172.5°	640.8	640.3	639.9	639.4	639.3	639.3	639.3	639.3	639.3	640.0	640.6
175°	645.5	645.1	644.6	644.2	643.9	643.9	643.9	643.9	643.9	644.6	645.2
177.5°	647.6	647.2	646.8	646.4	646.2	646.2	646.2	646.2	646.2	646.8	647.4
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5	647.5



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2	1637.2
2.5°	1726.9	1726.9	1729.1	1737.6	1738.7	1746.0	1743.7
5°	1897.9	1911.2	1916.1	1937.2	1949.8	1955.4	1944.2
7.5°	2107.0	2144.7	2162.4	2184.4	2204.0	2209.8	2194.5
10°	2259.6	2298.8	2331.7	2352.1	2371.0	2383.6	2399.8
12.5°	2407.0	2455.2	2486.5	2515.2	2534.7	2550.7	2553.3
15°	2567.2	2640.1	2695.5	2736.1	2756.5	2767.0	2762.8
17.5°	2728.8	2796.4	2835.8	2877.3	2905.5	2906.9	2907.7
20°	2820.2	2886.1	2931.7	2962.5	2994.1	2992.7	2999.6
22.5°	2881.4	2933.2	2968.1	2990.5	3001.3	2996.1	2997.4
25°	2909.9	2925.3	2919.1	2883.3	2874.3	2841.3	2846.9
27.5°	2762.5	2689.6	2614.2	2517.2	2440.7	2379.5	2382.7
30°	2562.3	2433.4	2286.2	2162.8	2052.1	2021.2	1955.4
32.5°	2282.5	2089.1	1916.7	1801.8	1706.7	1681.0	1623.4
35°	1808.2	1620.4	1443.1	1336.5	1294.5	1235.6	1234.9
37.5°	1405.5	1240.1	1146.3	1066.4	1024.5	988.9	985.4
40°	1182.3	1053.4	982.6	925.1	883.8	857.1	850.9
42.5°	1026.4	922.2	855.9	820.3	788.5	774.7	764.5
45°	838.2	768.1	721.8	689.6	674.9	664.4	658.8
47.5°	701.2	654.2	622.7	601.2	589.2	578.2	581.1
50°	626.6	588.0	564.9	544.6	535.5	527.7	528.4
52.5°	566.6	532.0	513.3	498.6	487.2	481.8	479.1
55°	480.8	459.1	440.1	429.6	423.3	415.6	413.5
57.5°	410.1	393.3	377.9	366.0	364.4	357.0	358.0
60°	363.0	349.0	336.4	330.1	325.2	318.9	321.0
62.5°	324.3	312.5	301.1	295.9	291.0	286.3	287.3
65°	265.6	254.4	247.4	244.6	242.5	240.4	238.3
67.5°	211.7	204.8	200.5	194.4	190.1	189.4	187.3
70°	178.0	168.9	161.2	153.5	151.4	150.7	151.4
72.5°	142.7	137.0	134.8	131.1	130.6	128.9	130.1
75°	107.3	105.1	103.7	100.9	100.9	100.9	100.9
77.5°	79.1	77.8	77.0	76.4	75.7	74.7	74.5
80°	61.7	61.0	59.6	59.6	58.9	59.6	58.9
82.5°	46.5	46.4	45.0	45.0	44.3	43.9	44.3
85°	23.8	23.1	24.5	23.1	23.8	22.5	23.8
87.5°	9.5	9.5	9.0	9.1	8.6	9.7	8.6
90°	13.6	14.0	14.4	14.6	14.8	15.1	15.2
92.5°	20.6	21.0	21.1	21.0	20.8	20.7	20.5
95°	39.0	39.4	39.7	39.7	39.7	39.7	39.7
97.5°	60.5	61.0	61.2	61.2	61.1	61.1	61.0
100°	75.8	76.2	76.4	76.6	76.9	77.0	77.3
102.5°	93.7	94.0	94.2	94.2	94.1	94.1	94.0
105°	120.0	120.0	120.1	120.4	120.6	120.8	121.1
107.5°	149.3	149.6	149.8	149.6	149.5	149.4	149.3
110°	168.7	169.2	169.2	169.1	168.8	168.6	168.4



TEST NUMBER: P332367-940

CATALOG NUMBER: S123RDIP-S1165D585U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	188.1	188.6	188.9	188.9	188.8	188.8	188.7
115°	217.0	217.1	217.1	217.0	216.9	216.8	216.7
117.5°	246.5	246.5	246.3	246.0	245.7	245.4	245.0
120°	266.2	266.1	265.9	265.6	265.5	265.2	265.0
122.5°	286.0	285.7	285.3	285.1	284.7	284.5	284.1
125°	315.5	315.0	314.6	314.1	313.7	313.3	312.8
127.5°	344.6	344.0	343.5	343.0	342.4	341.9	341.3
130°	364.4	363.9	363.3	362.5	361.7	360.9	360.1
132.5°	383.2	382.6	382.1	381.5	380.8	380.2	379.6
135°	411.6	411.2	410.8	410.6	410.4	410.2	409.9
137.5°	439.3	438.9	438.5	438.0	437.6	437.1	436.7
140°	457.9	457.8	457.4	456.6	455.8	455.0	454.2
142.5°	475.0	474.9	474.6	473.9	473.3	472.7	472.1
145°	500.2	500.1	499.7	499.3	498.8	498.4	497.9
147.5°	524.0	524.0	523.6	523.0	522.3	521.7	520.9
150°	538.6	538.6	538.3	537.6	536.9	536.3	535.6
152.5°	552.2	552.4	552.1	551.6	551.0	550.5	549.8
155°	572.0	572.5	572.3	571.5	570.7	570.0	569.2
157.5°	588.9	589.3	589.2	588.6	588.0	587.4	586.7
160°	599.3	599.9	599.9	599.5	599.1	598.6	598.2
162.5°	609.1	609.7	609.6	608.9	608.1	607.4	606.7
165°	621.5	622.2	622.1	621.3	620.5	619.8	619.0
167.5°	631.6	632.3	632.3	631.6	630.9	630.2	629.5
170°	637.1	637.9	637.9	637.1	636.3	635.5	634.7
172.5°	641.3	642.0	642.0	641.2	640.4	639.6	638.8
175°	646.0	646.7	646.6	645.8	645.0	644.2	643.4
177.5°	647.9	648.5	648.4	647.7	647.1	646.5	645.9
180°	647.5	647.5	647.5	647.5	647.5	647.5	647.5

(END OF REPORT)